

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332407-935

Luminaire Tested: **S123RDIW-S340D1535U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332407-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D1535U935-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5750.9 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332407-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P332407-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29	20				
1	91	87	84	80	81	77	74	72	59	57	55	42	40	39	26	25	25	18				
2	83	76	71	66	73	68	63	59	52	49	46	37	35	33	23	22	21	15				
3	76	67	61	55	67	60	54	50	46	42	39	33	30	28	21	19	18	13				
4	70	60	52	47	61	53	47	42	41	36	33	29	27	24	18	17	16	11				
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10				
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12	9				
7	54	43	35	30	48	38	32	27	30	25	22	21	19	16	14	12	11	8				
8	50	39	31	26	44	35	28	24	27	22	19	20	17	14	13	11	10	7				
9	47	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	7				
10	43	32	25	21	38	29	23	19	22	18	15	17	14	12	11	9	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5044	5044	5044	5044
5°	6013	5065	4460	5065
10°	7507	5037	4030	5037
15°	8811	4985	3675	4985
20°	9835	4907	3373	4907
25°	9678	4827	3188	4827
30°	6955	4753	2997	4753
35°	4644	4654	2872	4654
40°	3421	4539	2746	4539
45°	2871	4332	2620	4332
50°	2534	4064	2445	4064
55°	2222	3757	2205	3757
60°	1978	3462	2019	3462
65°	1737	3148	1880	3148
70°	1363	2867	1718	2867
75°	1198	2504	1568	2504
80°	1048	2126	1543	2126
85°	840	1717	1643	1717



TEST NUMBER: P332407-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.1	0.8
10°-20°	144.0	2.5
20°-30°	226.2	3.9
30°-40°	236.0	4.1
40°-50°	201.9	3.5
50°-60°	153.9	2.7
60°-70°	98.7	1.7
70°-80°	47.5	0.8
80°-90°	17.4	0.3
90°-100°	107.7	1.9
100°-110°	322.3	5.6
110°-120°	548.1	9.5
120°-130°	721.0	12.5
130°-140°	810.4	14.1
140°-150°	796.6	13.9
150°-160°	670.6	11.7
160°-170°	446.4	7.8
170°-180°	156.3	2.7
0°-30°	416.2	7.2
0°-40°	652.2	11.3
0°-60°	1008.0	17.5
0°-90°	1171.6	20.4
90°-120°	978.1	17.0
90°-150°	3306.0	57.5
90°-180°	4579.0	79.6
0°-180°	5750.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	469	469	469	469	469	
5°	556	469	413	469	556	57
15°	791	447	330	447	791	224
25°	815	406	268	406	815	350
35°	353	354	219	354	353	232
45°	189	285	172	285	189	148
55°	118	200	118	200	118	107
65°	68	124	74	124	68	67
75°	29	60	38	60	29	31
85°	7	14	13	14	7	9
90°	39	1	39	1	39	19
95°	101	77	101	77	101	104
105°	309	292	309	292	309	328
115°	553	552	553	552	553	548
125°	798	808	798	808	798	714
135°	1046	1048	1046	1048	1046	805
145°	1271	1271	1271	1271	1271	793
155°	1453	1455	1453	1455	1453	669
165°	1580	1585	1580	1585	1580	446
175°	1642	1649	1642	1649	1642	156
180°	1653	1653	1653	1653	1653	



TEST NUMBER: P332407-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	499.1	499.7	497.7	497.3	494.9	494.3	494.3	490.9	488.8	486.1	484.5
5°	556.5	559.6	558.0	554.5	548.5	547.0	543.2	537.2	530.4	521.9	518.0
7.5°	628.1	632.5	630.8	625.3	618.9	613.8	603.0	593.1	579.1	566.8	556.3
10°	686.8	682.3	678.6	673.2	667.4	658.0	646.7	631.3	613.5	599.3	583.8
12.5°	730.8	730.0	725.5	719.9	711.7	702.7	688.9	670.1	649.4	629.0	611.1
15°	790.7	791.9	788.9	783.2	771.5	755.6	734.8	726.9	697.2	675.2	653.2
17.5°	832.2	832.0	831.6	823.5	811.7	800.4	781.0	760.4	733.6	702.5	672.8
20°	858.6	856.5	857.0	847.9	839.1	826.0	807.2	777.3	755.3	719.4	688.6
22.5°	857.9	857.5	859.0	855.9	849.5	839.6	824.7	799.4	771.3	735.0	700.5
25°	814.9	813.2	822.6	825.3	835.5	837.3	832.8	819.1	792.4	755.0	712.3
27.5°	681.9	681.1	698.5	720.5	748.2	769.8	790.7	800.7	792.4	765.6	722.8
30°	559.6	578.5	587.4	619.1	654.4	696.5	733.4	768.4	777.1	765.4	730.4
32.5°	464.7	481.1	488.5	515.7	548.6	598.0	653.3	703.0	738.1	747.0	725.9
35°	353.4	353.6	370.5	382.5	413.0	463.7	517.5	584.1	650.3	700.5	705.7
37.5°	282.1	283.0	293.3	305.2	328.1	354.9	402.3	457.6	534.1	611.1	656.3
40°	243.5	245.3	253.0	264.8	281.2	301.5	338.4	390.5	454.3	540.0	610.0
42.5°	218.8	221.7	225.7	234.8	245.0	264.0	293.8	334.1	392.1	473.1	553.9
45°	188.6	190.2	193.2	197.4	206.6	219.8	239.9	267.0	315.1	380.3	461.2
47.5°	166.3	165.5	168.7	172.0	178.2	187.3	200.7	222.7	257.1	309.4	378.0
50°	151.3	151.0	153.3	155.8	161.7	168.3	179.3	196.0	223.3	266.6	329.4
52.5°	137.2	137.8	139.5	142.7	146.9	152.2	162.1	174.2	197.6	235.0	287.3
55°	118.4	119.0	121.1	123.0	126.0	131.4	137.6	147.7	163.7	189.8	232.9
57.5°	102.5	102.2	104.3	104.8	108.1	112.5	117.4	125.2	136.8	156.2	185.2
60°	91.9	91.3	93.1	94.5	96.3	99.9	103.9	111.5	120.8	135.0	159.9
62.5°	82.2	82.0	83.3	84.7	86.2	89.5	92.8	98.7	106.0	118.0	137.8
65°	68.2	68.8	69.4	70.0	70.8	72.8	76.0	80.1	85.1	93.5	107.7
67.5°	53.6	54.2	54.4	55.6	57.3	58.6	60.6	64.1	67.7	74.7	82.8
70°	43.3	43.1	43.3	43.9	46.1	48.3	51.0	53.6	55.8	60.8	67.6
72.5°	37.2	36.9	37.4	37.5	38.6	39.2	40.8	43.3	46.1	49.5	54.4
75°	28.8	28.8	28.8	28.8	29.7	30.0	30.7	31.3	32.3	33.9	37.5
77.5°	21.4	21.4	21.7	21.9	22.0	22.3	22.6	23.2	23.6	24.5	26.0
80°	16.9	17.0	16.9	17.0	17.0	17.5	17.7	18.3	18.4	19.5	20.1
82.5°	12.7	12.6	12.7	12.9	12.9	13.3	13.3	13.8	13.8	14.3	14.9
85°	6.8	6.5	6.8	6.6	7.1	6.6	6.8	7.2	7.2	7.4	8.3
87.5°	9.4	9.6	9.1	9.2	9.1	9.0	8.9	8.6	8.7	8.4	7.7
90°	38.9	38.4	37.8	37.2	36.7	35.8	34.6	33.5	32.3	31.2	27.4
92.5°	52.4	52.8	53.1	53.5	53.8	53.6	52.6	51.7	50.8	49.9	47.7
95°	101.3	101.3	101.3	101.3	101.3	100.7	99.5	98.4	97.2	96.1	93.8
97.5°	155.8	155.9	156.0	156.2	156.3	155.7	154.3	153.0	151.7	150.3	148.7
100°	197.3	196.7	196.2	195.6	195.0	194.3	193.5	192.6	191.7	190.9	189.4
102.5°	240.0	240.0	240.1	240.3	240.4	240.0	239.2	238.3	237.5	236.5	234.6
105°	309.0	308.4	307.9	307.3	306.7	306.4	306.4	306.4	306.4	306.4	303.8
107.5°	380.9	381.3	381.6	381.9	382.3	382.0	381.1	380.2	379.3	378.3	377.3
110°	429.7	430.3	430.9	431.4	432.0	431.8	430.6	429.5	428.3	427.1	426.5



TEST NUMBER: P332407-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	481.6	481.8	481.9	482.1	482.2	481.5	480.1	478.7	477.3	476.0	475.9
115°	553.1	553.4	553.7	554.0	554.2	554.2	554.0	553.7	553.4	553.1	553.7
117.5°	625.5	626.4	627.2	627.9	628.8	629.2	629.3	629.3	629.4	629.5	630.2
120°	676.4	677.0	677.6	678.2	678.7	679.2	679.5	679.8	680.0	680.4	681.7
122.5°	725.2	726.1	726.9	727.7	728.5	729.3	730.0	730.7	731.5	732.3	733.1
125°	798.5	799.6	800.8	801.9	803.1	804.3	805.4	806.6	807.7	808.9	809.4
127.5°	871.4	872.8	874.1	875.5	876.8	878.2	879.9	881.5	883.0	884.7	885.4
130°	919.2	921.3	923.3	925.3	927.3	928.9	930.1	931.2	932.4	933.5	934.4
132.5°	969.1	970.6	972.2	973.8	975.3	976.8	978.2	979.6	980.9	982.3	982.9
135°	1046.5	1047.1	1047.6	1048.2	1048.8	1049.6	1050.8	1052.0	1053.1	1054.3	1054.6
137.5°	1114.7	1115.9	1117.0	1118.0	1119.1	1120.3	1121.5	1122.7	1123.9	1125.2	1124.4
140°	1159.4	1161.4	1163.5	1165.4	1167.5	1168.6	1169.0	1169.2	1169.5	1169.8	1169.5
142.5°	1205.1	1206.7	1208.2	1209.8	1211.3	1212.3	1212.5	1212.9	1213.1	1213.4	1212.9
145°	1271.1	1272.2	1273.4	1274.5	1275.7	1276.4	1276.7	1276.9	1277.3	1277.6	1276.7
147.5°	1329.7	1331.5	1333.3	1335.0	1336.7	1337.6	1337.6	1337.6	1337.6	1337.6	1336.7
150°	1367.2	1368.9	1370.6	1372.3	1374.1	1374.9	1374.9	1374.9	1374.9	1374.9	1374.3
152.5°	1403.5	1405.0	1406.5	1408.0	1409.5	1410.1	1409.5	1409.1	1408.7	1408.2	1407.8
155°	1452.9	1454.8	1456.9	1458.9	1460.9	1461.4	1460.2	1459.1	1457.9	1456.7	1456.5
157.5°	1497.8	1499.3	1501.0	1502.6	1504.3	1504.4	1503.2	1502.0	1500.8	1499.6	1499.3
160°	1526.8	1528.0	1529.1	1530.3	1531.5	1531.3	1529.9	1528.4	1527.0	1525.5	1525.5
162.5°	1548.7	1550.5	1552.4	1554.2	1556.1	1556.3	1554.8	1553.3	1552.0	1550.5	1550.2
165°	1580.1	1582.1	1584.2	1586.1	1588.2	1588.3	1586.6	1584.8	1583.1	1581.4	1581.4
167.5°	1606.8	1608.6	1610.4	1612.2	1613.9	1613.9	1612.2	1610.4	1608.6	1606.8	1606.6
170°	1620.3	1622.4	1624.4	1626.4	1628.4	1628.4	1626.4	1624.4	1622.4	1620.3	1620.3
172.5°	1630.7	1632.7	1634.8	1636.8	1638.8	1638.9	1637.1	1635.3	1633.6	1631.8	1631.8
175°	1642.4	1644.4	1646.4	1648.5	1650.5	1650.6	1648.9	1647.2	1645.5	1643.7	1643.7
177.5°	1648.6	1650.3	1651.8	1653.5	1655.1	1655.2	1653.8	1652.4	1651.1	1649.7	1649.7
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332407-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	483.8	483.4	481.1	478.5	475.2	472.9	471.1	470.2	467.3	463.7	461.4
5°	513.8	507.7	501.3	493.4	486.2	478.8	474.2	468.8	462.2	454.8	449.5
7.5°	545.7	533.9	521.2	508.1	495.2	483.5	473.2	464.4	453.9	443.2	435.8
10°	570.3	553.0	535.2	516.9	500.3	484.7	472.6	460.8	448.2	435.9	426.6
12.5°	592.6	569.9	549.3	526.8	505.6	486.9	469.6	455.6	440.4	427.4	416.9
15°	620.9	597.5	572.7	538.6	510.3	486.6	465.5	447.3	428.9	412.8	402.6
17.5°	647.2	612.3	578.8	550.4	513.6	484.1	458.3	436.5	416.2	399.2	386.6
20°	658.1	624.2	588.0	551.6	515.6	482.4	452.5	428.4	407.4	388.1	376.5
22.5°	664.7	626.4	588.1	549.1	510.7	476.3	446.8	420.3	397.4	379.2	364.8
25°	672.4	626.6	584.5	546.0	506.9	469.6	434.5	406.4	381.8	362.3	347.1
27.5°	677.4	623.6	573.9	531.1	491.4	454.3	422.1	392.3	367.2	346.6	330.3
30°	678.4	621.2	565.7	519.4	479.1	444.9	410.8	382.4	355.9	334.0	318.7
32.5°	679.7	615.3	554.6	505.4	464.1	430.3	399.4	372.2	345.1	323.6	308.0
35°	674.4	612.0	537.8	481.2	439.9	407.2	379.4	354.2	327.6	306.7	290.8
37.5°	651.6	599.0	520.4	454.0	410.8	380.6	357.8	336.0	311.5	289.0	274.1
40°	628.7	586.2	506.9	437.5	392.4	361.3	340.8	323.0	299.3	278.2	262.2
42.5°	594.5	568.6	494.0	420.2	371.5	341.6	324.3	307.5	286.8	265.4	250.3
45°	531.8	535.2	467.8	392.5	342.6	312.5	296.3	284.6	266.2	248.6	233.1
47.5°	453.1	485.0	437.0	363.2	312.2	284.0	269.8	259.6	247.1	229.8	215.7
50°	401.8	447.3	412.2	343.5	293.1	265.0	251.0	242.7	231.9	218.3	204.8
52.5°	354.5	403.4	382.4	321.4	272.3	246.7	233.0	226.2	217.6	204.7	192.6
55°	289.0	338.6	333.8	288.3	241.3	218.3	207.8	200.2	194.4	184.8	175.1
57.5°	233.8	280.8	283.3	251.3	214.0	191.1	182.2	176.4	172.6	165.4	156.4
60°	199.0	242.1	250.6	226.4	194.4	174.4	165.5	160.8	157.9	152.1	145.3
62.5°	170.1	206.8	216.4	199.1	175.6	156.8	149.9	145.5	143.4	138.4	132.4
65°	130.2	160.7	169.9	160.3	148.0	133.0	127.3	123.6	121.7	119.0	114.5
67.5°	97.9	120.1	130.3	123.5	119.0	109.5	106.0	103.9	102.3	100.4	96.7
70°	78.6	95.1	105.5	103.8	100.1	95.1	92.5	91.1	89.5	87.8	84.6
72.5°	63.2	74.6	84.3	85.2	82.3	81.3	79.0	78.4	77.4	75.5	73.7
75°	41.9	49.8	56.6	59.2	60.4	61.4	60.4	60.2	60.0	58.4	57.3
77.5°	27.5	31.7	36.0	40.5	42.4	43.7	44.0	44.8	44.2	43.4	42.9
80°	21.1	22.0	25.1	28.8	31.9	33.1	33.9	34.3	34.1	33.9	33.1
82.5°	15.3	16.1	17.6	20.2	22.7	24.7	25.2	25.1	25.6	25.7	25.1
85°	8.3	8.4	8.9	9.2	10.6	12.8	13.4	13.9	14.2	14.2	13.0
87.5°	7.3	6.4	5.9	5.3	5.2	4.8	5.2	5.4	6.1	6.0	6.6
90°	23.7	19.9	16.2	12.8	10.0	7.1	4.2	1.3	4.2	7.1	10.0
92.5°	45.5	43.5	41.3	39.3	37.3	35.3	33.4	31.4	33.4	35.3	37.3
95°	91.4	89.1	86.9	84.7	82.7	80.7	78.6	76.6	78.6	80.7	82.7
97.5°	147.0	145.3	143.6	142.1	140.6	139.1	137.6	136.0	137.6	139.1	140.6
100°	188.0	186.5	185.1	183.5	181.8	180.0	178.3	176.6	178.3	180.0	181.8
102.5°	232.7	230.8	228.9	227.5	226.4	225.4	224.4	223.3	224.4	225.4	226.4
105°	301.2	298.6	296.0	294.5	293.9	293.3	292.7	292.1	292.7	293.3	293.9
107.5°	376.3	375.2	374.2	373.5	373.2	372.8	372.5	372.1	372.5	372.8	373.2
110°	426.0	425.4	424.8	424.3	423.7	423.1	422.6	422.0	422.6	423.1	423.7



TEST NUMBER: P332407-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	475.7	475.6	475.5	475.3	474.9	474.6	474.2	473.9	474.2	474.6	474.9
115°	554.2	554.8	555.4	555.3	554.4	553.5	552.7	551.8	552.7	553.5	554.4
117.5°	630.9	631.7	632.4	632.5	632.0	631.4	630.8	630.3	630.8	631.4	632.0
120°	683.2	684.7	686.1	686.0	684.2	682.5	680.8	679.1	680.8	682.5	684.2
122.5°	733.7	734.5	735.3	735.0	733.7	732.5	731.2	730.0	731.2	732.5	733.7
125°	810.0	810.6	811.1	811.1	810.2	809.3	808.4	807.5	808.4	809.3	810.2
127.5°	886.0	886.6	887.3	886.7	884.8	883.0	881.1	879.3	881.1	883.0	884.8
130°	935.2	936.1	936.9	936.3	933.9	931.6	929.4	927.0	929.4	931.6	933.9
132.5°	983.6	984.2	984.9	984.0	981.7	979.4	977.1	974.8	977.1	979.4	981.7
135°	1054.8	1055.2	1055.4	1054.7	1052.9	1051.2	1049.5	1047.8	1049.5	1051.2	1052.9
137.5°	1123.6	1122.9	1122.1	1121.0	1119.6	1118.2	1116.7	1115.3	1116.7	1118.2	1119.6
140°	1169.2	1169.0	1168.6	1167.8	1166.3	1164.9	1163.5	1162.0	1163.5	1164.9	1166.3
142.5°	1212.4	1211.9	1211.3	1210.4	1208.9	1207.5	1206.0	1204.6	1206.0	1207.5	1208.9
145°	1275.8	1275.0	1274.1	1273.4	1272.8	1272.2	1271.7	1271.1	1271.7	1272.2	1272.8
147.5°	1335.9	1335.2	1334.3	1333.4	1332.4	1331.3	1330.2	1329.2	1330.2	1331.3	1332.4
150°	1373.8	1373.2	1372.6	1372.1	1371.5	1370.9	1370.4	1369.8	1370.4	1370.9	1371.5
152.5°	1407.5	1407.1	1406.8	1406.2	1405.4	1404.6	1403.8	1403.0	1403.8	1404.6	1405.4
155°	1456.1	1455.9	1455.6	1455.4	1455.4	1455.4	1455.4	1455.4	1455.4	1455.4	1455.4
157.5°	1499.1	1498.9	1498.7	1498.7	1499.1	1499.4	1499.8	1500.1	1499.8	1499.4	1499.1
160°	1525.5	1525.5	1525.5	1525.9	1526.4	1527.0	1527.6	1528.2	1527.6	1527.0	1526.4
162.5°	1550.1	1549.8	1549.5	1549.9	1550.7	1551.4	1552.3	1553.1	1552.3	1551.4	1550.7
165°	1581.4	1581.4	1581.4	1581.8	1582.7	1583.6	1584.4	1585.3	1584.4	1583.6	1582.7
167.5°	1606.4	1606.1	1605.9	1606.4	1607.5	1608.7	1609.8	1611.0	1609.8	1608.7	1607.5
170°	1620.3	1620.3	1620.3	1620.9	1622.0	1623.2	1624.4	1625.5	1624.4	1623.2	1622.0
172.5°	1631.8	1631.8	1631.8	1632.4	1633.5	1634.6	1635.8	1636.9	1635.8	1634.6	1633.5
175°	1643.7	1643.7	1643.7	1644.3	1645.5	1646.6	1647.8	1648.9	1647.8	1646.6	1645.5
177.5°	1649.7	1649.7	1649.7	1650.1	1651.1	1652.0	1652.9	1653.8	1652.9	1652.0	1651.1
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332407-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	460.5	458.5	457.0	453.8	451.8	449.5	447.3	448.7	448.5	448.4	448.4
5°	445.1	440.5	436.3	430.8	427.5	423.3	420.1	419.7	420.4	417.7	416.0
7.5°	429.8	423.5	417.5	411.6	405.2	400.1	397.0	395.5	393.5	391.8	389.9
10°	419.0	411.6	405.8	398.4	391.6	385.6	381.8	379.1	377.7	376.3	373.7
12.5°	407.9	400.7	393.3	384.9	378.4	371.4	368.6	365.7	363.0	361.4	357.8
15°	391.8	382.4	374.5	365.7	358.4	351.6	347.7	341.8	341.0	339.0	335.4
17.5°	375.5	365.3	354.5	347.9	339.8	332.7	326.6	324.7	318.9	316.8	313.6
20°	362.7	353.3	345.0	336.4	324.6	318.0	313.1	310.6	305.9	303.1	301.1
22.5°	351.6	342.0	332.5	322.4	312.7	305.2	301.7	297.6	295.2	291.2	289.0
25°	335.8	325.4	313.9	303.1	296.1	290.5	284.8	281.2	277.6	275.8	271.8
27.5°	317.5	306.5	295.8	287.6	279.0	273.5	268.4	265.2	260.8	257.8	255.5
30°	307.3	294.5	285.2	277.8	266.8	261.6	257.8	253.7	250.6	247.4	245.1
32.5°	295.6	283.9	275.2	266.0	257.5	251.8	246.8	243.3	240.6	237.5	235.3
35°	277.2	267.4	258.4	249.2	242.9	237.1	231.3	228.3	225.7	222.8	220.8
37.5°	260.6	251.4	242.8	234.1	226.4	221.6	217.0	214.6	211.1	209.2	207.2
40°	250.4	241.3	232.1	223.7	215.7	212.1	207.8	204.4	201.2	199.8	197.6
42.5°	239.1	230.1	222.3	213.3	206.6	201.7	197.9	194.2	191.7	189.7	188.5
45°	222.5	214.5	206.8	197.8	191.6	187.4	183.0	179.5	177.4	175.9	173.7
47.5°	206.3	198.3	190.5	182.7	176.7	171.9	167.4	165.1	162.1	160.4	158.9
50°	194.6	187.4	179.2	171.9	165.9	161.1	157.5	154.5	151.9	149.6	148.6
52.5°	183.8	176.2	169.0	162.3	155.9	150.5	147.2	144.0	142.1	139.6	138.4
55°	166.1	158.7	152.7	146.0	139.8	135.2	131.2	128.4	126.4	123.6	122.0
57.5°	149.5	142.8	135.6	129.8	123.5	119.6	116.2	112.4	109.9	107.8	106.2
60°	138.2	130.6	124.3	119.0	113.3	108.3	105.3	102.3	99.7	97.5	96.1
62.5°	126.5	119.9	113.9	108.1	102.9	98.5	95.1	92.6	90.2	88.9	87.4
65°	108.5	103.3	97.3	92.5	87.6	84.5	81.6	79.5	77.8	76.8	75.6
67.5°	92.0	87.0	81.7	77.0	73.7	71.3	69.5	67.6	66.7	65.4	64.7
70°	81.3	76.0	71.4	67.8	64.6	62.8	61.6	60.2	59.4	57.8	57.0
72.5°	69.6	65.8	62.4	59.5	56.9	55.3	53.7	52.0	50.7	48.9	48.1
75°	54.8	51.3	48.7	46.8	45.1	43.0	40.7	38.9	38.3	37.7	37.5
77.5°	40.6	38.4	36.5	34.8	32.8	31.3	30.7	30.3	30.2	29.9	29.9
80°	31.9	29.9	28.5	26.5	25.3	25.3	25.3	24.9	25.1	25.1	25.1
82.5°	23.7	21.9	21.1	20.4	20.1	20.3	20.3	20.4	20.2	20.6	20.4
85°	12.2	12.4	12.8	12.7	12.8	12.8	13.3	13.0	13.3	12.8	13.3
87.5°	7.1	8.2	9.1	10.0	10.9	11.5	11.9	12.1	12.6	12.7	12.9
90°	12.8	16.2	19.9	23.7	27.4	31.2	32.3	33.5	34.6	35.8	36.7
92.5°	39.3	41.3	43.5	45.5	47.7	49.9	50.8	51.7	52.6	53.6	53.8
95°	84.7	86.9	89.1	91.4	93.8	96.1	97.2	98.4	99.5	100.7	101.3
97.5°	142.1	143.6	145.3	147.0	148.7	150.3	151.7	153.0	154.3	155.7	156.3
100°	183.5	185.1	186.5	188.0	189.4	190.9	191.7	192.6	193.5	194.3	195.0
102.5°	227.5	228.9	230.8	232.7	234.6	236.5	237.5	238.3	239.2	240.0	240.4
105°	294.5	296.0	298.6	301.2	303.8	306.4	306.4	306.4	306.4	306.4	306.7
107.5°	373.5	374.2	375.2	376.3	377.3	378.3	379.3	380.2	381.1	382.0	382.3
110°	424.3	424.8	425.4	426.0	426.5	427.1	428.3	429.5	430.6	431.8	432.0



TEST NUMBER: P332407-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	475.3	475.5	475.6	475.7	475.9	476.0	477.3	478.7	480.1	481.5	482.2
115°	555.3	555.4	554.8	554.2	553.7	553.1	553.4	553.7	554.0	554.2	554.2
117.5°	632.5	632.4	631.7	630.9	630.2	629.5	629.4	629.3	629.3	629.2	628.8
120°	686.0	686.1	684.7	683.2	681.7	680.4	680.0	679.8	679.5	679.2	678.7
122.5°	735.0	735.3	734.5	733.7	733.1	732.3	731.5	730.7	730.0	729.3	728.5
125°	811.1	811.1	810.6	810.0	809.4	808.9	807.7	806.6	805.4	804.3	803.1
127.5°	886.7	887.3	886.6	886.0	885.4	884.7	883.0	881.5	879.9	878.2	876.8
130°	936.3	936.9	936.1	935.2	934.4	933.5	932.4	931.2	930.1	928.9	927.3
132.5°	984.0	984.9	984.2	983.6	982.9	982.3	980.9	979.6	978.2	976.8	975.3
135°	1054.7	1055.4	1055.2	1054.8	1054.6	1054.3	1053.1	1052.0	1050.8	1049.6	1048.8
137.5°	1121.0	1122.1	1122.9	1123.6	1124.4	1125.2	1123.9	1122.7	1121.5	1120.3	1119.1
140°	1167.8	1168.6	1169.0	1169.2	1169.5	1169.8	1169.5	1169.2	1169.0	1168.6	1167.5
142.5°	1210.4	1211.3	1211.9	1212.4	1212.9	1213.4	1213.1	1212.9	1212.5	1212.3	1211.3
145°	1273.4	1274.1	1275.0	1275.8	1276.7	1277.6	1277.3	1276.9	1276.7	1276.4	1275.7
147.5°	1333.4	1334.3	1335.2	1335.9	1336.7	1337.6	1337.6	1337.6	1337.6	1337.6	1336.7
150°	1372.1	1372.6	1373.2	1373.8	1374.3	1374.9	1374.9	1374.9	1374.9	1374.9	1374.1
152.5°	1406.2	1406.8	1407.1	1407.5	1407.8	1408.2	1408.7	1409.1	1409.5	1410.1	1409.5
155°	1455.4	1455.6	1455.9	1456.1	1456.5	1456.7	1457.9	1459.1	1460.2	1461.4	1460.9
157.5°	1498.7	1498.7	1498.9	1499.1	1499.3	1499.6	1500.8	1502.0	1503.2	1504.4	1504.3
160°	1525.9	1525.5	1525.5	1525.5	1525.5	1525.5	1527.0	1528.4	1529.9	1531.3	1531.5
162.5°	1549.9	1549.5	1549.8	1550.1	1550.2	1550.5	1552.0	1553.3	1554.8	1556.3	1556.1
165°	1581.8	1581.4	1581.4	1581.4	1581.4	1581.4	1583.1	1584.8	1586.6	1588.3	1588.2
167.5°	1606.4	1605.9	1606.1	1606.4	1606.6	1606.8	1608.6	1610.4	1612.2	1613.9	1613.9
170°	1620.9	1620.3	1620.3	1620.3	1620.3	1620.3	1622.4	1624.4	1626.4	1628.4	1628.4
172.5°	1632.4	1631.8	1631.8	1631.8	1631.8	1631.8	1633.6	1635.3	1637.1	1638.9	1638.8
175°	1644.3	1643.7	1643.7	1643.7	1643.7	1643.7	1645.5	1647.2	1648.9	1650.6	1650.5
177.5°	1650.1	1649.7	1649.7	1649.7	1649.7	1649.7	1651.1	1652.4	1653.8	1655.2	1655.1
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332407-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	446.4	446.3	446.4	445.8	446.4	446.3	446.4	448.4	448.4	448.5	448.7
5°	415.4	415.3	414.7	412.8	414.7	415.3	415.4	416.0	417.7	420.4	419.7
7.5°	388.3	388.1	386.3	386.3	386.3	388.1	388.3	389.9	391.8	393.5	395.5
10°	372.3	372.5	370.1	368.7	370.1	372.5	372.3	373.7	376.3	377.7	379.1
12.5°	356.7	355.9	353.9	352.3	353.9	355.9	356.7	357.8	361.4	363.0	365.7
15°	336.2	334.2	329.4	329.8	329.4	334.2	336.2	335.4	339.0	341.0	341.8
17.5°	312.0	310.6	310.5	307.6	310.5	310.6	312.0	313.6	316.8	318.9	324.7
20°	297.9	296.9	297.3	294.5	297.3	296.9	297.9	301.1	303.1	305.9	310.6
22.5°	286.8	285.8	284.1	283.3	284.1	285.8	286.8	289.0	291.2	295.2	297.6
25°	270.6	269.0	267.4	268.4	267.4	269.0	270.6	271.8	275.8	277.6	281.2
27.5°	254.4	253.2	251.6	251.4	251.6	253.2	254.4	255.5	257.8	260.8	265.2
30°	244.1	242.9	242.1	241.1	242.1	242.9	244.1	245.1	247.4	250.6	253.7
32.5°	233.7	233.4	232.0	231.8	232.0	233.4	233.7	235.3	237.5	240.6	243.3
35°	220.1	218.9	218.4	218.6	218.4	218.9	220.1	220.8	222.8	225.7	228.3
37.5°	207.1	205.5	204.7	204.1	204.7	205.5	207.1	207.2	209.2	211.1	214.6
40°	197.8	196.2	195.8	195.4	195.8	196.2	197.8	197.6	199.8	201.2	204.4
42.5°	187.4	186.8	186.5	185.7	186.5	186.8	187.4	188.5	189.7	191.7	194.2
45°	173.1	172.9	171.7	172.1	171.7	172.9	173.1	173.7	175.9	177.4	179.5
47.5°	158.1	157.2	156.4	157.0	156.4	157.2	158.1	158.9	160.4	162.1	165.1
50°	147.8	147.4	145.6	146.0	145.6	147.4	147.8	148.6	149.6	151.9	154.5
52.5°	137.6	136.0	135.3	135.1	135.3	136.0	137.6	138.4	139.6	142.1	144.0
55°	120.5	118.7	118.0	117.5	118.0	118.7	120.5	122.0	123.6	126.4	128.4
57.5°	103.8	103.4	102.7	103.1	102.7	103.4	103.8	106.2	107.8	109.9	112.4
60°	94.1	94.1	94.1	93.8	94.1	94.1	94.1	96.1	97.5	99.7	102.3
62.5°	86.5	86.0	85.9	86.2	85.9	86.0	86.5	87.4	88.9	90.2	92.6
65°	75.0	74.8	74.0	73.8	74.0	74.8	75.0	75.6	76.8	77.8	79.5
67.5°	64.1	63.5	63.2	62.9	63.2	63.5	64.1	64.7	65.4	66.7	67.6
70°	56.0	55.5	54.3	54.6	54.3	55.5	56.0	57.0	57.8	59.4	60.2
72.5°	47.2	46.8	46.5	46.2	46.5	46.8	47.2	48.1	48.9	50.7	52.0
75°	37.3	37.1	36.9	37.7	36.9	37.1	37.3	37.5	37.7	38.3	38.9
77.5°	29.9	29.9	30.0	29.7	30.0	29.9	29.9	29.9	29.9	30.2	30.3
80°	25.1	25.1	24.9	24.9	24.9	25.1	25.1	25.1	25.1	25.1	24.9
82.5°	20.1	20.2	20.4	20.1	20.4	20.2	20.1	20.4	20.6	20.2	20.4
85°	13.3	13.0	13.4	13.3	13.4	13.0	13.3	13.3	12.8	13.3	13.0
87.5°	13.3	13.2	13.3	13.6	13.3	13.2	13.3	12.9	12.7	12.6	12.1
90°	37.2	37.8	38.4	38.9	38.4	37.8	37.2	36.7	35.8	34.6	33.5
92.5°	53.5	53.1	52.8	52.4	52.8	53.1	53.5	53.8	53.6	52.6	51.7
95°	101.3	101.3	101.3	101.3	101.3	101.3	101.3	101.3	100.7	99.5	98.4
97.5°	156.2	156.0	155.9	155.8	155.9	156.0	156.2	156.3	155.7	154.3	153.0
100°	195.6	196.2	196.7	197.3	196.7	196.2	195.6	195.0	194.3	193.5	192.6
102.5°	240.3	240.1	240.0	240.0	240.0	240.1	240.3	240.4	240.0	239.2	238.3
105°	307.3	307.9	308.4	309.0	308.4	307.9	307.3	306.7	306.4	306.4	306.4
107.5°	381.9	381.6	381.3	380.9	381.3	381.6	381.9	382.3	382.0	381.1	380.2
110°	431.4	430.9	430.3	429.7	430.3	430.9	431.4	432.0	431.8	430.6	429.5



TEST NUMBER: P332407-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	482.1	481.9	481.8	481.6	481.8	481.9	482.1	482.2	481.5	480.1	478.7
115°	554.0	553.7	553.4	553.1	553.4	553.7	554.0	554.2	554.2	554.0	553.7
117.5°	627.9	627.2	626.4	625.5	626.4	627.2	627.9	628.8	629.2	629.3	629.3
120°	678.2	677.6	677.0	676.4	677.0	677.6	678.2	678.7	679.2	679.5	679.8
122.5°	727.7	726.9	726.1	725.2	726.1	726.9	727.7	728.5	729.3	730.0	730.7
125°	801.9	800.8	799.6	798.5	799.6	800.8	801.9	803.1	804.3	805.4	806.6
127.5°	875.5	874.1	872.8	871.4	872.8	874.1	875.5	876.8	878.2	879.9	881.5
130°	925.3	923.3	921.3	919.2	921.3	923.3	925.3	927.3	928.9	930.1	931.2
132.5°	973.8	972.2	970.6	969.1	970.6	972.2	973.8	975.3	976.8	978.2	979.6
135°	1048.2	1047.6	1047.1	1046.5	1047.1	1047.6	1048.2	1048.8	1049.6	1050.8	1052.0
137.5°	1118.0	1117.0	1115.9	1114.7	1115.9	1117.0	1118.0	1119.1	1120.3	1121.5	1122.7
140°	1165.4	1163.5	1161.4	1159.4	1161.4	1163.5	1165.4	1167.5	1168.6	1169.0	1169.2
142.5°	1209.8	1208.2	1206.7	1205.1	1206.7	1208.2	1209.8	1211.3	1212.3	1212.5	1212.9
145°	1274.5	1273.4	1272.2	1271.1	1272.2	1273.4	1274.5	1275.7	1276.4	1276.7	1276.9
147.5°	1335.0	1333.3	1331.5	1329.7	1331.5	1333.3	1335.0	1336.7	1337.6	1337.6	1337.6
150°	1372.3	1370.6	1368.9	1367.2	1368.9	1370.6	1372.3	1374.1	1374.9	1374.9	1374.9
152.5°	1408.0	1406.5	1405.0	1403.5	1405.0	1406.5	1408.0	1409.5	1410.1	1409.5	1409.1
155°	1458.9	1456.9	1454.8	1452.9	1454.8	1456.9	1458.9	1460.9	1461.4	1460.2	1459.1
157.5°	1502.6	1501.0	1499.3	1497.8	1499.3	1501.0	1502.6	1504.3	1504.4	1503.2	1502.0
160°	1530.3	1529.1	1528.0	1526.8	1528.0	1529.1	1530.3	1531.5	1531.3	1529.9	1528.4
162.5°	1554.2	1552.4	1550.5	1548.7	1550.5	1552.4	1554.2	1556.1	1556.3	1554.8	1553.3
165°	1586.1	1584.2	1582.1	1580.1	1582.1	1584.2	1586.1	1588.2	1588.3	1586.6	1584.8
167.5°	1612.2	1610.4	1608.6	1606.8	1608.6	1610.4	1612.2	1613.9	1613.9	1612.2	1610.4
170°	1626.4	1624.4	1622.4	1620.3	1622.4	1624.4	1626.4	1628.4	1628.4	1626.4	1624.4
172.5°	1636.8	1634.8	1632.7	1630.7	1632.7	1634.8	1636.8	1638.8	1638.9	1637.1	1635.3
175°	1648.5	1646.4	1644.4	1642.4	1644.4	1646.4	1648.5	1650.5	1650.6	1648.9	1647.2
177.5°	1653.5	1651.8	1650.3	1648.6	1650.3	1651.8	1653.5	1655.1	1655.2	1653.8	1652.4
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332407-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	447.3	449.5	451.8	453.8	457.0	458.5	460.5	461.4	463.7	467.3	470.2
5°	420.1	423.3	427.5	430.8	436.3	440.5	445.1	449.5	454.8	462.2	468.8
7.5°	397.0	400.1	405.2	411.6	417.5	423.5	429.8	435.8	443.2	453.9	464.4
10°	381.8	385.6	391.6	398.4	405.8	411.6	419.0	426.6	435.9	448.2	460.8
12.5°	368.6	371.4	378.4	384.9	393.3	400.7	407.9	416.9	427.4	440.4	455.6
15°	347.7	351.6	358.4	365.7	374.5	382.4	391.8	402.6	412.8	428.9	447.3
17.5°	326.6	332.7	339.8	347.9	354.5	365.3	375.5	386.6	399.2	416.2	436.5
20°	313.1	318.0	324.6	336.4	345.0	353.3	362.7	376.5	388.1	407.4	428.4
22.5°	301.7	305.2	312.7	322.4	332.5	342.0	351.6	364.8	379.2	397.4	420.3
25°	284.8	290.5	296.1	303.1	313.9	325.4	335.8	347.1	362.3	381.8	406.4
27.5°	268.4	273.5	279.0	287.6	295.8	306.5	317.5	330.3	346.6	367.2	392.3
30°	257.8	261.6	266.8	277.8	285.2	294.5	307.3	318.7	334.0	355.9	382.4
32.5°	246.8	251.8	257.5	266.0	275.2	283.9	295.6	308.0	323.6	345.1	372.2
35°	231.3	237.1	242.9	249.2	258.4	267.4	277.2	290.8	306.7	327.6	354.2
37.5°	217.0	221.6	226.4	234.1	242.8	251.4	260.6	274.1	289.0	311.5	336.0
40°	207.8	212.1	215.7	223.7	232.1	241.3	250.4	262.2	278.2	299.3	323.0
42.5°	197.9	201.7	206.6	213.3	222.3	230.1	239.1	250.3	265.4	286.8	307.5
45°	183.0	187.4	191.6	197.8	206.8	214.5	222.5	233.1	248.6	266.2	284.6
47.5°	167.4	171.9	176.7	182.7	190.5	198.3	206.3	215.7	229.8	247.1	259.6
50°	157.5	161.1	165.9	171.9	179.2	187.4	194.6	204.8	218.3	231.9	242.7
52.5°	147.2	150.5	155.9	162.3	169.0	176.2	183.8	192.6	204.7	217.6	226.2
55°	131.2	135.2	139.8	146.0	152.7	158.7	166.1	175.1	184.8	194.4	200.2
57.5°	116.2	119.6	123.5	129.8	135.6	142.8	149.5	156.4	165.4	172.6	176.4
60°	105.3	108.3	113.3	119.0	124.3	130.6	138.2	145.3	152.1	157.9	160.8
62.5°	95.1	98.5	102.9	108.1	113.9	119.9	126.5	132.4	138.4	143.4	145.5
65°	81.6	84.5	87.6	92.5	97.3	103.3	108.5	114.5	119.0	121.7	123.6
67.5°	69.5	71.3	73.7	77.0	81.7	87.0	92.0	96.7	100.4	102.3	103.9
70°	61.6	62.8	64.6	67.8	71.4	76.0	81.3	84.6	87.8	89.5	91.1
72.5°	53.7	55.3	56.9	59.5	62.4	65.8	69.6	73.7	75.5	77.4	78.4
75°	40.7	43.0	45.1	46.8	48.7	51.3	54.8	57.3	58.4	60.0	60.2
77.5°	30.7	31.3	32.8	34.8	36.5	38.4	40.6	42.9	43.4	44.2	44.8
80°	25.3	25.3	25.3	26.5	28.5	29.9	31.9	33.1	33.9	34.1	34.3
82.5°	20.3	20.3	20.1	20.4	21.1	21.9	23.7	25.1	25.7	25.6	25.1
85°	13.3	12.8	12.8	12.7	12.8	12.4	12.2	13.0	14.2	14.2	13.9
87.5°	11.9	11.5	10.9	10.0	9.1	8.2	7.1	6.6	6.0	6.1	5.4
90°	32.3	31.2	27.4	23.7	19.9	16.2	12.8	10.0	7.1	4.2	1.3
92.5°	50.8	49.9	47.7	45.5	43.5	41.3	39.3	37.3	35.3	33.4	31.4
95°	97.2	96.1	93.8	91.4	89.1	86.9	84.7	82.7	80.7	78.6	76.6
97.5°	151.7	150.3	148.7	147.0	145.3	143.6	142.1	140.6	139.1	137.6	136.0
100°	191.7	190.9	189.4	188.0	186.5	185.1	183.5	181.8	180.0	178.3	176.6
102.5°	237.5	236.5	234.6	232.7	230.8	228.9	227.5	226.4	225.4	224.4	223.3
105°	306.4	306.4	303.8	301.2	298.6	296.0	294.5	293.9	293.3	292.7	292.1
107.5°	379.3	378.3	377.3	376.3	375.2	374.2	373.5	373.2	372.8	372.5	372.1
110°	428.3	427.1	426.5	426.0	425.4	424.8	424.3	423.7	423.1	422.6	422.0



TEST NUMBER: P332407-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	477.3	476.0	475.9	475.7	475.6	475.5	475.3	474.9	474.6	474.2	473.9
115°	553.4	553.1	553.7	554.2	554.8	555.4	555.3	554.4	553.5	552.7	551.8
117.5°	629.4	629.5	630.2	630.9	631.7	632.4	632.5	632.0	631.4	630.8	630.3
120°	680.0	680.4	681.7	683.2	684.7	686.1	686.0	684.2	682.5	680.8	679.1
122.5°	731.5	732.3	733.1	733.7	734.5	735.3	735.0	733.7	732.5	731.2	730.0
125°	807.7	808.9	809.4	810.0	810.6	811.1	811.1	810.2	809.3	808.4	807.5
127.5°	883.0	884.7	885.4	886.0	886.6	887.3	886.7	884.8	883.0	881.1	879.3
130°	932.4	933.5	934.4	935.2	936.1	936.9	936.3	933.9	931.6	929.4	927.0
132.5°	980.9	982.3	982.9	983.6	984.2	984.9	984.0	981.7	979.4	977.1	974.8
135°	1053.1	1054.3	1054.6	1054.8	1055.2	1055.4	1054.7	1052.9	1051.2	1049.5	1047.8
137.5°	1123.9	1125.2	1124.4	1123.6	1122.9	1122.1	1121.0	1119.6	1118.2	1116.7	1115.3
140°	1169.5	1169.8	1169.5	1169.2	1169.0	1168.6	1167.8	1166.3	1164.9	1163.5	1162.0
142.5°	1213.1	1213.4	1212.9	1212.4	1211.9	1211.3	1210.4	1208.9	1207.5	1206.0	1204.6
145°	1277.3	1277.6	1276.7	1275.8	1275.0	1274.1	1273.4	1272.8	1272.2	1271.7	1271.1
147.5°	1337.6	1337.6	1336.7	1335.9	1335.2	1334.3	1333.4	1332.4	1331.3	1330.2	1329.2
150°	1374.9	1374.9	1374.3	1373.8	1373.2	1372.6	1372.1	1371.5	1370.9	1370.4	1369.8
152.5°	1408.7	1408.2	1407.8	1407.5	1407.1	1406.8	1406.2	1405.4	1404.6	1403.8	1403.0
155°	1457.9	1456.7	1456.5	1456.1	1455.9	1455.6	1455.4	1455.4	1455.4	1455.4	1455.4
157.5°	1500.8	1499.6	1499.3	1499.1	1498.9	1498.7	1498.7	1499.1	1499.4	1499.8	1500.1
160°	1527.0	1525.5	1525.5	1525.5	1525.5	1525.5	1525.9	1526.4	1527.0	1527.6	1528.2
162.5°	1552.0	1550.5	1550.2	1550.1	1549.8	1549.5	1549.9	1550.7	1551.4	1552.3	1553.1
165°	1583.1	1581.4	1581.4	1581.4	1581.4	1581.4	1581.8	1582.7	1583.6	1584.4	1585.3
167.5°	1608.6	1606.8	1606.6	1606.4	1606.1	1605.9	1606.4	1607.5	1608.7	1609.8	1611.0
170°	1622.4	1620.3	1620.3	1620.3	1620.3	1620.3	1620.9	1622.0	1623.2	1624.4	1625.5
172.5°	1633.6	1631.8	1631.8	1631.8	1631.8	1631.8	1632.4	1633.5	1634.6	1635.8	1636.9
175°	1645.5	1643.7	1643.7	1643.7	1643.7	1643.7	1644.3	1645.5	1646.6	1647.8	1648.9
177.5°	1651.1	1649.7	1649.7	1649.7	1649.7	1649.7	1650.1	1651.1	1652.0	1652.9	1653.8
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332407-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	471.1	472.9	475.2	478.5	481.1	483.4	483.8	484.5	486.1	488.8	490.9
5°	474.2	478.8	486.2	493.4	501.3	507.7	513.8	518.0	521.9	530.4	537.2
7.5°	473.2	483.5	495.2	508.1	521.2	533.9	545.7	556.3	566.8	579.1	593.1
10°	472.6	484.7	500.3	516.9	535.2	553.0	570.3	583.8	599.3	613.5	631.3
12.5°	469.6	486.9	505.6	526.8	549.3	569.9	592.6	611.1	629.0	649.4	670.1
15°	465.5	486.6	510.3	538.6	572.7	597.5	620.9	653.2	675.2	697.2	726.9
17.5°	458.3	484.1	513.6	550.4	578.8	612.3	647.2	672.8	702.5	733.6	760.4
20°	452.5	482.4	515.6	551.6	588.0	624.2	658.1	688.6	719.4	755.3	777.3
22.5°	446.8	476.3	510.7	549.1	588.1	626.4	664.7	700.5	735.0	771.3	799.4
25°	434.5	469.6	506.9	546.0	584.5	626.6	672.4	712.3	755.0	792.4	819.1
27.5°	422.1	454.3	491.4	531.1	573.9	623.6	677.4	722.8	765.6	792.4	800.7
30°	410.8	444.9	479.1	519.4	565.7	621.2	678.4	730.4	765.4	777.1	768.4
32.5°	399.4	430.3	464.1	505.4	554.6	615.3	679.7	725.9	747.0	738.1	703.0
35°	379.4	407.2	439.9	481.2	537.8	612.0	674.4	705.7	700.5	650.3	584.1
37.5°	357.8	380.6	410.8	454.0	520.4	599.0	651.6	656.3	611.1	534.1	457.6
40°	340.8	361.3	392.4	437.5	506.9	586.2	628.7	610.0	540.0	454.3	390.5
42.5°	324.3	341.6	371.5	420.2	494.0	568.6	594.5	553.9	473.1	392.1	334.1
45°	296.3	312.5	342.6	392.5	467.8	535.2	531.8	461.2	380.3	315.1	267.0
47.5°	269.8	284.0	312.2	363.2	437.0	485.0	453.1	378.0	309.4	257.1	222.7
50°	251.0	265.0	293.1	343.5	412.2	447.3	401.8	329.4	266.6	223.3	196.0
52.5°	233.0	246.7	272.3	321.4	382.4	403.4	354.5	287.3	235.0	197.6	174.2
55°	207.8	218.3	241.3	288.3	333.8	338.6	289.0	232.9	189.8	163.7	147.7
57.5°	182.2	191.1	214.0	251.3	283.3	280.8	233.8	185.2	156.2	136.8	125.2
60°	165.5	174.4	194.4	226.4	250.6	242.1	199.0	159.9	135.0	120.8	111.5
62.5°	149.9	156.8	175.6	199.1	216.4	206.8	170.1	137.8	118.0	106.0	98.7
65°	127.3	133.0	148.0	160.3	169.9	160.7	130.2	107.7	93.5	85.1	80.1
67.5°	106.0	109.5	119.0	123.5	130.3	120.1	97.9	82.8	74.7	67.7	64.1
70°	92.5	95.1	100.1	103.8	105.5	95.1	78.6	67.6	60.8	55.8	53.6
72.5°	79.0	81.3	82.3	85.2	84.3	74.6	63.2	54.4	49.5	46.1	43.3
75°	60.4	61.4	60.4	59.2	56.6	49.8	41.9	37.5	33.9	32.3	31.3
77.5°	44.0	43.7	42.4	40.5	36.0	31.7	27.5	26.0	24.5	23.6	23.2
80°	33.9	33.1	31.9	28.8	25.1	22.0	21.1	20.1	19.5	18.4	18.3
82.5°	25.2	24.7	22.7	20.2	17.6	16.1	15.3	14.9	14.3	13.8	13.8
85°	13.4	12.8	10.6	9.2	8.9	8.4	8.3	8.3	7.4	7.2	7.2
87.5°	5.2	4.8	5.2	5.3	5.9	6.4	7.3	7.7	8.4	8.7	8.6
90°	4.2	7.1	10.0	12.8	16.2	19.9	23.7	27.4	31.2	32.3	33.5
92.5°	33.4	35.3	37.3	39.3	41.3	43.5	45.5	47.7	49.9	50.8	51.7
95°	78.6	80.7	82.7	84.7	86.9	89.1	91.4	93.8	96.1	97.2	98.4
97.5°	137.6	139.1	140.6	142.1	143.6	145.3	147.0	148.7	150.3	151.7	153.0
100°	178.3	180.0	181.8	183.5	185.1	186.5	188.0	189.4	190.9	191.7	192.6
102.5°	224.4	225.4	226.4	227.5	228.9	230.8	232.7	234.6	236.5	237.5	238.3
105°	292.7	293.3	293.9	294.5	296.0	298.6	301.2	303.8	306.4	306.4	306.4
107.5°	372.5	372.8	373.2	373.5	374.2	375.2	376.3	377.3	378.3	379.3	380.2
110°	422.6	423.1	423.7	424.3	424.8	425.4	426.0	426.5	427.1	428.3	429.5



TEST NUMBER: P332407-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	474.2	474.6	474.9	475.3	475.5	475.6	475.7	475.9	476.0	477.3	478.7
115°	552.7	553.5	554.4	555.3	555.4	554.8	554.2	553.7	553.1	553.4	553.7
117.5°	630.8	631.4	632.0	632.5	632.4	631.7	630.9	630.2	629.5	629.4	629.3
120°	680.8	682.5	684.2	686.0	686.1	684.7	683.2	681.7	680.4	680.0	679.8
122.5°	731.2	732.5	733.7	735.0	735.3	734.5	733.7	733.1	732.3	731.5	730.7
125°	808.4	809.3	810.2	811.1	811.1	810.6	810.0	809.4	808.9	807.7	806.6
127.5°	881.1	883.0	884.8	886.7	887.3	886.6	886.0	885.4	884.7	883.0	881.5
130°	929.4	931.6	933.9	936.3	936.9	936.1	935.2	934.4	933.5	932.4	931.2
132.5°	977.1	979.4	981.7	984.0	984.9	984.2	983.6	982.9	982.3	980.9	979.6
135°	1049.5	1051.2	1052.9	1054.7	1055.4	1055.2	1054.8	1054.6	1054.3	1053.1	1052.0
137.5°	1116.7	1118.2	1119.6	1121.0	1122.1	1122.9	1123.6	1124.4	1125.2	1123.9	1122.7
140°	1163.5	1164.9	1166.3	1167.8	1168.6	1169.0	1169.2	1169.5	1169.8	1169.5	1169.2
142.5°	1206.0	1207.5	1208.9	1210.4	1211.3	1211.9	1212.4	1212.9	1213.4	1213.1	1212.9
145°	1271.7	1272.2	1272.8	1273.4	1274.1	1275.0	1275.8	1276.7	1277.6	1277.3	1276.9
147.5°	1330.2	1331.3	1332.4	1333.4	1334.3	1335.2	1335.9	1336.7	1337.6	1337.6	1337.6
150°	1370.4	1370.9	1371.5	1372.1	1372.6	1373.2	1373.8	1374.3	1374.9	1374.9	1374.9
152.5°	1403.8	1404.6	1405.4	1406.2	1406.8	1407.1	1407.5	1407.8	1408.2	1408.7	1409.1
155°	1455.4	1455.4	1455.4	1455.4	1455.6	1455.9	1456.1	1456.5	1456.7	1457.9	1459.1
157.5°	1499.8	1499.4	1499.1	1498.7	1498.7	1498.9	1499.1	1499.3	1499.6	1500.8	1502.0
160°	1527.6	1527.0	1526.4	1525.9	1525.5	1525.5	1525.5	1525.5	1525.5	1527.0	1528.4
162.5°	1552.3	1551.4	1550.7	1549.9	1549.5	1549.8	1550.1	1550.2	1550.5	1552.0	1553.3
165°	1584.4	1583.6	1582.7	1581.8	1581.4	1581.4	1581.4	1581.4	1581.4	1583.1	1584.8
167.5°	1609.8	1608.7	1607.5	1606.4	1605.9	1606.1	1606.4	1606.6	1606.8	1608.6	1610.4
170°	1624.4	1623.2	1622.0	1620.9	1620.3	1620.3	1620.3	1620.3	1620.3	1622.4	1624.4
172.5°	1635.8	1634.6	1633.5	1632.4	1631.8	1631.8	1631.8	1631.8	1631.8	1633.6	1635.3
175°	1647.8	1646.6	1645.5	1644.3	1643.7	1643.7	1643.7	1643.7	1643.7	1645.5	1647.2
177.5°	1652.9	1652.0	1651.1	1650.1	1649.7	1649.7	1649.7	1649.7	1649.7	1651.1	1652.4
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332407-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	494.3	494.3	494.9	497.3	497.7	499.7	499.1
5°	543.2	547.0	548.5	554.5	558.0	559.6	556.5
7.5°	603.0	613.8	618.9	625.3	630.8	632.5	628.1
10°	646.7	658.0	667.4	673.2	678.6	682.3	686.8
12.5°	688.9	702.7	711.7	719.9	725.5	730.0	730.8
15°	734.8	755.6	771.5	783.2	788.9	791.9	790.7
17.5°	781.0	800.4	811.7	823.5	831.6	832.0	832.2
20°	807.2	826.0	839.1	847.9	857.0	856.5	858.6
22.5°	824.7	839.6	849.5	855.9	859.0	857.5	857.9
25°	832.8	837.3	835.5	825.3	822.6	813.2	814.9
27.5°	790.7	769.8	748.2	720.5	698.5	681.1	681.9
30°	733.4	696.5	654.4	619.1	587.4	578.5	559.6
32.5°	653.3	598.0	548.6	515.7	488.5	481.1	464.7
35°	517.5	463.7	413.0	382.5	370.5	353.6	353.4
37.5°	402.3	354.9	328.1	305.2	293.3	283.0	282.1
40°	338.4	301.5	281.2	264.8	253.0	245.3	243.5
42.5°	293.8	264.0	245.0	234.8	225.7	221.7	218.8
45°	239.9	219.8	206.6	197.4	193.2	190.2	188.6
47.5°	200.7	187.3	178.2	172.0	168.7	165.5	166.3
50°	179.3	168.3	161.7	155.8	153.3	151.0	151.3
52.5°	162.1	152.2	146.9	142.7	139.5	137.8	137.2
55°	137.6	131.4	126.0	123.0	121.1	119.0	118.4
57.5°	117.4	112.5	108.1	104.8	104.3	102.2	102.5
60°	103.9	99.9	96.3	94.5	93.1	91.3	91.9
62.5°	92.8	89.5	86.2	84.7	83.3	82.0	82.2
65°	76.0	72.8	70.8	70.0	69.4	68.8	68.2
67.5°	60.6	58.6	57.3	55.6	54.4	54.2	53.6
70°	51.0	48.3	46.1	43.9	43.3	43.1	43.3
72.5°	40.8	39.2	38.6	37.5	37.4	36.9	37.2
75°	30.7	30.0	29.7	28.8	28.8	28.8	28.8
77.5°	22.6	22.3	22.0	21.9	21.7	21.4	21.4
80°	17.7	17.5	17.0	17.0	16.9	17.0	16.9
82.5°	13.3	13.3	12.9	12.9	12.7	12.6	12.7
85°	6.8	6.6	7.1	6.6	6.8	6.5	6.8
87.5°	8.9	9.0	9.1	9.2	9.1	9.6	9.4
90°	34.6	35.8	36.7	37.2	37.8	38.4	38.9
92.5°	52.6	53.6	53.8	53.5	53.1	52.8	52.4
95°	99.5	100.7	101.3	101.3	101.3	101.3	101.3
97.5°	154.3	155.7	156.3	156.2	156.0	155.9	155.8
100°	193.5	194.3	195.0	195.6	196.2	196.7	197.3
102.5°	239.2	240.0	240.4	240.3	240.1	240.0	240.0
105°	306.4	306.4	306.7	307.3	307.9	308.4	309.0
107.5°	381.1	382.0	382.3	381.9	381.6	381.3	380.9
110°	430.6	431.8	432.0	431.4	430.9	430.3	429.7



TEST NUMBER: P332407-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	480.1	481.5	482.2	482.1	481.9	481.8	481.6
115°	554.0	554.2	554.2	554.0	553.7	553.4	553.1
117.5°	629.3	629.2	628.8	627.9	627.2	626.4	625.5
120°	679.5	679.2	678.7	678.2	677.6	677.0	676.4
122.5°	730.0	729.3	728.5	727.7	726.9	726.1	725.2
125°	805.4	804.3	803.1	801.9	800.8	799.6	798.5
127.5°	879.9	878.2	876.8	875.5	874.1	872.8	871.4
130°	930.1	928.9	927.3	925.3	923.3	921.3	919.2
132.5°	978.2	976.8	975.3	973.8	972.2	970.6	969.1
135°	1050.8	1049.6	1048.8	1048.2	1047.6	1047.1	1046.5
137.5°	1121.5	1120.3	1119.1	1118.0	1117.0	1115.9	1114.7
140°	1169.0	1168.6	1167.5	1165.4	1163.5	1161.4	1159.4
142.5°	1212.5	1212.3	1211.3	1209.8	1208.2	1206.7	1205.1
145°	1276.7	1276.4	1275.7	1274.5	1273.4	1272.2	1271.1
147.5°	1337.6	1337.6	1336.7	1335.0	1333.3	1331.5	1329.7
150°	1374.9	1374.9	1374.1	1372.3	1370.6	1368.9	1367.2
152.5°	1409.5	1410.1	1409.5	1408.0	1406.5	1405.0	1403.5
155°	1460.2	1461.4	1460.9	1458.9	1456.9	1454.8	1452.9
157.5°	1503.2	1504.4	1504.3	1502.6	1501.0	1499.3	1497.8
160°	1529.9	1531.3	1531.5	1530.3	1529.1	1528.0	1526.8
162.5°	1554.8	1556.3	1556.1	1554.2	1552.4	1550.5	1548.7
165°	1586.6	1588.3	1588.2	1586.1	1584.2	1582.1	1580.1
167.5°	1612.2	1613.9	1613.9	1612.2	1610.4	1608.6	1606.8
170°	1626.4	1628.4	1628.4	1626.4	1624.4	1622.4	1620.3
172.5°	1637.1	1638.9	1638.8	1636.8	1634.8	1632.7	1630.7
175°	1648.9	1650.6	1650.5	1648.5	1646.4	1644.4	1642.4
177.5°	1653.8	1655.2	1655.1	1653.5	1651.8	1650.3	1648.6
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8

(END OF REPORT)