

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332409-935

Luminaire Tested: **S123RDIW-S340D1535U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332409-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S340D1535U935-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5701.7 lumens  
Efficiency: N/A  
Efficacy: 106.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332409-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332409-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	47	47	47	28	28	28	20
1	91	87	83	80	80	77	74	71	58	56	55	41	40	39	25	25	24	17
2	83	76	70	65	73	67	63	59	51	48	45	36	34	33	22	21	20	14
3	76	67	60	55	67	59	54	49	45	41	38	32	30	28	20	19	17	12
4	69	59	52	46	61	52	46	41	40	36	32	28	26	24	18	16	15	11
5	63	52	45	39	56	47	40	35	36	31	28	26	23	20	16	14	13	9
6	58	47	39	34	51	42	35	31	32	28	24	23	20	18	14	13	12	8
7	54	42	35	29	47	38	31	27	29	24	21	21	18	16	13	12	10	7
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	12	10	9	7
9	46	35	28	23	41	31	25	21	24	20	17	17	14	12	11	10	8	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	10	9	8	5

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5324	5324	5324
5°	5344	5271	5302
10°	5314	5205	5187
15°	5258	5084	5029
20°	5179	4931	4816
25°	5099	4760	4608
30°	4992	4561	4313
35°	4882	4365	4043
40°	4780	4131	3710
45°	4647	3902	3408
50°	4501	3641	3069
55°	4352	3342	2755
60°	4215	3023	2409
65°	4037	2677	2063
70°	3811	2247	1668
75°	3489	1768	1568
80°	3106	1568	1438
85°	2631	1383	1284



TEST NUMBER: P332409-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.5	0.8
10°-20°	129.2	2.3
20°-30°	186.1	3.3
30°-40°	209.6	3.7
40°-50°	200.5	3.5
50°-60°	164.2	2.9
60°-70°	110.8	1.9
70°-80°	55.7	1.0
80°-90°	19.6	0.3
90°-100°	107.7	1.9
100°-110°	322.3	5.7
110°-120°	548.1	9.6
120°-130°	721.0	12.6
130°-140°	810.4	14.2
140°-150°	796.6	14.0
150°-160°	670.6	11.8
160°-170°	446.4	7.8
170°-180°	156.3	2.7
0°-30°	361.8	6.3
0°-40°	571.4	10.0
0°-60°	936.2	16.4
0°-90°	1122.4	19.7
90°-120°	978.1	17.2
90°-150°	3306.0	58.0
90°-180°	4579.0	80.3
0°-180°	5701.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	495	495	495	495	495	
5°	495	492	488	491	491	47
15°	472	467	456	454	451	133
25°	429	419	401	393	388	197
35°	372	356	332	315	308	232
45°	305	286	256	234	224	235
55°	232	211	178	156	147	208
65°	158	136	105	86	81	157
75°	84	64	42	39	38	89
85°	21	13	11	10	10	24
90°	1	14	31	36	39	6
95°	77	86	96	101	101	86
105°	292	295	306	307	309	313
115°	552	555	553	554	553	546
125°	808	811	809	804	798	720
135°	1048	1055	1054	1049	1046	807
145°	1271	1274	1278	1276	1271	794
155°	1455	1456	1457	1461	1453	670
165°	1585	1582	1581	1588	1580	447
175°	1649	1644	1644	1651	1642	157
180°	1653	1653	1653	1653	1653	



TEST NUMBER: P332409-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	496.3	495.9	495.7	495.4	495.2	494.6	493.7	492.8	492.0	491.1	491.9
5°	494.6	494.2	493.8	493.4	492.8	492.1	491.0	490.0	488.9	487.8	488.6
7.5°	490.1	489.6	489.1	488.6	488.2	487.2	485.9	484.5	483.0	481.6	482.1
10°	486.2	485.6	485.0	484.4	483.7	482.6	481.0	479.4	477.8	476.2	476.3
12.5°	480.8	480.1	479.4	478.7	478.0	476.6	474.7	472.8	470.8	468.8	468.7
15°	471.8	470.8	469.8	468.8	467.9	466.1	463.6	461.2	458.7	456.2	455.7
17.5°	460.5	459.3	458.2	457.0	455.9	453.7	450.6	447.4	444.3	441.1	440.1
20°	452.1	450.7	449.3	447.9	446.4	444.0	440.7	437.2	433.9	430.5	429.3
22.5°	442.8	441.2	439.5	437.9	436.3	433.7	430.1	426.5	422.8	419.2	417.8
25°	429.3	427.1	424.8	422.6	420.3	417.2	413.1	409.0	404.8	400.8	398.9
27.5°	412.8	410.4	407.9	405.4	402.9	399.5	394.9	390.3	385.7	381.2	378.6
30°	401.6	398.9	396.2	393.6	390.9	387.0	382.0	377.0	372.0	367.0	364.0
32.5°	390.4	387.3	384.3	381.3	378.2	374.1	368.8	363.5	358.3	352.9	349.7
35°	371.5	368.2	365.1	361.9	358.7	354.3	348.8	343.2	337.7	332.2	328.4
37.5°	352.4	348.8	345.3	341.7	338.1	333.4	327.5	321.6	315.7	309.8	305.5
40°	340.2	336.3	332.3	328.5	324.5	319.3	313.1	306.7	300.4	294.0	289.5
42.5°	326.4	322.4	318.6	314.6	310.7	305.5	298.9	292.4	285.9	279.3	274.2
45°	305.3	301.3	297.3	293.3	289.2	283.8	277.0	270.1	263.2	256.3	251.2
47.5°	284.2	279.8	275.3	271.0	266.6	261.0	254.1	247.2	240.4	233.5	228.0
50°	268.8	264.6	260.5	256.2	252.0	246.3	239.1	231.9	224.6	217.4	211.9
52.5°	255.0	250.5	245.9	241.3	236.8	230.9	223.8	216.6	209.5	202.3	196.7
55°	231.9	227.5	223.2	218.8	214.4	208.4	200.9	193.3	185.7	178.1	173.0
57.5°	210.5	205.8	201.0	196.2	191.5	185.3	177.7	170.0	162.5	154.9	150.0
60°	195.8	190.9	186.0	181.1	176.2	170.0	162.6	155.2	147.8	140.4	135.6
62.5°	181.0	176.1	171.2	166.3	161.4	155.2	147.8	140.4	133.0	125.6	121.1
65°	158.5	153.6	148.7	143.8	138.9	132.9	126.0	119.0	112.1	105.1	100.7
67.5°	136.0	131.0	126.0	121.1	116.1	110.3	103.6	96.9	90.2	83.6	80.3
70°	121.1	116.3	111.5	106.7	101.9	96.3	90.1	83.9	77.7	71.4	68.3
72.5°	106.4	101.7	96.9	92.1	87.4	82.2	76.5	70.9	65.2	59.5	57.0
75°	83.9	79.6	75.3	71.0	66.7	62.2	57.3	52.3	47.4	42.5	41.7
77.5°	63.3	59.4	55.5	51.7	47.9	44.3	41.2	38.0	34.9	31.7	31.3
80°	50.1	46.5	42.9	39.2	35.6	32.8	30.9	29.0	27.1	25.3	25.0
82.5°	37.6	34.4	31.3	28.2	25.0	23.0	22.1	21.3	20.4	19.5	19.2
85°	21.3	19.3	17.3	15.4	13.4	12.3	12.1	11.8	11.5	11.2	11.0
87.5°	7.9	7.7	7.6	7.3	7.1	7.4	8.2	8.9	9.6	10.4	10.6
90°	1.3	4.2	7.1	10.0	12.8	16.2	19.9	23.7	27.4	31.2	32.3
92.5°	31.4	33.4	35.3	37.3	39.3	41.3	43.5	45.5	47.7	49.9	50.8
95°	76.6	78.6	80.7	82.7	84.7	86.9	89.1	91.4	93.8	96.1	97.2
97.5°	136.0	137.6	139.1	140.6	142.1	143.6	145.3	147.0	148.7	150.3	151.7
100°	176.6	178.3	180.0	181.8	183.5	185.1	186.5	188.0	189.4	190.9	191.7
102.5°	223.3	224.4	225.4	226.4	227.5	228.9	230.8	232.7	234.6	236.5	237.5
105°	292.1	292.7	293.3	293.9	294.5	296.0	298.6	301.2	303.8	306.4	306.4
107.5°	372.1	372.5	372.8	373.2	373.5	374.2	375.2	376.3	377.3	378.3	379.3
110°	422.0	422.6	423.1	423.7	424.3	424.8	425.4	426.0	426.5	427.1	428.3



TEST NUMBER: P332409-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	473.9	474.2	474.6	474.9	475.3	475.5	475.6	475.7	475.9	476.0	477.3
115°	551.8	552.7	553.5	554.4	555.3	555.4	554.8	554.2	553.7	553.1	553.4
117.5°	630.3	630.8	631.4	632.0	632.5	632.4	631.7	630.9	630.2	629.5	629.4
120°	679.1	680.8	682.5	684.2	686.0	686.1	684.7	683.2	681.7	680.4	680.0
122.5°	730.0	731.2	732.5	733.7	735.0	735.3	734.5	733.7	733.1	732.3	731.5
125°	807.5	808.4	809.3	810.2	811.1	811.1	810.6	810.0	809.4	808.9	807.7
127.5°	879.3	881.1	883.0	884.8	886.7	887.3	886.6	886.0	885.4	884.7	883.0
130°	927.0	929.4	931.6	933.9	936.3	936.9	936.1	935.2	934.4	933.5	932.4
132.5°	974.8	977.1	979.4	981.7	984.0	984.9	984.2	983.6	982.9	982.3	980.9
135°	1047.8	1049.5	1051.2	1052.9	1054.7	1055.4	1055.2	1054.8	1054.6	1054.3	1053.1
137.5°	1115.3	1116.7	1118.2	1119.6	1121.0	1122.1	1122.9	1123.6	1124.4	1125.2	1123.9
140°	1162.0	1163.5	1164.9	1166.3	1167.8	1168.6	1169.0	1169.2	1169.5	1169.8	1169.5
142.5°	1204.6	1206.0	1207.5	1208.9	1210.4	1211.3	1211.9	1212.4	1212.9	1213.4	1213.1
145°	1271.1	1271.7	1272.2	1272.8	1273.4	1274.1	1275.0	1275.8	1276.7	1277.6	1277.3
147.5°	1329.2	1330.2	1331.3	1332.4	1333.4	1334.3	1335.2	1335.9	1336.7	1337.6	1337.6
150°	1369.8	1370.4	1370.9	1371.5	1372.1	1372.6	1373.2	1373.8	1374.3	1374.9	1374.9
152.5°	1403.0	1403.8	1404.6	1405.4	1406.2	1406.8	1407.1	1407.5	1407.8	1408.2	1408.7
155°	1455.4	1455.4	1455.4	1455.4	1455.4	1455.6	1455.9	1456.1	1456.5	1456.7	1457.9
157.5°	1500.1	1499.8	1499.4	1499.1	1498.7	1498.7	1498.9	1499.1	1499.3	1499.6	1500.8
160°	1528.2	1527.6	1527.0	1526.4	1525.9	1525.5	1525.5	1525.5	1525.5	1525.5	1527.0
162.5°	1553.1	1552.3	1551.4	1550.7	1549.9	1549.5	1549.8	1550.1	1550.2	1550.5	1552.0
165°	1585.3	1584.4	1583.6	1582.7	1581.8	1581.4	1581.4	1581.4	1581.4	1581.4	1583.1
167.5°	1611.0	1609.8	1608.7	1607.5	1606.4	1605.9	1606.1	1606.4	1606.6	1606.8	1608.6
170°	1625.5	1624.4	1623.2	1622.0	1620.9	1620.3	1620.3	1620.3	1620.3	1620.3	1622.4
172.5°	1636.9	1635.8	1634.6	1633.5	1632.4	1631.8	1631.8	1631.8	1631.8	1631.8	1633.6
175°	1648.9	1647.8	1646.6	1645.5	1644.3	1643.7	1643.7	1643.7	1643.7	1643.7	1645.5
177.5°	1653.8	1652.9	1652.0	1651.1	1650.1	1649.7	1649.7	1649.7	1649.7	1649.7	1651.1
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332409-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	492.7	493.4	494.3	494.6	494.5	494.3	494.1	494.0
5°	489.5	490.3	491.0	491.4	491.2	491.0	490.9	490.7
7.5°	482.6	483.0	483.5	483.5	483.2	482.9	482.6	482.3
10°	476.4	476.5	476.6	476.4	476.0	475.5	475.0	474.6
12.5°	468.7	468.6	468.6	468.3	467.8	467.3	466.7	466.2
15°	455.2	454.8	454.3	453.8	453.2	452.5	451.9	451.3
17.5°	439.2	438.2	437.3	436.4	435.4	434.5	433.6	432.7
20°	428.2	427.0	425.9	424.7	423.6	422.6	421.5	420.4
22.5°	416.4	414.9	413.5	412.2	411.2	410.3	409.2	408.3
25°	397.0	395.2	393.3	391.8	390.9	389.9	388.9	388.0
27.5°	376.0	373.4	370.8	368.8	367.2	365.8	364.3	362.7
30°	361.0	358.0	355.0	352.8	351.3	349.9	348.4	347.0
32.5°	346.3	343.0	339.7	337.3	335.8	334.3	332.8	331.3
35°	324.5	320.6	316.8	314.1	312.5	310.9	309.3	307.7
37.5°	301.1	296.7	292.4	289.2	287.2	285.2	283.3	281.3
40°	284.8	280.2	275.5	272.2	270.1	268.1	266.0	264.0
42.5°	269.1	264.2	259.1	255.6	253.7	251.9	250.1	248.2
45°	246.2	241.1	236.0	232.4	230.3	228.2	226.0	223.9
47.5°	222.4	216.9	211.4	207.7	205.8	203.9	201.9	200.0
50°	206.4	200.9	195.4	191.6	189.5	187.4	185.4	183.3
52.5°	190.9	185.1	179.4	175.6	173.7	171.9	170.1	168.2
55°	167.8	162.6	157.5	153.9	152.2	150.4	148.6	146.8
57.5°	145.1	140.2	135.3	132.1	130.6	129.1	127.6	126.1
60°	130.8	126.0	121.1	118.0	116.5	114.9	113.5	111.9
62.5°	116.6	112.1	107.5	104.4	102.9	101.3	99.7	98.2
65°	96.3	92.0	87.6	85.0	83.9	83.0	82.1	81.0
67.5°	77.1	73.8	70.5	68.4	67.3	66.3	65.3	64.2
70°	65.2	62.1	58.9	56.9	55.9	54.9	53.9	53.0
72.5°	54.4	51.9	49.3	47.9	47.4	47.0	46.7	46.2
75°	40.7	39.9	38.9	38.4	38.2	38.1	37.9	37.7
77.5°	30.7	30.2	29.8	29.4	29.3	29.1	28.9	28.8
80°	24.7	24.5	24.2	24.0	23.8	23.6	23.4	23.2
82.5°	18.9	18.7	18.4	18.3	18.3	18.2	18.2	18.2
85°	10.8	10.7	10.5	10.4	10.4	10.4	10.4	10.4
87.5°	10.8	10.8	11.0	11.1	11.2	11.2	11.3	11.3
90°	33.5	34.6	35.8	36.7	37.2	37.8	38.4	38.9
92.5°	51.7	52.6	53.6	53.8	53.5	53.1	52.8	52.4
95°	98.4	99.5	100.7	101.3	101.3	101.3	101.3	101.3
97.5°	153.0	154.3	155.7	156.3	156.2	156.0	155.9	155.8
100°	192.6	193.5	194.3	195.0	195.6	196.2	196.7	197.3
102.5°	238.3	239.2	240.0	240.4	240.3	240.1	240.0	240.0
105°	306.4	306.4	306.4	306.7	307.3	307.9	308.4	309.0
107.5°	380.2	381.1	382.0	382.3	381.9	381.6	381.3	380.9
110°	429.5	430.6	431.8	432.0	431.4	430.9	430.3	429.7





TEST NUMBER: P332409-935

CATALOG NUMBER: S123RDIW-S340D1535U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	478.7	480.1	481.5	482.2	482.1	481.9	481.8	481.6
115°	553.7	554.0	554.2	554.2	554.0	553.7	553.4	553.1
117.5°	629.3	629.3	629.2	628.8	627.9	627.2	626.4	625.5
120°	679.8	679.5	679.2	678.7	678.2	677.6	677.0	676.4
122.5°	730.7	730.0	729.3	728.5	727.7	726.9	726.1	725.2
125°	806.6	805.4	804.3	803.1	801.9	800.8	799.6	798.5
127.5°	881.5	879.9	878.2	876.8	875.5	874.1	872.8	871.4
130°	931.2	930.1	928.9	927.3	925.3	923.3	921.3	919.2
132.5°	979.6	978.2	976.8	975.3	973.8	972.2	970.6	969.1
135°	1052.0	1050.8	1049.6	1048.8	1048.2	1047.6	1047.1	1046.5
137.5°	1122.7	1121.5	1120.3	1119.1	1118.0	1117.0	1115.9	1114.7
140°	1169.2	1169.0	1168.6	1167.5	1165.4	1163.5	1161.4	1159.4
142.5°	1212.9	1212.5	1212.3	1211.3	1209.8	1208.2	1206.7	1205.1
145°	1276.9	1276.7	1276.4	1275.7	1274.5	1273.4	1272.2	1271.1
147.5°	1337.6	1337.6	1337.6	1336.7	1335.0	1333.3	1331.5	1329.7
150°	1374.9	1374.9	1374.9	1374.1	1372.3	1370.6	1368.9	1367.2
152.5°	1409.1	1409.5	1410.1	1409.5	1408.0	1406.5	1405.0	1403.5
155°	1459.1	1460.2	1461.4	1460.9	1458.9	1456.9	1454.8	1452.9
157.5°	1502.0	1503.2	1504.4	1504.3	1502.6	1501.0	1499.3	1497.8
160°	1528.4	1529.9	1531.3	1531.5	1530.3	1529.1	1528.0	1526.8
162.5°	1553.3	1554.8	1556.3	1556.1	1554.2	1552.4	1550.5	1548.7
165°	1584.8	1586.6	1588.3	1588.2	1586.1	1584.2	1582.1	1580.1
167.5°	1610.4	1612.2	1613.9	1613.9	1612.2	1610.4	1608.6	1606.8
170°	1624.4	1626.4	1628.4	1628.4	1626.4	1624.4	1622.4	1620.3
172.5°	1635.3	1637.1	1638.9	1638.8	1636.8	1634.8	1632.7	1630.7
175°	1647.2	1648.9	1650.6	1650.5	1648.5	1646.4	1644.4	1642.4
177.5°	1652.4	1653.8	1655.2	1655.1	1653.5	1651.8	1650.3	1648.6
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8

(END OF REPORT)