

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332392-935

Luminaire Tested: **S123RDIW-S340D460U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332392-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D460U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2706.7 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332392-935

CATALOG NUMBER: S123RDIW-S340D460U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332392-935

CATALOG NUMBER: S123RDIW-S340D460U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	81	75	70	80	74	69	64	61	57	54	49	47	44	38	37	35	30
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	35	33	31	28	26	22
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	28	25	23	20
6	62	50	43	37	57	46	39	34	39	34	30	32	28	25	25	22	20	17
7	57	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	29	49	38	31	27	32	27	23	26	23	20	21	18	16	14
9	50	38	30	25	45	35	28	24	29	24	21	24	21	18	20	17	15	13
10	46	35	28	23	42	32	26	21	27	22	19	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5324	5324	5324
5°	5344	5271	5302
10°	5314	5205	5187
15°	5258	5084	5029
20°	5179	4931	4816
25°	5099	4760	4608
30°	4992	4561	4313
35°	4882	4365	4043
40°	4780	4131	3710
45°	4647	3902	3408
50°	4501	3641	3069
55°	4352	3342	2755
60°	4215	3023	2409
65°	4037	2677	2063
70°	3811	2247	1668
75°	3489	1768	1568
80°	3106	1568	1438
85°	2631	1383	1284



TEST NUMBER: P332392-935

CATALOG NUMBER: S123RDIW-S340D460U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.5	1.7
10°-20°	129.2	4.8
20°-30°	186.1	6.9
30°-40°	209.6	7.7
40°-50°	200.5	7.4
50°-60°	164.2	6.1
60°-70°	110.8	4.1
70°-80°	55.7	2.1
80°-90°	16.2	0.6
90°-100°	18.9	0.7
100°-110°	90.2	3.3
110°-120°	216.7	8.0
120°-130°	276.0	10.2
130°-140°	294.8	10.9
140°-150°	275.7	10.2
150°-160°	222.4	8.2
160°-170°	143.5	5.3
170°-180°	49.5	1.8
0°-30°	361.8	13.4
0°-40°	571.4	21.1
0°-60°	936.2	34.6
0°-90°	1118.9	41.3
90°-120°	325.9	12.0
90°-150°	1172.4	43.3
90°-180°	1588.0	58.7
0°-180°	2706.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	495	495	495	495	495	
5°	495	492	488	491	491	47
15°	472	467	456	454	451	133
25°	429	419	401	393	388	197
35°	372	356	332	315	308	232
45°	305	286	256	234	224	235
55°	232	211	178	156	147	208
65°	158	136	105	86	81	157
75°	84	64	42	39	38	89
85°	21	13	11	10	10	24
90°	0	4	9	11	12	2
95°	24	9	12	15	15	29
105°	115	117	85	20	17	122
115°	216	219	222	226	228	213
125°	305	308	309	310	311	272
135°	379	382	383	384	383	292
145°	438	440	441	442	442	274
155°	482	482	482	484	482	222
165°	509	508	507	510	508	144
175°	521	519	519	522	519	50
180°	521	521	521	521	521	



TEST NUMBER: P332392-935

CATALOG NUMBER: S123RDIW-S340D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	496.3	495.9	495.7	495.4	495.2	494.6	493.7	492.8	492.0	491.1	491.9
5°	494.6	494.2	493.8	493.4	492.8	492.1	491.0	490.0	488.9	487.8	488.6
7.5°	490.1	489.6	489.1	488.6	488.2	487.2	485.9	484.5	483.0	481.6	482.1
10°	486.2	485.6	485.0	484.4	483.7	482.6	481.0	479.4	477.8	476.2	476.3
12.5°	480.8	480.1	479.4	478.7	478.0	476.6	474.7	472.8	470.8	468.8	468.7
15°	471.8	470.8	469.8	468.8	467.9	466.1	463.6	461.2	458.7	456.2	455.7
17.5°	460.5	459.3	458.2	457.0	455.9	453.7	450.6	447.4	444.3	441.1	440.1
20°	452.1	450.7	449.3	447.9	446.4	444.0	440.7	437.2	433.9	430.5	429.3
22.5°	442.8	441.2	439.5	437.9	436.3	433.7	430.1	426.5	422.8	419.2	417.8
25°	429.3	427.1	424.8	422.6	420.3	417.2	413.1	409.0	404.8	400.8	398.9
27.5°	412.8	410.4	407.9	405.4	402.9	399.5	394.9	390.3	385.7	381.2	378.6
30°	401.6	398.9	396.2	393.6	390.9	387.0	382.0	377.0	372.0	367.0	364.0
32.5°	390.4	387.3	384.3	381.3	378.2	374.1	368.8	363.5	358.3	352.9	349.7
35°	371.5	368.2	365.1	361.9	358.7	354.3	348.8	343.2	337.7	332.2	328.4
37.5°	352.4	348.8	345.3	341.7	338.1	333.4	327.5	321.6	315.7	309.8	305.5
40°	340.2	336.3	332.3	328.5	324.5	319.3	313.1	306.7	300.4	294.0	289.5
42.5°	326.4	322.4	318.6	314.6	310.7	305.5	298.9	292.4	285.9	279.3	274.2
45°	305.3	301.3	297.3	293.3	289.2	283.8	277.0	270.1	263.2	256.3	251.2
47.5°	284.2	279.8	275.3	271.0	266.6	261.0	254.1	247.2	240.4	233.5	228.0
50°	268.8	264.6	260.5	256.2	252.0	246.3	239.1	231.9	224.6	217.4	211.9
52.5°	255.0	250.5	245.9	241.3	236.8	230.9	223.8	216.6	209.5	202.3	196.7
55°	231.9	227.5	223.2	218.8	214.4	208.4	200.9	193.3	185.7	178.1	173.0
57.5°	210.5	205.8	201.0	196.2	191.5	185.3	177.7	170.0	162.5	154.9	150.0
60°	195.8	190.9	186.0	181.1	176.2	170.0	162.6	155.2	147.8	140.4	135.6
62.5°	181.0	176.1	171.2	166.3	161.4	155.2	147.8	140.4	133.0	125.6	121.1
65°	158.5	153.6	148.7	143.8	138.9	132.9	126.0	119.0	112.1	105.1	100.7
67.5°	136.0	131.0	126.0	121.1	116.1	110.3	103.6	96.9	90.2	83.6	80.3
70°	121.1	116.3	111.5	106.7	101.9	96.3	90.1	83.9	77.7	71.4	68.3
72.5°	106.4	101.7	96.9	92.1	87.4	82.2	76.5	70.9	65.2	59.5	57.0
75°	83.9	79.6	75.3	71.0	66.7	62.2	57.3	52.3	47.4	42.5	41.7
77.5°	63.3	59.4	55.5	51.7	47.9	44.3	41.2	38.0	34.9	31.7	31.3
80°	50.1	46.5	42.9	39.2	35.6	32.8	30.9	29.0	27.1	25.3	25.0
82.5°	37.6	34.4	31.3	28.2	25.0	23.0	22.1	21.3	20.4	19.5	19.2
85°	21.3	19.3	17.3	15.4	13.4	12.3	12.1	11.8	11.5	11.2	11.0
87.5°	7.7	7.1	6.5	5.9	5.3	5.2	5.3	5.6	5.8	6.0	6.0
90°	0.3	1.2	2.1	2.9	3.8	4.8	5.9	7.1	8.2	9.3	9.6
92.5°	7.2	7.0	6.7	6.5	6.2	6.5	7.4	8.2	9.0	9.9	10.4
95°	23.6	20.1	16.5	13.0	9.5	8.2	9.1	10.1	11.0	12.0	12.6
97.5°	47.4	45.8	44.3	42.7	41.1	37.2	31.0	24.8	18.7	12.5	13.2
100°	65.3	67.1	68.8	70.5	72.2	66.4	53.0	39.6	26.2	12.7	13.4
102.5°	85.8	87.0	88.3	89.5	90.7	84.0	69.4	54.8	40.1	25.5	23.3
105°	115.3	116.2	117.2	118.1	119.1	115.6	107.9	100.2	92.5	84.7	69.5
107.5°	146.4	147.1	147.9	148.6	149.4	150.4	151.6	152.8	154.0	155.2	144.1
110°	167.1	167.8	168.5	169.2	169.9	170.7	171.6	172.5	173.5	174.4	171.6



TEST NUMBER: P332392-935

CATALOG NUMBER: S123RDIW-S340D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	186.9	187.5	188.1	188.7	189.4	190.2	191.1	192.1	193.0	194.0	194.0
115°	216.2	216.7	217.2	217.7	218.3	219.0	219.7	220.5	221.3	222.1	222.9
117.5°	244.6	245.3	245.9	246.5	247.2	247.7	248.1	248.5	248.9	249.3	249.9
120°	262.3	263.0	263.8	264.6	265.4	265.9	266.1	266.4	266.7	266.9	267.6
122.5°	280.3	280.9	281.5	282.1	282.8	283.3	283.6	283.9	284.2	284.6	285.0
125°	304.8	305.5	306.2	306.9	307.5	308.1	308.4	308.8	309.1	309.4	309.6
127.5°	328.6	329.3	330.0	330.7	331.4	331.9	332.3	332.8	333.2	333.6	333.9
130°	343.5	344.2	344.9	345.6	346.3	346.8	347.2	347.5	347.8	348.1	348.4
132.5°	357.7	358.4	359.1	359.8	360.5	360.9	361.3	361.5	361.8	362.1	362.4
135°	379.4	380.0	380.5	381.0	381.5	381.9	382.3	382.6	383.0	383.3	383.6
137.5°	398.0	398.7	399.3	400.0	400.6	401.1	401.3	401.5	401.7	401.8	402.3
140°	410.4	411.0	411.5	412.0	412.5	412.8	413.1	413.4	413.6	413.9	414.2
142.5°	421.9	422.4	422.9	423.4	424.0	424.3	424.6	424.8	425.1	425.3	425.6
145°	437.9	438.5	439.1	439.7	440.3	440.7	440.8	441.0	441.2	441.3	441.5
147.5°	453.0	453.4	453.7	454.2	454.5	454.9	455.0	455.2	455.4	455.6	455.7
150°	462.3	462.5	462.8	463.0	463.3	463.5	463.6	463.8	464.0	464.2	464.3
152.5°	470.6	470.7	470.9	471.0	471.1	471.2	471.3	471.4	471.5	471.7	471.9
155°	482.3	482.2	482.0	481.9	481.7	481.6	481.7	481.8	481.9	482.0	482.4
157.5°	491.5	491.5	491.5	491.5	491.5	491.4	491.3	491.2	491.1	491.0	491.5
160°	497.1	497.0	496.9	496.8	496.7	496.6	496.5	496.5	496.4	496.3	496.8
162.5°	502.3	502.1	501.9	501.7	501.4	501.3	501.2	501.1	501.0	500.9	501.5
165°	508.7	508.4	508.2	507.9	507.6	507.5	507.4	507.3	507.2	507.1	507.8
167.5°	513.7	513.3	513.0	512.6	512.3	512.1	512.1	512.1	512.1	512.1	512.8
170°	516.4	516.1	515.7	515.4	515.1	514.9	514.9	514.9	514.9	514.9	515.6
172.5°	518.2	517.9	517.5	517.0	516.6	516.4	516.5	516.6	516.7	516.7	517.4
175°	520.6	520.2	519.8	519.4	518.9	518.8	518.8	518.9	519.0	519.1	519.7
177.5°	521.2	520.9	520.6	520.2	519.9	519.8	519.9	519.9	520.0	520.0	520.6
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6



TEST NUMBER: P332392-935

CATALOG NUMBER: S123RDIW-S340D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	492.7	493.4	494.3	494.6	494.5	494.3	494.1	494.0
5°	489.5	490.3	491.0	491.4	491.2	491.0	490.9	490.7
7.5°	482.6	483.0	483.5	483.5	483.2	482.9	482.6	482.3
10°	476.4	476.5	476.6	476.4	476.0	475.5	475.0	474.6
12.5°	468.7	468.6	468.6	468.3	467.8	467.3	466.7	466.2
15°	455.2	454.8	454.3	453.8	453.2	452.5	451.9	451.3
17.5°	439.2	438.2	437.3	436.4	435.4	434.5	433.6	432.7
20°	428.2	427.0	425.9	424.7	423.6	422.6	421.5	420.4
22.5°	416.4	414.9	413.5	412.2	411.2	410.3	409.2	408.3
25°	397.0	395.2	393.3	391.8	390.9	389.9	388.9	388.0
27.5°	376.0	373.4	370.8	368.8	367.2	365.8	364.3	362.7
30°	361.0	358.0	355.0	352.8	351.3	349.9	348.4	347.0
32.5°	346.3	343.0	339.7	337.3	335.8	334.3	332.8	331.3
35°	324.5	320.6	316.8	314.1	312.5	310.9	309.3	307.7
37.5°	301.1	296.7	292.4	289.2	287.2	285.2	283.3	281.3
40°	284.8	280.2	275.5	272.2	270.1	268.1	266.0	264.0
42.5°	269.1	264.2	259.1	255.6	253.7	251.9	250.1	248.2
45°	246.2	241.1	236.0	232.4	230.3	228.2	226.0	223.9
47.5°	222.4	216.9	211.4	207.7	205.8	203.9	201.9	200.0
50°	206.4	200.9	195.4	191.6	189.5	187.4	185.4	183.3
52.5°	190.9	185.1	179.4	175.6	173.7	171.9	170.1	168.2
55°	167.8	162.6	157.5	153.9	152.2	150.4	148.6	146.8
57.5°	145.1	140.2	135.3	132.1	130.6	129.1	127.6	126.1
60°	130.8	126.0	121.1	118.0	116.5	114.9	113.5	111.9
62.5°	116.6	112.1	107.5	104.4	102.9	101.3	99.7	98.2
65°	96.3	92.0	87.6	85.0	83.9	83.0	82.1	81.0
67.5°	77.1	73.8	70.5	68.4	67.3	66.3	65.3	64.2
70°	65.2	62.1	58.9	56.9	55.9	54.9	53.9	53.0
72.5°	54.4	51.9	49.3	47.9	47.4	47.0	46.7	46.2
75°	40.7	39.9	38.9	38.4	38.2	38.1	37.9	37.7
77.5°	30.7	30.2	29.8	29.4	29.3	29.1	28.9	28.8
80°	24.7	24.5	24.2	24.0	23.8	23.6	23.4	23.2
82.5°	18.9	18.7	18.4	18.3	18.3	18.2	18.2	18.2
85°	10.8	10.7	10.5	10.4	10.4	10.4	10.4	10.4
87.5°	6.0	6.0	6.0	6.0	5.9	5.9	5.9	5.9
90°	10.0	10.3	10.7	10.9	11.1	11.3	11.5	11.6
92.5°	11.0	11.5	12.1	12.4	12.6	12.7	12.7	12.8
95°	13.2	13.8	14.4	14.7	14.7	14.7	14.7	14.7
97.5°	13.9	14.6	15.2	15.6	15.7	15.8	15.8	15.9
100°	14.1	14.8	15.5	15.9	16.0	16.1	16.2	16.3
102.5°	21.2	19.0	17.0	15.9	16.1	16.3	16.4	16.5
105°	54.2	39.1	23.8	16.4	16.5	16.7	16.9	17.0
107.5°	132.9	121.8	110.6	99.4	87.8	76.4	64.9	53.5
110°	168.8	165.9	163.1	155.6	143.3	131.0	118.6	106.4



TEST NUMBER: P332392-935

CATALOG NUMBER: S123RDIW-S340D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	194.1	194.1	194.2	192.9	190.3	187.7	185.1	182.5
115°	223.8	224.6	225.5	226.1	226.4	226.8	227.1	227.5
117.5°	250.6	251.3	252.0	252.4	252.4	252.5	252.6	252.7
120°	268.3	269.0	269.7	270.0	270.0	270.0	270.0	270.0
122.5°	285.5	286.0	286.5	286.7	286.8	286.9	287.0	287.1
125°	309.8	310.0	310.1	310.3	310.5	310.6	310.8	311.0
127.5°	334.2	334.4	334.7	334.8	334.6	334.4	334.2	334.1
130°	348.8	349.1	349.5	349.6	349.4	349.2	349.0	348.9
132.5°	362.7	363.1	363.4	363.5	363.3	363.0	362.7	362.6
135°	383.8	384.1	384.4	384.4	384.1	383.8	383.6	383.3
137.5°	402.7	403.0	403.5	403.6	403.5	403.3	403.1	402.9
140°	414.6	414.9	415.3	415.3	415.2	415.0	414.8	414.7
142.5°	425.9	426.2	426.5	426.5	426.2	426.0	425.8	425.5
145°	441.7	441.9	442.0	442.1	442.1	442.1	442.1	442.1
147.5°	455.9	456.1	456.2	456.1	455.7	455.3	455.0	454.5
150°	464.5	464.7	464.9	464.9	464.6	464.3	464.1	463.8
152.5°	472.3	472.5	472.9	472.8	472.4	472.0	471.7	471.2
155°	482.8	483.3	483.7	483.6	483.1	482.6	482.1	481.6
157.5°	492.1	492.6	493.1	493.0	492.3	491.7	491.0	490.3
160°	497.3	497.8	498.3	498.3	497.7	497.1	496.5	495.9
162.5°	502.1	502.7	503.3	503.3	502.7	502.2	501.7	501.2
165°	508.5	509.2	509.9	509.9	509.3	508.8	508.2	507.6
167.5°	513.5	514.1	514.8	514.8	514.1	513.5	512.8	512.1
170°	516.3	516.9	517.6	517.6	516.9	516.3	515.6	514.9
172.5°	518.1	518.8	519.4	519.4	518.7	517.9	517.2	516.4
175°	520.3	520.9	521.5	521.5	520.8	520.1	519.4	518.8
177.5°	521.2	521.7	522.3	522.2	521.5	520.8	520.1	519.4
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6

(END OF REPORT)