

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332441-830

Luminaire Tested: **S123RDIW-S775D1030U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332441-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D1030U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6120.6 lumens
Efficiency: N/A
Efficacy: 116.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332441-830

CATALOG NUMBER: S123RDIW-S775D1030U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332441-830

CATALOG NUMBER: S123RDIW-S775D1030U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	88	81	75	70	81	75	70	65	63	59	56	51	49	46	41	39	38	33
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	36	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	21
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	19	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13099	13099	13099
5°	13149	12967	13042
10°	13074	12804	12761
15°	12933	12504	12373
20°	12741	12129	11848
25°	12542	11709	11334
30°	12279	11225	10611
35°	12009	10738	9947
40°	11760	10165	9125
45°	11432	9601	8383
50°	11072	8957	7552
55°	10704	8223	6778
60°	10368	7436	5927
65°	9928	6584	5076
70°	9379	5530	4101
75°	8576	4350	3855
80°	7649	3856	3546
85°	6459	3409	3162



TEST NUMBER: P332441-830

CATALOG NUMBER: S123RDIW-S775D1030U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.3	1.9
10°-20°	317.9	5.2
20°-30°	457.8	7.5
30°-40°	515.7	8.4
40°-50°	493.3	8.1
50°-60°	404.0	6.6
60°-70°	272.6	4.5
70°-80°	137.1	2.2
80°-90°	39.9	0.7
90°-100°	79.2	1.3
100°-110°	237.0	3.9
110°-120°	403.1	6.6
120°-130°	530.3	8.7
130°-140°	596.0	9.7
140°-150°	585.8	9.6
150°-160°	493.2	8.1
160°-170°	328.3	5.4
170°-180°	115.0	1.9
0°-30°	890.0	14.5
0°-40°	1405.7	23.0
0°-60°	2303.0	37.6
0°-90°	2752.6	45.0
90°-120°	719.4	11.8
90°-150°	2431.5	39.7
90°-180°	3368.0	55.0
0°-180°	6120.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1217	1217	1217	1217	1217	
5°	1217	1212	1200	1208	1207	115
15°	1161	1149	1122	1117	1110	327
25°	1056	1030	986	966	954	485
35°	914	877	817	776	757	572
45°	751	705	631	576	551	579
55°	570	520	438	383	361	511
65°	390	334	258	212	199	386
75°	206	159	105	95	93	220
85°	52	32	28	26	26	59
90°	1	11	23	27	29	6
95°	56	63	71	74	74	63
105°	215	217	225	226	227	230
115°	406	408	407	408	407	401
125°	594	597	595	591	587	529
135°	771	776	775	772	770	594
145°	935	937	940	938	935	584
155°	1070	1070	1071	1075	1069	493
165°	1166	1163	1163	1168	1162	329
175°	1213	1209	1209	1214	1208	115
180°	1216	1216	1216	1216	1216	



TEST NUMBER: P332441-830

CATALOG NUMBER: S123RDIW-S775D1030U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9
2.5°	1220.8	1220.1	1219.4	1218.7	1218.0	1216.6	1214.5	1212.4	1210.3	1208.2	1210.1
5°	1216.9	1215.8	1214.7	1213.6	1212.5	1210.6	1208.0	1205.3	1202.7	1200.1	1202.0
7.5°	1205.6	1204.5	1203.2	1202.0	1200.9	1198.5	1195.1	1191.8	1188.4	1184.9	1186.0
10°	1196.2	1194.6	1193.1	1191.6	1190.0	1187.2	1183.3	1179.4	1175.4	1171.5	1171.7
12.5°	1182.7	1181.0	1179.3	1177.6	1175.9	1172.6	1167.8	1163.0	1158.1	1153.3	1153.2
15°	1160.6	1158.2	1155.7	1153.4	1150.9	1146.7	1140.6	1134.4	1128.2	1122.1	1121.1
17.5°	1132.7	1130.0	1127.2	1124.4	1121.5	1116.3	1108.4	1100.6	1092.8	1085.1	1082.7
20°	1112.3	1108.7	1105.2	1101.7	1098.3	1092.3	1083.9	1075.6	1067.3	1058.9	1056.1
22.5°	1089.4	1085.3	1081.3	1077.2	1073.2	1066.8	1057.9	1049.0	1040.2	1031.3	1027.7
25°	1056.0	1050.6	1045.0	1039.5	1034.1	1026.2	1016.2	1006.1	996.0	985.9	981.3
27.5°	1015.5	1009.5	1003.4	997.4	991.4	982.7	971.5	960.3	949.0	937.7	931.3
30°	987.9	981.3	974.8	968.2	961.6	952.2	939.9	927.6	915.3	903.1	895.6
32.5°	960.3	952.8	945.4	937.9	930.5	920.2	907.2	894.3	881.3	868.3	860.2
35°	913.9	906.0	898.1	890.2	882.3	871.6	858.0	844.3	830.8	817.2	807.8
37.5°	867.0	858.1	849.3	840.6	831.8	820.2	805.7	791.2	776.7	762.1	751.4
40°	836.9	827.3	817.6	807.9	798.3	785.7	770.2	754.6	739.0	723.4	712.0
42.5°	803.0	793.3	783.6	774.0	764.4	751.5	735.4	719.3	703.2	687.1	674.7
45°	751.0	741.2	731.3	721.4	711.5	698.2	681.3	664.4	647.5	630.7	618.1
47.5°	699.2	688.3	677.5	666.7	655.8	642.0	625.1	608.1	591.3	574.4	560.8
50°	661.2	650.9	640.6	630.3	620.0	606.0	588.2	570.4	552.7	534.9	521.3
52.5°	627.3	616.1	604.9	593.7	582.6	568.2	550.5	533.0	515.4	497.8	483.7
55°	570.4	559.7	548.9	538.2	527.4	512.7	494.1	475.5	456.9	438.2	425.5
57.5°	517.9	506.2	494.6	482.8	471.1	455.9	437.2	418.4	399.6	381.0	368.9
60°	481.6	469.6	457.5	445.4	433.4	418.2	400.0	381.8	363.6	345.4	333.6
62.5°	445.3	433.2	421.1	409.1	397.1	381.9	363.7	345.5	327.3	309.1	297.9
65°	389.8	377.8	365.7	353.6	341.6	327.0	309.9	292.8	275.7	258.5	247.8
67.5°	334.4	322.2	310.0	297.7	285.6	271.3	254.9	238.5	222.1	205.7	197.7
70°	298.0	286.3	274.4	262.5	250.7	237.0	221.7	206.4	191.1	175.7	168.0
72.5°	261.7	250.1	238.4	226.7	215.1	202.3	188.3	174.4	160.4	146.5	140.2
75°	206.2	195.8	185.2	174.7	164.2	152.9	140.8	128.8	116.7	104.6	102.5
77.5°	155.7	146.2	136.7	127.1	117.6	109.1	101.2	93.5	85.8	77.9	76.8
80°	123.4	114.3	105.4	96.4	87.4	80.6	76.0	71.4	66.8	62.2	61.5
82.5°	92.6	84.8	77.0	69.3	61.5	56.6	54.4	52.2	50.1	48.0	47.3
85°	52.3	47.5	42.7	37.8	33.0	30.3	29.6	28.9	28.3	27.6	27.2
87.5°	19.1	17.6	16.1	14.6	13.1	12.6	13.2	13.8	14.3	14.9	14.8
90°	0.9	3.1	5.2	7.4	9.4	11.9	14.6	17.4	20.2	22.9	23.8
92.5°	23.1	24.5	26.0	27.4	28.8	30.3	32.0	33.6	35.1	36.7	37.3
95°	56.4	57.8	59.3	60.8	62.3	63.9	65.6	67.3	69.0	70.7	71.5
97.5°	100.1	101.1	102.3	103.4	104.5	105.7	106.9	108.1	109.3	110.6	111.6
100°	129.9	131.1	132.4	133.7	135.0	136.1	137.2	138.3	139.3	140.3	141.0
102.5°	164.3	165.0	165.8	166.5	167.3	168.3	169.8	171.2	172.6	174.0	174.7
105°	214.9	215.3	215.7	216.1	216.6	217.7	219.6	221.5	223.5	225.4	225.4
107.5°	273.7	273.9	274.2	274.5	274.7	275.2	276.0	276.7	277.5	278.2	278.9
110°	310.4	310.8	311.2	311.6	312.1	312.5	312.9	313.3	313.8	314.1	315.0



TEST NUMBER: P332441-830

CATALOG NUMBER: S123RDIW-S775D1030U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	348.6	348.8	349.0	349.3	349.6	349.7	349.8	349.9	350.0	350.1	351.1
115°	405.9	406.4	407.1	407.7	408.4	408.5	408.0	407.6	407.2	406.8	407.0
117.5°	463.5	463.9	464.4	464.8	465.2	465.1	464.6	464.0	463.4	463.0	462.9
120°	499.5	500.7	502.0	503.2	504.5	504.6	503.5	502.5	501.4	500.4	500.1
122.5°	536.9	537.8	538.8	539.6	540.5	540.7	540.3	539.7	539.1	538.6	538.0
125°	594.0	594.6	595.2	595.9	596.5	596.6	596.2	595.8	595.3	594.9	594.1
127.5°	646.7	648.0	649.4	650.7	652.1	652.5	652.1	651.6	651.1	650.6	649.5
130°	681.8	683.5	685.2	686.9	688.6	689.1	688.5	687.9	687.2	686.5	685.7
132.5°	716.9	718.6	720.3	722.1	723.8	724.3	723.9	723.4	722.9	722.5	721.4
135°	770.6	771.8	773.2	774.4	775.7	776.2	776.0	775.8	775.6	775.3	774.5
137.5°	820.3	821.3	822.4	823.4	824.5	825.3	825.9	826.4	827.0	827.6	826.6
140°	854.6	855.7	856.8	857.8	858.8	859.5	859.7	860.0	860.2	860.4	860.2
142.5°	886.0	887.0	888.1	889.1	890.2	890.9	891.3	891.6	892.1	892.5	892.2
145°	934.8	935.3	935.7	936.1	936.5	937.1	937.7	938.4	939.0	939.6	939.4
147.5°	977.6	978.4	979.1	980.0	980.7	981.4	981.9	982.6	983.2	983.7	983.7
150°	1007.4	1007.9	1008.2	1008.7	1009.1	1009.6	1009.9	1010.4	1010.8	1011.3	1011.3
152.5°	1031.9	1032.5	1033.0	1033.7	1034.3	1034.6	1034.9	1035.2	1035.5	1035.7	1036.0
155°	1070.4	1070.4	1070.4	1070.4	1070.4	1070.5	1070.7	1071.0	1071.2	1071.4	1072.2
157.5°	1103.3	1103.1	1102.8	1102.5	1102.3	1102.2	1102.4	1102.6	1102.8	1102.9	1103.8
160°	1123.9	1123.5	1123.0	1122.7	1122.2	1122.0	1122.0	1122.0	1122.0	1122.0	1123.0
162.5°	1142.3	1141.7	1141.0	1140.5	1139.9	1139.6	1139.8	1140.0	1140.2	1140.4	1141.4
165°	1165.9	1165.3	1164.7	1164.0	1163.4	1163.1	1163.1	1163.1	1163.1	1163.1	1164.3
167.5°	1184.9	1184.0	1183.2	1182.3	1181.5	1181.1	1181.3	1181.5	1181.7	1181.8	1183.1
170°	1195.5	1194.7	1193.8	1193.0	1192.1	1191.8	1191.8	1191.8	1191.8	1191.8	1193.2
172.5°	1203.9	1203.1	1202.2	1201.4	1200.5	1200.1	1200.1	1200.1	1200.1	1200.1	1201.5
175°	1212.8	1211.9	1211.1	1210.2	1209.4	1208.9	1208.9	1208.9	1208.9	1208.9	1210.2
177.5°	1216.4	1215.7	1215.0	1214.3	1213.6	1213.3	1213.3	1213.3	1213.3	1213.3	1214.3
180°	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6



TEST NUMBER: P332441-830

CATALOG NUMBER: S123RDIW-S775D1030U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9
2.5°	1212.0	1214.0	1215.9	1216.7	1216.4	1216.0	1215.6	1215.3
5°	1204.0	1206.0	1208.0	1208.7	1208.3	1207.9	1207.4	1207.0
7.5°	1187.1	1188.2	1189.3	1189.5	1188.7	1188.0	1187.2	1186.5
10°	1172.0	1172.1	1172.3	1172.0	1170.8	1169.7	1168.7	1167.5
12.5°	1153.0	1152.9	1152.8	1152.1	1150.8	1149.5	1148.3	1147.0
15°	1119.9	1118.8	1117.8	1116.4	1114.9	1113.3	1111.8	1110.3
17.5°	1080.3	1078.1	1075.7	1073.5	1071.1	1068.8	1066.6	1064.3
20°	1053.3	1050.4	1047.5	1044.8	1042.2	1039.5	1036.9	1034.3
22.5°	1024.3	1020.7	1017.1	1014.1	1011.6	1009.2	1006.7	1004.3
25°	976.8	972.1	967.5	964.0	961.6	959.1	956.8	954.3
27.5°	924.9	918.6	912.2	907.1	903.4	899.8	896.1	892.4
30°	888.2	880.6	873.2	867.7	864.2	860.7	857.1	853.7
32.5°	852.0	843.9	835.7	829.7	826.0	822.4	818.7	815.0
35°	798.3	788.9	779.5	772.8	768.8	764.9	760.9	757.0
37.5°	740.6	730.0	719.3	711.5	706.6	701.7	696.9	692.0
40°	700.6	689.2	677.8	669.6	664.5	659.5	654.4	649.4
42.5°	662.1	649.7	637.3	628.8	624.2	619.7	615.2	610.7
45°	605.7	593.1	580.6	571.7	566.5	561.2	556.0	550.7
47.5°	547.1	533.6	520.0	510.9	506.1	501.4	496.8	492.1
50°	507.7	494.1	480.5	471.2	466.2	461.1	456.1	451.0
52.5°	469.6	455.4	441.3	432.0	427.4	422.9	418.4	413.9
55°	412.7	400.0	387.3	378.7	374.4	369.9	365.6	361.2
57.5°	356.9	344.9	332.9	325.0	321.3	317.5	313.8	310.1
60°	321.7	309.9	298.0	290.3	286.5	282.8	279.1	275.3
62.5°	286.8	275.7	264.6	257.0	253.1	249.2	245.3	241.4
65°	237.0	226.3	215.6	209.0	206.6	204.2	201.8	199.3
67.5°	189.6	181.6	173.5	168.2	165.7	163.1	160.5	157.9
70°	160.3	152.6	145.0	140.0	137.5	135.1	132.7	130.3
72.5°	133.9	127.6	121.4	117.7	116.7	115.7	114.7	113.7
75°	100.2	98.0	95.9	94.5	94.1	93.7	93.2	92.7
77.5°	75.6	74.4	73.2	72.4	72.0	71.5	71.1	70.7
80°	60.9	60.2	59.6	59.0	58.5	58.2	57.7	57.2
82.5°	46.7	46.0	45.3	45.0	44.9	44.8	44.7	44.6
85°	26.8	26.3	25.9	25.6	25.6	25.6	25.6	25.6
87.5°	14.8	14.8	14.8	14.8	14.7	14.6	14.5	14.4
90°	24.6	25.4	26.3	27.0	27.3	27.8	28.2	28.7
92.5°	38.0	38.7	39.4	39.6	39.3	39.1	38.8	38.5
95°	72.4	73.2	74.1	74.5	74.5	74.5	74.5	74.5
97.5°	112.5	113.5	114.5	114.9	114.8	114.8	114.7	114.6
100°	141.7	142.3	142.9	143.5	143.8	144.3	144.7	145.2
102.5°	175.2	175.9	176.5	176.8	176.7	176.6	176.5	176.4
105°	225.4	225.4	225.4	225.6	226.0	226.4	226.9	227.2
107.5°	279.7	280.3	281.0	281.2	281.0	280.7	280.4	280.1
110°	315.8	316.7	317.5	317.7	317.4	316.9	316.5	316.0



TEST NUMBER: P332441-830

CATALOG NUMBER: S123RDIW-S775D1030U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	352.1	353.1	354.1	354.6	354.5	354.4	354.4	354.3
115°	407.2	407.5	407.6	407.6	407.5	407.2	407.0	406.8
117.5°	462.9	462.8	462.8	462.4	461.8	461.3	460.6	460.1
120°	499.9	499.7	499.5	499.2	498.8	498.3	497.9	497.5
122.5°	537.4	536.9	536.4	535.7	535.2	534.6	534.0	533.4
125°	593.2	592.4	591.5	590.7	589.8	589.0	588.1	587.3
127.5°	648.3	647.1	645.9	644.8	643.9	642.9	641.9	640.9
130°	684.9	684.0	683.2	682.0	680.5	679.0	677.6	676.1
132.5°	720.5	719.4	718.4	717.4	716.1	715.0	713.9	712.8
135°	773.6	772.8	771.9	771.4	770.9	770.5	770.1	769.7
137.5°	825.8	824.8	824.0	823.1	822.3	821.5	820.7	819.9
140°	860.0	859.7	859.5	858.7	857.1	855.7	854.2	852.7
142.5°	892.0	891.8	891.6	890.9	889.8	888.6	887.5	886.4
145°	939.2	939.0	938.8	938.2	937.4	936.5	935.7	934.8
147.5°	983.7	983.7	983.7	983.1	981.8	980.5	979.3	978.0
150°	1011.3	1011.3	1011.3	1010.6	1009.4	1008.0	1006.8	1005.5
152.5°	1036.3	1036.7	1037.1	1036.7	1035.6	1034.4	1033.3	1032.3
155°	1073.1	1073.9	1074.8	1074.5	1073.0	1071.5	1070.1	1068.6
157.5°	1104.7	1105.6	1106.5	1106.4	1105.1	1104.0	1102.8	1101.5
160°	1124.2	1125.2	1126.2	1126.3	1125.5	1124.6	1123.8	1122.9
162.5°	1142.5	1143.5	1144.6	1144.4	1143.1	1141.7	1140.4	1139.0
165°	1165.6	1166.9	1168.2	1168.1	1166.6	1165.1	1163.6	1162.2
167.5°	1184.4	1185.7	1187.0	1187.0	1185.7	1184.4	1183.1	1181.8
170°	1194.7	1196.2	1197.7	1197.7	1196.2	1194.7	1193.2	1191.8
172.5°	1202.8	1204.1	1205.4	1205.3	1203.8	1202.3	1200.8	1199.4
175°	1211.4	1212.8	1214.0	1213.9	1212.4	1210.9	1209.5	1208.0
177.5°	1215.3	1216.4	1217.4	1217.3	1216.1	1214.9	1213.7	1212.6
180°	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6

(END OF REPORT)