

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332444-830

Luminaire Tested: **S123RDIW-S775D1320U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332444-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D1320U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7728.2 lumens
Efficiency: N/A
Efficacy: 125.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332444-830

CATALOG NUMBER: S123RDIW-S775D1320U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332444-830

CATALOG NUMBER: S123RDIW-S775D1320U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	86	79	74	69	78	72	67	63	58	55	52	46	43	41	34	32	31	26
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	30	28	27	22
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	42	60	50	44	38	41	36	32	33	29	26	25	22	20	17
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	45	37	32	51	41	34	29	34	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	31	26	22	24	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13099	13099	13099
5°	13149	12967	13042
10°	13074	12804	12761
15°	12933	12504	12373
20°	12741	12129	11848
25°	12542	11709	11334
30°	12279	11225	10611
35°	12009	10738	9947
40°	11760	10165	9125
45°	11432	9601	8383
50°	11072	8957	7552
55°	10704	8223	6778
60°	10368	7436	5927
65°	9928	6584	5076
70°	9379	5530	4101
75°	8576	4350	3855
80°	7649	3856	3546
85°	6459	3409	3162



TEST NUMBER: P332444-830

CATALOG NUMBER: S123RDIW-S775D1320U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.3	1.5
10°-20°	317.9	4.1
20°-30°	457.8	5.9
30°-40°	515.7	6.7
40°-50°	493.3	6.4
50°-60°	404.0	5.2
60°-70°	272.6	3.5
70°-80°	137.1	1.8
80°-90°	40.8	0.5
90°-100°	59.3	0.8
100°-110°	282.7	3.7
110°-120°	679.0	8.8
120°-130°	864.6	11.2
130°-140°	923.8	12.0
140°-150°	863.8	11.2
150°-160°	696.8	9.0
160°-170°	449.7	5.8
170°-180°	155.0	2.0
0°-30°	890.0	11.5
0°-40°	1405.7	18.2
0°-60°	2303.0	29.8
0°-90°	2753.6	35.6
90°-120°	1020.9	13.2
90°-150°	3673.1	47.5
90°-180°	4975.0	64.4
0°-180°	7728.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1217	1217	1217	1217	1217	
5°	1217	1212	1200	1208	1207	115
15°	1161	1149	1122	1117	1110	327
25°	1056	1030	986	966	954	485
35°	914	877	817	776	757	572
45°	751	705	631	576	551	579
55°	570	520	438	383	361	511
65°	390	334	258	212	199	386
75°	206	159	105	95	93	220
85°	52	32	28	26	26	59
90°	1	14	29	34	36	6
95°	74	28	38	46	46	91
105°	361	368	265	63	53	383
115°	678	685	696	707	713	669
125°	955	964	970	972	974	853
135°	1189	1196	1201	1204	1201	915
145°	1372	1380	1383	1385	1385	858
155°	1511	1509	1510	1515	1509	696
165°	1594	1590	1589	1598	1590	450
175°	1631	1626	1626	1634	1625	155
180°	1631	1631	1631	1631	1631	



TEST NUMBER: P332444-830

CATALOG NUMBER: S123RDIW-S775D1320U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9
2.5°	1220.8	1220.1	1219.4	1218.7	1218.0	1216.6	1214.5	1212.4	1210.3	1208.2	1210.1
5°	1216.9	1215.8	1214.7	1213.6	1212.5	1210.6	1208.0	1205.3	1202.7	1200.1	1202.0
7.5°	1205.6	1204.5	1203.2	1202.0	1200.9	1198.5	1195.1	1191.8	1188.4	1184.9	1186.0
10°	1196.2	1194.6	1193.1	1191.6	1190.0	1187.2	1183.3	1179.4	1175.4	1171.5	1171.7
12.5°	1182.7	1181.0	1179.3	1177.6	1175.9	1172.6	1167.8	1163.0	1158.1	1153.3	1153.2
15°	1160.6	1158.2	1155.7	1153.4	1150.9	1146.7	1140.6	1134.4	1128.2	1122.1	1121.1
17.5°	1132.7	1130.0	1127.2	1124.4	1121.5	1116.3	1108.4	1100.6	1092.8	1085.1	1082.7
20°	1112.3	1108.7	1105.2	1101.7	1098.3	1092.3	1083.9	1075.6	1067.3	1058.9	1056.1
22.5°	1089.4	1085.3	1081.3	1077.2	1073.2	1066.8	1057.9	1049.0	1040.2	1031.3	1027.7
25°	1056.0	1050.6	1045.0	1039.5	1034.1	1026.2	1016.2	1006.1	996.0	985.9	981.3
27.5°	1015.5	1009.5	1003.4	997.4	991.4	982.7	971.5	960.3	949.0	937.7	931.3
30°	987.9	981.3	974.8	968.2	961.6	952.2	939.9	927.6	915.3	903.1	895.6
32.5°	960.3	952.8	945.4	937.9	930.5	920.2	907.2	894.3	881.3	868.3	860.2
35°	913.9	906.0	898.1	890.2	882.3	871.6	858.0	844.3	830.8	817.2	807.8
37.5°	867.0	858.1	849.3	840.6	831.8	820.2	805.7	791.2	776.7	762.1	751.4
40°	836.9	827.3	817.6	807.9	798.3	785.7	770.2	754.6	739.0	723.4	712.0
42.5°	803.0	793.3	783.6	774.0	764.4	751.5	735.4	719.3	703.2	687.1	674.7
45°	751.0	741.2	731.3	721.4	711.5	698.2	681.3	664.4	647.5	630.7	618.1
47.5°	699.2	688.3	677.5	666.7	655.8	642.0	625.1	608.1	591.3	574.4	560.8
50°	661.2	650.9	640.6	630.3	620.0	606.0	588.2	570.4	552.7	534.9	521.3
52.5°	627.3	616.1	604.9	593.7	582.6	568.2	550.5	533.0	515.4	497.8	483.7
55°	570.4	559.7	548.9	538.2	527.4	512.7	494.1	475.5	456.9	438.2	425.5
57.5°	517.9	506.2	494.6	482.8	471.1	455.9	437.2	418.4	399.6	381.0	368.9
60°	481.6	469.6	457.5	445.4	433.4	418.2	400.0	381.8	363.6	345.4	333.6
62.5°	445.3	433.2	421.1	409.1	397.1	381.9	363.7	345.5	327.3	309.1	297.9
65°	389.8	377.8	365.7	353.6	341.6	327.0	309.9	292.8	275.7	258.5	247.8
67.5°	334.4	322.2	310.0	297.7	285.6	271.3	254.9	238.5	222.1	205.7	197.7
70°	298.0	286.3	274.4	262.5	250.7	237.0	221.7	206.4	191.1	175.7	168.0
72.5°	261.7	250.1	238.4	226.7	215.1	202.3	188.3	174.4	160.4	146.5	140.2
75°	206.2	195.8	185.2	174.7	164.2	152.9	140.8	128.8	116.7	104.6	102.5
77.5°	155.7	146.2	136.7	127.1	117.6	109.1	101.2	93.5	85.8	77.9	76.8
80°	123.4	114.3	105.4	96.4	87.4	80.6	76.0	71.4	66.8	62.2	61.5
82.5°	92.6	84.8	77.0	69.3	61.5	56.6	54.4	52.2	50.1	48.0	47.3
85°	52.3	47.5	42.7	37.8	33.0	30.3	29.6	28.9	28.3	27.6	27.2
87.5°	19.2	17.8	16.4	15.0	13.7	13.3	13.9	14.7	15.4	16.1	16.1
90°	1.2	3.9	6.6	9.3	12.0	15.1	18.6	22.1	25.5	29.1	30.2
92.5°	22.5	21.8	21.0	20.3	19.5	20.5	23.1	25.7	28.4	31.0	32.7
95°	73.9	62.9	51.8	40.8	29.8	25.7	28.7	31.7	34.6	37.6	39.5
97.5°	148.5	143.6	138.6	133.7	128.8	116.6	97.2	77.9	58.4	39.0	41.2
100°	204.8	210.2	215.6	220.9	226.4	208.0	166.1	124.0	82.0	40.0	42.1
102.5°	268.8	272.7	276.5	280.4	284.4	263.3	217.4	171.5	125.6	79.7	73.0
105°	361.2	364.1	367.1	370.0	373.0	362.4	338.1	313.9	289.6	265.4	217.7
107.5°	458.6	461.0	463.4	465.7	468.1	471.2	475.0	478.8	482.7	486.4	451.5
110°	523.6	525.8	527.8	530.0	532.2	534.7	537.7	540.6	543.7	546.6	537.7



TEST NUMBER: P332444-830

CATALOG NUMBER: S123RDIW-S775D1320U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	585.6	587.6	589.5	591.4	593.3	595.8	598.8	601.7	604.7	607.7	607.8
115°	677.5	679.1	680.7	682.3	683.9	686.0	688.3	690.8	693.2	695.7	698.3
117.5°	766.5	768.5	770.4	772.4	774.4	776.0	777.2	778.5	779.8	781.0	783.2
120°	821.7	824.2	826.5	829.0	831.4	833.0	833.8	834.6	835.5	836.2	838.4
122.5°	878.0	880.0	881.9	883.9	885.9	887.4	888.4	889.5	890.5	891.6	893.1
125°	955.0	957.2	959.3	961.5	963.7	965.3	966.3	967.4	968.5	969.6	970.1
127.5°	1029.6	1031.8	1034.0	1036.1	1038.3	1040.0	1041.3	1042.6	1043.9	1045.2	1046.0
130°	1076.2	1078.4	1080.5	1082.7	1084.9	1086.5	1087.5	1088.6	1089.7	1090.7	1091.8
132.5°	1120.8	1122.9	1125.1	1127.3	1129.4	1131.0	1131.8	1132.7	1133.5	1134.3	1135.5
135°	1188.9	1190.5	1192.1	1193.7	1195.4	1196.7	1197.8	1198.9	1200.0	1201.1	1201.8
137.5°	1247.1	1249.2	1251.2	1253.2	1255.3	1256.6	1257.2	1257.8	1258.4	1259.0	1260.3
140°	1285.9	1287.5	1289.1	1290.7	1292.3	1293.5	1294.4	1295.1	1296.0	1296.8	1297.9
142.5°	1321.7	1323.3	1325.0	1326.6	1328.2	1329.5	1330.2	1331.1	1331.8	1332.7	1333.5
145°	1372.0	1373.9	1375.7	1377.6	1379.5	1380.6	1381.2	1381.8	1382.3	1382.8	1383.4
147.5°	1419.2	1420.4	1421.6	1422.9	1424.2	1425.0	1425.6	1426.1	1426.6	1427.2	1427.8
150°	1448.3	1449.1	1449.9	1450.7	1451.5	1452.2	1452.7	1453.2	1453.8	1454.3	1454.9
152.5°	1474.4	1474.8	1475.2	1475.6	1475.9	1476.3	1476.7	1477.0	1477.2	1477.6	1478.6
155°	1511.3	1510.8	1510.2	1509.7	1509.1	1509.0	1509.3	1509.6	1509.9	1510.0	1511.5
157.5°	1539.9	1539.8	1539.8	1539.7	1539.6	1539.5	1539.3	1539.0	1538.7	1538.4	1540.0
160°	1557.4	1557.1	1556.8	1556.5	1556.2	1556.0	1555.8	1555.5	1555.2	1554.9	1556.5
162.5°	1573.9	1573.1	1572.4	1571.7	1571.0	1570.6	1570.3	1570.0	1569.7	1569.4	1571.3
165°	1593.7	1592.9	1592.0	1591.3	1590.4	1590.0	1589.7	1589.4	1589.1	1588.8	1591.0
167.5°	1609.2	1608.2	1607.0	1606.0	1604.9	1604.4	1604.4	1604.4	1604.4	1604.4	1606.6
170°	1618.0	1616.8	1615.8	1614.8	1613.6	1613.1	1613.1	1613.1	1613.1	1613.1	1615.2
172.5°	1623.8	1622.5	1621.2	1619.9	1618.6	1618.1	1618.3	1618.5	1618.7	1618.9	1621.1
175°	1631.3	1629.9	1628.6	1627.2	1625.9	1625.3	1625.6	1625.9	1626.2	1626.5	1628.3
177.5°	1633.2	1632.1	1631.1	1630.0	1628.9	1628.5	1628.7	1628.9	1629.1	1629.4	1631.1
180°	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3



TEST NUMBER: P332444-830

CATALOG NUMBER: S123RDIW-S775D1320U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9
2.5°	1212.0	1214.0	1215.9	1216.7	1216.4	1216.0	1215.6	1215.3
5°	1204.0	1206.0	1208.0	1208.7	1208.3	1207.9	1207.4	1207.0
7.5°	1187.1	1188.2	1189.3	1189.5	1188.7	1188.0	1187.2	1186.5
10°	1172.0	1172.1	1172.3	1172.0	1170.8	1169.7	1168.7	1167.5
12.5°	1153.0	1152.9	1152.8	1152.1	1150.8	1149.5	1148.3	1147.0
15°	1119.9	1118.8	1117.8	1116.4	1114.9	1113.3	1111.8	1110.3
17.5°	1080.3	1078.1	1075.7	1073.5	1071.1	1068.8	1066.6	1064.3
20°	1053.3	1050.4	1047.5	1044.8	1042.2	1039.5	1036.9	1034.3
22.5°	1024.3	1020.7	1017.1	1014.1	1011.6	1009.2	1006.7	1004.3
25°	976.8	972.1	967.5	964.0	961.6	959.1	956.8	954.3
27.5°	924.9	918.6	912.2	907.1	903.4	899.8	896.1	892.4
30°	888.2	880.6	873.2	867.7	864.2	860.7	857.1	853.7
32.5°	852.0	843.9	835.7	829.7	826.0	822.4	818.7	815.0
35°	798.3	788.9	779.5	772.8	768.8	764.9	760.9	757.0
37.5°	740.6	730.0	719.3	711.5	706.6	701.7	696.9	692.0
40°	700.6	689.2	677.8	669.6	664.5	659.5	654.4	649.4
42.5°	662.1	649.7	637.3	628.8	624.2	619.7	615.2	610.7
45°	605.7	593.1	580.6	571.7	566.5	561.2	556.0	550.7
47.5°	547.1	533.6	520.0	510.9	506.1	501.4	496.8	492.1
50°	507.7	494.1	480.5	471.2	466.2	461.1	456.1	451.0
52.5°	469.6	455.4	441.3	432.0	427.4	422.9	418.4	413.9
55°	412.7	400.0	387.3	378.7	374.4	369.9	365.6	361.2
57.5°	356.9	344.9	332.9	325.0	321.3	317.5	313.8	310.1
60°	321.7	309.9	298.0	290.3	286.5	282.8	279.1	275.3
62.5°	286.8	275.7	264.6	257.0	253.1	249.2	245.3	241.4
65°	237.0	226.3	215.6	209.0	206.6	204.2	201.8	199.3
67.5°	189.6	181.6	173.5	168.2	165.7	163.1	160.5	157.9
70°	160.3	152.6	145.0	140.0	137.5	135.1	132.7	130.3
72.5°	133.9	127.6	121.4	117.7	116.7	115.7	114.7	113.7
75°	100.2	98.0	95.9	94.5	94.1	93.7	93.2	92.7
77.5°	75.6	74.4	73.2	72.4	72.0	71.5	71.1	70.7
80°	60.9	60.2	59.6	59.0	58.5	58.2	57.7	57.2
82.5°	46.7	46.0	45.3	45.0	44.9	44.8	44.7	44.6
85°	26.8	26.3	25.9	25.6	25.6	25.6	25.6	25.6
87.5°	16.1	16.2	16.2	16.2	16.1	16.1	16.0	15.9
90°	31.2	32.3	33.4	34.2	34.8	35.3	35.8	36.4
92.5°	34.5	36.2	37.9	38.9	39.3	39.6	39.9	40.2
95°	41.4	43.3	45.1	46.1	46.1	46.1	46.1	46.1
97.5°	43.4	45.5	47.6	48.8	49.1	49.4	49.7	50.0
100°	44.3	46.5	48.6	49.9	50.0	50.3	50.6	50.9
102.5°	66.4	59.7	53.1	50.0	50.4	50.9	51.4	51.8
105°	170.0	122.4	74.7	51.2	51.7	52.2	52.8	53.3
107.5°	416.6	381.6	346.7	311.2	275.3	239.3	203.4	167.5
110°	528.8	519.9	511.0	487.3	448.8	410.3	371.8	333.3



TEST NUMBER: P332444-830

CATALOG NUMBER: S123RDIW-S775D1320U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	608.0	608.1	608.3	604.4	596.2	588.1	579.9	571.8
115°	701.1	703.7	706.4	708.3	709.4	710.5	711.5	712.7
117.5°	785.3	787.4	789.6	790.8	791.0	791.2	791.5	791.6
120°	840.6	842.7	844.9	845.9	845.9	845.9	845.9	845.9
122.5°	894.6	896.1	897.6	898.4	898.6	898.8	899.1	899.3
125°	970.6	971.2	971.7	972.2	972.8	973.4	973.8	974.4
127.5°	1046.9	1047.7	1048.7	1048.8	1048.3	1047.7	1047.2	1046.6
130°	1092.9	1094.0	1095.0	1095.3	1094.8	1094.3	1093.7	1093.2
132.5°	1136.5	1137.6	1138.7	1138.9	1138.1	1137.4	1136.6	1135.9
135°	1202.7	1203.4	1204.3	1204.3	1203.4	1202.7	1201.8	1201.1
137.5°	1261.6	1262.8	1264.1	1264.5	1263.9	1263.5	1262.9	1262.3
140°	1298.9	1300.0	1301.1	1301.4	1300.8	1300.2	1299.8	1299.2
142.5°	1334.4	1335.2	1336.1	1336.1	1335.4	1334.6	1333.9	1333.1
145°	1383.9	1384.4	1385.0	1385.3	1385.3	1385.3	1385.3	1385.3
147.5°	1428.2	1428.8	1429.4	1429.0	1427.8	1426.5	1425.3	1424.0
150°	1455.4	1455.9	1456.5	1456.3	1455.6	1454.7	1454.0	1453.1
152.5°	1479.5	1480.5	1481.5	1481.4	1480.1	1478.8	1477.6	1476.4
155°	1512.8	1514.1	1515.5	1515.3	1513.7	1512.1	1510.5	1508.9
157.5°	1541.7	1543.3	1544.9	1544.6	1542.6	1540.5	1538.3	1536.3
160°	1558.1	1559.8	1561.4	1561.2	1559.3	1557.5	1555.6	1553.7
162.5°	1573.1	1575.0	1576.8	1576.9	1575.2	1573.6	1571.9	1570.2
165°	1593.2	1595.3	1597.5	1597.6	1595.7	1593.8	1592.0	1590.1
167.5°	1608.7	1610.8	1613.0	1613.0	1610.8	1608.7	1606.6	1604.4
170°	1617.4	1619.6	1621.7	1621.7	1619.6	1617.4	1615.2	1613.1
172.5°	1623.2	1625.4	1627.6	1627.4	1625.0	1622.7	1620.3	1618.0
175°	1630.2	1632.1	1634.0	1633.8	1631.7	1629.6	1627.4	1625.2
177.5°	1632.8	1634.6	1636.3	1636.1	1633.9	1631.7	1629.6	1627.4
180°	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3

(END OF REPORT)