

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332397-935

Luminaire Tested: **S123RDIW-S340D755U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332397-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D755U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3373.9 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332397-935

CATALOG NUMBER: S123RDIW-S340D755U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332397-935

CATALOG NUMBER: S123RDIW-S340D755U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35	28
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	78	69	62	57	71	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19	16
6	61	49	41	36	55	45	38	33	36	31	28	28	25	22	21	19	17	14
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	21	24	20	18	18	15	14	11
9	48	37	29	24	44	33	27	23	27	23	19	22	18	16	16	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5324	5324	5324
5°	5344	5271	5302
10°	5314	5205	5187
15°	5258	5084	5029
20°	5179	4931	4816
25°	5099	4760	4608
30°	4992	4561	4313
35°	4882	4365	4043
40°	4780	4131	3710
45°	4647	3902	3408
50°	4501	3641	3069
55°	4352	3342	2755
60°	4215	3023	2409
65°	4037	2677	2063
70°	3811	2247	1668
75°	3489	1768	1568
80°	3106	1568	1438
85°	2631	1383	1284



TEST NUMBER: P332397-935

CATALOG NUMBER: S123RDIW-S340D755U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.5	1.4
10°-20°	129.2	3.8
20°-30°	186.1	5.5
30°-40°	209.6	6.2
40°-50°	200.5	5.9
50°-60°	164.2	4.9
60°-70°	110.8	3.3
70°-80°	55.7	1.7
80°-90°	17.2	0.5
90°-100°	53.0	1.6
100°-110°	158.6	4.7
110°-120°	269.8	8.0
120°-130°	354.9	10.5
130°-140°	398.9	11.8
140°-150°	392.1	11.6
150°-160°	330.1	9.8
160°-170°	219.7	6.5
170°-180°	76.9	2.3
0°-30°	361.8	10.7
0°-40°	571.4	16.9
0°-60°	936.2	27.7
0°-90°	1119.9	33.2
90°-120°	481.4	14.3
90°-150°	1627.3	48.2
90°-180°	2254.0	66.8
0°-180°	3373.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	495	495	495	495	495	
5°	495	492	488	491	491	47
15°	472	467	456	454	451	133
25°	429	419	401	393	388	197
35°	372	356	332	315	308	232
45°	305	286	256	234	224	235
55°	232	211	178	156	147	208
65°	158	136	105	86	81	157
75°	84	64	42	39	38	89
85°	21	13	11	10	10	24
90°	1	7	15	18	19	3
95°	38	42	47	50	50	42
105°	144	145	151	151	152	154
115°	272	273	272	273	272	269
125°	398	399	398	396	393	354
135°	516	519	519	516	515	397
145°	626	627	629	628	626	391
155°	716	716	717	719	715	330
165°	780	778	778	782	778	220
175°	812	809	809	812	808	77
180°	814	814	814	814	814	



TEST NUMBER: P332397-935

CATALOG NUMBER: S123RDIW-S340D755U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	496.3	495.9	495.7	495.4	495.2	494.6	493.7	492.8	492.0	491.1	491.9
5°	494.6	494.2	493.8	493.4	492.8	492.1	491.0	490.0	488.9	487.8	488.6
7.5°	490.1	489.6	489.1	488.6	488.2	487.2	485.9	484.5	483.0	481.6	482.1
10°	486.2	485.6	485.0	484.4	483.7	482.6	481.0	479.4	477.8	476.2	476.3
12.5°	480.8	480.1	479.4	478.7	478.0	476.6	474.7	472.8	470.8	468.8	468.7
15°	471.8	470.8	469.8	468.8	467.9	466.1	463.6	461.2	458.7	456.2	455.7
17.5°	460.5	459.3	458.2	457.0	455.9	453.7	450.6	447.4	444.3	441.1	440.1
20°	452.1	450.7	449.3	447.9	446.4	444.0	440.7	437.2	433.9	430.5	429.3
22.5°	442.8	441.2	439.5	437.9	436.3	433.7	430.1	426.5	422.8	419.2	417.8
25°	429.3	427.1	424.8	422.6	420.3	417.2	413.1	409.0	404.8	400.8	398.9
27.5°	412.8	410.4	407.9	405.4	402.9	399.5	394.9	390.3	385.7	381.2	378.6
30°	401.6	398.9	396.2	393.6	390.9	387.0	382.0	377.0	372.0	367.0	364.0
32.5°	390.4	387.3	384.3	381.3	378.2	374.1	368.8	363.5	358.3	352.9	349.7
35°	371.5	368.2	365.1	361.9	358.7	354.3	348.8	343.2	337.7	332.2	328.4
37.5°	352.4	348.8	345.3	341.7	338.1	333.4	327.5	321.6	315.7	309.8	305.5
40°	340.2	336.3	332.3	328.5	324.5	319.3	313.1	306.7	300.4	294.0	289.5
42.5°	326.4	322.4	318.6	314.6	310.7	305.5	298.9	292.4	285.9	279.3	274.2
45°	305.3	301.3	297.3	293.3	289.2	283.8	277.0	270.1	263.2	256.3	251.2
47.5°	284.2	279.8	275.3	271.0	266.6	261.0	254.1	247.2	240.4	233.5	228.0
50°	268.8	264.6	260.5	256.2	252.0	246.3	239.1	231.9	224.6	217.4	211.9
52.5°	255.0	250.5	245.9	241.3	236.8	230.9	223.8	216.6	209.5	202.3	196.7
55°	231.9	227.5	223.2	218.8	214.4	208.4	200.9	193.3	185.7	178.1	173.0
57.5°	210.5	205.8	201.0	196.2	191.5	185.3	177.7	170.0	162.5	154.9	150.0
60°	195.8	190.9	186.0	181.1	176.2	170.0	162.6	155.2	147.8	140.4	135.6
62.5°	181.0	176.1	171.2	166.3	161.4	155.2	147.8	140.4	133.0	125.6	121.1
65°	158.5	153.6	148.7	143.8	138.9	132.9	126.0	119.0	112.1	105.1	100.7
67.5°	136.0	131.0	126.0	121.1	116.1	110.3	103.6	96.9	90.2	83.6	80.3
70°	121.1	116.3	111.5	106.7	101.9	96.3	90.1	83.9	77.7	71.4	68.3
72.5°	106.4	101.7	96.9	92.1	87.4	82.2	76.5	70.9	65.2	59.5	57.0
75°	83.9	79.6	75.3	71.0	66.7	62.2	57.3	52.3	47.4	42.5	41.7
77.5°	63.3	59.4	55.5	51.7	47.9	44.3	41.2	38.0	34.9	31.7	31.3
80°	50.1	46.5	42.9	39.2	35.6	32.8	30.9	29.0	27.1	25.3	25.0
82.5°	37.6	34.4	31.3	28.2	25.0	23.0	22.1	21.3	20.4	19.5	19.2
85°	21.3	19.3	17.3	15.4	13.4	12.3	12.1	11.8	11.5	11.2	11.0
87.5°	7.8	7.3	6.8	6.4	5.9	5.8	6.1	6.5	6.9	7.2	7.3
90°	0.6	2.1	3.4	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9
92.5°	15.5	16.4	17.4	18.3	19.3	20.3	21.4	22.5	23.5	24.5	25.0
95°	37.7	38.7	39.7	40.7	41.7	42.7	43.9	45.0	46.1	47.3	47.9
97.5°	67.0	67.7	68.4	69.2	69.9	70.7	71.5	72.3	73.2	74.0	74.6
100°	86.9	87.7	88.6	89.5	90.3	91.1	91.8	92.6	93.2	93.9	94.4
102.5°	109.9	110.5	111.0	111.4	111.9	112.7	113.7	114.6	115.5	116.4	116.8
105°	143.8	144.0	144.4	144.6	144.9	145.7	147.0	148.3	149.6	150.8	150.8
107.5°	183.1	183.3	183.5	183.7	183.8	184.2	184.7	185.2	185.7	186.2	186.7
110°	207.7	208.0	208.3	208.5	208.8	209.1	209.4	209.7	210.0	210.3	210.9



TEST NUMBER: P332397-935

CATALOG NUMBER: S123RDIW-S340D755U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	233.2	233.4	233.6	233.8	233.9	234.0	234.1	234.2	234.2	234.3	235.0
115°	271.6	272.0	272.4	272.9	273.3	273.4	273.1	272.9	272.5	272.2	272.4
117.5°	310.2	310.5	310.7	311.1	311.3	311.3	310.9	310.6	310.2	309.8	309.8
120°	334.2	335.1	336.0	336.8	337.7	337.7	337.0	336.3	335.6	334.8	334.8
122.5°	359.3	359.9	360.5	361.2	361.8	361.9	361.5	361.2	360.8	360.4	360.1
125°	397.5	398.0	398.4	398.8	399.2	399.2	399.0	398.7	398.4	398.1	397.6
127.5°	432.7	433.7	434.6	435.5	436.4	436.7	436.4	436.1	435.8	435.5	434.6
130°	456.3	457.4	458.6	459.7	460.8	461.2	460.8	460.4	459.9	459.5	458.9
132.5°	479.8	481.0	482.1	483.2	484.4	484.7	484.5	484.1	483.8	483.5	482.8
135°	515.7	516.6	517.5	518.3	519.1	519.5	519.4	519.2	519.1	518.9	518.3
137.5°	549.0	549.7	550.4	551.1	551.8	552.3	552.7	553.1	553.5	553.8	553.2
140°	572.0	572.7	573.4	574.1	574.8	575.2	575.4	575.5	575.7	575.8	575.7
142.5°	593.0	593.7	594.3	595.0	595.7	596.2	596.5	596.8	597.0	597.3	597.1
145°	625.7	625.9	626.2	626.5	626.8	627.2	627.6	628.0	628.4	628.9	628.7
147.5°	654.3	654.8	655.3	655.8	656.3	656.8	657.2	657.5	658.0	658.4	658.4
150°	674.2	674.5	674.8	675.1	675.4	675.6	675.9	676.2	676.5	676.7	676.7
152.5°	690.6	691.0	691.4	691.8	692.2	692.4	692.6	692.8	692.9	693.1	693.4
155°	716.4	716.4	716.4	716.4	716.4	716.4	716.6	716.8	716.9	717.0	717.6
157.5°	738.4	738.2	738.0	737.9	737.7	737.7	737.8	737.9	738.0	738.1	738.7
160°	752.2	751.9	751.7	751.3	751.1	750.9	750.9	750.9	750.9	750.9	751.7
162.5°	764.5	764.1	763.6	763.3	762.8	762.8	762.8	762.9	763.1	763.2	763.9
165°	780.3	779.9	779.5	779.0	778.6	778.3	778.3	778.3	778.3	778.3	779.2
167.5°	793.0	792.4	791.9	791.3	790.7	790.5	790.6	790.7	790.8	790.9	791.8
170°	800.1	799.5	799.0	798.4	797.8	797.5	797.5	797.5	797.5	797.5	798.6
172.5°	805.7	805.2	804.6	804.0	803.5	803.1	803.1	803.1	803.1	803.1	804.1
175°	811.6	811.1	810.5	809.9	809.3	809.1	809.1	809.1	809.1	809.1	809.9
177.5°	814.1	813.6	813.1	812.7	812.3	812.0	812.0	812.0	812.0	812.0	812.7
180°	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6



TEST NUMBER: P332397-935

CATALOG NUMBER: S123RDIW-S340D755U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	492.7	493.4	494.3	494.6	494.5	494.3	494.1	494.0
5°	489.5	490.3	491.0	491.4	491.2	491.0	490.9	490.7
7.5°	482.6	483.0	483.5	483.5	483.2	482.9	482.6	482.3
10°	476.4	476.5	476.6	476.4	476.0	475.5	475.0	474.6
12.5°	468.7	468.6	468.6	468.3	467.8	467.3	466.7	466.2
15°	455.2	454.8	454.3	453.8	453.2	452.5	451.9	451.3
17.5°	439.2	438.2	437.3	436.4	435.4	434.5	433.6	432.7
20°	428.2	427.0	425.9	424.7	423.6	422.6	421.5	420.4
22.5°	416.4	414.9	413.5	412.2	411.2	410.3	409.2	408.3
25°	397.0	395.2	393.3	391.8	390.9	389.9	388.9	388.0
27.5°	376.0	373.4	370.8	368.8	367.2	365.8	364.3	362.7
30°	361.0	358.0	355.0	352.8	351.3	349.9	348.4	347.0
32.5°	346.3	343.0	339.7	337.3	335.8	334.3	332.8	331.3
35°	324.5	320.6	316.8	314.1	312.5	310.9	309.3	307.7
37.5°	301.1	296.7	292.4	289.2	287.2	285.2	283.3	281.3
40°	284.8	280.2	275.5	272.2	270.1	268.1	266.0	264.0
42.5°	269.1	264.2	259.1	255.6	253.7	251.9	250.1	248.2
45°	246.2	241.1	236.0	232.4	230.3	228.2	226.0	223.9
47.5°	222.4	216.9	211.4	207.7	205.8	203.9	201.9	200.0
50°	206.4	200.9	195.4	191.6	189.5	187.4	185.4	183.3
52.5°	190.9	185.1	179.4	175.6	173.7	171.9	170.1	168.2
55°	167.8	162.6	157.5	153.9	152.2	150.4	148.6	146.8
57.5°	145.1	140.2	135.3	132.1	130.6	129.1	127.6	126.1
60°	130.8	126.0	121.1	118.0	116.5	114.9	113.5	111.9
62.5°	116.6	112.1	107.5	104.4	102.9	101.3	99.7	98.2
65°	96.3	92.0	87.6	85.0	83.9	83.0	82.1	81.0
67.5°	77.1	73.8	70.5	68.4	67.3	66.3	65.3	64.2
70°	65.2	62.1	58.9	56.9	55.9	54.9	53.9	53.0
72.5°	54.4	51.9	49.3	47.9	47.4	47.0	46.7	46.2
75°	40.7	39.9	38.9	38.4	38.2	38.1	37.9	37.7
77.5°	30.7	30.2	29.8	29.4	29.3	29.1	28.9	28.8
80°	24.7	24.5	24.2	24.0	23.8	23.6	23.4	23.2
82.5°	18.9	18.7	18.4	18.3	18.3	18.2	18.2	18.2
85°	10.8	10.7	10.5	10.4	10.4	10.4	10.4	10.4
87.5°	7.3	7.4	7.4	7.4	7.4	7.4	7.4	7.4
90°	16.4	17.0	17.7	18.0	18.3	18.6	18.9	19.2
92.5°	25.5	25.9	26.3	26.5	26.3	26.2	26.0	25.8
95°	48.4	49.0	49.6	49.9	49.9	49.9	49.9	49.9
97.5°	75.3	75.9	76.6	76.9	76.9	76.8	76.7	76.7
100°	94.8	95.2	95.7	96.0	96.3	96.6	96.9	97.1
102.5°	117.3	117.7	118.1	118.3	118.3	118.2	118.1	118.1
105°	150.8	150.8	150.8	150.9	151.3	151.5	151.8	152.1
107.5°	187.1	187.6	188.0	188.2	188.0	187.9	187.7	187.5
110°	211.4	212.0	212.5	212.7	212.4	212.1	211.8	211.5



TEST NUMBER: P332397-935

CATALOG NUMBER: S123RDIW-S340D755U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	235.7	236.3	237.0	237.3	237.3	237.2	237.1	237.1
115°	272.5	272.7	272.9	272.9	272.7	272.5	272.4	272.2
117.5°	309.8	309.7	309.7	309.5	309.1	308.7	308.3	307.9
120°	334.6	334.4	334.3	334.1	333.8	333.6	333.2	332.9
122.5°	359.7	359.3	359.0	358.6	358.2	357.7	357.4	357.0
125°	397.0	396.4	395.9	395.3	394.8	394.2	393.6	393.0
127.5°	433.9	433.1	432.3	431.5	430.9	430.2	429.6	429.0
130°	458.4	457.8	457.2	456.4	455.5	454.4	453.5	452.5
132.5°	482.2	481.5	480.8	480.1	479.3	478.5	477.8	477.0
135°	517.8	517.2	516.7	516.3	515.9	515.7	515.4	515.1
137.5°	552.6	552.0	551.5	550.9	550.4	549.7	549.2	548.7
140°	575.5	575.4	575.2	574.6	573.7	572.7	571.7	570.7
142.5°	597.0	596.8	596.7	596.2	595.5	594.7	593.9	593.1
145°	628.5	628.4	628.3	627.9	627.3	626.8	626.2	625.7
147.5°	658.4	658.4	658.4	658.0	657.1	656.3	655.4	654.5
150°	676.7	676.7	676.7	676.3	675.5	674.7	673.8	673.0
152.5°	693.6	693.8	694.1	693.8	693.0	692.3	691.6	690.9
155°	718.2	718.8	719.3	719.1	718.1	717.1	716.1	715.1
157.5°	739.3	739.9	740.5	740.4	739.6	738.8	738.0	737.2
160°	752.3	753.0	753.7	753.8	753.3	752.7	752.1	751.6
162.5°	764.6	765.3	766.0	765.9	765.0	764.1	763.2	762.2
165°	780.1	780.9	781.8	781.7	780.8	779.7	778.8	777.7
167.5°	792.6	793.6	794.4	794.4	793.6	792.6	791.8	790.9
170°	799.5	800.6	801.5	801.5	800.6	799.5	798.6	797.5
172.5°	804.9	805.8	806.7	806.7	805.6	804.7	803.7	802.7
175°	810.8	811.6	812.4	812.4	811.4	810.4	809.4	808.4
177.5°	813.4	814.1	814.8	814.7	813.9	813.0	812.3	811.5
180°	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6

(END OF REPORT)