

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332412-935

Luminaire Tested: **S123RDIW-S560D460U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332412-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D460U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3426.4 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.23
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332412-935

CATALOG NUMBER: S123RDIW-S560D460U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332412-935

CATALOG NUMBER: S123RDIW-S560D460U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	68	66	63	59	56	54	51	47	45	43	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	33
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	32	29
5	70	58	50	44	64	54	47	42	47	42	37	40	36	33	34	31	28	25
6	64	52	44	39	59	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	47	39	34	55	44	37	32	39	33	29	33	29	26	29	25	23	20
8	55	43	35	30	51	40	34	29	35	30	26	31	26	23	26	23	20	18
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8753	8753	8753
5°	8787	8666	8715
10°	8737	8557	8528
15°	8643	8357	8269
20°	8514	8107	7918
25°	8381	7826	7574
30°	8206	7501	7091
35°	8025	7176	6646
40°	7859	6794	6097
45°	7640	6416	5602
50°	7400	5987	5047
55°	7156	5495	4530
60°	6928	4969	3961
65°	6635	4401	3393
70°	6266	3695	2738
75°	5731	2907	2578
80°	5114	2579	2368
85°	4323	2272	2112



TEST NUMBER: P332412-935

CATALOG NUMBER: S123RDIW-S560D460U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.4	2.2
10°-20°	212.5	6.2
20°-30°	305.9	8.9
30°-40°	344.6	10.1
40°-50°	329.7	9.6
50°-60°	270.0	7.9
60°-70°	182.2	5.3
70°-80°	91.6	2.7
80°-90°	25.7	0.8
90°-100°	18.9	0.6
100°-110°	90.2	2.6
110°-120°	216.7	6.3
120°-130°	276.0	8.1
130°-140°	294.8	8.6
140°-150°	275.7	8.0
150°-160°	222.4	6.5
160°-170°	143.5	4.2
170°-180°	49.5	1.4
0°-30°	594.8	17.4
0°-40°	939.4	27.4
0°-60°	1539.1	44.9
0°-90°	1838.6	53.7
90°-120°	325.9	9.5
90°-150°	1172.4	34.2
90°-180°	1588.0	46.3
0°-180°	3426.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	813	813	813	813	813	
5°	813	810	802	808	807	77
15°	776	768	750	747	742	218
25°	706	688	659	645	638	324
35°	611	586	546	519	506	382
45°	502	471	422	385	368	387
55°	381	348	293	256	241	342
65°	260	223	173	142	133	258
75°	138	106	70	64	62	147
85°	35	21	18	17	17	39
90°	0	4	9	11	12	3
95°	24	9	12	15	15	29
105°	115	117	85	20	17	122
115°	216	219	222	226	228	213
125°	305	308	309	310	311	272
135°	379	382	383	384	383	292
145°	438	440	441	442	442	274
155°	482	482	482	484	482	222
165°	509	508	507	510	508	144
175°	521	519	519	522	519	50
180°	521	521	521	521	521	



TEST NUMBER: P332412-935

CATALOG NUMBER: S123RDIW-S560D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2
2.5°	815.9	815.4	814.9	814.4	814.0	813.0	811.7	810.2	808.8	807.4	808.7
5°	813.2	812.5	811.8	811.1	810.3	809.1	807.3	805.6	803.7	802.0	803.3
7.5°	805.7	804.9	804.1	803.3	802.5	801.0	798.7	796.4	794.1	791.9	792.6
10°	799.4	798.3	797.3	796.3	795.3	793.4	790.8	788.2	785.5	782.9	783.0
12.5°	790.4	789.3	788.1	787.0	785.8	783.7	780.4	777.2	774.0	770.8	770.7
15°	775.6	774.0	772.4	770.8	769.2	766.3	762.2	758.1	754.0	749.9	749.2
17.5°	757.0	755.2	753.3	751.4	749.5	746.0	740.7	735.6	730.3	725.1	723.6
20°	743.3	741.0	738.7	736.2	733.9	730.0	724.4	718.8	713.3	707.7	705.8
22.5°	728.0	725.3	722.6	719.9	717.2	712.9	707.0	701.0	695.2	689.2	686.8
25°	705.7	702.1	698.4	694.7	691.0	685.9	679.1	672.4	665.6	658.9	655.8
27.5°	678.6	674.6	670.5	666.5	662.5	656.7	649.2	641.7	634.2	626.7	622.4
30°	660.2	655.8	651.4	647.0	642.7	636.3	628.1	619.9	611.7	603.5	598.5
32.5°	641.7	636.8	631.8	626.8	621.8	615.0	606.3	597.6	588.9	580.2	574.8
35°	610.7	605.5	600.2	595.0	589.6	582.5	573.3	564.3	555.2	546.1	539.8
37.5°	579.4	573.5	567.7	561.7	555.9	548.1	538.4	528.7	519.0	509.3	502.1
40°	559.3	552.8	546.4	539.9	533.5	525.0	514.7	504.3	493.9	483.5	475.8
42.5°	536.6	530.1	523.7	517.3	510.8	502.2	491.5	480.7	469.9	459.2	450.8
45°	501.9	495.3	488.7	482.2	475.5	466.6	455.3	444.0	432.7	421.5	413.1
47.5°	467.2	459.9	452.7	445.5	438.2	429.0	417.7	406.4	395.1	383.8	374.8
50°	441.9	435.0	428.1	421.2	414.3	404.9	393.0	381.3	369.4	357.5	348.4
52.5°	419.2	411.7	404.2	396.7	389.3	379.7	367.9	356.2	344.4	332.7	323.2
55°	381.3	374.0	366.9	359.6	352.5	342.7	330.2	317.8	305.3	292.8	284.3
57.5°	346.1	338.3	330.5	322.6	314.8	304.6	292.1	279.7	267.1	254.6	246.6
60°	321.8	313.8	305.7	297.6	289.6	279.5	267.3	255.2	243.0	230.8	222.9
62.5°	297.6	289.6	281.5	273.4	265.4	255.2	243.1	230.9	218.7	206.6	199.1
65°	260.5	252.4	244.4	236.3	228.3	218.5	207.1	195.7	184.3	172.8	165.7
67.5°	223.4	215.3	207.2	199.0	190.9	181.3	170.3	159.4	148.4	137.4	132.1
70°	199.1	191.2	183.4	175.5	167.6	158.4	148.2	137.9	127.7	117.4	112.3
72.5°	174.9	167.1	159.3	151.5	143.7	135.2	125.9	116.5	107.2	97.9	93.7
75°	137.8	130.8	123.8	116.8	109.7	102.1	94.1	86.0	78.0	69.9	68.4
77.5°	104.1	97.7	91.4	85.0	78.6	72.8	67.7	62.5	57.3	52.1	51.3
80°	82.5	76.5	70.4	64.4	58.4	53.9	50.8	47.7	44.6	41.6	41.1
82.5°	61.9	56.7	51.5	46.3	41.1	37.8	36.3	35.0	33.5	32.0	31.6
85°	35.0	31.8	28.5	25.3	22.0	20.2	19.8	19.4	18.9	18.4	18.2
87.5°	12.7	11.6	10.5	9.4	8.3	7.8	8.0	8.3	8.5	8.7	8.7
90°	0.3	1.2	2.1	2.9	3.8	4.8	5.9	7.1	8.2	9.3	9.6
92.5°	7.2	7.0	6.7	6.5	6.2	6.5	7.4	8.2	9.0	9.9	10.4
95°	23.6	20.1	16.5	13.0	9.5	8.2	9.1	10.1	11.0	12.0	12.6
97.5°	47.4	45.8	44.3	42.7	41.1	37.2	31.0	24.8	18.7	12.5	13.2
100°	65.3	67.1	68.8	70.5	72.2	66.4	53.0	39.6	26.2	12.7	13.4
102.5°	85.8	87.0	88.3	89.5	90.7	84.0	69.4	54.8	40.1	25.5	23.3
105°	115.3	116.2	117.2	118.1	119.1	115.6	107.9	100.2	92.5	84.7	69.5
107.5°	146.4	147.1	147.9	148.6	149.4	150.4	151.6	152.8	154.0	155.2	144.1
110°	167.1	167.8	168.5	169.2	169.9	170.7	171.6	172.5	173.5	174.4	171.6



TEST NUMBER: P332412-935

CATALOG NUMBER: S123RDIW-S560D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	186.9	187.5	188.1	188.7	189.4	190.2	191.1	192.1	193.0	194.0	194.0
115°	216.2	216.7	217.2	217.7	218.3	219.0	219.7	220.5	221.3	222.1	222.9
117.5°	244.6	245.3	245.9	246.5	247.2	247.7	248.1	248.5	248.9	249.3	249.9
120°	262.3	263.0	263.8	264.6	265.4	265.9	266.1	266.4	266.7	266.9	267.6
122.5°	280.3	280.9	281.5	282.1	282.8	283.3	283.6	283.9	284.2	284.6	285.0
125°	304.8	305.5	306.2	306.9	307.5	308.1	308.4	308.8	309.1	309.4	309.6
127.5°	328.6	329.3	330.0	330.7	331.4	331.9	332.3	332.8	333.2	333.6	333.9
130°	343.5	344.2	344.9	345.6	346.3	346.8	347.2	347.5	347.8	348.1	348.4
132.5°	357.7	358.4	359.1	359.8	360.5	360.9	361.3	361.5	361.8	362.1	362.4
135°	379.4	380.0	380.5	381.0	381.5	381.9	382.3	382.6	383.0	383.3	383.6
137.5°	398.0	398.7	399.3	400.0	400.6	401.1	401.3	401.5	401.7	401.8	402.3
140°	410.4	411.0	411.5	412.0	412.5	412.8	413.1	413.4	413.6	413.9	414.2
142.5°	421.9	422.4	422.9	423.4	424.0	424.3	424.6	424.8	425.1	425.3	425.6
145°	437.9	438.5	439.1	439.7	440.3	440.7	440.8	441.0	441.2	441.3	441.5
147.5°	453.0	453.4	453.7	454.2	454.5	454.9	455.0	455.2	455.4	455.6	455.7
150°	462.3	462.5	462.8	463.0	463.3	463.5	463.6	463.8	464.0	464.2	464.3
152.5°	470.6	470.7	470.9	471.0	471.1	471.2	471.3	471.4	471.5	471.7	471.9
155°	482.3	482.2	482.0	481.9	481.7	481.6	481.7	481.8	481.9	482.0	482.4
157.5°	491.5	491.5	491.5	491.5	491.5	491.4	491.3	491.2	491.1	491.0	491.5
160°	497.1	497.0	496.9	496.8	496.7	496.6	496.5	496.5	496.4	496.3	496.8
162.5°	502.3	502.1	501.9	501.7	501.4	501.3	501.2	501.1	501.0	500.9	501.5
165°	508.7	508.4	508.2	507.9	507.6	507.5	507.4	507.3	507.2	507.1	507.8
167.5°	513.7	513.3	513.0	512.6	512.3	512.1	512.1	512.1	512.1	512.1	512.8
170°	516.4	516.1	515.7	515.4	515.1	514.9	514.9	514.9	514.9	514.9	515.6
172.5°	518.2	517.9	517.5	517.0	516.6	516.4	516.5	516.6	516.7	516.7	517.4
175°	520.6	520.2	519.8	519.4	518.9	518.8	518.8	518.9	519.0	519.1	519.7
177.5°	521.2	520.9	520.6	520.2	519.9	519.8	519.9	519.9	520.0	520.0	520.6
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6



TEST NUMBER: P332412-935

CATALOG NUMBER: S123RDIW-S560D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2
2.5°	810.0	811.3	812.6	813.1	812.9	812.6	812.4	812.2
5°	804.6	806.0	807.3	807.8	807.5	807.2	806.9	806.6
7.5°	793.3	794.0	794.8	794.9	794.4	793.9	793.4	792.9
10°	783.2	783.3	783.4	783.2	782.5	781.7	781.0	780.2
12.5°	770.6	770.5	770.4	769.9	769.0	768.2	767.4	766.5
15°	748.5	747.7	747.0	746.1	745.0	744.1	743.0	742.0
17.5°	722.0	720.5	718.8	717.4	715.8	714.3	712.7	711.3
20°	703.9	702.0	700.1	698.3	696.5	694.7	692.9	691.2
22.5°	684.5	682.1	679.8	677.7	676.1	674.4	672.8	671.1
25°	652.7	649.6	646.6	644.2	642.7	641.0	639.4	637.7
27.5°	618.1	613.9	609.6	606.2	603.7	601.3	598.8	596.3
30°	593.5	588.5	583.6	579.9	577.6	575.2	572.8	570.5
32.5°	569.4	563.9	558.4	554.5	552.1	549.6	547.1	544.7
35°	533.5	527.2	520.9	516.4	513.8	511.2	508.5	505.8
37.5°	495.0	487.8	480.7	475.5	472.3	469.0	465.7	462.4
40°	468.2	460.5	453.0	447.5	444.1	440.7	437.4	433.9
42.5°	442.6	434.2	425.9	420.2	417.2	414.1	411.1	408.1
45°	404.8	396.4	388.1	382.1	378.6	375.1	371.5	368.0
47.5°	365.7	356.6	347.5	341.4	338.3	335.1	332.0	328.8
50°	339.3	330.2	321.2	314.9	311.5	308.2	304.8	301.4
52.5°	313.8	304.4	294.9	288.7	285.7	282.7	279.7	276.6
55°	275.9	267.3	258.8	253.1	250.2	247.3	244.4	241.4
57.5°	238.5	230.5	222.5	217.2	214.7	212.2	209.7	207.2
60°	215.0	207.1	199.1	194.0	191.5	189.0	186.5	184.0
62.5°	191.7	184.3	176.8	171.8	169.2	166.5	163.9	161.4
65°	158.4	151.3	144.0	139.7	138.1	136.5	134.8	133.2
67.5°	126.7	121.3	116.0	112.4	110.7	109.0	107.3	105.6
70°	107.1	102.0	96.9	93.5	91.9	90.3	88.7	87.0
72.5°	89.5	85.3	81.1	78.7	78.0	77.3	76.6	75.9
75°	67.0	65.5	64.1	63.2	62.9	62.6	62.3	62.0
77.5°	50.5	49.8	48.9	48.4	48.1	47.8	47.5	47.2
80°	40.6	40.2	39.8	39.4	39.2	38.8	38.6	38.2
82.5°	31.2	30.7	30.3	30.0	30.0	30.0	29.9	29.8
85°	17.9	17.6	17.3	17.1	17.1	17.1	17.1	17.1
87.5°	8.6	8.6	8.5	8.4	8.4	8.3	8.2	8.1
90°	10.0	10.3	10.7	10.9	11.1	11.3	11.5	11.6
92.5°	11.0	11.5	12.1	12.4	12.6	12.7	12.7	12.8
95°	13.2	13.8	14.4	14.7	14.7	14.7	14.7	14.7
97.5°	13.9	14.6	15.2	15.6	15.7	15.8	15.8	15.9
100°	14.1	14.8	15.5	15.9	16.0	16.1	16.2	16.3
102.5°	21.2	19.0	17.0	15.9	16.1	16.3	16.4	16.5
105°	54.2	39.1	23.8	16.4	16.5	16.7	16.9	17.0
107.5°	132.9	121.8	110.6	99.4	87.8	76.4	64.9	53.5
110°	168.8	165.9	163.1	155.6	143.3	131.0	118.6	106.4



TEST NUMBER: P332412-935

CATALOG NUMBER: S123RDIW-S560D460U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	194.1	194.1	194.2	192.9	190.3	187.7	185.1	182.5
115°	223.8	224.6	225.5	226.1	226.4	226.8	227.1	227.5
117.5°	250.6	251.3	252.0	252.4	252.4	252.5	252.6	252.7
120°	268.3	269.0	269.7	270.0	270.0	270.0	270.0	270.0
122.5°	285.5	286.0	286.5	286.7	286.8	286.9	287.0	287.1
125°	309.8	310.0	310.1	310.3	310.5	310.6	310.8	311.0
127.5°	334.2	334.4	334.7	334.8	334.6	334.4	334.2	334.1
130°	348.8	349.1	349.5	349.6	349.4	349.2	349.0	348.9
132.5°	362.7	363.1	363.4	363.5	363.3	363.0	362.7	362.6
135°	383.8	384.1	384.4	384.4	384.1	383.8	383.6	383.3
137.5°	402.7	403.0	403.5	403.6	403.5	403.3	403.1	402.9
140°	414.6	414.9	415.3	415.3	415.2	415.0	414.8	414.7
142.5°	425.9	426.2	426.5	426.5	426.2	426.0	425.8	425.5
145°	441.7	441.9	442.0	442.1	442.1	442.1	442.1	442.1
147.5°	455.9	456.1	456.2	456.1	455.7	455.3	455.0	454.5
150°	464.5	464.7	464.9	464.9	464.6	464.3	464.1	463.8
152.5°	472.3	472.5	472.9	472.8	472.4	472.0	471.7	471.2
155°	482.8	483.3	483.7	483.6	483.1	482.6	482.1	481.6
157.5°	492.1	492.6	493.1	493.0	492.3	491.7	491.0	490.3
160°	497.3	497.8	498.3	498.3	497.7	497.1	496.5	495.9
162.5°	502.1	502.7	503.3	503.3	502.7	502.2	501.7	501.2
165°	508.5	509.2	509.9	509.9	509.3	508.8	508.2	507.6
167.5°	513.5	514.1	514.8	514.8	514.1	513.5	512.8	512.1
170°	516.3	516.9	517.6	517.6	516.9	516.3	515.6	514.9
172.5°	518.1	518.8	519.4	519.4	518.7	517.9	517.2	516.4
175°	520.3	520.9	521.5	521.5	520.8	520.1	519.4	518.8
177.5°	521.2	521.7	522.3	522.2	521.5	520.8	520.1	519.4
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6

(END OF REPORT)