

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332203-930

Luminaire Tested: **S123DIW-S1000D1320U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332203-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S1000D1320U930-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7091.6 lumens  
Efficiency: N/A  
Efficacy: 101.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332203-930

CATALOG NUMBER: S123DIW-S1000D1320U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332203-930

CATALOG NUMBER: S123DIW-S1000D1320U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40
2	88	81	75	70	81	75	69	65	63	59	55	52	49	47	42	40	38	33
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	34	32	28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	42	62	52	45	39	44	38	34	37	32	29	30	27	24	21
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21	18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	21	19	16
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	23	19	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13891	13891	13891
5°	13956	13765	13861
10°	13864	13645	13729
15°	13701	13490	13515
20°	13512	13270	13283
25°	13258	13007	12981
30°	12978	12716	12619
35°	12686	12408	12248
40°	12381	12067	11880
45°	12044	11756	11469
50°	11707	11372	11055
55°	11265	10975	10640
60°	10820	10512	10176
65°	10427	10004	9694
70°	9847	9429	9010
75°	9000	8675	8305
80°	8114	7773	7705
85°	7126	6854	6570



TEST NUMBER: P332203-930

CATALOG NUMBER: S123DIW-S1000D1320U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.6	1.7
10°-20°	343.3	4.8
20°-30°	507.0	7.1
30°-40°	592.3	8.4
40°-50°	595.5	8.4
50°-60°	523.1	7.4
60°-70°	389.7	5.5
70°-80°	222.0	3.1
80°-90°	67.7	1.0
90°-100°	87.7	1.2
100°-110°	262.5	3.7
110°-120°	446.4	6.3
120°-130°	587.2	8.3
130°-140°	660.0	9.3
140°-150°	648.8	9.1
150°-160°	546.2	7.7
160°-170°	363.6	5.1
170°-180°	127.3	1.8
0°-30°	971.9	13.7
0°-40°	1564.1	22.1
0°-60°	2682.6	37.8
0°-90°	3362.0	47.4
90°-120°	796.6	11.2
90°-150°	2692.5	38.0
90°-180°	3730.0	52.6
0°-180°	7091.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1290	1290	1290	1290	1290	
5°	1292	1286	1274	1284	1283	122
15°	1230	1224	1211	1219	1213	346
25°	1116	1109	1095	1096	1093	514
35°	965	958	944	938	932	604
45°	791	786	772	759	753	611
55°	600	598	585	573	567	538
65°	409	404	393	384	381	404
75°	216	212	209	203	200	231
85°	58	56	56	53	53	63
90°	1	12	25	29	32	7
95°	62	70	78	82	82	70
105°	238	240	250	250	252	255
115°	449	452	450	451	450	444
125°	658	661	659	655	650	586
135°	853	859	859	854	852	657
145°	1035	1037	1040	1039	1035	646
155°	1185	1185	1186	1190	1183	545
165°	1291	1288	1288	1294	1287	364
175°	1343	1339	1339	1344	1338	128
180°	1346	1346	1346	1346	1346	



TEST NUMBER: P332203-930

CATALOG NUMBER: S123DIW-S1000D1320U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1294.9	1294.2	1293.4	1292.6	1291.8	1290.3	1288.2	1286.0	1283.9	1281.7	1283.6
5°	1291.6	1290.4	1289.2	1287.9	1286.7	1284.7	1282.1	1279.3	1276.6	1273.9	1276.4
7.5°	1279.0	1277.7	1276.5	1275.3	1274.1	1272.0	1269.3	1266.4	1263.6	1260.8	1263.0
10°	1268.4	1267.1	1265.8	1264.6	1263.4	1261.2	1258.0	1254.7	1251.6	1248.4	1250.6
12.5°	1254.1	1253.1	1252.1	1251.0	1250.0	1248.0	1245.0	1241.9	1238.9	1235.9	1237.5
15°	1229.5	1228.5	1227.5	1226.5	1225.6	1223.4	1220.3	1217.1	1213.8	1210.6	1212.6
17.5°	1200.9	1199.5	1198.3	1197.0	1195.7	1193.5	1190.3	1187.1	1183.9	1180.6	1182.0
20°	1179.6	1178.1	1176.6	1175.1	1173.6	1171.3	1168.1	1164.9	1161.7	1158.5	1159.4
22.5°	1155.6	1154.1	1152.7	1151.1	1149.7	1147.4	1144.1	1140.9	1137.8	1134.5	1135.3
25°	1116.3	1114.8	1113.4	1111.9	1110.4	1108.1	1104.8	1101.6	1098.5	1095.2	1095.4
27.5°	1074.4	1072.9	1071.5	1070.1	1068.6	1066.2	1062.7	1059.3	1055.8	1052.4	1052.6
30°	1044.2	1042.9	1041.7	1040.5	1039.3	1036.9	1033.5	1030.0	1026.5	1023.1	1023.1
32.5°	1014.0	1012.4	1010.7	1009.1	1007.5	1005.3	1002.7	1000.0	997.4	994.7	993.3
35°	965.4	963.9	962.5	961.0	959.4	957.2	953.9	950.7	947.5	944.3	942.8
37.5°	915.7	913.8	911.9	910.0	908.2	905.6	902.4	899.1	895.9	892.6	890.8
40°	881.1	879.5	878.1	876.6	875.1	872.7	869.2	865.8	862.3	858.8	856.9
42.5°	846.4	844.7	843.1	841.4	839.8	837.1	833.7	830.3	826.8	823.4	821.4
45°	791.2	790.2	789.2	788.2	787.3	785.1	782.0	778.7	775.5	772.3	769.4
47.5°	736.4	734.9	733.5	732.1	730.7	728.4	725.5	722.4	719.4	716.4	713.5
50°	699.1	697.8	696.6	695.4	694.1	691.9	688.7	685.5	682.3	679.1	676.4
52.5°	660.0	659.2	658.4	657.5	656.6	654.5	651.2	647.8	644.3	640.9	638.6
55°	600.3	600.1	599.8	599.6	599.3	597.6	594.4	591.2	588.0	584.8	582.0
57.5°	543.5	542.7	541.8	541.0	540.1	538.4	535.9	533.3	530.8	528.2	525.8
60°	502.6	502.4	502.1	501.9	501.7	500.1	497.1	494.2	491.2	488.3	486.0
62.5°	466.3	465.6	465.0	464.3	463.7	461.9	458.9	456.0	453.1	450.0	447.8
65°	409.4	408.2	407.0	405.8	404.6	402.7	400.2	397.8	395.3	392.8	390.9
67.5°	349.4	348.2	347.2	346.1	345.0	343.5	341.6	339.7	337.9	336.0	334.3
70°	312.9	311.4	310.0	308.5	307.0	305.5	304.0	302.6	301.1	299.6	297.9
72.5°	274.8	273.7	272.6	271.5	270.4	269.0	267.3	265.7	264.0	262.3	260.8
75°	216.4	215.4	214.4	213.4	212.5	211.6	210.8	210.1	209.4	208.6	207.4
77.5°	164.7	164.1	163.5	163.1	162.5	161.8	160.9	160.0	159.1	158.2	157.4
80°	130.9	130.2	129.5	128.7	128.0	127.3	126.9	126.4	125.9	125.4	125.1
82.5°	98.1	97.9	97.8	97.7	97.5	97.3	97.3	97.2	97.1	97.0	96.5
85°	57.7	57.2	56.7	56.3	55.8	55.5	55.5	55.5	55.5	55.5	55.0
87.5°	23.3	23.2	23.1	22.9	22.8	23.0	23.4	23.8	24.2	24.6	24.6
90°	1.1	3.4	5.8	8.1	10.4	13.1	16.2	19.2	22.3	25.4	26.3
92.5°	25.6	27.1	28.8	30.4	32.0	33.7	35.4	37.1	38.9	40.6	41.3
95°	62.4	64.0	65.7	67.3	69.0	70.8	72.6	74.5	76.4	78.3	79.2
97.5°	110.8	112.0	113.2	114.5	115.7	117.0	118.4	119.7	121.1	122.5	123.5
100°	143.8	145.2	146.6	148.1	149.4	150.7	151.9	153.1	154.3	155.5	156.1
102.5°	181.9	182.7	183.6	184.4	185.2	186.5	188.0	189.6	191.1	192.7	193.4
105°	237.9	238.4	238.9	239.3	239.8	241.1	243.2	245.3	247.4	249.6	249.6
107.5°	303.0	303.4	303.6	303.9	304.2	304.8	305.6	306.5	307.3	308.1	308.9
110°	343.6	344.1	344.6	345.0	345.5	346.0	346.5	347.0	347.4	347.9	348.9



TEST NUMBER: P332203-930

CATALOG NUMBER: S123DIW-S1000D1320U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	386.0	386.2	386.5	386.8	387.1	387.3	387.3	387.4	387.6	387.7	388.8
115°	449.4	450.1	450.8	451.5	452.2	452.3	451.8	451.4	450.9	450.5	450.7
117.5°	513.3	513.7	514.2	514.7	515.2	515.1	514.5	513.9	513.2	512.7	512.6
120°	553.0	554.4	555.9	557.3	558.6	558.8	557.6	556.4	555.3	554.1	553.8
122.5°	594.5	595.5	596.6	597.6	598.6	598.8	598.2	597.6	597.0	596.4	595.7
125°	657.7	658.4	659.1	659.8	660.6	660.6	660.1	659.7	659.3	658.8	657.9
127.5°	716.1	717.6	719.1	720.6	722.1	722.6	722.1	721.5	721.1	720.6	719.2
130°	755.0	756.8	758.8	760.7	762.5	763.1	762.4	761.7	761.0	760.3	759.4
132.5°	793.9	795.8	797.7	799.6	801.4	802.1	801.6	801.1	800.5	800.1	798.9
135°	853.4	854.8	856.1	857.5	859.0	859.6	859.3	859.1	858.8	858.6	857.7
137.5°	908.3	909.5	910.7	911.8	913.1	914.0	914.5	915.2	915.7	916.4	915.3
140°	946.4	947.5	948.8	949.9	951.1	951.8	952.0	952.3	952.5	952.8	952.5
142.5°	981.0	982.3	983.4	984.6	985.8	986.6	987.0	987.4	987.8	988.3	988.1
145°	1035.2	1035.7	1036.2	1036.7	1037.1	1037.7	1038.4	1039.1	1039.8	1040.5	1040.2
147.5°	1082.6	1083.5	1084.3	1085.2	1086.0	1086.7	1087.4	1088.0	1088.7	1089.3	1089.3
150°	1115.6	1116.1	1116.6	1117.0	1117.4	1117.9	1118.4	1118.8	1119.3	1119.8	1119.8
152.5°	1142.6	1143.3	1143.9	1144.6	1145.3	1145.7	1146.1	1146.3	1146.6	1146.9	1147.3
155°	1185.4	1185.4	1185.4	1185.4	1185.4	1185.5	1185.7	1185.9	1186.2	1186.4	1187.4
157.5°	1221.7	1221.5	1221.2	1220.9	1220.6	1220.6	1220.7	1220.9	1221.2	1221.3	1222.3
160°	1244.6	1244.1	1243.7	1243.2	1242.7	1242.4	1242.4	1242.4	1242.4	1242.4	1243.7
162.5°	1264.9	1264.2	1263.6	1262.9	1262.2	1262.0	1262.2	1262.4	1262.6	1262.7	1264.0
165°	1291.1	1290.4	1289.7	1289.0	1288.3	1287.9	1287.9	1287.9	1287.9	1287.9	1289.3
167.5°	1312.1	1311.1	1310.2	1309.2	1308.3	1307.9	1308.1	1308.3	1308.5	1308.6	1310.1
170°	1323.9	1323.0	1322.0	1321.1	1320.1	1319.6	1319.6	1319.6	1319.6	1319.6	1321.3
172.5°	1333.2	1332.3	1331.3	1330.4	1329.4	1328.9	1328.9	1328.9	1328.9	1328.9	1330.4
175°	1343.0	1342.0	1341.1	1340.1	1339.1	1338.7	1338.7	1338.7	1338.7	1338.7	1340.1
177.5°	1347.0	1346.2	1345.4	1344.7	1343.9	1343.5	1343.5	1343.5	1343.5	1343.5	1344.7
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1



TEST NUMBER: P332203-930

CATALOG NUMBER: S123DIW-S1000D1320U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1285.6	1287.6	1289.6	1290.5	1290.2	1290.0	1289.8	1289.6
5°	1278.8	1281.2	1283.8	1284.7	1284.3	1283.8	1283.3	1282.8
7.5°	1265.3	1267.5	1269.7	1270.6	1270.3	1270.1	1269.7	1269.4
10°	1252.8	1255.0	1257.3	1258.1	1257.6	1257.1	1256.6	1256.1
12.5°	1239.2	1240.8	1242.4	1243.1	1242.8	1242.5	1242.2	1241.9
15°	1214.6	1216.5	1218.5	1218.8	1217.3	1215.8	1214.3	1212.8
17.5°	1183.4	1184.8	1186.2	1186.6	1186.1	1185.5	1185.0	1184.5
20°	1160.4	1161.5	1162.5	1162.5	1161.8	1161.1	1160.3	1159.6
22.5°	1136.1	1136.9	1137.7	1137.6	1136.7	1135.7	1134.8	1133.8
25°	1095.7	1096.0	1096.3	1096.0	1095.2	1094.5	1093.7	1093.0
27.5°	1052.8	1053.0	1053.2	1052.8	1051.9	1050.9	1050.0	1049.0
30°	1023.1	1023.1	1023.1	1022.2	1020.5	1018.8	1017.1	1015.3
32.5°	991.9	990.6	989.2	988.0	987.1	986.1	985.2	984.2
35°	941.3	939.9	938.4	937.0	935.8	934.6	933.4	932.1
37.5°	889.1	887.3	885.5	884.2	883.5	882.6	881.8	881.1
40°	854.9	853.0	851.0	849.5	848.5	847.5	846.5	845.5
42.5°	819.4	817.4	815.5	814.0	813.0	812.0	811.1	810.1
45°	766.4	763.4	760.5	758.4	757.2	755.9	754.7	753.4
47.5°	710.5	707.7	704.7	702.8	701.6	700.6	699.5	698.4
50°	673.7	671.0	668.2	666.2	664.7	663.2	661.7	660.2
52.5°	636.3	634.0	631.7	629.7	628.3	626.8	625.3	623.9
55°	579.4	576.7	574.0	571.9	570.7	569.5	568.3	567.0
57.5°	523.3	521.0	518.5	516.6	515.2	513.7	512.3	510.9
60°	483.8	481.6	479.4	477.7	476.4	475.2	473.9	472.7
62.5°	445.6	443.4	441.2	439.7	438.8	438.0	437.2	436.3
65°	388.9	386.9	384.9	383.6	382.9	382.1	381.3	380.6
67.5°	332.6	330.8	329.1	327.8	326.7	325.6	324.6	323.6
70°	296.1	294.4	292.7	291.2	290.0	288.8	287.6	286.3
72.5°	259.3	257.7	256.2	255.1	254.5	253.8	253.2	252.6
75°	206.2	204.9	203.7	202.7	201.9	201.2	200.5	199.7
77.5°	156.5	155.7	154.9	154.5	154.5	154.5	154.5	154.5
80°	124.9	124.7	124.4	124.3	124.3	124.3	124.3	124.3
82.5°	96.1	95.6	95.2	94.9	94.7	94.5	94.3	94.1
85°	54.5	54.0	53.5	53.2	53.2	53.2	53.2	53.2
87.5°	24.6	24.5	24.5	24.6	24.7	24.8	24.9	24.9
90°	27.2	28.2	29.1	29.8	30.3	30.8	31.2	31.7
92.5°	42.1	42.9	43.6	43.9	43.5	43.3	43.0	42.7
95°	80.1	81.0	82.0	82.5	82.5	82.5	82.5	82.5
97.5°	124.6	125.7	126.8	127.3	127.2	127.1	127.0	126.9
100°	156.9	157.5	158.2	158.8	159.3	159.8	160.3	160.7
102.5°	194.0	194.8	195.5	195.8	195.7	195.6	195.5	195.4
105°	249.6	249.6	249.6	249.8	250.3	250.7	251.2	251.7
107.5°	309.7	310.4	311.1	311.4	311.1	310.8	310.5	310.2
110°	349.8	350.7	351.6	351.9	351.4	351.0	350.5	350.0





TEST NUMBER: P332203-930

CATALOG NUMBER: S123DIW-S1000D1320U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	389.9	391.0	392.2	392.6	392.6	392.5	392.4	392.3
115°	450.9	451.2	451.4	451.4	451.2	450.9	450.7	450.5
117.5°	512.6	512.5	512.4	512.1	511.4	510.8	510.1	509.5
120°	553.6	553.4	553.2	552.8	552.4	551.9	551.4	550.9
122.5°	595.2	594.5	593.9	593.3	592.6	592.0	591.3	590.7
125°	656.9	656.0	655.0	654.1	653.1	652.2	651.3	650.3
127.5°	717.9	716.6	715.3	714.0	713.0	711.9	710.9	709.7
130°	758.4	757.5	756.5	755.2	753.6	752.0	750.3	748.7
132.5°	797.8	796.6	795.6	794.3	793.0	791.8	790.5	789.3
135°	856.7	855.8	854.8	854.2	853.7	853.2	852.7	852.3
137.5°	914.4	913.4	912.4	911.5	910.6	909.7	908.8	907.9
140°	952.3	952.0	951.8	950.9	949.3	947.5	945.9	944.3
142.5°	987.8	987.6	987.3	986.6	985.3	984.1	982.8	981.5
145°	1040.0	1039.8	1039.6	1039.0	1038.0	1037.1	1036.2	1035.2
147.5°	1089.3	1089.3	1089.3	1088.7	1087.3	1085.8	1084.4	1083.0
150°	1119.8	1119.8	1119.8	1119.1	1117.7	1116.3	1114.8	1113.5
152.5°	1147.6	1148.0	1148.3	1147.9	1146.7	1145.5	1144.3	1143.0
155°	1188.3	1189.3	1190.2	1189.8	1188.2	1186.6	1184.9	1183.2
157.5°	1223.3	1224.3	1225.3	1225.1	1223.8	1222.5	1221.2	1219.9
160°	1244.8	1246.0	1247.2	1247.3	1246.3	1245.5	1244.5	1243.5
162.5°	1265.1	1266.3	1267.5	1267.3	1265.8	1264.3	1262.8	1261.3
165°	1290.8	1292.2	1293.6	1293.5	1291.8	1290.2	1288.5	1286.9
167.5°	1311.6	1313.0	1314.5	1314.5	1313.0	1311.6	1310.1	1308.6
170°	1323.0	1324.6	1326.2	1326.2	1324.6	1323.0	1321.3	1319.6
172.5°	1331.9	1333.3	1334.8	1334.7	1333.1	1331.4	1329.8	1328.1
175°	1341.5	1343.0	1344.3	1344.2	1342.6	1340.9	1339.3	1337.7
177.5°	1345.8	1347.0	1348.1	1348.0	1346.6	1345.3	1344.0	1342.7
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1

(END OF REPORT)