

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332438-935

Luminaire Tested: **S123RDIW-S775D1030U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332438-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S775D1030U935-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1030 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6174.8 lumens  
Efficiency: N/A  
Efficacy: 117.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332438-935

CATALOG NUMBER: S123RDIW-S775D1030U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332438-935

CATALOG NUMBER: S123RDIW-S775D1030U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43																												
1	97	93	89	86	88	85	82	79	70	68	66	57	55	54	44	43	43	37																												
2	88	81	76	71	81	75	70	65	62	58	55	50	48	46	40	38	37	32																												
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	35	33	32	27																												
4	74	64	56	51	68	59	52	47	49	44	41	40	37	34	32	30	28	24																												
5	68	57	49	44	62	53	46	41	44	39	35	36	33	30	29	26	24	21																												
6	63	51	44	38	57	47	41	36	40	35	31	33	29	26	26	24	22	19																												
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17																												
8	54	42	35	30	49	39	32	28	33	28	24	28	24	21	22	20	18	15																												
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14																												
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	16	14	13																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11334	11334	11334	11334
5°	13511	11382	10024	11382
10°	16869	11317	9055	11317
15°	19801	11202	8259	11202
20°	22100	11030	7581	11030
25°	21747	10847	7163	10847
30°	15632	10679	6734	10679
35°	10437	10461	6457	10461
40°	7690	10197	6169	10197
45°	6450	9736	5888	9736
50°	5692	9133	5494	9133
55°	4992	8443	4958	8443
60°	4445	7782	4540	7782
65°	3904	7073	4225	7073
70°	3065	6442	3858	6442
75°	2699	5627	3523	5627
80°	2349	4779	3465	4779
85°	1890	3841	3680	3841



TEST NUMBER: P332438-935

CATALOG NUMBER: S123RDIW-S775D1030U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.6	1.7
10°-20°	323.5	5.2
20°-30°	508.3	8.2
30°-40°	530.3	8.6
40°-50°	453.8	7.3
50°-60°	345.9	5.6
60°-70°	221.7	3.6
70°-80°	106.6	1.7
80°-90°	31.5	0.5
90°-100°	42.3	0.7
100°-110°	201.7	3.3
110°-120°	484.5	7.8
120°-130°	616.9	10.0
130°-140°	659.2	10.7
140°-150°	616.4	10.0
150°-160°	497.2	8.1
160°-170°	320.9	5.2
170°-180°	110.6	1.8
0°-30°	935.3	15.1
0°-40°	1465.6	23.7
0°-60°	2265.3	36.7
0°-90°	2625.1	42.5
90°-120°	728.5	11.8
90°-150°	2621.0	42.4
90°-180°	3550.0	57.5
0°-180°	6174.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1053	1053	1053	1053	1053	
5°	1250	1053	928	1053	1250	129
15°	1777	1005	741	1005	1777	504
25°	1831	913	603	913	1831	787
35°	794	796	491	796	794	521
45°	424	640	387	640	424	333
55°	266	450	264	450	266	240
65°	153	278	166	278	153	151
75°	65	135	85	135	65	70
85°	15	31	30	31	15	18
90°	26	1	26	1	26	12
95°	33	53	33	53	33	27
105°	38	258	38	258	38	87
115°	508	484	508	484	508	470
125°	695	682	695	682	695	621
135°	857	848	857	848	857	661
145°	988	979	988	979	988	617
155°	1077	1078	1077	1078	1077	496
165°	1135	1137	1135	1137	1135	320
175°	1160	1164	1160	1164	1160	110
180°	1164	1164	1164	1164	1164	



TEST NUMBER: P332438-935

CATALOG NUMBER: S123RDIW-S775D1030U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1121.5	1123.0	1118.3	1117.6	1112.2	1110.7	1110.7	1103.1	1098.5	1092.4	1088.7
5°	1250.4	1257.7	1254.0	1246.0	1232.4	1229.2	1220.7	1207.2	1191.9	1172.9	1163.9
7.5°	1411.4	1421.3	1417.6	1405.0	1390.9	1379.4	1355.2	1332.7	1301.3	1273.7	1250.1
10°	1543.4	1533.1	1525.0	1512.8	1499.8	1478.5	1453.3	1418.6	1378.5	1346.9	1311.7
12.5°	1642.3	1640.5	1630.3	1617.7	1599.3	1579.2	1548.2	1505.9	1459.2	1413.7	1373.5
15°	1776.9	1779.7	1772.9	1759.8	1733.7	1698.1	1651.2	1633.6	1566.9	1517.3	1467.7
17.5°	1870.2	1869.7	1868.7	1850.6	1823.9	1798.6	1755.1	1708.9	1648.5	1578.6	1511.8
20°	1929.3	1924.9	1925.7	1905.4	1885.6	1856.3	1814.0	1746.8	1697.2	1616.5	1547.5
22.5°	1927.9	1927.0	1930.4	1923.5	1909.0	1886.6	1853.2	1796.6	1733.3	1651.8	1574.2
25°	1831.1	1827.5	1848.7	1854.5	1877.5	1881.5	1871.6	1840.6	1780.5	1696.7	1600.7
27.5°	1532.5	1530.5	1569.8	1619.0	1681.4	1729.9	1776.8	1799.4	1780.5	1720.5	1624.4
30°	1257.7	1300.0	1319.9	1391.1	1470.4	1565.1	1648.0	1726.9	1746.3	1720.2	1641.2
32.5°	1044.2	1081.2	1097.7	1158.8	1232.8	1343.7	1468.1	1579.8	1658.7	1678.7	1631.2
35°	794.3	794.7	832.6	859.6	928.2	1042.2	1163.0	1312.7	1461.4	1574.1	1585.8
37.5°	633.8	636.0	658.9	685.9	737.3	797.6	904.0	1028.4	1200.2	1373.2	1474.6
40°	547.3	551.3	568.4	595.0	632.0	677.5	760.4	877.7	1021.0	1213.5	1370.8
42.5°	491.7	498.3	507.1	527.6	550.5	593.1	660.2	750.7	881.1	1063.1	1244.6
45°	423.7	427.3	434.1	443.6	464.3	494.0	539.2	599.9	708.2	854.7	1036.3
47.5°	373.8	371.9	379.0	386.7	400.5	420.8	451.0	500.7	577.8	695.3	849.5
50°	339.9	339.4	344.4	350.3	363.3	378.2	403.0	440.4	501.7	599.1	740.2
52.5°	308.2	309.9	313.4	320.7	330.1	342.2	364.4	391.3	444.0	528.1	645.7
55°	266.0	267.3	272.2	276.3	283.1	295.2	309.3	331.7	367.8	426.5	523.3
57.5°	230.2	229.6	234.4	235.4	243.1	253.0	263.8	281.3	307.5	350.9	416.2
60°	206.5	205.1	209.1	212.3	216.4	224.5	233.5	250.6	271.4	303.3	359.3
62.5°	184.9	184.2	187.2	190.3	193.6	201.0	208.6	221.8	238.2	265.2	309.5
65°	153.3	154.6	155.9	157.3	159.1	163.6	170.8	179.9	191.1	210.1	242.0
67.5°	120.5	121.8	122.3	125.0	128.9	131.7	136.1	144.1	152.0	168.0	186.1
70°	97.4	96.9	97.4	98.8	103.7	108.7	114.5	120.4	125.3	136.6	151.9
72.5°	83.7	82.8	84.0	84.3	86.7	88.1	91.8	97.3	103.7	111.3	122.3
75°	64.9	64.9	64.9	64.9	66.7	67.6	69.0	70.3	72.6	76.2	84.3
77.5°	48.0	48.0	48.6	49.2	49.5	50.0	50.9	52.2	53.0	54.9	58.5
80°	37.9	38.3	37.9	38.3	38.3	39.2	39.7	41.0	41.5	43.7	45.1
82.5°	28.5	28.2	28.5	28.9	28.9	29.9	30.0	30.9	31.0	32.2	33.6
85°	15.3	14.5	15.3	14.9	15.8	14.9	15.3	16.2	16.2	16.7	18.5
87.5°	8.8	9.5	8.6	9.0	8.9	9.1	9.0	8.8	9.4	8.9	8.7
90°	25.9	25.6	25.1	24.8	24.4	23.8	23.1	22.3	21.5	20.8	18.3
92.5°	28.7	28.5	28.2	28.0	27.8	27.0	25.8	24.6	23.3	22.1	20.2
95°	32.9	32.9	32.9	32.9	32.9	32.2	30.8	29.5	28.2	26.8	24.7
97.5°	35.6	35.5	35.2	35.0	34.9	34.0	32.5	30.9	29.4	27.8	41.7
100°	36.3	36.2	35.9	35.7	35.6	34.7	33.1	31.6	30.0	28.5	58.5
102.5°	37.0	36.7	36.3	36.0	35.6	37.8	42.6	47.4	52.2	56.9	89.6
105°	38.1	37.6	37.3	36.9	36.5	53.3	87.3	121.4	155.4	189.4	206.7
107.5°	119.5	145.2	170.8	196.4	222.1	247.4	272.3	297.2	322.2	347.2	344.4
110°	237.8	265.3	292.7	320.3	347.8	364.6	371.0	377.4	383.7	390.0	387.9



TEST NUMBER: P332438-935

CATALOG NUMBER: S123RDIW-S775D1030U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	408.0	413.8	419.7	425.4	431.2	434.0	433.9	433.9	433.7	433.6	431.5
115°	508.5	507.7	507.0	506.2	505.4	504.1	502.1	500.2	498.3	496.4	494.6
117.5°	564.9	564.7	564.6	564.4	564.3	563.4	561.9	560.3	558.8	557.2	556.4
120°	603.6	603.6	603.6	603.6	603.6	602.9	601.3	599.8	598.2	596.7	596.2
122.5°	641.7	641.5	641.4	641.2	641.1	640.4	639.4	638.3	637.2	636.1	635.4
125°	695.3	694.9	694.5	694.1	693.8	693.4	693.0	692.6	692.2	691.8	691.0
127.5°	746.8	747.3	747.6	748.0	748.4	748.3	747.6	747.0	746.4	745.8	744.9
130°	780.1	780.4	780.8	781.2	781.6	781.4	780.6	779.9	779.1	778.3	777.6
132.5°	810.5	811.1	811.6	812.1	812.6	812.5	811.8	811.0	810.2	809.4	808.8
135°	857.0	857.6	858.2	858.8	859.3	859.3	858.8	858.2	857.6	857.0	856.3
137.5°	900.8	901.1	901.6	901.9	902.3	902.1	901.1	900.2	899.2	898.4	897.9
140°	927.0	927.5	927.8	928.2	928.6	928.4	927.6	926.9	926.1	925.3	924.7
142.5°	951.2	951.8	952.4	952.9	953.4	953.4	952.8	952.2	951.6	950.9	950.4
145°	988.4	988.4	988.4	988.4	988.4	988.3	987.9	987.5	987.1	986.7	986.4
147.5°	1016.2	1017.0	1017.9	1018.8	1019.7	1019.9	1019.5	1019.2	1018.7	1018.4	1018.0
150°	1036.9	1037.5	1038.0	1038.6	1039.2	1039.3	1038.9	1038.5	1038.1	1037.8	1037.3
152.5°	1053.5	1054.4	1055.2	1056.1	1057.0	1057.1	1056.4	1055.8	1055.1	1054.4	1054.1
155°	1076.7	1077.8	1079.0	1080.1	1081.2	1081.4	1080.4	1079.4	1078.5	1077.5	1077.4
157.5°	1096.2	1097.7	1099.2	1100.7	1102.2	1102.3	1101.2	1100.1	1098.9	1097.8	1097.9
160°	1108.6	1110.0	1111.4	1112.7	1114.0	1114.1	1113.0	1111.8	1110.7	1109.6	1109.7
162.5°	1120.4	1121.6	1122.8	1124.0	1125.2	1125.2	1123.9	1122.5	1121.2	1119.9	1120.1
165°	1134.6	1135.9	1137.3	1138.7	1140.0	1139.9	1138.3	1136.8	1135.3	1133.8	1133.9
167.5°	1144.8	1146.3	1147.9	1149.4	1151.0	1151.0	1149.4	1147.9	1146.3	1144.8	1144.8
170°	1151.1	1152.5	1154.1	1155.6	1157.2	1157.2	1155.6	1154.1	1152.5	1151.1	1151.1
172.5°	1154.5	1156.2	1157.9	1159.6	1161.2	1161.3	1159.8	1158.3	1156.8	1155.2	1155.0
175°	1159.7	1161.2	1162.8	1164.3	1165.9	1166.0	1164.6	1163.2	1161.9	1160.5	1160.4
177.5°	1161.2	1162.8	1164.3	1165.9	1167.4	1167.5	1166.3	1165.1	1163.9	1162.6	1162.4
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332438-935

CATALOG NUMBER: S123RDIW-S775D1030U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1087.3	1086.2	1081.2	1075.4	1067.8	1062.7	1058.8	1056.6	1050.2	1042.2	1036.8
5°	1154.4	1140.9	1126.5	1108.9	1092.7	1076.0	1065.7	1053.4	1038.6	1021.9	1010.2
7.5°	1226.4	1199.9	1171.3	1141.9	1112.7	1086.6	1063.5	1043.7	1020.0	996.1	979.4
10°	1281.6	1242.8	1202.6	1161.7	1124.2	1089.1	1062.0	1035.4	1007.0	979.6	958.8
12.5°	1331.7	1280.7	1234.4	1184.0	1136.2	1094.2	1055.2	1023.9	989.7	960.4	936.8
15°	1395.2	1342.9	1286.9	1210.3	1146.8	1093.6	1046.3	1005.2	963.8	927.7	904.7
17.5°	1454.5	1375.8	1300.7	1236.7	1154.2	1087.7	1029.9	980.9	935.4	897.2	868.8
20°	1479.0	1402.8	1321.2	1239.7	1158.5	1084.1	1016.9	962.9	915.5	872.3	846.1
22.5°	1493.7	1407.5	1321.5	1233.9	1147.7	1070.4	1004.0	944.4	893.2	852.0	819.8
25°	1511.0	1408.3	1313.5	1227.0	1139.1	1055.2	976.4	913.3	857.8	814.1	779.8
27.5°	1522.3	1401.4	1289.6	1193.3	1104.2	1020.7	948.4	881.6	825.3	779.0	742.3
30°	1524.5	1396.0	1271.2	1167.1	1076.4	999.8	923.2	859.2	799.7	750.5	716.3
32.5°	1527.4	1382.7	1246.3	1135.7	1042.9	967.0	897.6	836.5	775.5	727.1	692.2
35°	1515.5	1375.4	1208.5	1081.4	988.5	915.1	852.4	796.1	736.2	689.2	653.6
37.5°	1464.3	1346.0	1169.4	1020.3	923.2	855.1	804.1	754.9	700.0	649.4	615.9
40°	1412.7	1317.2	1139.1	983.2	881.8	811.8	765.9	725.7	672.5	625.3	589.2
42.5°	1335.9	1277.9	1110.3	944.2	834.8	767.5	728.8	691.1	644.5	596.4	562.5
45°	1195.0	1202.6	1051.2	882.2	769.9	702.3	665.8	639.6	598.2	558.5	523.8
47.5°	1018.3	1089.9	981.9	816.1	701.5	638.0	606.1	583.3	555.3	516.4	484.7
50°	902.9	1005.2	926.3	771.7	658.6	595.5	564.0	545.4	521.1	490.4	460.2
52.5°	796.5	906.5	859.3	722.3	612.1	554.4	523.6	508.3	489.0	460.1	432.8
55°	649.5	761.0	750.1	647.7	542.3	490.4	467.0	449.9	436.8	415.2	393.6
57.5°	525.5	631.0	636.6	564.8	480.8	429.6	409.4	396.5	388.0	371.6	351.6
60°	447.2	544.1	563.0	508.9	436.8	391.8	371.9	361.5	354.7	341.7	326.4
62.5°	382.3	464.8	486.2	447.3	394.6	352.4	336.9	326.9	322.3	311.0	297.5
65°	292.6	361.1	381.8	360.2	332.7	298.9	286.3	277.7	273.6	267.3	257.4
67.5°	220.0	269.9	292.7	277.4	267.5	246.2	238.1	233.5	229.9	225.6	217.3
70°	176.7	213.7	237.1	233.1	225.0	213.7	207.8	204.7	201.0	197.4	190.2
72.5°	142.1	167.6	189.5	191.6	184.9	182.6	177.5	176.2	174.0	169.7	165.7
75°	94.2	111.8	127.1	132.9	135.7	137.9	135.7	135.3	134.7	131.2	128.9
77.5°	61.7	71.2	80.8	90.8	95.1	98.2	98.9	100.6	99.4	97.5	96.3
80°	47.4	49.6	56.3	64.9	71.6	74.4	76.2	77.1	76.6	76.2	74.4
82.5°	34.4	36.2	39.4	45.5	51.1	55.6	56.7	56.6	57.5	57.8	56.3
85°	18.5	18.9	19.8	20.8	23.8	28.8	30.2	31.1	32.0	32.0	29.3
87.5°	9.0	8.1	8.3	7.8	8.5	8.5	10.3	11.7	12.5	11.4	11.8
90°	15.8	13.3	10.8	8.5	6.6	4.7	2.8	0.9	2.8	4.7	6.6
92.5°	18.3	16.5	14.6	13.9	14.5	15.0	15.6	16.1	15.6	15.0	14.5
95°	22.6	20.5	18.3	21.3	29.1	37.0	44.9	52.8	44.9	37.0	29.1
97.5°	55.5	69.4	83.2	91.9	95.4	98.9	102.5	106.0	102.5	98.9	95.4
100°	88.5	118.5	148.4	161.5	157.6	153.9	150.0	146.1	150.0	153.9	157.6
102.5°	122.4	155.2	187.9	202.9	200.1	197.3	194.6	191.8	194.6	197.3	200.1
105°	223.9	241.3	258.6	266.1	264.1	261.9	259.8	257.7	259.8	261.9	264.1
107.5°	341.6	339.0	336.2	334.0	332.3	330.6	328.9	327.3	328.9	330.6	332.3
110°	385.8	383.7	381.6	379.7	378.2	376.7	375.1	373.6	375.1	376.7	378.2





TEST NUMBER: P332438-935

CATALOG NUMBER: S123RDIW-S775D1030U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	429.4	427.2	425.2	423.4	422.1	420.6	419.2	417.8	419.2	420.6	422.1
115°	492.9	491.2	489.5	488.0	486.9	485.7	484.6	483.5	484.6	485.7	486.9
117.5°	555.5	554.7	553.7	552.6	551.1	549.7	548.3	546.9	548.3	549.7	551.1
120°	595.6	595.0	594.4	593.2	591.5	589.8	588.1	586.3	588.1	589.8	591.5
122.5°	634.6	634.0	633.2	632.1	630.7	629.3	627.8	626.5	627.8	629.3	630.7
125°	690.3	689.5	688.8	687.6	686.0	684.5	683.0	681.5	683.0	684.5	686.0
127.5°	744.0	743.0	742.1	740.9	739.3	737.8	736.2	734.7	736.2	737.8	739.3
130°	776.8	776.0	775.2	774.1	772.6	771.0	769.5	767.9	769.5	771.0	772.6
132.5°	808.2	807.6	807.0	805.9	804.3	802.8	801.3	799.8	801.3	802.8	804.3
135°	855.5	854.7	853.9	853.0	851.8	850.7	849.5	848.3	849.5	850.7	851.8
137.5°	897.5	897.1	896.6	895.7	894.2	892.8	891.3	889.8	891.3	892.8	894.2
140°	924.2	923.6	923.0	922.1	921.0	919.9	918.7	917.6	918.7	919.9	921.0
142.5°	949.8	949.2	948.6	947.8	946.6	945.5	944.3	943.1	944.3	945.5	946.6
145°	985.9	985.6	985.2	984.3	983.0	981.6	980.2	979.0	980.2	981.6	983.0
147.5°	1017.6	1017.2	1016.8	1016.2	1015.3	1014.4	1013.6	1012.7	1013.6	1014.4	1015.3
150°	1037.0	1036.6	1036.2	1035.7	1035.2	1034.6	1034.0	1033.5	1034.0	1034.6	1035.2
152.5°	1053.9	1053.7	1053.4	1053.2	1052.9	1052.7	1052.4	1052.1	1052.4	1052.7	1052.9
155°	1077.1	1076.9	1076.8	1076.9	1077.3	1077.6	1078.0	1078.4	1078.0	1077.6	1077.3
157.5°	1098.1	1098.4	1098.5	1098.6	1098.7	1098.7	1098.8	1098.8	1098.8	1098.7	1098.7
160°	1109.9	1110.1	1110.3	1110.5	1110.7	1110.9	1111.0	1111.3	1111.0	1110.9	1110.7
162.5°	1120.3	1120.5	1120.7	1121.0	1121.5	1122.1	1122.5	1123.0	1122.5	1122.1	1121.5
165°	1134.1	1134.3	1134.5	1134.9	1135.5	1136.1	1136.6	1137.2	1136.6	1136.1	1135.5
167.5°	1144.8	1144.8	1144.8	1145.2	1146.0	1146.8	1147.5	1148.2	1147.5	1146.8	1146.0
170°	1151.1	1151.1	1151.1	1151.4	1152.2	1153.0	1153.7	1154.5	1153.7	1153.0	1152.2
172.5°	1154.9	1154.7	1154.6	1154.9	1155.9	1156.8	1157.7	1158.6	1157.7	1156.8	1155.9
175°	1160.2	1159.9	1159.8	1160.2	1161.1	1162.1	1163.0	1164.0	1163.0	1162.1	1161.1
177.5°	1162.4	1162.2	1162.0	1162.4	1163.1	1163.9	1164.6	1165.4	1164.6	1163.9	1163.1
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332438-935

CATALOG NUMBER: S123RDIW-S775D1030U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1035.0	1030.3	1027.1	1019.9	1015.1	1010.1	1005.0	1008.3	1008.0	1007.5	1007.5
5°	1000.3	989.9	980.4	968.3	960.6	951.1	943.9	943.1	944.9	938.5	934.9
7.5°	965.9	951.7	938.2	924.8	910.6	899.2	892.1	888.7	884.2	880.3	876.2
10°	941.7	925.0	911.9	895.3	879.9	866.4	857.8	852.0	848.8	845.7	839.8
12.5°	916.8	900.4	883.8	865.0	850.3	834.7	828.3	821.7	815.6	812.1	804.1
15°	880.4	859.2	841.6	821.7	805.6	790.2	781.2	768.1	766.3	761.8	753.7
17.5°	843.9	820.9	796.6	782.0	763.6	747.7	733.9	729.5	716.6	711.8	704.7
20°	815.0	793.8	775.3	756.0	729.4	714.5	703.7	697.8	687.4	681.1	676.6
22.5°	790.1	768.6	747.2	724.6	702.7	686.0	678.0	668.9	663.3	654.4	649.5
25°	754.6	731.2	705.5	681.1	665.4	652.7	640.1	632.0	623.9	619.8	610.8
27.5°	713.3	688.8	664.8	646.4	627.0	614.5	603.0	595.8	586.1	579.3	574.3
30°	690.6	661.8	641.0	624.3	599.5	587.8	579.3	570.2	563.0	555.8	550.9
32.5°	664.3	637.9	618.3	597.6	578.6	565.8	554.7	546.8	540.6	533.8	528.8
35°	622.9	600.9	580.6	559.8	545.9	532.8	519.8	513.0	507.1	500.8	496.3
37.5°	585.7	565.0	545.7	526.1	508.8	498.1	487.6	482.4	474.5	470.3	465.6
40°	562.6	542.3	521.5	502.7	484.6	476.5	467.0	459.3	452.1	449.0	444.0
42.5°	537.4	517.0	499.6	479.1	464.4	453.4	444.6	436.3	430.8	426.3	423.4
45°	499.9	481.9	464.8	444.4	430.5	421.0	411.1	403.5	398.5	395.4	390.4
47.5°	463.6	445.6	428.2	410.4	396.9	386.2	376.3	370.9	364.3	360.4	357.1
50°	437.2	421.0	402.5	386.3	372.8	362.0	353.9	347.1	341.2	336.3	334.1
52.5°	413.1	395.8	379.8	364.7	350.4	338.2	330.8	323.6	319.3	313.6	310.9
55°	373.2	356.5	343.0	328.1	314.2	303.8	294.8	288.5	284.0	277.7	274.1
57.5°	335.8	320.9	304.7	291.8	277.4	268.6	261.1	252.6	247.1	242.2	238.7
60°	310.6	293.4	279.5	267.3	254.7	243.4	236.7	229.9	224.0	219.0	215.9
62.5°	284.3	269.3	256.1	242.8	231.3	221.4	213.6	207.9	202.8	199.6	196.5
65°	243.8	232.1	218.6	207.8	197.0	189.8	183.5	178.5	174.9	172.6	170.0
67.5°	206.7	195.4	183.6	172.9	165.7	160.2	156.1	151.8	150.0	147.1	145.3
70°	182.5	170.8	160.5	152.4	145.2	141.1	138.4	135.3	133.5	129.8	128.0
72.5°	156.3	147.7	140.3	133.6	127.9	124.2	120.7	116.8	114.0	109.9	108.2
75°	123.0	115.4	109.5	105.0	101.4	96.4	91.5	87.5	86.1	84.7	84.3
77.5°	91.2	86.3	82.1	78.3	73.8	70.2	69.1	68.2	67.8	67.2	67.2
80°	71.6	67.2	64.0	59.5	56.8	56.8	56.8	55.9	56.3	56.3	56.3
82.5°	53.3	49.2	47.4	45.8	45.3	45.6	45.6	45.8	45.5	46.2	45.9
85°	27.5	28.0	28.8	28.4	28.8	28.8	29.8	29.3	29.8	28.8	29.8
87.5°	11.8	13.3	14.2	15.1	15.9	16.0	16.5	16.7	17.2	17.4	17.5
90°	8.5	10.8	13.3	15.8	18.3	20.8	21.5	22.3	23.1	23.8	24.4
92.5°	13.9	14.6	16.5	18.3	20.2	22.1	23.3	24.6	25.8	27.0	27.8
95°	21.3	18.3	20.5	22.6	24.7	26.8	28.2	29.5	30.8	32.2	32.9
97.5°	91.9	83.2	69.4	55.5	41.7	27.8	29.4	30.9	32.5	34.0	34.9
100°	161.5	148.4	118.5	88.5	58.5	28.5	30.0	31.6	33.1	34.7	35.6
102.5°	202.9	187.9	155.2	122.4	89.6	56.9	52.2	47.4	42.6	37.8	35.6
105°	266.1	258.6	241.3	223.9	206.7	189.4	155.4	121.4	87.3	53.3	36.5
107.5°	334.0	336.2	339.0	341.6	344.4	347.2	322.2	297.2	272.3	247.4	222.1
110°	379.7	381.6	383.7	385.8	387.9	390.0	383.7	377.4	371.0	364.6	347.8



TEST NUMBER: P332438-935

CATALOG NUMBER: S123RDIW-S775D1030U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	423.4	425.2	427.2	429.4	431.5	433.6	433.7	433.9	433.9	434.0	431.2
115°	488.0	489.5	491.2	492.9	494.6	496.4	498.3	500.2	502.1	504.1	505.4
117.5°	552.6	553.7	554.7	555.5	556.4	557.2	558.8	560.3	561.9	563.4	564.3
120°	593.2	594.4	595.0	595.6	596.2	596.7	598.2	599.8	601.3	602.9	603.6
122.5°	632.1	633.2	634.0	634.6	635.4	636.1	637.2	638.3	639.4	640.4	641.1
125°	687.6	688.8	689.5	690.3	691.0	691.8	692.2	692.6	693.0	693.4	693.8
127.5°	740.9	742.1	743.0	744.0	744.9	745.8	746.4	747.0	747.6	748.3	748.4
130°	774.1	775.2	776.0	776.8	777.6	778.3	779.1	779.9	780.6	781.4	781.6
132.5°	805.9	807.0	807.6	808.2	808.8	809.4	810.2	811.0	811.8	812.5	812.6
135°	853.0	853.9	854.7	855.5	856.3	857.0	857.6	858.2	858.8	859.3	859.3
137.5°	895.7	896.6	897.1	897.5	897.9	898.4	899.2	900.2	901.1	902.1	902.3
140°	922.1	923.0	923.6	924.2	924.7	925.3	926.1	926.9	927.6	928.4	928.6
142.5°	947.8	948.6	949.2	949.8	950.4	950.9	951.6	952.2	952.8	953.4	953.4
145°	984.3	985.2	985.6	985.9	986.4	986.7	987.1	987.5	987.9	988.3	988.4
147.5°	1016.2	1016.8	1017.2	1017.6	1018.0	1018.4	1018.7	1019.2	1019.5	1019.9	1019.7
150°	1035.7	1036.2	1036.6	1037.0	1037.3	1037.8	1038.1	1038.5	1038.9	1039.3	1039.2
152.5°	1053.2	1053.4	1053.7	1053.9	1054.1	1054.4	1055.1	1055.8	1056.4	1057.1	1057.0
155°	1076.9	1076.8	1076.9	1077.1	1077.4	1077.5	1078.5	1079.4	1080.4	1081.4	1081.2
157.5°	1098.6	1098.5	1098.4	1098.1	1097.9	1097.8	1098.9	1100.1	1101.2	1102.3	1102.2
160°	1110.5	1110.3	1110.1	1109.9	1109.7	1109.6	1110.7	1111.8	1113.0	1114.1	1114.0
162.5°	1121.0	1120.7	1120.5	1120.3	1120.1	1119.9	1121.2	1122.5	1123.9	1125.2	1125.2
165°	1134.9	1134.5	1134.3	1134.1	1133.9	1133.8	1135.3	1136.8	1138.3	1139.9	1140.0
167.5°	1145.2	1144.8	1144.8	1144.8	1144.8	1144.8	1146.3	1147.9	1149.4	1151.0	1151.0
170°	1151.4	1151.1	1151.1	1151.1	1151.1	1151.1	1152.5	1154.1	1155.6	1157.2	1157.2
172.5°	1154.9	1154.6	1154.7	1154.9	1155.0	1155.2	1156.8	1158.3	1159.8	1161.3	1161.2
175°	1160.2	1159.8	1159.9	1160.2	1160.4	1160.5	1161.9	1163.2	1164.6	1166.0	1165.9
177.5°	1162.4	1162.0	1162.2	1162.4	1162.4	1162.6	1163.9	1165.1	1166.3	1167.5	1167.4
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332438-935

CATALOG NUMBER: S123RDIW-S775D1030U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1003.2	1002.9	1003.2	1001.8	1003.2	1002.9	1003.2	1007.5	1007.5	1008.0	1008.3
5°	933.6	933.1	931.8	927.7	931.8	933.1	933.6	934.9	938.5	944.9	943.1
7.5°	872.7	872.1	868.1	868.2	868.1	872.1	872.7	876.2	880.3	884.2	888.7
10°	836.6	837.1	831.7	828.5	831.7	837.1	836.6	839.8	845.7	848.8	852.0
12.5°	801.7	799.6	795.2	791.8	795.2	799.6	801.7	804.1	812.1	815.6	821.7
15°	755.5	751.0	740.2	741.1	740.2	751.0	755.5	753.7	761.8	766.3	768.1
17.5°	701.1	697.8	697.6	691.3	697.6	697.8	701.1	704.7	711.8	716.6	729.5
20°	669.4	667.2	668.0	661.8	668.0	667.2	669.4	676.6	681.1	687.4	697.8
22.5°	644.5	642.3	638.5	636.5	638.5	642.3	644.5	649.5	654.4	663.3	668.9
25°	608.1	604.5	600.9	603.1	600.9	604.5	608.1	610.8	619.8	623.9	632.0
27.5°	571.7	568.9	565.3	564.9	565.3	568.9	571.7	574.3	579.3	586.1	595.8
30°	548.6	545.9	544.1	541.8	544.1	545.9	548.6	550.9	555.8	563.0	570.2
32.5°	525.1	524.6	521.3	520.9	521.3	524.6	525.1	528.8	533.8	540.6	546.8
35°	494.5	491.8	490.9	491.4	490.9	491.8	494.5	496.3	500.8	507.1	513.0
37.5°	465.4	461.8	460.1	458.6	460.1	461.8	465.4	465.6	470.3	474.5	482.4
40°	444.4	440.8	440.0	439.0	440.0	440.8	444.4	444.0	449.0	452.1	459.3
42.5°	421.0	419.6	419.0	417.4	419.0	419.6	421.0	423.4	426.3	430.8	436.3
45°	389.0	388.6	385.9	386.8	385.9	388.6	389.0	390.4	395.4	398.5	403.5
47.5°	355.3	353.4	351.5	352.7	351.5	353.4	355.3	357.1	360.4	364.3	370.9
50°	332.3	331.3	327.3	328.1	327.3	331.3	332.3	334.1	336.3	341.2	347.1
52.5°	309.2	305.7	304.2	303.7	304.2	305.7	309.2	310.9	313.6	319.3	323.6
55°	271.0	266.8	265.0	264.2	265.0	266.8	271.0	274.1	277.7	284.0	288.5
57.5°	233.4	232.3	230.9	231.9	230.9	232.3	233.4	238.7	242.2	247.1	252.6
60°	211.4	211.4	211.4	210.9	211.4	211.4	211.4	215.9	219.0	224.0	229.9
62.5°	194.5	193.4	193.0	193.6	193.0	193.4	194.5	196.5	199.6	202.8	207.9
65°	168.6	168.2	166.3	165.9	166.3	168.2	168.6	170.0	172.6	174.9	178.5
67.5°	144.1	142.5	142.0	141.4	142.0	142.5	144.1	145.3	147.1	150.0	151.8
70°	125.8	124.8	122.2	122.6	122.2	124.8	125.8	128.0	129.8	133.5	135.3
72.5°	105.9	105.0	104.5	103.8	104.5	105.0	105.9	108.2	109.9	114.0	116.8
75°	83.9	83.4	82.9	84.7	82.9	83.4	83.9	84.3	84.7	86.1	87.5
77.5°	67.2	67.2	67.4	66.7	67.4	67.2	67.2	67.2	67.2	67.8	68.2
80°	56.3	56.3	55.9	55.9	55.9	56.3	56.3	56.3	56.3	56.3	55.9
82.5°	45.2	45.5	45.8	45.1	45.8	45.5	45.2	45.9	46.2	45.5	45.8
85°	29.8	29.3	30.2	29.8	30.2	29.3	29.8	29.8	28.8	29.8	29.3
87.5°	18.3	17.7	17.7	18.2	17.7	17.7	18.3	17.5	17.4	17.2	16.7
90°	24.8	25.1	25.6	25.9	25.6	25.1	24.8	24.4	23.8	23.1	22.3
92.5°	28.0	28.2	28.5	28.7	28.5	28.2	28.0	27.8	27.0	25.8	24.6
95°	32.9	32.9	32.9	32.9	32.9	32.9	32.9	32.9	32.2	30.8	29.5
97.5°	35.0	35.2	35.5	35.6	35.5	35.2	35.0	34.9	34.0	32.5	30.9
100°	35.7	35.9	36.2	36.3	36.2	35.9	35.7	35.6	34.7	33.1	31.6
102.5°	36.0	36.3	36.7	37.0	36.7	36.3	36.0	35.6	37.8	42.6	47.4
105°	36.9	37.3	37.6	38.1	37.6	37.3	36.9	36.5	53.3	87.3	121.4
107.5°	196.4	170.8	145.2	119.5	145.2	170.8	196.4	222.1	247.4	272.3	297.2
110°	320.3	292.7	265.3	237.8	265.3	292.7	320.3	347.8	364.6	371.0	377.4



TEST NUMBER: P332438-935

CATALOG NUMBER: S123RDIW-S775D1030U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	425.4	419.7	413.8	408.0	413.8	419.7	425.4	431.2	434.0	433.9	433.9
115°	506.2	507.0	507.7	508.5	507.7	507.0	506.2	505.4	504.1	502.1	500.2
117.5°	564.4	564.6	564.7	564.9	564.7	564.6	564.4	564.3	563.4	561.9	560.3
120°	603.6	603.6	603.6	603.6	603.6	603.6	603.6	603.6	602.9	601.3	599.8
122.5°	641.2	641.4	641.5	641.7	641.5	641.4	641.2	641.1	640.4	639.4	638.3
125°	694.1	694.5	694.9	695.3	694.9	694.5	694.1	693.8	693.4	693.0	692.6
127.5°	748.0	747.6	747.3	746.8	747.3	747.6	748.0	748.4	748.3	747.6	747.0
130°	781.2	780.8	780.4	780.1	780.4	780.8	781.2	781.6	781.4	780.6	779.9
132.5°	812.1	811.6	811.1	810.5	811.1	811.6	812.1	812.6	812.5	811.8	811.0
135°	858.8	858.2	857.6	857.0	857.6	858.2	858.8	859.3	859.3	858.8	858.2
137.5°	901.9	901.6	901.1	900.8	901.1	901.6	901.9	902.3	902.1	901.1	900.2
140°	928.2	927.8	927.5	927.0	927.5	927.8	928.2	928.6	928.4	927.6	926.9
142.5°	952.9	952.4	951.8	951.2	951.8	952.4	952.9	953.4	953.4	952.8	952.2
145°	988.4	988.4	988.4	988.4	988.4	988.4	988.4	988.4	988.3	987.9	987.5
147.5°	1018.8	1017.9	1017.0	1016.2	1017.0	1017.9	1018.8	1019.7	1019.9	1019.5	1019.2
150°	1038.6	1038.0	1037.5	1036.9	1037.5	1038.0	1038.6	1039.2	1039.3	1038.9	1038.5
152.5°	1056.1	1055.2	1054.4	1053.5	1054.4	1055.2	1056.1	1057.0	1057.1	1056.4	1055.8
155°	1080.1	1079.0	1077.8	1076.7	1077.8	1079.0	1080.1	1081.2	1081.4	1080.4	1079.4
157.5°	1100.7	1099.2	1097.7	1096.2	1097.7	1099.2	1100.7	1102.2	1102.3	1101.2	1100.1
160°	1112.7	1111.4	1110.0	1108.6	1110.0	1111.4	1112.7	1114.0	1114.1	1113.0	1111.8
162.5°	1124.0	1122.8	1121.6	1120.4	1121.6	1122.8	1124.0	1125.2	1125.2	1123.9	1122.5
165°	1138.7	1137.3	1135.9	1134.6	1135.9	1137.3	1138.7	1140.0	1139.9	1138.3	1136.8
167.5°	1149.4	1147.9	1146.3	1144.8	1146.3	1147.9	1149.4	1151.0	1151.0	1149.4	1147.9
170°	1155.6	1154.1	1152.5	1151.1	1152.5	1154.1	1155.6	1157.2	1157.2	1155.6	1154.1
172.5°	1159.6	1157.9	1156.2	1154.5	1156.2	1157.9	1159.6	1161.2	1161.3	1159.8	1158.3
175°	1164.3	1162.8	1161.2	1159.7	1161.2	1162.8	1164.3	1165.9	1166.0	1164.6	1163.2
177.5°	1165.9	1164.3	1162.8	1161.2	1162.8	1164.3	1165.9	1167.4	1167.5	1166.3	1165.1
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332438-935

CATALOG NUMBER: S123RDIW-S775D1030U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1005.0	1010.1	1015.1	1019.9	1027.1	1030.3	1035.0	1036.8	1042.2	1050.2	1056.6
5°	943.9	951.1	960.6	968.3	980.4	989.9	1000.3	1010.2	1021.9	1038.6	1053.4
7.5°	892.1	899.2	910.6	924.8	938.2	951.7	965.9	979.4	996.1	1020.0	1043.7
10°	857.8	866.4	879.9	895.3	911.9	925.0	941.7	958.8	979.6	1007.0	1035.4
12.5°	828.3	834.7	850.3	865.0	883.8	900.4	916.8	936.8	960.4	989.7	1023.9
15°	781.2	790.2	805.6	821.7	841.6	859.2	880.4	904.7	927.7	963.8	1005.2
17.5°	733.9	747.7	763.6	782.0	796.6	820.9	843.9	868.8	897.2	935.4	980.9
20°	703.7	714.5	729.4	756.0	775.3	793.8	815.0	846.1	872.3	915.5	962.9
22.5°	678.0	686.0	702.7	724.6	747.2	768.6	790.1	819.8	852.0	893.2	944.4
25°	640.1	652.7	665.4	681.1	705.5	731.2	754.6	779.8	814.1	857.8	913.3
27.5°	603.0	614.5	627.0	646.4	664.8	688.8	713.3	742.3	779.0	825.3	881.6
30°	579.3	587.8	599.5	624.3	641.0	661.8	690.6	716.3	750.5	799.7	859.2
32.5°	554.7	565.8	578.6	597.6	618.3	637.9	664.3	692.2	727.1	775.5	836.5
35°	519.8	532.8	545.9	559.8	580.6	600.9	622.9	653.6	689.2	736.2	796.1
37.5°	487.6	498.1	508.8	526.1	545.7	565.0	585.7	615.9	649.4	700.0	754.9
40°	467.0	476.5	484.6	502.7	521.5	542.3	562.6	589.2	625.3	672.5	725.7
42.5°	444.6	453.4	464.4	479.1	499.6	517.0	537.4	562.5	596.4	644.5	691.1
45°	411.1	421.0	430.5	444.4	464.8	481.9	499.9	523.8	558.5	598.2	639.6
47.5°	376.3	386.2	396.9	410.4	428.2	445.6	463.6	484.7	516.4	555.3	583.3
50°	353.9	362.0	372.8	386.3	402.5	421.0	437.2	460.2	490.4	521.1	545.4
52.5°	330.8	338.2	350.4	364.7	379.8	395.8	413.1	432.8	460.1	489.0	508.3
55°	294.8	303.8	314.2	328.1	343.0	356.5	373.2	393.6	415.2	436.8	449.9
57.5°	261.1	268.6	277.4	291.8	304.7	320.9	335.8	351.6	371.6	388.0	396.5
60°	236.7	243.4	254.7	267.3	279.5	293.4	310.6	326.4	341.7	354.7	361.5
62.5°	213.6	221.4	231.3	242.8	256.1	269.3	284.3	297.5	311.0	322.3	326.9
65°	183.5	189.8	197.0	207.8	218.6	232.1	243.8	257.4	267.3	273.6	277.7
67.5°	156.1	160.2	165.7	172.9	183.6	195.4	206.7	217.3	225.6	229.9	233.5
70°	138.4	141.1	145.2	152.4	160.5	170.8	182.5	190.2	197.4	201.0	204.7
72.5°	120.7	124.2	127.9	133.6	140.3	147.7	156.3	165.7	169.7	174.0	176.2
75°	91.5	96.4	101.4	105.0	109.5	115.4	123.0	128.9	131.2	134.7	135.3
77.5°	69.1	70.2	73.8	78.3	82.1	86.3	91.2	96.3	97.5	99.4	100.6
80°	56.8	56.8	56.8	59.5	64.0	67.2	71.6	74.4	76.2	76.6	77.1
82.5°	45.6	45.6	45.3	45.8	47.4	49.2	53.3	56.3	57.8	57.5	56.6
85°	29.8	28.8	28.8	28.4	28.8	28.0	27.5	29.3	32.0	32.0	31.1
87.5°	16.5	16.0	15.9	15.1	14.2	13.3	11.8	11.8	11.4	12.5	11.7
90°	21.5	20.8	18.3	15.8	13.3	10.8	8.5	6.6	4.7	2.8	0.9
92.5°	23.3	22.1	20.2	18.3	16.5	14.6	13.9	14.5	15.0	15.6	16.1
95°	28.2	26.8	24.7	22.6	20.5	18.3	21.3	29.1	37.0	44.9	52.8
97.5°	29.4	27.8	41.7	55.5	69.4	83.2	91.9	95.4	98.9	102.5	106.0
100°	30.0	28.5	58.5	88.5	118.5	148.4	161.5	157.6	153.9	150.0	146.1
102.5°	52.2	56.9	89.6	122.4	155.2	187.9	202.9	200.1	197.3	194.6	191.8
105°	155.4	189.4	206.7	223.9	241.3	258.6	266.1	264.1	261.9	259.8	257.7
107.5°	322.2	347.2	344.4	341.6	339.0	336.2	334.0	332.3	330.6	328.9	327.3
110°	383.7	390.0	387.9	385.8	383.7	381.6	379.7	378.2	376.7	375.1	373.6



TEST NUMBER: P332438-935

CATALOG NUMBER: S123RDIW-S775D1030U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	433.7	433.6	431.5	429.4	427.2	425.2	423.4	422.1	420.6	419.2	417.8
115°	498.3	496.4	494.6	492.9	491.2	489.5	488.0	486.9	485.7	484.6	483.5
117.5°	558.8	557.2	556.4	555.5	554.7	553.7	552.6	551.1	549.7	548.3	546.9
120°	598.2	596.7	596.2	595.6	595.0	594.4	593.2	591.5	589.8	588.1	586.3
122.5°	637.2	636.1	635.4	634.6	634.0	633.2	632.1	630.7	629.3	627.8	626.5
125°	692.2	691.8	691.0	690.3	689.5	688.8	687.6	686.0	684.5	683.0	681.5
127.5°	746.4	745.8	744.9	744.0	743.0	742.1	740.9	739.3	737.8	736.2	734.7
130°	779.1	778.3	777.6	776.8	776.0	775.2	774.1	772.6	771.0	769.5	767.9
132.5°	810.2	809.4	808.8	808.2	807.6	807.0	805.9	804.3	802.8	801.3	799.8
135°	857.6	857.0	856.3	855.5	854.7	853.9	853.0	851.8	850.7	849.5	848.3
137.5°	899.2	898.4	897.9	897.5	897.1	896.6	895.7	894.2	892.8	891.3	889.8
140°	926.1	925.3	924.7	924.2	923.6	923.0	922.1	921.0	919.9	918.7	917.6
142.5°	951.6	950.9	950.4	949.8	949.2	948.6	947.8	946.6	945.5	944.3	943.1
145°	987.1	986.7	986.4	985.9	985.6	985.2	984.3	983.0	981.6	980.2	979.0
147.5°	1018.7	1018.4	1018.0	1017.6	1017.2	1016.8	1016.2	1015.3	1014.4	1013.6	1012.7
150°	1038.1	1037.8	1037.3	1037.0	1036.6	1036.2	1035.7	1035.2	1034.6	1034.0	1033.5
152.5°	1055.1	1054.4	1054.1	1053.9	1053.7	1053.4	1053.2	1052.9	1052.7	1052.4	1052.1
155°	1078.5	1077.5	1077.4	1077.1	1076.9	1076.8	1076.9	1077.3	1077.6	1078.0	1078.4
157.5°	1098.9	1097.8	1097.9	1098.1	1098.4	1098.5	1098.6	1098.7	1098.7	1098.8	1098.8
160°	1110.7	1109.6	1109.7	1109.9	1110.1	1110.3	1110.5	1110.7	1110.9	1111.0	1111.3
162.5°	1121.2	1119.9	1120.1	1120.3	1120.5	1120.7	1121.0	1121.5	1122.1	1122.5	1123.0
165°	1135.3	1133.8	1133.9	1134.1	1134.3	1134.5	1134.9	1135.5	1136.1	1136.6	1137.2
167.5°	1146.3	1144.8	1144.8	1144.8	1144.8	1144.8	1145.2	1146.0	1146.8	1147.5	1148.2
170°	1152.5	1151.1	1151.1	1151.1	1151.1	1151.1	1151.4	1152.2	1153.0	1153.7	1154.5
172.5°	1156.8	1155.2	1155.0	1154.9	1154.7	1154.6	1154.9	1155.9	1156.8	1157.7	1158.6
175°	1161.9	1160.5	1160.4	1160.2	1159.9	1159.8	1160.2	1161.1	1162.1	1163.0	1164.0
177.5°	1163.9	1162.6	1162.4	1162.4	1162.2	1162.0	1162.4	1163.1	1163.9	1164.6	1165.4
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332438-935

CATALOG NUMBER: S123RDIW-S775D1030U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1058.8	1062.7	1067.8	1075.4	1081.2	1086.2	1087.3	1088.7	1092.4	1098.5	1103.1
5°	1065.7	1076.0	1092.7	1108.9	1126.5	1140.9	1154.4	1163.9	1172.9	1191.9	1207.2
7.5°	1063.5	1086.6	1112.7	1141.9	1171.3	1199.9	1226.4	1250.1	1273.7	1301.3	1332.7
10°	1062.0	1089.1	1124.2	1161.7	1202.6	1242.8	1281.6	1311.7	1346.9	1378.5	1418.6
12.5°	1055.2	1094.2	1136.2	1184.0	1234.4	1280.7	1331.7	1373.5	1413.7	1459.2	1505.9
15°	1046.3	1093.6	1146.8	1210.3	1286.9	1342.9	1395.2	1467.7	1517.3	1566.9	1633.6
17.5°	1029.9	1087.7	1154.2	1236.7	1300.7	1375.8	1454.5	1511.8	1578.6	1648.5	1708.9
20°	1016.9	1084.1	1158.5	1239.7	1321.2	1402.8	1479.0	1547.5	1616.5	1697.2	1746.8
22.5°	1004.0	1070.4	1147.7	1233.9	1321.5	1407.5	1493.7	1574.2	1651.8	1733.3	1796.6
25°	976.4	1055.2	1139.1	1227.0	1313.5	1408.3	1511.0	1600.7	1696.7	1780.5	1840.6
27.5°	948.4	1020.7	1104.2	1193.3	1289.6	1401.4	1522.3	1624.4	1720.5	1780.5	1799.4
30°	923.2	999.8	1076.4	1167.1	1271.2	1396.0	1524.5	1641.2	1720.2	1746.3	1726.9
32.5°	897.6	967.0	1042.9	1135.7	1246.3	1382.7	1527.4	1631.2	1678.7	1658.7	1579.8
35°	852.4	915.1	988.5	1081.4	1208.5	1375.4	1515.5	1585.8	1574.1	1461.4	1312.7
37.5°	804.1	855.1	923.2	1020.3	1169.4	1346.0	1464.3	1474.6	1373.2	1200.2	1028.4
40°	765.9	811.8	881.8	983.2	1139.1	1317.2	1412.7	1370.8	1213.5	1021.0	877.7
42.5°	728.8	767.5	834.8	944.2	1110.3	1277.9	1335.9	1244.6	1063.1	881.1	750.7
45°	665.8	702.3	769.9	882.2	1051.2	1202.6	1195.0	1036.3	854.7	708.2	599.9
47.5°	606.1	638.0	701.5	816.1	981.9	1089.9	1018.3	849.5	695.3	577.8	500.7
50°	564.0	595.5	658.6	771.7	926.3	1005.2	902.9	740.2	599.1	501.7	440.4
52.5°	523.6	554.4	612.1	722.3	859.3	906.5	796.5	645.7	528.1	444.0	391.3
55°	467.0	490.4	542.3	647.7	750.1	761.0	649.5	523.3	426.5	367.8	331.7
57.5°	409.4	429.6	480.8	564.8	636.6	631.0	525.5	416.2	350.9	307.5	281.3
60°	371.9	391.8	436.8	508.9	563.0	544.1	447.2	359.3	303.3	271.4	250.6
62.5°	336.9	352.4	394.6	447.3	486.2	464.8	382.3	309.5	265.2	238.2	221.8
65°	286.3	298.9	332.7	360.2	381.8	361.1	292.6	242.0	210.1	191.1	179.9
67.5°	238.1	246.2	267.5	277.4	292.7	269.9	220.0	186.1	168.0	152.0	144.1
70°	207.8	213.7	225.0	233.1	237.1	213.7	176.7	151.9	136.6	125.3	120.4
72.5°	177.5	182.6	184.9	191.6	189.5	167.6	142.1	122.3	111.3	103.7	97.3
75°	135.7	137.9	135.7	132.9	127.1	111.8	94.2	84.3	76.2	72.6	70.3
77.5°	98.9	98.2	95.1	90.8	80.8	71.2	61.7	58.5	54.9	53.0	52.2
80°	76.2	74.4	71.6	64.9	56.3	49.6	47.4	45.1	43.7	41.5	41.0
82.5°	56.7	55.6	51.1	45.5	39.4	36.2	34.4	33.6	32.2	31.0	30.9
85°	30.2	28.8	23.8	20.8	19.8	18.9	18.5	18.5	16.7	16.2	16.2
87.5°	10.3	8.5	8.5	7.8	8.3	8.1	9.0	8.7	8.9	9.4	8.8
90°	2.8	4.7	6.6	8.5	10.8	13.3	15.8	18.3	20.8	21.5	22.3
92.5°	15.6	15.0	14.5	13.9	14.6	16.5	18.3	20.2	22.1	23.3	24.6
95°	44.9	37.0	29.1	21.3	18.3	20.5	22.6	24.7	26.8	28.2	29.5
97.5°	102.5	98.9	95.4	91.9	83.2	69.4	55.5	41.7	27.8	29.4	30.9
100°	150.0	153.9	157.6	161.5	148.4	118.5	88.5	58.5	28.5	30.0	31.6
102.5°	194.6	197.3	200.1	202.9	187.9	155.2	122.4	89.6	56.9	52.2	47.4
105°	259.8	261.9	264.1	266.1	258.6	241.3	223.9	206.7	189.4	155.4	121.4
107.5°	328.9	330.6	332.3	334.0	336.2	339.0	341.6	344.4	347.2	322.2	297.2
110°	375.1	376.7	378.2	379.7	381.6	383.7	385.8	387.9	390.0	383.7	377.4





TEST NUMBER: P332438-935

CATALOG NUMBER: S123RDIW-S775D1030U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	419.2	420.6	422.1	423.4	425.2	427.2	429.4	431.5	433.6	433.7	433.9
115°	484.6	485.7	486.9	488.0	489.5	491.2	492.9	494.6	496.4	498.3	500.2
117.5°	548.3	549.7	551.1	552.6	553.7	554.7	555.5	556.4	557.2	558.8	560.3
120°	588.1	589.8	591.5	593.2	594.4	595.0	595.6	596.2	596.7	598.2	599.8
122.5°	627.8	629.3	630.7	632.1	633.2	634.0	634.6	635.4	636.1	637.2	638.3
125°	683.0	684.5	686.0	687.6	688.8	689.5	690.3	691.0	691.8	692.2	692.6
127.5°	736.2	737.8	739.3	740.9	742.1	743.0	744.0	744.9	745.8	746.4	747.0
130°	769.5	771.0	772.6	774.1	775.2	776.0	776.8	777.6	778.3	779.1	779.9
132.5°	801.3	802.8	804.3	805.9	807.0	807.6	808.2	808.8	809.4	810.2	811.0
135°	849.5	850.7	851.8	853.0	853.9	854.7	855.5	856.3	857.0	857.6	858.2
137.5°	891.3	892.8	894.2	895.7	896.6	897.1	897.5	897.9	898.4	899.2	900.2
140°	918.7	919.9	921.0	922.1	923.0	923.6	924.2	924.7	925.3	926.1	926.9
142.5°	944.3	945.5	946.6	947.8	948.6	949.2	949.8	950.4	950.9	951.6	952.2
145°	980.2	981.6	983.0	984.3	985.2	985.6	985.9	986.4	986.7	987.1	987.5
147.5°	1013.6	1014.4	1015.3	1016.2	1016.8	1017.2	1017.6	1018.0	1018.4	1018.7	1019.2
150°	1034.0	1034.6	1035.2	1035.7	1036.2	1036.6	1037.0	1037.3	1037.8	1038.1	1038.5
152.5°	1052.4	1052.7	1052.9	1053.2	1053.4	1053.7	1053.9	1054.1	1054.4	1055.1	1055.8
155°	1078.0	1077.6	1077.3	1076.9	1076.8	1076.9	1077.1	1077.4	1077.5	1078.5	1079.4
157.5°	1098.8	1098.7	1098.7	1098.6	1098.5	1098.4	1098.1	1097.9	1097.8	1098.9	1100.1
160°	1111.0	1110.9	1110.7	1110.5	1110.3	1110.1	1109.9	1109.7	1109.6	1110.7	1111.8
162.5°	1122.5	1122.1	1121.5	1121.0	1120.7	1120.5	1120.3	1120.1	1119.9	1121.2	1122.5
165°	1136.6	1136.1	1135.5	1134.9	1134.5	1134.3	1134.1	1133.9	1133.8	1135.3	1136.8
167.5°	1147.5	1146.8	1146.0	1145.2	1144.8	1144.8	1144.8	1144.8	1144.8	1146.3	1147.9
170°	1153.7	1153.0	1152.2	1151.4	1151.1	1151.1	1151.1	1151.1	1151.1	1152.5	1154.1
172.5°	1157.7	1156.8	1155.9	1154.9	1154.6	1154.7	1154.9	1155.0	1155.2	1156.8	1158.3
175°	1163.0	1162.1	1161.1	1160.2	1159.8	1159.9	1160.2	1160.4	1160.5	1161.9	1163.2
177.5°	1164.6	1163.9	1163.1	1162.4	1162.0	1162.2	1162.4	1162.4	1162.6	1163.9	1165.1
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332438-935

CATALOG NUMBER: S123RDIW-S775D1030U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1110.7	1110.7	1112.2	1117.6	1118.3	1123.0	1121.5
5°	1220.7	1229.2	1232.4	1246.0	1254.0	1257.7	1250.4
7.5°	1355.2	1379.4	1390.9	1405.0	1417.6	1421.3	1411.4
10°	1453.3	1478.5	1499.8	1512.8	1525.0	1533.1	1543.4
12.5°	1548.2	1579.2	1599.3	1617.7	1630.3	1640.5	1642.3
15°	1651.2	1698.1	1733.7	1759.8	1772.9	1779.7	1776.9
17.5°	1755.1	1798.6	1823.9	1850.6	1868.7	1869.7	1870.2
20°	1814.0	1856.3	1885.6	1905.4	1925.7	1924.9	1929.3
22.5°	1853.2	1886.6	1909.0	1923.5	1930.4	1927.0	1927.9
25°	1871.6	1881.5	1877.5	1854.5	1848.7	1827.5	1831.1
27.5°	1776.8	1729.9	1681.4	1619.0	1569.8	1530.5	1532.5
30°	1648.0	1565.1	1470.4	1391.1	1319.9	1300.0	1257.7
32.5°	1468.1	1343.7	1232.8	1158.8	1097.7	1081.2	1044.2
35°	1163.0	1042.2	928.2	859.6	832.6	794.7	794.3
37.5°	904.0	797.6	737.3	685.9	658.9	636.0	633.8
40°	760.4	677.5	632.0	595.0	568.4	551.3	547.3
42.5°	660.2	593.1	550.5	527.6	507.1	498.3	491.7
45°	539.2	494.0	464.3	443.6	434.1	427.3	423.7
47.5°	451.0	420.8	400.5	386.7	379.0	371.9	373.8
50°	403.0	378.2	363.3	350.3	344.4	339.4	339.9
52.5°	364.4	342.2	330.1	320.7	313.4	309.9	308.2
55°	309.3	295.2	283.1	276.3	272.2	267.3	266.0
57.5°	263.8	253.0	243.1	235.4	234.4	229.6	230.2
60°	233.5	224.5	216.4	212.3	209.1	205.1	206.5
62.5°	208.6	201.0	193.6	190.3	187.2	184.2	184.9
65°	170.8	163.6	159.1	157.3	155.9	154.6	153.3
67.5°	136.1	131.7	128.9	125.0	122.3	121.8	120.5
70°	114.5	108.7	103.7	98.8	97.4	96.9	97.4
72.5°	91.8	88.1	86.7	84.3	84.0	82.8	83.7
75°	69.0	67.6	66.7	64.9	64.9	64.9	64.9
77.5°	50.9	50.0	49.5	49.2	48.6	48.0	48.0
80°	39.7	39.2	38.3	38.3	37.9	38.3	37.9
82.5°	30.0	29.9	28.9	28.9	28.5	28.2	28.5
85°	15.3	14.9	15.8	14.9	15.3	14.5	15.3
87.5°	9.0	9.1	8.9	9.0	8.6	9.5	8.8
90°	23.1	23.8	24.4	24.8	25.1	25.6	25.9
92.5°	25.8	27.0	27.8	28.0	28.2	28.5	28.7
95°	30.8	32.2	32.9	32.9	32.9	32.9	32.9
97.5°	32.5	34.0	34.9	35.0	35.2	35.5	35.6
100°	33.1	34.7	35.6	35.7	35.9	36.2	36.3
102.5°	42.6	37.8	35.6	36.0	36.3	36.7	37.0
105°	87.3	53.3	36.5	36.9	37.3	37.6	38.1
107.5°	272.3	247.4	222.1	196.4	170.8	145.2	119.5
110°	371.0	364.6	347.8	320.3	292.7	265.3	237.8



TEST NUMBER: P332438-935

CATALOG NUMBER: S123RDIW-S775D1030U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	433.9	434.0	431.2	425.4	419.7	413.8	408.0
115°	502.1	504.1	505.4	506.2	507.0	507.7	508.5
117.5°	561.9	563.4	564.3	564.4	564.6	564.7	564.9
120°	601.3	602.9	603.6	603.6	603.6	603.6	603.6
122.5°	639.4	640.4	641.1	641.2	641.4	641.5	641.7
125°	693.0	693.4	693.8	694.1	694.5	694.9	695.3
127.5°	747.6	748.3	748.4	748.0	747.6	747.3	746.8
130°	780.6	781.4	781.6	781.2	780.8	780.4	780.1
132.5°	811.8	812.5	812.6	812.1	811.6	811.1	810.5
135°	858.8	859.3	859.3	858.8	858.2	857.6	857.0
137.5°	901.1	902.1	902.3	901.9	901.6	901.1	900.8
140°	927.6	928.4	928.6	928.2	927.8	927.5	927.0
142.5°	952.8	953.4	953.4	952.9	952.4	951.8	951.2
145°	987.9	988.3	988.4	988.4	988.4	988.4	988.4
147.5°	1019.5	1019.9	1019.7	1018.8	1017.9	1017.0	1016.2
150°	1038.9	1039.3	1039.2	1038.6	1038.0	1037.5	1036.9
152.5°	1056.4	1057.1	1057.0	1056.1	1055.2	1054.4	1053.5
155°	1080.4	1081.4	1081.2	1080.1	1079.0	1077.8	1076.7
157.5°	1101.2	1102.3	1102.2	1100.7	1099.2	1097.7	1096.2
160°	1113.0	1114.1	1114.0	1112.7	1111.4	1110.0	1108.6
162.5°	1123.9	1125.2	1125.2	1124.0	1122.8	1121.6	1120.4
165°	1138.3	1139.9	1140.0	1138.7	1137.3	1135.9	1134.6
167.5°	1149.4	1151.0	1151.0	1149.4	1147.9	1146.3	1144.8
170°	1155.6	1157.2	1157.2	1155.6	1154.1	1152.5	1151.1
172.5°	1159.8	1161.3	1161.2	1159.6	1157.9	1156.2	1154.5
175°	1164.6	1166.0	1165.9	1164.3	1162.8	1161.2	1159.7
177.5°	1166.3	1167.5	1167.4	1165.9	1164.3	1162.8	1161.2
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0

(END OF REPORT)