

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332191-930

Luminaire Tested: **S123DIW-S1000D755U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332191-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D755U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5494.7 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332191-930

CATALOG NUMBER: S123DIW-S1000D755U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332191-930

CATALOG NUMBER: S123DIW-S1000D755U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	77	77	77	66	66	66	61
1	100	96	92	88	94	90	86	83	78	76	73	68	66	64	59	57	56	51
2	91	84	77	72	85	78	73	68	69	64	61	60	57	54	51	49	47	43
3	83	73	66	60	78	69	62	57	61	55	51	53	49	45	46	43	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	64	52	44	38	60	49	42	36	44	37	33	38	33	30	33	29	26	24
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	27	24	21
8	55	43	35	29	52	41	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13891	13891	13891
5°	13956	13765	13861
10°	13864	13645	13729
15°	13701	13490	13515
20°	13512	13270	13283
25°	13258	13007	12981
30°	12978	12716	12619
35°	12686	12408	12248
40°	12381	12067	11880
45°	12044	11756	11469
50°	11707	11372	11055
55°	11265	10975	10640
60°	10820	10512	10176
65°	10427	10004	9694
70°	9847	9429	9010
75°	9000	8675	8305
80°	8114	7773	7705
85°	7126	6854	6570



TEST NUMBER: P332191-930

CATALOG NUMBER: S123DIW-S1000D755U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.6	2.2
10°-20°	343.3	6.2
20°-30°	507.0	9.2
30°-40°	592.3	10.8
40°-50°	595.5	10.8
50°-60°	523.1	9.5
60°-70°	389.7	7.1
70°-80°	222.0	4.0
80°-90°	66.0	1.2
90°-100°	50.2	0.9
100°-110°	150.2	2.7
110°-120°	255.5	4.6
120°-130°	336.1	6.1
130°-140°	377.7	6.9
140°-150°	371.3	6.8
150°-160°	312.6	5.7
160°-170°	208.1	3.8
170°-180°	72.9	1.3
0°-30°	971.9	17.7
0°-40°	1564.1	28.5
0°-60°	2682.6	48.8
0°-90°	3360.3	61.2
90°-120°	455.9	8.3
90°-150°	1540.9	28.0
90°-180°	2134.0	38.8
0°-180°	5494.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1290	1290	1290	1290	1290	
5°	1292	1286	1274	1284	1283	122
15°	1230	1224	1211	1219	1213	346
25°	1116	1109	1095	1096	1093	514
35°	965	958	944	938	932	604
45°	791	786	772	759	753	611
55°	600	598	585	573	567	538
65°	409	404	393	384	381	404
75°	216	212	209	203	200	231
85°	58	56	56	53	53	63
90°	1	7	14	17	18	5
95°	36	40	45	47	47	40
105°	136	138	143	143	144	146
115°	257	259	258	258	258	254
125°	376	378	377	375	372	336
135°	488	492	491	489	488	376
145°	592	594	596	595	592	370
155°	678	678	679	681	677	312
165°	739	737	737	740	736	208
175°	768	766	766	769	766	73
180°	770	770	770	770	770	



TEST NUMBER: P332191-930

CATALOG NUMBER: S123DIW-S1000D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1294.9	1294.2	1293.4	1292.6	1291.8	1290.3	1288.2	1286.0	1283.9	1281.7	1283.6
5°	1291.6	1290.4	1289.2	1287.9	1286.7	1284.7	1282.1	1279.3	1276.6	1273.9	1276.4
7.5°	1279.0	1277.7	1276.5	1275.3	1274.1	1272.0	1269.3	1266.4	1263.6	1260.8	1263.0
10°	1268.4	1267.1	1265.8	1264.6	1263.4	1261.2	1258.0	1254.7	1251.6	1248.4	1250.6
12.5°	1254.1	1253.1	1252.1	1251.0	1250.0	1248.0	1245.0	1241.9	1238.9	1235.9	1237.5
15°	1229.5	1228.5	1227.5	1226.5	1225.6	1223.4	1220.3	1217.1	1213.8	1210.6	1212.6
17.5°	1200.9	1199.5	1198.3	1197.0	1195.7	1193.5	1190.3	1187.1	1183.9	1180.6	1182.0
20°	1179.6	1178.1	1176.6	1175.1	1173.6	1171.3	1168.1	1164.9	1161.7	1158.5	1159.4
22.5°	1155.6	1154.1	1152.7	1151.1	1149.7	1147.4	1144.1	1140.9	1137.8	1134.5	1135.3
25°	1116.3	1114.8	1113.4	1111.9	1110.4	1108.1	1104.8	1101.6	1098.5	1095.2	1095.4
27.5°	1074.4	1072.9	1071.5	1070.1	1068.6	1066.2	1062.7	1059.3	1055.8	1052.4	1052.6
30°	1044.2	1042.9	1041.7	1040.5	1039.3	1036.9	1033.5	1030.0	1026.5	1023.1	1023.1
32.5°	1014.0	1012.4	1010.7	1009.1	1007.5	1005.3	1002.7	1000.0	997.4	994.7	993.3
35°	965.4	963.9	962.5	961.0	959.4	957.2	953.9	950.7	947.5	944.3	942.8
37.5°	915.7	913.8	911.9	910.0	908.2	905.6	902.4	899.1	895.9	892.6	890.8
40°	881.1	879.5	878.1	876.6	875.1	872.7	869.2	865.8	862.3	858.8	856.9
42.5°	846.4	844.7	843.1	841.4	839.8	837.1	833.7	830.3	826.8	823.4	821.4
45°	791.2	790.2	789.2	788.2	787.3	785.1	782.0	778.7	775.5	772.3	769.4
47.5°	736.4	734.9	733.5	732.1	730.7	728.4	725.5	722.4	719.4	716.4	713.5
50°	699.1	697.8	696.6	695.4	694.1	691.9	688.7	685.5	682.3	679.1	676.4
52.5°	660.0	659.2	658.4	657.5	656.6	654.5	651.2	647.8	644.3	640.9	638.6
55°	600.3	600.1	599.8	599.6	599.3	597.6	594.4	591.2	588.0	584.8	582.0
57.5°	543.5	542.7	541.8	541.0	540.1	538.4	535.9	533.3	530.8	528.2	525.8
60°	502.6	502.4	502.1	501.9	501.7	500.1	497.1	494.2	491.2	488.3	486.0
62.5°	466.3	465.6	465.0	464.3	463.7	461.9	458.9	456.0	453.1	450.0	447.8
65°	409.4	408.2	407.0	405.8	404.6	402.7	400.2	397.8	395.3	392.8	390.9
67.5°	349.4	348.2	347.2	346.1	345.0	343.5	341.6	339.7	337.9	336.0	334.3
70°	312.9	311.4	310.0	308.5	307.0	305.5	304.0	302.6	301.1	299.6	297.9
72.5°	274.8	273.7	272.6	271.5	270.4	269.0	267.3	265.7	264.0	262.3	260.8
75°	216.4	215.4	214.4	213.4	212.5	211.6	210.8	210.1	209.4	208.6	207.4
77.5°	164.7	164.1	163.5	163.1	162.5	161.8	160.9	160.0	159.1	158.2	157.4
80°	130.9	130.2	129.5	128.7	128.0	127.3	126.9	126.4	125.9	125.4	125.1
82.5°	98.1	97.9	97.8	97.7	97.5	97.3	97.3	97.2	97.1	97.0	96.5
85°	57.7	57.2	56.7	56.3	55.8	55.5	55.5	55.5	55.5	55.5	55.0
87.5°	23.2	22.9	22.6	22.3	21.9	21.9	22.0	22.1	22.3	22.4	22.3
90°	0.6	2.0	3.3	4.6	6.0	7.5	9.3	11.0	12.8	14.5	15.1
92.5°	14.7	15.6	16.5	17.4	18.3	19.2	20.2	21.3	22.3	23.2	23.6
95°	35.7	36.6	37.6	38.6	39.5	40.4	41.6	42.6	43.7	44.8	45.3
97.5°	63.4	64.1	64.8	65.6	66.2	66.9	67.8	68.5	69.3	70.1	70.7
100°	82.3	83.1	83.9	84.7	85.5	86.3	86.9	87.6	88.3	88.9	89.4
102.5°	104.1	104.6	105.1	105.5	106.0	106.7	107.6	108.5	109.3	110.2	110.6
105°	136.2	136.4	136.7	137.0	137.2	137.9	139.2	140.4	141.6	142.8	142.8
107.5°	173.4	173.6	173.7	173.9	174.1	174.4	174.9	175.4	175.9	176.3	176.8
110°	196.7	197.0	197.2	197.5	197.7	198.0	198.3	198.5	198.9	199.1	199.7



TEST NUMBER: P332191-930

CATALOG NUMBER: S123DIW-S1000D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	220.9	221.0	221.2	221.4	221.5	221.6	221.7	221.8	221.8	221.8	222.5
115°	257.2	257.6	258.0	258.4	258.8	258.9	258.6	258.4	258.0	257.8	258.0
117.5°	293.8	294.0	294.2	294.6	294.8	294.8	294.4	294.1	293.8	293.3	293.3
120°	316.5	317.3	318.1	318.9	319.8	319.8	319.1	318.5	317.8	317.1	317.0
122.5°	340.2	340.8	341.4	342.0	342.6	342.7	342.3	342.0	341.7	341.3	341.0
125°	376.4	376.8	377.2	377.6	378.1	378.1	377.8	377.6	377.2	377.0	376.5
127.5°	409.8	410.7	411.6	412.4	413.3	413.5	413.3	412.9	412.6	412.4	411.6
130°	432.1	433.2	434.2	435.3	436.3	436.8	436.3	435.9	435.5	435.1	434.6
132.5°	454.4	455.4	456.5	457.5	458.7	459.0	458.8	458.4	458.1	457.9	457.2
135°	488.4	489.2	490.0	490.8	491.5	492.0	491.8	491.6	491.5	491.4	490.8
137.5°	519.8	520.5	521.1	521.9	522.5	523.0	523.3	523.7	524.1	524.4	523.8
140°	541.6	542.3	543.0	543.6	544.3	544.7	544.9	544.9	545.1	545.3	545.1
142.5°	561.5	562.1	562.8	563.5	564.1	564.6	564.8	565.1	565.3	565.6	565.4
145°	592.5	592.7	593.0	593.2	593.5	593.9	594.3	594.7	595.1	595.5	595.3
147.5°	619.5	620.0	620.5	621.0	621.5	621.9	622.3	622.6	623.1	623.5	623.5
150°	638.5	638.7	639.0	639.3	639.5	639.8	640.0	640.3	640.6	640.8	640.8
152.5°	654.0	654.3	654.7	655.1	655.4	655.7	655.8	656.0	656.2	656.3	656.6
155°	678.4	678.4	678.4	678.4	678.4	678.4	678.6	678.7	678.8	679.0	679.6
157.5°	699.2	699.0	698.9	698.7	698.5	698.5	698.6	698.7	698.9	699.0	699.5
160°	712.2	712.0	711.8	711.4	711.2	711.0	711.0	711.0	711.0	711.0	711.8
162.5°	723.9	723.5	723.1	722.8	722.4	722.3	722.4	722.4	722.6	722.7	723.3
165°	738.9	738.5	738.1	737.7	737.3	737.0	737.0	737.0	737.0	737.0	737.8
167.5°	750.9	750.3	749.8	749.3	748.7	748.5	748.6	748.7	748.9	748.9	749.7
170°	757.7	757.1	756.6	756.0	755.5	755.2	755.2	755.2	755.2	755.2	756.2
172.5°	763.0	762.5	761.9	761.3	760.8	760.5	760.5	760.5	760.5	760.5	761.4
175°	768.5	768.0	767.4	767.0	766.4	766.1	766.1	766.1	766.1	766.1	767.0
177.5°	770.9	770.4	770.0	769.6	769.2	768.9	768.9	768.9	768.9	768.9	769.6
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4



TEST NUMBER: P332191-930

CATALOG NUMBER: S123DIW-S1000D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1285.6	1287.6	1289.6	1290.5	1290.2	1290.0	1289.8	1289.6
5°	1278.8	1281.2	1283.8	1284.7	1284.3	1283.8	1283.3	1282.8
7.5°	1265.3	1267.5	1269.7	1270.6	1270.3	1270.1	1269.7	1269.4
10°	1252.8	1255.0	1257.3	1258.1	1257.6	1257.1	1256.6	1256.1
12.5°	1239.2	1240.8	1242.4	1243.1	1242.8	1242.5	1242.2	1241.9
15°	1214.6	1216.5	1218.5	1218.8	1217.3	1215.8	1214.3	1212.8
17.5°	1183.4	1184.8	1186.2	1186.6	1186.1	1185.5	1185.0	1184.5
20°	1160.4	1161.5	1162.5	1162.5	1161.8	1161.1	1160.3	1159.6
22.5°	1136.1	1136.9	1137.7	1137.6	1136.7	1135.7	1134.8	1133.8
25°	1095.7	1096.0	1096.3	1096.0	1095.2	1094.5	1093.7	1093.0
27.5°	1052.8	1053.0	1053.2	1052.8	1051.9	1050.9	1050.0	1049.0
30°	1023.1	1023.1	1023.1	1022.2	1020.5	1018.8	1017.1	1015.3
32.5°	991.9	990.6	989.2	988.0	987.1	986.1	985.2	984.2
35°	941.3	939.9	938.4	937.0	935.8	934.6	933.4	932.1
37.5°	889.1	887.3	885.5	884.2	883.5	882.6	881.8	881.1
40°	854.9	853.0	851.0	849.5	848.5	847.5	846.5	845.5
42.5°	819.4	817.4	815.5	814.0	813.0	812.0	811.1	810.1
45°	766.4	763.4	760.5	758.4	757.2	755.9	754.7	753.4
47.5°	710.5	707.7	704.7	702.8	701.6	700.6	699.5	698.4
50°	673.7	671.0	668.2	666.2	664.7	663.2	661.7	660.2
52.5°	636.3	634.0	631.7	629.7	628.3	626.8	625.3	623.9
55°	579.4	576.7	574.0	571.9	570.7	569.5	568.3	567.0
57.5°	523.3	521.0	518.5	516.6	515.2	513.7	512.3	510.9
60°	483.8	481.6	479.4	477.7	476.4	475.2	473.9	472.7
62.5°	445.6	443.4	441.2	439.7	438.8	438.0	437.2	436.3
65°	388.9	386.9	384.9	383.6	382.9	382.1	381.3	380.6
67.5°	332.6	330.8	329.1	327.8	326.7	325.6	324.6	323.6
70°	296.1	294.4	292.7	291.2	290.0	288.8	287.6	286.3
72.5°	259.3	257.7	256.2	255.1	254.5	253.8	253.2	252.6
75°	206.2	204.9	203.7	202.7	201.9	201.2	200.5	199.7
77.5°	156.5	155.7	154.9	154.5	154.5	154.5	154.5	154.5
80°	124.9	124.7	124.4	124.3	124.3	124.3	124.3	124.3
82.5°	96.1	95.6	95.2	94.9	94.7	94.5	94.3	94.1
85°	54.5	54.0	53.5	53.2	53.2	53.2	53.2	53.2
87.5°	22.3	22.2	22.1	22.1	22.1	22.2	22.3	22.3
90°	15.6	16.1	16.7	17.0	17.4	17.6	17.9	18.2
92.5°	24.1	24.5	24.9	25.1	24.9	24.8	24.6	24.5
95°	45.8	46.4	47.0	47.2	47.2	47.2	47.2	47.2
97.5°	71.3	71.9	72.6	72.8	72.8	72.7	72.6	72.6
100°	89.8	90.2	90.6	90.9	91.2	91.5	91.7	92.0
102.5°	111.0	111.5	111.9	112.0	112.0	111.9	111.9	111.9
105°	142.8	142.8	142.8	142.9	143.2	143.5	143.7	144.1
107.5°	177.2	177.7	178.1	178.2	178.1	177.9	177.7	177.6
110°	200.2	200.7	201.2	201.4	201.1	200.8	200.6	200.3



TEST NUMBER: P332191-930

CATALOG NUMBER: S123DIW-S1000D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	223.1	223.8	224.5	224.7	224.7	224.6	224.5	224.5
115°	258.0	258.2	258.4	258.4	258.2	258.0	258.0	257.8
117.5°	293.3	293.3	293.3	293.1	292.7	292.3	292.0	291.6
120°	316.8	316.7	316.6	316.3	316.1	315.8	315.5	315.3
122.5°	340.6	340.2	339.9	339.6	339.2	338.8	338.4	338.0
125°	375.9	375.4	374.9	374.3	373.8	373.2	372.7	372.2
127.5°	410.8	410.1	409.4	408.6	408.1	407.4	406.8	406.2
130°	434.1	433.5	432.9	432.2	431.3	430.3	429.4	428.4
132.5°	456.6	455.9	455.3	454.6	453.9	453.1	452.4	451.7
135°	490.3	489.8	489.3	488.9	488.5	488.3	488.0	487.7
137.5°	523.3	522.7	522.2	521.6	521.1	520.6	520.1	519.6
140°	544.9	544.9	544.7	544.1	543.2	542.3	541.4	540.4
142.5°	565.3	565.2	565.0	564.6	563.9	563.1	562.4	561.7
145°	595.2	595.1	594.9	594.6	594.0	593.5	593.0	592.5
147.5°	623.5	623.5	623.5	623.1	622.2	621.4	620.6	619.8
150°	640.8	640.8	640.8	640.4	639.6	638.9	638.1	637.2
152.5°	656.8	657.0	657.2	657.0	656.2	655.6	654.8	654.2
155°	680.0	680.6	681.1	680.9	680.0	679.1	678.1	677.2
157.5°	700.1	700.7	701.2	701.1	700.3	699.6	698.9	698.1
160°	712.4	713.1	713.7	713.8	713.3	712.7	712.2	711.7
162.5°	724.0	724.7	725.4	725.3	724.4	723.6	722.7	721.8
165°	738.7	739.5	740.3	740.2	739.3	738.3	737.4	736.5
167.5°	750.6	751.5	752.3	752.3	751.5	750.6	749.7	748.9
170°	757.1	758.1	759.0	759.0	758.1	757.1	756.2	755.2
172.5°	762.2	763.0	763.9	763.9	762.9	762.0	761.0	760.1
175°	767.8	768.5	769.3	769.3	768.3	767.4	766.5	765.5
177.5°	770.2	770.9	771.5	771.4	770.7	769.9	769.2	768.4
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4

(END OF REPORT)