

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332446-935

Luminaire Tested: **S123RDIW-S775D1535U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332446-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D1535U935-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7910.1 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332446-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332446-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33			33
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	37	36	35	29			29
2	86	79	74	69	78	72	67	63	58	54	51	45	42	40	33	31	30	25			25
3	79	70	63	58	71	63	58	53	51	47	44	40	37	35	29	28	26	21			21
4	72	62	55	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19			19
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16			16
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18	15			15
7	57	45	37	32	51	41	34	30	33	29	25	26	23	20	20	18	16	13			13
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	18	16	14	12			12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11			11
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10			10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11334	11334	11334	11334
5°	13511	11382	10024	11382
10°	16869	11317	9055	11317
15°	19801	11202	8259	11202
20°	22100	11030	7581	11030
25°	21747	10847	7163	10847
30°	15632	10679	6734	10679
35°	10437	10461	6457	10461
40°	7690	10197	6169	10197
45°	6450	9736	5888	9736
50°	5692	9133	5494	9133
55°	4992	8443	4958	8443
60°	4445	7782	4540	7782
65°	3904	7073	4225	7073
70°	3065	6442	3858	6442
75°	2699	5627	3523	5627
80°	2349	4779	3465	4779
85°	1890	3841	3680	3841



TEST NUMBER: P332446-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	1.3
10°-20°	323.5	4.1
20°-30°	508.3	6.4
30°-40°	530.3	6.7
40°-50°	453.8	5.7
50°-60°	345.9	4.4
60°-70°	221.7	2.8
70°-80°	106.6	1.3
80°-90°	33.1	0.4
90°-100°	63.0	0.8
100°-110°	300.2	3.8
110°-120°	721.1	9.1
120°-130°	918.3	11.6
130°-140°	981.1	12.4
140°-150°	917.5	11.6
150°-160°	740.1	9.4
160°-170°	477.6	6.0
170°-180°	164.6	2.1
0°-30°	935.3	11.8
0°-40°	1465.6	18.5
0°-60°	2265.3	28.6
0°-90°	2626.7	33.2
90°-120°	1084.3	13.7
90°-150°	3901.2	49.3
90°-180°	5283.0	66.8
0°-180°	7910.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1053	1053	1053	1053	1053	
5°	1250	1053	928	1053	1250	129
15°	1777	1005	741	1005	1777	504
25°	1831	913	603	913	1831	787
35°	794	796	491	796	794	521
45°	424	640	387	640	424	333
55°	266	450	264	450	266	240
65°	153	278	166	278	153	151
75°	65	135	85	135	65	70
85°	15	31	30	31	15	19
90°	39	1	39	1	39	18
95°	49	78	49	78	49	41
105°	57	384	57	384	57	129
115°	757	720	757	720	757	699
125°	1035	1014	1035	1014	1035	924
135°	1276	1263	1276	1263	1276	984
145°	1471	1457	1471	1457	1471	918
155°	1603	1605	1603	1605	1603	739
165°	1689	1693	1689	1693	1689	477
175°	1726	1732	1726	1732	1726	164
180°	1732	1732	1732	1732	1732	



TEST NUMBER: P332446-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1121.5	1123.0	1118.3	1117.6	1112.2	1110.7	1110.7	1103.1	1098.5	1092.4	1088.7
5°	1250.4	1257.7	1254.0	1246.0	1232.4	1229.2	1220.7	1207.2	1191.9	1172.9	1163.9
7.5°	1411.4	1421.3	1417.6	1405.0	1390.9	1379.4	1355.2	1332.7	1301.3	1273.7	1250.1
10°	1543.4	1533.1	1525.0	1512.8	1499.8	1478.5	1453.3	1418.6	1378.5	1346.9	1311.7
12.5°	1642.3	1640.5	1630.3	1617.7	1599.3	1579.2	1548.2	1505.9	1459.2	1413.7	1373.5
15°	1776.9	1779.7	1772.9	1759.8	1733.7	1698.1	1651.2	1633.6	1566.9	1517.3	1467.7
17.5°	1870.2	1869.7	1868.7	1850.6	1823.9	1798.6	1755.1	1708.9	1648.5	1578.6	1511.8
20°	1929.3	1924.9	1925.7	1905.4	1885.6	1856.3	1814.0	1746.8	1697.2	1616.5	1547.5
22.5°	1927.9	1927.0	1930.4	1923.5	1909.0	1886.6	1853.2	1796.6	1733.3	1651.8	1574.2
25°	1831.1	1827.5	1848.7	1854.5	1877.5	1881.5	1871.6	1840.6	1780.5	1696.7	1600.7
27.5°	1532.5	1530.5	1569.8	1619.0	1681.4	1729.9	1776.8	1799.4	1780.5	1720.5	1624.4
30°	1257.7	1300.0	1319.9	1391.1	1470.4	1565.1	1648.0	1726.9	1746.3	1720.2	1641.2
32.5°	1044.2	1081.2	1097.7	1158.8	1232.8	1343.7	1468.1	1579.8	1658.7	1678.7	1631.2
35°	794.3	794.7	832.6	859.6	928.2	1042.2	1163.0	1312.7	1461.4	1574.1	1585.8
37.5°	633.8	636.0	658.9	685.9	737.3	797.6	904.0	1028.4	1200.2	1373.2	1474.6
40°	547.3	551.3	568.4	595.0	632.0	677.5	760.4	877.7	1021.0	1213.5	1370.8
42.5°	491.7	498.3	507.1	527.6	550.5	593.1	660.2	750.7	881.1	1063.1	1244.6
45°	423.7	427.3	434.1	443.6	464.3	494.0	539.2	599.9	708.2	854.7	1036.3
47.5°	373.8	371.9	379.0	386.7	400.5	420.8	451.0	500.7	577.8	695.3	849.5
50°	339.9	339.4	344.4	350.3	363.3	378.2	403.0	440.4	501.7	599.1	740.2
52.5°	308.2	309.9	313.4	320.7	330.1	342.2	364.4	391.3	444.0	528.1	645.7
55°	266.0	267.3	272.2	276.3	283.1	295.2	309.3	331.7	367.8	426.5	523.3
57.5°	230.2	229.6	234.4	235.4	243.1	253.0	263.8	281.3	307.5	350.9	416.2
60°	206.5	205.1	209.1	212.3	216.4	224.5	233.5	250.6	271.4	303.3	359.3
62.5°	184.9	184.2	187.2	190.3	193.6	201.0	208.6	221.8	238.2	265.2	309.5
65°	153.3	154.6	155.9	157.3	159.1	163.6	170.8	179.9	191.1	210.1	242.0
67.5°	120.5	121.8	122.3	125.0	128.9	131.7	136.1	144.1	152.0	168.0	186.1
70°	97.4	96.9	97.4	98.8	103.7	108.7	114.5	120.4	125.3	136.6	151.9
72.5°	83.7	82.8	84.0	84.3	86.7	88.1	91.8	97.3	103.7	111.3	122.3
75°	64.9	64.9	64.9	64.9	66.7	67.6	69.0	70.3	72.6	76.2	84.3
77.5°	48.0	48.0	48.6	49.2	49.5	50.0	50.9	52.2	53.0	54.9	58.5
80°	37.9	38.3	37.9	38.3	38.3	39.2	39.7	41.0	41.5	43.7	45.1
82.5°	28.5	28.2	28.5	28.9	28.9	29.9	30.0	30.9	31.0	32.2	33.6
85°	15.3	14.5	15.3	14.9	15.8	14.9	15.3	16.2	16.2	16.7	18.5
87.5°	11.4	12.0	11.1	11.4	11.2	11.5	11.2	10.9	11.5	10.8	10.5
90°	38.6	38.1	37.5	36.9	36.3	35.5	34.4	33.1	32.0	30.9	27.2
92.5°	42.7	42.4	42.0	41.7	41.3	40.3	38.5	36.6	34.8	33.0	30.1
95°	48.9	48.9	48.9	48.9	48.9	47.9	45.9	43.9	41.9	39.9	36.8
97.5°	53.0	52.8	52.4	52.2	51.9	50.6	48.3	46.1	43.7	41.4	62.1
100°	54.1	53.8	53.5	53.2	53.0	51.7	49.3	47.0	44.8	42.4	87.1
102.5°	55.1	54.6	54.1	53.6	53.0	56.3	63.5	70.5	77.6	84.7	133.5
105°	56.7	56.1	55.5	54.9	54.3	79.4	130.0	180.6	231.3	281.9	307.6
107.5°	177.9	216.0	254.2	292.4	330.5	368.2	405.3	442.4	479.6	516.7	512.6
110°	354.0	394.9	435.8	476.6	517.5	542.8	552.2	561.6	571.1	580.5	577.4



TEST NUMBER: P332446-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	607.3	616.0	624.6	633.2	641.9	646.1	645.9	645.8	645.6	645.4	642.2
115°	756.9	755.7	754.6	753.5	752.3	750.3	747.4	744.6	741.7	738.8	736.2
117.5°	840.8	840.6	840.3	840.1	839.9	838.6	836.3	834.1	831.7	829.5	828.1
120°	898.5	898.5	898.5	898.5	898.5	897.3	895.0	892.8	890.4	888.1	887.3
122.5°	955.1	954.8	954.6	954.4	954.2	953.3	951.7	950.0	948.5	946.8	945.7
125°	1034.9	1034.3	1033.7	1033.2	1032.6	1032.0	1031.5	1030.9	1030.4	1029.8	1028.6
127.5°	1111.6	1112.2	1112.8	1113.4	1113.9	1113.7	1112.8	1111.9	1110.9	1110.1	1108.7
130°	1161.1	1161.6	1162.2	1162.8	1163.3	1163.0	1161.9	1160.7	1159.6	1158.5	1157.4
132.5°	1206.3	1207.1	1208.0	1208.8	1209.5	1209.4	1208.2	1207.1	1205.9	1204.8	1203.9
135°	1275.6	1276.4	1277.3	1278.2	1279.0	1279.0	1278.2	1277.3	1276.4	1275.6	1274.5
137.5°	1340.7	1341.3	1341.9	1342.5	1343.0	1342.6	1341.3	1339.9	1338.5	1337.1	1336.5
140°	1379.8	1380.4	1381.0	1381.6	1382.2	1381.8	1380.7	1379.6	1378.5	1377.3	1376.4
142.5°	1415.9	1416.7	1417.5	1418.3	1419.1	1419.0	1418.2	1417.2	1416.3	1415.4	1414.5
145°	1471.3	1471.3	1471.3	1471.3	1471.3	1470.9	1470.4	1469.8	1469.2	1468.7	1468.1
147.5°	1512.4	1513.7	1515.1	1516.4	1517.7	1518.1	1517.5	1516.9	1516.4	1515.8	1515.2
150°	1543.3	1544.2	1545.1	1545.9	1546.8	1546.9	1546.4	1545.8	1545.2	1544.6	1544.0
152.5°	1568.1	1569.3	1570.6	1572.0	1573.3	1573.5	1572.4	1571.4	1570.4	1569.3	1569.0
155°	1602.6	1604.2	1605.9	1607.7	1609.4	1609.6	1608.1	1606.7	1605.2	1603.8	1603.5
157.5°	1631.6	1633.8	1636.1	1638.3	1640.5	1640.8	1639.1	1637.4	1635.6	1633.9	1634.3
160°	1650.2	1652.2	1654.2	1656.1	1658.2	1658.3	1656.6	1654.9	1653.2	1651.5	1651.7
162.5°	1667.7	1669.5	1671.2	1673.0	1674.7	1674.6	1672.8	1670.8	1668.9	1666.9	1667.2
165°	1688.8	1690.7	1692.8	1694.8	1696.8	1696.7	1694.4	1692.0	1689.8	1687.5	1687.8
167.5°	1704.0	1706.2	1708.6	1710.8	1713.1	1713.1	1710.8	1708.6	1706.2	1704.0	1704.0
170°	1713.2	1715.5	1717.8	1720.1	1722.4	1722.4	1720.1	1717.8	1715.5	1713.2	1713.2
172.5°	1718.4	1720.9	1723.5	1726.0	1728.5	1728.5	1726.3	1724.0	1721.7	1719.4	1719.2
175°	1726.1	1728.4	1730.7	1732.9	1735.3	1735.4	1733.4	1731.4	1729.4	1727.4	1727.1
177.5°	1728.5	1730.7	1733.0	1735.3	1737.6	1737.8	1735.9	1734.1	1732.3	1730.5	1730.3
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332446-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1087.3	1086.2	1081.2	1075.4	1067.8	1062.7	1058.8	1056.6	1050.2	1042.2	1036.8
5°	1154.4	1140.9	1126.5	1108.9	1092.7	1076.0	1065.7	1053.4	1038.6	1021.9	1010.2
7.5°	1226.4	1199.9	1171.3	1141.9	1112.7	1086.6	1063.5	1043.7	1020.0	996.1	979.4
10°	1281.6	1242.8	1202.6	1161.7	1124.2	1089.1	1062.0	1035.4	1007.0	979.6	958.8
12.5°	1331.7	1280.7	1234.4	1184.0	1136.2	1094.2	1055.2	1023.9	989.7	960.4	936.8
15°	1395.2	1342.9	1286.9	1210.3	1146.8	1093.6	1046.3	1005.2	963.8	927.7	904.7
17.5°	1454.5	1375.8	1300.7	1236.7	1154.2	1087.7	1029.9	980.9	935.4	897.2	868.8
20°	1479.0	1402.8	1321.2	1239.7	1158.5	1084.1	1016.9	962.9	915.5	872.3	846.1
22.5°	1493.7	1407.5	1321.5	1233.9	1147.7	1070.4	1004.0	944.4	893.2	852.0	819.8
25°	1511.0	1408.3	1313.5	1227.0	1139.1	1055.2	976.4	913.3	857.8	814.1	779.8
27.5°	1522.3	1401.4	1289.6	1193.3	1104.2	1020.7	948.4	881.6	825.3	779.0	742.3
30°	1524.5	1396.0	1271.2	1167.1	1076.4	999.8	923.2	859.2	799.7	750.5	716.3
32.5°	1527.4	1382.7	1246.3	1135.7	1042.9	967.0	897.6	836.5	775.5	727.1	692.2
35°	1515.5	1375.4	1208.5	1081.4	988.5	915.1	852.4	796.1	736.2	689.2	653.6
37.5°	1464.3	1346.0	1169.4	1020.3	923.2	855.1	804.1	754.9	700.0	649.4	615.9
40°	1412.7	1317.2	1139.1	983.2	881.8	811.8	765.9	725.7	672.5	625.3	589.2
42.5°	1335.9	1277.9	1110.3	944.2	834.8	767.5	728.8	691.1	644.5	596.4	562.5
45°	1195.0	1202.6	1051.2	882.2	769.9	702.3	665.8	639.6	598.2	558.5	523.8
47.5°	1018.3	1089.9	981.9	816.1	701.5	638.0	606.1	583.3	555.3	516.4	484.7
50°	902.9	1005.2	926.3	771.7	658.6	595.5	564.0	545.4	521.1	490.4	460.2
52.5°	796.5	906.5	859.3	722.3	612.1	554.4	523.6	508.3	489.0	460.1	432.8
55°	649.5	761.0	750.1	647.7	542.3	490.4	467.0	449.9	436.8	415.2	393.6
57.5°	525.5	631.0	636.6	564.8	480.8	429.6	409.4	396.5	388.0	371.6	351.6
60°	447.2	544.1	563.0	508.9	436.8	391.8	371.9	361.5	354.7	341.7	326.4
62.5°	382.3	464.8	486.2	447.3	394.6	352.4	336.9	326.9	322.3	311.0	297.5
65°	292.6	361.1	381.8	360.2	332.7	298.9	286.3	277.7	273.6	267.3	257.4
67.5°	220.0	269.9	292.7	277.4	267.5	246.2	238.1	233.5	229.9	225.6	217.3
70°	176.7	213.7	237.1	233.1	225.0	213.7	207.8	204.7	201.0	197.4	190.2
72.5°	142.1	167.6	189.5	191.6	184.9	182.6	177.5	176.2	174.0	169.7	165.7
75°	94.2	111.8	127.1	132.9	135.7	137.9	135.7	135.3	134.7	131.2	128.9
77.5°	61.7	71.2	80.8	90.8	95.1	98.2	98.9	100.6	99.4	97.5	96.3
80°	47.4	49.6	56.3	64.9	71.6	74.4	76.2	77.1	76.6	76.2	74.4
82.5°	34.4	36.2	39.4	45.5	51.1	55.6	56.7	56.6	57.5	57.8	56.3
85°	18.5	18.9	19.8	20.8	23.8	28.8	30.2	31.1	32.0	32.0	29.3
87.5°	10.4	9.4	9.3	8.7	9.2	9.0	10.6	11.8	12.7	11.9	12.4
90°	23.4	19.7	16.0	12.7	9.9	7.0	4.1	1.3	4.1	7.0	9.9
92.5°	27.4	24.5	21.7	20.8	21.5	22.3	23.2	23.9	23.2	22.3	21.5
95°	33.6	30.5	27.3	31.6	43.3	55.1	66.8	78.5	66.8	55.1	43.3
97.5°	82.7	103.2	123.8	136.7	142.0	147.3	152.6	157.8	152.6	147.3	142.0
100°	131.7	176.3	220.9	240.4	234.7	228.9	223.3	217.6	223.3	228.9	234.7
102.5°	182.2	230.9	279.7	302.0	297.8	293.8	289.6	285.5	289.6	293.8	297.8
105°	333.4	359.1	384.9	396.1	393.0	389.9	386.8	383.6	386.8	389.9	393.0
107.5°	508.6	504.5	500.4	497.1	494.6	492.1	489.6	487.1	489.6	492.1	494.6
110°	574.2	571.1	567.9	565.2	562.9	560.6	558.4	556.0	558.4	560.6	562.9



TEST NUMBER: P332446-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	639.1	635.9	632.8	630.2	628.2	626.1	624.1	622.0	624.1	626.1	628.2
115°	733.7	731.2	728.6	726.4	724.7	723.0	721.3	719.5	721.3	723.0	724.7
117.5°	826.8	825.5	824.2	822.5	820.4	818.2	816.1	814.0	816.1	818.2	820.4
120°	886.4	885.5	884.8	883.0	880.5	877.9	875.3	872.7	875.3	877.9	880.5
122.5°	944.7	943.6	942.5	940.9	938.7	936.7	934.5	932.5	934.5	936.7	938.7
125°	1027.4	1026.3	1025.2	1023.5	1021.1	1018.9	1016.6	1014.3	1016.6	1018.9	1021.1
127.5°	1107.3	1106.0	1104.6	1102.8	1100.4	1098.2	1095.9	1093.6	1095.9	1098.2	1100.4
130°	1156.2	1155.0	1153.9	1152.2	1149.9	1147.6	1145.3	1143.0	1145.3	1147.6	1149.9
132.5°	1203.0	1202.0	1201.2	1199.5	1197.2	1195.0	1192.7	1190.4	1192.7	1195.0	1197.2
135°	1273.3	1272.1	1271.0	1269.6	1267.9	1266.2	1264.5	1262.7	1264.5	1266.2	1267.9
137.5°	1335.8	1335.2	1334.6	1333.2	1331.0	1328.9	1326.7	1324.5	1326.7	1328.9	1331.0
140°	1375.5	1374.7	1373.8	1372.6	1370.9	1369.2	1367.4	1365.7	1367.4	1369.2	1370.9
142.5°	1413.7	1412.8	1412.0	1410.7	1408.9	1407.2	1405.5	1403.8	1405.5	1407.2	1408.9
145°	1467.5	1467.0	1466.4	1465.1	1463.1	1461.1	1459.1	1457.1	1459.1	1461.1	1463.1
147.5°	1514.7	1514.1	1513.5	1512.5	1511.2	1509.9	1508.6	1507.3	1508.6	1509.9	1511.2
150°	1543.5	1542.9	1542.3	1541.6	1540.8	1539.9	1539.0	1538.2	1539.0	1539.9	1540.8
152.5°	1568.7	1568.3	1568.0	1567.6	1567.2	1566.8	1566.4	1566.0	1566.4	1566.8	1567.2
155°	1603.3	1603.0	1602.7	1602.8	1603.4	1604.0	1604.6	1605.1	1604.6	1604.0	1603.4
157.5°	1634.5	1634.8	1635.1	1635.3	1635.3	1635.4	1635.5	1635.5	1635.5	1635.4	1635.3
160°	1652.0	1652.3	1652.6	1652.9	1653.2	1653.5	1653.7	1654.1	1653.7	1653.5	1653.2
162.5°	1667.5	1667.8	1668.0	1668.5	1669.3	1670.1	1670.8	1671.5	1670.8	1670.1	1669.3
165°	1688.1	1688.3	1688.7	1689.2	1690.1	1690.9	1691.8	1692.6	1691.8	1690.9	1690.1
167.5°	1704.0	1704.0	1704.0	1704.5	1705.7	1706.8	1708.0	1709.1	1708.0	1706.8	1705.7
170°	1713.2	1713.2	1713.2	1713.8	1714.9	1716.1	1717.3	1718.4	1717.3	1716.1	1714.9
172.5°	1719.0	1718.7	1718.5	1719.1	1720.5	1721.8	1723.2	1724.6	1723.2	1721.8	1720.5
175°	1726.8	1726.6	1726.2	1726.8	1728.3	1729.7	1731.1	1732.5	1731.1	1729.7	1728.3
177.5°	1730.0	1729.8	1729.6	1730.0	1731.2	1732.3	1733.5	1734.6	1733.5	1732.3	1731.2
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332446-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1035.0	1030.3	1027.1	1019.9	1015.1	1010.1	1005.0	1008.3	1008.0	1007.5	1007.5
5°	1000.3	989.9	980.4	968.3	960.6	951.1	943.9	943.1	944.9	938.5	934.9
7.5°	965.9	951.7	938.2	924.8	910.6	899.2	892.1	888.7	884.2	880.3	876.2
10°	941.7	925.0	911.9	895.3	879.9	866.4	857.8	852.0	848.8	845.7	839.8
12.5°	916.8	900.4	883.8	865.0	850.3	834.7	828.3	821.7	815.6	812.1	804.1
15°	880.4	859.2	841.6	821.7	805.6	790.2	781.2	768.1	766.3	761.8	753.7
17.5°	843.9	820.9	796.6	782.0	763.6	747.7	733.9	729.5	716.6	711.8	704.7
20°	815.0	793.8	775.3	756.0	729.4	714.5	703.7	697.8	687.4	681.1	676.6
22.5°	790.1	768.6	747.2	724.6	702.7	686.0	678.0	668.9	663.3	654.4	649.5
25°	754.6	731.2	705.5	681.1	665.4	652.7	640.1	632.0	623.9	619.8	610.8
27.5°	713.3	688.8	664.8	646.4	627.0	614.5	603.0	595.8	586.1	579.3	574.3
30°	690.6	661.8	641.0	624.3	599.5	587.8	579.3	570.2	563.0	555.8	550.9
32.5°	664.3	637.9	618.3	597.6	578.6	565.8	554.7	546.8	540.6	533.8	528.8
35°	622.9	600.9	580.6	559.8	545.9	532.8	519.8	513.0	507.1	500.8	496.3
37.5°	585.7	565.0	545.7	526.1	508.8	498.1	487.6	482.4	474.5	470.3	465.6
40°	562.6	542.3	521.5	502.7	484.6	476.5	467.0	459.3	452.1	449.0	444.0
42.5°	537.4	517.0	499.6	479.1	464.4	453.4	444.6	436.3	430.8	426.3	423.4
45°	499.9	481.9	464.8	444.4	430.5	421.0	411.1	403.5	398.5	395.4	390.4
47.5°	463.6	445.6	428.2	410.4	396.9	386.2	376.3	370.9	364.3	360.4	357.1
50°	437.2	421.0	402.5	386.3	372.8	362.0	353.9	347.1	341.2	336.3	334.1
52.5°	413.1	395.8	379.8	364.7	350.4	338.2	330.8	323.6	319.3	313.6	310.9
55°	373.2	356.5	343.0	328.1	314.2	303.8	294.8	288.5	284.0	277.7	274.1
57.5°	335.8	320.9	304.7	291.8	277.4	268.6	261.1	252.6	247.1	242.2	238.7
60°	310.6	293.4	279.5	267.3	254.7	243.4	236.7	229.9	224.0	219.0	215.9
62.5°	284.3	269.3	256.1	242.8	231.3	221.4	213.6	207.9	202.8	199.6	196.5
65°	243.8	232.1	218.6	207.8	197.0	189.8	183.5	178.5	174.9	172.6	170.0
67.5°	206.7	195.4	183.6	172.9	165.7	160.2	156.1	151.8	150.0	147.1	145.3
70°	182.5	170.8	160.5	152.4	145.2	141.1	138.4	135.3	133.5	129.8	128.0
72.5°	156.3	147.7	140.3	133.6	127.9	124.2	120.7	116.8	114.0	109.9	108.2
75°	123.0	115.4	109.5	105.0	101.4	96.4	91.5	87.5	86.1	84.7	84.3
77.5°	91.2	86.3	82.1	78.3	73.8	70.2	69.1	68.2	67.8	67.2	67.2
80°	71.6	67.2	64.0	59.5	56.8	56.8	56.8	55.9	56.3	56.3	56.3
82.5°	53.3	49.2	47.4	45.8	45.3	45.6	45.6	45.8	45.5	46.2	45.9
85°	27.5	28.0	28.8	28.4	28.8	28.8	29.8	29.3	29.8	28.8	29.8
87.5°	12.7	14.4	15.5	16.6	17.7	18.1	18.7	18.9	19.5	19.7	19.9
90°	12.7	16.0	19.7	23.4	27.2	30.9	32.0	33.1	34.4	35.5	36.3
92.5°	20.8	21.7	24.5	27.4	30.1	33.0	34.8	36.6	38.5	40.3	41.3
95°	31.6	27.3	30.5	33.6	36.8	39.9	41.9	43.9	45.9	47.9	48.9
97.5°	136.7	123.8	103.2	82.7	62.1	41.4	43.7	46.1	48.3	50.6	51.9
100°	240.4	220.9	176.3	131.7	87.1	42.4	44.8	47.0	49.3	51.7	53.0
102.5°	302.0	279.7	230.9	182.2	133.5	84.7	77.6	70.5	63.5	56.3	53.0
105°	396.1	384.9	359.1	333.4	307.6	281.9	231.3	180.6	130.0	79.4	54.3
107.5°	497.1	500.4	504.5	508.6	512.6	516.7	479.6	442.4	405.3	368.2	330.5
110°	565.2	567.9	571.1	574.2	577.4	580.5	571.1	561.6	552.2	542.8	517.5



TEST NUMBER: P332446-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	630.2	632.8	635.9	639.1	642.2	645.4	645.6	645.8	645.9	646.1	641.9
115°	726.4	728.6	731.2	733.7	736.2	738.8	741.7	744.6	747.4	750.3	752.3
117.5°	822.5	824.2	825.5	826.8	828.1	829.5	831.7	834.1	836.3	838.6	839.9
120°	883.0	884.8	885.5	886.4	887.3	888.1	890.4	892.8	895.0	897.3	898.5
122.5°	940.9	942.5	943.6	944.7	945.7	946.8	948.5	950.0	951.7	953.3	954.2
125°	1023.5	1025.2	1026.3	1027.4	1028.6	1029.8	1030.4	1030.9	1031.5	1032.0	1032.6
127.5°	1102.8	1104.6	1106.0	1107.3	1108.7	1110.1	1110.9	1111.9	1112.8	1113.7	1113.9
130°	1152.2	1153.9	1155.0	1156.2	1157.4	1158.5	1159.6	1160.7	1161.9	1163.0	1163.3
132.5°	1199.5	1201.2	1202.0	1203.0	1203.9	1204.8	1205.9	1207.1	1208.2	1209.4	1209.5
135°	1269.6	1271.0	1272.1	1273.3	1274.5	1275.6	1276.4	1277.3	1278.2	1279.0	1279.0
137.5°	1333.2	1334.6	1335.2	1335.8	1336.5	1337.1	1338.5	1339.9	1341.3	1342.6	1343.0
140°	1372.6	1373.8	1374.7	1375.5	1376.4	1377.3	1378.5	1379.6	1380.7	1381.8	1382.2
142.5°	1410.7	1412.0	1412.8	1413.7	1414.5	1415.4	1416.3	1417.2	1418.2	1419.0	1419.1
145°	1465.1	1466.4	1467.0	1467.5	1468.1	1468.7	1469.2	1469.8	1470.4	1470.9	1471.3
147.5°	1512.5	1513.5	1514.1	1514.7	1515.2	1515.8	1516.4	1516.9	1517.5	1518.1	1517.7
150°	1541.6	1542.3	1542.9	1543.5	1544.0	1544.6	1545.2	1545.8	1546.4	1546.9	1546.8
152.5°	1567.6	1568.0	1568.3	1568.7	1569.0	1569.3	1570.4	1571.4	1572.4	1573.5	1573.3
155°	1602.8	1602.7	1603.0	1603.3	1603.5	1603.8	1605.2	1606.7	1608.1	1609.6	1609.4
157.5°	1635.3	1635.1	1634.8	1634.5	1634.3	1633.9	1635.6	1637.4	1639.1	1640.8	1640.5
160°	1652.9	1652.6	1652.3	1652.0	1651.7	1651.5	1653.2	1654.9	1656.6	1658.3	1658.2
162.5°	1668.5	1668.0	1667.8	1667.5	1667.2	1666.9	1668.9	1670.8	1672.8	1674.6	1674.7
165°	1689.2	1688.7	1688.3	1688.1	1687.8	1687.5	1689.8	1692.0	1694.4	1696.7	1696.8
167.5°	1704.5	1704.0	1704.0	1704.0	1704.0	1704.0	1706.2	1708.6	1710.8	1713.1	1713.1
170°	1713.8	1713.2	1713.2	1713.2	1713.2	1713.2	1715.5	1717.8	1720.1	1722.4	1722.4
172.5°	1719.1	1718.5	1718.7	1719.0	1719.2	1719.4	1721.7	1724.0	1726.3	1728.5	1728.5
175°	1726.8	1726.2	1726.6	1726.8	1727.1	1727.4	1729.4	1731.4	1733.4	1735.4	1735.3
177.5°	1730.0	1729.6	1729.8	1730.0	1730.3	1730.5	1732.3	1734.1	1735.9	1737.8	1737.6
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332446-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1003.2	1002.9	1003.2	1001.8	1003.2	1002.9	1003.2	1007.5	1007.5	1008.0	1008.3
5°	933.6	933.1	931.8	927.7	931.8	933.1	933.6	934.9	938.5	944.9	943.1
7.5°	872.7	872.1	868.1	868.2	868.1	872.1	872.7	876.2	880.3	884.2	888.7
10°	836.6	837.1	831.7	828.5	831.7	837.1	836.6	839.8	845.7	848.8	852.0
12.5°	801.7	799.6	795.2	791.8	795.2	799.6	801.7	804.1	812.1	815.6	821.7
15°	755.5	751.0	740.2	741.1	740.2	751.0	755.5	753.7	761.8	766.3	768.1
17.5°	701.1	697.8	697.6	691.3	697.6	697.8	701.1	704.7	711.8	716.6	729.5
20°	669.4	667.2	668.0	661.8	668.0	667.2	669.4	676.6	681.1	687.4	697.8
22.5°	644.5	642.3	638.5	636.5	638.5	642.3	644.5	649.5	654.4	663.3	668.9
25°	608.1	604.5	600.9	603.1	600.9	604.5	608.1	610.8	619.8	623.9	632.0
27.5°	571.7	568.9	565.3	564.9	565.3	568.9	571.7	574.3	579.3	586.1	595.8
30°	548.6	545.9	544.1	541.8	544.1	545.9	548.6	550.9	555.8	563.0	570.2
32.5°	525.1	524.6	521.3	520.9	521.3	524.6	525.1	528.8	533.8	540.6	546.8
35°	494.5	491.8	490.9	491.4	490.9	491.8	494.5	496.3	500.8	507.1	513.0
37.5°	465.4	461.8	460.1	458.6	460.1	461.8	465.4	465.6	470.3	474.5	482.4
40°	444.4	440.8	440.0	439.0	440.0	440.8	444.4	444.0	449.0	452.1	459.3
42.5°	421.0	419.6	419.0	417.4	419.0	419.6	421.0	423.4	426.3	430.8	436.3
45°	389.0	388.6	385.9	386.8	385.9	388.6	389.0	390.4	395.4	398.5	403.5
47.5°	355.3	353.4	351.5	352.7	351.5	353.4	355.3	357.1	360.4	364.3	370.9
50°	332.3	331.3	327.3	328.1	327.3	331.3	332.3	334.1	336.3	341.2	347.1
52.5°	309.2	305.7	304.2	303.7	304.2	305.7	309.2	310.9	313.6	319.3	323.6
55°	271.0	266.8	265.0	264.2	265.0	266.8	271.0	274.1	277.7	284.0	288.5
57.5°	233.4	232.3	230.9	231.9	230.9	232.3	233.4	238.7	242.2	247.1	252.6
60°	211.4	211.4	211.4	210.9	211.4	211.4	211.4	215.9	219.0	224.0	229.9
62.5°	194.5	193.4	193.0	193.6	193.0	193.4	194.5	196.5	199.6	202.8	207.9
65°	168.6	168.2	166.3	165.9	166.3	168.2	168.6	170.0	172.6	174.9	178.5
67.5°	144.1	142.5	142.0	141.4	142.0	142.5	144.1	145.3	147.1	150.0	151.8
70°	125.8	124.8	122.2	122.6	122.2	124.8	125.8	128.0	129.8	133.5	135.3
72.5°	105.9	105.0	104.5	103.8	104.5	105.0	105.9	108.2	109.9	114.0	116.8
75°	83.9	83.4	82.9	84.7	82.9	83.4	83.9	84.3	84.7	86.1	87.5
77.5°	67.2	67.2	67.4	66.7	67.4	67.2	67.2	67.2	67.2	67.8	68.2
80°	56.3	56.3	55.9	55.9	55.9	56.3	56.3	56.3	56.3	56.3	55.9
82.5°	45.2	45.5	45.8	45.1	45.8	45.5	45.2	45.9	46.2	45.5	45.8
85°	29.8	29.3	30.2	29.8	30.2	29.3	29.8	29.8	28.8	29.8	29.3
87.5°	20.8	20.1	20.2	20.7	20.2	20.1	20.8	19.9	19.7	19.5	18.9
90°	36.9	37.5	38.1	38.6	38.1	37.5	36.9	36.3	35.5	34.4	33.1
92.5°	41.7	42.0	42.4	42.7	42.4	42.0	41.7	41.3	40.3	38.5	36.6
95°	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	47.9	45.9	43.9
97.5°	52.2	52.4	52.8	53.0	52.8	52.4	52.2	51.9	50.6	48.3	46.1
100°	53.2	53.5	53.8	54.1	53.8	53.5	53.2	53.0	51.7	49.3	47.0
102.5°	53.6	54.1	54.6	55.1	54.6	54.1	53.6	53.0	56.3	63.5	70.5
105°	54.9	55.5	56.1	56.7	56.1	55.5	54.9	54.3	79.4	130.0	180.6
107.5°	292.4	254.2	216.0	177.9	216.0	254.2	292.4	330.5	368.2	405.3	442.4
110°	476.6	435.8	394.9	354.0	394.9	435.8	476.6	517.5	542.8	552.2	561.6



TEST NUMBER: P332446-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	633.2	624.6	616.0	607.3	616.0	624.6	633.2	641.9	646.1	645.9	645.8
115°	753.5	754.6	755.7	756.9	755.7	754.6	753.5	752.3	750.3	747.4	744.6
117.5°	840.1	840.3	840.6	840.8	840.6	840.3	840.1	839.9	838.6	836.3	834.1
120°	898.5	898.5	898.5	898.5	898.5	898.5	898.5	898.5	897.3	895.0	892.8
122.5°	954.4	954.6	954.8	955.1	954.8	954.6	954.4	954.2	953.3	951.7	950.0
125°	1033.2	1033.7	1034.3	1034.9	1034.3	1033.7	1033.2	1032.6	1032.0	1031.5	1030.9
127.5°	1113.4	1112.8	1112.2	1111.6	1112.2	1112.8	1113.4	1113.9	1113.7	1112.8	1111.9
130°	1162.8	1162.2	1161.6	1161.1	1161.6	1162.2	1162.8	1163.3	1163.0	1161.9	1160.7
132.5°	1208.8	1208.0	1207.1	1206.3	1207.1	1208.0	1208.8	1209.5	1209.4	1208.2	1207.1
135°	1278.2	1277.3	1276.4	1275.6	1276.4	1277.3	1278.2	1279.0	1279.0	1278.2	1277.3
137.5°	1342.5	1341.9	1341.3	1340.7	1341.3	1341.9	1342.5	1343.0	1342.6	1341.3	1339.9
140°	1381.6	1381.0	1380.4	1379.8	1380.4	1381.0	1381.6	1382.2	1381.8	1380.7	1379.6
142.5°	1418.3	1417.5	1416.7	1415.9	1416.7	1417.5	1418.3	1419.1	1419.0	1418.2	1417.2
145°	1471.3	1471.3	1471.3	1471.3	1471.3	1471.3	1471.3	1471.3	1470.9	1470.4	1469.8
147.5°	1516.4	1515.1	1513.7	1512.4	1513.7	1515.1	1516.4	1517.7	1518.1	1517.5	1516.9
150°	1545.9	1545.1	1544.2	1543.3	1544.2	1545.1	1545.9	1546.8	1546.9	1546.4	1545.8
152.5°	1572.0	1570.6	1569.3	1568.1	1569.3	1570.6	1572.0	1573.3	1573.5	1572.4	1571.4
155°	1607.7	1605.9	1604.2	1602.6	1604.2	1605.9	1607.7	1609.4	1609.6	1608.1	1606.7
157.5°	1638.3	1636.1	1633.8	1631.6	1633.8	1636.1	1638.3	1640.5	1640.8	1639.1	1637.4
160°	1656.1	1654.2	1652.2	1650.2	1652.2	1654.2	1656.1	1658.2	1658.3	1656.6	1654.9
162.5°	1673.0	1671.2	1669.5	1667.7	1669.5	1671.2	1673.0	1674.7	1674.6	1672.8	1670.8
165°	1694.8	1692.8	1690.7	1688.8	1690.7	1692.8	1694.8	1696.8	1696.7	1694.4	1692.0
167.5°	1710.8	1708.6	1706.2	1704.0	1706.2	1708.6	1710.8	1713.1	1713.1	1710.8	1708.6
170°	1720.1	1717.8	1715.5	1713.2	1715.5	1717.8	1720.1	1722.4	1722.4	1720.1	1717.8
172.5°	1726.0	1723.5	1720.9	1718.4	1720.9	1723.5	1726.0	1728.5	1728.5	1726.3	1724.0
175°	1732.9	1730.7	1728.4	1726.1	1728.4	1730.7	1732.9	1735.3	1735.4	1733.4	1731.4
177.5°	1735.3	1733.0	1730.7	1728.5	1730.7	1733.0	1735.3	1737.6	1737.8	1735.9	1734.1
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332446-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1005.0	1010.1	1015.1	1019.9	1027.1	1030.3	1035.0	1036.8	1042.2	1050.2	1056.6
5°	943.9	951.1	960.6	968.3	980.4	989.9	1000.3	1010.2	1021.9	1038.6	1053.4
7.5°	892.1	899.2	910.6	924.8	938.2	951.7	965.9	979.4	996.1	1020.0	1043.7
10°	857.8	866.4	879.9	895.3	911.9	925.0	941.7	958.8	979.6	1007.0	1035.4
12.5°	828.3	834.7	850.3	865.0	883.8	900.4	916.8	936.8	960.4	989.7	1023.9
15°	781.2	790.2	805.6	821.7	841.6	859.2	880.4	904.7	927.7	963.8	1005.2
17.5°	733.9	747.7	763.6	782.0	796.6	820.9	843.9	868.8	897.2	935.4	980.9
20°	703.7	714.5	729.4	756.0	775.3	793.8	815.0	846.1	872.3	915.5	962.9
22.5°	678.0	686.0	702.7	724.6	747.2	768.6	790.1	819.8	852.0	893.2	944.4
25°	640.1	652.7	665.4	681.1	705.5	731.2	754.6	779.8	814.1	857.8	913.3
27.5°	603.0	614.5	627.0	646.4	664.8	688.8	713.3	742.3	779.0	825.3	881.6
30°	579.3	587.8	599.5	624.3	641.0	661.8	690.6	716.3	750.5	799.7	859.2
32.5°	554.7	565.8	578.6	597.6	618.3	637.9	664.3	692.2	727.1	775.5	836.5
35°	519.8	532.8	545.9	559.8	580.6	600.9	622.9	653.6	689.2	736.2	796.1
37.5°	487.6	498.1	508.8	526.1	545.7	565.0	585.7	615.9	649.4	700.0	754.9
40°	467.0	476.5	484.6	502.7	521.5	542.3	562.6	589.2	625.3	672.5	725.7
42.5°	444.6	453.4	464.4	479.1	499.6	517.0	537.4	562.5	596.4	644.5	691.1
45°	411.1	421.0	430.5	444.4	464.8	481.9	499.9	523.8	558.5	598.2	639.6
47.5°	376.3	386.2	396.9	410.4	428.2	445.6	463.6	484.7	516.4	555.3	583.3
50°	353.9	362.0	372.8	386.3	402.5	421.0	437.2	460.2	490.4	521.1	545.4
52.5°	330.8	338.2	350.4	364.7	379.8	395.8	413.1	432.8	460.1	489.0	508.3
55°	294.8	303.8	314.2	328.1	343.0	356.5	373.2	393.6	415.2	436.8	449.9
57.5°	261.1	268.6	277.4	291.8	304.7	320.9	335.8	351.6	371.6	388.0	396.5
60°	236.7	243.4	254.7	267.3	279.5	293.4	310.6	326.4	341.7	354.7	361.5
62.5°	213.6	221.4	231.3	242.8	256.1	269.3	284.3	297.5	311.0	322.3	326.9
65°	183.5	189.8	197.0	207.8	218.6	232.1	243.8	257.4	267.3	273.6	277.7
67.5°	156.1	160.2	165.7	172.9	183.6	195.4	206.7	217.3	225.6	229.9	233.5
70°	138.4	141.1	145.2	152.4	160.5	170.8	182.5	190.2	197.4	201.0	204.7
72.5°	120.7	124.2	127.9	133.6	140.3	147.7	156.3	165.7	169.7	174.0	176.2
75°	91.5	96.4	101.4	105.0	109.5	115.4	123.0	128.9	131.2	134.7	135.3
77.5°	69.1	70.2	73.8	78.3	82.1	86.3	91.2	96.3	97.5	99.4	100.6
80°	56.8	56.8	56.8	59.5	64.0	67.2	71.6	74.4	76.2	76.6	77.1
82.5°	45.6	45.6	45.3	45.8	47.4	49.2	53.3	56.3	57.8	57.5	56.6
85°	29.8	28.8	28.8	28.4	28.8	28.0	27.5	29.3	32.0	32.0	31.1
87.5°	18.7	18.1	17.7	16.6	15.5	14.4	12.7	12.4	11.9	12.7	11.8
90°	32.0	30.9	27.2	23.4	19.7	16.0	12.7	9.9	7.0	4.1	1.3
92.5°	34.8	33.0	30.1	27.4	24.5	21.7	20.8	21.5	22.3	23.2	23.9
95°	41.9	39.9	36.8	33.6	30.5	27.3	31.6	43.3	55.1	66.8	78.5
97.5°	43.7	41.4	62.1	82.7	103.2	123.8	136.7	142.0	147.3	152.6	157.8
100°	44.8	42.4	87.1	131.7	176.3	220.9	240.4	234.7	228.9	223.3	217.6
102.5°	77.6	84.7	133.5	182.2	230.9	279.7	302.0	297.8	293.8	289.6	285.5
105°	231.3	281.9	307.6	333.4	359.1	384.9	396.1	393.0	389.9	386.8	383.6
107.5°	479.6	516.7	512.6	508.6	504.5	500.4	497.1	494.6	492.1	489.6	487.1
110°	571.1	580.5	577.4	574.2	571.1	567.9	565.2	562.9	560.6	558.4	556.0



TEST NUMBER: P332446-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	645.6	645.4	642.2	639.1	635.9	632.8	630.2	628.2	626.1	624.1	622.0
115°	741.7	738.8	736.2	733.7	731.2	728.6	726.4	724.7	723.0	721.3	719.5
117.5°	831.7	829.5	828.1	826.8	825.5	824.2	822.5	820.4	818.2	816.1	814.0
120°	890.4	888.1	887.3	886.4	885.5	884.8	883.0	880.5	877.9	875.3	872.7
122.5°	948.5	946.8	945.7	944.7	943.6	942.5	940.9	938.7	936.7	934.5	932.5
125°	1030.4	1029.8	1028.6	1027.4	1026.3	1025.2	1023.5	1021.1	1018.9	1016.6	1014.3
127.5°	1110.9	1110.1	1108.7	1107.3	1106.0	1104.6	1102.8	1100.4	1098.2	1095.9	1093.6
130°	1159.6	1158.5	1157.4	1156.2	1155.0	1153.9	1152.2	1149.9	1147.6	1145.3	1143.0
132.5°	1205.9	1204.8	1203.9	1203.0	1202.0	1201.2	1199.5	1197.2	1195.0	1192.7	1190.4
135°	1276.4	1275.6	1274.5	1273.3	1272.1	1271.0	1269.6	1267.9	1266.2	1264.5	1262.7
137.5°	1338.5	1337.1	1336.5	1335.8	1335.2	1334.6	1333.2	1331.0	1328.9	1326.7	1324.5
140°	1378.5	1377.3	1376.4	1375.5	1374.7	1373.8	1372.6	1370.9	1369.2	1367.4	1365.7
142.5°	1416.3	1415.4	1414.5	1413.7	1412.8	1412.0	1410.7	1408.9	1407.2	1405.5	1403.8
145°	1469.2	1468.7	1468.1	1467.5	1467.0	1466.4	1465.1	1463.1	1461.1	1459.1	1457.1
147.5°	1516.4	1515.8	1515.2	1514.7	1514.1	1513.5	1512.5	1511.2	1509.9	1508.6	1507.3
150°	1545.2	1544.6	1544.0	1543.5	1542.9	1542.3	1541.6	1540.8	1539.9	1539.0	1538.2
152.5°	1570.4	1569.3	1569.0	1568.7	1568.3	1568.0	1567.6	1567.2	1566.8	1566.4	1566.0
155°	1605.2	1603.8	1603.5	1603.3	1603.0	1602.7	1602.8	1603.4	1604.0	1604.6	1605.1
157.5°	1635.6	1633.9	1634.3	1634.5	1634.8	1635.1	1635.3	1635.3	1635.4	1635.5	1635.5
160°	1653.2	1651.5	1651.7	1652.0	1652.3	1652.6	1652.9	1653.2	1653.5	1653.7	1654.1
162.5°	1668.9	1666.9	1667.2	1667.5	1667.8	1668.0	1668.5	1669.3	1670.1	1670.8	1671.5
165°	1689.8	1687.5	1687.8	1688.1	1688.3	1688.7	1689.2	1690.1	1690.9	1691.8	1692.6
167.5°	1706.2	1704.0	1704.0	1704.0	1704.0	1704.0	1704.5	1705.7	1706.8	1708.0	1709.1
170°	1715.5	1713.2	1713.2	1713.2	1713.2	1713.2	1713.8	1714.9	1716.1	1717.3	1718.4
172.5°	1721.7	1719.4	1719.2	1719.0	1718.7	1718.5	1719.1	1720.5	1721.8	1723.2	1724.6
175°	1729.4	1727.4	1727.1	1726.8	1726.6	1726.2	1726.8	1728.3	1729.7	1731.1	1732.5
177.5°	1732.3	1730.5	1730.3	1730.0	1729.8	1729.6	1730.0	1731.2	1732.3	1733.5	1734.6
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332446-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1058.8	1062.7	1067.8	1075.4	1081.2	1086.2	1087.3	1088.7	1092.4	1098.5	1103.1
5°	1065.7	1076.0	1092.7	1108.9	1126.5	1140.9	1154.4	1163.9	1172.9	1191.9	1207.2
7.5°	1063.5	1086.6	1112.7	1141.9	1171.3	1199.9	1226.4	1250.1	1273.7	1301.3	1332.7
10°	1062.0	1089.1	1124.2	1161.7	1202.6	1242.8	1281.6	1311.7	1346.9	1378.5	1418.6
12.5°	1055.2	1094.2	1136.2	1184.0	1234.4	1280.7	1331.7	1373.5	1413.7	1459.2	1505.9
15°	1046.3	1093.6	1146.8	1210.3	1286.9	1342.9	1395.2	1467.7	1517.3	1566.9	1633.6
17.5°	1029.9	1087.7	1154.2	1236.7	1300.7	1375.8	1454.5	1511.8	1578.6	1648.5	1708.9
20°	1016.9	1084.1	1158.5	1239.7	1321.2	1402.8	1479.0	1547.5	1616.5	1697.2	1746.8
22.5°	1004.0	1070.4	1147.7	1233.9	1321.5	1407.5	1493.7	1574.2	1651.8	1733.3	1796.6
25°	976.4	1055.2	1139.1	1227.0	1313.5	1408.3	1511.0	1600.7	1696.7	1780.5	1840.6
27.5°	948.4	1020.7	1104.2	1193.3	1289.6	1401.4	1522.3	1624.4	1720.5	1780.5	1799.4
30°	923.2	999.8	1076.4	1167.1	1271.2	1396.0	1524.5	1641.2	1720.2	1746.3	1726.9
32.5°	897.6	967.0	1042.9	1135.7	1246.3	1382.7	1527.4	1631.2	1678.7	1658.7	1579.8
35°	852.4	915.1	988.5	1081.4	1208.5	1375.4	1515.5	1585.8	1574.1	1461.4	1312.7
37.5°	804.1	855.1	923.2	1020.3	1169.4	1346.0	1464.3	1474.6	1373.2	1200.2	1028.4
40°	765.9	811.8	881.8	983.2	1139.1	1317.2	1412.7	1370.8	1213.5	1021.0	877.7
42.5°	728.8	767.5	834.8	944.2	1110.3	1277.9	1335.9	1244.6	1063.1	881.1	750.7
45°	665.8	702.3	769.9	882.2	1051.2	1202.6	1195.0	1036.3	854.7	708.2	599.9
47.5°	606.1	638.0	701.5	816.1	981.9	1089.9	1018.3	849.5	695.3	577.8	500.7
50°	564.0	595.5	658.6	771.7	926.3	1005.2	902.9	740.2	599.1	501.7	440.4
52.5°	523.6	554.4	612.1	722.3	859.3	906.5	796.5	645.7	528.1	444.0	391.3
55°	467.0	490.4	542.3	647.7	750.1	761.0	649.5	523.3	426.5	367.8	331.7
57.5°	409.4	429.6	480.8	564.8	636.6	631.0	525.5	416.2	350.9	307.5	281.3
60°	371.9	391.8	436.8	508.9	563.0	544.1	447.2	359.3	303.3	271.4	250.6
62.5°	336.9	352.4	394.6	447.3	486.2	464.8	382.3	309.5	265.2	238.2	221.8
65°	286.3	298.9	332.7	360.2	381.8	361.1	292.6	242.0	210.1	191.1	179.9
67.5°	238.1	246.2	267.5	277.4	292.7	269.9	220.0	186.1	168.0	152.0	144.1
70°	207.8	213.7	225.0	233.1	237.1	213.7	176.7	151.9	136.6	125.3	120.4
72.5°	177.5	182.6	184.9	191.6	189.5	167.6	142.1	122.3	111.3	103.7	97.3
75°	135.7	137.9	135.7	132.9	127.1	111.8	94.2	84.3	76.2	72.6	70.3
77.5°	98.9	98.2	95.1	90.8	80.8	71.2	61.7	58.5	54.9	53.0	52.2
80°	76.2	74.4	71.6	64.9	56.3	49.6	47.4	45.1	43.7	41.5	41.0
82.5°	56.7	55.6	51.1	45.5	39.4	36.2	34.4	33.6	32.2	31.0	30.9
85°	30.2	28.8	23.8	20.8	19.8	18.9	18.5	18.5	16.7	16.2	16.2
87.5°	10.6	9.0	9.2	8.7	9.3	9.4	10.4	10.5	10.8	11.5	10.9
90°	4.1	7.0	9.9	12.7	16.0	19.7	23.4	27.2	30.9	32.0	33.1
92.5°	23.2	22.3	21.5	20.8	21.7	24.5	27.4	30.1	33.0	34.8	36.6
95°	66.8	55.1	43.3	31.6	27.3	30.5	33.6	36.8	39.9	41.9	43.9
97.5°	152.6	147.3	142.0	136.7	123.8	103.2	82.7	62.1	41.4	43.7	46.1
100°	223.3	228.9	234.7	240.4	220.9	176.3	131.7	87.1	42.4	44.8	47.0
102.5°	289.6	293.8	297.8	302.0	279.7	230.9	182.2	133.5	84.7	77.6	70.5
105°	386.8	389.9	393.0	396.1	384.9	359.1	333.4	307.6	281.9	231.3	180.6
107.5°	489.6	492.1	494.6	497.1	500.4	504.5	508.6	512.6	516.7	479.6	442.4
110°	558.4	560.6	562.9	565.2	567.9	571.1	574.2	577.4	580.5	571.1	561.6



TEST NUMBER: P332446-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	624.1	626.1	628.2	630.2	632.8	635.9	639.1	642.2	645.4	645.6	645.8
115°	721.3	723.0	724.7	726.4	728.6	731.2	733.7	736.2	738.8	741.7	744.6
117.5°	816.1	818.2	820.4	822.5	824.2	825.5	826.8	828.1	829.5	831.7	834.1
120°	875.3	877.9	880.5	883.0	884.8	885.5	886.4	887.3	888.1	890.4	892.8
122.5°	934.5	936.7	938.7	940.9	942.5	943.6	944.7	945.7	946.8	948.5	950.0
125°	1016.6	1018.9	1021.1	1023.5	1025.2	1026.3	1027.4	1028.6	1029.8	1030.4	1030.9
127.5°	1095.9	1098.2	1100.4	1102.8	1104.6	1106.0	1107.3	1108.7	1110.1	1110.9	1111.9
130°	1145.3	1147.6	1149.9	1152.2	1153.9	1155.0	1156.2	1157.4	1158.5	1159.6	1160.7
132.5°	1192.7	1195.0	1197.2	1199.5	1201.2	1202.0	1203.0	1203.9	1204.8	1205.9	1207.1
135°	1264.5	1266.2	1267.9	1269.6	1271.0	1272.1	1273.3	1274.5	1275.6	1276.4	1277.3
137.5°	1326.7	1328.9	1331.0	1333.2	1334.6	1335.2	1335.8	1336.5	1337.1	1338.5	1339.9
140°	1367.4	1369.2	1370.9	1372.6	1373.8	1374.7	1375.5	1376.4	1377.3	1378.5	1379.6
142.5°	1405.5	1407.2	1408.9	1410.7	1412.0	1412.8	1413.7	1414.5	1415.4	1416.3	1417.2
145°	1459.1	1461.1	1463.1	1465.1	1466.4	1467.0	1467.5	1468.1	1468.7	1469.2	1469.8
147.5°	1508.6	1509.9	1511.2	1512.5	1513.5	1514.1	1514.7	1515.2	1515.8	1516.4	1516.9
150°	1539.0	1539.9	1540.8	1541.6	1542.3	1542.9	1543.5	1544.0	1544.6	1545.2	1545.8
152.5°	1566.4	1566.8	1567.2	1567.6	1568.0	1568.3	1568.7	1569.0	1569.3	1570.4	1571.4
155°	1604.6	1604.0	1603.4	1602.8	1602.7	1603.0	1603.3	1603.5	1603.8	1605.2	1606.7
157.5°	1635.5	1635.4	1635.3	1635.3	1635.1	1634.8	1634.5	1634.3	1633.9	1635.6	1637.4
160°	1653.7	1653.5	1653.2	1652.9	1652.6	1652.3	1652.0	1651.7	1651.5	1653.2	1654.9
162.5°	1670.8	1670.1	1669.3	1668.5	1668.0	1667.8	1667.5	1667.2	1666.9	1668.9	1670.8
165°	1691.8	1690.9	1690.1	1689.2	1688.7	1688.3	1688.1	1687.8	1687.5	1689.8	1692.0
167.5°	1708.0	1706.8	1705.7	1704.5	1704.0	1704.0	1704.0	1704.0	1704.0	1706.2	1708.6
170°	1717.3	1716.1	1714.9	1713.8	1713.2	1713.2	1713.2	1713.2	1713.2	1715.5	1717.8
172.5°	1723.2	1721.8	1720.5	1719.1	1718.5	1718.7	1719.0	1719.2	1719.4	1721.7	1724.0
175°	1731.1	1729.7	1728.3	1726.8	1726.2	1726.6	1726.8	1727.1	1727.4	1729.4	1731.4
177.5°	1733.5	1732.3	1731.2	1730.0	1729.6	1729.8	1730.0	1730.3	1730.5	1732.3	1734.1
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5



TEST NUMBER: P332446-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1110.7	1110.7	1112.2	1117.6	1118.3	1123.0	1121.5
5°	1220.7	1229.2	1232.4	1246.0	1254.0	1257.7	1250.4
7.5°	1355.2	1379.4	1390.9	1405.0	1417.6	1421.3	1411.4
10°	1453.3	1478.5	1499.8	1512.8	1525.0	1533.1	1543.4
12.5°	1548.2	1579.2	1599.3	1617.7	1630.3	1640.5	1642.3
15°	1651.2	1698.1	1733.7	1759.8	1772.9	1779.7	1776.9
17.5°	1755.1	1798.6	1823.9	1850.6	1868.7	1869.7	1870.2
20°	1814.0	1856.3	1885.6	1905.4	1925.7	1924.9	1929.3
22.5°	1853.2	1886.6	1909.0	1923.5	1930.4	1927.0	1927.9
25°	1871.6	1881.5	1877.5	1854.5	1848.7	1827.5	1831.1
27.5°	1776.8	1729.9	1681.4	1619.0	1569.8	1530.5	1532.5
30°	1648.0	1565.1	1470.4	1391.1	1319.9	1300.0	1257.7
32.5°	1468.1	1343.7	1232.8	1158.8	1097.7	1081.2	1044.2
35°	1163.0	1042.2	928.2	859.6	832.6	794.7	794.3
37.5°	904.0	797.6	737.3	685.9	658.9	636.0	633.8
40°	760.4	677.5	632.0	595.0	568.4	551.3	547.3
42.5°	660.2	593.1	550.5	527.6	507.1	498.3	491.7
45°	539.2	494.0	464.3	443.6	434.1	427.3	423.7
47.5°	451.0	420.8	400.5	386.7	379.0	371.9	373.8
50°	403.0	378.2	363.3	350.3	344.4	339.4	339.9
52.5°	364.4	342.2	330.1	320.7	313.4	309.9	308.2
55°	309.3	295.2	283.1	276.3	272.2	267.3	266.0
57.5°	263.8	253.0	243.1	235.4	234.4	229.6	230.2
60°	233.5	224.5	216.4	212.3	209.1	205.1	206.5
62.5°	208.6	201.0	193.6	190.3	187.2	184.2	184.9
65°	170.8	163.6	159.1	157.3	155.9	154.6	153.3
67.5°	136.1	131.7	128.9	125.0	122.3	121.8	120.5
70°	114.5	108.7	103.7	98.8	97.4	96.9	97.4
72.5°	91.8	88.1	86.7	84.3	84.0	82.8	83.7
75°	69.0	67.6	66.7	64.9	64.9	64.9	64.9
77.5°	50.9	50.0	49.5	49.2	48.6	48.0	48.0
80°	39.7	39.2	38.3	38.3	37.9	38.3	37.9
82.5°	30.0	29.9	28.9	28.9	28.5	28.2	28.5
85°	15.3	14.9	15.8	14.9	15.3	14.5	15.3
87.5°	11.2	11.5	11.2	11.4	11.1	12.0	11.4
90°	34.4	35.5	36.3	36.9	37.5	38.1	38.6
92.5°	38.5	40.3	41.3	41.7	42.0	42.4	42.7
95°	45.9	47.9	48.9	48.9	48.9	48.9	48.9
97.5°	48.3	50.6	51.9	52.2	52.4	52.8	53.0
100°	49.3	51.7	53.0	53.2	53.5	53.8	54.1
102.5°	63.5	56.3	53.0	53.6	54.1	54.6	55.1
105°	130.0	79.4	54.3	54.9	55.5	56.1	56.7
107.5°	405.3	368.2	330.5	292.4	254.2	216.0	177.9
110°	552.2	542.8	517.5	476.6	435.8	394.9	354.0



TEST NUMBER: P332446-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	645.9	646.1	641.9	633.2	624.6	616.0	607.3
115°	747.4	750.3	752.3	753.5	754.6	755.7	756.9
117.5°	836.3	838.6	839.9	840.1	840.3	840.6	840.8
120°	895.0	897.3	898.5	898.5	898.5	898.5	898.5
122.5°	951.7	953.3	954.2	954.4	954.6	954.8	955.1
125°	1031.5	1032.0	1032.6	1033.2	1033.7	1034.3	1034.9
127.5°	1112.8	1113.7	1113.9	1113.4	1112.8	1112.2	1111.6
130°	1161.9	1163.0	1163.3	1162.8	1162.2	1161.6	1161.1
132.5°	1208.2	1209.4	1209.5	1208.8	1208.0	1207.1	1206.3
135°	1278.2	1279.0	1279.0	1278.2	1277.3	1276.4	1275.6
137.5°	1341.3	1342.6	1343.0	1342.5	1341.9	1341.3	1340.7
140°	1380.7	1381.8	1382.2	1381.6	1381.0	1380.4	1379.8
142.5°	1418.2	1419.0	1419.1	1418.3	1417.5	1416.7	1415.9
145°	1470.4	1470.9	1471.3	1471.3	1471.3	1471.3	1471.3
147.5°	1517.5	1518.1	1517.7	1516.4	1515.1	1513.7	1512.4
150°	1546.4	1546.9	1546.8	1545.9	1545.1	1544.2	1543.3
152.5°	1572.4	1573.5	1573.3	1572.0	1570.6	1569.3	1568.1
155°	1608.1	1609.6	1609.4	1607.7	1605.9	1604.2	1602.6
157.5°	1639.1	1640.8	1640.5	1638.3	1636.1	1633.8	1631.6
160°	1656.6	1658.3	1658.2	1656.1	1654.2	1652.2	1650.2
162.5°	1672.8	1674.6	1674.7	1673.0	1671.2	1669.5	1667.7
165°	1694.4	1696.7	1696.8	1694.8	1692.8	1690.7	1688.8
167.5°	1710.8	1713.1	1713.1	1710.8	1708.6	1706.2	1704.0
170°	1720.1	1722.4	1722.4	1720.1	1717.8	1715.5	1713.2
172.5°	1726.3	1728.5	1728.5	1726.0	1723.5	1720.9	1718.4
175°	1733.4	1735.4	1735.3	1732.9	1730.7	1728.4	1726.1
177.5°	1735.9	1737.8	1737.6	1735.3	1733.0	1730.7	1728.5
180°	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5	1732.5

(END OF REPORT)