

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332449-935

Luminaire Tested: **S123RDIW-S775D1535U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332449-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S775D1535U935-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7095.4 lumens  
Efficiency: N/A  
Efficacy: 104.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332449-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332449-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	86	79	73	69	78	72	67	63	58	55	52	46	43	41	34	32	31	26
3	79	70	63	57	71	64	58	53	52	47	44	40	37	35	30	28	27	22
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	42	60	50	43	38	41	36	32	32	29	26	24	22	20	17
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	45	37	32	51	41	34	29	34	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	31	26	22	24	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11965	11965	11965
5°	12011	11846	11914
10°	11943	11696	11657
15°	11814	11422	11303
20°	11639	11080	10822
25°	11457	10696	10354
30°	11216	10253	9692
35°	10970	9809	9087
40°	10742	9285	8335
45°	10443	8770	7658
50°	10114	8182	6899
55°	9779	7512	6191
60°	9472	6794	5414
65°	9070	6016	4638
70°	8567	5051	3745
75°	7835	3976	3523
80°	6986	3521	3242
85°	5903	3112	2890



TEST NUMBER: P332449-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	104.4	1.5
10°-20°	290.4	4.1
20°-30°	418.2	5.9
30°-40°	471.1	6.6
40°-50°	450.7	6.4
50°-60°	369.0	5.2
60°-70°	249.0	3.5
70°-80°	125.3	1.8
80°-90°	38.0	0.5
90°-100°	107.7	1.5
100°-110°	322.3	4.5
110°-120°	548.1	7.7
120°-130°	721.0	10.2
130°-140°	810.4	11.4
140°-150°	796.6	11.2
150°-160°	670.6	9.5
160°-170°	446.4	6.3
170°-180°	156.3	2.2
0°-30°	813.0	11.5
0°-40°	1284.1	18.1
0°-60°	2103.8	29.7
0°-90°	2516.1	35.5
90°-120°	978.1	13.8
90°-150°	3306.0	46.6
90°-180°	4579.0	64.5
0°-180°	7095.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1112	1112	1112	1112	1112	
5°	1112	1107	1096	1104	1103	105
15°	1060	1049	1025	1020	1014	299
25°	965	941	901	882	872	443
35°	835	801	746	709	692	522
45°	686	644	576	526	503	529
55°	521	475	400	350	330	467
65°	356	305	236	194	182	352
75°	188	145	96	87	85	201
85°	48	29	25	24	23	54
90°	1	14	31	36	39	7
95°	77	86	96	101	101	86
105°	292	295	306	307	309	313
115°	552	555	553	554	553	546
125°	808	811	809	804	798	720
135°	1048	1055	1054	1049	1046	807
145°	1271	1274	1278	1276	1271	794
155°	1455	1456	1457	1461	1453	670
165°	1585	1582	1581	1588	1580	447
175°	1649	1644	1644	1651	1642	157
180°	1653	1653	1653	1653	1653	



TEST NUMBER: P332449-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1115.2	1114.6	1113.9	1113.3	1112.7	1111.4	1109.4	1107.5	1105.6	1103.6	1105.4
5°	1111.6	1110.6	1109.6	1108.6	1107.6	1105.9	1103.5	1101.0	1098.6	1096.3	1098.0
7.5°	1101.3	1100.3	1099.2	1098.0	1097.0	1094.8	1091.7	1088.6	1085.5	1082.4	1083.4
10°	1092.7	1091.2	1089.9	1088.5	1087.0	1084.5	1080.9	1077.4	1073.8	1070.1	1070.3
12.5°	1080.4	1078.8	1077.3	1075.7	1074.2	1071.2	1066.8	1062.4	1057.9	1053.5	1053.4
15°	1060.2	1058.0	1055.8	1053.6	1051.4	1047.5	1041.9	1036.3	1030.6	1025.0	1024.1
17.5°	1034.7	1032.3	1029.7	1027.1	1024.5	1019.7	1012.5	1005.4	998.2	991.2	989.0
20°	1016.1	1012.8	1009.6	1006.4	1003.2	997.8	990.2	982.6	975.0	967.3	964.8
22.5°	995.1	991.4	987.7	984.0	980.3	974.5	966.4	958.3	950.2	942.1	938.8
25°	964.7	959.7	954.6	949.6	944.6	937.5	928.2	919.0	909.8	900.6	896.4
27.5°	927.6	922.1	916.6	911.1	905.6	897.7	887.4	877.2	866.9	856.6	850.8
30°	902.4	896.4	890.4	884.4	878.4	869.8	858.6	847.3	836.1	824.9	818.1
32.5°	877.2	870.4	863.6	856.8	850.0	840.6	828.7	816.9	805.0	793.2	785.7
35°	834.8	827.6	820.4	813.2	806.0	796.2	783.8	771.3	758.9	746.5	737.9
37.5°	791.9	783.9	775.8	767.8	759.8	749.2	736.0	722.7	709.5	696.2	686.4
40°	764.5	755.7	746.8	738.0	729.3	717.7	703.5	689.3	675.0	660.8	650.4
42.5°	733.5	724.7	715.8	707.1	698.3	686.5	671.8	657.0	642.4	627.7	616.3
45°	686.0	677.1	668.0	659.0	650.0	637.8	622.3	606.9	591.5	576.1	564.6
47.5°	638.7	628.8	618.9	609.0	599.1	586.4	571.0	555.5	540.1	524.7	512.3
50°	604.0	594.6	585.2	575.8	566.4	553.5	537.4	521.1	504.9	488.6	476.2
52.5°	573.0	562.8	552.6	542.3	532.2	519.0	502.9	486.9	470.8	454.7	441.9
55°	521.1	511.3	501.4	491.6	481.8	468.4	451.3	434.4	417.3	400.3	388.7
57.5°	473.1	462.4	451.8	441.0	430.3	416.5	399.3	382.2	365.1	348.0	337.0
60°	440.0	429.0	417.9	406.9	395.9	382.0	365.4	348.8	332.2	315.6	304.7
62.5°	406.7	395.7	384.7	373.7	362.7	348.9	332.3	315.6	299.0	282.3	272.2
65°	356.1	345.1	334.1	323.0	312.0	298.7	283.1	267.4	251.8	236.2	226.4
67.5°	305.5	294.3	283.2	272.0	260.9	247.8	232.8	217.8	202.9	187.9	180.6
70°	272.2	261.5	250.6	239.8	229.0	216.5	202.5	188.6	174.5	160.5	153.4
72.5°	239.1	228.4	217.7	207.1	196.5	184.8	172.0	159.3	146.5	133.8	128.0
75°	188.4	178.8	169.2	159.5	150.0	139.7	128.6	117.6	106.6	95.6	93.6
77.5°	142.2	133.5	124.8	116.1	107.5	99.6	92.5	85.4	78.4	71.2	70.2
80°	112.7	104.4	96.3	88.1	79.8	73.6	69.4	65.2	61.0	56.8	56.2
82.5°	84.6	77.5	70.3	63.3	56.2	51.7	49.7	47.7	45.8	43.8	43.2
85°	47.8	43.4	39.0	34.5	30.1	27.6	27.0	26.4	25.8	25.2	24.9
87.5°	17.6	16.4	15.2	14.0	12.8	12.6	13.3	14.1	14.9	15.6	15.7
90°	1.3	4.2	7.1	10.0	12.8	16.2	19.9	23.7	27.4	31.2	32.3
92.5°	31.4	33.4	35.3	37.3	39.3	41.3	43.5	45.5	47.7	49.9	50.8
95°	76.6	78.6	80.7	82.7	84.7	86.9	89.1	91.4	93.8	96.1	97.2
97.5°	136.0	137.6	139.1	140.6	142.1	143.6	145.3	147.0	148.7	150.3	151.7
100°	176.6	178.3	180.0	181.8	183.5	185.1	186.5	188.0	189.4	190.9	191.7
102.5°	223.3	224.4	225.4	226.4	227.5	228.9	230.8	232.7	234.6	236.5	237.5
105°	292.1	292.7	293.3	293.9	294.5	296.0	298.6	301.2	303.8	306.4	306.4
107.5°	372.1	372.5	372.8	373.2	373.5	374.2	375.2	376.3	377.3	378.3	379.3
110°	422.0	422.6	423.1	423.7	424.3	424.8	425.4	426.0	426.5	427.1	428.3



TEST NUMBER: P332449-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	473.9	474.2	474.6	474.9	475.3	475.5	475.6	475.7	475.9	476.0	477.3
115°	551.8	552.7	553.5	554.4	555.3	555.4	554.8	554.2	553.7	553.1	553.4
117.5°	630.3	630.8	631.4	632.0	632.5	632.4	631.7	630.9	630.2	629.5	629.4
120°	679.1	680.8	682.5	684.2	686.0	686.1	684.7	683.2	681.7	680.4	680.0
122.5°	730.0	731.2	732.5	733.7	735.0	735.3	734.5	733.7	733.1	732.3	731.5
125°	807.5	808.4	809.3	810.2	811.1	811.1	810.6	810.0	809.4	808.9	807.7
127.5°	879.3	881.1	883.0	884.8	886.7	887.3	886.6	886.0	885.4	884.7	883.0
130°	927.0	929.4	931.6	933.9	936.3	936.9	936.1	935.2	934.4	933.5	932.4
132.5°	974.8	977.1	979.4	981.7	984.0	984.9	984.2	983.6	982.9	982.3	980.9
135°	1047.8	1049.5	1051.2	1052.9	1054.7	1055.4	1055.2	1054.8	1054.6	1054.3	1053.1
137.5°	1115.3	1116.7	1118.2	1119.6	1121.0	1122.1	1122.9	1123.6	1124.4	1125.2	1123.9
140°	1162.0	1163.5	1164.9	1166.3	1167.8	1168.6	1169.0	1169.2	1169.5	1169.8	1169.5
142.5°	1204.6	1206.0	1207.5	1208.9	1210.4	1211.3	1211.9	1212.4	1212.9	1213.4	1213.1
145°	1271.1	1271.7	1272.2	1272.8	1273.4	1274.1	1275.0	1275.8	1276.7	1277.6	1277.3
147.5°	1329.2	1330.2	1331.3	1332.4	1333.4	1334.3	1335.2	1335.9	1336.7	1337.6	1337.6
150°	1369.8	1370.4	1370.9	1371.5	1372.1	1372.6	1373.2	1373.8	1374.3	1374.9	1374.9
152.5°	1403.0	1403.8	1404.6	1405.4	1406.2	1406.8	1407.1	1407.5	1407.8	1408.2	1408.7
155°	1455.4	1455.4	1455.4	1455.4	1455.4	1455.6	1455.9	1456.1	1456.5	1456.7	1457.9
157.5°	1500.1	1499.8	1499.4	1499.1	1498.7	1498.7	1498.9	1499.1	1499.3	1499.6	1500.8
160°	1528.2	1527.6	1527.0	1526.4	1525.9	1525.5	1525.5	1525.5	1525.5	1525.5	1527.0
162.5°	1553.1	1552.3	1551.4	1550.7	1549.9	1549.5	1549.8	1550.1	1550.2	1550.5	1552.0
165°	1585.3	1584.4	1583.6	1582.7	1581.8	1581.4	1581.4	1581.4	1581.4	1581.4	1583.1
167.5°	1611.0	1609.8	1608.7	1607.5	1606.4	1605.9	1606.1	1606.4	1606.6	1606.8	1608.6
170°	1625.5	1624.4	1623.2	1622.0	1620.9	1620.3	1620.3	1620.3	1620.3	1620.3	1622.4
172.5°	1636.9	1635.8	1634.6	1633.5	1632.4	1631.8	1631.8	1631.8	1631.8	1631.8	1633.6
175°	1648.9	1647.8	1646.6	1645.5	1644.3	1643.7	1643.7	1643.7	1643.7	1643.7	1645.5
177.5°	1653.8	1652.9	1652.0	1651.1	1650.1	1649.7	1649.7	1649.7	1649.7	1649.7	1651.1
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332449-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1107.2	1109.0	1110.7	1111.5	1111.1	1110.8	1110.4	1110.2
5°	1099.8	1101.6	1103.5	1104.1	1103.8	1103.4	1102.9	1102.6
7.5°	1084.4	1085.4	1086.4	1086.6	1085.9	1085.2	1084.5	1083.8
10°	1070.6	1070.7	1070.9	1070.6	1069.5	1068.5	1067.6	1066.5
12.5°	1053.3	1053.2	1053.1	1052.4	1051.3	1050.1	1049.0	1047.8
15°	1023.0	1022.0	1021.1	1019.9	1018.5	1017.0	1015.6	1014.3
17.5°	986.9	984.8	982.7	980.6	978.4	976.4	974.3	972.2
20°	962.2	959.5	956.9	954.4	952.0	949.6	947.2	944.8
22.5°	935.6	932.4	929.1	926.3	924.1	921.9	919.6	917.4
25°	892.3	888.0	883.8	880.6	878.4	876.2	874.0	871.8
27.5°	844.9	839.1	833.3	828.6	825.3	821.9	818.6	815.2
30°	811.3	804.4	797.6	792.6	789.5	786.3	783.0	779.8
32.5°	778.3	770.9	763.4	757.9	754.6	751.2	747.9	744.5
35°	729.3	720.7	712.0	705.9	702.3	698.7	695.1	691.5
37.5°	676.6	666.8	657.0	650.0	645.5	641.0	636.6	632.1
40°	640.0	629.6	619.1	611.7	607.0	602.4	597.8	593.2
42.5°	604.9	593.5	582.1	574.4	570.2	566.1	562.0	557.8
45°	553.3	541.8	530.4	522.3	517.5	512.6	507.9	503.1
47.5°	499.8	487.4	475.0	466.7	462.4	458.1	453.8	449.5
50°	463.8	451.3	438.9	430.4	425.9	421.2	416.6	412.0
52.5°	429.0	416.0	403.1	394.6	390.5	386.3	382.2	378.1
55°	377.0	365.4	353.8	345.9	342.0	337.9	334.0	329.9
57.5°	326.1	315.0	304.1	296.9	293.5	290.1	286.6	283.3
60°	293.9	283.1	272.2	265.2	261.7	258.3	254.9	251.5
62.5°	262.0	251.8	241.7	234.8	231.2	227.6	224.1	220.5
65°	216.5	206.7	196.9	190.9	188.7	186.5	184.3	182.1
67.5°	173.2	165.9	158.5	153.7	151.4	149.0	146.6	144.2
70°	146.5	139.4	132.4	127.9	125.6	123.4	121.2	119.0
72.5°	122.3	116.6	110.9	107.5	106.6	105.7	104.8	103.8
75°	91.5	89.5	87.6	86.4	85.9	85.6	85.2	84.7
77.5°	69.1	67.9	66.9	66.1	65.8	65.3	64.9	64.6
80°	55.6	55.0	54.4	53.9	53.5	53.1	52.7	52.3
82.5°	42.6	42.0	41.4	41.1	41.0	40.9	40.8	40.7
85°	24.5	24.0	23.7	23.4	23.4	23.4	23.4	23.4
87.5°	15.8	15.8	15.9	15.9	15.8	15.8	15.8	15.8
90°	33.5	34.6	35.8	36.7	37.2	37.8	38.4	38.9
92.5°	51.7	52.6	53.6	53.8	53.5	53.1	52.8	52.4
95°	98.4	99.5	100.7	101.3	101.3	101.3	101.3	101.3
97.5°	153.0	154.3	155.7	156.3	156.2	156.0	155.9	155.8
100°	192.6	193.5	194.3	195.0	195.6	196.2	196.7	197.3
102.5°	238.3	239.2	240.0	240.4	240.3	240.1	240.0	240.0
105°	306.4	306.4	306.4	306.7	307.3	307.9	308.4	309.0
107.5°	380.2	381.1	382.0	382.3	381.9	381.6	381.3	380.9
110°	429.5	430.6	431.8	432.0	431.4	430.9	430.3	429.7





TEST NUMBER: P332449-935

CATALOG NUMBER: S123RDIW-S775D1535U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	478.7	480.1	481.5	482.2	482.1	481.9	481.8	481.6
115°	553.7	554.0	554.2	554.2	554.0	553.7	553.4	553.1
117.5°	629.3	629.3	629.2	628.8	627.9	627.2	626.4	625.5
120°	679.8	679.5	679.2	678.7	678.2	677.6	677.0	676.4
122.5°	730.7	730.0	729.3	728.5	727.7	726.9	726.1	725.2
125°	806.6	805.4	804.3	803.1	801.9	800.8	799.6	798.5
127.5°	881.5	879.9	878.2	876.8	875.5	874.1	872.8	871.4
130°	931.2	930.1	928.9	927.3	925.3	923.3	921.3	919.2
132.5°	979.6	978.2	976.8	975.3	973.8	972.2	970.6	969.1
135°	1052.0	1050.8	1049.6	1048.8	1048.2	1047.6	1047.1	1046.5
137.5°	1122.7	1121.5	1120.3	1119.1	1118.0	1117.0	1115.9	1114.7
140°	1169.2	1169.0	1168.6	1167.5	1165.4	1163.5	1161.4	1159.4
142.5°	1212.9	1212.5	1212.3	1211.3	1209.8	1208.2	1206.7	1205.1
145°	1276.9	1276.7	1276.4	1275.7	1274.5	1273.4	1272.2	1271.1
147.5°	1337.6	1337.6	1337.6	1336.7	1335.0	1333.3	1331.5	1329.7
150°	1374.9	1374.9	1374.9	1374.1	1372.3	1370.6	1368.9	1367.2
152.5°	1409.1	1409.5	1410.1	1409.5	1408.0	1406.5	1405.0	1403.5
155°	1459.1	1460.2	1461.4	1460.9	1458.9	1456.9	1454.8	1452.9
157.5°	1502.0	1503.2	1504.4	1504.3	1502.6	1501.0	1499.3	1497.8
160°	1528.4	1529.9	1531.3	1531.5	1530.3	1529.1	1528.0	1526.8
162.5°	1553.3	1554.8	1556.3	1556.1	1554.2	1552.4	1550.5	1548.7
165°	1584.8	1586.6	1588.3	1588.2	1586.1	1584.2	1582.1	1580.1
167.5°	1610.4	1612.2	1613.9	1613.9	1612.2	1610.4	1608.6	1606.8
170°	1624.4	1626.4	1628.4	1628.4	1626.4	1624.4	1622.4	1620.3
172.5°	1635.3	1637.1	1638.9	1638.8	1636.8	1634.8	1632.7	1630.7
175°	1647.2	1648.9	1650.6	1650.5	1648.5	1646.4	1644.4	1642.4
177.5°	1652.4	1653.8	1655.2	1655.1	1653.5	1651.8	1650.3	1648.6
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8

(END OF REPORT)