

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332434-935

Luminaire Tested: **S123RDIW-S775D755U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332434-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D755U935-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5224.8 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332434-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332434-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	91	87	91	87	84	81	74	72	70	62	60	59	51	50	49	43
2	90	83	77	72	83	77	72	68	66	62	59	55	52	50	45	44	42	37
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	59	51	45	64	55	48	42	47	42	38	40	36	33	33	30	28	25
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	30	27	25	22
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20	18
9	52	40	32	28	48	37	31	26	33	27	24	28	24	21	24	21	18	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11334	11334	11334	11334
5°	13511	11382	10024	11382
10°	16869	11317	9055	11317
15°	19801	11202	8259	11202
20°	22100	11030	7581	11030
25°	21747	10847	7163	10847
30°	15632	10679	6734	10679
35°	10437	10461	6457	10461
40°	7690	10197	6169	10197
45°	6450	9736	5888	9736
50°	5692	9133	5494	9133
55°	4992	8443	4958	8443
60°	4445	7782	4540	7782
65°	3904	7073	4225	7073
70°	3065	6442	3858	6442
75°	2699	5627	3523	5627
80°	2349	4779	3465	4779
85°	1890	3841	3680	3841



TEST NUMBER: P332434-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	2.0
10°-20°	323.5	6.2
20°-30°	508.3	9.7
30°-40°	530.3	10.1
40°-50°	453.8	8.7
50°-60°	345.9	6.6
60°-70°	221.7	4.2
70°-80°	106.6	2.0
80°-90°	30.6	0.6
90°-100°	31.0	0.6
100°-110°	147.8	2.8
110°-120°	355.0	6.8
120°-130°	452.0	8.7
130°-140°	482.9	9.2
140°-150°	451.6	8.6
150°-160°	364.3	7.0
160°-170°	235.1	4.5
170°-180°	81.0	1.6
0°-30°	935.3	17.9
0°-40°	1465.6	28.1
0°-60°	2265.3	43.4
0°-90°	2624.2	50.2
90°-120°	533.7	10.2
90°-150°	1920.2	36.8
90°-180°	2601.0	49.8
0°-180°	5224.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1053	1053	1053	1053	1053	
5°	1250	1053	928	1053	1250	129
15°	1777	1005	741	1005	1777	504
25°	1831	913	603	913	1831	787
35°	794	796	491	796	794	521
45°	424	640	387	640	424	333
55°	266	450	264	450	266	240
65°	153	278	166	278	153	151
75°	65	135	85	135	65	70
85°	15	31	30	31	15	18
90°	19	1	19	1	19	9
95°	24	39	24	39	24	20
105°	28	189	28	189	28	64
115°	373	354	373	354	373	344
125°	509	499	509	499	509	455
135°	628	622	628	622	628	484
145°	724	717	724	717	724	452
155°	789	790	789	790	789	364
165°	831	833	831	833	831	235
175°	850	853	850	853	850	81
180°	853	853	853	853	853	



TEST NUMBER: P332434-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1121.5	1123.0	1118.3	1117.6	1112.2	1110.7	1110.7	1103.1	1098.5	1092.4	1088.7
5°	1250.4	1257.7	1254.0	1246.0	1232.4	1229.2	1220.7	1207.2	1191.9	1172.9	1163.9
7.5°	1411.4	1421.3	1417.6	1405.0	1390.9	1379.4	1355.2	1332.7	1301.3	1273.7	1250.1
10°	1543.4	1533.1	1525.0	1512.8	1499.8	1478.5	1453.3	1418.6	1378.5	1346.9	1311.7
12.5°	1642.3	1640.5	1630.3	1617.7	1599.3	1579.2	1548.2	1505.9	1459.2	1413.7	1373.5
15°	1776.9	1779.7	1772.9	1759.8	1733.7	1698.1	1651.2	1633.6	1566.9	1517.3	1467.7
17.5°	1870.2	1869.7	1868.7	1850.6	1823.9	1798.6	1755.1	1708.9	1648.5	1578.6	1511.8
20°	1929.3	1924.9	1925.7	1905.4	1885.6	1856.3	1814.0	1746.8	1697.2	1616.5	1547.5
22.5°	1927.9	1927.0	1930.4	1923.5	1909.0	1886.6	1853.2	1796.6	1733.3	1651.8	1574.2
25°	1831.1	1827.5	1848.7	1854.5	1877.5	1881.5	1871.6	1840.6	1780.5	1696.7	1600.7
27.5°	1532.5	1530.5	1569.8	1619.0	1681.4	1729.9	1776.8	1799.4	1780.5	1720.5	1624.4
30°	1257.7	1300.0	1319.9	1391.1	1470.4	1565.1	1648.0	1726.9	1746.3	1720.2	1641.2
32.5°	1044.2	1081.2	1097.7	1158.8	1232.8	1343.7	1468.1	1579.8	1658.7	1678.7	1631.2
35°	794.3	794.7	832.6	859.6	928.2	1042.2	1163.0	1312.7	1461.4	1574.1	1585.8
37.5°	633.8	636.0	658.9	685.9	737.3	797.6	904.0	1028.4	1200.2	1373.2	1474.6
40°	547.3	551.3	568.4	595.0	632.0	677.5	760.4	877.7	1021.0	1213.5	1370.8
42.5°	491.7	498.3	507.1	527.6	550.5	593.1	660.2	750.7	881.1	1063.1	1244.6
45°	423.7	427.3	434.1	443.6	464.3	494.0	539.2	599.9	708.2	854.7	1036.3
47.5°	373.8	371.9	379.0	386.7	400.5	420.8	451.0	500.7	577.8	695.3	849.5
50°	339.9	339.4	344.4	350.3	363.3	378.2	403.0	440.4	501.7	599.1	740.2
52.5°	308.2	309.9	313.4	320.7	330.1	342.2	364.4	391.3	444.0	528.1	645.7
55°	266.0	267.3	272.2	276.3	283.1	295.2	309.3	331.7	367.8	426.5	523.3
57.5°	230.2	229.6	234.4	235.4	243.1	253.0	263.8	281.3	307.5	350.9	416.2
60°	206.5	205.1	209.1	212.3	216.4	224.5	233.5	250.6	271.4	303.3	359.3
62.5°	184.9	184.2	187.2	190.3	193.6	201.0	208.6	221.8	238.2	265.2	309.5
65°	153.3	154.6	155.9	157.3	159.1	163.6	170.8	179.9	191.1	210.1	242.0
67.5°	120.5	121.8	122.3	125.0	128.9	131.7	136.1	144.1	152.0	168.0	186.1
70°	97.4	96.9	97.4	98.8	103.7	108.7	114.5	120.4	125.3	136.6	151.9
72.5°	83.7	82.8	84.0	84.3	86.7	88.1	91.8	97.3	103.7	111.3	122.3
75°	64.9	64.9	64.9	64.9	66.7	67.6	69.0	70.3	72.6	76.2	84.3
77.5°	48.0	48.0	48.6	49.2	49.5	50.0	50.9	52.2	53.0	54.9	58.5
80°	37.9	38.3	37.9	38.3	38.3	39.2	39.7	41.0	41.5	43.7	45.1
82.5°	28.5	28.2	28.5	28.9	28.9	29.9	30.0	30.9	31.0	32.2	33.6
85°	15.3	14.5	15.3	14.9	15.8	14.9	15.3	16.2	16.2	16.7	18.5
87.5°	7.4	8.1	7.3	7.6	7.6	7.8	7.7	7.6	8.2	7.7	7.7
90°	19.0	18.7	18.4	18.2	17.9	17.5	16.9	16.4	15.8	15.2	13.3
92.5°	21.0	20.8	20.7	20.5	20.3	19.8	18.9	18.0	17.1	16.2	14.8
95°	24.1	24.1	24.1	24.1	24.1	23.6	22.6	21.6	20.7	19.6	18.1
97.5°	26.1	26.0	25.8	25.7	25.6	24.9	23.8	22.6	21.5	20.4	30.6
100°	26.6	26.4	26.3	26.2	26.1	25.4	24.3	23.2	22.0	20.9	42.9
102.5°	27.1	26.9	26.6	26.3	26.1	27.7	31.3	34.7	38.2	41.7	65.7
105°	27.9	27.6	27.3	27.0	26.8	39.1	64.0	88.9	113.8	138.8	151.4
107.5°	87.6	106.3	125.1	143.9	162.7	181.2	199.5	217.7	236.0	254.3	252.4
110°	174.3	194.3	214.5	234.6	254.8	267.2	271.8	276.5	281.1	285.8	284.2



TEST NUMBER: P332434-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	298.9	303.2	307.5	311.7	315.9	318.1	318.0	317.9	317.8	317.7	316.2
115°	372.6	372.0	371.4	370.8	370.3	369.3	367.9	366.5	365.1	363.7	362.4
117.5°	413.9	413.7	413.6	413.5	413.4	412.8	411.6	410.5	409.4	408.3	407.6
120°	442.2	442.2	442.2	442.2	442.2	441.7	440.6	439.5	438.3	437.1	436.8
122.5°	470.1	470.0	469.8	469.8	469.7	469.2	468.4	467.6	466.8	466.1	465.5
125°	509.4	509.1	508.9	508.6	508.2	508.0	507.7	507.4	507.1	506.9	506.3
127.5°	547.2	547.4	547.7	548.0	548.3	548.2	547.8	547.3	546.8	546.4	545.7
130°	571.4	571.8	572.0	572.3	572.7	572.5	571.9	571.4	570.8	570.2	569.6
132.5°	593.7	594.2	594.6	595.0	595.4	595.3	594.7	594.2	593.6	593.1	592.5
135°	627.8	628.3	628.7	629.1	629.6	629.6	629.1	628.7	628.3	627.8	627.3
137.5°	660.0	660.2	660.5	660.8	661.1	660.9	660.2	659.5	658.8	658.1	657.9
140°	679.2	679.5	679.8	680.0	680.4	680.2	679.6	679.1	678.5	678.0	677.5
142.5°	696.9	697.3	697.8	698.1	698.5	698.4	698.0	697.6	697.2	696.7	696.3
145°	724.2	724.2	724.2	724.2	724.2	724.0	723.8	723.5	723.2	722.9	722.6
147.5°	744.4	745.1	745.7	746.4	747.0	747.3	746.9	746.7	746.4	746.1	745.8
150°	759.7	760.1	760.5	761.0	761.4	761.4	761.1	760.9	760.6	760.3	760.0
152.5°	771.8	772.5	773.1	773.8	774.4	774.5	774.0	773.4	772.9	772.5	772.3
155°	788.8	789.6	790.5	791.3	792.2	792.3	791.5	790.8	790.1	789.5	789.3
157.5°	803.1	804.3	805.3	806.4	807.5	807.6	806.8	806.0	805.1	804.3	804.4
160°	812.3	813.2	814.2	815.2	816.2	816.2	815.5	814.6	813.7	812.9	813.0
162.5°	820.9	821.7	822.6	823.5	824.3	824.3	823.4	822.4	821.5	820.4	820.6
165°	831.2	832.2	833.2	834.2	835.2	835.1	834.0	832.8	831.7	830.6	830.8
167.5°	838.7	839.8	840.9	842.1	843.3	843.3	842.1	840.9	839.8	838.7	838.7
170°	843.3	844.4	845.5	846.7	847.8	847.8	846.7	845.5	844.4	843.3	843.3
172.5°	845.8	847.1	848.3	849.5	850.8	850.8	849.7	848.6	847.5	846.4	846.2
175°	849.6	850.8	851.9	853.0	854.1	854.2	853.3	852.2	851.3	850.2	850.2
177.5°	850.8	851.9	853.0	854.1	855.2	855.4	854.5	853.6	852.6	851.8	851.7
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332434-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1087.3	1086.2	1081.2	1075.4	1067.8	1062.7	1058.8	1056.6	1050.2	1042.2	1036.8
5°	1154.4	1140.9	1126.5	1108.9	1092.7	1076.0	1065.7	1053.4	1038.6	1021.9	1010.2
7.5°	1226.4	1199.9	1171.3	1141.9	1112.7	1086.6	1063.5	1043.7	1020.0	996.1	979.4
10°	1281.6	1242.8	1202.6	1161.7	1124.2	1089.1	1062.0	1035.4	1007.0	979.6	958.8
12.5°	1331.7	1280.7	1234.4	1184.0	1136.2	1094.2	1055.2	1023.9	989.7	960.4	936.8
15°	1395.2	1342.9	1286.9	1210.3	1146.8	1093.6	1046.3	1005.2	963.8	927.7	904.7
17.5°	1454.5	1375.8	1300.7	1236.7	1154.2	1087.7	1029.9	980.9	935.4	897.2	868.8
20°	1479.0	1402.8	1321.2	1239.7	1158.5	1084.1	1016.9	962.9	915.5	872.3	846.1
22.5°	1493.7	1407.5	1321.5	1233.9	1147.7	1070.4	1004.0	944.4	893.2	852.0	819.8
25°	1511.0	1408.3	1313.5	1227.0	1139.1	1055.2	976.4	913.3	857.8	814.1	779.8
27.5°	1522.3	1401.4	1289.6	1193.3	1104.2	1020.7	948.4	881.6	825.3	779.0	742.3
30°	1524.5	1396.0	1271.2	1167.1	1076.4	999.8	923.2	859.2	799.7	750.5	716.3
32.5°	1527.4	1382.7	1246.3	1135.7	1042.9	967.0	897.6	836.5	775.5	727.1	692.2
35°	1515.5	1375.4	1208.5	1081.4	988.5	915.1	852.4	796.1	736.2	689.2	653.6
37.5°	1464.3	1346.0	1169.4	1020.3	923.2	855.1	804.1	754.9	700.0	649.4	615.9
40°	1412.7	1317.2	1139.1	983.2	881.8	811.8	765.9	725.7	672.5	625.3	589.2
42.5°	1335.9	1277.9	1110.3	944.2	834.8	767.5	728.8	691.1	644.5	596.4	562.5
45°	1195.0	1202.6	1051.2	882.2	769.9	702.3	665.8	639.6	598.2	558.5	523.8
47.5°	1018.3	1089.9	981.9	816.1	701.5	638.0	606.1	583.3	555.3	516.4	484.7
50°	902.9	1005.2	926.3	771.7	658.6	595.5	564.0	545.4	521.1	490.4	460.2
52.5°	796.5	906.5	859.3	722.3	612.1	554.4	523.6	508.3	489.0	460.1	432.8
55°	649.5	761.0	750.1	647.7	542.3	490.4	467.0	449.9	436.8	415.2	393.6
57.5°	525.5	631.0	636.6	564.8	480.8	429.6	409.4	396.5	388.0	371.6	351.6
60°	447.2	544.1	563.0	508.9	436.8	391.8	371.9	361.5	354.7	341.7	326.4
62.5°	382.3	464.8	486.2	447.3	394.6	352.4	336.9	326.9	322.3	311.0	297.5
65°	292.6	361.1	381.8	360.2	332.7	298.9	286.3	277.7	273.6	267.3	257.4
67.5°	220.0	269.9	292.7	277.4	267.5	246.2	238.1	233.5	229.9	225.6	217.3
70°	176.7	213.7	237.1	233.1	225.0	213.7	207.8	204.7	201.0	197.4	190.2
72.5°	142.1	167.6	189.5	191.6	184.9	182.6	177.5	176.2	174.0	169.7	165.7
75°	94.2	111.8	127.1	132.9	135.7	137.9	135.7	135.3	134.7	131.2	128.9
77.5°	61.7	71.2	80.8	90.8	95.1	98.2	98.9	100.6	99.4	97.5	96.3
80°	47.4	49.6	56.3	64.9	71.6	74.4	76.2	77.1	76.6	76.2	74.4
82.5°	34.4	36.2	39.4	45.5	51.1	55.6	56.7	56.6	57.5	57.8	56.3
85°	18.5	18.9	19.8	20.8	23.8	28.8	30.2	31.1	32.0	32.0	29.3
87.5°	8.1	7.3	7.7	7.4	8.2	8.3	10.2	11.7	12.3	11.1	11.5
90°	11.5	9.7	7.9	6.3	4.8	3.4	2.1	0.6	2.1	3.4	4.8
92.5°	13.4	12.1	10.7	10.2	10.6	11.0	11.4	11.8	11.4	11.0	10.6
95°	16.5	15.0	13.4	15.6	21.4	27.1	32.9	38.7	32.9	27.1	21.4
97.5°	40.6	50.8	61.0	67.3	69.9	72.5	75.1	77.7	75.1	72.5	69.9
100°	64.8	86.8	108.7	118.3	115.5	112.7	109.9	107.1	109.9	112.7	115.5
102.5°	89.6	113.7	137.7	148.6	146.6	144.6	142.6	140.5	142.6	144.6	146.6
105°	164.1	176.8	189.4	195.0	193.5	191.9	190.4	188.8	190.4	191.9	193.5
107.5°	250.3	248.3	246.3	244.7	243.5	242.2	241.0	239.7	241.0	242.2	243.5
110°	282.7	281.1	279.6	278.2	277.1	276.0	274.8	273.7	274.8	276.0	277.1



TEST NUMBER: P332434-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	314.6	313.1	311.5	310.2	309.2	308.2	307.1	306.2	307.1	308.2	309.2
115°	361.1	359.9	358.6	357.6	356.7	355.9	355.0	354.1	355.0	355.9	356.7
117.5°	407.0	406.3	405.7	404.8	403.8	402.8	401.7	400.7	401.7	402.8	403.8
120°	436.4	435.9	435.5	434.6	433.3	432.1	430.8	429.6	430.8	432.1	433.3
122.5°	465.0	464.4	463.9	463.1	462.1	461.1	460.0	459.0	460.0	461.1	462.1
125°	505.8	505.1	504.6	503.8	502.7	501.5	500.4	499.3	500.4	501.5	502.7
127.5°	545.0	544.4	543.7	542.8	541.7	540.5	539.4	538.3	539.4	540.5	541.7
130°	569.1	568.5	568.0	567.1	566.0	564.9	563.8	562.6	563.8	564.9	566.0
132.5°	592.1	591.7	591.2	590.5	589.3	588.1	587.0	585.9	587.0	588.1	589.3
135°	626.7	626.2	625.6	624.9	624.1	623.2	622.4	621.6	622.4	623.2	624.1
137.5°	657.5	657.2	656.9	656.3	655.1	654.1	653.0	651.9	653.0	654.1	655.1
140°	677.1	676.7	676.2	675.6	674.8	673.9	673.0	672.2	673.0	673.9	674.8
142.5°	695.9	695.4	695.0	694.4	693.5	692.7	691.8	691.0	691.8	692.7	693.5
145°	722.4	722.0	721.8	721.2	720.1	719.2	718.2	717.2	718.2	719.2	720.1
147.5°	745.5	745.3	744.9	744.5	743.8	743.2	742.5	741.9	742.5	743.2	743.8
150°	759.7	759.5	759.1	758.8	758.4	757.9	757.5	757.2	757.5	757.9	758.4
152.5°	772.1	772.0	771.8	771.6	771.4	771.2	771.0	770.8	771.0	771.2	771.4
155°	789.2	789.0	788.8	788.9	789.2	789.5	789.8	790.1	789.8	789.5	789.2
157.5°	804.5	804.7	804.9	804.9	804.9	804.9	805.0	805.0	805.0	804.9	804.9
160°	813.1	813.3	813.5	813.6	813.7	813.9	814.0	814.2	814.0	813.9	813.7
162.5°	820.8	820.9	821.0	821.3	821.7	822.0	822.4	822.8	822.4	822.0	821.7
165°	830.9	831.0	831.2	831.5	831.9	832.3	832.8	833.2	832.8	832.3	831.9
167.5°	838.7	838.7	838.7	839.0	839.6	840.2	840.7	841.3	840.7	840.2	839.6
170°	843.3	843.3	843.3	843.6	844.1	844.7	845.2	845.8	845.2	844.7	844.1
172.5°	846.1	846.0	845.8	846.2	846.9	847.5	848.2	848.9	848.2	847.5	846.9
175°	850.0	849.8	849.7	850.0	850.7	851.4	852.0	852.8	852.0	851.4	850.7
177.5°	851.5	851.4	851.4	851.5	852.1	852.6	853.3	853.8	853.3	852.6	852.1
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332434-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1035.0	1030.3	1027.1	1019.9	1015.1	1010.1	1005.0	1008.3	1008.0	1007.5	1007.5
5°	1000.3	989.9	980.4	968.3	960.6	951.1	943.9	943.1	944.9	938.5	934.9
7.5°	965.9	951.7	938.2	924.8	910.6	899.2	892.1	888.7	884.2	880.3	876.2
10°	941.7	925.0	911.9	895.3	879.9	866.4	857.8	852.0	848.8	845.7	839.8
12.5°	916.8	900.4	883.8	865.0	850.3	834.7	828.3	821.7	815.6	812.1	804.1
15°	880.4	859.2	841.6	821.7	805.6	790.2	781.2	768.1	766.3	761.8	753.7
17.5°	843.9	820.9	796.6	782.0	763.6	747.7	733.9	729.5	716.6	711.8	704.7
20°	815.0	793.8	775.3	756.0	729.4	714.5	703.7	697.8	687.4	681.1	676.6
22.5°	790.1	768.6	747.2	724.6	702.7	686.0	678.0	668.9	663.3	654.4	649.5
25°	754.6	731.2	705.5	681.1	665.4	652.7	640.1	632.0	623.9	619.8	610.8
27.5°	713.3	688.8	664.8	646.4	627.0	614.5	603.0	595.8	586.1	579.3	574.3
30°	690.6	661.8	641.0	624.3	599.5	587.8	579.3	570.2	563.0	555.8	550.9
32.5°	664.3	637.9	618.3	597.6	578.6	565.8	554.7	546.8	540.6	533.8	528.8
35°	622.9	600.9	580.6	559.8	545.9	532.8	519.8	513.0	507.1	500.8	496.3
37.5°	585.7	565.0	545.7	526.1	508.8	498.1	487.6	482.4	474.5	470.3	465.6
40°	562.6	542.3	521.5	502.7	484.6	476.5	467.0	459.3	452.1	449.0	444.0
42.5°	537.4	517.0	499.6	479.1	464.4	453.4	444.6	436.3	430.8	426.3	423.4
45°	499.9	481.9	464.8	444.4	430.5	421.0	411.1	403.5	398.5	395.4	390.4
47.5°	463.6	445.6	428.2	410.4	396.9	386.2	376.3	370.9	364.3	360.4	357.1
50°	437.2	421.0	402.5	386.3	372.8	362.0	353.9	347.1	341.2	336.3	334.1
52.5°	413.1	395.8	379.8	364.7	350.4	338.2	330.8	323.6	319.3	313.6	310.9
55°	373.2	356.5	343.0	328.1	314.2	303.8	294.8	288.5	284.0	277.7	274.1
57.5°	335.8	320.9	304.7	291.8	277.4	268.6	261.1	252.6	247.1	242.2	238.7
60°	310.6	293.4	279.5	267.3	254.7	243.4	236.7	229.9	224.0	219.0	215.9
62.5°	284.3	269.3	256.1	242.8	231.3	221.4	213.6	207.9	202.8	199.6	196.5
65°	243.8	232.1	218.6	207.8	197.0	189.8	183.5	178.5	174.9	172.6	170.0
67.5°	206.7	195.4	183.6	172.9	165.7	160.2	156.1	151.8	150.0	147.1	145.3
70°	182.5	170.8	160.5	152.4	145.2	141.1	138.4	135.3	133.5	129.8	128.0
72.5°	156.3	147.7	140.3	133.6	127.9	124.2	120.7	116.8	114.0	109.9	108.2
75°	123.0	115.4	109.5	105.0	101.4	96.4	91.5	87.5	86.1	84.7	84.3
77.5°	91.2	86.3	82.1	78.3	73.8	70.2	69.1	68.2	67.8	67.2	67.2
80°	71.6	67.2	64.0	59.5	56.8	56.8	56.8	55.9	56.3	56.3	56.3
82.5°	53.3	49.2	47.4	45.8	45.3	45.6	45.6	45.8	45.5	46.2	45.9
85°	27.5	28.0	28.8	28.4	28.8	28.8	29.8	29.3	29.8	28.8	29.8
87.5°	11.4	12.7	13.5	14.2	14.9	15.0	15.4	15.5	16.0	16.1	16.2
90°	6.3	7.9	9.7	11.5	13.3	15.2	15.8	16.4	16.9	17.5	17.9
92.5°	10.2	10.7	12.1	13.4	14.8	16.2	17.1	18.0	18.9	19.8	20.3
95°	15.6	13.4	15.0	16.5	18.1	19.6	20.7	21.6	22.6	23.6	24.1
97.5°	67.3	61.0	50.8	40.6	30.6	20.4	21.5	22.6	23.8	24.9	25.6
100°	118.3	108.7	86.8	64.8	42.9	20.9	22.0	23.2	24.3	25.4	26.1
102.5°	148.6	137.7	113.7	89.6	65.7	41.7	38.2	34.7	31.3	27.7	26.1
105°	195.0	189.4	176.8	164.1	151.4	138.8	113.8	88.9	64.0	39.1	26.8
107.5°	244.7	246.3	248.3	250.3	252.4	254.3	236.0	217.7	199.5	181.2	162.7
110°	278.2	279.6	281.1	282.7	284.2	285.8	281.1	276.5	271.8	267.2	254.8



TEST NUMBER: P332434-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	310.2	311.5	313.1	314.6	316.2	317.7	317.8	317.9	318.0	318.1	315.9
115°	357.6	358.6	359.9	361.1	362.4	363.7	365.1	366.5	367.9	369.3	370.3
117.5°	404.8	405.7	406.3	407.0	407.6	408.3	409.4	410.5	411.6	412.8	413.4
120°	434.6	435.5	435.9	436.4	436.8	437.1	438.3	439.5	440.6	441.7	442.2
122.5°	463.1	463.9	464.4	465.0	465.5	466.1	466.8	467.6	468.4	469.2	469.7
125°	503.8	504.6	505.1	505.8	506.3	506.9	507.1	507.4	507.7	508.0	508.2
127.5°	542.8	543.7	544.4	545.0	545.7	546.4	546.8	547.3	547.8	548.2	548.3
130°	567.1	568.0	568.5	569.1	569.6	570.2	570.8	571.4	571.9	572.5	572.7
132.5°	590.5	591.2	591.7	592.1	592.5	593.1	593.6	594.2	594.7	595.3	595.4
135°	624.9	625.6	626.2	626.7	627.3	627.8	628.3	628.7	629.1	629.6	629.6
137.5°	656.3	656.9	657.2	657.5	657.9	658.1	658.8	659.5	660.2	660.9	661.1
140°	675.6	676.2	676.7	677.1	677.5	678.0	678.5	679.1	679.6	680.2	680.4
142.5°	694.4	695.0	695.4	695.9	696.3	696.7	697.2	697.6	698.0	698.4	698.5
145°	721.2	721.8	722.0	722.4	722.6	722.9	723.2	723.5	723.8	724.0	724.2
147.5°	744.5	744.9	745.3	745.5	745.8	746.1	746.4	746.7	746.9	747.3	747.0
150°	758.8	759.1	759.5	759.7	760.0	760.3	760.6	760.9	761.1	761.4	761.4
152.5°	771.6	771.8	772.0	772.1	772.3	772.5	772.9	773.4	774.0	774.5	774.4
155°	788.9	788.8	789.0	789.2	789.3	789.5	790.1	790.8	791.5	792.3	792.2
157.5°	804.9	804.9	804.7	804.5	804.4	804.3	805.1	806.0	806.8	807.6	807.5
160°	813.6	813.5	813.3	813.1	813.0	812.9	813.7	814.6	815.5	816.2	816.2
162.5°	821.3	821.0	820.9	820.8	820.6	820.4	821.5	822.4	823.4	824.3	824.3
165°	831.5	831.2	831.0	830.9	830.8	830.6	831.7	832.8	834.0	835.1	835.2
167.5°	839.0	838.7	838.7	838.7	838.7	838.7	839.8	840.9	842.1	843.3	843.3
170°	843.6	843.3	843.3	843.3	843.3	843.3	844.4	845.5	846.7	847.8	847.8
172.5°	846.2	845.8	846.0	846.1	846.2	846.4	847.5	848.6	849.7	850.8	850.8
175°	850.0	849.7	849.8	850.0	850.2	850.2	851.3	852.2	853.3	854.2	854.1
177.5°	851.5	851.4	851.4	851.5	851.7	851.8	852.6	853.6	854.5	855.4	855.2
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332434-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1003.2	1002.9	1003.2	1001.8	1003.2	1002.9	1003.2	1007.5	1007.5	1008.0	1008.3
5°	933.6	933.1	931.8	927.7	931.8	933.1	933.6	934.9	938.5	944.9	943.1
7.5°	872.7	872.1	868.1	868.2	868.1	872.1	872.7	876.2	880.3	884.2	888.7
10°	836.6	837.1	831.7	828.5	831.7	837.1	836.6	839.8	845.7	848.8	852.0
12.5°	801.7	799.6	795.2	791.8	795.2	799.6	801.7	804.1	812.1	815.6	821.7
15°	755.5	751.0	740.2	741.1	740.2	751.0	755.5	753.7	761.8	766.3	768.1
17.5°	701.1	697.8	697.6	691.3	697.6	697.8	701.1	704.7	711.8	716.6	729.5
20°	669.4	667.2	668.0	661.8	668.0	667.2	669.4	676.6	681.1	687.4	697.8
22.5°	644.5	642.3	638.5	636.5	638.5	642.3	644.5	649.5	654.4	663.3	668.9
25°	608.1	604.5	600.9	603.1	600.9	604.5	608.1	610.8	619.8	623.9	632.0
27.5°	571.7	568.9	565.3	564.9	565.3	568.9	571.7	574.3	579.3	586.1	595.8
30°	548.6	545.9	544.1	541.8	544.1	545.9	548.6	550.9	555.8	563.0	570.2
32.5°	525.1	524.6	521.3	520.9	521.3	524.6	525.1	528.8	533.8	540.6	546.8
35°	494.5	491.8	490.9	491.4	490.9	491.8	494.5	496.3	500.8	507.1	513.0
37.5°	465.4	461.8	460.1	458.6	460.1	461.8	465.4	465.6	470.3	474.5	482.4
40°	444.4	440.8	440.0	439.0	440.0	440.8	444.4	444.0	449.0	452.1	459.3
42.5°	421.0	419.6	419.0	417.4	419.0	419.6	421.0	423.4	426.3	430.8	436.3
45°	389.0	388.6	385.9	386.8	385.9	388.6	389.0	390.4	395.4	398.5	403.5
47.5°	355.3	353.4	351.5	352.7	351.5	353.4	355.3	357.1	360.4	364.3	370.9
50°	332.3	331.3	327.3	328.1	327.3	331.3	332.3	334.1	336.3	341.2	347.1
52.5°	309.2	305.7	304.2	303.7	304.2	305.7	309.2	310.9	313.6	319.3	323.6
55°	271.0	266.8	265.0	264.2	265.0	266.8	271.0	274.1	277.7	284.0	288.5
57.5°	233.4	232.3	230.9	231.9	230.9	232.3	233.4	238.7	242.2	247.1	252.6
60°	211.4	211.4	211.4	210.9	211.4	211.4	211.4	215.9	219.0	224.0	229.9
62.5°	194.5	193.4	193.0	193.6	193.0	193.4	194.5	196.5	199.6	202.8	207.9
65°	168.6	168.2	166.3	165.9	166.3	168.2	168.6	170.0	172.6	174.9	178.5
67.5°	144.1	142.5	142.0	141.4	142.0	142.5	144.1	145.3	147.1	150.0	151.8
70°	125.8	124.8	122.2	122.6	122.2	124.8	125.8	128.0	129.8	133.5	135.3
72.5°	105.9	105.0	104.5	103.8	104.5	105.0	105.9	108.2	109.9	114.0	116.8
75°	83.9	83.4	82.9	84.7	82.9	83.4	83.9	84.3	84.7	86.1	87.5
77.5°	67.2	67.2	67.4	66.7	67.4	67.2	67.2	67.2	67.2	67.8	68.2
80°	56.3	56.3	55.9	55.9	55.9	56.3	56.3	56.3	56.3	56.3	55.9
82.5°	45.2	45.5	45.8	45.1	45.8	45.5	45.2	45.9	46.2	45.5	45.8
85°	29.8	29.3	30.2	29.8	30.2	29.3	29.8	29.8	28.8	29.8	29.3
87.5°	17.0	16.3	16.4	16.8	16.4	16.3	17.0	16.2	16.1	16.0	15.5
90°	18.2	18.4	18.7	19.0	18.7	18.4	18.2	17.9	17.5	16.9	16.4
92.5°	20.5	20.7	20.8	21.0	20.8	20.7	20.5	20.3	19.8	18.9	18.0
95°	24.1	24.1	24.1	24.1	24.1	24.1	24.1	24.1	23.6	22.6	21.6
97.5°	25.7	25.8	26.0	26.1	26.0	25.8	25.7	25.6	24.9	23.8	22.6
100°	26.2	26.3	26.4	26.6	26.4	26.3	26.2	26.1	25.4	24.3	23.2
102.5°	26.3	26.6	26.9	27.1	26.9	26.6	26.3	26.1	27.7	31.3	34.7
105°	27.0	27.3	27.6	27.9	27.6	27.3	27.0	26.8	39.1	64.0	88.9
107.5°	143.9	125.1	106.3	87.6	106.3	125.1	143.9	162.7	181.2	199.5	217.7
110°	234.6	214.5	194.3	174.3	194.3	214.5	234.6	254.8	267.2	271.8	276.5



TEST NUMBER: P332434-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	311.7	307.5	303.2	298.9	303.2	307.5	311.7	315.9	318.1	318.0	317.9
115°	370.8	371.4	372.0	372.6	372.0	371.4	370.8	370.3	369.3	367.9	366.5
117.5°	413.5	413.6	413.7	413.9	413.7	413.6	413.5	413.4	412.8	411.6	410.5
120°	442.2	442.2	442.2	442.2	442.2	442.2	442.2	442.2	441.7	440.6	439.5
122.5°	469.8	469.8	470.0	470.1	470.0	469.8	469.8	469.7	469.2	468.4	467.6
125°	508.6	508.9	509.1	509.4	509.1	508.9	508.6	508.2	508.0	507.7	507.4
127.5°	548.0	547.7	547.4	547.2	547.4	547.7	548.0	548.3	548.2	547.8	547.3
130°	572.3	572.0	571.8	571.4	571.8	572.0	572.3	572.7	572.5	571.9	571.4
132.5°	595.0	594.6	594.2	593.7	594.2	594.6	595.0	595.4	595.3	594.7	594.2
135°	629.1	628.7	628.3	627.8	628.3	628.7	629.1	629.6	629.6	629.1	628.7
137.5°	660.8	660.5	660.2	660.0	660.2	660.5	660.8	661.1	660.9	660.2	659.5
140°	680.0	679.8	679.5	679.2	679.5	679.8	680.0	680.4	680.2	679.6	679.1
142.5°	698.1	697.8	697.3	696.9	697.3	697.8	698.1	698.5	698.4	698.0	697.6
145°	724.2	724.2	724.2	724.2	724.2	724.2	724.2	724.2	724.0	723.8	723.5
147.5°	746.4	745.7	745.1	744.4	745.1	745.7	746.4	747.0	747.3	746.9	746.7
150°	761.0	760.5	760.1	759.7	760.1	760.5	761.0	761.4	761.4	761.1	760.9
152.5°	773.8	773.1	772.5	771.8	772.5	773.1	773.8	774.4	774.5	774.0	773.4
155°	791.3	790.5	789.6	788.8	789.6	790.5	791.3	792.2	792.3	791.5	790.8
157.5°	806.4	805.3	804.3	803.1	804.3	805.3	806.4	807.5	807.6	806.8	806.0
160°	815.2	814.2	813.2	812.3	813.2	814.2	815.2	816.2	816.2	815.5	814.6
162.5°	823.5	822.6	821.7	820.9	821.7	822.6	823.5	824.3	824.3	823.4	822.4
165°	834.2	833.2	832.2	831.2	832.2	833.2	834.2	835.2	835.1	834.0	832.8
167.5°	842.1	840.9	839.8	838.7	839.8	840.9	842.1	843.3	843.3	842.1	840.9
170°	846.7	845.5	844.4	843.3	844.4	845.5	846.7	847.8	847.8	846.7	845.5
172.5°	849.5	848.3	847.1	845.8	847.1	848.3	849.5	850.8	850.8	849.7	848.6
175°	853.0	851.9	850.8	849.6	850.8	851.9	853.0	854.1	854.2	853.3	852.2
177.5°	854.1	853.0	851.9	850.8	851.9	853.0	854.1	855.2	855.4	854.5	853.6
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332434-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1005.0	1010.1	1015.1	1019.9	1027.1	1030.3	1035.0	1036.8	1042.2	1050.2	1056.6
5°	943.9	951.1	960.6	968.3	980.4	989.9	1000.3	1010.2	1021.9	1038.6	1053.4
7.5°	892.1	899.2	910.6	924.8	938.2	951.7	965.9	979.4	996.1	1020.0	1043.7
10°	857.8	866.4	879.9	895.3	911.9	925.0	941.7	958.8	979.6	1007.0	1035.4
12.5°	828.3	834.7	850.3	865.0	883.8	900.4	916.8	936.8	960.4	989.7	1023.9
15°	781.2	790.2	805.6	821.7	841.6	859.2	880.4	904.7	927.7	963.8	1005.2
17.5°	733.9	747.7	763.6	782.0	796.6	820.9	843.9	868.8	897.2	935.4	980.9
20°	703.7	714.5	729.4	756.0	775.3	793.8	815.0	846.1	872.3	915.5	962.9
22.5°	678.0	686.0	702.7	724.6	747.2	768.6	790.1	819.8	852.0	893.2	944.4
25°	640.1	652.7	665.4	681.1	705.5	731.2	754.6	779.8	814.1	857.8	913.3
27.5°	603.0	614.5	627.0	646.4	664.8	688.8	713.3	742.3	779.0	825.3	881.6
30°	579.3	587.8	599.5	624.3	641.0	661.8	690.6	716.3	750.5	799.7	859.2
32.5°	554.7	565.8	578.6	597.6	618.3	637.9	664.3	692.2	727.1	775.5	836.5
35°	519.8	532.8	545.9	559.8	580.6	600.9	622.9	653.6	689.2	736.2	796.1
37.5°	487.6	498.1	508.8	526.1	545.7	565.0	585.7	615.9	649.4	700.0	754.9
40°	467.0	476.5	484.6	502.7	521.5	542.3	562.6	589.2	625.3	672.5	725.7
42.5°	444.6	453.4	464.4	479.1	499.6	517.0	537.4	562.5	596.4	644.5	691.1
45°	411.1	421.0	430.5	444.4	464.8	481.9	499.9	523.8	558.5	598.2	639.6
47.5°	376.3	386.2	396.9	410.4	428.2	445.6	463.6	484.7	516.4	555.3	583.3
50°	353.9	362.0	372.8	386.3	402.5	421.0	437.2	460.2	490.4	521.1	545.4
52.5°	330.8	338.2	350.4	364.7	379.8	395.8	413.1	432.8	460.1	489.0	508.3
55°	294.8	303.8	314.2	328.1	343.0	356.5	373.2	393.6	415.2	436.8	449.9
57.5°	261.1	268.6	277.4	291.8	304.7	320.9	335.8	351.6	371.6	388.0	396.5
60°	236.7	243.4	254.7	267.3	279.5	293.4	310.6	326.4	341.7	354.7	361.5
62.5°	213.6	221.4	231.3	242.8	256.1	269.3	284.3	297.5	311.0	322.3	326.9
65°	183.5	189.8	197.0	207.8	218.6	232.1	243.8	257.4	267.3	273.6	277.7
67.5°	156.1	160.2	165.7	172.9	183.6	195.4	206.7	217.3	225.6	229.9	233.5
70°	138.4	141.1	145.2	152.4	160.5	170.8	182.5	190.2	197.4	201.0	204.7
72.5°	120.7	124.2	127.9	133.6	140.3	147.7	156.3	165.7	169.7	174.0	176.2
75°	91.5	96.4	101.4	105.0	109.5	115.4	123.0	128.9	131.2	134.7	135.3
77.5°	69.1	70.2	73.8	78.3	82.1	86.3	91.2	96.3	97.5	99.4	100.6
80°	56.8	56.8	56.8	59.5	64.0	67.2	71.6	74.4	76.2	76.6	77.1
82.5°	45.6	45.6	45.3	45.8	47.4	49.2	53.3	56.3	57.8	57.5	56.6
85°	29.8	28.8	28.8	28.4	28.8	28.0	27.5	29.3	32.0	32.0	31.1
87.5°	15.4	15.0	14.9	14.2	13.5	12.7	11.4	11.5	11.1	12.3	11.7
90°	15.8	15.2	13.3	11.5	9.7	7.9	6.3	4.8	3.4	2.1	0.6
92.5°	17.1	16.2	14.8	13.4	12.1	10.7	10.2	10.6	11.0	11.4	11.8
95°	20.7	19.6	18.1	16.5	15.0	13.4	15.6	21.4	27.1	32.9	38.7
97.5°	21.5	20.4	30.6	40.6	50.8	61.0	67.3	69.9	72.5	75.1	77.7
100°	22.0	20.9	42.9	64.8	86.8	108.7	118.3	115.5	112.7	109.9	107.1
102.5°	38.2	41.7	65.7	89.6	113.7	137.7	148.6	146.6	144.6	142.6	140.5
105°	113.8	138.8	151.4	164.1	176.8	189.4	195.0	193.5	191.9	190.4	188.8
107.5°	236.0	254.3	252.4	250.3	248.3	246.3	244.7	243.5	242.2	241.0	239.7
110°	281.1	285.8	284.2	282.7	281.1	279.6	278.2	277.1	276.0	274.8	273.7



TEST NUMBER: P332434-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	317.8	317.7	316.2	314.6	313.1	311.5	310.2	309.2	308.2	307.1	306.2
115°	365.1	363.7	362.4	361.1	359.9	358.6	357.6	356.7	355.9	355.0	354.1
117.5°	409.4	408.3	407.6	407.0	406.3	405.7	404.8	403.8	402.8	401.7	400.7
120°	438.3	437.1	436.8	436.4	435.9	435.5	434.6	433.3	432.1	430.8	429.6
122.5°	466.8	466.1	465.5	465.0	464.4	463.9	463.1	462.1	461.1	460.0	459.0
125°	507.1	506.9	506.3	505.8	505.1	504.6	503.8	502.7	501.5	500.4	499.3
127.5°	546.8	546.4	545.7	545.0	544.4	543.7	542.8	541.7	540.5	539.4	538.3
130°	570.8	570.2	569.6	569.1	568.5	568.0	567.1	566.0	564.9	563.8	562.6
132.5°	593.6	593.1	592.5	592.1	591.7	591.2	590.5	589.3	588.1	587.0	585.9
135°	628.3	627.8	627.3	626.7	626.2	625.6	624.9	624.1	623.2	622.4	621.6
137.5°	658.8	658.1	657.9	657.5	657.2	656.9	656.3	655.1	654.1	653.0	651.9
140°	678.5	678.0	677.5	677.1	676.7	676.2	675.6	674.8	673.9	673.0	672.2
142.5°	697.2	696.7	696.3	695.9	695.4	695.0	694.4	693.5	692.7	691.8	691.0
145°	723.2	722.9	722.6	722.4	722.0	721.8	721.2	720.1	719.2	718.2	717.2
147.5°	746.4	746.1	745.8	745.5	745.3	744.9	744.5	743.8	743.2	742.5	741.9
150°	760.6	760.3	760.0	759.7	759.5	759.1	758.8	758.4	757.9	757.5	757.2
152.5°	772.9	772.5	772.3	772.1	772.0	771.8	771.6	771.4	771.2	771.0	770.8
155°	790.1	789.5	789.3	789.2	789.0	788.8	788.9	789.2	789.5	789.8	790.1
157.5°	805.1	804.3	804.4	804.5	804.7	804.9	804.9	804.9	804.9	805.0	805.0
160°	813.7	812.9	813.0	813.1	813.3	813.5	813.6	813.7	813.9	814.0	814.2
162.5°	821.5	820.4	820.6	820.8	820.9	821.0	821.3	821.7	822.0	822.4	822.8
165°	831.7	830.6	830.8	830.9	831.0	831.2	831.5	831.9	832.3	832.8	833.2
167.5°	839.8	838.7	838.7	838.7	838.7	838.7	839.0	839.6	840.2	840.7	841.3
170°	844.4	843.3	843.3	843.3	843.3	843.3	843.6	844.1	844.7	845.2	845.8
172.5°	847.5	846.4	846.2	846.1	846.0	845.8	846.2	846.9	847.5	848.2	848.9
175°	851.3	850.2	850.2	850.0	849.8	849.7	850.0	850.7	851.4	852.0	852.8
177.5°	852.6	851.8	851.7	851.5	851.4	851.4	851.5	852.1	852.6	853.3	853.8
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332434-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1058.8	1062.7	1067.8	1075.4	1081.2	1086.2	1087.3	1088.7	1092.4	1098.5	1103.1
5°	1065.7	1076.0	1092.7	1108.9	1126.5	1140.9	1154.4	1163.9	1172.9	1191.9	1207.2
7.5°	1063.5	1086.6	1112.7	1141.9	1171.3	1199.9	1226.4	1250.1	1273.7	1301.3	1332.7
10°	1062.0	1089.1	1124.2	1161.7	1202.6	1242.8	1281.6	1311.7	1346.9	1378.5	1418.6
12.5°	1055.2	1094.2	1136.2	1184.0	1234.4	1280.7	1331.7	1373.5	1413.7	1459.2	1505.9
15°	1046.3	1093.6	1146.8	1210.3	1286.9	1342.9	1395.2	1467.7	1517.3	1566.9	1633.6
17.5°	1029.9	1087.7	1154.2	1236.7	1300.7	1375.8	1454.5	1511.8	1578.6	1648.5	1708.9
20°	1016.9	1084.1	1158.5	1239.7	1321.2	1402.8	1479.0	1547.5	1616.5	1697.2	1746.8
22.5°	1004.0	1070.4	1147.7	1233.9	1321.5	1407.5	1493.7	1574.2	1651.8	1733.3	1796.6
25°	976.4	1055.2	1139.1	1227.0	1313.5	1408.3	1511.0	1600.7	1696.7	1780.5	1840.6
27.5°	948.4	1020.7	1104.2	1193.3	1289.6	1401.4	1522.3	1624.4	1720.5	1780.5	1799.4
30°	923.2	999.8	1076.4	1167.1	1271.2	1396.0	1524.5	1641.2	1720.2	1746.3	1726.9
32.5°	897.6	967.0	1042.9	1135.7	1246.3	1382.7	1527.4	1631.2	1678.7	1658.7	1579.8
35°	852.4	915.1	988.5	1081.4	1208.5	1375.4	1515.5	1585.8	1574.1	1461.4	1312.7
37.5°	804.1	855.1	923.2	1020.3	1169.4	1346.0	1464.3	1474.6	1373.2	1200.2	1028.4
40°	765.9	811.8	881.8	983.2	1139.1	1317.2	1412.7	1370.8	1213.5	1021.0	877.7
42.5°	728.8	767.5	834.8	944.2	1110.3	1277.9	1335.9	1244.6	1063.1	881.1	750.7
45°	665.8	702.3	769.9	882.2	1051.2	1202.6	1195.0	1036.3	854.7	708.2	599.9
47.5°	606.1	638.0	701.5	816.1	981.9	1089.9	1018.3	849.5	695.3	577.8	500.7
50°	564.0	595.5	658.6	771.7	926.3	1005.2	902.9	740.2	599.1	501.7	440.4
52.5°	523.6	554.4	612.1	722.3	859.3	906.5	796.5	645.7	528.1	444.0	391.3
55°	467.0	490.4	542.3	647.7	750.1	761.0	649.5	523.3	426.5	367.8	331.7
57.5°	409.4	429.6	480.8	564.8	636.6	631.0	525.5	416.2	350.9	307.5	281.3
60°	371.9	391.8	436.8	508.9	563.0	544.1	447.2	359.3	303.3	271.4	250.6
62.5°	336.9	352.4	394.6	447.3	486.2	464.8	382.3	309.5	265.2	238.2	221.8
65°	286.3	298.9	332.7	360.2	381.8	361.1	292.6	242.0	210.1	191.1	179.9
67.5°	238.1	246.2	267.5	277.4	292.7	269.9	220.0	186.1	168.0	152.0	144.1
70°	207.8	213.7	225.0	233.1	237.1	213.7	176.7	151.9	136.6	125.3	120.4
72.5°	177.5	182.6	184.9	191.6	189.5	167.6	142.1	122.3	111.3	103.7	97.3
75°	135.7	137.9	135.7	132.9	127.1	111.8	94.2	84.3	76.2	72.6	70.3
77.5°	98.9	98.2	95.1	90.8	80.8	71.2	61.7	58.5	54.9	53.0	52.2
80°	76.2	74.4	71.6	64.9	56.3	49.6	47.4	45.1	43.7	41.5	41.0
82.5°	56.7	55.6	51.1	45.5	39.4	36.2	34.4	33.6	32.2	31.0	30.9
85°	30.2	28.8	23.8	20.8	19.8	18.9	18.5	18.5	16.7	16.2	16.2
87.5°	10.2	8.3	8.2	7.4	7.7	7.3	8.1	7.7	7.7	8.2	7.6
90°	2.1	3.4	4.8	6.3	7.9	9.7	11.5	13.3	15.2	15.8	16.4
92.5°	11.4	11.0	10.6	10.2	10.7	12.1	13.4	14.8	16.2	17.1	18.0
95°	32.9	27.1	21.4	15.6	13.4	15.0	16.5	18.1	19.6	20.7	21.6
97.5°	75.1	72.5	69.9	67.3	61.0	50.8	40.6	30.6	20.4	21.5	22.6
100°	109.9	112.7	115.5	118.3	108.7	86.8	64.8	42.9	20.9	22.0	23.2
102.5°	142.6	144.6	146.6	148.6	137.7	113.7	89.6	65.7	41.7	38.2	34.7
105°	190.4	191.9	193.5	195.0	189.4	176.8	164.1	151.4	138.8	113.8	88.9
107.5°	241.0	242.2	243.5	244.7	246.3	248.3	250.3	252.4	254.3	236.0	217.7
110°	274.8	276.0	277.1	278.2	279.6	281.1	282.7	284.2	285.8	281.1	276.5



TEST NUMBER: P332434-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	307.1	308.2	309.2	310.2	311.5	313.1	314.6	316.2	317.7	317.8	317.9
115°	355.0	355.9	356.7	357.6	358.6	359.9	361.1	362.4	363.7	365.1	366.5
117.5°	401.7	402.8	403.8	404.8	405.7	406.3	407.0	407.6	408.3	409.4	410.5
120°	430.8	432.1	433.3	434.6	435.5	435.9	436.4	436.8	437.1	438.3	439.5
122.5°	460.0	461.1	462.1	463.1	463.9	464.4	465.0	465.5	466.1	466.8	467.6
125°	500.4	501.5	502.7	503.8	504.6	505.1	505.8	506.3	506.9	507.1	507.4
127.5°	539.4	540.5	541.7	542.8	543.7	544.4	545.0	545.7	546.4	546.8	547.3
130°	563.8	564.9	566.0	567.1	568.0	568.5	569.1	569.6	570.2	570.8	571.4
132.5°	587.0	588.1	589.3	590.5	591.2	591.7	592.1	592.5	593.1	593.6	594.2
135°	622.4	623.2	624.1	624.9	625.6	626.2	626.7	627.3	627.8	628.3	628.7
137.5°	653.0	654.1	655.1	656.3	656.9	657.2	657.5	657.9	658.1	658.8	659.5
140°	673.0	673.9	674.8	675.6	676.2	676.7	677.1	677.5	678.0	678.5	679.1
142.5°	691.8	692.7	693.5	694.4	695.0	695.4	695.9	696.3	696.7	697.2	697.6
145°	718.2	719.2	720.1	721.2	721.8	722.0	722.4	722.6	722.9	723.2	723.5
147.5°	742.5	743.2	743.8	744.5	744.9	745.3	745.5	745.8	746.1	746.4	746.7
150°	757.5	757.9	758.4	758.8	759.1	759.5	759.7	760.0	760.3	760.6	760.9
152.5°	771.0	771.2	771.4	771.6	771.8	772.0	772.1	772.3	772.5	772.9	773.4
155°	789.8	789.5	789.2	788.9	788.8	789.0	789.2	789.3	789.5	790.1	790.8
157.5°	805.0	804.9	804.9	804.9	804.9	804.7	804.5	804.4	804.3	805.1	806.0
160°	814.0	813.9	813.7	813.6	813.5	813.3	813.1	813.0	812.9	813.7	814.6
162.5°	822.4	822.0	821.7	821.3	821.0	820.9	820.8	820.6	820.4	821.5	822.4
165°	832.8	832.3	831.9	831.5	831.2	831.0	830.9	830.8	830.6	831.7	832.8
167.5°	840.7	840.2	839.6	839.0	838.7	838.7	838.7	838.7	838.7	839.8	840.9
170°	845.2	844.7	844.1	843.6	843.3	843.3	843.3	843.3	843.3	844.4	845.5
172.5°	848.2	847.5	846.9	846.2	845.8	846.0	846.1	846.2	846.4	847.5	848.6
175°	852.0	851.4	850.7	850.0	849.7	849.8	850.0	850.2	850.2	851.3	852.2
177.5°	853.3	852.6	852.1	851.5	851.4	851.4	851.5	851.7	851.8	852.6	853.6
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332434-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
2.5°	1110.7	1110.7	1112.2	1117.6	1118.3	1123.0	1121.5
5°	1220.7	1229.2	1232.4	1246.0	1254.0	1257.7	1250.4
7.5°	1355.2	1379.4	1390.9	1405.0	1417.6	1421.3	1411.4
10°	1453.3	1478.5	1499.8	1512.8	1525.0	1533.1	1543.4
12.5°	1548.2	1579.2	1599.3	1617.7	1630.3	1640.5	1642.3
15°	1651.2	1698.1	1733.7	1759.8	1772.9	1779.7	1776.9
17.5°	1755.1	1798.6	1823.9	1850.6	1868.7	1869.7	1870.2
20°	1814.0	1856.3	1885.6	1905.4	1925.7	1924.9	1929.3
22.5°	1853.2	1886.6	1909.0	1923.5	1930.4	1927.0	1927.9
25°	1871.6	1881.5	1877.5	1854.5	1848.7	1827.5	1831.1
27.5°	1776.8	1729.9	1681.4	1619.0	1569.8	1530.5	1532.5
30°	1648.0	1565.1	1470.4	1391.1	1319.9	1300.0	1257.7
32.5°	1468.1	1343.7	1232.8	1158.8	1097.7	1081.2	1044.2
35°	1163.0	1042.2	928.2	859.6	832.6	794.7	794.3
37.5°	904.0	797.6	737.3	685.9	658.9	636.0	633.8
40°	760.4	677.5	632.0	595.0	568.4	551.3	547.3
42.5°	660.2	593.1	550.5	527.6	507.1	498.3	491.7
45°	539.2	494.0	464.3	443.6	434.1	427.3	423.7
47.5°	451.0	420.8	400.5	386.7	379.0	371.9	373.8
50°	403.0	378.2	363.3	350.3	344.4	339.4	339.9
52.5°	364.4	342.2	330.1	320.7	313.4	309.9	308.2
55°	309.3	295.2	283.1	276.3	272.2	267.3	266.0
57.5°	263.8	253.0	243.1	235.4	234.4	229.6	230.2
60°	233.5	224.5	216.4	212.3	209.1	205.1	206.5
62.5°	208.6	201.0	193.6	190.3	187.2	184.2	184.9
65°	170.8	163.6	159.1	157.3	155.9	154.6	153.3
67.5°	136.1	131.7	128.9	125.0	122.3	121.8	120.5
70°	114.5	108.7	103.7	98.8	97.4	96.9	97.4
72.5°	91.8	88.1	86.7	84.3	84.0	82.8	83.7
75°	69.0	67.6	66.7	64.9	64.9	64.9	64.9
77.5°	50.9	50.0	49.5	49.2	48.6	48.0	48.0
80°	39.7	39.2	38.3	38.3	37.9	38.3	37.9
82.5°	30.0	29.9	28.9	28.9	28.5	28.2	28.5
85°	15.3	14.9	15.8	14.9	15.3	14.5	15.3
87.5°	7.7	7.8	7.6	7.6	7.3	8.1	7.4
90°	16.9	17.5	17.9	18.2	18.4	18.7	19.0
92.5°	18.9	19.8	20.3	20.5	20.7	20.8	21.0
95°	22.6	23.6	24.1	24.1	24.1	24.1	24.1
97.5°	23.8	24.9	25.6	25.7	25.8	26.0	26.1
100°	24.3	25.4	26.1	26.2	26.3	26.4	26.6
102.5°	31.3	27.7	26.1	26.3	26.6	26.9	27.1
105°	64.0	39.1	26.8	27.0	27.3	27.6	27.9
107.5°	199.5	181.2	162.7	143.9	125.1	106.3	87.6
110°	271.8	267.2	254.8	234.6	214.5	194.3	174.3



TEST NUMBER: P332434-935

CATALOG NUMBER: S123RDIW-S775D755U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	318.0	318.1	315.9	311.7	307.5	303.2	298.9
115°	367.9	369.3	370.3	370.8	371.4	372.0	372.6
117.5°	411.6	412.8	413.4	413.5	413.6	413.7	413.9
120°	440.6	441.7	442.2	442.2	442.2	442.2	442.2
122.5°	468.4	469.2	469.7	469.8	469.8	470.0	470.1
125°	507.7	508.0	508.2	508.6	508.9	509.1	509.4
127.5°	547.8	548.2	548.3	548.0	547.7	547.4	547.2
130°	571.9	572.5	572.7	572.3	572.0	571.8	571.4
132.5°	594.7	595.3	595.4	595.0	594.6	594.2	593.7
135°	629.1	629.6	629.6	629.1	628.7	628.3	627.8
137.5°	660.2	660.9	661.1	660.8	660.5	660.2	660.0
140°	679.6	680.2	680.4	680.0	679.8	679.5	679.2
142.5°	698.0	698.4	698.5	698.1	697.8	697.3	696.9
145°	723.8	724.0	724.2	724.2	724.2	724.2	724.2
147.5°	746.9	747.3	747.0	746.4	745.7	745.1	744.4
150°	761.1	761.4	761.4	761.0	760.5	760.1	759.7
152.5°	774.0	774.5	774.4	773.8	773.1	772.5	771.8
155°	791.5	792.3	792.2	791.3	790.5	789.6	788.8
157.5°	806.8	807.6	807.5	806.4	805.3	804.3	803.1
160°	815.5	816.2	816.2	815.2	814.2	813.2	812.3
162.5°	823.4	824.3	824.3	823.5	822.6	821.7	820.9
165°	834.0	835.1	835.2	834.2	833.2	832.2	831.2
167.5°	842.1	843.3	843.3	842.1	840.9	839.8	838.7
170°	846.7	847.8	847.8	846.7	845.5	844.4	843.3
172.5°	849.7	850.8	850.8	849.5	848.3	847.1	845.8
175°	853.3	854.2	854.1	853.0	851.9	850.8	849.6
177.5°	854.5	855.4	855.2	854.1	853.0	851.9	850.8
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8

(END OF REPORT)