

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332106-930

Luminaire Tested: **S123DIW-S340D1030U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332106-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D1030U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4514.0 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332106-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332106-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	92	88	84	81	82	79	75	73	61	59	57	45	43	42	30	29	28	21
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	67	60	55	68	60	54	50	47	43	39	35	32	30	23	21	20	15
4	70	60	52	46	62	53	47	42	42	37	33	31	28	25	21	19	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	17	15	11
6	59	47	39	34	52	42	36	31	33	28	25	25	21	19	17	15	13	10
7	54	42	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	42	31	25	21	25	20	17	19	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4755	4755	4755
5°	4778	4712	4744
10°	4746	4671	4701
15°	4690	4619	4627
20°	4625	4543	4548
25°	4538	4454	4444
30°	4443	4354	4320
35°	4343	4248	4193
40°	4239	4131	4068
45°	4122	4025	3927
50°	4007	3893	3785
55°	3856	3757	3643
60°	3705	3597	3483
65°	3568	3423	3319
70°	3371	3229	3084
75°	3082	2969	2845
80°	2777	2665	2641
85°	2433	2347	2260



TEST NUMBER: P332106-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.6	0.9
10°-20°	117.5	2.6
20°-30°	173.6	3.8
30°-40°	202.8	4.5
40°-50°	203.9	4.5
50°-60°	179.1	4.0
60°-70°	133.4	3.0
70°-80°	76.0	1.7
80°-90°	24.9	0.6
90°-100°	40.1	0.9
100°-110°	191.0	4.2
110°-120°	458.8	10.2
120°-130°	584.2	12.9
130°-140°	624.2	13.8
140°-150°	583.7	12.9
150°-160°	470.8	10.4
160°-170°	303.9	6.7
170°-180°	104.7	2.3
0°-30°	332.7	7.4
0°-40°	535.5	11.9
0°-60°	918.4	20.3
0°-90°	1152.7	25.5
90°-120°	689.8	15.3
90°-150°	2481.9	55.0
90°-180°	3361.0	74.5
0°-180°	4514.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	442	442	442	442	442	
5°	442	440	436	440	439	42
15°	421	419	414	417	415	119
25°	382	380	375	375	374	176
35°	330	328	323	321	319	207
45°	271	269	264	260	258	209
55°	206	205	200	196	194	184
65°	140	138	134	132	130	138
75°	74	73	71	70	68	79
85°	20	19	19	18	18	22
90°	1	9	20	23	24	3
95°	50	19	25	31	31	62
105°	244	248	179	43	36	259
115°	458	463	470	478	482	452
125°	645	652	655	657	658	576
135°	803	808	812	814	812	618
145°	927	932	934	936	936	580
155°	1021	1020	1020	1024	1020	470
165°	1077	1074	1074	1079	1074	304
175°	1102	1098	1099	1104	1098	105
180°	1102	1102	1102	1102	1102	



TEST NUMBER: P332106-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	443.4	443.0	442.8	442.5	442.2	441.7	441.0	440.3	439.5	438.8	439.4
5°	442.2	441.7	441.3	440.9	440.5	439.9	438.9	438.0	437.0	436.1	436.9
7.5°	437.9	437.4	437.0	436.6	436.2	435.5	434.6	433.6	432.6	431.6	432.4
10°	434.2	433.8	433.3	432.9	432.5	431.8	430.6	429.6	428.4	427.4	428.1
12.5°	429.3	429.0	428.6	428.3	428.0	427.2	426.2	425.2	424.1	423.1	423.7
15°	420.9	420.6	420.2	419.9	419.6	418.8	417.8	416.6	415.6	414.5	415.2
17.5°	411.1	410.7	410.3	409.8	409.4	408.6	407.5	406.4	405.3	404.2	404.6
20°	403.8	403.3	402.8	402.3	401.8	401.0	399.9	398.8	397.7	396.6	397.0
22.5°	395.6	395.1	394.6	394.1	393.6	392.8	391.7	390.6	389.5	388.4	388.7
25°	382.1	381.6	381.2	380.7	380.2	379.4	378.2	377.2	376.0	375.0	375.0
27.5°	367.8	367.3	366.8	366.3	365.8	365.0	363.9	362.6	361.5	360.3	360.4
30°	357.5	357.0	356.6	356.2	355.8	355.0	353.8	352.6	351.5	350.3	350.3
32.5°	347.2	346.6	346.0	345.4	345.0	344.1	343.2	342.3	341.4	340.6	340.1
35°	330.5	330.0	329.5	329.0	328.5	327.7	326.6	325.5	324.4	323.3	322.8
37.5°	313.5	312.8	312.2	311.5	311.0	310.1	308.9	307.8	306.7	305.6	305.0
40°	301.7	301.1	300.6	300.1	299.6	298.7	297.6	296.4	295.2	294.0	293.3
42.5°	289.8	289.2	288.6	288.0	287.5	286.6	285.4	284.2	283.1	281.8	281.2
45°	270.8	270.5	270.2	269.9	269.5	268.8	267.7	266.6	265.5	264.4	263.4
47.5°	252.1	251.6	251.1	250.6	250.1	249.4	248.3	247.3	246.3	245.2	244.3
50°	239.3	238.9	238.5	238.1	237.7	236.8	235.8	234.7	233.6	232.5	231.5
52.5°	225.9	225.7	225.3	225.1	224.8	224.0	222.9	221.8	220.6	219.4	218.7
55°	205.5	205.5	205.4	205.3	205.2	204.6	203.5	202.4	201.3	200.2	199.3
57.5°	186.1	185.8	185.5	185.2	184.9	184.3	183.4	182.5	181.7	180.8	180.0
60°	172.1	172.0	171.9	171.9	171.8	171.2	170.2	169.2	168.2	167.1	166.4
62.5°	159.6	159.4	159.2	159.0	158.7	158.2	157.1	156.1	155.1	154.1	153.4
65°	140.1	139.7	139.3	138.9	138.5	137.9	137.1	136.2	135.3	134.4	133.8
67.5°	119.6	119.2	118.9	118.5	118.1	117.6	117.0	116.3	115.7	115.0	114.5
70°	107.1	106.6	106.2	105.6	105.1	104.6	104.1	103.5	103.1	102.6	102.0
72.5°	94.1	93.7	93.4	92.9	92.5	92.1	91.6	91.0	90.4	89.8	89.3
75°	74.1	73.7	73.4	73.1	72.7	72.4	72.2	71.9	71.7	71.4	71.0
77.5°	56.3	56.2	56.0	55.8	55.6	55.4	55.1	54.8	54.5	54.1	53.9
80°	44.8	44.6	44.4	44.1	43.8	43.6	43.5	43.3	43.1	43.0	42.8
82.5°	33.6	33.5	33.5	33.4	33.3	33.3	33.3	33.3	33.3	33.2	33.0
85°	19.7	19.6	19.4	19.2	19.1	19.0	19.0	19.0	19.0	19.0	18.8
87.5°	8.1	8.2	8.4	8.6	8.7	9.0	9.4	9.8	10.2	10.6	10.7
90°	0.8	2.6	4.5	6.3	8.1	10.2	12.6	14.9	17.3	19.6	20.4
92.5°	15.2	14.8	14.2	13.7	13.2	13.9	15.7	17.4	19.2	21.0	22.1
95°	50.0	42.5	35.1	27.6	20.1	17.4	19.4	21.4	23.4	25.4	26.7
97.5°	100.4	97.0	93.7	90.3	87.0	78.8	65.7	52.6	39.5	26.3	27.8
100°	138.4	142.0	145.7	149.3	153.0	140.6	112.2	83.8	55.4	27.0	28.5
102.5°	181.6	184.3	186.9	189.5	192.1	177.9	146.9	115.9	84.9	53.9	49.4
105°	244.0	246.1	248.0	250.1	252.0	244.8	228.4	212.1	195.8	179.4	147.2
107.5°	309.9	311.4	313.1	314.7	316.3	318.4	321.0	323.5	326.1	328.7	305.1
110°	353.8	355.2	356.7	358.2	359.5	361.3	363.3	365.3	367.3	369.3	363.3



TEST NUMBER: P332106-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	395.7	397.0	398.3	399.7	401.0	402.6	404.6	406.6	408.6	410.6	410.7
115°	457.8	458.9	459.9	461.1	462.1	463.5	465.1	466.8	468.4	470.0	471.9
117.5°	517.9	519.2	520.6	521.9	523.3	524.3	525.2	526.0	526.8	527.7	529.1
120°	555.2	556.8	558.5	560.1	561.7	562.9	563.4	563.9	564.5	565.0	566.5
122.5°	593.2	594.5	595.9	597.2	598.6	599.6	600.3	601.0	601.7	602.3	603.4
125°	645.3	646.8	648.2	649.6	651.1	652.2	652.9	653.6	654.4	655.1	655.5
127.5°	695.7	697.2	698.6	700.1	701.6	702.7	703.6	704.5	705.3	706.2	706.8
130°	727.2	728.6	730.1	731.6	733.0	734.1	734.8	735.6	736.3	737.0	737.8
132.5°	757.3	758.8	760.2	761.7	763.1	764.2	764.8	765.3	765.9	766.5	767.2
135°	803.3	804.5	805.5	806.6	807.7	808.6	809.3	810.1	810.8	811.5	812.0
137.5°	842.6	844.0	845.4	846.8	848.2	849.1	849.5	849.9	850.3	850.7	851.5
140°	868.9	869.9	871.1	872.1	873.2	874.0	874.6	875.1	875.6	876.2	876.9
142.5°	893.1	894.1	895.3	896.3	897.5	898.3	898.8	899.4	899.9	900.4	901.1
145°	927.0	928.2	929.5	930.8	932.1	932.9	933.3	933.6	934.0	934.3	934.7
147.5°	959.0	959.8	960.6	961.4	962.3	962.9	963.2	963.6	963.9	964.3	964.7
150°	978.6	979.1	979.7	980.2	980.7	981.2	981.5	981.9	982.3	982.7	983.0
152.5°	996.3	996.5	996.8	997.0	997.3	997.5	997.8	997.9	998.2	998.4	999.1
155°	1021.2	1020.8	1020.4	1020.1	1019.7	1019.6	1019.8	1019.9	1020.2	1020.3	1021.2
157.5°	1040.5	1040.5	1040.4	1040.4	1040.3	1040.2	1040.1	1039.8	1039.7	1039.5	1040.6
160°	1052.3	1052.1	1051.9	1051.7	1051.6	1051.3	1051.2	1051.0	1050.8	1050.7	1051.7
162.5°	1063.4	1062.9	1062.5	1062.0	1061.5	1061.2	1061.0	1060.9	1060.6	1060.5	1061.7
165°	1076.8	1076.3	1075.8	1075.2	1074.6	1074.3	1074.1	1073.9	1073.7	1073.6	1075.1
167.5°	1087.3	1086.6	1085.9	1085.2	1084.4	1084.0	1084.0	1084.0	1084.0	1084.0	1085.5
170°	1093.2	1092.5	1091.8	1091.0	1090.3	1090.0	1090.0	1090.0	1090.0	1090.0	1091.4
172.5°	1097.1	1096.3	1095.4	1094.5	1093.6	1093.3	1093.4	1093.6	1093.7	1093.9	1095.4
175°	1102.2	1101.3	1100.4	1099.5	1098.6	1098.2	1098.4	1098.6	1098.8	1098.9	1100.2
177.5°	1103.5	1102.8	1102.1	1101.4	1100.7	1100.3	1100.5	1100.7	1100.7	1100.9	1102.1
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2



TEST NUMBER: P332106-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	440.1	440.8	441.5	441.8	441.7	441.6	441.6	441.5
5°	437.8	438.6	439.5	439.9	439.7	439.5	439.3	439.1
7.5°	433.2	433.9	434.6	435.0	434.9	434.8	434.7	434.6
10°	428.9	429.7	430.4	430.7	430.6	430.4	430.2	430.1
12.5°	424.2	424.8	425.3	425.6	425.5	425.3	425.3	425.2
15°	415.8	416.5	417.2	417.3	416.7	416.2	415.7	415.2
17.5°	405.1	405.6	406.1	406.3	406.0	405.9	405.7	405.5
20°	397.3	397.6	397.9	398.0	397.7	397.5	397.2	397.0
22.5°	388.9	389.2	389.5	389.5	389.1	388.8	388.5	388.2
25°	375.1	375.2	375.3	375.2	375.0	374.7	374.5	374.2
27.5°	360.4	360.5	360.5	360.4	360.1	359.8	359.5	359.1
30°	350.3	350.3	350.3	349.9	349.4	348.8	348.2	347.6
32.5°	339.6	339.1	338.7	338.3	337.9	337.6	337.3	337.0
35°	322.3	321.8	321.2	320.8	320.4	319.9	319.5	319.1
37.5°	304.4	303.8	303.1	302.7	302.5	302.1	301.9	301.7
40°	292.7	292.0	291.3	290.8	290.5	290.2	289.8	289.5
42.5°	280.5	279.8	279.2	278.7	278.3	278.0	277.7	277.3
45°	262.4	261.4	260.3	259.7	259.2	258.8	258.4	258.0
47.5°	243.3	242.3	241.2	240.6	240.2	239.9	239.5	239.1
50°	230.6	229.7	228.8	228.0	227.6	227.1	226.6	226.0
52.5°	217.8	217.0	216.2	215.6	215.1	214.6	214.1	213.6
55°	198.4	197.4	196.5	195.8	195.4	194.9	194.5	194.1
57.5°	179.2	178.3	177.5	176.8	176.3	175.9	175.4	174.9
60°	165.7	164.9	164.1	163.5	163.1	162.7	162.2	161.8
62.5°	152.5	151.8	151.1	150.5	150.3	149.9	149.7	149.4
65°	133.1	132.5	131.8	131.3	131.1	130.8	130.5	130.3
67.5°	113.8	113.2	112.7	112.2	111.9	111.5	111.1	110.8
70°	101.4	100.8	100.2	99.7	99.3	98.9	98.4	98.0
72.5°	88.8	88.2	87.7	87.3	87.2	86.9	86.7	86.4
75°	70.6	70.1	69.7	69.4	69.1	68.9	68.6	68.4
77.5°	53.6	53.3	53.0	52.9	52.9	52.9	52.9	52.9
80°	42.7	42.6	42.6	42.6	42.6	42.6	42.6	42.6
82.5°	32.9	32.8	32.6	32.4	32.4	32.4	32.3	32.2
85°	18.7	18.5	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	10.8	10.8	10.9	11.0	11.1	11.2	11.3	11.3
90°	21.1	21.9	22.6	23.1	23.5	23.8	24.2	24.5
92.5°	23.3	24.5	25.6	26.3	26.5	26.7	27.0	27.1
95°	28.0	29.2	30.5	31.1	31.1	31.1	31.1	31.1
97.5°	29.3	30.7	32.2	33.0	33.2	33.3	33.6	33.8
100°	29.9	31.4	32.9	33.7	33.8	34.0	34.2	34.4
102.5°	44.8	40.4	35.8	33.8	34.1	34.4	34.7	35.1
105°	115.0	82.7	50.5	34.6	35.0	35.3	35.6	36.0
107.5°	281.4	257.9	234.2	210.3	186.0	161.8	137.5	113.2
110°	357.3	351.3	345.3	329.3	303.3	277.2	251.2	225.2



TEST NUMBER: P332106-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	410.8	410.9	411.0	408.3	402.8	397.4	391.8	386.4
115°	473.7	475.5	477.4	478.6	479.3	480.0	480.8	481.5
117.5°	530.6	532.1	533.5	534.3	534.4	534.6	534.8	534.9
120°	567.9	569.4	570.9	571.6	571.6	571.6	571.6	571.6
122.5°	604.4	605.4	606.4	607.1	607.2	607.3	607.5	607.6
125°	655.8	656.2	656.6	657.0	657.3	657.6	658.0	658.4
127.5°	707.4	707.9	708.6	708.7	708.3	707.9	707.6	707.2
130°	738.5	739.2	739.9	740.1	739.7	739.4	739.0	738.7
132.5°	767.9	768.7	769.4	769.5	769.0	768.5	768.0	767.4
135°	812.6	813.2	813.7	813.7	813.2	812.6	812.0	811.5
137.5°	852.4	853.3	854.2	854.4	854.0	853.7	853.3	853.0
140°	877.7	878.4	879.1	879.3	879.0	878.6	878.2	877.8
142.5°	901.6	902.2	902.8	902.8	902.3	901.8	901.3	900.7
145°	935.1	935.5	935.8	936.0	936.0	936.0	936.0	936.0
147.5°	965.1	965.4	965.8	965.6	964.7	963.8	963.0	962.2
150°	983.4	983.7	984.1	984.1	983.5	982.9	982.4	981.9
152.5°	999.7	1000.4	1001.0	1000.9	1000.0	999.2	998.4	997.6
155°	1022.1	1023.0	1024.0	1023.9	1022.8	1021.7	1020.6	1019.5
157.5°	1041.7	1042.8	1043.8	1043.7	1042.3	1040.9	1039.4	1038.0
160°	1052.8	1053.9	1055.0	1054.9	1053.6	1052.4	1051.1	1049.8
162.5°	1062.9	1064.2	1065.4	1065.4	1064.4	1063.2	1062.1	1060.9
165°	1076.4	1077.9	1079.4	1079.5	1078.2	1076.9	1075.6	1074.4
167.5°	1087.0	1088.4	1089.9	1089.9	1088.4	1087.0	1085.5	1084.0
170°	1092.8	1094.3	1095.8	1095.8	1094.3	1092.8	1091.4	1090.0
172.5°	1096.8	1098.2	1099.7	1099.6	1098.0	1096.4	1094.8	1093.2
175°	1101.5	1102.8	1104.1	1104.0	1102.5	1101.1	1099.6	1098.1
177.5°	1103.3	1104.4	1105.5	1105.5	1104.0	1102.5	1101.1	1099.6
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2

(END OF REPORT)