

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332114-930

Luminaire Tested: **S123DIW-S340D1535U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332114-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D1535U930-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6190.8 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332114-930

CATALOG NUMBER: S123DIW-S340D1535U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332114-930

CATALOG NUMBER: S123DIW-S340D1535U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19				
1	91	87	83	80	80	77	74	71	58	56	54	41	39	38	25	24	24	16				
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14				
3	76	67	60	54	66	59	53	49	45	41	38	32	29	27	19	18	17	12				
4	69	59	52	46	61	52	46	41	40	36	32	28	25	23	17	16	15	10				
5	63	52	45	39	56	46	40	35	35	31	28	25	22	20	16	14	13	9				
6	58	47	39	34	51	42	35	30	32	27	24	23	20	18	14	13	11	8				
7	54	42	34	29	47	37	31	26	29	24	21	21	18	15	13	11	10	7				
8	50	38	31	26	44	34	28	23	26	22	18	19	16	14	12	10	9	6				
9	46	34	27	23	41	31	25	20	24	19	16	17	14	12	11	9	8	6				
10	43	31	25	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4219	4219	4219	4219
5°	5032	4238	3756	4238
10°	6299	4217	3393	4217
15°	7725	4182	3158	4182
20°	9203	4129	3007	4129
25°	9772	4065	2973	4065
30°	8376	4018	2988	4018
35°	5825	3951	3020	3951
40°	4388	3873	3011	3873
45°	3643	3755	2973	3755
50°	3264	3518	2946	3518
55°	3051	3262	2909	3262
60°	2863	2992	2878	2992
65°	2690	2728	2786	2728
70°	2521	2426	2653	2426
75°	2258	2125	2433	2125
80°	1977	1742	2095	1742
85°	1556	1272	1408	1272



TEST NUMBER: P332114-930

CATALOG NUMBER: S123DIW-S340D1535U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.6	0.6
10°-20°	123.8	2.0
20°-30°	207.8	3.4
30°-40°	235.3	3.8
40°-50°	211.0	3.4
50°-60°	170.3	2.8
60°-70°	118.7	1.9
70°-80°	62.4	1.0
80°-90°	19.8	0.3
90°-100°	59.6	1.0
100°-110°	284.3	4.6
110°-120°	682.8	11.0
120°-130°	869.5	14.0
130°-140°	929.1	15.0
140°-150°	868.8	14.0
150°-160°	700.8	11.3
160°-170°	452.3	7.3
170°-180°	155.9	2.5
0°-30°	370.3	6.0
0°-40°	605.6	9.8
0°-60°	986.9	15.9
0°-90°	1187.8	19.2
90°-120°	1026.8	16.6
90°-150°	3694.1	59.7
90°-180°	5003.0	80.8
0°-180°	6190.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	392	392	392	392	392	
5°	466	392	348	392	466	48
15°	693	375	283	375	693	200
25°	823	342	250	342	823	361
35°	443	301	230	301	443	288
45°	239	247	195	247	239	189
55°	163	174	155	174	163	146
65°	106	107	109	107	106	105
75°	54	51	58	51	54	58
85°	13	10	11	10	13	16
90°	36	1	36	1	36	17
95°	46	74	46	74	46	39
105°	54	363	54	363	54	123
115°	717	681	717	681	717	662
125°	980	960	980	960	980	875
135°	1208	1196	1208	1196	1208	931
145°	1393	1380	1393	1380	1393	870
155°	1518	1520	1518	1520	1518	700
165°	1599	1603	1599	1603	1599	452
175°	1634	1640	1634	1640	1634	156
180°	1640	1640	1640	1640	1640	



TEST NUMBER: P332114-930

CATALOG NUMBER: S123DIW-S340D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	416.0	415.7	415.0	415.6	414.3	412.7	412.5	411.0	406.6	406.3	405.1
5°	465.7	464.2	464.0	463.8	461.1	457.5	450.7	450.1	441.0	436.5	431.0
7.5°	530.1	530.8	528.1	525.7	517.6	512.2	504.8	495.5	484.3	472.9	465.4
10°	576.3	582.5	574.8	569.4	564.5	555.2	544.4	530.8	517.4	501.7	489.7
12.5°	625.8	628.8	627.3	622.3	614.7	600.5	581.3	566.4	554.0	527.7	517.1
15°	693.2	704.8	697.4	680.4	680.7	667.2	642.2	614.7	600.0	577.0	545.7
17.5°	765.2	766.5	763.4	749.2	739.7	721.1	698.0	671.6	642.0	614.2	580.9
20°	803.4	802.3	795.7	788.2	771.9	757.5	732.2	702.8	664.8	637.4	601.1
22.5°	824.7	822.8	819.6	813.4	799.9	784.4	761.7	729.5	693.3	655.7	613.8
25°	822.8	825.2	825.7	823.9	819.2	809.9	792.1	766.4	730.3	681.8	638.2
27.5°	748.4	751.9	762.0	771.0	781.1	791.3	789.9	777.2	750.5	708.7	655.3
30°	673.9	666.3	685.1	708.8	725.0	753.5	769.4	770.4	755.4	719.5	667.4
32.5°	570.5	578.9	587.3	616.4	651.8	683.7	715.5	741.0	744.0	720.1	674.6
35°	443.3	453.8	469.0	484.1	522.1	554.8	610.7	659.3	698.0	703.1	675.2
37.5°	357.3	362.4	372.0	387.3	412.1	450.9	494.0	555.5	611.6	653.4	655.2
40°	312.3	313.8	324.6	336.1	356.3	388.2	427.1	481.5	548.7	607.1	631.4
42.5°	278.5	281.8	286.5	297.6	313.6	337.6	373.8	418.7	480.4	547.5	595.0
45°	239.3	243.1	246.0	253.4	264.8	281.0	306.1	347.2	394.1	463.4	527.4
47.5°	213.4	213.7	215.8	221.4	229.2	241.3	259.2	285.5	328.6	384.8	450.5
50°	194.9	197.9	198.7	203.0	209.1	218.0	232.8	255.3	290.6	340.0	400.4
52.5°	181.8	182.7	184.8	188.0	193.3	200.2	213.1	230.6	258.4	300.5	356.0
55°	162.6	162.6	164.7	167.1	170.2	176.4	185.0	197.9	219.0	251.7	297.7
57.5°	144.8	145.8	147.2	148.0	150.6	154.7	161.8	171.7	187.4	212.5	249.1
60°	133.0	134.7	134.4	136.0	138.3	141.5	147.6	155.6	169.6	189.7	220.5
62.5°	122.6	122.5	122.5	124.3	126.5	129.6	133.6	140.5	152.5	170.3	196.5
65°	105.6	105.3	106.6	107.7	108.4	110.7	113.7	119.8	127.8	141.1	161.4
67.5°	90.5	89.4	90.1	90.5	91.8	93.6	96.4	100.2	106.5	117.2	132.5
70°	80.1	79.2	79.0	79.4	80.6	81.9	84.0	87.6	93.4	102.0	113.2
72.5°	69.5	68.9	68.8	69.7	70.2	71.1	72.6	75.8	80.6	87.0	97.4
75°	54.3	54.3	54.3	54.5	55.1	55.8	57.0	58.7	62.3	66.9	73.9
77.5°	40.7	40.7	40.4	40.4	41.3	41.6	41.8	43.5	45.5	48.5	53.6
80°	31.9	31.0	31.3	31.9	32.3	32.4	33.0	33.4	35.1	36.9	40.4
82.5°	23.7	22.9	23.0	23.9	24.0	24.1	24.7	25.2	25.8	27.4	29.4
85°	12.6	12.6	12.7	12.7	12.9	12.7	13.3	13.5	13.5	14.4	15.6
87.5°	11.9	11.5	11.5	11.6	11.3	11.3	11.3	11.2	11.1	11.0	10.4
90°	36.5	36.0	35.5	35.0	34.4	33.6	32.5	31.4	30.3	29.3	25.8
92.5°	40.4	40.1	39.8	39.5	39.1	38.2	36.4	34.7	32.9	31.2	28.5
95°	46.3	46.3	46.3	46.3	46.3	45.3	43.5	41.6	39.7	37.7	34.8
97.5°	50.2	50.0	49.7	49.4	49.2	47.9	45.7	43.6	41.4	39.2	58.8
100°	51.2	51.0	50.6	50.4	50.1	48.9	46.7	44.5	42.4	40.2	82.5
102.5°	52.2	51.7	51.2	50.7	50.2	53.3	60.1	66.8	73.5	80.2	126.4
105°	53.6	53.1	52.6	52.0	51.4	75.2	123.1	171.0	219.0	266.9	291.3
107.5°	168.4	204.6	240.7	276.9	313.0	348.6	383.8	418.9	454.1	489.3	485.4
110°	335.2	373.9	412.6	451.3	490.1	514.0	522.9	531.8	540.8	549.7	546.7



TEST NUMBER: P332114-930

CATALOG NUMBER: S123DIW-S340D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	575.0	583.3	591.4	599.6	607.8	611.8	611.6	611.5	611.3	611.1	608.1
115°	716.7	715.6	714.5	713.5	712.3	710.5	707.8	705.1	702.3	699.6	697.2
117.5°	796.1	796.0	795.7	795.5	795.3	794.1	791.9	789.8	787.6	785.5	784.2
120°	850.8	850.8	850.8	850.8	850.8	849.7	847.5	845.4	843.2	841.0	840.2
122.5°	904.4	904.2	903.9	903.8	903.5	902.7	901.2	899.6	898.1	896.6	895.5
125°	980.0	979.4	978.8	978.4	977.8	977.2	976.7	976.2	975.7	975.1	974.0
127.5°	1052.6	1053.1	1053.7	1054.3	1054.8	1054.6	1053.8	1052.9	1052.0	1051.2	1049.9
130°	1099.4	1099.9	1100.5	1101.1	1101.6	1101.3	1100.2	1099.1	1098.0	1097.0	1095.9
132.5°	1142.3	1143.0	1143.9	1144.6	1145.3	1145.2	1144.1	1143.0	1141.9	1140.8	1140.0
135°	1207.9	1208.7	1209.5	1210.3	1211.1	1211.1	1210.3	1209.5	1208.7	1207.9	1206.8
137.5°	1269.6	1270.1	1270.6	1271.2	1271.7	1271.4	1270.1	1268.8	1267.5	1266.2	1265.6
140°	1306.6	1307.2	1307.7	1308.2	1308.8	1308.5	1307.4	1306.4	1305.3	1304.2	1303.3
142.5°	1340.8	1341.5	1342.2	1343.0	1343.8	1343.7	1342.9	1342.0	1341.1	1340.3	1339.5
145°	1393.2	1393.2	1393.2	1393.2	1393.2	1392.9	1392.4	1391.8	1391.2	1390.7	1390.2
147.5°	1432.2	1433.4	1434.7	1435.9	1437.1	1437.5	1437.0	1436.4	1435.9	1435.3	1434.8
150°	1461.4	1462.2	1463.1	1463.9	1464.7	1464.8	1464.3	1463.7	1463.1	1462.6	1462.1
152.5°	1484.8	1486.0	1487.3	1488.6	1489.8	1490.0	1489.0	1488.0	1487.0	1486.0	1485.7
155°	1517.5	1519.1	1520.7	1522.3	1524.0	1524.1	1522.7	1521.4	1520.0	1518.7	1518.4
157.5°	1545.0	1547.1	1549.2	1551.4	1553.5	1553.7	1552.1	1550.5	1548.8	1547.2	1547.5
160°	1562.6	1564.5	1566.4	1568.2	1570.2	1570.3	1568.6	1567.1	1565.5	1563.8	1564.1
162.5°	1579.2	1580.9	1582.5	1584.2	1585.8	1585.8	1584.0	1582.1	1580.3	1578.4	1578.7
165°	1599.1	1601.0	1603.0	1604.8	1606.7	1606.6	1604.4	1602.2	1600.1	1597.9	1598.2
167.5°	1613.6	1615.7	1617.9	1620.0	1622.2	1622.2	1620.0	1617.9	1615.7	1613.6	1613.6
170°	1622.3	1624.5	1626.6	1628.8	1631.0	1631.0	1628.8	1626.6	1624.5	1622.3	1622.3
172.5°	1627.2	1629.5	1632.0	1634.3	1636.7	1636.8	1634.7	1632.5	1630.4	1628.2	1627.9
175°	1634.5	1636.6	1638.8	1641.0	1643.2	1643.3	1641.4	1639.5	1637.6	1635.7	1635.4
177.5°	1636.7	1638.8	1641.0	1643.2	1645.4	1645.6	1643.8	1642.1	1640.4	1638.7	1638.4
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332114-930

CATALOG NUMBER: S123DIW-S340D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	404.1	403.0	401.8	399.7	397.8	395.3	394.4	393.5	390.8	388.4	386.5
5°	428.8	424.3	417.7	411.6	406.7	400.0	396.2	392.2	386.5	381.4	377.2
7.5°	454.7	445.7	435.4	424.3	413.8	403.8	395.7	388.5	380.5	373.0	367.0
10°	475.2	462.3	447.8	432.3	419.0	406.1	395.3	385.8	375.5	366.6	359.1
12.5°	498.6	479.5	459.6	440.7	424.9	407.0	393.9	381.8	370.1	359.5	351.1
15°	526.3	502.0	478.4	452.4	428.5	406.1	390.5	375.3	361.8	350.8	340.1
17.5°	551.5	524.0	492.9	461.3	432.4	405.9	384.1	366.9	350.0	336.6	326.0
20°	565.8	534.5	499.4	466.5	434.6	405.0	381.0	360.5	342.3	328.0	316.1
22.5°	578.1	541.4	505.1	469.9	434.4	402.5	375.4	354.2	334.5	320.6	307.9
25°	590.9	547.0	510.5	469.4	429.7	396.6	366.2	342.3	322.5	306.1	293.1
27.5°	601.9	546.7	503.4	459.0	422.1	389.0	356.5	330.8	309.9	292.1	278.8
30°	609.1	547.4	495.9	452.1	414.8	380.7	349.1	323.3	301.3	283.2	270.7
32.5°	613.7	546.9	489.1	442.3	403.2	373.0	341.0	314.3	291.6	273.9	261.9
35°	616.4	543.6	477.3	422.2	384.7	355.1	328.4	300.7	277.0	260.4	246.7
37.5°	611.0	536.5	463.7	402.8	361.7	332.7	310.1	286.6	263.8	245.6	233.8
40°	602.7	532.0	453.0	389.1	345.8	318.0	298.8	275.6	253.2	235.9	224.9
42.5°	586.7	522.8	441.3	374.0	329.5	301.6	283.9	264.5	243.3	227.1	216.1
45°	547.8	502.6	423.7	351.2	305.2	276.4	260.8	246.7	227.6	211.8	202.3
47.5°	493.7	472.2	398.4	327.2	279.9	252.2	235.9	224.7	210.7	197.9	188.8
50°	456.2	447.3	381.2	310.7	263.1	235.9	220.3	210.1	200.0	187.3	179.0
52.5°	412.9	418.4	361.2	293.8	245.9	219.2	204.6	196.4	187.3	176.8	169.5
55°	352.0	371.9	326.5	265.1	220.3	194.9	181.0	173.8	168.4	160.7	154.4
57.5°	294.9	320.2	289.0	235.7	195.2	173.3	160.0	152.1	148.7	144.6	139.7
60°	261.0	286.0	262.3	216.0	178.4	157.4	145.7	139.0	135.6	132.7	128.6
62.5°	230.7	256.1	236.2	195.9	161.8	142.4	132.2	125.6	123.0	121.6	118.0
65°	189.1	211.0	197.7	164.7	138.1	121.0	111.7	107.1	104.7	104.1	101.8
67.5°	153.9	170.6	160.9	136.6	115.7	100.9	93.0	89.1	87.2	87.0	85.3
70°	130.9	146.4	139.0	117.0	99.0	87.4	80.6	77.1	76.0	75.8	74.8
72.5°	112.9	123.8	117.9	99.5	85.6	75.1	70.0	66.4	65.2	65.5	64.8
75°	83.6	91.7	88.3	75.6	64.4	57.6	53.4	51.1	50.0	50.5	49.7
77.5°	60.2	65.3	62.2	53.4	46.5	41.6	38.5	37.1	36.0	36.0	35.7
80°	45.4	48.4	46.7	41.4	35.7	31.6	29.0	28.1	27.6	27.3	27.1
82.5°	32.4	34.9	32.9	29.3	25.4	22.8	21.4	20.2	19.8	19.9	19.7
85°	16.3	17.3	16.6	14.3	12.7	11.6	10.8	10.3	9.9	10.0	9.7
87.5°	10.0	9.5	8.3	7.1	6.3	5.3	4.7	3.9	4.2	4.6	5.1
90°	22.2	18.7	15.2	12.1	9.4	6.6	3.9	1.2	3.9	6.6	9.4
92.5°	25.9	23.2	20.5	19.6	20.4	21.1	21.9	22.7	21.9	21.1	20.4
95°	31.8	28.9	25.8	29.9	41.0	52.2	63.3	74.4	63.3	52.2	41.0
97.5°	78.3	97.8	117.2	129.5	134.4	139.5	144.5	149.4	144.5	139.5	134.4
100°	124.7	167.0	209.2	227.6	222.3	216.8	211.4	206.0	211.4	216.8	222.3
102.5°	172.5	218.7	264.8	285.9	282.0	278.2	274.3	270.4	274.3	278.2	282.0
105°	315.7	340.1	364.4	375.1	372.2	369.2	366.2	363.2	366.2	369.2	372.2
107.5°	481.6	477.7	473.9	470.8	468.4	465.9	463.6	461.2	463.6	465.9	468.4
110°	543.7	540.8	537.8	535.2	533.0	530.8	528.7	526.5	528.7	530.8	533.0



TEST NUMBER: P332114-930

CATALOG NUMBER: S123DIW-S340D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	605.2	602.2	599.2	596.7	594.8	592.9	590.9	589.0	590.9	592.9	594.8
115°	694.7	692.4	689.9	687.9	686.2	684.6	683.0	681.3	683.0	684.6	686.2
117.5°	782.9	781.7	780.5	778.9	776.8	774.8	772.8	770.8	772.8	774.8	776.8
120°	839.4	838.5	837.8	836.2	833.7	831.3	828.8	826.4	828.8	831.3	833.7
122.5°	894.5	893.5	892.5	891.0	888.9	887.0	884.9	883.0	884.9	887.0	888.9
125°	972.9	971.8	970.8	969.1	966.9	964.8	962.6	960.4	962.6	964.8	966.9
127.5°	1048.6	1047.3	1045.9	1044.2	1042.0	1039.9	1037.7	1035.5	1037.7	1039.9	1042.0
130°	1094.8	1093.7	1092.7	1091.0	1088.8	1086.7	1084.5	1082.3	1084.5	1086.7	1088.8
132.5°	1139.1	1138.2	1137.4	1135.9	1133.7	1131.6	1129.4	1127.2	1129.4	1131.6	1133.7
135°	1205.7	1204.6	1203.5	1202.2	1200.6	1199.0	1197.3	1195.7	1197.3	1199.0	1200.6
137.5°	1264.9	1264.4	1263.8	1262.4	1260.4	1258.3	1256.3	1254.2	1256.3	1258.3	1260.4
140°	1302.5	1301.7	1300.9	1299.8	1298.1	1296.5	1294.9	1293.2	1294.9	1296.5	1298.1
142.5°	1338.6	1337.8	1337.0	1335.8	1334.2	1332.5	1330.9	1329.3	1330.9	1332.5	1334.2
145°	1389.6	1389.1	1388.5	1387.3	1385.4	1383.6	1381.6	1379.7	1381.6	1383.6	1385.4
147.5°	1434.3	1433.7	1433.1	1432.2	1431.0	1429.8	1428.6	1427.3	1428.6	1429.8	1431.0
150°	1461.6	1461.0	1460.4	1459.8	1459.0	1458.2	1457.3	1456.5	1457.3	1458.2	1459.0
152.5°	1485.4	1485.1	1484.7	1484.4	1484.0	1483.6	1483.3	1482.9	1483.3	1483.6	1484.0
155°	1518.2	1517.9	1517.6	1517.8	1518.3	1518.8	1519.4	1519.9	1519.4	1518.8	1518.3
157.5°	1547.8	1548.0	1548.3	1548.5	1548.5	1548.6	1548.7	1548.7	1548.7	1548.6	1548.5
160°	1564.3	1564.6	1564.9	1565.1	1565.5	1565.7	1565.9	1566.3	1565.9	1565.7	1565.5
162.5°	1579.0	1579.2	1579.5	1580.0	1580.7	1581.4	1582.1	1582.8	1582.1	1581.4	1580.7
165°	1598.5	1598.7	1599.0	1599.5	1600.4	1601.2	1602.0	1602.8	1602.0	1601.2	1600.4
167.5°	1613.6	1613.6	1613.6	1614.0	1615.2	1616.2	1617.3	1618.4	1617.3	1616.2	1615.2
170°	1622.3	1622.3	1622.3	1622.9	1623.9	1625.0	1626.1	1627.2	1626.1	1625.0	1623.9
172.5°	1627.7	1627.5	1627.3	1627.8	1629.1	1630.4	1631.7	1633.0	1631.7	1630.4	1629.1
175°	1635.2	1634.9	1634.6	1635.2	1636.6	1637.9	1639.2	1640.5	1639.2	1637.9	1636.6
177.5°	1638.2	1638.0	1637.8	1638.2	1639.3	1640.4	1641.4	1642.5	1641.4	1640.4	1639.3
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332114-930

CATALOG NUMBER: S123DIW-S340D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	385.5	384.4	382.9	380.7	378.8	375.9	375.9	376.3	376.3	376.3	375.9
5°	373.8	371.0	367.5	363.5	359.4	355.1	354.4	352.9	351.8	351.0	350.1
7.5°	361.4	356.4	351.4	345.8	340.7	336.6	333.6	331.2	329.6	327.9	326.7
10°	353.1	346.8	341.0	335.1	328.6	323.4	320.2	318.0	316.3	314.7	314.0
12.5°	343.2	336.1	329.5	323.9	316.9	311.6	308.5	307.4	305.5	302.2	300.6
15°	328.8	322.1	314.4	305.8	302.4	296.0	292.3	290.6	289.4	287.0	286.3
17.5°	316.4	307.8	299.0	292.6	286.3	281.0	279.0	276.9	275.4	273.4	272.7
20°	306.6	298.8	290.8	284.0	277.3	271.6	269.9	268.4	266.8	266.0	265.1
22.5°	296.5	288.8	282.1	275.7	268.6	264.9	263.1	261.4	260.3	259.7	258.9
25°	282.4	275.6	268.2	262.5	256.8	254.3	253.2	252.3	251.4	250.5	250.3
27.5°	269.9	262.4	256.4	251.0	247.0	244.9	243.8	243.4	243.5	243.9	244.1
30°	260.4	253.6	248.7	244.1	240.3	238.4	238.1	238.1	239.0	239.1	239.5
32.5°	251.8	246.1	241.2	236.8	233.9	232.6	233.3	233.3	233.9	234.4	235.1
35°	239.1	234.2	230.4	226.6	224.1	224.7	225.1	225.4	226.4	227.6	228.3
37.5°	227.1	222.8	218.8	215.9	214.7	215.7	216.7	217.4	218.6	219.5	220.2
40°	218.4	215.2	211.4	208.7	209.1	209.7	210.4	211.4	212.4	213.0	213.7
42.5°	210.3	207.0	204.1	201.9	202.4	203.2	203.6	204.1	205.2	206.3	206.7
45°	198.1	195.4	192.8	191.4	191.8	192.2	192.6	193.1	194.1	194.9	195.1
47.5°	184.3	182.5	180.7	179.4	180.0	179.9	180.3	181.6	181.8	182.3	183.4
50°	175.5	173.8	171.7	171.3	171.3	171.3	171.5	173.0	173.0	173.8	174.6
52.5°	165.8	164.7	163.4	162.7	162.3	162.3	163.1	163.9	164.2	165.3	166.1
55°	151.4	150.3	149.1	148.5	148.1	148.5	150.0	150.4	151.4	152.0	152.5
57.5°	136.4	135.5	134.6	134.3	134.2	134.7	135.5	136.6	136.9	138.7	139.5
60°	126.5	125.1	124.4	124.4	124.0	125.7	125.4	127.3	127.7	128.8	130.1
62.5°	116.3	114.5	114.2	114.2	114.8	115.3	115.8	116.6	117.6	119.0	120.1
65°	99.9	99.0	100.3	100.1	99.7	100.9	100.9	101.8	103.0	104.3	106.4
67.5°	84.4	83.9	84.0	84.0	84.5	85.2	85.8	86.6	88.0	89.4	90.7
70°	73.9	74.4	73.5	74.3	74.8	75.0	75.4	76.6	78.0	79.0	80.6
72.5°	63.7	63.7	63.8	64.1	64.7	65.0	65.4	66.7	68.3	69.1	70.4
75°	49.0	48.8	49.4	49.4	50.3	50.7	51.1	51.7	53.2	54.3	55.3
77.5°	35.8	36.0	35.9	36.5	36.3	36.4	37.5	38.1	38.2	40.5	41.0
80°	27.0	27.3	27.6	27.7	27.9	27.6	28.9	29.4	29.4	30.7	31.7
82.5°	19.4	19.6	20.1	20.3	20.3	20.7	20.8	21.2	21.7	22.3	23.5
85°	9.7	10.3	10.4	10.3	10.4	10.0	10.6	10.8	11.0	11.0	11.0
87.5°	5.5	6.2	6.8	7.7	8.2	9.0	9.3	9.1	9.4	10.0	9.6
90°	12.1	15.2	18.7	22.2	25.8	29.3	30.3	31.4	32.5	33.6	34.4
92.5°	19.6	20.5	23.2	25.9	28.5	31.2	32.9	34.7	36.4	38.2	39.1
95°	29.9	25.8	28.9	31.8	34.8	37.7	39.7	41.6	43.5	45.3	46.3
97.5°	129.5	117.2	97.8	78.3	58.8	39.2	41.4	43.6	45.7	47.9	49.2
100°	227.6	209.2	167.0	124.7	82.5	40.2	42.4	44.5	46.7	48.9	50.1
102.5°	285.9	264.8	218.7	172.5	126.4	80.2	73.5	66.8	60.1	53.3	50.2
105°	375.1	364.4	340.1	315.7	291.3	266.9	219.0	171.0	123.1	75.2	51.4
107.5°	470.8	473.9	477.7	481.6	485.4	489.3	454.1	418.9	383.8	348.6	313.0
110°	535.2	537.8	540.8	543.7	546.7	549.7	540.8	531.8	522.9	514.0	490.1



TEST NUMBER: P332114-930

CATALOG NUMBER: S123DIW-S340D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	596.7	599.2	602.2	605.2	608.1	611.1	611.3	611.5	611.6	611.8	607.8
115°	687.9	689.9	692.4	694.7	697.2	699.6	702.3	705.1	707.8	710.5	712.3
117.5°	778.9	780.5	781.7	782.9	784.2	785.5	787.6	789.8	791.9	794.1	795.3
120°	836.2	837.8	838.5	839.4	840.2	841.0	843.2	845.4	847.5	849.7	850.8
122.5°	891.0	892.5	893.5	894.5	895.5	896.6	898.1	899.6	901.2	902.7	903.5
125°	969.1	970.8	971.8	972.9	974.0	975.1	975.7	976.2	976.7	977.2	977.8
127.5°	1044.2	1045.9	1047.3	1048.6	1049.9	1051.2	1052.0	1052.9	1053.8	1054.6	1054.8
130°	1091.0	1092.7	1093.7	1094.8	1095.9	1097.0	1098.0	1099.1	1100.2	1101.3	1101.6
132.5°	1135.9	1137.4	1138.2	1139.1	1140.0	1140.8	1141.9	1143.0	1144.1	1145.2	1145.3
135°	1202.2	1203.5	1204.6	1205.7	1206.8	1207.9	1208.7	1209.5	1210.3	1211.1	1211.1
137.5°	1262.4	1263.8	1264.4	1264.9	1265.6	1266.2	1267.5	1268.8	1270.1	1271.4	1271.7
140°	1299.8	1300.9	1301.7	1302.5	1303.3	1304.2	1305.3	1306.4	1307.4	1308.5	1308.8
142.5°	1335.8	1337.0	1337.8	1338.6	1339.5	1340.3	1341.1	1342.0	1342.9	1343.7	1343.8
145°	1387.3	1388.5	1389.1	1389.6	1390.2	1390.7	1391.2	1391.8	1392.4	1392.9	1393.2
147.5°	1432.2	1433.1	1433.7	1434.3	1434.8	1435.3	1435.9	1436.4	1437.0	1437.5	1437.1
150°	1459.8	1460.4	1461.0	1461.6	1462.1	1462.6	1463.1	1463.7	1464.3	1464.8	1464.7
152.5°	1484.4	1484.7	1485.1	1485.4	1485.7	1486.0	1487.0	1488.0	1489.0	1490.0	1489.8
155°	1517.8	1517.6	1517.9	1518.2	1518.4	1518.7	1520.0	1521.4	1522.7	1524.1	1524.0
157.5°	1548.5	1548.3	1548.0	1547.8	1547.5	1547.2	1548.8	1550.5	1552.1	1553.7	1553.5
160°	1565.1	1564.9	1564.6	1564.3	1564.1	1563.8	1565.5	1567.1	1568.6	1570.3	1570.2
162.5°	1580.0	1579.5	1579.2	1579.0	1578.7	1578.4	1580.3	1582.1	1584.0	1585.8	1585.8
165°	1599.5	1599.0	1598.7	1598.5	1598.2	1597.9	1600.1	1602.2	1604.4	1606.6	1606.7
167.5°	1614.0	1613.6	1613.6	1613.6	1613.6	1613.6	1615.7	1617.9	1620.0	1622.2	1622.2
170°	1622.9	1622.3	1622.3	1622.3	1622.3	1622.3	1624.5	1626.6	1628.8	1631.0	1631.0
172.5°	1627.8	1627.3	1627.5	1627.7	1627.9	1628.2	1630.4	1632.5	1634.7	1636.8	1636.7
175°	1635.2	1634.6	1634.9	1635.2	1635.4	1635.7	1637.6	1639.5	1641.4	1643.3	1643.2
177.5°	1638.2	1637.8	1638.0	1638.2	1638.4	1638.7	1640.4	1642.1	1643.8	1645.6	1645.4
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332114-930

CATALOG NUMBER: S123DIW-S340D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	374.9	374.7	375.8	375.0	375.8	374.7	374.9	375.9	376.3	376.3	376.3
5°	348.9	349.5	347.6	347.6	347.6	349.5	348.9	350.1	351.0	351.8	352.9
7.5°	325.8	325.0	325.1	324.0	325.1	325.0	325.8	326.7	327.9	329.6	331.2
10°	311.7	310.5	310.1	310.4	310.1	310.5	311.7	314.0	314.7	316.3	318.0
12.5°	299.9	299.8	297.3	297.3	297.3	299.8	299.9	300.6	302.2	305.5	307.4
15°	286.3	282.7	282.3	283.4	282.3	282.7	286.3	286.3	287.0	289.4	290.6
17.5°	272.5	270.5	270.7	270.1	270.7	270.5	272.5	272.7	273.4	275.4	276.9
20°	265.1	264.0	263.8	262.5	263.8	264.0	265.1	265.1	266.0	266.8	268.4
22.5°	258.4	258.1	258.2	256.7	258.2	258.1	258.4	258.9	259.7	260.3	261.4
25°	250.1	251.1	250.3	250.3	250.3	251.1	250.1	250.3	250.5	251.4	252.3
27.5°	244.5	244.5	244.1	244.1	244.1	244.5	244.5	244.1	243.9	243.5	243.4
30°	240.3	240.1	240.4	240.4	240.4	240.1	240.3	239.5	239.1	239.0	238.1
32.5°	236.0	236.3	236.4	236.5	236.4	236.3	236.0	235.1	234.4	233.9	233.3
35°	229.4	229.7	230.2	229.8	230.2	229.7	229.4	228.3	227.6	226.4	225.4
37.5°	220.5	221.4	221.3	221.5	221.3	221.4	220.5	220.2	219.5	218.6	217.4
40°	213.9	214.4	214.3	214.3	214.3	214.4	213.9	213.7	213.0	212.4	211.4
42.5°	207.0	207.4	206.9	206.7	206.9	207.4	207.0	206.7	206.3	205.2	204.1
45°	195.8	195.4	196.0	195.3	196.0	195.4	195.8	195.1	194.9	194.1	193.1
47.5°	183.3	183.7	183.8	184.4	183.8	183.7	183.3	183.4	182.3	181.8	181.6
50°	175.0	176.1	176.1	175.9	176.1	176.1	175.0	174.6	173.8	173.0	173.0
52.5°	166.7	167.2	168.0	168.0	168.0	167.2	166.7	166.1	165.3	164.2	163.9
55°	154.0	154.4	154.8	155.0	154.8	154.4	154.0	152.5	152.0	151.4	150.4
57.5°	140.9	140.7	141.6	141.9	141.6	140.7	140.9	139.5	138.7	136.9	136.6
60°	131.6	131.6	133.1	133.7	133.1	131.6	131.6	130.1	128.8	127.7	127.3
62.5°	121.7	122.4	123.8	123.1	123.8	122.4	121.7	120.1	119.0	117.6	116.6
65°	107.3	108.8	108.7	109.4	108.7	108.8	107.3	106.4	104.3	103.0	101.8
67.5°	92.2	93.2	94.6	94.7	94.6	93.2	92.2	90.7	89.4	88.0	86.6
70°	82.0	83.0	83.7	84.3	83.7	83.0	82.0	80.6	79.0	78.0	76.6
72.5°	72.2	72.6	74.5	73.7	74.5	72.6	72.2	70.4	69.1	68.3	66.7
75°	56.6	58.0	59.1	58.5	59.1	58.0	56.6	55.3	54.3	53.2	51.7
77.5°	41.8	43.2	43.7	43.2	43.7	43.2	41.8	41.0	40.5	38.2	38.1
80°	33.0	32.9	34.0	33.8	34.0	32.9	33.0	31.7	30.7	29.4	29.4
82.5°	24.2	24.1	24.5	24.7	24.5	24.1	24.2	23.5	22.3	21.7	21.2
85°	11.7	12.3	11.6	11.4	11.6	12.3	11.7	11.0	11.0	11.0	10.8
87.5°	9.7	9.9	9.8	9.8	9.8	9.9	9.7	9.6	10.0	9.4	9.1
90°	35.0	35.5	36.0	36.5	36.0	35.5	35.0	34.4	33.6	32.5	31.4
92.5°	39.5	39.8	40.1	40.4	40.1	39.8	39.5	39.1	38.2	36.4	34.7
95°	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3	45.3	43.5	41.6
97.5°	49.4	49.7	50.0	50.2	50.0	49.7	49.4	49.2	47.9	45.7	43.6
100°	50.4	50.6	51.0	51.2	51.0	50.6	50.4	50.1	48.9	46.7	44.5
102.5°	50.7	51.2	51.7	52.2	51.7	51.2	50.7	50.2	53.3	60.1	66.8
105°	52.0	52.6	53.1	53.6	53.1	52.6	52.0	51.4	75.2	123.1	171.0
107.5°	276.9	240.7	204.6	168.4	204.6	240.7	276.9	313.0	348.6	383.8	418.9
110°	451.3	412.6	373.9	335.2	373.9	412.6	451.3	490.1	514.0	522.9	531.8



TEST NUMBER: P332114-930

CATALOG NUMBER: S123DIW-S340D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	599.6	591.4	583.3	575.0	583.3	591.4	599.6	607.8	611.8	611.6	611.5
115°	713.5	714.5	715.6	716.7	715.6	714.5	713.5	712.3	710.5	707.8	705.1
117.5°	795.5	795.7	796.0	796.1	796.0	795.7	795.5	795.3	794.1	791.9	789.8
120°	850.8	850.8	850.8	850.8	850.8	850.8	850.8	850.8	849.7	847.5	845.4
122.5°	903.8	903.9	904.2	904.4	904.2	903.9	903.8	903.5	902.7	901.2	899.6
125°	978.4	978.8	979.4	980.0	979.4	978.8	978.4	977.8	977.2	976.7	976.2
127.5°	1054.3	1053.7	1053.1	1052.6	1053.1	1053.7	1054.3	1054.8	1054.6	1053.8	1052.9
130°	1101.1	1100.5	1099.9	1099.4	1099.9	1100.5	1101.1	1101.6	1101.3	1100.2	1099.1
132.5°	1144.6	1143.9	1143.0	1142.3	1143.0	1143.9	1144.6	1145.3	1145.2	1144.1	1143.0
135°	1210.3	1209.5	1208.7	1207.9	1208.7	1209.5	1210.3	1211.1	1211.1	1210.3	1209.5
137.5°	1271.2	1270.6	1270.1	1269.6	1270.1	1270.6	1271.2	1271.7	1271.4	1270.1	1268.8
140°	1308.2	1307.7	1307.2	1306.6	1307.2	1307.7	1308.2	1308.8	1308.5	1307.4	1306.4
142.5°	1343.0	1342.2	1341.5	1340.8	1341.5	1342.2	1343.0	1343.8	1343.7	1342.9	1342.0
145°	1393.2	1393.2	1393.2	1393.2	1393.2	1393.2	1393.2	1393.2	1392.9	1392.4	1391.8
147.5°	1435.9	1434.7	1433.4	1432.2	1433.4	1434.7	1435.9	1437.1	1437.5	1437.0	1436.4
150°	1463.9	1463.1	1462.2	1461.4	1462.2	1463.1	1463.9	1464.7	1464.8	1464.3	1463.7
152.5°	1488.6	1487.3	1486.0	1484.8	1486.0	1487.3	1488.6	1489.8	1490.0	1489.0	1488.0
155°	1522.3	1520.7	1519.1	1517.5	1519.1	1520.7	1522.3	1524.0	1524.1	1522.7	1521.4
157.5°	1551.4	1549.2	1547.1	1545.0	1547.1	1549.2	1551.4	1553.5	1553.7	1552.1	1550.5
160°	1568.2	1566.4	1564.5	1562.6	1564.5	1566.4	1568.2	1570.2	1570.3	1568.6	1567.1
162.5°	1584.2	1582.5	1580.9	1579.2	1580.9	1582.5	1584.2	1585.8	1585.8	1584.0	1582.1
165°	1604.8	1603.0	1601.0	1599.1	1601.0	1603.0	1604.8	1606.7	1606.6	1604.4	1602.2
167.5°	1620.0	1617.9	1615.7	1613.6	1615.7	1617.9	1620.0	1622.2	1622.2	1620.0	1617.9
170°	1628.8	1626.6	1624.5	1622.3	1624.5	1626.6	1628.8	1631.0	1631.0	1628.8	1626.6
172.5°	1634.3	1632.0	1629.5	1627.2	1629.5	1632.0	1634.3	1636.7	1636.8	1634.7	1632.5
175°	1641.0	1638.8	1636.6	1634.5	1636.6	1638.8	1641.0	1643.2	1643.3	1641.4	1639.5
177.5°	1643.2	1641.0	1638.8	1636.7	1638.8	1641.0	1643.2	1645.4	1645.6	1643.8	1642.1
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332114-930

CATALOG NUMBER: S123DIW-S340D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	375.9	375.9	378.8	380.7	382.9	384.4	385.5	386.5	388.4	390.8	393.5
5°	354.4	355.1	359.4	363.5	367.5	371.0	373.8	377.2	381.4	386.5	392.2
7.5°	333.6	336.6	340.7	345.8	351.4	356.4	361.4	367.0	373.0	380.5	388.5
10°	320.2	323.4	328.6	335.1	341.0	346.8	353.1	359.1	366.6	375.5	385.8
12.5°	308.5	311.6	316.9	323.9	329.5	336.1	343.2	351.1	359.5	370.1	381.8
15°	292.3	296.0	302.4	305.8	314.4	322.1	328.8	340.1	350.8	361.8	375.3
17.5°	279.0	281.0	286.3	292.6	299.0	307.8	316.4	326.0	336.6	350.0	366.9
20°	269.9	271.6	277.3	284.0	290.8	298.8	306.6	316.1	328.0	342.3	360.5
22.5°	263.1	264.9	268.6	275.7	282.1	288.8	296.5	307.9	320.6	334.5	354.2
25°	253.2	254.3	256.8	262.5	268.2	275.6	282.4	293.1	306.1	322.5	342.3
27.5°	243.8	244.9	247.0	251.0	256.4	262.4	269.9	278.8	292.1	309.9	330.8
30°	238.1	238.4	240.3	244.1	248.7	253.6	260.4	270.7	283.2	301.3	323.3
32.5°	233.3	232.6	233.9	236.8	241.2	246.1	251.8	261.9	273.9	291.6	314.3
35°	225.1	224.7	224.1	226.6	230.4	234.2	239.1	246.7	260.4	277.0	300.7
37.5°	216.7	215.7	214.7	215.9	218.8	222.8	227.1	233.8	245.6	263.8	286.6
40°	210.4	209.7	209.1	208.7	211.4	215.2	218.4	224.9	235.9	253.2	275.6
42.5°	203.6	203.2	202.4	201.9	204.1	207.0	210.3	216.1	227.1	243.3	264.5
45°	192.6	192.2	191.8	191.4	192.8	195.4	198.1	202.3	211.8	227.6	246.7
47.5°	180.3	179.9	180.0	179.4	180.7	182.5	184.3	188.8	197.9	210.7	224.7
50°	171.5	171.3	171.3	171.3	171.7	173.8	175.5	179.0	187.3	200.0	210.1
52.5°	163.1	162.3	162.3	162.7	163.4	164.7	165.8	169.5	176.8	187.3	196.4
55°	150.0	148.5	148.1	148.5	149.1	150.3	151.4	154.4	160.7	168.4	173.8
57.5°	135.5	134.7	134.2	134.3	134.6	135.5	136.4	139.7	144.6	148.7	152.1
60°	125.4	125.7	124.0	124.4	124.4	125.1	126.5	128.6	132.7	135.6	139.0
62.5°	115.8	115.3	114.8	114.2	114.2	114.5	116.3	118.0	121.6	123.0	125.6
65°	100.9	100.9	99.7	100.1	100.3	99.0	99.9	101.8	104.1	104.7	107.1
67.5°	85.8	85.2	84.5	84.0	84.0	83.9	84.4	85.3	87.0	87.2	89.1
70°	75.4	75.0	74.8	74.3	73.5	74.4	73.9	74.8	75.8	76.0	77.1
72.5°	65.4	65.0	64.7	64.1	63.8	63.7	63.7	64.8	65.5	65.2	66.4
75°	51.1	50.7	50.3	49.4	49.4	48.8	49.0	49.7	50.5	50.0	51.1
77.5°	37.5	36.4	36.3	36.5	35.9	36.0	35.8	35.7	36.0	36.0	37.1
80°	28.9	27.6	27.9	27.7	27.6	27.3	27.0	27.1	27.3	27.6	28.1
82.5°	20.8	20.7	20.3	20.3	20.1	19.6	19.4	19.7	19.9	19.8	20.2
85°	10.6	10.0	10.4	10.3	10.4	10.3	9.7	9.7	10.0	9.9	10.3
87.5°	9.3	9.0	8.2	7.7	6.8	6.2	5.5	5.1	4.6	4.2	3.9
90°	30.3	29.3	25.8	22.2	18.7	15.2	12.1	9.4	6.6	3.9	1.2
92.5°	32.9	31.2	28.5	25.9	23.2	20.5	19.6	20.4	21.1	21.9	22.7
95°	39.7	37.7	34.8	31.8	28.9	25.8	29.9	41.0	52.2	63.3	74.4
97.5°	41.4	39.2	58.8	78.3	97.8	117.2	129.5	134.4	139.5	144.5	149.4
100°	42.4	40.2	82.5	124.7	167.0	209.2	227.6	222.3	216.8	211.4	206.0
102.5°	73.5	80.2	126.4	172.5	218.7	264.8	285.9	282.0	278.2	274.3	270.4
105°	219.0	266.9	291.3	315.7	340.1	364.4	375.1	372.2	369.2	366.2	363.2
107.5°	454.1	489.3	485.4	481.6	477.7	473.9	470.8	468.4	465.9	463.6	461.2
110°	540.8	549.7	546.7	543.7	540.8	537.8	535.2	533.0	530.8	528.7	526.5



TEST NUMBER: P332114-930

CATALOG NUMBER: S123DIW-S340D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	611.3	611.1	608.1	605.2	602.2	599.2	596.7	594.8	592.9	590.9	589.0
115°	702.3	699.6	697.2	694.7	692.4	689.9	687.9	686.2	684.6	683.0	681.3
117.5°	787.6	785.5	784.2	782.9	781.7	780.5	778.9	776.8	774.8	772.8	770.8
120°	843.2	841.0	840.2	839.4	838.5	837.8	836.2	833.7	831.3	828.8	826.4
122.5°	898.1	896.6	895.5	894.5	893.5	892.5	891.0	888.9	887.0	884.9	883.0
125°	975.7	975.1	974.0	972.9	971.8	970.8	969.1	966.9	964.8	962.6	960.4
127.5°	1052.0	1051.2	1049.9	1048.6	1047.3	1045.9	1044.2	1042.0	1039.9	1037.7	1035.5
130°	1098.0	1097.0	1095.9	1094.8	1093.7	1092.7	1091.0	1088.8	1086.7	1084.5	1082.3
132.5°	1141.9	1140.8	1140.0	1139.1	1138.2	1137.4	1135.9	1133.7	1131.6	1129.4	1127.2
135°	1208.7	1207.9	1206.8	1205.7	1204.6	1203.5	1202.2	1200.6	1199.0	1197.3	1195.7
137.5°	1267.5	1266.2	1265.6	1264.9	1264.4	1263.8	1262.4	1260.4	1258.3	1256.3	1254.2
140°	1305.3	1304.2	1303.3	1302.5	1301.7	1300.9	1299.8	1298.1	1296.5	1294.9	1293.2
142.5°	1341.1	1340.3	1339.5	1338.6	1337.8	1337.0	1335.8	1334.2	1332.5	1330.9	1329.3
145°	1391.2	1390.7	1390.2	1389.6	1389.1	1388.5	1387.3	1385.4	1383.6	1381.6	1379.7
147.5°	1435.9	1435.3	1434.8	1434.3	1433.7	1433.1	1432.2	1431.0	1429.8	1428.6	1427.3
150°	1463.1	1462.6	1462.1	1461.6	1461.0	1460.4	1459.8	1459.0	1458.2	1457.3	1456.5
152.5°	1487.0	1486.0	1485.7	1485.4	1485.1	1484.7	1484.4	1484.0	1483.6	1483.3	1482.9
155°	1520.0	1518.7	1518.4	1518.2	1517.9	1517.6	1517.8	1518.3	1518.8	1519.4	1519.9
157.5°	1548.8	1547.2	1547.5	1547.8	1548.0	1548.3	1548.5	1548.5	1548.6	1548.7	1548.7
160°	1565.5	1563.8	1564.1	1564.3	1564.6	1564.9	1565.1	1565.5	1565.7	1565.9	1566.3
162.5°	1580.3	1578.4	1578.7	1579.0	1579.2	1579.5	1580.0	1580.7	1581.4	1582.1	1582.8
165°	1600.1	1597.9	1598.2	1598.5	1598.7	1599.0	1599.5	1600.4	1601.2	1602.0	1602.8
167.5°	1615.7	1613.6	1613.6	1613.6	1613.6	1613.6	1614.0	1615.2	1616.2	1617.3	1618.4
170°	1624.5	1622.3	1622.3	1622.3	1622.3	1622.3	1622.9	1623.9	1625.0	1626.1	1627.2
172.5°	1630.4	1628.2	1627.9	1627.7	1627.5	1627.3	1627.8	1629.1	1630.4	1631.7	1633.0
175°	1637.6	1635.7	1635.4	1635.2	1634.9	1634.6	1635.2	1636.6	1637.9	1639.2	1640.5
177.5°	1640.4	1638.7	1638.4	1638.2	1638.0	1637.8	1638.2	1639.3	1640.4	1641.4	1642.5
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332114-930

CATALOG NUMBER: S123DIW-S340D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	394.4	395.3	397.8	399.7	401.8	403.0	404.1	405.1	406.3	406.6	411.0
5°	396.2	400.0	406.7	411.6	417.7	424.3	428.8	431.0	436.5	441.0	450.1
7.5°	395.7	403.8	413.8	424.3	435.4	445.7	454.7	465.4	472.9	484.3	495.5
10°	395.3	406.1	419.0	432.3	447.8	462.3	475.2	489.7	501.7	517.4	530.8
12.5°	393.9	407.0	424.9	440.7	459.6	479.5	498.6	517.1	527.7	554.0	566.4
15°	390.5	406.1	428.5	452.4	478.4	502.0	526.3	545.7	577.0	600.0	614.7
17.5°	384.1	405.9	432.4	461.3	492.9	524.0	551.5	580.9	614.2	642.0	671.6
20°	381.0	405.0	434.6	466.5	499.4	534.5	565.8	601.1	637.4	664.8	702.8
22.5°	375.4	402.5	434.4	469.9	505.1	541.4	578.1	613.8	655.7	693.3	729.5
25°	366.2	396.6	429.7	469.4	510.5	547.0	590.9	638.2	681.8	730.3	766.4
27.5°	356.5	389.0	422.1	459.0	503.4	546.7	601.9	655.3	708.7	750.5	777.2
30°	349.1	380.7	414.8	452.1	495.9	547.4	609.1	667.4	719.5	755.4	770.4
32.5°	341.0	373.0	403.2	442.3	489.1	546.9	613.7	674.6	720.1	744.0	741.0
35°	328.4	355.1	384.7	422.2	477.3	543.6	616.4	675.2	703.1	698.0	659.3
37.5°	310.1	332.7	361.7	402.8	463.7	536.5	611.0	655.2	653.4	611.6	555.5
40°	298.8	318.0	345.8	389.1	453.0	532.0	602.7	631.4	607.1	548.7	481.5
42.5°	283.9	301.6	329.5	374.0	441.3	522.8	586.7	595.0	547.5	480.4	418.7
45°	260.8	276.4	305.2	351.2	423.7	502.6	547.8	527.4	463.4	394.1	347.2
47.5°	235.9	252.2	279.9	327.2	398.4	472.2	493.7	450.5	384.8	328.6	285.5
50°	220.3	235.9	263.1	310.7	381.2	447.3	456.2	400.4	340.0	290.6	255.3
52.5°	204.6	219.2	245.9	293.8	361.2	418.4	412.9	356.0	300.5	258.4	230.6
55°	181.0	194.9	220.3	265.1	326.5	371.9	352.0	297.7	251.7	219.0	197.9
57.5°	160.0	173.3	195.2	235.7	289.0	320.2	294.9	249.1	212.5	187.4	171.7
60°	145.7	157.4	178.4	216.0	262.3	286.0	261.0	220.5	189.7	169.6	155.6
62.5°	132.2	142.4	161.8	195.9	236.2	256.1	230.7	196.5	170.3	152.5	140.5
65°	111.7	121.0	138.1	164.7	197.7	211.0	189.1	161.4	141.1	127.8	119.8
67.5°	93.0	100.9	115.7	136.6	160.9	170.6	153.9	132.5	117.2	106.5	100.2
70°	80.6	87.4	99.0	117.0	139.0	146.4	130.9	113.2	102.0	93.4	87.6
72.5°	70.0	75.1	85.6	99.5	117.9	123.8	112.9	97.4	87.0	80.6	75.8
75°	53.4	57.6	64.4	75.6	88.3	91.7	83.6	73.9	66.9	62.3	58.7
77.5°	38.5	41.6	46.5	53.4	62.2	65.3	60.2	53.6	48.5	45.5	43.5
80°	29.0	31.6	35.7	41.4	46.7	48.4	45.4	40.4	36.9	35.1	33.4
82.5°	21.4	22.8	25.4	29.3	32.9	34.9	32.4	29.4	27.4	25.8	25.2
85°	10.8	11.6	12.7	14.3	16.6	17.3	16.3	15.6	14.4	13.5	13.5
87.5°	4.7	5.3	6.3	7.1	8.3	9.5	10.0	10.4	11.0	11.1	11.2
90°	3.9	6.6	9.4	12.1	15.2	18.7	22.2	25.8	29.3	30.3	31.4
92.5°	21.9	21.1	20.4	19.6	20.5	23.2	25.9	28.5	31.2	32.9	34.7
95°	63.3	52.2	41.0	29.9	25.8	28.9	31.8	34.8	37.7	39.7	41.6
97.5°	144.5	139.5	134.4	129.5	117.2	97.8	78.3	58.8	39.2	41.4	43.6
100°	211.4	216.8	222.3	227.6	209.2	167.0	124.7	82.5	40.2	42.4	44.5
102.5°	274.3	278.2	282.0	285.9	264.8	218.7	172.5	126.4	80.2	73.5	66.8
105°	366.2	369.2	372.2	375.1	364.4	340.1	315.7	291.3	266.9	219.0	171.0
107.5°	463.6	465.9	468.4	470.8	473.9	477.7	481.6	485.4	489.3	454.1	418.9
110°	528.7	530.8	533.0	535.2	537.8	540.8	543.7	546.7	549.7	540.8	531.8



TEST NUMBER: P332114-930

CATALOG NUMBER: S123DIW-S340D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	590.9	592.9	594.8	596.7	599.2	602.2	605.2	608.1	611.1	611.3	611.5
115°	683.0	684.6	686.2	687.9	689.9	692.4	694.7	697.2	699.6	702.3	705.1
117.5°	772.8	774.8	776.8	778.9	780.5	781.7	782.9	784.2	785.5	787.6	789.8
120°	828.8	831.3	833.7	836.2	837.8	838.5	839.4	840.2	841.0	843.2	845.4
122.5°	884.9	887.0	888.9	891.0	892.5	893.5	894.5	895.5	896.6	898.1	899.6
125°	962.6	964.8	966.9	969.1	970.8	971.8	972.9	974.0	975.1	975.7	976.2
127.5°	1037.7	1039.9	1042.0	1044.2	1045.9	1047.3	1048.6	1049.9	1051.2	1052.0	1052.9
130°	1084.5	1086.7	1088.8	1091.0	1092.7	1093.7	1094.8	1095.9	1097.0	1098.0	1099.1
132.5°	1129.4	1131.6	1133.7	1135.9	1137.4	1138.2	1139.1	1140.0	1140.8	1141.9	1143.0
135°	1197.3	1199.0	1200.6	1202.2	1203.5	1204.6	1205.7	1206.8	1207.9	1208.7	1209.5
137.5°	1256.3	1258.3	1260.4	1262.4	1263.8	1264.4	1264.9	1265.6	1266.2	1267.5	1268.8
140°	1294.9	1296.5	1298.1	1299.8	1300.9	1301.7	1302.5	1303.3	1304.2	1305.3	1306.4
142.5°	1330.9	1332.5	1334.2	1335.8	1337.0	1337.8	1338.6	1339.5	1340.3	1341.1	1342.0
145°	1381.6	1383.6	1385.4	1387.3	1388.5	1389.1	1389.6	1390.2	1390.7	1391.2	1391.8
147.5°	1428.6	1429.8	1431.0	1432.2	1433.1	1433.7	1434.3	1434.8	1435.3	1435.9	1436.4
150°	1457.3	1458.2	1459.0	1459.8	1460.4	1461.0	1461.6	1462.1	1462.6	1463.1	1463.7
152.5°	1483.3	1483.6	1484.0	1484.4	1484.7	1485.1	1485.4	1485.7	1486.0	1487.0	1488.0
155°	1519.4	1518.8	1518.3	1517.8	1517.6	1517.9	1518.2	1518.4	1518.7	1520.0	1521.4
157.5°	1548.7	1548.6	1548.5	1548.5	1548.3	1548.0	1547.8	1547.5	1547.2	1548.8	1550.5
160°	1565.9	1565.7	1565.5	1565.1	1564.9	1564.6	1564.3	1564.1	1563.8	1565.5	1567.1
162.5°	1582.1	1581.4	1580.7	1580.0	1579.5	1579.2	1579.0	1578.7	1578.4	1580.3	1582.1
165°	1602.0	1601.2	1600.4	1599.5	1599.0	1598.7	1598.5	1598.2	1597.9	1600.1	1602.2
167.5°	1617.3	1616.2	1615.2	1614.0	1613.6	1613.6	1613.6	1613.6	1613.6	1615.7	1617.9
170°	1626.1	1625.0	1623.9	1622.9	1622.3	1622.3	1622.3	1622.3	1622.3	1624.5	1626.6
172.5°	1631.7	1630.4	1629.1	1627.8	1627.3	1627.5	1627.7	1627.9	1628.2	1630.4	1632.5
175°	1639.2	1637.9	1636.6	1635.2	1634.6	1634.9	1635.2	1635.4	1635.7	1637.6	1639.5
177.5°	1641.4	1640.4	1639.3	1638.2	1637.8	1638.0	1638.2	1638.4	1638.7	1640.4	1642.1
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332114-930

CATALOG NUMBER: S123DIW-S340D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	412.5	412.7	414.3	415.6	415.0	415.7	416.0
5°	450.7	457.5	461.1	463.8	464.0	464.2	465.7
7.5°	504.8	512.2	517.6	525.7	528.1	530.8	530.1
10°	544.4	555.2	564.5	569.4	574.8	582.5	576.3
12.5°	581.3	600.5	614.7	622.3	627.3	628.8	625.8
15°	642.2	667.2	680.7	680.4	697.4	704.8	693.2
17.5°	698.0	721.1	739.7	749.2	763.4	766.5	765.2
20°	732.2	757.5	771.9	788.2	795.7	802.3	803.4
22.5°	761.7	784.4	799.9	813.4	819.6	822.8	824.7
25°	792.1	809.9	819.2	823.9	825.7	825.2	822.8
27.5°	789.9	791.3	781.1	771.0	762.0	751.9	748.4
30°	769.4	753.5	725.0	708.8	685.1	666.3	673.9
32.5°	715.5	683.7	651.8	616.4	587.3	578.9	570.5
35°	610.7	554.8	522.1	484.1	469.0	453.8	443.3
37.5°	494.0	450.9	412.1	387.3	372.0	362.4	357.3
40°	427.1	388.2	356.3	336.1	324.6	313.8	312.3
42.5°	373.8	337.6	313.6	297.6	286.5	281.8	278.5
45°	306.1	281.0	264.8	253.4	246.0	243.1	239.3
47.5°	259.2	241.3	229.2	221.4	215.8	213.7	213.4
50°	232.8	218.0	209.1	203.0	198.7	197.9	194.9
52.5°	213.1	200.2	193.3	188.0	184.8	182.7	181.8
55°	185.0	176.4	170.2	167.1	164.7	162.6	162.6
57.5°	161.8	154.7	150.6	148.0	147.2	145.8	144.8
60°	147.6	141.5	138.3	136.0	134.4	134.7	133.0
62.5°	133.6	129.6	126.5	124.3	122.5	122.5	122.6
65°	113.7	110.7	108.4	107.7	106.6	105.3	105.6
67.5°	96.4	93.6	91.8	90.5	90.1	89.4	90.5
70°	84.0	81.9	80.6	79.4	79.0	79.2	80.1
72.5°	72.6	71.1	70.2	69.7	68.8	68.9	69.5
75°	57.0	55.8	55.1	54.5	54.3	54.3	54.3
77.5°	41.8	41.6	41.3	40.4	40.4	40.7	40.7
80°	33.0	32.4	32.3	31.9	31.3	31.0	31.9
82.5°	24.7	24.1	24.0	23.9	23.0	22.9	23.7
85°	13.3	12.7	12.9	12.7	12.7	12.6	12.6
87.5°	11.3	11.3	11.3	11.6	11.5	11.5	11.9
90°	32.5	33.6	34.4	35.0	35.5	36.0	36.5
92.5°	36.4	38.2	39.1	39.5	39.8	40.1	40.4
95°	43.5	45.3	46.3	46.3	46.3	46.3	46.3
97.5°	45.7	47.9	49.2	49.4	49.7	50.0	50.2
100°	46.7	48.9	50.1	50.4	50.6	51.0	51.2
102.5°	60.1	53.3	50.2	50.7	51.2	51.7	52.2
105°	123.1	75.2	51.4	52.0	52.6	53.1	53.6
107.5°	383.8	348.6	313.0	276.9	240.7	204.6	168.4
110°	522.9	514.0	490.1	451.3	412.6	373.9	335.2



TEST NUMBER: P332114-930

CATALOG NUMBER: S123DIW-S340D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	611.6	611.8	607.8	599.6	591.4	583.3	575.0
115°	707.8	710.5	712.3	713.5	714.5	715.6	716.7
117.5°	791.9	794.1	795.3	795.5	795.7	796.0	796.1
120°	847.5	849.7	850.8	850.8	850.8	850.8	850.8
122.5°	901.2	902.7	903.5	903.8	903.9	904.2	904.4
125°	976.7	977.2	977.8	978.4	978.8	979.4	980.0
127.5°	1053.8	1054.6	1054.8	1054.3	1053.7	1053.1	1052.6
130°	1100.2	1101.3	1101.6	1101.1	1100.5	1099.9	1099.4
132.5°	1144.1	1145.2	1145.3	1144.6	1143.9	1143.0	1142.3
135°	1210.3	1211.1	1211.1	1210.3	1209.5	1208.7	1207.9
137.5°	1270.1	1271.4	1271.7	1271.2	1270.6	1270.1	1269.6
140°	1307.4	1308.5	1308.8	1308.2	1307.7	1307.2	1306.6
142.5°	1342.9	1343.7	1343.8	1343.0	1342.2	1341.5	1340.8
145°	1392.4	1392.9	1393.2	1393.2	1393.2	1393.2	1393.2
147.5°	1437.0	1437.5	1437.1	1435.9	1434.7	1433.4	1432.2
150°	1464.3	1464.8	1464.7	1463.9	1463.1	1462.2	1461.4
152.5°	1489.0	1490.0	1489.8	1488.6	1487.3	1486.0	1484.8
155°	1522.7	1524.1	1524.0	1522.3	1520.7	1519.1	1517.5
157.5°	1552.1	1553.7	1553.5	1551.4	1549.2	1547.1	1545.0
160°	1568.6	1570.3	1570.2	1568.2	1566.4	1564.5	1562.6
162.5°	1584.0	1585.8	1585.8	1584.2	1582.5	1580.9	1579.2
165°	1604.4	1606.6	1606.7	1604.8	1603.0	1601.0	1599.1
167.5°	1620.0	1622.2	1622.2	1620.0	1617.9	1615.7	1613.6
170°	1628.8	1631.0	1631.0	1628.8	1626.6	1624.5	1622.3
172.5°	1634.7	1636.8	1636.7	1634.3	1632.0	1629.5	1627.2
175°	1641.4	1643.3	1643.2	1641.0	1638.8	1636.6	1634.5
177.5°	1643.8	1645.6	1645.4	1643.2	1641.0	1638.8	1636.7
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5

(END OF REPORT)