

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332094-930

Luminaire Tested: **S123DIW-S340D460U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332094-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D460U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2654.5 lumens
Efficiency: N/A
Efficacy: 115.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332094-930

CATALOG NUMBER: S123DIW-S340D460U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332094-930

CATALOG NUMBER: S123DIW-S340D460U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43				
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36				
2	88	80	74	69	80	74	68	64	61	57	54	49	47	44	39	37	35	30				
3	80	70	63	57	73	65	58	53	54	49	45	44	40	38	34	32	30	26				
4	73	62	54	48	66	57	50	45	48	43	39	39	35	32	31	28	26	22				
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23	19				
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17				
7	57	45	37	31	52	41	34	29	35	29	25	29	25	21	23	20	18	15				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4755	4755	4755
5°	4778	4712	4744
10°	4746	4671	4701
15°	4690	4619	4627
20°	4625	4543	4548
25°	4538	4454	4444
30°	4443	4354	4320
35°	4343	4248	4193
40°	4239	4131	4068
45°	4122	4025	3927
50°	4007	3893	3785
55°	3856	3757	3643
60°	3705	3597	3483
65°	3568	3423	3319
70°	3371	3229	3084
75°	3082	2969	2845
80°	2777	2665	2641
85°	2433	2347	2260



TEST NUMBER: P332094-930

CATALOG NUMBER: S123DIW-S340D460U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.6	1.6
10°-20°	117.5	4.4
20°-30°	173.6	6.5
30°-40°	202.8	7.6
40°-50°	203.9	7.7
50°-60°	179.1	6.7
60°-70°	133.4	5.0
70°-80°	76.0	2.9
80°-90°	23.2	0.9
90°-100°	17.9	0.7
100°-110°	85.4	3.2
110°-120°	205.2	7.7
120°-130°	261.3	9.8
130°-140°	279.2	10.5
140°-150°	261.1	9.8
150°-160°	210.6	7.9
160°-170°	135.9	5.1
170°-180°	46.8	1.8
0°-30°	332.7	12.5
0°-40°	535.5	20.2
0°-60°	918.4	34.6
0°-90°	1151.0	43.4
90°-120°	308.6	11.6
90°-150°	1110.2	41.8
90°-180°	1504.0	56.7
0°-180°	2654.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	442	442	442	442	442	
5°	442	440	436	440	439	42
15°	421	419	414	417	415	119
25°	382	380	375	375	374	176
35°	330	328	323	321	319	207
45°	271	269	264	260	258	209
55°	206	205	200	196	194	184
65°	140	138	134	132	130	138
75°	74	73	71	70	68	79
85°	20	19	19	18	18	22
90°	0	4	9	10	11	2
95°	22	8	11	14	14	28
105°	109	111	80	19	16	116
115°	205	207	210	214	215	202
125°	289	291	293	294	294	258
135°	359	362	363	364	363	277
145°	415	417	418	419	419	259
155°	457	456	456	458	456	210
165°	482	481	480	483	481	136
175°	493	491	492	494	491	47
180°	493	493	493	493	493	



TEST NUMBER: P332094-930

CATALOG NUMBER: S123DIW-S340D460U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	443.4	443.0	442.8	442.5	442.2	441.7	441.0	440.3	439.5	438.8	439.4
5°	442.2	441.7	441.3	440.9	440.5	439.9	438.9	438.0	437.0	436.1	436.9
7.5°	437.9	437.4	437.0	436.6	436.2	435.5	434.6	433.6	432.6	431.6	432.4
10°	434.2	433.8	433.3	432.9	432.5	431.8	430.6	429.6	428.4	427.4	428.1
12.5°	429.3	429.0	428.6	428.3	428.0	427.2	426.2	425.2	424.1	423.1	423.7
15°	420.9	420.6	420.2	419.9	419.6	418.8	417.8	416.6	415.6	414.5	415.2
17.5°	411.1	410.7	410.3	409.8	409.4	408.6	407.5	406.4	405.3	404.2	404.6
20°	403.8	403.3	402.8	402.3	401.8	401.0	399.9	398.8	397.7	396.6	397.0
22.5°	395.6	395.1	394.6	394.1	393.6	392.8	391.7	390.6	389.5	388.4	388.7
25°	382.1	381.6	381.2	380.7	380.2	379.4	378.2	377.2	376.0	375.0	375.0
27.5°	367.8	367.3	366.8	366.3	365.8	365.0	363.9	362.6	361.5	360.3	360.4
30°	357.5	357.0	356.6	356.2	355.8	355.0	353.8	352.6	351.5	350.3	350.3
32.5°	347.2	346.6	346.0	345.4	345.0	344.1	343.2	342.3	341.4	340.6	340.1
35°	330.5	330.0	329.5	329.0	328.5	327.7	326.6	325.5	324.4	323.3	322.8
37.5°	313.5	312.8	312.2	311.5	311.0	310.1	308.9	307.8	306.7	305.6	305.0
40°	301.7	301.1	300.6	300.1	299.6	298.7	297.6	296.4	295.2	294.0	293.3
42.5°	289.8	289.2	288.6	288.0	287.5	286.6	285.4	284.2	283.1	281.8	281.2
45°	270.8	270.5	270.2	269.9	269.5	268.8	267.7	266.6	265.5	264.4	263.4
47.5°	252.1	251.6	251.1	250.6	250.1	249.4	248.3	247.3	246.3	245.2	244.3
50°	239.3	238.9	238.5	238.1	237.7	236.8	235.8	234.7	233.6	232.5	231.5
52.5°	225.9	225.7	225.3	225.1	224.8	224.0	222.9	221.8	220.6	219.4	218.7
55°	205.5	205.5	205.4	205.3	205.2	204.6	203.5	202.4	201.3	200.2	199.3
57.5°	186.1	185.8	185.5	185.2	184.9	184.3	183.4	182.5	181.7	180.8	180.0
60°	172.1	172.0	171.9	171.9	171.8	171.2	170.2	169.2	168.2	167.1	166.4
62.5°	159.6	159.4	159.2	159.0	158.7	158.2	157.1	156.1	155.1	154.1	153.4
65°	140.1	139.7	139.3	138.9	138.5	137.9	137.1	136.2	135.3	134.4	133.8
67.5°	119.6	119.2	118.9	118.5	118.1	117.6	117.0	116.3	115.7	115.0	114.5
70°	107.1	106.6	106.2	105.6	105.1	104.6	104.1	103.5	103.1	102.6	102.0
72.5°	94.1	93.7	93.4	92.9	92.5	92.1	91.6	91.0	90.4	89.8	89.3
75°	74.1	73.7	73.4	73.1	72.7	72.4	72.2	71.9	71.7	71.4	71.0
77.5°	56.3	56.2	56.0	55.8	55.6	55.4	55.1	54.8	54.5	54.1	53.9
80°	44.8	44.6	44.4	44.1	43.8	43.6	43.5	43.3	43.1	43.0	42.8
82.5°	33.6	33.5	33.5	33.4	33.3	33.3	33.3	33.3	33.3	33.2	33.0
85°	19.7	19.6	19.4	19.2	19.1	19.0	19.0	19.0	19.0	19.0	18.8
87.5°	8.0	7.9	7.9	7.8	7.8	7.9	8.0	8.2	8.3	8.5	8.5
90°	0.3	1.1	2.0	2.8	3.6	4.6	5.6	6.7	7.7	8.8	9.1
92.5°	6.8	6.6	6.4	6.1	5.9	6.2	7.0	7.7	8.6	9.4	9.9
95°	22.3	19.0	15.7	12.3	9.0	7.7	8.6	9.5	10.4	11.3	11.9
97.5°	44.9	43.4	41.9	40.4	38.9	35.2	29.4	23.5	17.7	11.8	12.5
100°	61.9	63.5	65.1	66.8	68.4	62.9	50.2	37.5	24.8	12.1	12.7
102.5°	81.2	82.4	83.6	84.8	85.9	79.6	65.7	51.9	38.0	24.1	22.1
105°	109.2	110.1	111.0	111.9	112.8	109.5	102.2	94.9	87.6	80.2	65.8
107.5°	138.6	139.3	140.1	140.7	141.5	142.4	143.6	144.7	145.9	147.0	136.5
110°	158.2	158.9	159.6	160.2	160.9	161.6	162.5	163.4	164.3	165.2	162.5



TEST NUMBER: P332094-930

CATALOG NUMBER: S123DIW-S340D460U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	177.0	177.6	178.1	178.7	179.4	180.1	181.0	181.9	182.8	183.7	183.7
115°	204.7	205.2	205.7	206.2	206.7	207.3	208.1	208.8	209.5	210.3	211.1
117.5°	231.6	232.3	232.8	233.4	234.1	234.6	234.9	235.3	235.7	236.0	236.7
120°	248.3	249.1	249.8	250.5	251.3	251.8	252.0	252.3	252.5	252.7	253.4
122.5°	265.4	266.0	266.5	267.2	267.7	268.2	268.6	268.8	269.1	269.5	269.9
125°	288.6	289.3	289.9	290.6	291.2	291.7	292.0	292.4	292.7	293.0	293.2
127.5°	311.2	311.9	312.5	313.2	313.8	314.3	314.7	315.1	315.5	315.9	316.2
130°	325.3	326.0	326.6	327.3	327.9	328.4	328.7	329.1	329.4	329.6	330.0
132.5°	338.8	339.4	340.1	340.7	341.4	341.8	342.1	342.3	342.6	342.8	343.2
135°	359.3	359.8	360.3	360.8	361.3	361.7	362.0	362.3	362.6	363.0	363.2
137.5°	376.9	377.6	378.1	378.8	379.4	379.8	380.0	380.2	380.3	380.5	380.9
140°	388.7	389.1	389.6	390.1	390.6	390.9	391.2	391.4	391.7	391.9	392.2
142.5°	399.5	400.0	400.5	401.0	401.5	401.8	402.0	402.3	402.5	402.8	403.0
145°	414.7	415.2	415.8	416.4	416.9	417.3	417.4	417.6	417.8	417.9	418.1
147.5°	428.9	429.3	429.7	430.1	430.4	430.7	430.9	431.0	431.2	431.4	431.5
150°	437.7	438.0	438.2	438.5	438.7	438.9	439.0	439.2	439.4	439.5	439.7
152.5°	445.6	445.7	445.9	446.0	446.1	446.2	446.3	446.4	446.5	446.6	446.9
155°	456.7	456.6	456.4	456.3	456.2	456.1	456.2	456.2	456.3	456.4	456.8
157.5°	465.5	465.4	465.4	465.4	465.4	465.3	465.2	465.1	465.0	465.0	465.5
160°	470.7	470.6	470.5	470.4	470.3	470.3	470.2	470.1	470.0	469.9	470.4
162.5°	475.6	475.5	475.2	475.1	474.8	474.7	474.6	474.5	474.4	474.3	474.9
165°	481.7	481.4	481.2	480.9	480.7	480.5	480.5	480.4	480.3	480.2	480.9
167.5°	486.4	486.1	485.8	485.4	485.1	484.9	484.9	484.9	484.9	484.9	485.6
170°	489.0	488.7	488.4	488.0	487.7	487.5	487.5	487.5	487.5	487.5	488.2
172.5°	490.7	490.4	490.0	489.6	489.2	489.0	489.1	489.2	489.3	489.3	489.9
175°	493.0	492.6	492.2	491.8	491.4	491.2	491.3	491.4	491.5	491.5	492.1
177.5°	493.6	493.3	492.9	492.6	492.3	492.2	492.3	492.3	492.4	492.4	492.9
180°	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0



TEST NUMBER: P332094-930

CATALOG NUMBER: S123DIW-S340D460U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	440.1	440.8	441.5	441.8	441.7	441.6	441.6	441.5
5°	437.8	438.6	439.5	439.9	439.7	439.5	439.3	439.1
7.5°	433.2	433.9	434.6	435.0	434.9	434.8	434.7	434.6
10°	428.9	429.7	430.4	430.7	430.6	430.4	430.2	430.1
12.5°	424.2	424.8	425.3	425.6	425.5	425.3	425.3	425.2
15°	415.8	416.5	417.2	417.3	416.7	416.2	415.7	415.2
17.5°	405.1	405.6	406.1	406.3	406.0	405.9	405.7	405.5
20°	397.3	397.6	397.9	398.0	397.7	397.5	397.2	397.0
22.5°	388.9	389.2	389.5	389.5	389.1	388.8	388.5	388.2
25°	375.1	375.2	375.3	375.2	375.0	374.7	374.5	374.2
27.5°	360.4	360.5	360.5	360.4	360.1	359.8	359.5	359.1
30°	350.3	350.3	350.3	349.9	349.4	348.8	348.2	347.6
32.5°	339.6	339.1	338.7	338.3	337.9	337.6	337.3	337.0
35°	322.3	321.8	321.2	320.8	320.4	319.9	319.5	319.1
37.5°	304.4	303.8	303.1	302.7	302.5	302.1	301.9	301.7
40°	292.7	292.0	291.3	290.8	290.5	290.2	289.8	289.5
42.5°	280.5	279.8	279.2	278.7	278.3	278.0	277.7	277.3
45°	262.4	261.4	260.3	259.7	259.2	258.8	258.4	258.0
47.5°	243.3	242.3	241.2	240.6	240.2	239.9	239.5	239.1
50°	230.6	229.7	228.8	228.0	227.6	227.1	226.6	226.0
52.5°	217.8	217.0	216.2	215.6	215.1	214.6	214.1	213.6
55°	198.4	197.4	196.5	195.8	195.4	194.9	194.5	194.1
57.5°	179.2	178.3	177.5	176.8	176.3	175.9	175.4	174.9
60°	165.7	164.9	164.1	163.5	163.1	162.7	162.2	161.8
62.5°	152.5	151.8	151.1	150.5	150.3	149.9	149.7	149.4
65°	133.1	132.5	131.8	131.3	131.1	130.8	130.5	130.3
67.5°	113.8	113.2	112.7	112.2	111.9	111.5	111.1	110.8
70°	101.4	100.8	100.2	99.7	99.3	98.9	98.4	98.0
72.5°	88.8	88.2	87.7	87.3	87.2	86.9	86.7	86.4
75°	70.6	70.1	69.7	69.4	69.1	68.9	68.6	68.4
77.5°	53.6	53.3	53.0	52.9	52.9	52.9	52.9	52.9
80°	42.7	42.6	42.6	42.6	42.6	42.6	42.6	42.6
82.5°	32.9	32.8	32.6	32.4	32.4	32.4	32.3	32.2
85°	18.7	18.5	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	8.5	8.4	8.4	8.5	8.5	8.5	8.6	8.6
90°	9.5	9.8	10.1	10.4	10.5	10.7	10.8	11.0
92.5°	10.4	10.9	11.5	11.7	11.9	12.0	12.1	12.1
95°	12.5	13.0	13.6	13.9	13.9	13.9	13.9	13.9
97.5°	13.1	13.8	14.4	14.8	14.8	14.9	15.0	15.1
100°	13.4	14.0	14.7	15.1	15.2	15.2	15.3	15.4
102.5°	20.1	18.0	16.1	15.1	15.2	15.4	15.5	15.7
105°	51.4	37.0	22.6	15.5	15.7	15.8	16.0	16.1
107.5°	125.9	115.4	104.8	94.1	83.2	72.3	61.5	50.6
110°	159.8	157.1	154.4	147.3	135.7	124.0	112.3	100.8



TEST NUMBER: P332094-930

CATALOG NUMBER: S123DIW-S340D460U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	183.8	183.8	183.8	182.6	180.2	177.7	175.3	172.8
115°	211.9	212.7	213.5	214.1	214.4	214.7	215.1	215.4
117.5°	237.3	238.0	238.6	239.0	239.0	239.1	239.2	239.3
120°	254.0	254.7	255.4	255.7	255.7	255.7	255.7	255.7
122.5°	270.4	270.8	271.3	271.5	271.6	271.7	271.7	271.8
125°	293.3	293.5	293.7	293.8	294.0	294.2	294.3	294.5
127.5°	316.4	316.7	316.9	317.0	316.8	316.7	316.5	316.3
130°	330.3	330.6	330.9	331.0	330.8	330.7	330.5	330.4
132.5°	343.5	343.8	344.1	344.2	344.0	343.7	343.5	343.3
135°	363.5	363.7	363.9	363.9	363.7	363.5	363.2	363.0
137.5°	381.3	381.6	382.0	382.2	382.0	381.9	381.7	381.6
140°	392.6	392.9	393.2	393.3	393.1	393.0	392.8	392.6
142.5°	403.3	403.6	403.8	403.8	403.6	403.4	403.2	402.9
145°	418.2	418.4	418.6	418.7	418.7	418.7	418.7	418.7
147.5°	431.7	431.9	432.0	431.9	431.5	431.1	430.8	430.4
150°	439.9	440.0	440.2	440.2	439.9	439.7	439.4	439.2
152.5°	447.2	447.4	447.8	447.7	447.4	446.9	446.6	446.2
155°	457.2	457.6	458.0	458.0	457.5	457.0	456.5	456.1
157.5°	465.9	466.4	466.9	466.8	466.2	465.6	465.0	464.3
160°	470.9	471.4	471.9	471.9	471.3	470.8	470.2	469.6
162.5°	475.5	476.1	476.5	476.6	476.1	475.6	475.1	474.6
165°	481.5	482.2	482.8	482.8	482.2	481.8	481.2	480.6
167.5°	486.2	486.8	487.5	487.5	486.8	486.2	485.6	484.9
170°	488.9	489.5	490.2	490.2	489.5	488.9	488.2	487.5
172.5°	490.6	491.2	491.9	491.9	491.1	490.4	489.8	489.0
175°	492.7	493.3	493.8	493.8	493.2	492.5	491.9	491.2
177.5°	493.5	494.0	494.6	494.5	493.8	493.2	492.5	491.9
180°	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0

(END OF REPORT)