

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332181-840

Luminaire Tested: **S123DIW-S1000D460U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332181-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D460U840-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5896.8 lumens
Efficiency: N/A
Efficacy: 127.6 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332181-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332181-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	99	95	92	98	94	91	88	85	82	80	76	74	73	69	67	66	62
2	94	87	81	75	89	83	77	72	75	70	67	68	64	61	61	58	56	53
3	86	77	69	63	82	73	66	61	66	61	57	60	56	52	54	51	48	45
4	79	68	60	54	75	65	58	52	59	53	49	54	49	45	49	45	42	39
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	40	37	34
6	67	55	47	41	64	53	45	39	48	42	37	44	39	35	40	36	32	30
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	37	32	29	26
8	58	45	37	32	55	44	36	31	40	34	29	37	31	28	34	29	26	24
9	54	42	34	29	51	40	33	28	37	31	26	34	29	25	31	27	23	21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15268	15268	15268	15268
5°	18208	15333	13588	15333
10°	22789	15255	12273	15255
15°	27952	15133	11426	15133
20°	33298	14940	10879	14940
25°	35357	14707	10757	14707
30°	30305	14537	10813	14537
35°	21077	14294	10926	14294
40°	15874	14011	10893	14011
45°	13181	13589	10753	13589
50°	11807	12727	10655	12727
55°	11038	11798	10524	11798
60°	10355	10828	10415	10828
65°	9732	9872	10083	9872
70°	9127	8781	9602	8781
75°	8172	7690	8804	7690
80°	7153	6304	7581	6304
85°	5595	4582	5088	4582



TEST NUMBER: P332181-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.7	2.4
10°-20°	448.0	7.6
20°-30°	751.9	12.8
30°-40°	851.4	14.4
40°-50°	763.5	12.9
50°-60°	616.1	10.4
60°-70°	429.4	7.3
70°-80°	225.7	3.8
80°-90°	56.9	1.0
90°-100°	37.9	0.6
100°-110°	113.6	1.9
110°-120°	193.2	3.3
120°-130°	254.1	4.3
130°-140°	285.6	4.8
140°-150°	280.8	4.8
150°-160°	236.4	4.0
160°-170°	157.3	2.7
170°-180°	55.1	0.9
0°-30°	1339.7	22.7
0°-40°	2191.1	37.2
0°-60°	3570.7	60.6
0°-90°	4282.7	72.6
90°-120°	344.8	5.8
90°-150°	1165.3	19.8
90°-180°	1614.0	27.4
0°-180°	5896.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1685	1419	1258	1419	1685	175
15°	2508	1358	1025	1358	2508	724
25°	2977	1238	906	1238	2977	1306
35°	1604	1088	832	1088	1604	1042
45°	866	893	706	893	866	685
55°	588	629	561	629	588	528
65°	382	388	396	388	382	380
75°	196	185	212	185	196	210
85°	45	37	41	37	45	54
90°	14	0	14	0	14	9
95°	36	27	36	27	36	37
105°	109	103	109	103	109	116
115°	195	194	195	194	195	193
125°	281	285	281	285	281	252
135°	369	369	369	369	369	284
145°	448	448	448	448	448	280
155°	512	513	512	513	512	236
165°	557	559	557	559	557	157
175°	579	581	579	581	579	55
180°	583	583	583	583	583	



TEST NUMBER: P332181-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1505.2	1504.2	1501.4	1503.6	1499.2	1493.2	1492.6	1487.1	1471.2	1470.1	1465.7
5°	1685.1	1679.5	1678.8	1678.2	1668.5	1655.5	1630.7	1628.7	1595.7	1579.2	1559.2
7.5°	1917.8	1920.8	1910.7	1901.9	1872.5	1853.1	1826.5	1792.6	1752.1	1711.0	1683.6
10°	2085.0	2107.7	2079.5	2060.2	2042.4	2008.7	1969.5	1920.8	1872.0	1814.9	1771.6
12.5°	2264.2	2275.3	2269.7	2251.6	2223.8	2172.5	2103.1	2049.4	2004.5	1909.5	1871.1
15°	2508.3	2550.2	2523.5	2461.5	2463.0	2414.2	2323.4	2223.8	2170.9	2087.7	1974.4
17.5°	2768.3	2773.6	2762.2	2710.6	2676.2	2609.2	2525.5	2429.9	2322.8	2222.1	2101.9
20°	2906.9	2902.8	2878.7	2851.9	2792.8	2740.6	2649.2	2542.6	2405.2	2306.2	2175.0
22.5°	2983.8	2977.0	2965.6	2943.2	2894.0	2837.9	2755.8	2639.4	2508.6	2372.3	2220.6
25°	2977.0	2985.9	2987.3	2981.1	2964.0	2930.2	2865.6	2772.9	2642.3	2467.1	2309.1
27.5°	2707.5	2720.3	2756.9	2789.6	2825.9	2863.1	2858.1	2812.1	2715.4	2564.0	2370.9
30°	2438.2	2410.7	2478.7	2564.7	2623.0	2726.1	2783.9	2787.3	2733.0	2603.1	2414.8
32.5°	2064.4	2094.6	2124.7	2230.4	2358.0	2473.8	2588.7	2681.2	2691.8	2605.4	2440.6
35°	1604.0	1641.7	1696.7	1751.7	1889.2	2007.3	2209.4	2385.3	2525.5	2544.1	2443.0
37.5°	1292.5	1311.2	1345.9	1401.1	1491.0	1631.1	1787.5	2009.8	2212.9	2364.0	2370.6
40°	1129.7	1135.3	1174.5	1216.4	1289.2	1404.6	1545.5	1742.0	1985.3	2196.4	2284.3
42.5°	1007.7	1019.8	1036.4	1076.7	1134.7	1221.5	1352.5	1515.0	1738.0	1980.7	2152.8
45°	865.9	879.6	889.9	916.8	958.0	1016.3	1107.8	1256.2	1425.9	1676.8	1908.3
47.5°	772.1	773.3	780.9	801.1	829.2	873.0	937.7	1033.0	1188.8	1392.3	1630.0
50°	705.1	716.1	718.8	734.6	756.6	788.9	842.5	923.6	1051.5	1230.1	1448.7
52.5°	657.8	661.1	668.8	680.2	699.4	724.6	771.0	834.6	934.8	1087.1	1288.1
55°	588.2	588.2	595.8	604.7	615.7	638.4	669.3	716.1	792.3	910.6	1076.8
57.5°	523.9	527.4	532.7	535.4	544.8	559.8	585.6	621.1	678.0	769.0	901.2
60°	481.0	487.3	486.6	492.0	500.3	512.0	533.9	562.8	613.7	686.5	797.9
62.5°	443.6	443.2	443.1	449.7	458.0	469.1	483.4	508.4	551.6	616.1	710.9
65°	382.1	380.7	385.6	389.6	392.4	400.6	411.6	433.6	462.5	510.6	584.1
67.5°	327.4	323.4	326.0	327.4	332.0	338.5	348.8	362.4	385.4	424.0	479.4
70°	290.0	286.6	285.9	287.2	291.3	296.2	303.8	316.8	338.1	369.0	409.6
72.5°	251.6	249.1	249.0	252.1	254.0	257.1	262.5	274.5	291.3	314.6	352.4
75°	196.5	196.5	196.5	197.2	199.2	202.1	206.1	212.4	225.4	241.9	267.3
77.5°	147.3	147.2	146.3	146.2	149.3	150.5	151.5	157.2	164.5	175.6	194.2
80°	115.4	112.0	113.4	115.4	116.8	117.5	119.6	121.0	127.1	133.3	146.3
82.5°	85.7	82.9	83.1	86.3	86.5	87.3	89.4	91.3	93.6	99.3	106.2
85°	45.3	45.3	46.0	46.0	46.8	46.0	48.1	48.8	48.8	52.2	56.4
87.5°	19.3	18.1	18.6	19.1	18.5	19.0	19.5	20.0	20.4	20.9	21.2
90°	13.7	13.5	13.3	13.1	12.9	12.6	12.2	11.8	11.4	11.0	9.7
92.5°	18.5	18.6	18.7	18.9	19.0	18.9	18.6	18.2	17.9	17.6	16.9
95°	35.6	35.6	35.6	35.6	35.6	35.4	35.0	34.6	34.2	33.8	33.0
97.5°	54.9	54.9	55.0	55.0	55.0	54.8	54.4	53.9	53.4	53.0	52.4
100°	69.6	69.4	69.2	69.0	68.8	68.5	68.2	67.9	67.6	67.3	66.8
102.5°	84.5	84.6	84.6	84.7	84.7	84.6	84.3	84.0	83.7	83.4	82.7
105°	109.0	108.8	108.6	108.4	108.1	108.0	108.0	108.0	108.0	108.0	107.0
107.5°	134.3	134.4	134.5	134.6	134.7	134.6	134.3	134.0	133.7	133.4	133.0
110°	151.5	151.7	151.9	152.1	152.3	152.2	151.8	151.4	151.0	150.6	150.4



TEST NUMBER: P332181-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.8	169.9	169.9	169.9	170.0	169.8	169.3	168.7	168.2	167.7	167.7
115°	195.0	195.1	195.2	195.3	195.4	195.4	195.3	195.2	195.1	195.0	195.2
117.5°	220.5	220.8	221.1	221.4	221.7	221.8	221.8	221.9	221.9	221.9	222.2
120°	238.4	238.6	238.8	239.0	239.2	239.4	239.5	239.6	239.7	239.8	240.3
122.5°	255.6	255.9	256.2	256.5	256.8	257.0	257.3	257.6	257.8	258.1	258.4
125°	281.4	281.9	282.3	282.7	283.1	283.5	283.9	284.3	284.7	285.1	285.3
127.5°	307.2	307.6	308.1	308.6	309.0	309.5	310.1	310.7	311.2	311.8	312.0
130°	324.0	324.8	325.5	326.2	326.9	327.4	327.8	328.2	328.6	329.0	329.3
132.5°	341.5	342.1	342.6	343.3	343.8	344.3	344.8	345.3	345.8	346.3	346.5
135°	368.9	369.1	369.3	369.5	369.7	370.0	370.4	370.8	371.2	371.6	371.7
137.5°	392.9	393.3	393.7	394.0	394.5	394.9	395.4	395.8	396.2	396.6	396.4
140°	408.7	409.4	410.1	410.8	411.5	411.9	412.0	412.1	412.2	412.3	412.2
142.5°	424.7	425.4	425.9	426.5	427.0	427.3	427.4	427.5	427.6	427.7	427.6
145°	448.1	448.5	448.9	449.3	449.7	449.9	450.0	450.1	450.2	450.3	450.0
147.5°	468.7	469.3	469.9	470.6	471.2	471.5	471.5	471.5	471.5	471.5	471.2
150°	481.9	482.5	483.1	483.7	484.3	484.6	484.6	484.6	484.6	484.6	484.4
152.5°	494.7	495.2	495.7	496.3	496.9	497.1	496.9	496.7	496.6	496.3	496.2
155°	512.1	512.8	513.5	514.2	514.9	515.1	514.7	514.3	513.9	513.5	513.4
157.5°	528.0	528.5	529.1	529.7	530.2	530.3	529.9	529.5	529.0	528.6	528.5
160°	538.2	538.6	539.0	539.4	539.8	539.8	539.3	538.8	538.3	537.8	537.8
162.5°	545.8	546.5	547.1	547.9	548.5	548.6	548.1	547.5	547.0	546.5	546.4
165°	556.9	557.6	558.4	559.1	559.8	559.9	559.3	558.7	558.1	557.4	557.4
167.5°	566.3	567.0	567.6	568.3	568.9	568.9	568.3	567.6	567.0	566.3	566.3
170°	571.2	571.9	572.6	573.3	574.0	574.0	573.3	572.6	571.9	571.2	571.2
172.5°	574.8	575.5	576.2	576.9	577.6	577.6	577.0	576.4	575.8	575.1	575.1
175°	579.0	579.7	580.4	581.1	581.8	581.8	581.2	580.6	580.0	579.4	579.4
177.5°	581.1	581.7	582.3	582.8	583.4	583.4	583.0	582.5	582.0	581.5	581.5
180°	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6



TEST NUMBER: P332181-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1462.4	1457.9	1453.6	1445.9	1439.3	1430.0	1427.1	1423.9	1414.0	1405.2	1398.6
5°	1551.7	1535.2	1511.2	1489.1	1471.3	1447.2	1433.5	1419.1	1398.5	1379.9	1364.8
7.5°	1645.2	1612.8	1575.4	1534.9	1497.3	1461.0	1431.7	1405.6	1376.7	1349.4	1328.1
10°	1719.4	1672.6	1620.4	1564.1	1516.0	1469.3	1430.1	1395.7	1358.6	1326.3	1299.5
12.5°	1804.0	1734.7	1662.7	1594.3	1537.4	1472.6	1425.1	1381.4	1339.4	1300.5	1270.4
15°	1904.2	1816.2	1731.1	1636.9	1550.3	1469.3	1412.9	1358.0	1309.1	1269.3	1230.8
17.5°	1995.5	1895.8	1783.5	1669.1	1564.6	1468.4	1389.6	1327.4	1266.4	1217.6	1179.2
20°	2047.2	1933.8	1806.6	1687.8	1572.4	1465.1	1378.6	1304.3	1238.3	1186.8	1143.5
22.5°	2091.7	1959.0	1827.6	1700.4	1571.8	1456.3	1358.2	1281.8	1210.3	1159.8	1113.8
25°	2137.9	1979.1	1847.2	1698.1	1554.5	1434.9	1324.9	1238.3	1166.9	1107.8	1060.4
27.5°	2177.5	1977.8	1821.2	1660.8	1527.2	1407.3	1290.0	1197.1	1121.3	1057.0	1009.0
30°	2203.8	1980.5	1794.3	1635.6	1500.9	1377.2	1263.0	1169.6	1089.9	1024.6	979.3
32.5°	2220.4	1978.8	1769.6	1600.3	1459.1	1349.7	1234.0	1137.2	1055.3	991.1	947.4
35°	2230.0	1966.8	1727.0	1527.6	1391.6	1285.1	1188.2	1087.8	1002.0	942.2	892.7
37.5°	2210.7	1941.4	1677.5	1457.5	1308.6	1203.7	1122.2	1036.7	954.5	888.7	846.1
40°	2180.5	1924.9	1639.0	1408.1	1251.4	1150.3	1081.0	997.1	916.0	853.5	813.6
42.5°	2122.7	1891.3	1596.7	1353.1	1192.0	1091.0	1027.1	957.0	880.3	821.6	781.7
45°	1981.9	1818.4	1533.2	1270.6	1104.3	999.9	943.5	892.7	823.2	766.2	731.8
47.5°	1786.5	1708.5	1441.4	1183.7	1012.8	912.3	853.7	812.8	762.1	716.1	683.1
50°	1650.6	1618.4	1379.2	1124.3	951.8	853.5	797.2	760.0	723.7	677.6	647.3
52.5°	1494.0	1513.9	1306.7	1062.7	889.7	793.0	740.0	710.5	677.4	639.6	613.3
55°	1273.4	1345.5	1181.3	959.4	797.2	705.1	654.9	628.7	609.6	581.4	558.7
57.5°	1066.8	1158.6	1045.8	852.8	706.3	626.8	578.8	550.3	538.0	523.2	505.3
60°	944.2	1034.9	949.1	781.3	645.3	569.7	527.0	503.0	490.7	480.4	465.2
62.5°	834.9	926.7	854.4	708.8	585.3	515.2	478.2	454.6	445.0	439.7	426.8
65°	684.5	763.5	715.4	595.8	499.6	437.8	404.0	387.6	378.7	376.6	368.3
67.5°	557.0	617.2	582.2	494.2	418.5	365.1	336.5	322.4	315.6	314.9	308.7
70°	473.5	529.9	503.0	423.3	358.0	316.1	291.3	279.0	274.9	274.2	270.7
72.5°	408.6	447.9	426.6	360.1	309.6	271.6	253.5	240.5	235.8	236.8	234.5
75°	302.4	331.9	319.5	273.5	233.0	208.2	193.1	184.9	180.8	182.8	180.1
77.5°	217.5	236.3	225.1	193.3	168.2	150.4	139.3	134.1	130.5	130.3	129.1
80°	164.2	175.2	169.1	149.8	129.2	114.1	105.1	101.7	99.7	99.0	98.3
82.5°	116.9	126.3	119.1	105.8	91.8	82.7	77.7	73.1	71.6	72.0	71.3
85°	59.1	62.5	59.8	51.5	46.0	41.9	39.2	37.1	35.7	36.5	35.0
87.5°	22.0	22.3	20.4	18.0	16.7	14.7	14.5	13.3	12.4	12.6	12.2
90°	8.4	7.0	5.7	4.5	3.5	2.5	1.5	0.5	1.5	2.5	3.5
92.5°	16.1	15.3	14.5	13.8	13.1	12.4	11.8	11.1	11.8	12.4	13.1
95°	32.2	31.4	30.6	29.9	29.2	28.4	27.7	27.0	27.7	28.4	29.2
97.5°	51.8	51.2	50.6	50.1	49.6	49.0	48.5	48.0	48.5	49.0	49.6
100°	66.2	65.7	65.2	64.6	64.0	63.4	62.8	62.2	62.8	63.4	64.0
102.5°	82.0	81.4	80.7	80.2	79.8	79.5	79.1	78.7	79.1	79.5	79.8
105°	106.1	105.2	104.3	103.8	103.6	103.4	103.2	103.0	103.2	103.4	103.6
107.5°	132.6	132.3	131.9	131.7	131.5	131.4	131.3	131.2	131.3	131.4	131.5
110°	150.2	150.0	149.8	149.6	149.4	149.2	149.0	148.8	149.0	149.2	149.4



TEST NUMBER: P332181-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	167.7	167.6	167.6	167.5	167.4	167.3	167.1	167.0	167.1	167.3	167.4
115°	195.4	195.6	195.8	195.7	195.4	195.1	194.8	194.5	194.8	195.1	195.4
117.5°	222.4	222.7	222.9	223.0	222.8	222.6	222.4	222.2	222.4	222.6	222.8
120°	240.9	241.4	241.9	241.8	241.2	240.5	239.9	239.3	239.9	240.5	241.2
122.5°	258.6	258.9	259.1	259.0	258.6	258.2	257.7	257.3	257.7	258.2	258.6
125°	285.5	285.7	285.9	285.9	285.6	285.3	285.0	284.7	285.0	285.3	285.6
127.5°	312.3	312.6	312.8	312.6	311.8	311.2	310.5	309.9	310.5	311.2	311.8
130°	329.6	329.9	330.2	330.0	329.2	328.4	327.6	326.8	327.6	328.4	329.2
132.5°	346.7	346.9	347.2	346.9	346.1	345.3	344.4	343.6	344.4	345.3	346.1
135°	371.8	371.9	372.0	371.7	371.1	370.5	369.9	369.3	369.9	370.5	371.1
137.5°	396.1	395.8	395.6	395.2	394.7	394.2	393.6	393.1	393.6	394.2	394.7
140°	412.1	412.0	411.9	411.6	411.1	410.6	410.1	409.6	410.1	410.6	411.1
142.5°	427.4	427.2	427.0	426.7	426.2	425.7	425.2	424.6	425.2	425.7	426.2
145°	449.7	449.4	449.1	448.9	448.7	448.5	448.3	448.1	448.3	448.5	448.7
147.5°	470.9	470.6	470.3	470.0	469.6	469.3	468.9	468.6	468.9	469.3	469.6
150°	484.2	484.0	483.8	483.6	483.4	483.2	483.0	482.8	483.0	483.2	483.4
152.5°	496.1	495.9	495.8	495.6	495.3	495.1	494.8	494.5	494.8	495.1	495.3
155°	513.3	513.2	513.1	513.0	513.0	513.0	513.0	513.0	513.0	513.0	513.0
157.5°	528.5	528.4	528.3	528.3	528.4	528.6	528.7	528.8	528.7	528.6	528.4
160°	537.8	537.8	537.8	537.9	538.1	538.3	538.5	538.7	538.5	538.3	538.1
162.5°	546.3	546.2	546.2	546.3	546.5	546.8	547.1	547.4	547.1	546.8	546.5
165°	557.4	557.4	557.4	557.5	557.8	558.2	558.5	558.8	558.5	558.2	557.8
167.5°	566.2	566.1	566.0	566.2	566.6	567.0	567.4	567.8	567.4	567.0	566.6
170°	571.2	571.2	571.2	571.4	571.8	572.2	572.6	573.0	572.6	572.2	571.8
172.5°	575.1	575.1	575.1	575.3	575.8	576.2	576.6	577.0	576.6	576.2	575.8
175°	579.4	579.4	579.4	579.6	580.0	580.4	580.8	581.2	580.8	580.4	580.0
177.5°	581.5	581.5	581.5	581.7	582.0	582.3	582.6	583.0	582.6	582.3	582.0
180°	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6



TEST NUMBER: P332181-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1394.7	1390.9	1385.4	1377.2	1370.6	1360.1	1360.1	1361.8	1361.8	1361.2	1360.1
5°	1352.4	1342.1	1329.8	1315.3	1300.2	1285.1	1282.3	1276.9	1272.7	1269.9	1266.5
7.5°	1307.8	1289.5	1271.4	1251.2	1232.8	1217.6	1207.0	1198.2	1192.5	1186.5	1182.1
10°	1277.5	1254.9	1233.6	1212.2	1188.8	1170.3	1158.6	1150.3	1144.2	1138.7	1136.0
12.5°	1241.7	1215.8	1192.3	1172.0	1146.5	1127.4	1116.3	1112.5	1105.2	1093.6	1087.5
15°	1189.5	1165.5	1137.3	1106.4	1094.0	1070.7	1057.6	1051.5	1047.3	1038.3	1035.6
17.5°	1144.9	1113.4	1081.8	1058.7	1035.7	1016.8	1009.5	1001.8	996.3	989.1	986.8
20°	1109.1	1081.0	1052.1	1027.3	1003.3	982.7	976.5	971.0	965.5	962.1	959.4
22.5°	1072.9	1044.7	1020.8	997.6	972.0	958.5	951.8	945.7	941.9	939.6	936.8
25°	1021.9	997.1	970.4	949.7	929.1	920.2	916.0	912.6	909.9	906.5	905.7
27.5°	976.2	949.3	927.6	908.4	893.5	886.1	882.1	880.4	881.0	882.2	883.0
30°	942.2	917.5	899.6	883.0	869.3	862.4	861.7	861.7	864.5	865.2	866.6
32.5°	910.8	890.5	872.6	856.7	846.3	841.5	844.1	844.1	846.4	848.2	850.6
35°	865.2	847.3	833.5	819.8	810.9	812.9	814.4	815.7	819.1	823.2	826.1
37.5°	821.6	806.1	791.8	781.0	777.0	780.6	784.0	786.9	790.8	794.0	796.8
40°	790.3	778.6	764.9	755.3	756.6	758.7	761.4	764.9	768.3	770.3	773.2
42.5°	761.1	748.9	738.5	730.5	732.5	735.1	736.7	738.5	742.5	746.2	747.8
45°	716.8	707.1	697.5	692.7	694.1	695.5	696.8	698.9	702.4	705.1	705.8
47.5°	666.8	660.1	653.7	649.0	651.2	650.7	652.5	656.8	657.9	659.5	663.4
50°	635.0	628.7	621.3	619.9	619.9	619.9	620.6	626.0	626.0	628.7	631.6
52.5°	599.8	595.8	591.0	588.5	587.4	587.4	590.3	593.1	594.2	598.0	600.8
55°	547.8	543.6	539.5	537.3	536.0	537.3	542.9	544.2	547.8	549.8	551.8
57.5°	493.4	490.3	487.0	485.8	485.5	487.4	490.4	494.5	495.3	501.7	504.8
60°	457.7	452.8	450.1	450.1	448.8	454.9	453.5	460.4	461.8	466.0	470.7
62.5°	420.8	414.3	413.2	413.2	415.3	417.0	418.9	421.9	425.6	430.7	434.4
65°	361.4	358.0	362.8	362.1	360.8	364.9	364.9	368.3	372.4	377.3	384.9
67.5°	305.3	303.5	303.9	303.9	306.0	308.3	310.2	313.3	318.2	323.3	328.2
70°	267.3	269.4	266.0	268.7	270.7	271.5	272.9	276.9	282.5	285.9	291.3
72.5°	230.5	230.4	230.8	231.9	233.9	235.2	236.5	241.3	247.2	250.1	254.6
75°	177.3	176.6	178.6	178.6	182.1	183.5	184.9	186.9	192.4	196.5	200.0
77.5°	129.5	130.3	129.9	132.2	131.3	131.5	135.8	137.8	138.5	146.5	148.3
80°	97.6	99.0	99.7	100.4	101.0	99.7	104.4	106.5	106.5	111.3	114.7
82.5°	70.1	70.9	72.7	73.4	73.5	74.9	75.3	76.9	78.5	80.6	85.0
85°	35.0	37.1	37.8	37.1	37.8	36.5	38.5	39.2	39.9	39.9	39.9
87.5°	11.9	12.7	12.4	13.2	12.9	13.7	13.8	12.8	12.9	14.6	12.5
90°	4.5	5.7	7.0	8.4	9.7	11.0	11.4	11.8	12.2	12.6	12.9
92.5°	13.8	14.5	15.3	16.1	16.9	17.6	17.9	18.2	18.6	18.9	19.0
95°	29.9	30.6	31.4	32.2	33.0	33.8	34.2	34.6	35.0	35.4	35.6
97.5°	50.1	50.6	51.2	51.8	52.4	53.0	53.4	53.9	54.4	54.8	55.0
100°	64.6	65.2	65.7	66.2	66.8	67.3	67.6	67.9	68.2	68.5	68.8
102.5°	80.2	80.7	81.4	82.0	82.7	83.4	83.7	84.0	84.3	84.6	84.7
105°	103.8	104.3	105.2	106.1	107.0	108.0	108.0	108.0	108.0	108.0	108.1
107.5°	131.7	131.9	132.3	132.6	133.0	133.4	133.7	134.0	134.3	134.6	134.7
110°	149.6	149.8	150.0	150.2	150.4	150.6	151.0	151.4	151.8	152.2	152.3



TEST NUMBER: P332181-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	167.5	167.6	167.6	167.7	167.7	167.7	168.2	168.7	169.3	169.8	170.0
115°	195.7	195.8	195.6	195.4	195.2	195.0	195.1	195.2	195.3	195.4	195.4
117.5°	223.0	222.9	222.7	222.4	222.2	221.9	221.9	221.9	221.8	221.8	221.7
120°	241.8	241.9	241.4	240.9	240.3	239.8	239.7	239.6	239.5	239.4	239.2
122.5°	259.0	259.1	258.9	258.6	258.4	258.1	257.8	257.6	257.3	257.0	256.8
125°	285.9	285.9	285.7	285.5	285.3	285.1	284.7	284.3	283.9	283.5	283.1
127.5°	312.6	312.8	312.6	312.3	312.0	311.8	311.2	310.7	310.1	309.5	309.0
130°	330.0	330.2	329.9	329.6	329.3	329.0	328.6	328.2	327.8	327.4	326.9
132.5°	346.9	347.2	346.9	346.7	346.5	346.3	345.8	345.3	344.8	344.3	343.8
135°	371.7	372.0	371.9	371.8	371.7	371.6	371.2	370.8	370.4	370.0	369.7
137.5°	395.2	395.6	395.8	396.1	396.4	396.6	396.2	395.8	395.4	394.9	394.5
140°	411.6	411.9	412.0	412.1	412.2	412.3	412.2	412.1	412.0	411.9	411.5
142.5°	426.7	427.0	427.2	427.4	427.6	427.7	427.6	427.5	427.4	427.3	427.0
145°	448.9	449.1	449.4	449.7	450.0	450.3	450.2	450.1	450.0	449.9	449.7
147.5°	470.0	470.3	470.6	470.9	471.2	471.5	471.5	471.5	471.5	471.5	471.2
150°	483.6	483.8	484.0	484.2	484.4	484.6	484.6	484.6	484.6	484.6	484.3
152.5°	495.6	495.8	495.9	496.1	496.2	496.3	496.6	496.7	496.9	497.1	496.9
155°	513.0	513.1	513.2	513.3	513.4	513.5	513.9	514.3	514.7	515.1	514.9
157.5°	528.3	528.3	528.4	528.5	528.5	528.6	529.0	529.5	529.9	530.3	530.2
160°	537.9	537.8	537.8	537.8	537.8	537.8	538.3	538.8	539.3	539.8	539.8
162.5°	546.3	546.2	546.2	546.3	546.4	546.5	547.0	547.5	548.1	548.6	548.5
165°	557.5	557.4	557.4	557.4	557.4	557.4	558.1	558.7	559.3	559.9	559.8
167.5°	566.2	566.0	566.1	566.2	566.3	566.3	567.0	567.6	568.3	568.9	568.9
170°	571.4	571.2	571.2	571.2	571.2	571.2	571.9	572.6	573.3	574.0	574.0
172.5°	575.3	575.1	575.1	575.1	575.1	575.1	575.8	576.4	577.0	577.6	577.6
175°	579.6	579.4	579.4	579.4	579.4	579.4	580.0	580.6	581.2	581.8	581.8
177.5°	581.7	581.5	581.5	581.5	581.5	581.5	582.0	582.5	583.0	583.4	583.4
180°	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6



TEST NUMBER: P332181-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1356.2	1355.7	1359.6	1356.9	1359.6	1355.7	1356.2	1360.1	1361.2	1361.8	1361.8
5°	1262.4	1264.5	1257.6	1257.6	1257.6	1264.5	1262.4	1266.5	1269.9	1272.7	1276.9
7.5°	1178.8	1175.8	1176.1	1172.4	1176.1	1175.8	1178.8	1182.1	1186.5	1192.5	1198.2
10°	1127.7	1123.6	1122.2	1122.9	1122.2	1123.6	1127.7	1136.0	1138.7	1144.2	1150.3
12.5°	1085.4	1084.6	1075.5	1075.6	1075.5	1084.6	1085.4	1087.5	1093.6	1105.2	1112.5
15°	1035.6	1022.6	1021.2	1025.3	1021.2	1022.6	1035.6	1035.6	1038.3	1047.3	1051.5
17.5°	985.7	978.9	979.3	977.2	979.3	978.9	985.7	986.8	989.1	996.3	1001.8
20°	959.4	955.2	954.5	949.7	954.5	955.2	959.4	959.4	962.1	965.5	971.0
22.5°	935.1	933.8	934.2	928.9	934.2	933.8	935.1	936.8	939.6	941.9	945.7
25°	905.0	908.5	905.7	905.7	905.7	908.5	905.0	905.7	906.5	909.9	912.6
27.5°	884.7	884.5	883.2	883.2	883.2	884.5	884.7	883.0	882.2	881.0	880.4
30°	869.3	868.6	870.0	870.0	870.0	868.6	869.3	866.6	865.2	864.5	861.7
32.5°	853.9	854.9	855.2	855.7	855.2	854.9	853.9	850.6	848.2	846.4	844.1
35°	830.1	830.8	832.9	831.5	832.9	830.8	830.1	826.1	823.2	819.1	815.7
37.5°	798.0	801.1	800.4	801.5	800.4	801.1	798.0	796.8	794.0	790.8	786.9
40°	773.8	775.9	775.2	775.2	775.2	775.9	773.8	773.2	770.3	768.3	764.9
42.5°	749.0	750.5	748.8	747.7	748.8	750.5	749.0	747.8	746.2	742.5	738.5
45°	708.5	707.1	709.2	706.4	709.2	707.1	708.5	705.8	705.1	702.4	698.9
47.5°	663.2	664.5	665.1	667.1	665.1	664.5	663.2	663.4	659.5	657.9	656.8
50°	632.9	637.0	637.0	636.3	637.0	637.0	632.9	631.6	628.7	626.0	626.0
52.5°	603.2	605.1	607.9	607.7	607.9	605.1	603.2	600.8	598.0	594.2	593.1
55°	557.3	558.7	560.1	560.8	560.1	558.7	557.3	551.8	549.8	547.8	544.2
57.5°	509.8	509.2	512.5	513.5	512.5	509.2	509.8	504.8	501.7	495.3	494.5
60°	476.3	476.3	481.7	483.8	481.7	476.3	476.3	470.7	466.0	461.8	460.4
62.5°	440.5	442.7	448.2	445.4	448.2	442.7	440.5	434.4	430.7	425.6	421.9
65°	388.3	393.7	393.0	395.9	393.0	393.7	388.3	384.9	377.3	372.4	368.3
67.5°	333.7	337.1	342.0	342.5	342.0	337.1	333.7	328.2	323.3	318.2	313.3
70°	296.9	300.3	303.1	305.1	303.1	300.3	296.9	291.3	285.9	282.5	276.9
72.5°	261.2	263.0	269.5	266.6	269.5	263.0	261.2	254.6	250.1	247.2	241.3
75°	204.8	209.5	213.7	211.7	213.7	209.5	204.8	200.0	196.5	192.4	186.9
77.5°	151.5	156.2	158.1	156.4	158.1	156.2	151.5	148.3	146.5	138.5	137.8
80°	119.6	118.9	123.0	122.3	123.0	118.9	119.6	114.7	111.3	106.5	106.5
82.5°	87.7	87.1	89.0	89.4	89.0	87.1	87.7	85.0	80.6	78.5	76.9
85°	42.6	44.6	41.9	41.2	41.9	44.6	42.6	39.9	39.9	39.9	39.2
87.5°	12.5	12.5	12.0	11.5	12.0	12.5	12.5	12.5	14.6	12.9	12.8
90°	13.1	13.3	13.5	13.7	13.5	13.3	13.1	12.9	12.6	12.2	11.8
92.5°	18.9	18.7	18.6	18.5	18.6	18.7	18.9	19.0	18.9	18.6	18.2
95°	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.6	35.4	35.0	34.6
97.5°	55.0	55.0	54.9	54.9	54.9	55.0	55.0	55.0	54.8	54.4	53.9
100°	69.0	69.2	69.4	69.6	69.4	69.2	69.0	68.8	68.5	68.2	67.9
102.5°	84.7	84.6	84.6	84.5	84.6	84.6	84.7	84.7	84.6	84.3	84.0
105°	108.4	108.6	108.8	109.0	108.8	108.6	108.4	108.1	108.0	108.0	108.0
107.5°	134.6	134.5	134.4	134.3	134.4	134.5	134.6	134.7	134.6	134.3	134.0
110°	152.1	151.9	151.7	151.5	151.7	151.9	152.1	152.3	152.2	151.8	151.4



TEST NUMBER: P332181-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	169.9	169.9	169.9	169.8	169.9	169.9	169.9	170.0	169.8	169.3	168.7
115°	195.3	195.2	195.1	195.0	195.1	195.2	195.3	195.4	195.4	195.3	195.2
117.5°	221.4	221.1	220.8	220.5	220.8	221.1	221.4	221.7	221.8	221.8	221.9
120°	239.0	238.8	238.6	238.4	238.6	238.8	239.0	239.2	239.4	239.5	239.6
122.5°	256.5	256.2	255.9	255.6	255.9	256.2	256.5	256.8	257.0	257.3	257.6
125°	282.7	282.3	281.9	281.4	281.9	282.3	282.7	283.1	283.5	283.9	284.3
127.5°	308.6	308.1	307.6	307.2	307.6	308.1	308.6	309.0	309.5	310.1	310.7
130°	326.2	325.5	324.8	324.0	324.8	325.5	326.2	326.9	327.4	327.8	328.2
132.5°	343.3	342.6	342.1	341.5	342.1	342.6	343.3	343.8	344.3	344.8	345.3
135°	369.5	369.3	369.1	368.9	369.1	369.3	369.5	369.7	370.0	370.4	370.8
137.5°	394.0	393.7	393.3	392.9	393.3	393.7	394.0	394.5	394.9	395.4	395.8
140°	410.8	410.1	409.4	408.7	409.4	410.1	410.8	411.5	411.9	412.0	412.1
142.5°	426.5	425.9	425.4	424.7	425.4	425.9	426.5	427.0	427.3	427.4	427.5
145°	449.3	448.9	448.5	448.1	448.5	448.9	449.3	449.7	449.9	450.0	450.1
147.5°	470.6	469.9	469.3	468.7	469.3	469.9	470.6	471.2	471.5	471.5	471.5
150°	483.7	483.1	482.5	481.9	482.5	483.1	483.7	484.3	484.6	484.6	484.6
152.5°	496.3	495.7	495.2	494.7	495.2	495.7	496.3	496.9	497.1	496.9	496.7
155°	514.2	513.5	512.8	512.1	512.8	513.5	514.2	514.9	515.1	514.7	514.3
157.5°	529.7	529.1	528.5	528.0	528.5	529.1	529.7	530.2	530.3	529.9	529.5
160°	539.4	539.0	538.6	538.2	538.6	539.0	539.4	539.8	539.8	539.3	538.8
162.5°	547.9	547.1	546.5	545.8	546.5	547.1	547.9	548.5	548.6	548.1	547.5
165°	559.1	558.4	557.6	556.9	557.6	558.4	559.1	559.8	559.9	559.3	558.7
167.5°	568.3	567.6	567.0	566.3	567.0	567.6	568.3	568.9	568.9	568.3	567.6
170°	573.3	572.6	571.9	571.2	571.9	572.6	573.3	574.0	574.0	573.3	572.6
172.5°	576.9	576.2	575.5	574.8	575.5	576.2	576.9	577.6	577.6	577.0	576.4
175°	581.1	580.4	579.7	579.0	579.7	580.4	581.1	581.8	581.8	581.2	580.6
177.5°	582.8	582.3	581.7	581.1	581.7	582.3	582.8	583.4	583.4	583.0	582.5
180°	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6



TEST NUMBER: P332181-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1360.1	1360.1	1370.6	1377.2	1385.4	1390.9	1394.7	1398.6	1405.2	1414.0	1423.9
5°	1282.3	1285.1	1300.2	1315.3	1329.8	1342.1	1352.4	1364.8	1379.9	1398.5	1419.1
7.5°	1207.0	1217.6	1232.8	1251.2	1271.4	1289.5	1307.8	1328.1	1349.4	1376.7	1405.6
10°	1158.6	1170.3	1188.8	1212.2	1233.6	1254.9	1277.5	1299.5	1326.3	1358.6	1395.7
12.5°	1116.3	1127.4	1146.5	1172.0	1192.3	1215.8	1241.7	1270.4	1300.5	1339.4	1381.4
15°	1057.6	1070.7	1094.0	1106.4	1137.3	1165.5	1189.5	1230.8	1269.3	1309.1	1358.0
17.5°	1009.5	1016.8	1035.7	1058.7	1081.8	1113.4	1144.9	1179.2	1217.6	1266.4	1327.4
20°	976.5	982.7	1003.3	1027.3	1052.1	1081.0	1109.1	1143.5	1186.8	1238.3	1304.3
22.5°	951.8	958.5	972.0	997.6	1020.8	1044.7	1072.9	1113.8	1159.8	1210.3	1281.8
25°	916.0	920.2	929.1	949.7	970.4	997.1	1021.9	1060.4	1107.8	1166.9	1238.3
27.5°	882.1	886.1	893.5	908.4	927.6	949.3	976.2	1009.0	1057.0	1121.3	1197.1
30°	861.7	862.4	869.3	883.0	899.6	917.5	942.2	979.3	1024.6	1089.9	1169.6
32.5°	844.1	841.5	846.3	856.7	872.6	890.5	910.8	947.4	991.1	1055.3	1137.2
35°	814.4	812.9	810.9	819.8	833.5	847.3	865.2	892.7	942.2	1002.0	1087.8
37.5°	784.0	780.6	777.0	781.0	791.8	806.1	821.6	846.1	888.7	954.5	1036.7
40°	761.4	758.7	756.6	755.3	764.9	778.6	790.3	813.6	853.5	916.0	997.1
42.5°	736.7	735.1	732.5	730.5	738.5	748.9	761.1	781.7	821.6	880.3	957.0
45°	696.8	695.5	694.1	692.7	697.5	707.1	716.8	731.8	766.2	823.2	892.7
47.5°	652.5	650.7	651.2	649.0	653.7	660.1	666.8	683.1	716.1	762.1	812.8
50°	620.6	619.9	619.9	619.9	621.3	628.7	635.0	647.3	677.6	723.7	760.0
52.5°	590.3	587.4	587.4	588.5	591.0	595.8	599.8	613.3	639.6	677.4	710.5
55°	542.9	537.3	536.0	537.3	539.5	543.6	547.8	558.7	581.4	609.6	628.7
57.5°	490.4	487.4	485.5	485.8	487.0	490.3	493.4	505.3	523.2	538.0	550.3
60°	453.5	454.9	448.8	450.1	450.1	452.8	457.7	465.2	480.4	490.7	503.0
62.5°	418.9	417.0	415.3	413.2	413.2	414.3	420.8	426.8	439.7	445.0	454.6
65°	364.9	364.9	360.8	362.1	362.8	358.0	361.4	368.3	376.6	378.7	387.6
67.5°	310.2	308.3	306.0	303.9	303.9	303.5	305.3	308.7	314.9	315.6	322.4
70°	272.9	271.5	270.7	268.7	266.0	269.4	267.3	270.7	274.2	274.9	279.0
72.5°	236.5	235.2	233.9	231.9	230.8	230.4	230.5	234.5	236.8	235.8	240.5
75°	184.9	183.5	182.1	178.6	178.6	176.6	177.3	180.1	182.8	180.8	184.9
77.5°	135.8	131.5	131.3	132.2	129.9	130.3	129.5	129.1	130.3	130.5	134.1
80°	104.4	99.7	101.0	100.4	99.7	99.0	97.6	98.3	99.0	99.7	101.7
82.5°	75.3	74.9	73.5	73.4	72.7	70.9	70.1	71.3	72.0	71.6	73.1
85°	38.5	36.5	37.8	37.1	37.8	37.1	35.0	35.0	36.5	35.7	37.1
87.5°	13.8	13.7	12.9	13.2	12.4	12.7	11.9	12.2	12.6	12.4	13.3
90°	11.4	11.0	9.7	8.4	7.0	5.7	4.5	3.5	2.5	1.5	0.5
92.5°	17.9	17.6	16.9	16.1	15.3	14.5	13.8	13.1	12.4	11.8	11.1
95°	34.2	33.8	33.0	32.2	31.4	30.6	29.9	29.2	28.4	27.7	27.0
97.5°	53.4	53.0	52.4	51.8	51.2	50.6	50.1	49.6	49.0	48.5	48.0
100°	67.6	67.3	66.8	66.2	65.7	65.2	64.6	64.0	63.4	62.8	62.2
102.5°	83.7	83.4	82.7	82.0	81.4	80.7	80.2	79.8	79.5	79.1	78.7
105°	108.0	108.0	107.0	106.1	105.2	104.3	103.8	103.6	103.4	103.2	103.0
107.5°	133.7	133.4	133.0	132.6	132.3	131.9	131.7	131.5	131.4	131.3	131.2
110°	151.0	150.6	150.4	150.2	150.0	149.8	149.6	149.4	149.2	149.0	148.8



TEST NUMBER: P332181-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	168.2	167.7	167.7	167.7	167.6	167.6	167.5	167.4	167.3	167.1	167.0
115°	195.1	195.0	195.2	195.4	195.6	195.8	195.7	195.4	195.1	194.8	194.5
117.5°	221.9	221.9	222.2	222.4	222.7	222.9	223.0	222.8	222.6	222.4	222.2
120°	239.7	239.8	240.3	240.9	241.4	241.9	241.8	241.2	240.5	239.9	239.3
122.5°	257.8	258.1	258.4	258.6	258.9	259.1	259.0	258.6	258.2	257.7	257.3
125°	284.7	285.1	285.3	285.5	285.7	285.9	285.9	285.6	285.3	285.0	284.7
127.5°	311.2	311.8	312.0	312.3	312.6	312.8	312.6	311.8	311.2	310.5	309.9
130°	328.6	329.0	329.3	329.6	329.9	330.2	330.0	329.2	328.4	327.6	326.8
132.5°	345.8	346.3	346.5	346.7	346.9	347.2	346.9	346.1	345.3	344.4	343.6
135°	371.2	371.6	371.7	371.8	371.9	372.0	371.7	371.1	370.5	369.9	369.3
137.5°	396.2	396.6	396.4	396.1	395.8	395.6	395.2	394.7	394.2	393.6	393.1
140°	412.2	412.3	412.2	412.1	412.0	411.9	411.6	411.1	410.6	410.1	409.6
142.5°	427.6	427.7	427.6	427.4	427.2	427.0	426.7	426.2	425.7	425.2	424.6
145°	450.2	450.3	450.0	449.7	449.4	449.1	448.9	448.7	448.5	448.3	448.1
147.5°	471.5	471.5	471.2	470.9	470.6	470.3	470.0	469.6	469.3	468.9	468.6
150°	484.6	484.6	484.4	484.2	484.0	483.8	483.6	483.4	483.2	483.0	482.8
152.5°	496.6	496.3	496.2	496.1	495.9	495.8	495.6	495.3	495.1	494.8	494.5
155°	513.9	513.5	513.4	513.3	513.2	513.1	513.0	513.0	513.0	513.0	513.0
157.5°	529.0	528.6	528.5	528.5	528.4	528.3	528.3	528.4	528.6	528.7	528.8
160°	538.3	537.8	537.8	537.8	537.8	537.8	537.9	538.1	538.3	538.5	538.7
162.5°	547.0	546.5	546.4	546.3	546.2	546.2	546.3	546.5	546.8	547.1	547.4
165°	558.1	557.4	557.4	557.4	557.4	557.4	557.5	557.8	558.2	558.5	558.8
167.5°	567.0	566.3	566.3	566.2	566.1	566.0	566.2	566.6	567.0	567.4	567.8
170°	571.9	571.2	571.2	571.2	571.2	571.2	571.4	571.8	572.2	572.6	573.0
172.5°	575.8	575.1	575.1	575.1	575.1	575.1	575.3	575.8	576.2	576.6	577.0
175°	580.0	579.4	579.4	579.4	579.4	579.4	579.6	580.0	580.4	580.8	581.2
177.5°	582.0	581.5	581.5	581.5	581.5	581.5	581.7	582.0	582.3	582.6	583.0
180°	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6



TEST NUMBER: P332181-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1427.1	1430.0	1439.3	1445.9	1453.6	1457.9	1462.4	1465.7	1470.1	1471.2	1487.1
5°	1433.5	1447.2	1471.3	1489.1	1511.2	1535.2	1551.7	1559.2	1579.2	1595.7	1628.7
7.5°	1431.7	1461.0	1497.3	1534.9	1575.4	1612.8	1645.2	1683.6	1711.0	1752.1	1792.6
10°	1430.1	1469.3	1516.0	1564.1	1620.4	1672.6	1719.4	1771.6	1814.9	1872.0	1920.8
12.5°	1425.1	1472.6	1537.4	1594.3	1662.7	1734.7	1804.0	1871.1	1909.5	2004.5	2049.4
15°	1412.9	1469.3	1550.3	1636.9	1731.1	1816.2	1904.2	1974.4	2087.7	2170.9	2223.8
17.5°	1389.6	1468.4	1564.6	1669.1	1783.5	1895.8	1995.5	2101.9	2222.1	2322.8	2429.9
20°	1378.6	1465.1	1572.4	1687.8	1806.6	1933.8	2047.2	2175.0	2306.2	2405.2	2542.6
22.5°	1358.2	1456.3	1571.8	1700.4	1827.6	1959.0	2091.7	2220.6	2372.3	2508.6	2639.4
25°	1324.9	1434.9	1554.5	1698.1	1847.2	1979.1	2137.9	2309.1	2467.1	2642.3	2772.9
27.5°	1290.0	1407.3	1527.2	1660.8	1821.2	1977.8	2177.5	2370.9	2564.0	2715.4	2812.1
30°	1263.0	1377.2	1500.9	1635.6	1794.3	1980.5	2203.8	2414.8	2603.1	2733.0	2787.3
32.5°	1234.0	1349.7	1459.1	1600.3	1769.6	1978.8	2220.4	2440.6	2605.4	2691.8	2681.2
35°	1188.2	1285.1	1391.6	1527.6	1727.0	1966.8	2230.0	2443.0	2544.1	2525.5	2385.3
37.5°	1122.2	1203.7	1308.6	1457.5	1677.5	1941.4	2210.7	2370.6	2364.0	2212.9	2009.8
40°	1081.0	1150.3	1251.4	1408.1	1639.0	1924.9	2180.5	2284.3	2196.4	1985.3	1742.0
42.5°	1027.1	1091.0	1192.0	1353.1	1596.7	1891.3	2122.7	2152.8	1980.7	1738.0	1515.0
45°	943.5	999.9	1104.3	1270.6	1533.2	1818.4	1981.9	1908.3	1676.8	1425.9	1256.2
47.5°	853.7	912.3	1012.8	1183.7	1441.4	1708.5	1786.5	1630.0	1392.3	1188.8	1033.0
50°	797.2	853.5	951.8	1124.3	1379.2	1618.4	1650.6	1448.7	1230.1	1051.5	923.6
52.5°	740.0	793.0	889.7	1062.7	1306.7	1513.9	1494.0	1288.1	1087.1	934.8	834.6
55°	654.9	705.1	797.2	959.4	1181.3	1345.5	1273.4	1076.8	910.6	792.3	716.1
57.5°	578.8	626.8	706.3	852.8	1045.8	1158.6	1066.8	901.2	769.0	678.0	621.1
60°	527.0	569.7	645.3	781.3	949.1	1034.9	944.2	797.9	686.5	613.7	562.8
62.5°	478.2	515.2	585.3	708.8	854.4	926.7	834.9	710.9	616.1	551.6	508.4
65°	404.0	437.8	499.6	595.8	715.4	763.5	684.5	584.1	510.6	462.5	433.6
67.5°	336.5	365.1	418.5	494.2	582.2	617.2	557.0	479.4	424.0	385.4	362.4
70°	291.3	316.1	358.0	423.3	503.0	529.9	473.5	409.6	369.0	338.1	316.8
72.5°	253.5	271.6	309.6	360.1	426.6	447.9	408.6	352.4	314.6	291.3	274.5
75°	193.1	208.2	233.0	273.5	319.5	331.9	302.4	267.3	241.9	225.4	212.4
77.5°	139.3	150.4	168.2	193.3	225.1	236.3	217.5	194.2	175.6	164.5	157.2
80°	105.1	114.1	129.2	149.8	169.1	175.2	164.2	146.3	133.3	127.1	121.0
82.5°	77.7	82.7	91.8	105.8	119.1	126.3	116.9	106.2	99.3	93.6	91.3
85°	39.2	41.9	46.0	51.5	59.8	62.5	59.1	56.4	52.2	48.8	48.8
87.5°	14.5	14.7	16.7	18.0	20.4	22.3	22.0	21.2	20.9	20.4	20.0
90°	1.5	2.5	3.5	4.5	5.7	7.0	8.4	9.7	11.0	11.4	11.8
92.5°	11.8	12.4	13.1	13.8	14.5	15.3	16.1	16.9	17.6	17.9	18.2
95°	27.7	28.4	29.2	29.9	30.6	31.4	32.2	33.0	33.8	34.2	34.6
97.5°	48.5	49.0	49.6	50.1	50.6	51.2	51.8	52.4	53.0	53.4	53.9
100°	62.8	63.4	64.0	64.6	65.2	65.7	66.2	66.8	67.3	67.6	67.9
102.5°	79.1	79.5	79.8	80.2	80.7	81.4	82.0	82.7	83.4	83.7	84.0
105°	103.2	103.4	103.6	103.8	104.3	105.2	106.1	107.0	108.0	108.0	108.0
107.5°	131.3	131.4	131.5	131.7	131.9	132.3	132.6	133.0	133.4	133.7	134.0
110°	149.0	149.2	149.4	149.6	149.8	150.0	150.2	150.4	150.6	151.0	151.4



TEST NUMBER: P332181-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	167.1	167.3	167.4	167.5	167.6	167.6	167.7	167.7	167.7	168.2	168.7
115°	194.8	195.1	195.4	195.7	195.8	195.6	195.4	195.2	195.0	195.1	195.2
117.5°	222.4	222.6	222.8	223.0	222.9	222.7	222.4	222.2	221.9	221.9	221.9
120°	239.9	240.5	241.2	241.8	241.9	241.4	240.9	240.3	239.8	239.7	239.6
122.5°	257.7	258.2	258.6	259.0	259.1	258.9	258.6	258.4	258.1	257.8	257.6
125°	285.0	285.3	285.6	285.9	285.9	285.7	285.5	285.3	285.1	284.7	284.3
127.5°	310.5	311.2	311.8	312.6	312.8	312.6	312.3	312.0	311.8	311.2	310.7
130°	327.6	328.4	329.2	330.0	330.2	329.9	329.6	329.3	329.0	328.6	328.2
132.5°	344.4	345.3	346.1	346.9	347.2	346.9	346.7	346.5	346.3	345.8	345.3
135°	369.9	370.5	371.1	371.7	372.0	371.9	371.8	371.7	371.6	371.2	370.8
137.5°	393.6	394.2	394.7	395.2	395.6	395.8	396.1	396.4	396.6	396.2	395.8
140°	410.1	410.6	411.1	411.6	411.9	412.0	412.1	412.2	412.3	412.2	412.1
142.5°	425.2	425.7	426.2	426.7	427.0	427.2	427.4	427.6	427.7	427.6	427.5
145°	448.3	448.5	448.7	448.9	449.1	449.4	449.7	450.0	450.3	450.2	450.1
147.5°	468.9	469.3	469.6	470.0	470.3	470.6	470.9	471.2	471.5	471.5	471.5
150°	483.0	483.2	483.4	483.6	483.8	484.0	484.2	484.4	484.6	484.6	484.6
152.5°	494.8	495.1	495.3	495.6	495.8	495.9	496.1	496.2	496.3	496.6	496.7
155°	513.0	513.0	513.0	513.0	513.1	513.2	513.3	513.4	513.5	513.9	514.3
157.5°	528.7	528.6	528.4	528.3	528.3	528.4	528.5	528.5	528.6	529.0	529.5
160°	538.5	538.3	538.1	537.9	537.8	537.8	537.8	537.8	537.8	538.3	538.8
162.5°	547.1	546.8	546.5	546.3	546.2	546.2	546.3	546.4	546.5	547.0	547.5
165°	558.5	558.2	557.8	557.5	557.4	557.4	557.4	557.4	557.4	558.1	558.7
167.5°	567.4	567.0	566.6	566.2	566.0	566.1	566.2	566.3	566.3	567.0	567.6
170°	572.6	572.2	571.8	571.4	571.2	571.2	571.2	571.2	571.2	571.9	572.6
172.5°	576.6	576.2	575.8	575.3	575.1	575.1	575.1	575.1	575.1	575.8	576.4
175°	580.8	580.4	580.0	579.6	579.4	579.4	579.4	579.4	579.4	580.0	580.6
177.5°	582.6	582.3	582.0	581.7	581.5	581.5	581.5	581.5	581.5	582.0	582.5
180°	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6



TEST NUMBER: P332181-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1492.6	1493.2	1499.2	1503.6	1501.4	1504.2	1505.2
5°	1630.7	1655.5	1668.5	1678.2	1678.8	1679.5	1685.1
7.5°	1826.5	1853.1	1872.5	1901.9	1910.7	1920.8	1917.8
10°	1969.5	2008.7	2042.4	2060.2	2079.5	2107.7	2085.0
12.5°	2103.1	2172.5	2223.8	2251.6	2269.7	2275.3	2264.2
15°	2323.4	2414.2	2463.0	2461.5	2523.5	2550.2	2508.3
17.5°	2525.5	2609.2	2676.2	2710.6	2762.2	2773.6	2768.3
20°	2649.2	2740.6	2792.8	2851.9	2878.7	2902.8	2906.9
22.5°	2755.8	2837.9	2894.0	2943.2	2965.6	2977.0	2983.8
25°	2865.6	2930.2	2964.0	2981.1	2987.3	2985.9	2977.0
27.5°	2858.1	2863.1	2825.9	2789.6	2756.9	2720.3	2707.5
30°	2783.9	2726.1	2623.0	2564.7	2478.7	2410.7	2438.2
32.5°	2588.7	2473.8	2358.0	2230.4	2124.7	2094.6	2064.4
35°	2209.4	2007.3	1889.2	1751.7	1696.7	1641.7	1604.0
37.5°	1787.5	1631.1	1491.0	1401.1	1345.9	1311.2	1292.5
40°	1545.5	1404.6	1289.2	1216.4	1174.5	1135.3	1129.7
42.5°	1352.5	1221.5	1134.7	1076.7	1036.4	1019.8	1007.7
45°	1107.8	1016.3	958.0	916.8	889.9	879.6	865.9
47.5°	937.7	873.0	829.2	801.1	780.9	773.3	772.1
50°	842.5	788.9	756.6	734.6	718.8	716.1	705.1
52.5°	771.0	724.6	699.4	680.2	668.8	661.1	657.8
55°	669.3	638.4	615.7	604.7	595.8	588.2	588.2
57.5°	585.6	559.8	544.8	535.4	532.7	527.4	523.9
60°	533.9	512.0	500.3	492.0	486.6	487.3	481.0
62.5°	483.4	469.1	458.0	449.7	443.1	443.2	443.6
65°	411.6	400.6	392.4	389.6	385.6	380.7	382.1
67.5°	348.8	338.5	332.0	327.4	326.0	323.4	327.4
70°	303.8	296.2	291.3	287.2	285.9	286.6	290.0
72.5°	262.5	257.1	254.0	252.1	249.0	249.1	251.6
75°	206.1	202.1	199.2	197.2	196.5	196.5	196.5
77.5°	151.5	150.5	149.3	146.2	146.3	147.2	147.3
80°	119.6	117.5	116.8	115.4	113.4	112.0	115.4
82.5°	89.4	87.3	86.5	86.3	83.1	82.9	85.7
85°	48.1	46.0	46.8	46.0	46.0	45.3	45.3
87.5°	19.5	19.0	18.5	19.1	18.6	18.1	19.3
90°	12.2	12.6	12.9	13.1	13.3	13.5	13.7
92.5°	18.6	18.9	19.0	18.9	18.7	18.6	18.5
95°	35.0	35.4	35.6	35.6	35.6	35.6	35.6
97.5°	54.4	54.8	55.0	55.0	55.0	54.9	54.9
100°	68.2	68.5	68.8	69.0	69.2	69.4	69.6
102.5°	84.3	84.6	84.7	84.7	84.6	84.6	84.5
105°	108.0	108.0	108.1	108.4	108.6	108.8	109.0
107.5°	134.3	134.6	134.7	134.6	134.5	134.4	134.3
110°	151.8	152.2	152.3	152.1	151.9	151.7	151.5



TEST NUMBER: P332181-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	169.3	169.8	170.0	169.9	169.9	169.9	169.8
115°	195.3	195.4	195.4	195.3	195.2	195.1	195.0
117.5°	221.8	221.8	221.7	221.4	221.1	220.8	220.5
120°	239.5	239.4	239.2	239.0	238.8	238.6	238.4
122.5°	257.3	257.0	256.8	256.5	256.2	255.9	255.6
125°	283.9	283.5	283.1	282.7	282.3	281.9	281.4
127.5°	310.1	309.5	309.0	308.6	308.1	307.6	307.2
130°	327.8	327.4	326.9	326.2	325.5	324.8	324.0
132.5°	344.8	344.3	343.8	343.3	342.6	342.1	341.5
135°	370.4	370.0	369.7	369.5	369.3	369.1	368.9
137.5°	395.4	394.9	394.5	394.0	393.7	393.3	392.9
140°	412.0	411.9	411.5	410.8	410.1	409.4	408.7
142.5°	427.4	427.3	427.0	426.5	425.9	425.4	424.7
145°	450.0	449.9	449.7	449.3	448.9	448.5	448.1
147.5°	471.5	471.5	471.2	470.6	469.9	469.3	468.7
150°	484.6	484.6	484.3	483.7	483.1	482.5	481.9
152.5°	496.9	497.1	496.9	496.3	495.7	495.2	494.7
155°	514.7	515.1	514.9	514.2	513.5	512.8	512.1
157.5°	529.9	530.3	530.2	529.7	529.1	528.5	528.0
160°	539.3	539.8	539.8	539.4	539.0	538.6	538.2
162.5°	548.1	548.6	548.5	547.9	547.1	546.5	545.8
165°	559.3	559.9	559.8	559.1	558.4	557.6	556.9
167.5°	568.3	568.9	568.9	568.3	567.6	567.0	566.3
170°	573.3	574.0	574.0	573.3	572.6	571.9	571.2
172.5°	577.0	577.6	577.6	576.9	576.2	575.5	574.8
175°	581.2	581.8	581.8	581.1	580.4	579.7	579.0
177.5°	583.0	583.4	583.4	582.8	582.3	581.7	581.1
180°	582.6	582.6	582.6	582.6	582.6	582.6	582.6

(END OF REPORT)