

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332185-840

Luminaire Tested: **S123DIW-S1000D460U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332185-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S1000D460U840-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5775.3 lumens  
Efficiency: N/A  
Efficacy: 125.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 46.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332185-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332185-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76	72
1	103	98	94	90	97	93	90	86	84	81	79	75	73	71	67	66	64	61
2	93	86	79	74	88	81	76	71	73	69	65	66	63	59	59	57	54	51
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	53	49	46	43
4	78	67	58	52	74	64	56	50	58	52	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	42	37	42	38	35	32
6	66	54	45	39	63	51	43	38	47	40	35	42	37	33	38	34	30	28
7	61	49	40	34	58	46	39	33	42	36	31	39	33	29	35	31	27	25
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	22
9	53	40	33	27	50	39	32	27	36	29	25	33	27	24	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17206	17206	17206
5°	17286	17049	17168
10°	17171	16901	17006
15°	16971	16710	16741
20°	16736	16436	16452
25°	16422	16112	16079
30°	16075	15751	15631
35°	15713	15369	15172
40°	15336	14948	14716
45°	14918	14562	14206
50°	14502	14086	13695
55°	13955	13594	13181
60°	13403	13020	12605
65°	12918	12394	12006
70°	12198	11679	11160
75°	11146	10746	10289
80°	10054	9627	9540
85°	8830	8497	8139



TEST NUMBER: P332185-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	150.6	2.6
10°-20°	425.2	7.4
20°-30°	628.0	10.9
30°-40°	733.6	12.7
40°-50°	737.6	12.8
50°-60°	647.9	11.2
60°-70°	482.7	8.4
70°-80°	275.0	4.8
80°-90°	80.7	1.4
90°-100°	37.9	0.7
100°-110°	113.6	2.0
110°-120°	193.2	3.3
120°-130°	254.1	4.4
130°-140°	285.6	4.9
140°-150°	280.8	4.9
150°-160°	236.4	4.1
160°-170°	157.3	2.7
170°-180°	55.1	1.0
0°-30°	1203.8	20.8
0°-40°	1937.4	33.5
0°-60°	3322.8	57.5
0°-90°	4161.2	72.1
90°-120°	344.8	6.0
90°-150°	1165.3	20.2
90°-180°	1614.0	27.9
0°-180°	5775.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1598	1598	1598	1598	1598	
5°	1600	1593	1578	1591	1589	152
15°	1523	1517	1500	1509	1502	429
25°	1383	1374	1357	1358	1354	637
35°	1196	1187	1170	1162	1155	748
45°	980	974	957	941	933	756
55°	744	741	724	710	702	666
65°	507	500	487	476	471	500
75°	268	263	258	252	247	287
85°	72	69	69	66	66	78
90°	0	5	11	13	14	6
95°	27	30	34	36	36	30
105°	103	104	108	108	109	110
115°	194	196	195	195	195	192
125°	285	286	285	283	281	254
135°	369	372	372	370	369	284
145°	448	449	450	450	448	280
155°	513	513	514	515	512	236
165°	559	557	557	560	557	157
175°	581	580	579	582	579	55
180°	583	583	583	583	583	



TEST NUMBER: P332185-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1604.0	1603.1	1602.0	1601.0	1600.1	1598.2	1595.6	1592.9	1590.2	1587.5	1589.9
5°	1599.8	1598.3	1596.8	1595.3	1593.8	1591.3	1588.0	1584.6	1581.2	1577.9	1580.9
7.5°	1584.2	1582.7	1581.1	1579.6	1578.1	1575.6	1572.2	1568.6	1565.2	1561.7	1564.4
10°	1571.0	1569.5	1567.9	1566.4	1564.9	1562.2	1558.2	1554.2	1550.2	1546.3	1549.0
12.5°	1553.4	1552.2	1550.8	1549.5	1548.3	1545.8	1542.1	1538.3	1534.6	1530.9	1532.9
15°	1522.9	1521.7	1520.5	1519.2	1518.0	1515.4	1511.5	1507.5	1503.5	1499.5	1502.0
17.5°	1487.4	1485.8	1484.3	1482.7	1481.1	1478.3	1474.3	1470.4	1466.4	1462.4	1464.1
20°	1461.1	1459.3	1457.4	1455.5	1453.7	1450.8	1446.8	1442.9	1439.0	1434.9	1436.1
22.5°	1431.4	1429.6	1427.7	1425.8	1424.0	1421.2	1417.1	1413.2	1409.3	1405.2	1406.2
25°	1382.7	1380.9	1379.1	1377.3	1375.3	1372.5	1368.5	1364.5	1360.6	1356.6	1356.9
27.5°	1330.8	1329.0	1327.2	1325.4	1323.6	1320.6	1316.4	1312.1	1307.8	1303.5	1303.7
30°	1293.3	1291.8	1290.3	1288.8	1287.3	1284.3	1280.1	1275.8	1271.5	1267.3	1267.3
32.5°	1256.0	1253.9	1251.9	1249.9	1247.9	1245.3	1241.9	1238.7	1235.4	1232.0	1230.3
35°	1195.8	1194.0	1192.1	1190.3	1188.4	1185.6	1181.5	1177.6	1173.7	1169.6	1167.8
37.5°	1134.2	1131.9	1129.5	1127.2	1124.9	1121.8	1117.7	1113.7	1109.6	1105.6	1103.4
40°	1091.4	1089.4	1087.6	1085.8	1084.0	1081.0	1076.6	1072.4	1068.1	1063.8	1061.4
42.5°	1048.4	1046.3	1044.3	1042.2	1040.2	1036.9	1032.7	1028.4	1024.1	1019.9	1017.4
45°	980.0	978.8	977.5	976.3	975.1	972.5	968.6	964.5	960.6	956.6	953.0
47.5°	912.1	910.3	908.6	906.8	905.0	902.2	898.6	894.8	891.1	887.4	883.7
50°	866.0	864.3	862.8	861.3	859.8	857.1	853.0	849.1	845.2	841.2	837.8
52.5°	817.5	816.5	815.5	814.5	813.3	810.7	806.6	802.3	798.1	793.9	791.0
55°	743.6	743.3	743.0	742.7	742.4	740.2	736.3	732.3	728.3	724.4	720.9
57.5°	673.2	672.2	671.2	670.1	669.0	666.9	663.8	660.6	657.4	654.3	651.3
60°	622.6	622.3	622.0	621.7	621.4	619.5	615.7	612.1	608.4	604.8	602.0
62.5°	577.5	576.7	575.9	575.1	574.4	572.2	568.5	564.8	561.2	557.4	554.7
65°	507.2	505.6	504.1	502.6	501.1	498.8	495.7	492.7	489.6	486.6	484.1
67.5°	432.7	431.3	430.0	428.7	427.3	425.5	423.1	420.8	418.5	416.2	414.0
70°	387.6	385.8	384.0	382.1	380.3	378.4	376.6	374.8	372.9	371.1	369.0
72.5°	340.3	339.0	337.6	336.3	335.0	333.3	331.1	329.1	327.0	324.9	323.1
75°	268.0	266.8	265.6	264.4	263.2	262.1	261.2	260.2	259.3	258.4	256.9
77.5°	204.0	203.3	202.6	202.0	201.3	200.4	199.3	198.2	197.1	196.0	195.0
80°	162.2	161.3	160.4	159.5	158.5	157.7	157.1	156.5	155.9	155.3	155.0
82.5°	121.5	121.3	121.2	121.0	120.8	120.6	120.5	120.4	120.3	120.2	119.6
85°	71.5	70.9	70.3	69.7	69.1	68.8	68.8	68.8	68.8	68.8	68.1
87.5°	28.7	28.2	27.7	27.1	26.6	26.3	26.4	26.4	26.4	26.4	26.3
90°	0.5	1.5	2.5	3.5	4.5	5.7	7.0	8.4	9.7	11.0	11.4
92.5°	11.1	11.8	12.4	13.1	13.8	14.5	15.3	16.1	16.9	17.6	17.9
95°	27.0	27.7	28.4	29.2	29.9	30.6	31.4	32.2	33.0	33.8	34.2
97.5°	48.0	48.5	49.0	49.6	50.1	50.6	51.2	51.8	52.4	53.0	53.4
100°	62.2	62.8	63.4	64.0	64.6	65.2	65.7	66.2	66.8	67.3	67.6
102.5°	78.7	79.1	79.5	79.8	80.2	80.7	81.4	82.0	82.7	83.4	83.7
105°	103.0	103.2	103.4	103.6	103.8	104.3	105.2	106.1	107.0	108.0	108.0
107.5°	131.2	131.3	131.4	131.5	131.7	131.9	132.3	132.6	133.0	133.4	133.7
110°	148.8	149.0	149.2	149.4	149.6	149.8	150.0	150.2	150.4	150.6	151.0



TEST NUMBER: P332185-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.0	167.1	167.3	167.4	167.5	167.6	167.6	167.7	167.7	167.7	168.2
115°	194.5	194.8	195.1	195.4	195.7	195.8	195.6	195.4	195.2	195.0	195.1
117.5°	222.2	222.4	222.6	222.8	223.0	222.9	222.7	222.4	222.2	221.9	221.9
120°	239.3	239.9	240.5	241.2	241.8	241.9	241.4	240.9	240.3	239.8	239.7
122.5°	257.3	257.7	258.2	258.6	259.0	259.1	258.9	258.6	258.4	258.1	257.8
125°	284.7	285.0	285.3	285.6	285.9	285.9	285.7	285.5	285.3	285.1	284.7
127.5°	309.9	310.5	311.2	311.8	312.6	312.8	312.6	312.3	312.0	311.8	311.2
130°	326.8	327.6	328.4	329.2	330.0	330.2	329.9	329.6	329.3	329.0	328.6
132.5°	343.6	344.4	345.3	346.1	346.9	347.2	346.9	346.7	346.5	346.3	345.8
135°	369.3	369.9	370.5	371.1	371.7	372.0	371.9	371.8	371.7	371.6	371.2
137.5°	393.1	393.6	394.2	394.7	395.2	395.6	395.8	396.1	396.4	396.6	396.2
140°	409.6	410.1	410.6	411.1	411.6	411.9	412.0	412.1	412.2	412.3	412.2
142.5°	424.6	425.2	425.7	426.2	426.7	427.0	427.2	427.4	427.6	427.7	427.6
145°	448.1	448.3	448.5	448.7	448.9	449.1	449.4	449.7	450.0	450.3	450.2
147.5°	468.6	468.9	469.3	469.6	470.0	470.3	470.6	470.9	471.2	471.5	471.5
150°	482.8	483.0	483.2	483.4	483.6	483.8	484.0	484.2	484.4	484.6	484.6
152.5°	494.5	494.8	495.1	495.3	495.6	495.8	495.9	496.1	496.2	496.3	496.6
155°	513.0	513.0	513.0	513.0	513.0	513.1	513.2	513.3	513.4	513.5	513.9
157.5°	528.8	528.7	528.6	528.4	528.3	528.3	528.4	528.5	528.5	528.6	529.0
160°	538.7	538.5	538.3	538.1	537.9	537.8	537.8	537.8	537.8	537.8	538.3
162.5°	547.4	547.1	546.8	546.5	546.3	546.2	546.2	546.3	546.4	546.5	547.0
165°	558.8	558.5	558.2	557.8	557.5	557.4	557.4	557.4	557.4	557.4	558.1
167.5°	567.8	567.4	567.0	566.6	566.2	566.0	566.1	566.2	566.3	566.3	567.0
170°	573.0	572.6	572.2	571.8	571.4	571.2	571.2	571.2	571.2	571.2	571.9
172.5°	577.0	576.6	576.2	575.8	575.3	575.1	575.1	575.1	575.1	575.1	575.8
175°	581.2	580.8	580.4	580.0	579.6	579.4	579.4	579.4	579.4	579.4	580.0
177.5°	583.0	582.6	582.3	582.0	581.7	581.5	581.5	581.5	581.5	581.5	582.0
180°	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6



TEST NUMBER: P332185-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1592.4	1594.9	1597.3	1598.4	1598.1	1597.9	1597.6	1597.4
5°	1584.0	1587.0	1590.1	1591.3	1590.7	1590.1	1589.5	1588.9
7.5°	1567.2	1569.9	1572.7	1573.9	1573.5	1573.2	1572.8	1572.4
10°	1551.8	1554.5	1557.3	1558.3	1557.7	1557.1	1556.5	1555.9
12.5°	1534.9	1536.9	1538.9	1539.7	1539.4	1539.0	1538.6	1538.3
15°	1504.4	1506.8	1509.3	1509.6	1507.8	1505.9	1504.1	1502.3
17.5°	1465.8	1467.5	1469.3	1469.8	1469.2	1468.4	1467.7	1467.1
20°	1437.3	1438.7	1439.9	1440.0	1439.1	1438.1	1437.2	1436.3
22.5°	1407.2	1408.2	1409.2	1409.1	1408.0	1406.7	1405.6	1404.4
25°	1357.2	1357.6	1357.9	1357.6	1356.6	1355.6	1354.7	1353.8
27.5°	1304.0	1304.2	1304.5	1304.0	1302.9	1301.7	1300.6	1299.4
30°	1267.3	1267.3	1267.3	1266.2	1264.0	1261.9	1259.8	1257.6
32.5°	1228.6	1227.0	1225.3	1223.8	1222.6	1221.4	1220.3	1219.1
35°	1166.0	1164.2	1162.4	1160.6	1159.1	1157.6	1156.1	1154.6
37.5°	1101.3	1099.0	1096.8	1095.2	1094.3	1093.3	1092.3	1091.4
40°	1058.9	1056.5	1054.1	1052.2	1051.0	1049.8	1048.5	1047.3
42.5°	1014.9	1012.5	1010.1	1008.2	1007.0	1005.8	1004.6	1003.4
45°	949.3	945.6	942.0	939.4	937.9	936.3	934.8	933.2
47.5°	880.1	876.6	872.9	870.5	869.1	867.8	866.5	865.1
50°	834.5	831.1	827.7	825.2	823.3	821.4	819.6	817.8
52.5°	788.1	785.3	782.4	780.0	778.2	776.4	774.6	772.7
55°	717.6	714.3	710.9	708.4	706.9	705.4	703.9	702.4
57.5°	648.2	645.3	642.3	639.9	638.1	636.3	634.6	632.8
60°	599.3	596.5	593.8	591.7	590.1	588.5	587.0	585.5
62.5°	552.0	549.3	546.4	544.6	543.5	542.5	541.5	540.5
65°	481.7	479.2	476.8	475.1	474.2	473.3	472.3	471.4
67.5°	411.9	409.8	407.7	406.0	404.7	403.3	402.0	400.8
70°	366.8	364.7	362.5	360.7	359.2	357.7	356.2	354.6
72.5°	321.1	319.2	317.3	316.0	315.2	314.4	313.7	312.9
75°	255.4	253.8	252.3	251.1	250.1	249.2	248.3	247.4
77.5°	193.9	192.9	191.9	191.4	191.4	191.4	191.4	191.4
80°	154.7	154.4	154.1	153.9	153.9	153.9	153.9	153.9
82.5°	119.1	118.5	118.0	117.5	117.2	117.0	116.8	116.5
85°	67.5	66.9	66.2	65.9	65.9	65.9	65.9	65.9
87.5°	26.1	25.9	25.8	25.7	25.8	25.8	25.8	25.9
90°	11.8	12.2	12.6	12.9	13.1	13.3	13.5	13.7
92.5°	18.2	18.6	18.9	19.0	18.9	18.7	18.6	18.5
95°	34.6	35.0	35.4	35.6	35.6	35.6	35.6	35.6
97.5°	53.9	54.4	54.8	55.0	55.0	55.0	54.9	54.9
100°	67.9	68.2	68.5	68.8	69.0	69.2	69.4	69.6
102.5°	84.0	84.3	84.6	84.7	84.7	84.6	84.6	84.5
105°	108.0	108.0	108.0	108.1	108.4	108.6	108.8	109.0
107.5°	134.0	134.3	134.6	134.7	134.6	134.5	134.4	134.3
110°	151.4	151.8	152.2	152.3	152.1	151.9	151.7	151.5





TEST NUMBER: P332185-840

CATALOG NUMBER: S123DIW-S1000D460U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	168.7	169.3	169.8	170.0	169.9	169.9	169.9	169.8
115°	195.2	195.3	195.4	195.4	195.3	195.2	195.1	195.0
117.5°	221.9	221.8	221.8	221.7	221.4	221.1	220.8	220.5
120°	239.6	239.5	239.4	239.2	239.0	238.8	238.6	238.4
122.5°	257.6	257.3	257.0	256.8	256.5	256.2	255.9	255.6
125°	284.3	283.9	283.5	283.1	282.7	282.3	281.9	281.4
127.5°	310.7	310.1	309.5	309.0	308.6	308.1	307.6	307.2
130°	328.2	327.8	327.4	326.9	326.2	325.5	324.8	324.0
132.5°	345.3	344.8	344.3	343.8	343.3	342.6	342.1	341.5
135°	370.8	370.4	370.0	369.7	369.5	369.3	369.1	368.9
137.5°	395.8	395.4	394.9	394.5	394.0	393.7	393.3	392.9
140°	412.1	412.0	411.9	411.5	410.8	410.1	409.4	408.7
142.5°	427.5	427.4	427.3	427.0	426.5	425.9	425.4	424.7
145°	450.1	450.0	449.9	449.7	449.3	448.9	448.5	448.1
147.5°	471.5	471.5	471.5	471.2	470.6	469.9	469.3	468.7
150°	484.6	484.6	484.6	484.3	483.7	483.1	482.5	481.9
152.5°	496.7	496.9	497.1	496.9	496.3	495.7	495.2	494.7
155°	514.3	514.7	515.1	514.9	514.2	513.5	512.8	512.1
157.5°	529.5	529.9	530.3	530.2	529.7	529.1	528.5	528.0
160°	538.8	539.3	539.8	539.8	539.4	539.0	538.6	538.2
162.5°	547.5	548.1	548.6	548.5	547.9	547.1	546.5	545.8
165°	558.7	559.3	559.9	559.8	559.1	558.4	557.6	556.9
167.5°	567.6	568.3	568.9	568.9	568.3	567.6	567.0	566.3
170°	572.6	573.3	574.0	574.0	573.3	572.6	571.9	571.2
172.5°	576.4	577.0	577.6	577.6	576.9	576.2	575.5	574.8
175°	580.6	581.2	581.8	581.8	581.1	580.4	579.7	579.0
177.5°	582.5	583.0	583.4	583.4	582.8	582.3	581.7	581.1
180°	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6

(END OF REPORT)