

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332100-930

Luminaire Tested: **S123DIW-S340D755U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332100-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D755U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3614.5 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332100-930

CATALOG NUMBER: S123DIW-S340D755U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332100-930

CATALOG NUMBER: S123DIW-S340D755U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	39	39	39	39	39	39	32	
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	35	34	33	27	
2	85	78	72	67	76	70	65	61	56	53	49	43	40	38	31	29	28	31	29	28	22	
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	27	25	24	19	
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	24	22	20	16	
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	22	19	18	14	
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	20	17	16	12	
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	25	21	18	11	
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	22	19	16	10	
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11	21	17	15	9	
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10	19	16	13	8	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4755	4755	4755
5°	4778	4712	4744
10°	4746	4671	4701
15°	4690	4619	4627
20°	4625	4543	4548
25°	4538	4454	4444
30°	4443	4354	4320
35°	4343	4248	4193
40°	4239	4131	4068
45°	4122	4025	3927
50°	4007	3893	3785
55°	3856	3757	3643
60°	3705	3597	3483
65°	3568	3423	3319
70°	3371	3229	3084
75°	3082	2969	2845
80°	2777	2665	2641
85°	2433	2347	2260



TEST NUMBER: P332100-930

CATALOG NUMBER: S123DIW-S340D755U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.6	1.2
10°-20°	117.5	3.3
20°-30°	173.6	4.8
30°-40°	202.8	5.6
40°-50°	203.9	5.6
50°-60°	179.1	5.0
60°-70°	133.4	3.7
70°-80°	76.0	2.1
80°-90°	24.1	0.7
90°-100°	29.4	0.8
100°-110°	139.9	3.9
110°-120°	336.1	9.3
120°-130°	428.0	11.8
130°-140°	457.3	12.7
140°-150°	427.6	11.8
150°-160°	344.9	9.5
160°-170°	222.6	6.2
170°-180°	76.7	2.1
0°-30°	332.7	9.2
0°-40°	535.5	14.8
0°-60°	918.4	25.4
0°-90°	1151.9	31.9
90°-120°	505.4	14.0
90°-150°	1818.3	50.3
90°-180°	2463.0	68.1
0°-180°	3614.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	442	442	442	442	442	
5°	442	440	436	440	439	42
15°	421	419	414	417	415	119
25°	382	380	375	375	374	176
35°	330	328	323	321	319	207
45°	271	269	264	260	258	209
55°	206	205	200	196	194	184
65°	140	138	134	132	130	138
75°	74	73	71	70	68	79
85°	20	19	19	18	18	22
90°	1	7	14	17	18	3
95°	37	14	19	23	23	45
105°	179	182	131	31	26	190
115°	335	339	344	350	353	331
125°	473	477	480	481	482	422
135°	589	592	594	596	594	453
145°	679	683	684	686	686	425
155°	748	747	748	750	747	345
165°	789	787	786	791	787	223
175°	808	805	805	809	804	77
180°	808	808	808	808	808	



TEST NUMBER: P332100-930

CATALOG NUMBER: S123DIW-S340D755U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	443.4	443.0	442.8	442.5	442.2	441.7	441.0	440.3	439.5	438.8	439.4
5°	442.2	441.7	441.3	440.9	440.5	439.9	438.9	438.0	437.0	436.1	436.9
7.5°	437.9	437.4	437.0	436.6	436.2	435.5	434.6	433.6	432.6	431.6	432.4
10°	434.2	433.8	433.3	432.9	432.5	431.8	430.6	429.6	428.4	427.4	428.1
12.5°	429.3	429.0	428.6	428.3	428.0	427.2	426.2	425.2	424.1	423.1	423.7
15°	420.9	420.6	420.2	419.9	419.6	418.8	417.8	416.6	415.6	414.5	415.2
17.5°	411.1	410.7	410.3	409.8	409.4	408.6	407.5	406.4	405.3	404.2	404.6
20°	403.8	403.3	402.8	402.3	401.8	401.0	399.9	398.8	397.7	396.6	397.0
22.5°	395.6	395.1	394.6	394.1	393.6	392.8	391.7	390.6	389.5	388.4	388.7
25°	382.1	381.6	381.2	380.7	380.2	379.4	378.2	377.2	376.0	375.0	375.0
27.5°	367.8	367.3	366.8	366.3	365.8	365.0	363.9	362.6	361.5	360.3	360.4
30°	357.5	357.0	356.6	356.2	355.8	355.0	353.8	352.6	351.5	350.3	350.3
32.5°	347.2	346.6	346.0	345.4	345.0	344.1	343.2	342.3	341.4	340.6	340.1
35°	330.5	330.0	329.5	329.0	328.5	327.7	326.6	325.5	324.4	323.3	322.8
37.5°	313.5	312.8	312.2	311.5	311.0	310.1	308.9	307.8	306.7	305.6	305.0
40°	301.7	301.1	300.6	300.1	299.6	298.7	297.6	296.4	295.2	294.0	293.3
42.5°	289.8	289.2	288.6	288.0	287.5	286.6	285.4	284.2	283.1	281.8	281.2
45°	270.8	270.5	270.2	269.9	269.5	268.8	267.7	266.6	265.5	264.4	263.4
47.5°	252.1	251.6	251.1	250.6	250.1	249.4	248.3	247.3	246.3	245.2	244.3
50°	239.3	238.9	238.5	238.1	237.7	236.8	235.8	234.7	233.6	232.5	231.5
52.5°	225.9	225.7	225.3	225.1	224.8	224.0	222.9	221.8	220.6	219.4	218.7
55°	205.5	205.5	205.4	205.3	205.2	204.6	203.5	202.4	201.3	200.2	199.3
57.5°	186.1	185.8	185.5	185.2	184.9	184.3	183.4	182.5	181.7	180.8	180.0
60°	172.1	172.0	171.9	171.9	171.8	171.2	170.2	169.2	168.2	167.1	166.4
62.5°	159.6	159.4	159.2	159.0	158.7	158.2	157.1	156.1	155.1	154.1	153.4
65°	140.1	139.7	139.3	138.9	138.5	137.9	137.1	136.2	135.3	134.4	133.8
67.5°	119.6	119.2	118.9	118.5	118.1	117.6	117.0	116.3	115.7	115.0	114.5
70°	107.1	106.6	106.2	105.6	105.1	104.6	104.1	103.5	103.1	102.6	102.0
72.5°	94.1	93.7	93.4	92.9	92.5	92.1	91.6	91.0	90.4	89.8	89.3
75°	74.1	73.7	73.4	73.1	72.7	72.4	72.2	71.9	71.7	71.4	71.0
77.5°	56.3	56.2	56.0	55.8	55.6	55.4	55.1	54.8	54.5	54.1	53.9
80°	44.8	44.6	44.4	44.1	43.8	43.6	43.5	43.3	43.1	43.0	42.8
82.5°	33.6	33.5	33.5	33.4	33.3	33.3	33.3	33.3	33.3	33.2	33.0
85°	19.7	19.6	19.4	19.2	19.1	19.0	19.0	19.0	19.0	19.0	18.8
87.5°	8.0	8.1	8.2	8.2	8.3	8.5	8.7	9.0	9.3	9.5	9.6
90°	0.6	2.0	3.3	4.6	6.0	7.5	9.2	10.9	12.6	14.4	14.9
92.5°	11.2	10.8	10.4	10.0	9.7	10.1	11.4	12.7	14.0	15.3	16.2
95°	36.6	31.1	25.7	20.2	14.8	12.7	14.2	15.7	17.1	18.6	19.6
97.5°	73.5	71.1	68.6	66.2	63.8	57.7	48.1	38.5	28.9	19.3	20.4
100°	101.4	104.0	106.7	109.4	112.0	103.0	82.2	61.4	40.6	19.8	20.9
102.5°	133.1	135.0	136.9	138.8	140.7	130.4	107.6	84.9	62.2	39.5	36.2
105°	178.8	180.3	181.7	183.2	184.7	179.4	167.4	155.4	143.4	131.4	107.8
107.5°	227.0	228.2	229.3	230.6	231.7	233.3	235.1	237.0	239.0	240.8	223.5
110°	259.2	260.2	261.3	262.4	263.4	264.7	266.2	267.7	269.1	270.6	266.2



TEST NUMBER: P332100-930

CATALOG NUMBER: S123DIW-S340D755U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	289.9	290.8	291.8	292.8	293.8	295.0	296.4	297.9	299.4	300.8	300.9
115°	335.3	336.1	337.0	337.8	338.6	339.6	340.8	341.9	343.2	344.4	345.7
117.5°	379.4	380.4	381.4	382.4	383.4	384.2	384.7	385.4	386.0	386.6	387.7
120°	406.8	408.0	409.2	410.3	411.6	412.4	412.8	413.2	413.6	413.9	415.1
122.5°	434.6	435.6	436.6	437.6	438.5	439.3	439.8	440.3	440.8	441.3	442.1
125°	472.8	473.9	474.9	476.0	477.0	477.8	478.3	478.9	479.4	480.0	480.2
127.5°	509.7	510.8	511.8	512.9	514.0	514.9	515.5	516.1	516.7	517.4	517.8
130°	532.7	533.9	534.9	536.0	537.0	537.9	538.3	538.9	539.4	540.0	540.5
132.5°	554.8	555.9	556.9	558.0	559.1	559.9	560.3	560.7	561.1	561.6	562.1
135°	588.6	589.4	590.1	590.9	591.7	592.4	593.0	593.5	594.0	594.5	594.9
137.5°	617.3	618.3	619.4	620.4	621.4	622.1	622.3	622.6	623.0	623.2	623.9
140°	636.5	637.3	638.1	639.0	639.8	640.3	640.7	641.2	641.6	642.0	642.5
142.5°	654.3	655.1	655.9	656.7	657.5	658.1	658.5	658.9	659.3	659.7	660.1
145°	679.1	680.0	681.0	681.9	682.9	683.5	683.7	684.0	684.3	684.5	684.8
147.5°	702.5	703.1	703.8	704.3	705.0	705.4	705.7	706.0	706.2	706.5	706.8
150°	717.0	717.3	717.7	718.1	718.5	718.8	719.2	719.4	719.7	719.9	720.2
152.5°	729.9	730.1	730.3	730.4	730.7	730.8	731.0	731.2	731.3	731.5	731.9
155°	748.1	747.9	747.6	747.3	747.1	747.0	747.1	747.3	747.4	747.5	748.2
157.5°	762.3	762.3	762.2	762.2	762.2	762.1	762.0	761.8	761.7	761.6	762.4
160°	770.9	770.8	770.7	770.5	770.4	770.3	770.1	770.0	769.9	769.7	770.5
162.5°	779.1	778.8	778.4	778.0	777.7	777.5	777.3	777.2	777.1	776.9	777.9
165°	789.0	788.6	788.1	787.7	787.3	787.1	786.9	786.8	786.7	786.5	787.6
167.5°	796.6	796.1	795.6	795.0	794.5	794.2	794.2	794.2	794.2	794.2	795.2
170°	801.0	800.4	799.9	799.3	798.8	798.5	798.5	798.5	798.5	798.5	799.6
172.5°	803.8	803.2	802.5	801.9	801.3	801.0	801.1	801.2	801.3	801.4	802.5
175°	807.6	806.8	806.2	805.5	804.9	804.6	804.7	804.9	805.0	805.1	806.1
177.5°	808.5	808.0	807.4	806.9	806.3	806.2	806.2	806.3	806.5	806.6	807.4
180°	807.6	807.6	807.6	807.6	807.6	807.6	807.6	807.6	807.6	807.6	807.6



TEST NUMBER: P332100-930

CATALOG NUMBER: S123DIW-S340D755U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	441.8	441.8	441.8	441.8	441.8	441.8	441.8	441.8
2.5°	440.1	440.8	441.5	441.8	441.7	441.6	441.6	441.5
5°	437.8	438.6	439.5	439.9	439.7	439.5	439.3	439.1
7.5°	433.2	433.9	434.6	435.0	434.9	434.8	434.7	434.6
10°	428.9	429.7	430.4	430.7	430.6	430.4	430.2	430.1
12.5°	424.2	424.8	425.3	425.6	425.5	425.3	425.3	425.2
15°	415.8	416.5	417.2	417.3	416.7	416.2	415.7	415.2
17.5°	405.1	405.6	406.1	406.3	406.0	405.9	405.7	405.5
20°	397.3	397.6	397.9	398.0	397.7	397.5	397.2	397.0
22.5°	388.9	389.2	389.5	389.5	389.1	388.8	388.5	388.2
25°	375.1	375.2	375.3	375.2	375.0	374.7	374.5	374.2
27.5°	360.4	360.5	360.5	360.4	360.1	359.8	359.5	359.1
30°	350.3	350.3	350.3	349.9	349.4	348.8	348.2	347.6
32.5°	339.6	339.1	338.7	338.3	337.9	337.6	337.3	337.0
35°	322.3	321.8	321.2	320.8	320.4	319.9	319.5	319.1
37.5°	304.4	303.8	303.1	302.7	302.5	302.1	301.9	301.7
40°	292.7	292.0	291.3	290.8	290.5	290.2	289.8	289.5
42.5°	280.5	279.8	279.2	278.7	278.3	278.0	277.7	277.3
45°	262.4	261.4	260.3	259.7	259.2	258.8	258.4	258.0
47.5°	243.3	242.3	241.2	240.6	240.2	239.9	239.5	239.1
50°	230.6	229.7	228.8	228.0	227.6	227.1	226.6	226.0
52.5°	217.8	217.0	216.2	215.6	215.1	214.6	214.1	213.6
55°	198.4	197.4	196.5	195.8	195.4	194.9	194.5	194.1
57.5°	179.2	178.3	177.5	176.8	176.3	175.9	175.4	174.9
60°	165.7	164.9	164.1	163.5	163.1	162.7	162.2	161.8
62.5°	152.5	151.8	151.1	150.5	150.3	149.9	149.7	149.4
65°	133.1	132.5	131.8	131.3	131.1	130.8	130.5	130.3
67.5°	113.8	113.2	112.7	112.2	111.9	111.5	111.1	110.8
70°	101.4	100.8	100.2	99.7	99.3	98.9	98.4	98.0
72.5°	88.8	88.2	87.7	87.3	87.2	86.9	86.7	86.4
75°	70.6	70.1	69.7	69.4	69.1	68.9	68.6	68.4
77.5°	53.6	53.3	53.0	52.9	52.9	52.9	52.9	52.9
80°	42.7	42.6	42.6	42.6	42.6	42.6	42.6	42.6
82.5°	32.9	32.8	32.6	32.4	32.4	32.4	32.3	32.2
85°	18.7	18.5	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	9.6	9.7	9.7	9.8	9.8	9.9	9.9	9.9
90°	15.5	16.0	16.6	17.0	17.2	17.4	17.7	18.0
92.5°	17.0	17.9	18.8	19.2	19.4	19.6	19.7	19.9
95°	20.5	21.4	22.3	22.8	22.8	22.8	22.8	22.8
97.5°	21.4	22.5	23.6	24.2	24.3	24.5	24.6	24.7
100°	21.9	23.0	24.1	24.7	24.8	24.9	25.0	25.2
102.5°	32.9	29.6	26.3	24.7	24.9	25.2	25.4	25.7
105°	84.2	60.6	37.0	25.4	25.6	25.8	26.2	26.4
107.5°	206.2	188.9	171.6	154.1	136.2	118.5	100.7	82.9
110°	261.8	257.4	253.0	241.2	222.2	203.1	184.0	165.0



TEST NUMBER: P332100-930

CATALOG NUMBER: S123DIW-S340D755U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	301.0	301.1	301.2	299.1	295.1	291.1	287.1	283.1
115°	347.1	348.4	349.7	350.7	351.1	351.7	352.2	352.8
117.5°	388.7	389.8	390.9	391.4	391.6	391.7	391.8	391.9
120°	416.1	417.2	418.2	418.7	418.7	418.7	418.7	418.7
122.5°	442.8	443.5	444.3	444.7	444.8	444.9	445.1	445.2
125°	480.5	480.8	481.0	481.3	481.6	481.8	482.1	482.3
127.5°	518.3	518.7	519.1	519.2	518.9	518.6	518.4	518.1
130°	541.0	541.5	542.1	542.3	541.9	541.7	541.4	541.1
132.5°	562.6	563.1	563.7	563.8	563.4	563.0	562.6	562.2
135°	595.3	595.7	596.1	596.1	595.7	595.3	594.9	594.5
137.5°	624.5	625.2	625.8	626.0	625.7	625.4	625.2	624.9
140°	643.0	643.5	644.1	644.2	643.9	643.7	643.4	643.1
142.5°	660.6	661.0	661.4	661.5	661.0	660.7	660.3	659.9
145°	685.1	685.3	685.6	685.7	685.7	685.7	685.7	685.7
147.5°	707.0	707.3	707.6	707.4	706.8	706.1	705.6	704.9
150°	720.5	720.7	721.0	721.0	720.6	720.2	719.7	719.3
152.5°	732.4	732.9	733.4	733.3	732.7	732.1	731.5	730.8
155°	748.9	749.5	750.2	750.2	749.3	748.5	747.7	746.9
157.5°	763.2	763.9	764.8	764.7	763.6	762.5	761.6	760.5
160°	771.4	772.2	772.9	772.9	771.9	771.0	770.1	769.2
162.5°	778.8	779.7	780.6	780.6	779.8	778.9	778.1	777.3
165°	788.6	789.7	790.8	790.8	789.9	789.0	788.1	787.1
167.5°	796.3	797.4	798.5	798.5	797.4	796.3	795.2	794.2
170°	800.6	801.8	802.8	802.8	801.8	800.6	799.6	798.5
172.5°	803.6	804.6	805.7	805.6	804.5	803.3	802.1	801.0
175°	807.0	808.0	808.9	808.8	807.7	806.7	805.6	804.5
177.5°	808.3	809.1	810.0	809.8	808.8	807.7	806.7	805.6
180°	807.6	807.6	807.6	807.6	807.6	807.6	807.6	807.6

(END OF REPORT)