

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332142-930

Luminaire Tested: **S123DIW-S560D1320U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332142-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1320U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6197.0 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332142-930

CATALOG NUMBER: S123DIW-S560D1320U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332142-930

CATALOG NUMBER: S123DIW-S560D1320U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31
1	93	89	85	82	84	80	77	74	63	61	59	48	47	45	34	33	32	26
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	30	28	27	21
3	77	68	61	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	20	16
5	65	54	46	40	58	48	42	37	39	34	30	30	26	23	21	19	17	13
6	60	48	40	34	53	43	37	32	35	30	26	27	23	20	19	17	15	12
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13	10
8	51	39	32	26	46	35	29	24	29	24	20	22	19	16	16	14	12	9
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	15	12	11	8
10	44	32	25	21	40	30	23	19	24	19	16	19	15	13	14	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7819	7819	7819
5°	7854	7747	7800
10°	7803	7679	7726
15°	7710	7592	7608
20°	7605	7468	7475
25°	7462	7321	7305
30°	7305	7157	7102
35°	7139	6984	6893
40°	6968	6792	6687
45°	6779	6616	6454
50°	6589	6400	6223
55°	6341	6176	5988
60°	6090	5916	5726
65°	5871	5631	5456
70°	5542	5306	5070
75°	5065	4882	4675
80°	4568	4376	4339
85°	4001	3853	3705



TEST NUMBER: P332142-930

CATALOG NUMBER: S123DIW-S560D1320U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.4	1.1
10°-20°	193.2	3.1
20°-30°	285.4	4.6
30°-40°	333.3	5.4
40°-50°	335.1	5.4
50°-60°	294.4	4.8
60°-70°	219.3	3.5
70°-80°	124.9	2.0
80°-90°	39.8	0.6
90°-100°	51.3	0.8
100°-110°	244.5	3.9
110°-120°	587.3	9.5
120°-130°	747.9	12.1
130°-140°	799.1	12.9
140°-150°	747.2	12.1
150°-160°	602.7	9.7
160°-170°	389.0	6.3
170°-180°	134.1	2.2
0°-30°	547.0	8.8
0°-40°	880.3	14.2
0°-60°	1509.9	24.4
0°-90°	1893.9	30.6
90°-120°	883.1	14.3
90°-150°	3177.3	51.3
90°-180°	4303.0	69.4
0°-180°	6197.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	726	726	726	726	726	
5°	727	724	717	723	722	69
15°	692	689	681	686	683	195
25°	628	624	616	617	615	289
35°	543	539	532	528	525	340
45°	445	442	435	427	424	344
55°	338	337	329	322	319	303
65°	230	227	221	216	214	227
75°	122	119	117	114	112	130
85°	32	31	31	30	30	36
90°	1	12	25	29	32	5
95°	64	24	32	40	40	79
105°	312	318	230	54	46	331
115°	586	592	602	612	616	578
125°	826	834	839	841	843	737
135°	1028	1035	1039	1042	1039	791
145°	1187	1194	1196	1198	1198	743
155°	1307	1305	1306	1311	1305	602
165°	1379	1376	1374	1382	1375	389
175°	1411	1406	1407	1413	1406	134
180°	1411	1411	1411	1411	1411	



TEST NUMBER: P332142-930

CATALOG NUMBER: S123DIW-S560D1320U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	728.8	728.4	728.0	727.5	727.1	726.2	725.0	723.7	722.6	721.4	722.4
5°	726.9	726.3	725.5	724.9	724.1	723.1	721.5	720.0	718.5	717.0	718.4
7.5°	719.8	719.2	718.4	717.8	717.1	715.9	714.4	712.7	711.2	709.6	710.9
10°	713.9	713.1	712.5	711.8	711.1	709.8	708.0	706.2	704.4	702.6	703.8
12.5°	705.9	705.2	704.7	704.1	703.5	702.4	700.7	699.0	697.3	695.6	696.5
15°	691.9	691.5	690.9	690.3	689.7	688.6	686.8	685.0	683.1	681.3	682.5
17.5°	675.9	675.1	674.4	673.7	672.9	671.7	669.9	668.1	666.3	664.5	665.3
20°	663.9	663.1	662.2	661.4	660.6	659.3	657.5	655.7	653.8	652.0	652.6
22.5°	650.4	649.5	648.7	647.9	647.0	645.7	643.9	642.1	640.3	638.5	639.0
25°	628.3	627.5	626.6	625.8	624.9	623.6	621.8	620.0	618.2	616.4	616.5
27.5°	604.7	603.9	603.1	602.3	601.4	600.1	598.1	596.2	594.3	592.3	592.4
30°	587.7	587.0	586.3	585.6	584.9	583.6	581.6	579.7	577.8	575.8	575.8
32.5°	570.7	569.8	568.8	567.9	567.0	565.8	564.4	562.8	561.3	559.9	559.1
35°	543.3	542.5	541.7	540.9	540.1	538.7	536.9	535.1	533.3	531.5	530.7
37.5°	515.4	514.3	513.2	512.2	511.1	509.7	507.8	506.1	504.2	502.4	501.4
40°	495.9	495.0	494.2	493.4	492.5	491.1	489.2	487.3	485.3	483.4	482.2
42.5°	476.4	475.5	474.5	473.5	472.6	471.2	469.2	467.3	465.4	463.4	462.3
45°	445.3	444.7	444.2	443.6	443.0	441.9	440.1	438.3	436.5	434.6	433.0
47.5°	414.4	413.6	412.9	412.1	411.2	409.9	408.3	406.6	404.9	403.2	401.5
50°	393.5	392.7	392.1	391.3	390.7	389.5	387.6	385.8	384.0	382.2	380.7
52.5°	371.5	371.0	370.6	370.1	369.6	368.4	366.5	364.6	362.6	360.8	359.5
55°	337.9	337.7	337.6	337.5	337.3	336.3	334.5	332.7	330.9	329.1	327.6
57.5°	305.9	305.4	304.9	304.5	304.0	303.0	301.6	300.2	298.7	297.3	296.0
60°	282.9	282.7	282.7	282.5	282.3	281.4	279.8	278.1	276.5	274.8	273.5
62.5°	262.4	262.0	261.7	261.4	261.0	260.0	258.3	256.7	254.9	253.3	252.1
65°	230.5	229.8	229.1	228.4	227.7	226.7	225.3	223.9	222.5	221.1	220.0
67.5°	196.6	196.0	195.3	194.8	194.1	193.3	192.2	191.2	190.1	189.1	188.2
70°	176.1	175.3	174.5	173.7	172.8	171.9	171.1	170.3	169.4	168.6	167.6
72.5°	154.7	154.0	153.4	152.8	152.2	151.4	150.5	149.5	148.5	147.7	146.8
75°	121.8	121.2	120.7	120.1	119.6	119.1	118.6	118.2	117.8	117.4	116.8
77.5°	92.7	92.4	92.0	91.8	91.5	91.1	90.6	90.1	89.5	89.0	88.6
80°	73.7	73.3	72.9	72.5	72.0	71.7	71.4	71.1	70.8	70.6	70.4
82.5°	55.2	55.1	55.0	55.0	54.9	54.8	54.8	54.7	54.6	54.6	54.3
85°	32.4	32.2	32.0	31.6	31.4	31.2	31.2	31.2	31.2	31.2	31.0
87.5°	13.2	13.4	13.5	13.6	13.7	14.0	14.5	15.0	15.5	16.1	16.1
90°	1.1	3.3	5.7	8.1	10.4	13.0	16.1	19.1	22.1	25.2	26.1
92.5°	19.5	18.8	18.2	17.5	16.9	17.7	20.0	22.3	24.5	26.8	28.3
95°	63.9	54.4	44.8	35.3	25.8	22.3	24.8	27.4	29.9	32.5	34.2
97.5°	128.5	124.3	119.9	115.7	111.4	100.9	84.1	67.3	50.5	33.8	35.6
100°	177.2	181.8	186.5	191.1	195.8	179.9	143.7	107.3	70.9	34.6	36.4
102.5°	232.5	235.9	239.2	242.6	246.0	227.8	188.1	148.4	108.7	69.0	63.2
105°	312.4	315.0	317.6	320.1	322.6	313.5	292.4	271.5	250.5	229.6	188.3
107.5°	396.7	398.8	400.8	402.8	404.9	407.6	410.9	414.2	417.5	420.8	390.5
110°	452.9	454.8	456.6	458.4	460.3	462.5	465.1	467.7	470.3	472.8	465.1



TEST NUMBER: P332142-930

CATALOG NUMBER: S123DIW-S560D1320U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	506.5	508.3	509.9	511.6	513.2	515.4	518.0	520.5	523.1	525.6	525.8
115°	586.0	587.4	588.8	590.2	591.6	593.4	595.4	597.5	599.7	601.8	604.1
117.5°	663.0	664.7	666.4	668.1	669.8	671.2	672.3	673.4	674.5	675.6	677.4
120°	710.8	712.9	714.9	717.1	719.2	720.6	721.2	721.9	722.7	723.3	725.2
122.5°	759.5	761.2	762.9	764.6	766.3	767.6	768.5	769.4	770.3	771.2	772.5
125°	826.1	827.9	829.8	831.7	833.6	834.9	835.8	836.8	837.7	838.7	839.1
127.5°	890.6	892.5	894.4	896.3	898.1	899.6	900.7	901.9	902.9	904.1	904.8
130°	930.9	932.8	934.7	936.5	938.4	939.8	940.7	941.7	942.6	943.5	944.4
132.5°	969.5	971.3	973.2	975.1	977.0	978.3	979.0	979.7	980.5	981.2	982.2
135°	1028.4	1029.8	1031.2	1032.6	1034.0	1035.2	1036.1	1037.1	1038.0	1038.9	1039.6
137.5°	1078.7	1080.5	1082.3	1084.0	1085.8	1087.0	1087.4	1088.0	1088.5	1089.0	1090.1
140°	1112.3	1113.7	1115.1	1116.5	1117.9	1118.9	1119.7	1120.3	1121.0	1121.7	1122.7
142.5°	1143.3	1144.7	1146.1	1147.5	1148.9	1150.0	1150.6	1151.4	1152.0	1152.8	1153.5
145°	1186.7	1188.4	1190.0	1191.6	1193.3	1194.3	1194.7	1195.2	1195.7	1196.1	1196.6
147.5°	1227.6	1228.7	1229.7	1230.8	1231.9	1232.7	1233.1	1233.5	1234.0	1234.5	1235.0
150°	1252.8	1253.4	1254.2	1254.8	1255.6	1256.1	1256.6	1257.0	1257.5	1258.0	1258.5
152.5°	1275.4	1275.7	1276.0	1276.4	1276.7	1277.0	1277.3	1277.6	1277.8	1278.1	1279.0
155°	1307.3	1306.8	1306.4	1305.9	1305.4	1305.3	1305.5	1305.8	1306.0	1306.2	1307.4
157.5°	1332.0	1332.0	1332.0	1331.9	1331.8	1331.7	1331.5	1331.2	1331.0	1330.7	1332.1
160°	1347.1	1346.9	1346.6	1346.4	1346.1	1346.0	1345.7	1345.5	1345.2	1345.0	1346.4
162.5°	1361.4	1360.7	1360.2	1359.5	1358.9	1358.5	1358.3	1358.0	1357.8	1357.6	1359.2
165°	1378.6	1377.9	1377.1	1376.5	1375.7	1375.3	1375.1	1374.8	1374.6	1374.4	1376.2
167.5°	1392.0	1391.1	1390.1	1389.2	1388.2	1387.8	1387.8	1387.8	1387.8	1387.8	1389.7
170°	1399.5	1398.6	1397.7	1396.8	1395.8	1395.3	1395.3	1395.3	1395.3	1395.3	1397.2
172.5°	1404.6	1403.5	1402.3	1401.2	1400.1	1399.6	1399.8	1400.0	1400.2	1400.4	1402.2
175°	1411.0	1409.9	1408.8	1407.5	1406.4	1405.9	1406.1	1406.4	1406.6	1406.9	1408.5
177.5°	1412.8	1411.8	1410.9	1410.0	1409.0	1408.7	1408.8	1409.0	1409.2	1409.4	1410.9
180°	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0



TEST NUMBER: P332142-930

CATALOG NUMBER: S123DIW-S560D1320U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	723.6	724.6	725.8	726.3	726.2	726.0	725.9	725.9
5°	719.7	721.1	722.5	723.1	722.8	722.5	722.3	721.9
7.5°	712.1	713.3	714.6	715.1	714.9	714.8	714.6	714.4
10°	705.1	706.4	707.6	708.1	707.8	707.5	707.3	706.9
12.5°	697.4	698.4	699.3	699.6	699.4	699.3	699.1	699.0
15°	683.6	684.7	685.8	685.9	685.1	684.3	683.5	682.7
17.5°	666.1	666.8	667.6	667.8	667.6	667.2	666.9	666.6
20°	653.1	653.7	654.2	654.3	653.9	653.5	653.1	652.6
22.5°	639.4	639.8	640.3	640.3	639.8	639.2	638.7	638.1
25°	616.7	616.9	616.9	616.9	616.4	616.0	615.6	615.1
27.5°	592.6	592.6	592.7	592.6	592.0	591.5	590.9	590.4
30°	575.8	575.8	575.8	575.4	574.4	573.4	572.4	571.4
32.5°	558.3	557.5	556.7	556.0	555.5	555.1	554.5	554.0
35°	529.8	529.0	528.2	527.4	526.7	526.0	525.3	524.6
37.5°	500.3	499.4	498.4	497.7	497.3	496.8	496.4	495.9
40°	481.2	480.0	479.0	478.1	477.5	477.0	476.5	475.9
42.5°	461.2	460.1	458.9	458.1	457.5	457.1	456.5	455.9
45°	431.4	429.7	428.0	426.8	426.2	425.4	424.8	424.0
47.5°	399.9	398.3	396.6	395.5	394.9	394.3	393.7	393.1
50°	379.2	377.6	376.1	375.0	374.1	373.2	372.4	371.6
52.5°	358.2	356.9	355.6	354.4	353.6	352.8	352.0	351.1
55°	326.0	324.6	323.0	321.9	321.2	320.5	319.8	319.1
57.5°	294.6	293.2	291.9	290.7	289.9	289.2	288.4	287.6
60°	272.3	271.1	269.8	268.8	268.2	267.4	266.8	266.0
62.5°	250.8	249.6	248.3	247.4	247.0	246.5	246.1	245.6
65°	218.8	217.8	216.6	215.9	215.5	215.1	214.7	214.2
67.5°	187.2	186.2	185.2	184.4	183.8	183.3	182.7	182.1
70°	166.6	165.8	164.8	163.9	163.2	162.5	161.8	161.1
72.5°	145.9	145.0	144.2	143.6	143.2	142.8	142.5	142.1
75°	116.0	115.4	114.6	114.1	113.7	113.2	112.8	112.4
77.5°	88.1	87.6	87.2	86.9	86.9	86.9	86.9	86.9
80°	70.3	70.1	70.0	70.0	70.0	70.0	70.0	70.0
82.5°	54.1	53.8	53.6	53.4	53.3	53.2	53.1	53.0
85°	30.7	30.4	30.1	30.0	30.0	30.0	30.0	30.0
87.5°	16.1	16.2	16.3	16.4	16.5	16.6	16.7	16.8
90°	27.0	28.0	28.9	29.6	30.1	30.5	31.0	31.5
92.5°	29.8	31.3	32.8	33.7	34.0	34.2	34.5	34.8
95°	35.8	37.4	39.1	39.9	39.9	39.9	39.9	39.9
97.5°	37.5	39.4	41.2	42.2	42.5	42.7	43.0	43.2
100°	38.3	40.2	42.1	43.1	43.3	43.5	43.8	44.0
102.5°	57.4	51.6	45.9	43.2	43.6	44.0	44.4	44.8
105°	147.1	105.9	64.7	44.3	44.8	45.2	45.7	46.1
107.5°	360.4	330.1	299.9	269.2	238.1	207.0	175.9	144.9
110°	457.4	449.7	442.1	421.5	388.2	354.9	321.6	288.3



TEST NUMBER: P332142-930

CATALOG NUMBER: S123DIW-S560D1320U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	525.9	526.0	526.2	522.8	515.7	508.7	501.7	494.6
115°	606.4	608.7	611.1	612.7	613.6	614.6	615.5	616.4
117.5°	679.3	681.1	683.0	684.0	684.2	684.4	684.6	684.8
120°	727.1	729.0	730.8	731.7	731.7	731.7	731.7	731.7
122.5°	773.8	775.1	776.4	777.1	777.3	777.5	777.7	777.9
125°	839.6	840.1	840.5	841.0	841.5	842.0	842.4	842.9
127.5°	905.6	906.3	907.1	907.2	906.8	906.3	905.8	905.3
130°	945.3	946.3	947.2	947.5	947.0	946.6	946.1	945.6
132.5°	983.1	984.1	985.0	985.1	984.5	983.8	983.2	982.5
135°	1040.3	1041.0	1041.7	1041.7	1041.0	1040.3	1039.6	1038.9
137.5°	1091.3	1092.3	1093.5	1093.8	1093.3	1092.9	1092.4	1091.9
140°	1123.6	1124.5	1125.4	1125.7	1125.2	1124.7	1124.3	1123.8
142.5°	1154.2	1155.0	1155.8	1155.8	1155.1	1154.5	1153.8	1153.2
145°	1197.1	1197.5	1198.0	1198.2	1198.2	1198.2	1198.2	1198.2
147.5°	1235.4	1235.9	1236.4	1236.1	1235.0	1234.0	1232.9	1231.8
150°	1258.9	1259.4	1259.9	1259.7	1259.1	1258.3	1257.7	1256.9
152.5°	1279.8	1280.7	1281.5	1281.4	1280.3	1279.2	1278.1	1277.1
155°	1308.6	1309.7	1310.9	1310.8	1309.4	1308.0	1306.6	1305.2
157.5°	1333.6	1335.0	1336.4	1336.1	1334.3	1332.5	1330.6	1328.9
160°	1347.8	1349.2	1350.6	1350.5	1348.8	1347.2	1345.6	1343.9
162.5°	1360.7	1362.4	1363.9	1364.0	1362.5	1361.1	1359.7	1358.2
165°	1378.1	1380.0	1381.9	1381.9	1380.3	1378.7	1377.0	1375.4
167.5°	1391.6	1393.3	1395.2	1395.2	1393.3	1391.6	1389.7	1387.8
170°	1399.1	1400.9	1402.8	1402.8	1400.9	1399.1	1397.2	1395.3
172.5°	1404.1	1406.0	1407.9	1407.7	1405.7	1403.6	1401.6	1399.5
175°	1410.1	1411.8	1413.4	1413.2	1411.4	1409.6	1407.7	1405.8
177.5°	1412.3	1413.9	1415.4	1415.2	1413.3	1411.4	1409.6	1407.7
180°	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0

(END OF REPORT)