

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332148-930

Luminaire Tested: **S123DIW-S560D1535U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332148-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1535U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6897.6 lumens
Efficiency: N/A
Efficacy: 113.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332148-930

CATALOG NUMBER: S123DIW-S560D1535U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332148-930

CATALOG NUMBER: S123DIW-S560D1535U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	88	85	81	83	79	76	73	62	60	58	46	45	43	31	30	30	23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	48	44	40	36	33	30	24	23	21	16
4	70	60	52	46	62	54	47	42	42	38	34	32	29	26	22	20	18	14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11	8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	14	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7819	7819	7819
5°	7854	7747	7800
10°	7803	7679	7726
15°	7710	7592	7608
20°	7605	7468	7475
25°	7462	7321	7305
30°	7305	7157	7102
35°	7139	6984	6893
40°	6968	6792	6687
45°	6779	6616	6454
50°	6589	6400	6223
55°	6341	6176	5988
60°	6090	5916	5726
65°	5871	5631	5456
70°	5542	5306	5070
75°	5065	4882	4675
80°	4568	4376	4339
85°	4001	3853	3705



TEST NUMBER: P332148-930

CATALOG NUMBER: S123DIW-S560D1535U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.4	1.0
10°-20°	193.2	2.8
20°-30°	285.4	4.1
30°-40°	333.3	4.8
40°-50°	335.1	4.9
50°-60°	294.4	4.3
60°-70°	219.3	3.2
70°-80°	124.9	1.8
80°-90°	40.5	0.6
90°-100°	59.6	0.9
100°-110°	284.3	4.1
110°-120°	682.8	9.9
120°-130°	869.5	12.6
130°-140°	929.1	13.5
140°-150°	868.8	12.6
150°-160°	700.8	10.2
160°-170°	452.3	6.6
170°-180°	155.9	2.3
0°-30°	547.0	7.9
0°-40°	880.3	12.8
0°-60°	1509.9	21.9
0°-90°	1894.6	27.5
90°-120°	1026.8	14.9
90°-150°	3694.1	53.6
90°-180°	5003.0	72.5
0°-180°	6897.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	726	726	726	726	726	
5°	727	724	717	723	722	69
15°	692	689	681	686	683	195
25°	628	624	616	617	615	289
35°	543	539	532	528	525	340
45°	445	442	435	427	424	344
55°	338	337	329	322	319	303
65°	230	227	221	216	214	227
75°	122	119	117	114	112	130
85°	32	31	31	30	30	36
90°	1	14	29	34	36	5
95°	74	28	38	46	46	92
105°	363	370	267	63	54	385
115°	681	689	700	711	717	672
125°	960	970	975	978	980	857
135°	1196	1203	1208	1211	1208	920
145°	1380	1388	1391	1393	1393	863
155°	1520	1518	1519	1524	1518	700
165°	1603	1599	1598	1607	1599	453
175°	1640	1635	1636	1643	1634	156
180°	1640	1640	1640	1640	1640	



TEST NUMBER: P332148-930

CATALOG NUMBER: S123DIW-S560D1535U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	728.8	728.4	728.0	727.5	727.1	726.2	725.0	723.7	722.6	721.4	722.4
5°	726.9	726.3	725.5	724.9	724.1	723.1	721.5	720.0	718.5	717.0	718.4
7.5°	719.8	719.2	718.4	717.8	717.1	715.9	714.4	712.7	711.2	709.6	710.9
10°	713.9	713.1	712.5	711.8	711.1	709.8	708.0	706.2	704.4	702.6	703.8
12.5°	705.9	705.2	704.7	704.1	703.5	702.4	700.7	699.0	697.3	695.6	696.5
15°	691.9	691.5	690.9	690.3	689.7	688.6	686.8	685.0	683.1	681.3	682.5
17.5°	675.9	675.1	674.4	673.7	672.9	671.7	669.9	668.1	666.3	664.5	665.3
20°	663.9	663.1	662.2	661.4	660.6	659.3	657.5	655.7	653.8	652.0	652.6
22.5°	650.4	649.5	648.7	647.9	647.0	645.7	643.9	642.1	640.3	638.5	639.0
25°	628.3	627.5	626.6	625.8	624.9	623.6	621.8	620.0	618.2	616.4	616.5
27.5°	604.7	603.9	603.1	602.3	601.4	600.1	598.1	596.2	594.3	592.3	592.4
30°	587.7	587.0	586.3	585.6	584.9	583.6	581.6	579.7	577.8	575.8	575.8
32.5°	570.7	569.8	568.8	567.9	567.0	565.8	564.4	562.8	561.3	559.9	559.1
35°	543.3	542.5	541.7	540.9	540.1	538.7	536.9	535.1	533.3	531.5	530.7
37.5°	515.4	514.3	513.2	512.2	511.1	509.7	507.8	506.1	504.2	502.4	501.4
40°	495.9	495.0	494.2	493.4	492.5	491.1	489.2	487.3	485.3	483.4	482.2
42.5°	476.4	475.5	474.5	473.5	472.6	471.2	469.2	467.3	465.4	463.4	462.3
45°	445.3	444.7	444.2	443.6	443.0	441.9	440.1	438.3	436.5	434.6	433.0
47.5°	414.4	413.6	412.9	412.1	411.2	409.9	408.3	406.6	404.9	403.2	401.5
50°	393.5	392.7	392.1	391.3	390.7	389.5	387.6	385.8	384.0	382.2	380.7
52.5°	371.5	371.0	370.6	370.1	369.6	368.4	366.5	364.6	362.6	360.8	359.5
55°	337.9	337.7	337.6	337.5	337.3	336.3	334.5	332.7	330.9	329.1	327.6
57.5°	305.9	305.4	304.9	304.5	304.0	303.0	301.6	300.2	298.7	297.3	296.0
60°	282.9	282.7	282.7	282.5	282.3	281.4	279.8	278.1	276.5	274.8	273.5
62.5°	262.4	262.0	261.7	261.4	261.0	260.0	258.3	256.7	254.9	253.3	252.1
65°	230.5	229.8	229.1	228.4	227.7	226.7	225.3	223.9	222.5	221.1	220.0
67.5°	196.6	196.0	195.3	194.8	194.1	193.3	192.2	191.2	190.1	189.1	188.2
70°	176.1	175.3	174.5	173.7	172.8	171.9	171.1	170.3	169.4	168.6	167.6
72.5°	154.7	154.0	153.4	152.8	152.2	151.4	150.5	149.5	148.5	147.7	146.8
75°	121.8	121.2	120.7	120.1	119.6	119.1	118.6	118.2	117.8	117.4	116.8
77.5°	92.7	92.4	92.0	91.8	91.5	91.1	90.6	90.1	89.5	89.0	88.6
80°	73.7	73.3	72.9	72.5	72.0	71.7	71.4	71.1	70.8	70.6	70.4
82.5°	55.2	55.1	55.0	55.0	54.9	54.8	54.8	54.7	54.6	54.6	54.3
85°	32.4	32.2	32.0	31.6	31.4	31.2	31.2	31.2	31.2	31.2	31.0
87.5°	13.2	13.5	13.6	13.9	14.1	14.4	15.1	15.7	16.2	16.9	17.0
90°	1.2	3.9	6.6	9.4	12.1	15.2	18.7	22.2	25.8	29.3	30.3
92.5°	22.7	21.9	21.1	20.4	19.6	20.5	23.2	25.9	28.5	31.2	32.9
95°	74.4	63.3	52.2	41.0	29.9	25.8	28.9	31.8	34.8	37.7	39.7
97.5°	149.4	144.5	139.5	134.4	129.5	117.2	97.8	78.3	58.8	39.2	41.4
100°	206.0	211.4	216.8	222.3	227.6	209.2	167.0	124.7	82.5	40.2	42.4
102.5°	270.4	274.3	278.2	282.0	285.9	264.8	218.7	172.5	126.4	80.2	73.5
105°	363.2	366.2	369.2	372.2	375.1	364.4	340.1	315.7	291.3	266.9	219.0
107.5°	461.2	463.6	465.9	468.4	470.8	473.9	477.7	481.6	485.4	489.3	454.1
110°	526.5	528.7	530.8	533.0	535.2	537.8	540.8	543.7	546.7	549.7	540.8



TEST NUMBER: P332148-930

CATALOG NUMBER: S123DIW-S560D1535U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	589.0	590.9	592.9	594.8	596.7	599.2	602.2	605.2	608.1	611.1	611.3
115°	681.3	683.0	684.6	686.2	687.9	689.9	692.4	694.7	697.2	699.6	702.3
117.5°	770.8	772.8	774.8	776.8	778.9	780.5	781.7	782.9	784.2	785.5	787.6
120°	826.4	828.8	831.3	833.7	836.2	837.8	838.5	839.4	840.2	841.0	843.2
122.5°	883.0	884.9	887.0	888.9	891.0	892.5	893.5	894.5	895.5	896.6	898.1
125°	960.4	962.6	964.8	966.9	969.1	970.8	971.8	972.9	974.0	975.1	975.7
127.5°	1035.5	1037.7	1039.9	1042.0	1044.2	1045.9	1047.3	1048.6	1049.9	1051.2	1052.0
130°	1082.3	1084.5	1086.7	1088.8	1091.0	1092.7	1093.7	1094.8	1095.9	1097.0	1098.0
132.5°	1127.2	1129.4	1131.6	1133.7	1135.9	1137.4	1138.2	1139.1	1140.0	1140.8	1141.9
135°	1195.7	1197.3	1199.0	1200.6	1202.2	1203.5	1204.6	1205.7	1206.8	1207.9	1208.7
137.5°	1254.2	1256.3	1258.3	1260.4	1262.4	1263.8	1264.4	1264.9	1265.6	1266.2	1267.5
140°	1293.2	1294.9	1296.5	1298.1	1299.8	1300.9	1301.7	1302.5	1303.3	1304.2	1305.3
142.5°	1329.3	1330.9	1332.5	1334.2	1335.8	1337.0	1337.8	1338.6	1339.5	1340.3	1341.1
145°	1379.7	1381.6	1383.6	1385.4	1387.3	1388.5	1389.1	1389.6	1390.2	1390.7	1391.2
147.5°	1427.3	1428.6	1429.8	1431.0	1432.2	1433.1	1433.7	1434.3	1434.8	1435.3	1435.9
150°	1456.5	1457.3	1458.2	1459.0	1459.8	1460.4	1461.0	1461.6	1462.1	1462.6	1463.1
152.5°	1482.9	1483.3	1483.6	1484.0	1484.4	1484.7	1485.1	1485.4	1485.7	1486.0	1487.0
155°	1519.9	1519.4	1518.8	1518.3	1517.8	1517.6	1517.9	1518.2	1518.4	1518.7	1520.0
157.5°	1548.7	1548.7	1548.6	1548.5	1548.5	1548.3	1548.0	1547.8	1547.5	1547.2	1548.8
160°	1566.3	1565.9	1565.7	1565.5	1565.1	1564.9	1564.6	1564.3	1564.1	1563.8	1565.5
162.5°	1582.8	1582.1	1581.4	1580.7	1580.0	1579.5	1579.2	1579.0	1578.7	1578.4	1580.3
165°	1602.8	1602.0	1601.2	1600.4	1599.5	1599.0	1598.7	1598.5	1598.2	1597.9	1600.1
167.5°	1618.4	1617.3	1616.2	1615.2	1614.0	1613.6	1613.6	1613.6	1613.6	1613.6	1615.7
170°	1627.2	1626.1	1625.0	1623.9	1622.9	1622.3	1622.3	1622.3	1622.3	1622.3	1624.5
172.5°	1633.0	1631.7	1630.4	1629.1	1627.8	1627.3	1627.5	1627.7	1627.9	1628.2	1630.4
175°	1640.5	1639.2	1637.9	1636.6	1635.2	1634.6	1634.9	1635.2	1635.4	1635.7	1637.6
177.5°	1642.5	1641.4	1640.4	1639.3	1638.2	1637.8	1638.0	1638.2	1638.4	1638.7	1640.4
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332148-930

CATALOG NUMBER: S123DIW-S560D1535U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	723.6	724.6	725.8	726.3	726.2	726.0	725.9	725.9
5°	719.7	721.1	722.5	723.1	722.8	722.5	722.3	721.9
7.5°	712.1	713.3	714.6	715.1	714.9	714.8	714.6	714.4
10°	705.1	706.4	707.6	708.1	707.8	707.5	707.3	706.9
12.5°	697.4	698.4	699.3	699.6	699.4	699.3	699.1	699.0
15°	683.6	684.7	685.8	685.9	685.1	684.3	683.5	682.7
17.5°	666.1	666.8	667.6	667.8	667.6	667.2	666.9	666.6
20°	653.1	653.7	654.2	654.3	653.9	653.5	653.1	652.6
22.5°	639.4	639.8	640.3	640.3	639.8	639.2	638.7	638.1
25°	616.7	616.9	616.9	616.9	616.4	616.0	615.6	615.1
27.5°	592.6	592.6	592.7	592.6	592.0	591.5	590.9	590.4
30°	575.8	575.8	575.8	575.4	574.4	573.4	572.4	571.4
32.5°	558.3	557.5	556.7	556.0	555.5	555.1	554.5	554.0
35°	529.8	529.0	528.2	527.4	526.7	526.0	525.3	524.6
37.5°	500.3	499.4	498.4	497.7	497.3	496.8	496.4	495.9
40°	481.2	480.0	479.0	478.1	477.5	477.0	476.5	475.9
42.5°	461.2	460.1	458.9	458.1	457.5	457.1	456.5	455.9
45°	431.4	429.7	428.0	426.8	426.2	425.4	424.8	424.0
47.5°	399.9	398.3	396.6	395.5	394.9	394.3	393.7	393.1
50°	379.2	377.6	376.1	375.0	374.1	373.2	372.4	371.6
52.5°	358.2	356.9	355.6	354.4	353.6	352.8	352.0	351.1
55°	326.0	324.6	323.0	321.9	321.2	320.5	319.8	319.1
57.5°	294.6	293.2	291.9	290.7	289.9	289.2	288.4	287.6
60°	272.3	271.1	269.8	268.8	268.2	267.4	266.8	266.0
62.5°	250.8	249.6	248.3	247.4	247.0	246.5	246.1	245.6
65°	218.8	217.8	216.6	215.9	215.5	215.1	214.7	214.2
67.5°	187.2	186.2	185.2	184.4	183.8	183.3	182.7	182.1
70°	166.6	165.8	164.8	163.9	163.2	162.5	161.8	161.1
72.5°	145.9	145.0	144.2	143.6	143.2	142.8	142.5	142.1
75°	116.0	115.4	114.6	114.1	113.7	113.2	112.8	112.4
77.5°	88.1	87.6	87.2	86.9	86.9	86.9	86.9	86.9
80°	70.3	70.1	70.0	70.0	70.0	70.0	70.0	70.0
82.5°	54.1	53.8	53.6	53.4	53.3	53.2	53.1	53.0
85°	30.7	30.4	30.1	30.0	30.0	30.0	30.0	30.0
87.5°	17.0	17.1	17.3	17.4	17.4	17.6	17.7	17.8
90°	31.4	32.5	33.6	34.4	35.0	35.5	36.0	36.5
92.5°	34.7	36.4	38.2	39.1	39.5	39.8	40.1	40.4
95°	41.6	43.5	45.3	46.3	46.3	46.3	46.3	46.3
97.5°	43.6	45.7	47.9	49.2	49.4	49.7	50.0	50.2
100°	44.5	46.7	48.9	50.1	50.4	50.6	51.0	51.2
102.5°	66.8	60.1	53.3	50.2	50.7	51.2	51.7	52.2
105°	171.0	123.1	75.2	51.4	52.0	52.6	53.1	53.6
107.5°	418.9	383.8	348.6	313.0	276.9	240.7	204.6	168.4
110°	531.8	522.9	514.0	490.1	451.3	412.6	373.9	335.2



TEST NUMBER: P332148-930

CATALOG NUMBER: S123DIW-S560D1535U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	611.5	611.6	611.8	607.8	599.6	591.4	583.3	575.0
115°	705.1	707.8	710.5	712.3	713.5	714.5	715.6	716.7
117.5°	789.8	791.9	794.1	795.3	795.5	795.7	796.0	796.1
120°	845.4	847.5	849.7	850.8	850.8	850.8	850.8	850.8
122.5°	899.6	901.2	902.7	903.5	903.8	903.9	904.2	904.4
125°	976.2	976.7	977.2	977.8	978.4	978.8	979.4	980.0
127.5°	1052.9	1053.8	1054.6	1054.8	1054.3	1053.7	1053.1	1052.6
130°	1099.1	1100.2	1101.3	1101.6	1101.1	1100.5	1099.9	1099.4
132.5°	1143.0	1144.1	1145.2	1145.3	1144.6	1143.9	1143.0	1142.3
135°	1209.5	1210.3	1211.1	1211.1	1210.3	1209.5	1208.7	1207.9
137.5°	1268.8	1270.1	1271.4	1271.7	1271.2	1270.6	1270.1	1269.6
140°	1306.4	1307.4	1308.5	1308.8	1308.2	1307.7	1307.2	1306.6
142.5°	1342.0	1342.9	1343.7	1343.8	1343.0	1342.2	1341.5	1340.8
145°	1391.8	1392.4	1392.9	1393.2	1393.2	1393.2	1393.2	1393.2
147.5°	1436.4	1437.0	1437.5	1437.1	1435.9	1434.7	1433.4	1432.2
150°	1463.7	1464.3	1464.8	1464.7	1463.9	1463.1	1462.2	1461.4
152.5°	1488.0	1489.0	1490.0	1489.8	1488.6	1487.3	1486.0	1484.8
155°	1521.4	1522.7	1524.1	1524.0	1522.3	1520.7	1519.1	1517.5
157.5°	1550.5	1552.1	1553.7	1553.5	1551.4	1549.2	1547.1	1545.0
160°	1567.1	1568.6	1570.3	1570.2	1568.2	1566.4	1564.5	1562.6
162.5°	1582.1	1584.0	1585.8	1585.8	1584.2	1582.5	1580.9	1579.2
165°	1602.2	1604.4	1606.6	1606.7	1604.8	1603.0	1601.0	1599.1
167.5°	1617.9	1620.0	1622.2	1622.2	1620.0	1617.9	1615.7	1613.6
170°	1626.6	1628.8	1631.0	1631.0	1628.8	1626.6	1624.5	1622.3
172.5°	1632.5	1634.7	1636.8	1636.7	1634.3	1632.0	1629.5	1627.2
175°	1639.5	1641.4	1643.3	1643.2	1641.0	1638.8	1636.6	1634.5
177.5°	1642.1	1643.8	1645.6	1645.4	1643.2	1641.0	1638.8	1636.7
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5

(END OF REPORT)