

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332166-930

Luminaire Tested: **S123DIW-S775D1030U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332166-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S775D1030U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5947.8 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332166-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332166-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	35	31
3	80	70	63	57	73	65	58	53	54	49	45	44	40	38	34	32	30	26
4	73	62	54	48	67	57	50	45	48	43	39	39	35	32	31	28	26	22
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	32	27	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10687	10687	10687
5°	10737	10589	10662
10°	10665	10497	10563
15°	10541	10379	10398
20°	10394	10208	10219
25°	10200	10007	9987
30°	9984	9783	9708
35°	9759	9546	9423
40°	9524	9284	9140
45°	9266	9045	8824
50°	9008	8748	8505
55°	8668	8443	8188
60°	8325	8086	7830
65°	8023	7697	7457
70°	7578	7254	6930
75°	6924	6675	6392
80°	6248	5976	5926
85°	5483	5274	5064



TEST NUMBER: P332166-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	1.6
10°-20°	264.1	4.4
20°-30°	390.1	6.6
30°-40°	455.7	7.7
40°-50°	458.1	7.7
50°-60°	402.4	6.8
60°-70°	299.8	5.0
70°-80°	170.8	2.9
80°-90°	52.1	0.9
90°-100°	40.1	0.7
100°-110°	191.0	3.2
110°-120°	458.8	7.7
120°-130°	584.2	9.8
130°-140°	624.2	10.5
140°-150°	583.7	9.8
150°-160°	470.8	7.9
160°-170°	303.9	5.1
170°-180°	104.7	1.8
0°-30°	747.7	12.6
0°-40°	1203.3	20.2
0°-60°	2063.8	34.7
0°-90°	2586.6	43.5
90°-120°	689.8	11.6
90°-150°	2481.9	41.7
90°-180°	3361.0	56.5
0°-180°	5947.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	994	989	980	988	987	94
15°	946	942	931	938	933	267
25°	859	853	843	843	841	395
35°	743	737	726	721	717	464
45°	609	605	594	584	580	470
55°	462	460	450	441	436	414
65°	315	310	302	296	293	311
75°	166	163	160	156	154	178
85°	44	43	43	41	41	49
90°	1	9	20	23	24	5
95°	50	19	25	31	31	62
105°	244	248	179	43	36	259
115°	458	463	470	478	482	452
125°	645	652	655	657	658	576
135°	803	808	812	814	812	618
145°	927	932	934	936	936	580
155°	1021	1020	1020	1024	1020	470
165°	1077	1074	1074	1079	1074	304
175°	1102	1098	1099	1104	1098	105
180°	1102	1102	1102	1102	1102	



TEST NUMBER: P332166-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	996.2	995.6	995.1	994.4	993.8	992.7	991.0	989.4	987.7	986.0	987.5
5°	993.7	992.7	991.8	990.8	989.9	988.4	986.3	984.2	982.1	980.0	981.9
7.5°	984.0	983.0	982.0	981.1	980.2	978.6	976.4	974.3	972.1	970.0	971.7
10°	975.8	974.8	973.9	972.9	972.0	970.3	967.8	965.3	962.9	960.4	962.1
12.5°	964.8	964.0	963.3	962.5	961.6	960.1	957.8	955.4	953.2	950.8	952.1
15°	945.9	945.1	944.4	943.6	942.8	941.3	938.7	936.3	933.8	931.4	932.9
17.5°	923.8	922.8	921.9	920.9	919.9	918.2	915.7	913.2	910.8	908.3	909.4
20°	907.4	906.3	905.2	904.1	902.9	901.1	898.6	896.2	893.7	891.2	892.0
22.5°	889.0	887.9	886.7	885.6	884.4	882.6	880.2	877.8	875.3	872.8	873.4
25°	858.8	857.7	856.6	855.4	854.3	852.5	849.9	847.5	845.1	842.6	842.8
27.5°	826.6	825.4	824.3	823.2	822.1	820.3	817.6	815.0	812.3	809.6	809.8
30°	803.3	802.3	801.4	800.5	799.5	797.7	795.1	792.4	789.8	787.1	787.1
32.5°	780.1	778.9	777.6	776.3	775.1	773.5	771.4	769.3	767.3	765.2	764.2
35°	742.7	741.6	740.5	739.3	738.2	736.4	733.9	731.4	729.0	726.5	725.4
37.5°	704.4	703.0	701.6	700.1	698.7	696.8	694.2	691.7	689.2	686.7	685.3
40°	677.8	676.7	675.6	674.4	673.3	671.4	668.7	666.1	663.4	660.7	659.3
42.5°	651.2	649.9	648.6	647.3	646.0	644.1	641.4	638.7	636.1	633.4	631.9
45°	608.7	607.9	607.2	606.4	605.6	604.1	601.5	599.1	596.6	594.2	591.9
47.5°	566.5	565.4	564.3	563.2	562.1	560.4	558.1	555.8	553.4	551.1	548.9
50°	537.9	536.9	535.9	535.0	534.0	532.3	529.9	527.4	524.9	522.4	520.4
52.5°	507.8	507.1	506.5	505.8	505.2	503.5	500.9	498.3	495.7	493.1	491.3
55°	461.9	461.6	461.5	461.3	461.1	459.7	457.3	454.9	452.3	449.9	447.8
57.5°	418.2	417.5	416.9	416.2	415.6	414.3	412.3	410.3	408.3	406.3	404.5
60°	386.7	386.5	386.4	386.1	386.0	384.7	382.5	380.2	377.9	375.6	373.9
62.5°	358.7	358.2	357.8	357.3	356.8	355.4	353.1	350.8	348.5	346.3	344.5
65°	315.0	314.1	313.1	312.2	311.2	309.8	307.9	306.0	304.1	302.2	300.7
67.5°	268.7	267.9	267.1	266.2	265.4	264.2	262.9	261.4	259.9	258.5	257.1
70°	240.8	239.6	238.5	237.3	236.2	235.1	233.9	232.8	231.6	230.5	229.2
72.5°	211.4	210.5	209.7	208.9	208.1	207.0	205.7	204.4	203.1	201.8	200.6
75°	166.5	165.7	164.9	164.2	163.5	162.7	162.2	161.6	161.0	160.5	159.6
77.5°	126.7	126.3	125.9	125.5	125.0	124.5	123.8	123.1	122.5	121.7	121.1
80°	100.8	100.2	99.6	99.1	98.5	98.0	97.6	97.3	96.9	96.4	96.3
82.5°	75.5	75.3	75.3	75.1	75.0	74.9	74.8	74.8	74.7	74.6	74.3
85°	44.4	44.0	43.6	43.3	42.9	42.7	42.7	42.7	42.7	42.7	42.3
87.5°	17.9	17.9	17.8	17.6	17.5	17.7	18.0	18.3	18.7	18.9	18.9
90°	0.8	2.6	4.5	6.3	8.1	10.2	12.6	14.9	17.3	19.6	20.4
92.5°	15.2	14.8	14.2	13.7	13.2	13.9	15.7	17.4	19.2	21.0	22.1
95°	50.0	42.5	35.1	27.6	20.1	17.4	19.4	21.4	23.4	25.4	26.7
97.5°	100.4	97.0	93.7	90.3	87.0	78.8	65.7	52.6	39.5	26.3	27.8
100°	138.4	142.0	145.7	149.3	153.0	140.6	112.2	83.8	55.4	27.0	28.5
102.5°	181.6	184.3	186.9	189.5	192.1	177.9	146.9	115.9	84.9	53.9	49.4
105°	244.0	246.1	248.0	250.1	252.0	244.8	228.4	212.1	195.8	179.4	147.2
107.5°	309.9	311.4	313.1	314.7	316.3	318.4	321.0	323.5	326.1	328.7	305.1
110°	353.8	355.2	356.7	358.2	359.5	361.3	363.3	365.3	367.3	369.3	363.3



TEST NUMBER: P332166-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	395.7	397.0	398.3	399.7	401.0	402.6	404.6	406.6	408.6	410.6	410.7
115°	457.8	458.9	459.9	461.1	462.1	463.5	465.1	466.8	468.4	470.0	471.9
117.5°	517.9	519.2	520.6	521.9	523.3	524.3	525.2	526.0	526.8	527.7	529.1
120°	555.2	556.8	558.5	560.1	561.7	562.9	563.4	563.9	564.5	565.0	566.5
122.5°	593.2	594.5	595.9	597.2	598.6	599.6	600.3	601.0	601.7	602.3	603.4
125°	645.3	646.8	648.2	649.6	651.1	652.2	652.9	653.6	654.4	655.1	655.5
127.5°	695.7	697.2	698.6	700.1	701.6	702.7	703.6	704.5	705.3	706.2	706.8
130°	727.2	728.6	730.1	731.6	733.0	734.1	734.8	735.6	736.3	737.0	737.8
132.5°	757.3	758.8	760.2	761.7	763.1	764.2	764.8	765.3	765.9	766.5	767.2
135°	803.3	804.5	805.5	806.6	807.7	808.6	809.3	810.1	810.8	811.5	812.0
137.5°	842.6	844.0	845.4	846.8	848.2	849.1	849.5	849.9	850.3	850.7	851.5
140°	868.9	869.9	871.1	872.1	873.2	874.0	874.6	875.1	875.6	876.2	876.9
142.5°	893.1	894.1	895.3	896.3	897.5	898.3	898.8	899.4	899.9	900.4	901.1
145°	927.0	928.2	929.5	930.8	932.1	932.9	933.3	933.6	934.0	934.3	934.7
147.5°	959.0	959.8	960.6	961.4	962.3	962.9	963.2	963.6	963.9	964.3	964.7
150°	978.6	979.1	979.7	980.2	980.7	981.2	981.5	981.9	982.3	982.7	983.0
152.5°	996.3	996.5	996.8	997.0	997.3	997.5	997.8	997.9	998.2	998.4	999.1
155°	1021.2	1020.8	1020.4	1020.1	1019.7	1019.6	1019.8	1019.9	1020.2	1020.3	1021.2
157.5°	1040.5	1040.5	1040.4	1040.4	1040.3	1040.2	1040.1	1039.8	1039.7	1039.5	1040.6
160°	1052.3	1052.1	1051.9	1051.7	1051.6	1051.3	1051.2	1051.0	1050.8	1050.7	1051.7
162.5°	1063.4	1062.9	1062.5	1062.0	1061.5	1061.2	1061.0	1060.9	1060.6	1060.5	1061.7
165°	1076.8	1076.3	1075.8	1075.2	1074.6	1074.3	1074.1	1073.9	1073.7	1073.6	1075.1
167.5°	1087.3	1086.6	1085.9	1085.2	1084.4	1084.0	1084.0	1084.0	1084.0	1084.0	1085.5
170°	1093.2	1092.5	1091.8	1091.0	1090.3	1090.0	1090.0	1090.0	1090.0	1090.0	1091.4
172.5°	1097.1	1096.3	1095.4	1094.5	1093.6	1093.3	1093.4	1093.6	1093.7	1093.9	1095.4
175°	1102.2	1101.3	1100.4	1099.5	1098.6	1098.2	1098.4	1098.6	1098.8	1098.9	1100.2
177.5°	1103.5	1102.8	1102.1	1101.4	1100.7	1100.3	1100.5	1100.7	1100.7	1100.9	1102.1
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2



TEST NUMBER: P332166-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	989.0	990.6	992.1	992.8	992.6	992.5	992.3	992.1
5°	983.8	985.7	987.7	988.4	988.0	987.7	987.2	986.8
7.5°	973.4	975.1	976.8	977.5	977.3	977.1	976.8	976.6
10°	963.8	965.5	967.2	967.9	967.5	967.1	966.8	966.4
12.5°	953.3	954.6	955.9	956.3	956.1	955.9	955.7	955.4
15°	934.4	935.9	937.4	937.6	936.5	935.3	934.3	933.1
17.5°	910.4	911.5	912.6	912.9	912.5	912.1	911.7	911.3
20°	892.8	893.5	894.3	894.4	893.8	893.2	892.7	892.1
22.5°	874.0	874.7	875.2	875.1	874.5	873.8	873.0	872.3
25°	842.9	843.2	843.3	843.2	842.6	842.0	841.5	840.9
27.5°	809.9	810.1	810.2	809.9	809.3	808.5	807.8	807.1
30°	787.1	787.1	787.1	786.4	785.1	783.7	782.4	781.1
32.5°	763.1	762.1	761.0	760.1	759.4	758.6	757.9	757.2
35°	724.2	723.1	721.9	720.9	719.9	719.0	718.0	717.1
37.5°	684.0	682.6	681.3	680.3	679.6	679.1	678.4	677.8
40°	657.7	656.2	654.7	653.5	652.8	652.0	651.3	650.5
42.5°	630.4	628.8	627.4	626.2	625.5	624.7	623.9	623.2
45°	589.6	587.3	585.1	583.4	582.5	581.6	580.6	579.7
47.5°	546.7	544.5	542.2	540.6	539.8	539.0	538.2	537.3
50°	518.3	516.2	514.1	512.5	511.4	510.2	509.1	507.9
52.5°	489.5	487.7	485.9	484.5	483.4	482.2	481.1	480.0
55°	445.7	443.6	441.6	440.0	439.0	438.1	437.2	436.3
57.5°	402.6	400.8	398.9	397.5	396.3	395.3	394.1	393.1
60°	372.2	370.5	368.8	367.5	366.5	365.6	364.6	363.7
62.5°	342.8	341.1	339.4	338.3	337.6	337.0	336.3	335.7
65°	299.1	297.7	296.1	295.1	294.5	293.9	293.3	292.8
67.5°	255.8	254.5	253.2	252.1	251.4	250.5	249.7	248.9
70°	227.9	226.5	225.2	224.0	223.1	222.2	221.2	220.2
72.5°	199.4	198.3	197.1	196.2	195.8	195.3	194.8	194.3
75°	158.6	157.7	156.7	156.0	155.4	154.8	154.3	153.7
77.5°	120.4	119.8	119.1	118.9	118.9	118.9	118.9	118.9
80°	96.1	95.9	95.7	95.6	95.6	95.6	95.6	95.6
82.5°	73.9	73.6	73.2	73.0	72.9	72.7	72.6	72.4
85°	41.9	41.6	41.2	41.0	41.0	41.0	41.0	41.0
87.5°	18.9	18.9	18.9	19.0	19.0	19.1	19.2	19.2
90°	21.1	21.9	22.6	23.1	23.5	23.8	24.2	24.5
92.5°	23.3	24.5	25.6	26.3	26.5	26.7	27.0	27.1
95°	28.0	29.2	30.5	31.1	31.1	31.1	31.1	31.1
97.5°	29.3	30.7	32.2	33.0	33.2	33.3	33.6	33.8
100°	29.9	31.4	32.9	33.7	33.8	34.0	34.2	34.4
102.5°	44.8	40.4	35.8	33.8	34.1	34.4	34.7	35.1
105°	115.0	82.7	50.5	34.6	35.0	35.3	35.6	36.0
107.5°	281.4	257.9	234.2	210.3	186.0	161.8	137.5	113.2
110°	357.3	351.3	345.3	329.3	303.3	277.2	251.2	225.2



TEST NUMBER: P332166-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	410.8	410.9	411.0	408.3	402.8	397.4	391.8	386.4
115°	473.7	475.5	477.4	478.6	479.3	480.0	480.8	481.5
117.5°	530.6	532.1	533.5	534.3	534.4	534.6	534.8	534.9
120°	567.9	569.4	570.9	571.6	571.6	571.6	571.6	571.6
122.5°	604.4	605.4	606.4	607.1	607.2	607.3	607.5	607.6
125°	655.8	656.2	656.6	657.0	657.3	657.6	658.0	658.4
127.5°	707.4	707.9	708.6	708.7	708.3	707.9	707.6	707.2
130°	738.5	739.2	739.9	740.1	739.7	739.4	739.0	738.7
132.5°	767.9	768.7	769.4	769.5	769.0	768.5	768.0	767.4
135°	812.6	813.2	813.7	813.7	813.2	812.6	812.0	811.5
137.5°	852.4	853.3	854.2	854.4	854.0	853.7	853.3	853.0
140°	877.7	878.4	879.1	879.3	879.0	878.6	878.2	877.8
142.5°	901.6	902.2	902.8	902.8	902.3	901.8	901.3	900.7
145°	935.1	935.5	935.8	936.0	936.0	936.0	936.0	936.0
147.5°	965.1	965.4	965.8	965.6	964.7	963.8	963.0	962.2
150°	983.4	983.7	984.1	984.1	983.5	982.9	982.4	981.9
152.5°	999.7	1000.4	1001.0	1000.9	1000.0	999.2	998.4	997.6
155°	1022.1	1023.0	1024.0	1023.9	1022.8	1021.7	1020.6	1019.5
157.5°	1041.7	1042.8	1043.8	1043.7	1042.3	1040.9	1039.4	1038.0
160°	1052.8	1053.9	1055.0	1054.9	1053.6	1052.4	1051.1	1049.8
162.5°	1062.9	1064.2	1065.4	1065.4	1064.4	1063.2	1062.1	1060.9
165°	1076.4	1077.9	1079.4	1079.5	1078.2	1076.9	1075.6	1074.4
167.5°	1087.0	1088.4	1089.9	1089.9	1088.4	1087.0	1085.5	1084.0
170°	1092.8	1094.3	1095.8	1095.8	1094.3	1092.8	1091.4	1090.0
172.5°	1096.8	1098.2	1099.7	1099.6	1098.0	1096.4	1094.8	1093.2
175°	1101.5	1102.8	1104.1	1104.0	1102.5	1101.1	1099.6	1098.1
177.5°	1103.3	1104.4	1105.5	1105.5	1104.0	1102.5	1101.1	1099.6
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2

(END OF REPORT)