

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332106-840

Luminaire Tested: **S123DIW-S340D1030U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332106-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S340D1030U840-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1030 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5591.2 lumens  
Efficiency: N/A  
Efficacy: 147.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332106-840

CATALOG NUMBER: S123DIW-S340D1030U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332106-840

CATALOG NUMBER: S123DIW-S340D1030U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	92	88	84	81	82	79	75	73	61	59	57	45	43	42	30	29	28	21
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	67	60	55	68	60	54	50	47	43	39	35	32	30	23	21	20	15
4	70	60	52	46	62	53	47	42	42	37	33	31	28	25	21	19	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	17	15	11
6	59	47	39	34	52	42	36	31	33	28	25	25	21	19	17	15	13	10
7	54	42	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	42	31	25	21	25	20	17	19	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5890	5890	5890
5°	5919	5837	5877
10°	5879	5786	5822
15°	5810	5721	5731
20°	5730	5628	5632
25°	5621	5516	5505
30°	5504	5392	5351
35°	5380	5261	5194
40°	5251	5117	5039
45°	5107	4985	4864
50°	4963	4823	4687
55°	4778	4654	4511
60°	4590	4456	4316
65°	4422	4241	4111
70°	4176	3997	3821
75°	3818	3681	3523
80°	3440	3298	3267
85°	3013	2902	2791



TEST NUMBER: P332106-840

CATALOG NUMBER: S123DIW-S340D1030U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.5	0.9
10°-20°	145.6	2.6
20°-30°	215.0	3.8
30°-40°	251.2	4.5
40°-50°	252.5	4.5
50°-60°	221.8	4.0
60°-70°	165.2	3.0
70°-80°	94.1	1.7
80°-90°	30.8	0.6
90°-100°	49.6	0.9
100°-110°	236.6	4.2
110°-120°	568.2	10.2
120°-130°	723.6	12.9
130°-140°	773.1	13.8
140°-150°	723.0	12.9
150°-160°	583.2	10.4
160°-170°	376.4	6.7
170°-180°	129.7	2.3
0°-30°	412.1	7.4
0°-40°	663.3	11.9
0°-60°	1137.6	20.3
0°-90°	1427.8	25.5
90°-120°	854.5	15.3
90°-150°	3074.2	55.0
90°-180°	4163.0	74.5
0°-180°	5591.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	547	547	547	547	547	
5°	548	545	540	545	544	52
15°	521	519	513	517	514	147
25°	473	470	464	465	464	218
35°	409	406	400	398	395	256
45°	336	333	328	322	320	259
55°	255	254	248	243	240	228
65°	174	171	166	163	161	171
75°	92	90	88	86	85	98
85°	24	24	24	23	23	27
90°	1	11	24	28	30	4
95°	62	23	31	38	39	76
105°	302	308	222	53	45	320
115°	567	573	582	592	596	560
125°	799	807	811	813	816	714
135°	995	1001	1005	1008	1005	766
145°	1148	1155	1157	1159	1159	718
155°	1265	1263	1264	1268	1263	583
165°	1334	1331	1330	1337	1331	377
175°	1365	1361	1361	1368	1360	130
180°	1365	1365	1365	1365	1365	



TEST NUMBER: P332106-840

CATALOG NUMBER: S123DIW-S340D1030U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2
2.5°	549.2	548.8	548.5	548.2	547.8	547.1	546.2	545.3	544.4	543.5	544.3
5°	547.8	547.1	546.6	546.1	545.6	544.8	543.6	542.5	541.3	540.2	541.2
7.5°	542.4	541.8	541.3	540.8	540.3	539.4	538.3	537.0	535.8	534.6	535.5
10°	537.9	537.3	536.7	536.2	535.7	534.8	533.4	532.1	530.7	529.4	530.3
12.5°	531.8	531.4	530.9	530.5	530.1	529.2	528.0	526.6	525.3	524.1	524.8
15°	521.4	521.0	520.5	520.1	519.7	518.8	517.5	516.0	514.7	513.4	514.2
17.5°	509.2	508.7	508.2	507.6	507.1	506.1	504.7	503.4	502.0	500.7	501.2
20°	500.2	499.6	499.0	498.3	497.7	496.7	495.3	493.9	492.6	491.3	491.7
22.5°	490.0	489.4	488.8	488.2	487.6	486.6	485.1	483.8	482.4	481.1	481.4
25°	473.3	472.7	472.1	471.5	470.9	469.9	468.5	467.2	465.7	464.4	464.5
27.5°	455.6	454.9	454.3	453.7	453.1	452.1	450.7	449.2	447.8	446.3	446.4
30°	442.8	442.2	441.7	441.2	440.7	439.7	438.3	436.8	435.4	433.8	433.8
32.5°	430.0	429.3	428.6	427.9	427.3	426.3	425.2	424.0	422.9	421.8	421.2
35°	409.4	408.8	408.1	407.5	406.9	405.9	404.6	403.1	401.8	400.4	399.8
37.5°	388.3	387.5	386.7	385.9	385.2	384.1	382.6	381.2	379.9	378.5	377.8
40°	373.7	372.9	372.3	371.7	371.1	370.0	368.6	367.1	365.7	364.2	363.3
42.5°	358.9	358.2	357.5	356.8	356.1	355.0	353.6	352.0	350.6	349.1	348.3
45°	335.5	335.1	334.7	334.3	333.9	333.0	331.5	330.2	328.8	327.5	326.3
47.5°	312.3	311.6	311.0	310.4	309.8	308.9	307.6	306.3	305.1	303.8	302.6
50°	296.4	295.9	295.4	294.9	294.4	293.4	292.1	290.7	289.3	288.0	286.8
52.5°	279.8	279.5	279.1	278.8	278.4	277.5	276.1	274.7	273.3	271.8	270.8
55°	254.6	254.5	254.4	254.3	254.2	253.4	252.1	250.6	249.3	248.0	246.8
57.5°	230.5	230.1	229.7	229.4	229.0	228.3	227.2	226.1	225.1	224.0	223.0
60°	213.2	213.1	213.0	212.9	212.8	212.1	210.8	209.5	208.3	207.0	206.1
62.5°	197.7	197.4	197.2	196.9	196.6	195.9	194.6	193.4	192.1	190.9	190.0
65°	173.6	173.1	172.6	172.1	171.6	170.8	169.8	168.6	167.6	166.5	165.7
67.5°	148.1	147.6	147.2	146.7	146.3	145.6	144.9	144.1	143.3	142.5	141.8
70°	132.7	132.1	131.5	130.8	130.2	129.6	129.0	128.3	127.6	127.0	126.3
72.5°	116.5	116.0	115.6	115.1	114.6	114.1	113.4	112.7	112.0	111.3	110.6
75°	91.8	91.3	90.9	90.5	90.1	89.7	89.4	89.1	88.8	88.5	88.0
77.5°	69.8	69.6	69.4	69.2	68.9	68.6	68.3	67.9	67.5	67.1	66.8
80°	55.5	55.2	54.9	54.6	54.2	54.0	53.8	53.6	53.4	53.2	53.0
82.5°	41.6	41.5	41.5	41.4	41.3	41.3	41.2	41.2	41.2	41.1	40.9
85°	24.4	24.2	24.0	23.8	23.6	23.5	23.5	23.5	23.5	23.5	23.3
87.5°	10.0	10.2	10.4	10.6	10.8	11.1	11.6	12.1	12.6	13.1	13.2
90°	1.0	3.2	5.6	7.8	10.0	12.6	15.6	18.5	21.4	24.3	25.2
92.5°	18.9	18.3	17.6	17.0	16.4	17.2	19.4	21.5	23.7	26.0	27.4
95°	61.9	52.6	43.4	34.1	24.9	21.5	24.0	26.5	29.0	31.4	33.0
97.5°	124.3	120.2	116.0	111.9	107.8	97.6	81.4	65.1	48.9	32.6	34.4
100°	171.4	175.9	180.5	184.9	189.5	174.1	139.0	103.8	68.7	33.4	35.2
102.5°	225.0	228.2	231.5	234.7	237.9	220.4	182.0	143.6	105.1	66.8	61.2
105°	302.3	304.8	307.2	309.7	312.1	303.3	283.0	262.7	242.5	222.2	182.3
107.5°	383.8	385.8	387.8	389.8	391.7	394.4	397.6	400.7	403.9	407.2	377.9
110°	438.2	440.0	441.8	443.6	445.4	447.6	450.0	452.5	454.9	457.5	450.0



TEST NUMBER: P332106-840

CATALOG NUMBER: S123DIW-S340D1030U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	490.1	491.7	493.3	495.0	496.7	498.7	501.1	503.6	506.1	508.6	508.7
115°	567.0	568.4	569.7	571.1	572.4	574.1	576.1	578.1	580.2	582.2	584.5
117.5°	641.5	643.1	644.8	646.4	648.1	649.4	650.6	651.6	652.6	653.6	655.4
120°	687.7	689.7	691.8	693.8	695.8	697.2	697.8	698.5	699.2	699.8	701.7
122.5°	734.8	736.4	738.1	739.7	741.4	742.7	743.6	744.4	745.3	746.1	747.4
125°	799.3	801.1	802.8	804.7	806.5	807.9	808.7	809.6	810.5	811.4	811.9
127.5°	861.7	863.5	865.4	867.2	869.0	870.4	871.5	872.6	873.6	874.7	875.5
130°	900.7	902.5	904.3	906.2	908.0	909.3	910.2	911.1	912.0	912.9	913.8
132.5°	938.1	939.9	941.6	943.4	945.2	946.5	947.3	948.0	948.7	949.4	950.3
135°	995.0	996.4	997.7	999.1	1000.5	1001.6	1002.5	1003.4	1004.3	1005.2	1005.8
137.5°	1043.7	1045.4	1047.1	1048.8	1050.6	1051.7	1052.2	1052.7	1053.2	1053.7	1054.7
140°	1076.2	1077.5	1078.9	1080.3	1081.6	1082.6	1083.3	1084.0	1084.6	1085.3	1086.2
142.5°	1106.2	1107.5	1108.9	1110.2	1111.7	1112.7	1113.3	1114.0	1114.7	1115.3	1116.1
145°	1148.2	1149.7	1151.3	1153.0	1154.5	1155.5	1156.0	1156.4	1156.9	1157.3	1157.8
147.5°	1187.8	1188.8	1189.8	1190.8	1191.9	1192.7	1193.1	1193.6	1194.0	1194.5	1194.9
150°	1212.1	1212.7	1213.5	1214.2	1214.8	1215.4	1215.8	1216.3	1216.7	1217.2	1217.6
152.5°	1234.1	1234.4	1234.7	1235.0	1235.3	1235.6	1235.9	1236.1	1236.4	1236.7	1237.5
155°	1264.9	1264.4	1263.9	1263.5	1263.0	1262.9	1263.1	1263.3	1263.6	1263.8	1265.0
157.5°	1288.8	1288.8	1288.7	1288.7	1288.6	1288.5	1288.3	1288.0	1287.8	1287.6	1288.9
160°	1303.4	1303.1	1302.9	1302.7	1302.5	1302.2	1302.0	1301.8	1301.6	1301.4	1302.7
162.5°	1317.2	1316.6	1316.1	1315.5	1314.8	1314.4	1314.2	1314.0	1313.7	1313.5	1315.0
165°	1333.8	1333.1	1332.5	1331.8	1331.1	1330.7	1330.4	1330.2	1330.0	1329.8	1331.6
167.5°	1346.8	1345.9	1345.0	1344.1	1343.2	1342.7	1342.7	1342.7	1342.7	1342.7	1344.5
170°	1354.1	1353.2	1352.3	1351.4	1350.5	1350.1	1350.1	1350.1	1350.1	1350.1	1351.8
172.5°	1359.0	1357.9	1356.9	1355.7	1354.6	1354.2	1354.3	1354.5	1354.7	1354.9	1356.8
175°	1365.2	1364.1	1363.0	1361.9	1360.8	1360.3	1360.5	1360.8	1361.0	1361.2	1362.8
177.5°	1366.9	1365.9	1365.1	1364.2	1363.3	1362.9	1363.1	1363.3	1363.4	1363.6	1365.1
180°	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2



TEST NUMBER: P332106-840

CATALOG NUMBER: S123DIW-S340D1030U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2
2.5°	545.1	546.0	546.8	547.2	547.1	547.0	546.9	546.8
5°	542.3	543.3	544.4	544.8	544.6	544.4	544.1	543.9
7.5°	536.5	537.5	538.4	538.8	538.7	538.6	538.5	538.3
10°	531.3	532.2	533.1	533.5	533.3	533.1	532.9	532.7
12.5°	525.4	526.1	526.8	527.1	527.0	526.8	526.7	526.6
15°	515.0	515.8	516.7	516.8	516.1	515.5	514.9	514.3
17.5°	501.8	502.4	503.0	503.2	502.9	502.7	502.5	502.3
20°	492.1	492.5	492.9	493.0	492.6	492.3	492.0	491.7
22.5°	481.7	482.1	482.4	482.4	482.0	481.6	481.2	480.8
25°	464.6	464.7	464.8	464.7	464.4	464.1	463.8	463.5
27.5°	446.5	446.6	446.6	446.5	446.1	445.7	445.2	444.8
30°	433.8	433.8	433.8	433.4	432.7	432.0	431.3	430.5
32.5°	420.6	420.0	419.5	419.0	418.6	418.2	417.8	417.4
35°	399.2	398.6	397.9	397.4	396.9	396.3	395.8	395.3
37.5°	377.0	376.3	375.5	375.0	374.7	374.3	374.0	373.7
40°	362.5	361.7	360.8	360.2	359.8	359.4	359.0	358.6
42.5°	347.5	346.6	345.8	345.2	344.8	344.4	344.0	343.5
45°	325.0	323.8	322.4	321.6	321.0	320.5	320.0	319.5
47.5°	301.3	300.1	298.8	298.0	297.5	297.1	296.6	296.2
50°	285.7	284.5	283.4	282.5	281.9	281.2	280.6	279.9
52.5°	269.8	268.8	267.8	267.0	266.4	265.8	265.2	264.6
55°	245.7	244.5	243.4	242.6	242.1	241.5	241.0	240.4
57.5°	222.0	220.9	219.8	219.0	218.4	217.8	217.2	216.6
60°	205.2	204.2	203.3	202.6	202.0	201.5	201.0	200.5
62.5°	188.9	188.0	187.1	186.4	186.1	185.7	185.4	185.0
65°	164.9	164.1	163.2	162.7	162.4	162.0	161.7	161.4
67.5°	141.0	140.3	139.6	139.0	138.6	138.0	137.6	137.2
70°	125.6	124.8	124.1	123.5	123.0	122.5	121.9	121.4
72.5°	110.0	109.3	108.7	108.2	108.0	107.7	107.3	107.0
75°	87.5	86.8	86.3	85.9	85.6	85.3	85.0	84.7
77.5°	66.3	66.0	65.6	65.5	65.5	65.5	65.5	65.5
80°	52.9	52.8	52.7	52.7	52.7	52.7	52.7	52.7
82.5°	40.8	40.6	40.4	40.2	40.2	40.1	40.0	39.9
85°	23.1	22.9	22.7	22.6	22.6	22.6	22.6	22.6
87.5°	13.3	13.4	13.5	13.6	13.7	13.8	13.9	14.0
90°	26.2	27.1	28.0	28.6	29.1	29.5	30.0	30.4
92.5°	28.9	30.3	31.7	32.6	32.8	33.1	33.4	33.6
95°	34.6	36.2	37.8	38.6	38.6	38.6	38.6	38.6
97.5°	36.3	38.1	39.9	40.9	41.1	41.3	41.6	41.8
100°	37.1	38.9	40.7	41.7	41.9	42.1	42.4	42.6
102.5°	55.5	50.0	44.3	41.8	42.2	42.6	43.0	43.4
105°	142.4	102.4	62.5	42.8	43.3	43.7	44.1	44.6
107.5°	348.6	319.4	290.1	260.4	230.4	200.4	170.3	140.2
110°	442.6	435.2	427.7	407.9	375.7	343.4	311.1	278.9





TEST NUMBER: P332106-840

CATALOG NUMBER: S123DIW-S340D1030U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	508.9	509.0	509.1	505.7	499.0	492.2	485.3	478.6
115°	586.7	589.0	591.3	592.8	593.7	594.6	595.5	596.4
117.5°	657.2	659.0	660.9	661.9	662.0	662.2	662.4	662.6
120°	703.5	705.3	707.1	708.0	708.0	708.0	708.0	708.0
122.5°	748.6	749.9	751.1	751.9	752.0	752.2	752.5	752.7
125°	812.3	812.8	813.2	813.7	814.2	814.6	815.1	815.5
127.5°	876.2	876.9	877.7	877.8	877.3	876.9	876.5	876.0
130°	914.7	915.5	916.5	916.8	916.3	915.8	915.3	914.9
132.5°	951.2	952.1	953.0	953.1	952.5	951.9	951.3	950.6
135°	1006.5	1007.2	1007.8	1007.8	1007.2	1006.5	1005.8	1005.2
137.5°	1055.8	1056.9	1058.0	1058.3	1057.8	1057.4	1056.9	1056.5
140°	1087.1	1088.0	1088.9	1089.1	1088.7	1088.2	1087.8	1087.3
142.5°	1116.8	1117.5	1118.2	1118.2	1117.6	1117.0	1116.4	1115.7
145°	1158.2	1158.7	1159.1	1159.3	1159.3	1159.3	1159.3	1159.3
147.5°	1195.4	1195.8	1196.3	1196.0	1195.0	1193.9	1192.9	1191.8
150°	1218.1	1218.5	1219.0	1218.9	1218.2	1217.5	1216.9	1216.2
152.5°	1238.3	1239.1	1239.9	1239.8	1238.7	1237.7	1236.7	1235.7
155°	1266.1	1267.2	1268.4	1268.2	1266.9	1265.6	1264.1	1262.8
157.5°	1290.3	1291.6	1292.9	1292.7	1291.0	1289.3	1287.5	1285.8
160°	1304.0	1305.5	1306.8	1306.7	1305.0	1303.5	1301.9	1300.3
162.5°	1316.6	1318.2	1319.7	1319.7	1318.4	1317.0	1315.6	1314.1
165°	1333.3	1335.1	1337.0	1337.1	1335.5	1333.9	1332.3	1330.8
167.5°	1346.4	1348.2	1350.0	1350.0	1348.2	1346.4	1344.5	1342.7
170°	1353.6	1355.4	1357.3	1357.3	1355.4	1353.6	1351.8	1350.1
172.5°	1358.6	1360.3	1362.1	1362.0	1360.1	1358.1	1356.0	1354.1
175°	1364.3	1365.9	1367.6	1367.5	1365.6	1363.8	1362.0	1360.2
177.5°	1366.5	1368.0	1369.4	1369.3	1367.5	1365.6	1363.8	1362.0
180°	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2

(END OF REPORT)