

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332100-840

Luminaire Tested: **S123DIW-S340D755U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332100-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D755U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4477.0 lumens
Efficiency: N/A
Efficacy: 147.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332100-840

CATALOG NUMBER: S123DIW-S340D755U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332100-840

CATALOG NUMBER: S123DIW-S340D755U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	39	39	39	32				
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	27				
2	85	78	72	67	76	70	65	61	56	53	49	43	40	38	31	29	28	22				
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19				
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16				
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14				
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12				
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11				
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	10				
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11	9				
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5890	5890	5890
5°	5919	5837	5877
10°	5879	5786	5822
15°	5810	5721	5731
20°	5730	5628	5632
25°	5621	5516	5505
30°	5504	5392	5351
35°	5380	5261	5194
40°	5251	5117	5039
45°	5107	4985	4864
50°	4963	4823	4687
55°	4778	4654	4511
60°	4590	4456	4316
65°	4422	4241	4111
70°	4176	3997	3821
75°	3818	3681	3523
80°	3440	3298	3267
85°	3013	2902	2791



TEST NUMBER: P332100-840

CATALOG NUMBER: S123DIW-S340D755U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.5	1.2
10°-20°	145.6	3.3
20°-30°	215.0	4.8
30°-40°	251.2	5.6
40°-50°	252.5	5.6
50°-60°	221.8	5.0
60°-70°	165.2	3.7
70°-80°	94.1	2.1
80°-90°	29.8	0.7
90°-100°	36.4	0.8
100°-110°	173.3	3.9
110°-120°	416.3	9.3
120°-130°	530.1	11.8
130°-140°	566.4	12.7
140°-150°	529.7	11.8
150°-160°	427.3	9.5
160°-170°	275.7	6.2
170°-180°	95.0	2.1
0°-30°	412.1	9.2
0°-40°	663.3	14.8
0°-60°	1137.6	25.4
0°-90°	1426.8	31.9
90°-120°	626.0	14.0
90°-150°	2252.2	50.3
90°-180°	3050.0	68.1
0°-180°	4477.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	547	547	547	547	547	
5°	548	545	540	545	544	52
15°	521	519	513	517	514	147
25°	473	470	464	465	464	218
35°	409	406	400	398	395	256
45°	336	333	328	322	320	259
55°	255	254	248	243	240	228
65°	174	171	166	163	161	171
75°	92	90	88	86	85	98
85°	24	24	24	23	23	27
90°	1	8	18	21	22	3
95°	45	17	23	28	28	56
105°	222	225	163	39	33	235
115°	415	420	427	434	437	410
125°	586	591	594	596	597	523
135°	729	733	736	738	736	561
145°	841	846	848	849	849	526
155°	927	925	926	929	925	427
165°	977	975	974	980	975	276
175°	1000	997	997	1002	996	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P332100-840

CATALOG NUMBER: S123DIW-S340D755U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2
2.5°	549.2	548.8	548.5	548.2	547.8	547.1	546.2	545.3	544.4	543.5	544.3
5°	547.8	547.1	546.6	546.1	545.6	544.8	543.6	542.5	541.3	540.2	541.2
7.5°	542.4	541.8	541.3	540.8	540.3	539.4	538.3	537.0	535.8	534.6	535.5
10°	537.9	537.3	536.7	536.2	535.7	534.8	533.4	532.1	530.7	529.4	530.3
12.5°	531.8	531.4	530.9	530.5	530.1	529.2	528.0	526.6	525.3	524.1	524.8
15°	521.4	521.0	520.5	520.1	519.7	518.8	517.5	516.0	514.7	513.4	514.2
17.5°	509.2	508.7	508.2	507.6	507.1	506.1	504.7	503.4	502.0	500.7	501.2
20°	500.2	499.6	499.0	498.3	497.7	496.7	495.3	493.9	492.6	491.3	491.7
22.5°	490.0	489.4	488.8	488.2	487.6	486.6	485.1	483.8	482.4	481.1	481.4
25°	473.3	472.7	472.1	471.5	470.9	469.9	468.5	467.2	465.7	464.4	464.5
27.5°	455.6	454.9	454.3	453.7	453.1	452.1	450.7	449.2	447.8	446.3	446.4
30°	442.8	442.2	441.7	441.2	440.7	439.7	438.3	436.8	435.4	433.8	433.8
32.5°	430.0	429.3	428.6	427.9	427.3	426.3	425.2	424.0	422.9	421.8	421.2
35°	409.4	408.8	408.1	407.5	406.9	405.9	404.6	403.1	401.8	400.4	399.8
37.5°	388.3	387.5	386.7	385.9	385.2	384.1	382.6	381.2	379.9	378.5	377.8
40°	373.7	372.9	372.3	371.7	371.1	370.0	368.6	367.1	365.7	364.2	363.3
42.5°	358.9	358.2	357.5	356.8	356.1	355.0	353.6	352.0	350.6	349.1	348.3
45°	335.5	335.1	334.7	334.3	333.9	333.0	331.5	330.2	328.8	327.5	326.3
47.5°	312.3	311.6	311.0	310.4	309.8	308.9	307.6	306.3	305.1	303.8	302.6
50°	296.4	295.9	295.4	294.9	294.4	293.4	292.1	290.7	289.3	288.0	286.8
52.5°	279.8	279.5	279.1	278.8	278.4	277.5	276.1	274.7	273.3	271.8	270.8
55°	254.6	254.5	254.4	254.3	254.2	253.4	252.1	250.6	249.3	248.0	246.8
57.5°	230.5	230.1	229.7	229.4	229.0	228.3	227.2	226.1	225.1	224.0	223.0
60°	213.2	213.1	213.0	212.9	212.8	212.1	210.8	209.5	208.3	207.0	206.1
62.5°	197.7	197.4	197.2	196.9	196.6	195.9	194.6	193.4	192.1	190.9	190.0
65°	173.6	173.1	172.6	172.1	171.6	170.8	169.8	168.6	167.6	166.5	165.7
67.5°	148.1	147.6	147.2	146.7	146.3	145.6	144.9	144.1	143.3	142.5	141.8
70°	132.7	132.1	131.5	130.8	130.2	129.6	129.0	128.3	127.6	127.0	126.3
72.5°	116.5	116.0	115.6	115.1	114.6	114.1	113.4	112.7	112.0	111.3	110.6
75°	91.8	91.3	90.9	90.5	90.1	89.7	89.4	89.1	88.8	88.5	88.0
77.5°	69.8	69.6	69.4	69.2	68.9	68.6	68.3	67.9	67.5	67.1	66.8
80°	55.5	55.2	54.9	54.6	54.2	54.0	53.8	53.6	53.4	53.2	53.0
82.5°	41.6	41.5	41.5	41.4	41.3	41.3	41.2	41.2	41.2	41.1	40.9
85°	24.4	24.2	24.0	23.8	23.6	23.5	23.5	23.5	23.5	23.5	23.3
87.5°	9.9	10.0	10.1	10.2	10.3	10.5	10.8	11.1	11.5	11.8	11.9
90°	0.7	2.4	4.0	5.7	7.4	9.3	11.4	13.5	15.7	17.9	18.5
92.5°	13.8	13.3	12.9	12.4	12.0	12.5	14.1	15.8	17.4	19.0	20.1
95°	45.3	38.6	31.8	25.0	18.3	15.8	17.6	19.4	21.2	23.0	24.2
97.5°	91.1	88.1	85.0	82.0	79.0	71.5	59.6	47.7	35.9	23.9	25.2
100°	125.6	128.9	132.2	135.5	138.8	127.5	101.8	76.0	50.3	24.5	25.9
102.5°	164.8	167.2	169.6	172.0	174.3	161.5	133.3	105.1	77.1	48.9	44.8
105°	221.5	223.3	225.1	226.9	228.7	222.2	207.3	192.5	177.6	162.8	133.5
107.5°	281.1	282.7	284.1	285.6	287.0	288.9	291.2	293.6	296.0	298.3	276.8
110°	321.0	322.3	323.7	325.0	326.3	327.9	329.7	331.5	333.4	335.2	329.7



TEST NUMBER: P332100-840

CATALOG NUMBER: S123DIW-S340D755U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	359.1	360.2	361.4	362.6	363.9	365.4	367.2	369.0	370.8	372.6	372.7
115°	415.4	416.4	417.4	418.4	419.4	420.6	422.1	423.5	425.1	426.6	428.2
117.5°	470.0	471.2	472.4	473.6	474.8	475.8	476.6	477.4	478.1	478.9	480.2
120°	503.8	505.3	506.9	508.3	509.8	510.8	511.3	511.8	512.3	512.7	514.1
122.5°	538.4	539.6	540.8	542.0	543.2	544.1	544.7	545.4	546.0	546.6	547.5
125°	585.6	586.9	588.2	589.6	590.9	591.9	592.5	593.2	593.8	594.5	594.8
127.5°	631.4	632.7	634.0	635.3	636.6	637.7	638.5	639.2	640.1	640.9	641.4
130°	659.8	661.3	662.6	663.9	665.2	666.2	666.8	667.5	668.1	668.8	669.4
132.5°	687.2	688.5	689.8	691.2	692.6	693.5	694.0	694.5	695.0	695.6	696.2
135°	729.0	730.0	730.9	732.0	733.0	733.8	734.5	735.1	735.8	736.4	736.9
137.5°	764.7	765.9	767.2	768.4	769.7	770.5	770.8	771.2	771.6	771.9	772.7
140°	788.4	789.4	790.4	791.4	792.4	793.1	793.7	794.2	794.7	795.2	795.8
142.5°	810.4	811.4	812.4	813.4	814.5	815.2	815.7	816.2	816.7	817.2	817.7
145°	841.2	842.3	843.5	844.7	845.9	846.6	846.9	847.3	847.6	847.9	848.2
147.5°	870.2	870.9	871.7	872.4	873.2	873.7	874.1	874.4	874.7	875.0	875.5
150°	888.1	888.5	889.0	889.5	890.0	890.4	890.8	891.1	891.4	891.7	892.1
152.5°	904.0	904.3	904.5	904.7	905.0	905.2	905.4	905.6	905.8	906.1	906.6
155°	926.7	926.3	926.0	925.6	925.3	925.2	925.4	925.6	925.7	925.9	926.8
157.5°	944.2	944.2	944.1	944.1	944.1	944.0	943.8	943.6	943.5	943.3	944.3
160°	954.9	954.7	954.6	954.4	954.2	954.1	953.9	953.7	953.6	953.4	954.4
162.5°	965.0	964.6	964.1	963.7	963.3	963.0	962.8	962.7	962.5	962.3	963.5
165°	977.2	976.7	976.2	975.7	975.2	974.9	974.7	974.5	974.4	974.2	975.5
167.5°	986.7	986.0	985.4	984.7	984.1	983.7	983.7	983.7	983.7	983.7	985.0
170°	992.1	991.4	990.8	990.1	989.5	989.1	989.1	989.1	989.1	989.1	990.4
172.5°	995.6	994.8	994.0	993.3	992.5	992.1	992.3	992.4	992.5	992.7	994.0
175°	1000.3	999.4	998.6	997.7	996.9	996.6	996.7	996.9	997.1	997.2	998.5
177.5°	1001.4	1000.8	1000.1	999.5	998.8	998.6	998.7	998.8	999.0	999.1	1000.1
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3



TEST NUMBER: P332100-840

CATALOG NUMBER: S123DIW-S340D755U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2
2.5°	545.1	546.0	546.8	547.2	547.1	547.0	546.9	546.8
5°	542.3	543.3	544.4	544.8	544.6	544.4	544.1	543.9
7.5°	536.5	537.5	538.4	538.8	538.7	538.6	538.5	538.3
10°	531.3	532.2	533.1	533.5	533.3	533.1	532.9	532.7
12.5°	525.4	526.1	526.8	527.1	527.0	526.8	526.7	526.6
15°	515.0	515.8	516.7	516.8	516.1	515.5	514.9	514.3
17.5°	501.8	502.4	503.0	503.2	502.9	502.7	502.5	502.3
20°	492.1	492.5	492.9	493.0	492.6	492.3	492.0	491.7
22.5°	481.7	482.1	482.4	482.4	482.0	481.6	481.2	480.8
25°	464.6	464.7	464.8	464.7	464.4	464.1	463.8	463.5
27.5°	446.5	446.6	446.6	446.5	446.1	445.7	445.2	444.8
30°	433.8	433.8	433.8	433.4	432.7	432.0	431.3	430.5
32.5°	420.6	420.0	419.5	419.0	418.6	418.2	417.8	417.4
35°	399.2	398.6	397.9	397.4	396.9	396.3	395.8	395.3
37.5°	377.0	376.3	375.5	375.0	374.7	374.3	374.0	373.7
40°	362.5	361.7	360.8	360.2	359.8	359.4	359.0	358.6
42.5°	347.5	346.6	345.8	345.2	344.8	344.4	344.0	343.5
45°	325.0	323.8	322.4	321.6	321.0	320.5	320.0	319.5
47.5°	301.3	300.1	298.8	298.0	297.5	297.1	296.6	296.2
50°	285.7	284.5	283.4	282.5	281.9	281.2	280.6	279.9
52.5°	269.8	268.8	267.8	267.0	266.4	265.8	265.2	264.6
55°	245.7	244.5	243.4	242.6	242.1	241.5	241.0	240.4
57.5°	222.0	220.9	219.8	219.0	218.4	217.8	217.2	216.6
60°	205.2	204.2	203.3	202.6	202.0	201.5	201.0	200.5
62.5°	188.9	188.0	187.1	186.4	186.1	185.7	185.4	185.0
65°	164.9	164.1	163.2	162.7	162.4	162.0	161.7	161.4
67.5°	141.0	140.3	139.6	139.0	138.6	138.0	137.6	137.2
70°	125.6	124.8	124.1	123.5	123.0	122.5	121.9	121.4
72.5°	110.0	109.3	108.7	108.2	108.0	107.7	107.3	107.0
75°	87.5	86.8	86.3	85.9	85.6	85.3	85.0	84.7
77.5°	66.3	66.0	65.6	65.5	65.5	65.5	65.5	65.5
80°	52.9	52.8	52.7	52.7	52.7	52.7	52.7	52.7
82.5°	40.8	40.6	40.4	40.2	40.2	40.1	40.0	39.9
85°	23.1	22.9	22.7	22.6	22.6	22.6	22.6	22.6
87.5°	11.9	12.0	12.0	12.1	12.1	12.2	12.3	12.3
90°	19.2	19.8	20.5	21.0	21.3	21.6	21.9	22.3
92.5°	21.1	22.2	23.2	23.8	24.0	24.2	24.4	24.6
95°	25.3	26.5	27.7	28.3	28.3	28.3	28.3	28.3
97.5°	26.6	27.9	29.2	30.0	30.1	30.3	30.5	30.6
100°	27.2	28.5	29.8	30.6	30.7	30.9	31.0	31.2
102.5°	40.7	36.7	32.5	30.6	30.9	31.2	31.5	31.8
105°	104.3	75.0	45.8	31.4	31.7	32.0	32.4	32.7
107.5°	255.4	234.0	212.6	190.9	168.7	146.7	124.7	102.7
110°	324.3	318.8	313.4	298.8	275.2	251.6	227.9	204.4



TEST NUMBER: P332100-840

CATALOG NUMBER: S123DIW-S340D755U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	372.8	372.9	373.0	370.5	365.6	360.6	355.6	350.6
115°	429.9	431.5	433.1	434.3	434.9	435.7	436.3	437.0
117.5°	481.5	482.8	484.1	484.8	485.0	485.1	485.2	485.4
120°	515.4	516.7	518.1	518.7	518.7	518.7	518.7	518.7
122.5°	548.5	549.4	550.4	550.9	551.0	551.1	551.3	551.4
125°	595.1	595.5	595.8	596.1	596.5	596.8	597.1	597.4
127.5°	642.0	642.5	643.0	643.1	642.8	642.4	642.1	641.8
130°	670.1	670.8	671.5	671.7	671.3	671.0	670.7	670.2
132.5°	696.9	697.5	698.2	698.3	697.8	697.4	696.9	696.4
135°	737.4	737.9	738.4	738.4	737.9	737.4	736.9	736.4
137.5°	773.6	774.4	775.2	775.4	775.1	774.7	774.4	774.1
140°	796.5	797.1	797.8	798.0	797.6	797.3	797.0	796.6
142.5°	818.2	818.7	819.2	819.3	818.8	818.4	817.9	817.4
145°	848.6	848.9	849.2	849.4	849.4	849.4	849.4	849.4
147.5°	875.8	876.1	876.5	876.2	875.5	874.6	873.9	873.1
150°	892.4	892.7	893.0	893.0	892.5	892.0	891.5	891.0
152.5°	907.2	907.8	908.4	908.3	907.6	906.8	906.1	905.2
155°	927.6	928.4	929.3	929.2	928.2	927.2	926.1	925.1
157.5°	945.3	946.2	947.3	947.2	945.8	944.5	943.3	942.0
160°	955.4	956.4	957.4	957.4	956.1	955.0	953.8	952.7
162.5°	964.6	965.7	966.8	966.8	965.8	964.8	963.8	962.8
165°	976.8	978.2	979.5	979.6	978.5	977.2	976.1	974.9
167.5°	986.3	987.7	989.1	989.1	987.7	986.3	985.0	983.7
170°	991.7	993.1	994.4	994.4	993.1	991.7	990.4	989.1
172.5°	995.3	996.6	997.9	997.8	996.4	995.0	993.5	992.1
175°	999.6	1000.8	1001.9	1001.8	1000.5	999.2	997.8	996.5
177.5°	1001.2	1002.2	1003.3	1003.1	1001.8	1000.5	999.2	997.8
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3

(END OF REPORT)