

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332136-840

Luminaire Tested: **S123DIW-S560D1030U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332136-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1030U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6508.3 lumens
Efficiency: N/A
Efficacy: 144.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332136-840

CATALOG NUMBER: S123DIW-S560D1030U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332136-840

CATALOG NUMBER: S123DIW-S560D1030U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36	30
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31	25
3	78	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26	21
4	72	61	53	48	65	56	49	44	45	40	36	36	32	29	27	24	22	18
5	66	54	46	41	59	50	43	37	40	35	31	32	28	25	24	21	19	16
6	60	49	41	35	55	44	37	32	36	31	27	29	25	22	22	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9684	9684	9684
5°	9729	9596	9662
10°	9664	9512	9571
15°	9551	9404	9423
20°	9419	9251	9260
25°	9242	9069	9049
30°	9047	8866	8797
35°	8843	8650	8539
40°	8630	8413	8283
45°	8397	8196	7995
50°	8162	7927	7708
55°	7854	7651	7418
60°	7543	7326	7093
65°	7272	6976	6757
70°	6864	6571	6279
75°	6276	6047	5793
80°	5659	5424	5368
85°	4965	4780	4594



TEST NUMBER: P332136-840

CATALOG NUMBER: S123DIW-S560D1030U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.7	1.3
10°-20°	239.3	3.7
20°-30°	353.5	5.4
30°-40°	412.9	6.3
40°-50°	415.1	6.4
50°-60°	364.6	5.6
60°-70°	271.7	4.2
70°-80°	154.8	2.4
80°-90°	48.3	0.7
90°-100°	49.6	0.8
100°-110°	236.6	3.6
110°-120°	568.2	8.7
120°-130°	723.6	11.1
130°-140°	773.1	11.9
140°-150°	723.0	11.1
150°-160°	583.2	9.0
160°-170°	376.4	5.8
170°-180°	129.7	2.0
0°-30°	677.5	10.4
0°-40°	1090.4	16.8
0°-60°	1870.2	28.7
0°-90°	2344.9	36.0
90°-120°	854.5	13.1
90°-150°	3074.2	47.2
90°-180°	4163.0	64.0
0°-180°	6508.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	900	900	900	900	900	
5°	900	896	888	895	894	85
15°	857	854	844	850	846	242
25°	778	773	764	764	762	358
35°	673	668	658	654	650	421
45°	552	548	538	529	525	426
55°	418	417	408	399	395	375
65°	286	281	274	268	265	282
75°	151	148	145	142	139	161
85°	40	39	39	37	37	44
90°	1	11	24	28	30	5
95°	62	23	31	38	39	76
105°	302	308	222	53	45	320
115°	567	573	582	592	596	560
125°	799	807	811	813	816	714
135°	995	1001	1005	1008	1005	766
145°	1148	1155	1157	1159	1159	718
155°	1265	1263	1264	1268	1263	583
165°	1334	1331	1330	1337	1331	377
175°	1365	1361	1361	1368	1360	130
180°	1365	1365	1365	1365	1365	



TEST NUMBER: P332136-840

CATALOG NUMBER: S123DIW-S560D1030U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7
2.5°	902.7	902.2	901.7	901.1	900.6	899.5	898.0	896.5	895.0	893.5	894.8
5°	900.4	899.6	898.7	897.9	897.0	895.6	893.7	891.8	890.0	888.1	889.8
7.5°	891.6	890.8	889.9	889.1	888.2	886.8	884.8	882.8	880.9	879.0	880.5
10°	884.2	883.3	882.5	881.6	880.8	879.2	877.0	874.7	872.5	870.3	871.8
12.5°	874.3	873.5	872.8	872.1	871.4	870.0	867.9	865.8	863.7	861.6	862.7
15°	857.1	856.5	855.8	855.1	854.3	852.9	850.7	848.5	846.2	843.9	845.4
17.5°	837.2	836.3	835.4	834.5	833.5	832.0	829.8	827.6	825.4	823.0	824.0
20°	822.3	821.3	820.2	819.2	818.2	816.6	814.4	812.1	809.8	807.6	808.3
22.5°	805.6	804.6	803.5	802.5	801.4	799.8	797.6	795.4	793.1	790.9	791.4
25°	778.2	777.2	776.2	775.2	774.1	772.4	770.2	768.0	765.8	763.6	763.7
27.5°	749.0	748.0	747.0	746.0	745.0	743.3	740.8	738.5	736.1	733.7	733.8
30°	727.9	727.1	726.2	725.4	724.5	722.9	720.4	718.0	715.7	713.3	713.3
32.5°	706.9	705.8	704.6	703.5	702.4	700.8	699.0	697.1	695.3	693.5	692.5
35°	673.0	672.0	671.0	669.9	668.9	667.2	665.0	662.8	660.6	658.3	657.3
37.5°	638.3	637.0	635.7	634.4	633.1	631.4	629.0	626.8	624.5	622.3	621.1
40°	614.2	613.2	612.2	611.2	610.1	608.3	605.9	603.6	601.2	598.7	597.3
42.5°	590.1	589.0	587.7	586.5	585.4	583.6	581.2	578.9	576.4	574.0	572.6
45°	551.6	550.9	550.2	549.5	548.8	547.3	545.1	542.9	540.7	538.4	536.3
47.5°	513.3	512.3	511.4	510.4	509.4	507.8	505.7	503.6	501.5	499.4	497.4
50°	487.4	486.5	485.6	484.7	483.9	482.4	480.1	477.9	475.6	473.4	471.5
52.5°	460.1	459.5	459.0	458.4	457.8	456.3	453.9	451.6	449.2	446.9	445.2
55°	418.5	418.3	418.2	418.0	417.8	416.6	414.3	412.1	409.9	407.7	405.8
57.5°	378.9	378.3	377.7	377.2	376.6	375.4	373.5	371.8	370.0	368.2	366.6
60°	350.4	350.2	350.1	349.9	349.7	348.6	346.6	344.5	342.4	340.3	338.8
62.5°	325.1	324.6	324.2	323.8	323.3	322.0	319.9	317.9	315.8	313.8	312.3
65°	285.5	284.6	283.8	282.9	282.1	280.7	279.0	277.3	275.6	273.9	272.5
67.5°	243.5	242.8	242.0	241.3	240.4	239.4	238.1	236.8	235.5	234.3	233.1
70°	218.1	217.1	216.1	215.1	214.0	213.0	212.0	211.0	209.8	208.8	207.6
72.5°	191.6	190.8	190.1	189.2	188.5	187.5	186.4	185.2	184.0	182.9	181.8
75°	150.9	150.2	149.5	148.8	148.1	147.5	146.9	146.4	145.9	145.4	144.6
77.5°	114.8	114.4	114.0	113.7	113.3	112.8	112.2	111.6	110.9	110.3	109.8
80°	91.3	90.8	90.3	89.8	89.2	88.8	88.5	88.1	87.8	87.5	87.3
82.5°	68.4	68.3	68.2	68.1	68.0	67.9	67.9	67.8	67.7	67.7	67.3
85°	40.2	39.9	39.6	39.2	38.9	38.7	38.7	38.7	38.7	38.7	38.4
87.5°	16.3	16.4	16.4	16.4	16.5	16.7	17.2	17.6	18.1	18.5	18.5
90°	1.0	3.2	5.6	7.8	10.0	12.6	15.6	18.5	21.4	24.3	25.2
92.5°	18.9	18.3	17.6	17.0	16.4	17.2	19.4	21.5	23.7	26.0	27.4
95°	61.9	52.6	43.4	34.1	24.9	21.5	24.0	26.5	29.0	31.4	33.0
97.5°	124.3	120.2	116.0	111.9	107.8	97.6	81.4	65.1	48.9	32.6	34.4
100°	171.4	175.9	180.5	184.9	189.5	174.1	139.0	103.8	68.7	33.4	35.2
102.5°	225.0	228.2	231.5	234.7	237.9	220.4	182.0	143.6	105.1	66.8	61.2
105°	302.3	304.8	307.2	309.7	312.1	303.3	283.0	262.7	242.5	222.2	182.3
107.5°	383.8	385.8	387.8	389.8	391.7	394.4	397.6	400.7	403.9	407.2	377.9
110°	438.2	440.0	441.8	443.6	445.4	447.6	450.0	452.5	454.9	457.5	450.0



TEST NUMBER: P332136-840

CATALOG NUMBER: S123DIW-S560D1030U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	490.1	491.7	493.3	495.0	496.7	498.7	501.1	503.6	506.1	508.6	508.7
115°	567.0	568.4	569.7	571.1	572.4	574.1	576.1	578.1	580.2	582.2	584.5
117.5°	641.5	643.1	644.8	646.4	648.1	649.4	650.6	651.6	652.6	653.6	655.4
120°	687.7	689.7	691.8	693.8	695.8	697.2	697.8	698.5	699.2	699.8	701.7
122.5°	734.8	736.4	738.1	739.7	741.4	742.7	743.6	744.4	745.3	746.1	747.4
125°	799.3	801.1	802.8	804.7	806.5	807.9	808.7	809.6	810.5	811.4	811.9
127.5°	861.7	863.5	865.4	867.2	869.0	870.4	871.5	872.6	873.6	874.7	875.5
130°	900.7	902.5	904.3	906.2	908.0	909.3	910.2	911.1	912.0	912.9	913.8
132.5°	938.1	939.9	941.6	943.4	945.2	946.5	947.3	948.0	948.7	949.4	950.3
135°	995.0	996.4	997.7	999.1	1000.5	1001.6	1002.5	1003.4	1004.3	1005.2	1005.8
137.5°	1043.7	1045.4	1047.1	1048.8	1050.6	1051.7	1052.2	1052.7	1053.2	1053.7	1054.7
140°	1076.2	1077.5	1078.9	1080.3	1081.6	1082.6	1083.3	1084.0	1084.6	1085.3	1086.2
142.5°	1106.2	1107.5	1108.9	1110.2	1111.7	1112.7	1113.3	1114.0	1114.7	1115.3	1116.1
145°	1148.2	1149.7	1151.3	1153.0	1154.5	1155.5	1156.0	1156.4	1156.9	1157.3	1157.8
147.5°	1187.8	1188.8	1189.8	1190.8	1191.9	1192.7	1193.1	1193.6	1194.0	1194.5	1194.9
150°	1212.1	1212.7	1213.5	1214.2	1214.8	1215.4	1215.8	1216.3	1216.7	1217.2	1217.6
152.5°	1234.1	1234.4	1234.7	1235.0	1235.3	1235.6	1235.9	1236.1	1236.4	1236.7	1237.5
155°	1264.9	1264.4	1263.9	1263.5	1263.0	1262.9	1263.1	1263.3	1263.6	1263.8	1265.0
157.5°	1288.8	1288.8	1288.7	1288.7	1288.6	1288.5	1288.3	1288.0	1287.8	1287.6	1288.9
160°	1303.4	1303.1	1302.9	1302.7	1302.5	1302.2	1302.0	1301.8	1301.6	1301.4	1302.7
162.5°	1317.2	1316.6	1316.1	1315.5	1314.8	1314.4	1314.2	1314.0	1313.7	1313.5	1315.0
165°	1333.8	1333.1	1332.5	1331.8	1331.1	1330.7	1330.4	1330.2	1330.0	1329.8	1331.6
167.5°	1346.8	1345.9	1345.0	1344.1	1343.2	1342.7	1342.7	1342.7	1342.7	1342.7	1344.5
170°	1354.1	1353.2	1352.3	1351.4	1350.5	1350.1	1350.1	1350.1	1350.1	1350.1	1351.8
172.5°	1359.0	1357.9	1356.9	1355.7	1354.6	1354.2	1354.3	1354.5	1354.7	1354.9	1356.8
175°	1365.2	1364.1	1363.0	1361.9	1360.8	1360.3	1360.5	1360.8	1361.0	1361.2	1362.8
177.5°	1366.9	1365.9	1365.1	1364.2	1363.3	1362.9	1363.1	1363.3	1363.4	1363.6	1365.1
180°	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2



TEST NUMBER: P332136-840

CATALOG NUMBER: S123DIW-S560D1030U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7
2.5°	896.3	897.6	899.0	899.6	899.5	899.3	899.2	899.1
5°	891.5	893.2	894.9	895.6	895.2	894.9	894.6	894.2
7.5°	882.0	883.5	885.1	885.8	885.6	885.3	885.1	884.9
10°	873.3	874.9	876.5	877.1	876.8	876.4	876.1	875.7
12.5°	863.8	865.1	866.2	866.6	866.4	866.2	866.0	865.8
15°	846.8	848.1	849.5	849.6	848.6	847.6	846.6	845.6
17.5°	825.1	826.0	827.0	827.2	826.9	826.5	826.1	825.7
20°	809.0	809.7	810.3	810.4	809.9	809.4	808.9	808.4
22.5°	792.0	792.5	793.1	793.0	792.4	791.7	791.1	790.4
25°	763.9	764.1	764.2	764.1	763.6	763.1	762.4	761.9
27.5°	734.0	734.1	734.2	734.0	733.3	732.7	732.0	731.3
30°	713.3	713.3	713.3	712.7	711.4	710.2	709.0	707.8
32.5°	691.6	690.5	689.5	688.7	688.1	687.5	686.8	686.2
35°	656.2	655.2	654.2	653.3	652.4	651.6	650.7	649.8
37.5°	619.8	618.5	617.3	616.4	615.9	615.3	614.8	614.2
40°	596.0	594.6	593.3	592.2	591.5	590.9	590.2	589.5
42.5°	571.3	569.9	568.5	567.4	566.7	566.1	565.4	564.7
45°	534.3	532.2	530.2	528.7	527.9	526.9	526.1	525.2
47.5°	495.3	493.3	491.3	489.9	489.2	488.4	487.7	486.9
50°	469.7	467.8	465.9	464.4	463.3	462.3	461.3	460.3
52.5°	443.6	442.0	440.4	439.0	438.0	437.0	436.0	434.9
55°	403.8	402.0	400.1	398.7	397.9	397.0	396.2	395.3
57.5°	364.9	363.1	361.5	360.1	359.1	358.2	357.2	356.2
60°	337.3	335.8	334.2	333.0	332.1	331.2	330.4	329.5
62.5°	310.6	309.1	307.6	306.5	305.9	305.4	304.8	304.2
65°	271.0	269.7	268.3	267.4	266.9	266.4	265.9	265.3
67.5°	231.9	230.7	229.4	228.4	227.7	227.0	226.3	225.6
70°	206.4	205.3	204.1	203.0	202.2	201.3	200.5	199.5
72.5°	180.8	179.7	178.6	177.8	177.4	176.9	176.5	176.0
75°	143.7	142.9	142.0	141.3	140.8	140.3	139.8	139.3
77.5°	109.2	108.6	108.0	107.7	107.7	107.7	107.7	107.7
80°	87.1	86.8	86.7	86.6	86.6	86.6	86.6	86.6
82.5°	67.0	66.7	66.3	66.1	66.0	65.8	65.7	65.6
85°	38.0	37.7	37.3	37.2	37.2	37.2	37.2	37.2
87.5°	18.6	18.6	18.7	18.7	18.8	18.9	19.0	19.1
90°	26.2	27.1	28.0	28.6	29.1	29.5	30.0	30.4
92.5°	28.9	30.3	31.7	32.6	32.8	33.1	33.4	33.6
95°	34.6	36.2	37.8	38.6	38.6	38.6	38.6	38.6
97.5°	36.3	38.1	39.9	40.9	41.1	41.3	41.6	41.8
100°	37.1	38.9	40.7	41.7	41.9	42.1	42.4	42.6
102.5°	55.5	50.0	44.3	41.8	42.2	42.6	43.0	43.4
105°	142.4	102.4	62.5	42.8	43.3	43.7	44.1	44.6
107.5°	348.6	319.4	290.1	260.4	230.4	200.4	170.3	140.2
110°	442.6	435.2	427.7	407.9	375.7	343.4	311.1	278.9



TEST NUMBER: P332136-840

CATALOG NUMBER: S123DIW-S560D1030U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	508.9	509.0	509.1	505.7	499.0	492.2	485.3	478.6
115°	586.7	589.0	591.3	592.8	593.7	594.6	595.5	596.4
117.5°	657.2	659.0	660.9	661.9	662.0	662.2	662.4	662.6
120°	703.5	705.3	707.1	708.0	708.0	708.0	708.0	708.0
122.5°	748.6	749.9	751.1	751.9	752.0	752.2	752.5	752.7
125°	812.3	812.8	813.2	813.7	814.2	814.6	815.1	815.5
127.5°	876.2	876.9	877.7	877.8	877.3	876.9	876.5	876.0
130°	914.7	915.5	916.5	916.8	916.3	915.8	915.3	914.9
132.5°	951.2	952.1	953.0	953.1	952.5	951.9	951.3	950.6
135°	1006.5	1007.2	1007.8	1007.8	1007.2	1006.5	1005.8	1005.2
137.5°	1055.8	1056.9	1058.0	1058.3	1057.8	1057.4	1056.9	1056.5
140°	1087.1	1088.0	1088.9	1089.1	1088.7	1088.2	1087.8	1087.3
142.5°	1116.8	1117.5	1118.2	1118.2	1117.6	1117.0	1116.4	1115.7
145°	1158.2	1158.7	1159.1	1159.3	1159.3	1159.3	1159.3	1159.3
147.5°	1195.4	1195.8	1196.3	1196.0	1195.0	1193.9	1192.9	1191.8
150°	1218.1	1218.5	1219.0	1218.9	1218.2	1217.5	1216.9	1216.2
152.5°	1238.3	1239.1	1239.9	1239.8	1238.7	1237.7	1236.7	1235.7
155°	1266.1	1267.2	1268.4	1268.2	1266.9	1265.6	1264.1	1262.8
157.5°	1290.3	1291.6	1292.9	1292.7	1291.0	1289.3	1287.5	1285.8
160°	1304.0	1305.5	1306.8	1306.7	1305.0	1303.5	1301.9	1300.3
162.5°	1316.6	1318.2	1319.7	1319.7	1318.4	1317.0	1315.6	1314.1
165°	1333.3	1335.1	1337.0	1337.1	1335.5	1333.9	1332.3	1330.8
167.5°	1346.4	1348.2	1350.0	1350.0	1348.2	1346.4	1344.5	1342.7
170°	1353.6	1355.4	1357.3	1357.3	1355.4	1353.6	1351.8	1350.1
172.5°	1358.6	1360.3	1362.1	1362.0	1360.1	1358.1	1356.0	1354.1
175°	1364.3	1365.9	1367.6	1367.5	1365.6	1363.8	1362.0	1360.2
177.5°	1366.5	1368.0	1369.4	1369.3	1367.5	1365.6	1363.8	1362.0
180°	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2

(END OF REPORT)