

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332456-930

Luminaire Tested: **S123RDIW-S1000D755U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332456-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1000D755U930-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 755 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5555.7 lumens  
Efficiency: N/A  
Efficacy: 103.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332456-930

CATALOG NUMBER: S123RDIW-S1000D755U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332456-930

CATALOG NUMBER: S123RDIW-S1000D755U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	54	53	48
2	91	84	78	72	84	78	73	68	67	63	60	58	55	52	49	47	45	40
3	83	74	67	61	77	69	63	57	60	55	51	51	48	45	43	41	39	35
4	76	66	58	52	71	61	54	49	53	48	44	46	42	38	39	36	33	30
5	70	59	51	45	65	55	48	42	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	49	42	37	43	38	33	38	33	30	32	29	26	23
7	60	48	40	34	56	45	38	33	39	34	29	34	30	26	29	26	23	21
8	56	43	36	30	52	41	34	29	36	30	26	31	27	24	27	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	24	21	25	22	19	17
10	49	37	29	25	45	34	28	23	31	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14727	14727	14727
5°	14783	14579	14664
10°	14700	14397	14348
15°	14542	14060	13912
20°	14325	13639	13321
25°	14101	13166	12744
30°	13806	12621	11931
35°	13502	12073	11184
40°	13222	11428	10260
45°	12855	10794	9426
50°	12450	10071	8492
55°	12037	9246	7621
60°	11657	8361	6665
65°	11163	7404	5708
70°	10546	6216	4611
75°	9649	4891	4338
80°	8598	4333	3986
85°	7262	3841	3569



TEST NUMBER: P332456-930

CATALOG NUMBER: S123RDIW-S1000D755U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.5	2.3
10°-20°	357.5	6.4
20°-30°	514.7	9.3
30°-40°	579.8	10.4
40°-50°	554.7	10.0
50°-60°	454.2	8.2
60°-70°	306.5	5.5
70°-80°	154.2	2.8
80°-90°	43.1	0.8
90°-100°	29.4	0.5
100°-110°	139.9	2.5
110°-120°	336.1	6.0
120°-130°	428.0	7.7
130°-140°	457.3	8.2
140°-150°	427.6	7.7
150°-160°	344.9	6.2
160°-170°	222.6	4.0
170°-180°	76.7	1.4
0°-30°	1000.7	18.0
0°-40°	1580.5	28.4
0°-60°	2589.5	46.6
0°-90°	3093.2	55.7
90°-120°	505.4	9.1
90°-150°	1818.3	32.7
90°-180°	2463.0	44.3
0°-180°	5555.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1368	1368	1368	1368	1368	
5°	1368	1362	1349	1359	1357	130
15°	1305	1292	1262	1256	1248	367
25°	1187	1158	1109	1086	1073	546
35°	1028	986	919	873	851	643
45°	844	793	709	648	619	651
55°	641	585	493	431	406	575
65°	438	376	291	239	224	434
75°	232	178	118	107	104	247
85°	59	36	31	29	29	66
90°	1	7	14	17	18	5
95°	37	14	19	23	23	45
105°	179	182	131	31	26	190
115°	335	339	344	350	353	331
125°	473	477	480	481	482	422
135°	589	592	594	596	594	453
145°	679	683	684	686	686	425
155°	748	747	748	750	747	345
165°	789	787	786	791	787	223
175°	808	805	805	809	804	77
180°	808	808	808	808	808	



TEST NUMBER: P332456-930

CATALOG NUMBER: S123RDIW-S1000D755U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1372.6	1371.8	1371.1	1370.3	1369.5	1367.9	1365.5	1363.2	1360.8	1358.5	1360.6
5°	1368.2	1366.9	1365.7	1364.5	1363.3	1361.1	1358.2	1355.3	1352.3	1349.3	1351.5
7.5°	1355.5	1354.2	1352.9	1351.5	1350.2	1347.6	1343.8	1339.9	1336.1	1332.3	1333.5
10°	1344.9	1343.2	1341.4	1339.7	1338.0	1334.9	1330.5	1326.0	1321.6	1317.2	1317.4
12.5°	1329.8	1327.9	1326.0	1324.0	1322.1	1318.4	1313.0	1307.6	1302.2	1296.7	1296.6
15°	1305.0	1302.3	1299.5	1296.8	1294.1	1289.3	1282.4	1275.5	1268.6	1261.7	1260.5
17.5°	1273.7	1270.5	1267.4	1264.2	1261.0	1255.1	1246.3	1237.5	1228.7	1219.9	1217.3
20°	1250.6	1246.7	1242.7	1238.8	1234.8	1228.2	1218.8	1209.4	1200.0	1190.7	1187.5
22.5°	1224.8	1220.3	1215.8	1211.2	1206.7	1199.5	1189.4	1179.5	1169.5	1159.6	1155.6
25°	1187.3	1181.2	1175.0	1168.8	1162.7	1153.9	1142.6	1131.2	1119.9	1108.6	1103.3
27.5°	1141.8	1135.1	1128.2	1121.4	1114.6	1104.9	1092.3	1079.6	1067.0	1054.4	1047.2
30°	1110.8	1103.3	1096.0	1088.6	1081.2	1070.6	1056.8	1042.9	1029.2	1015.4	1007.0
32.5°	1079.7	1071.3	1062.9	1054.5	1046.2	1034.7	1020.1	1005.5	990.8	976.2	967.1
35°	1027.5	1018.6	1009.7	1000.9	992.1	979.9	964.7	949.3	934.1	918.8	908.2
37.5°	974.7	964.8	955.0	945.1	935.2	922.2	905.9	889.5	873.2	856.9	844.8
40°	941.0	930.2	919.2	908.4	897.6	883.4	865.9	848.4	830.9	813.3	800.5
42.5°	902.8	891.9	881.1	870.3	859.4	845.0	826.9	808.8	790.7	772.6	758.6
45°	844.5	833.3	822.2	811.1	800.1	785.1	766.1	747.1	728.1	709.1	695.0
47.5°	786.1	773.9	761.7	749.5	737.4	721.8	702.8	683.8	664.8	645.8	630.6
50°	743.5	731.9	720.3	708.7	697.1	681.3	661.4	641.4	621.4	601.4	586.1
52.5°	705.3	692.8	680.1	667.6	655.0	638.8	619.1	599.2	579.5	559.7	543.8
55°	641.4	629.3	617.2	605.1	593.0	576.5	555.5	534.6	513.6	492.7	478.4
57.5°	582.4	569.2	556.0	542.8	529.7	512.6	491.5	470.4	449.4	428.4	414.8
60°	541.5	528.0	514.4	500.8	487.2	470.3	449.8	429.3	408.9	388.4	375.0
62.5°	500.7	487.1	473.5	460.0	446.5	429.4	409.0	388.5	368.0	347.6	335.0
65°	438.3	424.8	411.2	397.6	384.1	367.7	348.5	329.2	310.0	290.7	278.7
67.5°	375.9	362.2	348.5	334.8	321.1	305.0	286.6	268.2	249.7	231.2	222.3
70°	335.1	321.8	308.5	295.1	281.8	266.6	249.3	232.0	214.7	197.5	188.9
72.5°	294.2	281.2	268.1	254.9	241.8	227.4	211.7	196.1	180.3	164.7	157.6
75°	232.0	220.0	208.2	196.4	184.6	171.9	158.3	144.7	131.2	117.6	115.1
77.5°	175.1	164.4	153.7	143.0	132.3	122.5	113.8	105.1	96.4	87.6	86.3
80°	138.7	128.6	118.5	108.4	98.2	90.7	85.4	80.2	75.1	69.9	69.1
82.5°	104.1	95.4	86.7	77.9	69.1	63.6	61.1	58.8	56.3	53.9	53.2
85°	58.8	53.4	47.9	42.6	37.1	34.0	33.3	32.5	31.8	31.1	30.6
87.5°	21.4	19.5	17.6	15.7	13.8	13.0	13.4	13.7	14.1	14.4	14.3
90°	0.6	2.0	3.3	4.6	6.0	7.5	9.2	10.9	12.6	14.4	14.9
92.5°	11.2	10.8	10.4	10.0	9.7	10.1	11.4	12.7	14.0	15.3	16.2
95°	36.6	31.1	25.7	20.2	14.8	12.7	14.2	15.7	17.1	18.6	19.6
97.5°	73.5	71.1	68.6	66.2	63.8	57.7	48.1	38.5	28.9	19.3	20.4
100°	101.4	104.0	106.7	109.4	112.0	103.0	82.2	61.4	40.6	19.8	20.9
102.5°	133.1	135.0	136.9	138.8	140.7	130.4	107.6	84.9	62.2	39.5	36.2
105°	178.8	180.3	181.7	183.2	184.7	179.4	167.4	155.4	143.4	131.4	107.8
107.5°	227.0	228.2	229.3	230.6	231.7	233.3	235.1	237.0	239.0	240.8	223.5
110°	259.2	260.2	261.3	262.4	263.4	264.7	266.2	267.7	269.1	270.6	266.2



TEST NUMBER: P332456-930

CATALOG NUMBER: S123RDIW-S1000D755U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	289.9	290.8	291.8	292.8	293.8	295.0	296.4	297.9	299.4	300.8	300.9
115°	335.3	336.1	337.0	337.8	338.6	339.6	340.8	341.9	343.2	344.4	345.7
117.5°	379.4	380.4	381.4	382.4	383.4	384.2	384.7	385.4	386.0	386.6	387.7
120°	406.8	408.0	409.2	410.3	411.6	412.4	412.8	413.2	413.6	413.9	415.1
122.5°	434.6	435.6	436.6	437.6	438.5	439.3	439.8	440.3	440.8	441.3	442.1
125°	472.8	473.9	474.9	476.0	477.0	477.8	478.3	478.9	479.4	480.0	480.2
127.5°	509.7	510.8	511.8	512.9	514.0	514.9	515.5	516.1	516.7	517.4	517.8
130°	532.7	533.9	534.9	536.0	537.0	537.9	538.3	538.9	539.4	540.0	540.5
132.5°	554.8	555.9	556.9	558.0	559.1	559.9	560.3	560.7	561.1	561.6	562.1
135°	588.6	589.4	590.1	590.9	591.7	592.4	593.0	593.5	594.0	594.5	594.9
137.5°	617.3	618.3	619.4	620.4	621.4	622.1	622.3	622.6	623.0	623.2	623.9
140°	636.5	637.3	638.1	639.0	639.8	640.3	640.7	641.2	641.6	642.0	642.5
142.5°	654.3	655.1	655.9	656.7	657.5	658.1	658.5	658.9	659.3	659.7	660.1
145°	679.1	680.0	681.0	681.9	682.9	683.5	683.7	684.0	684.3	684.5	684.8
147.5°	702.5	703.1	703.8	704.3	705.0	705.4	705.7	706.0	706.2	706.5	706.8
150°	717.0	717.3	717.7	718.1	718.5	718.8	719.2	719.4	719.7	719.9	720.2
152.5°	729.9	730.1	730.3	730.4	730.7	730.8	731.0	731.2	731.3	731.5	731.9
155°	748.1	747.9	747.6	747.3	747.1	747.0	747.1	747.3	747.4	747.5	748.2
157.5°	762.3	762.3	762.2	762.2	762.2	762.1	762.0	761.8	761.7	761.6	762.4
160°	770.9	770.8	770.7	770.5	770.4	770.3	770.1	770.0	769.9	769.7	770.5
162.5°	779.1	778.8	778.4	778.0	777.7	777.5	777.3	777.2	777.1	776.9	777.9
165°	789.0	788.6	788.1	787.7	787.3	787.1	786.9	786.8	786.7	786.5	787.6
167.5°	796.6	796.1	795.6	795.0	794.5	794.2	794.2	794.2	794.2	794.2	795.2
170°	801.0	800.4	799.9	799.3	798.8	798.5	798.5	798.5	798.5	798.5	799.6
172.5°	803.8	803.2	802.5	801.9	801.3	801.0	801.1	801.2	801.3	801.4	802.5
175°	807.6	806.8	806.2	805.5	804.9	804.6	804.7	804.9	805.0	805.1	806.1
177.5°	808.5	808.0	807.4	806.9	806.3	806.2	806.2	806.3	806.5	806.6	807.4
180°	807.6	807.6	807.6	807.6	807.6	807.6	807.6	807.6	807.6	807.6	807.6



TEST NUMBER: P332456-930

CATALOG NUMBER: S123RDIW-S1000D755U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1362.8	1365.0	1367.1	1368.0	1367.6	1367.3	1366.8	1366.4
5°	1353.8	1356.0	1358.2	1359.1	1358.6	1358.1	1357.6	1357.1
7.5°	1334.7	1335.9	1337.2	1337.4	1336.5	1335.7	1334.9	1334.0
10°	1317.7	1317.9	1318.2	1317.7	1316.4	1315.2	1313.9	1312.7
12.5°	1296.4	1296.3	1296.2	1295.3	1294.0	1292.5	1291.1	1289.6
15°	1259.2	1258.0	1256.8	1255.2	1253.5	1251.8	1250.1	1248.4
17.5°	1214.7	1212.1	1209.5	1206.9	1204.4	1201.8	1199.2	1196.6
20°	1184.2	1181.0	1177.9	1174.8	1171.8	1168.8	1165.9	1162.9
22.5°	1151.6	1147.6	1143.6	1140.2	1137.5	1134.7	1132.0	1129.2
25°	1098.2	1093.0	1087.9	1083.9	1081.2	1078.5	1075.8	1073.0
27.5°	1040.0	1032.8	1025.6	1019.9	1015.8	1011.6	1007.5	1003.4
30°	998.6	990.2	981.8	975.7	971.7	967.8	963.8	959.9
32.5°	957.9	948.8	939.6	932.9	928.8	924.6	920.5	916.3
35°	897.6	887.0	876.4	868.9	864.5	860.0	855.6	851.1
37.5°	832.8	820.8	808.8	800.0	794.5	789.0	783.6	778.1
40°	787.7	774.9	762.1	752.8	747.1	741.5	735.8	730.2
42.5°	744.5	730.5	716.5	706.9	701.9	696.8	691.7	686.6
45°	680.9	666.9	652.8	642.9	636.9	631.0	625.1	619.2
47.5°	615.2	600.0	584.7	574.4	569.1	563.9	558.6	553.3
50°	570.9	555.5	540.3	529.8	524.2	518.4	512.8	507.1
52.5°	528.0	512.1	496.2	485.7	480.6	475.6	470.5	465.4
55°	464.1	449.8	435.5	425.8	420.9	416.0	411.1	406.1
57.5°	401.3	387.8	374.3	365.4	361.3	357.0	352.9	348.6
60°	361.7	348.5	335.1	326.4	322.2	318.0	313.8	309.6
62.5°	322.5	310.0	297.4	288.9	284.6	280.2	275.8	271.4
65°	266.6	254.5	242.4	235.0	232.3	229.6	226.9	224.1
67.5°	213.2	204.2	195.2	189.1	186.3	183.4	180.4	177.6
70°	180.3	171.6	163.0	157.4	154.6	151.9	149.2	146.5
72.5°	150.6	143.5	136.5	132.4	131.3	130.1	129.0	127.8
75°	112.7	110.2	107.8	106.3	105.8	105.3	104.8	104.3
77.5°	85.0	83.6	82.3	81.4	81.0	80.5	80.0	79.5
80°	68.4	67.7	66.9	66.4	65.9	65.4	64.8	64.3
82.5°	52.4	51.7	51.0	50.5	50.5	50.4	50.2	50.1
85°	30.1	29.6	29.1	28.9	28.9	28.9	28.9	28.9
87.5°	14.3	14.2	14.0	13.9	13.8	13.6	13.5	13.4
90°	15.5	16.0	16.6	17.0	17.2	17.4	17.7	18.0
92.5°	17.0	17.9	18.8	19.2	19.4	19.6	19.7	19.9
95°	20.5	21.4	22.3	22.8	22.8	22.8	22.8	22.8
97.5°	21.4	22.5	23.6	24.2	24.3	24.5	24.6	24.7
100°	21.9	23.0	24.1	24.7	24.8	24.9	25.0	25.2
102.5°	32.9	29.6	26.3	24.7	24.9	25.2	25.4	25.7
105°	84.2	60.6	37.0	25.4	25.6	25.8	26.2	26.4
107.5°	206.2	188.9	171.6	154.1	136.2	118.5	100.7	82.9
110°	261.8	257.4	253.0	241.2	222.2	203.1	184.0	165.0





TEST NUMBER: P332456-930

CATALOG NUMBER: S123RDIW-S1000D755U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	301.0	301.1	301.2	299.1	295.1	291.1	287.1	283.1
115°	347.1	348.4	349.7	350.7	351.1	351.7	352.2	352.8
117.5°	388.7	389.8	390.9	391.4	391.6	391.7	391.8	391.9
120°	416.1	417.2	418.2	418.7	418.7	418.7	418.7	418.7
122.5°	442.8	443.5	444.3	444.7	444.8	444.9	445.1	445.2
125°	480.5	480.8	481.0	481.3	481.6	481.8	482.1	482.3
127.5°	518.3	518.7	519.1	519.2	518.9	518.6	518.4	518.1
130°	541.0	541.5	542.1	542.3	541.9	541.7	541.4	541.1
132.5°	562.6	563.1	563.7	563.8	563.4	563.0	562.6	562.2
135°	595.3	595.7	596.1	596.1	595.7	595.3	594.9	594.5
137.5°	624.5	625.2	625.8	626.0	625.7	625.4	625.2	624.9
140°	643.0	643.5	644.1	644.2	643.9	643.7	643.4	643.1
142.5°	660.6	661.0	661.4	661.5	661.0	660.7	660.3	659.9
145°	685.1	685.3	685.6	685.7	685.7	685.7	685.7	685.7
147.5°	707.0	707.3	707.6	707.4	706.8	706.1	705.6	704.9
150°	720.5	720.7	721.0	721.0	720.6	720.2	719.7	719.3
152.5°	732.4	732.9	733.4	733.3	732.7	732.1	731.5	730.8
155°	748.9	749.5	750.2	750.2	749.3	748.5	747.7	746.9
157.5°	763.2	763.9	764.8	764.7	763.6	762.5	761.6	760.5
160°	771.4	772.2	772.9	772.9	771.9	771.0	770.1	769.2
162.5°	778.8	779.7	780.6	780.6	779.8	778.9	778.1	777.3
165°	788.6	789.7	790.8	790.8	789.9	789.0	788.1	787.1
167.5°	796.3	797.4	798.5	798.5	797.4	796.3	795.2	794.2
170°	800.6	801.8	802.8	802.8	801.8	800.6	799.6	798.5
172.5°	803.6	804.6	805.7	805.6	804.5	803.3	802.1	801.0
175°	807.0	808.0	808.9	808.8	807.7	806.7	805.6	804.5
177.5°	808.3	809.1	810.0	809.8	808.8	807.7	806.7	805.6
180°	807.6	807.6	807.6	807.6	807.6	807.6	807.6	807.6

(END OF REPORT)