

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332143-840

Luminaire Tested: **S123DIW-S560D1320U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332143-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1320U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6965.6 lumens
Efficiency: N/A
Efficacy: 129.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332143-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332143-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35	28
2	86	78	72	67	77	71	66	61	57	53	50	44	41	39	32	30	29	24
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25	20
4	71	61	53	47	64	55	48	43	44	40	36	34	31	28	25	23	21	17
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18	15
6	60	48	40	35	54	44	37	32	36	31	27	28	24	21	21	18	16	13
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14	12
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	13	15	12	11	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9684	9684	9684
5°	9729	9596	9662
10°	9664	9512	9571
15°	9551	9404	9423
20°	9419	9251	9260
25°	9242	9069	9049
30°	9047	8866	8797
35°	8843	8650	8539
40°	8630	8413	8283
45°	8397	8196	7995
50°	8162	7927	7708
55°	7854	7651	7418
60°	7543	7326	7093
65°	7272	6976	6757
70°	6864	6571	6279
75°	6276	6047	5793
80°	5659	5424	5368
85°	4965	4780	4594



TEST NUMBER: P332143-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.7	1.2
10°-20°	239.3	3.4
20°-30°	353.5	5.1
30°-40°	412.9	5.9
40°-50°	415.1	6.0
50°-60°	364.6	5.2
60°-70°	271.7	3.9
70°-80°	154.8	2.2
80°-90°	49.4	0.7
90°-100°	108.6	1.6
100°-110°	325.1	4.7
110°-120°	553.0	7.9
120°-130°	727.3	10.4
130°-140°	817.5	11.7
140°-150°	803.6	11.5
150°-160°	676.5	9.7
160°-170°	450.3	6.5
170°-180°	157.7	2.3
0°-30°	677.5	9.7
0°-40°	1090.4	15.7
0°-60°	1870.2	26.8
0°-90°	2346.0	33.7
90°-120°	986.7	14.2
90°-150°	3335.1	47.9
90°-180°	4620.0	66.3
0°-180°	6965.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	900	900	900	900	900	
5°	900	896	888	895	894	85
15°	857	854	844	850	846	242
25°	778	773	764	764	762	358
35°	673	668	658	654	650	421
45°	552	548	538	529	525	426
55°	418	417	408	399	395	375
65°	286	281	274	268	265	282
75°	151	148	145	142	139	161
85°	40	39	39	37	37	44
90°	1	15	31	37	39	7
95°	77	87	97	102	102	87
105°	295	298	309	309	312	316
115°	557	560	558	559	558	551
125°	815	818	816	811	806	726
135°	1057	1064	1064	1058	1056	814
145°	1282	1285	1289	1287	1282	801
155°	1468	1468	1470	1474	1466	676
165°	1599	1596	1595	1602	1594	451
175°	1663	1658	1658	1665	1657	158
180°	1667	1667	1667	1667	1667	



TEST NUMBER: P332143-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7
2.5°	902.7	902.2	901.7	901.1	900.6	899.5	898.0	896.5	895.0	893.5	894.8
5°	900.4	899.6	898.7	897.9	897.0	895.6	893.7	891.8	890.0	888.1	889.8
7.5°	891.6	890.8	889.9	889.1	888.2	886.8	884.8	882.8	880.9	879.0	880.5
10°	884.2	883.3	882.5	881.6	880.8	879.2	877.0	874.7	872.5	870.3	871.8
12.5°	874.3	873.5	872.8	872.1	871.4	870.0	867.9	865.8	863.7	861.6	862.7
15°	857.1	856.5	855.8	855.1	854.3	852.9	850.7	848.5	846.2	843.9	845.4
17.5°	837.2	836.3	835.4	834.5	833.5	832.0	829.8	827.6	825.4	823.0	824.0
20°	822.3	821.3	820.2	819.2	818.2	816.6	814.4	812.1	809.8	807.6	808.3
22.5°	805.6	804.6	803.5	802.5	801.4	799.8	797.6	795.4	793.1	790.9	791.4
25°	778.2	777.2	776.2	775.2	774.1	772.4	770.2	768.0	765.8	763.6	763.7
27.5°	749.0	748.0	747.0	746.0	745.0	743.3	740.8	738.5	736.1	733.7	733.8
30°	727.9	727.1	726.2	725.4	724.5	722.9	720.4	718.0	715.7	713.3	713.3
32.5°	706.9	705.8	704.6	703.5	702.4	700.8	699.0	697.1	695.3	693.5	692.5
35°	673.0	672.0	671.0	669.9	668.9	667.2	665.0	662.8	660.6	658.3	657.3
37.5°	638.3	637.0	635.7	634.4	633.1	631.4	629.0	626.8	624.5	622.3	621.1
40°	614.2	613.2	612.2	611.2	610.1	608.3	605.9	603.6	601.2	598.7	597.3
42.5°	590.1	589.0	587.7	586.5	585.4	583.6	581.2	578.9	576.4	574.0	572.6
45°	551.6	550.9	550.2	549.5	548.8	547.3	545.1	542.9	540.7	538.4	536.3
47.5°	513.3	512.3	511.4	510.4	509.4	507.8	505.7	503.6	501.5	499.4	497.4
50°	487.4	486.5	485.6	484.7	483.9	482.4	480.1	477.9	475.6	473.4	471.5
52.5°	460.1	459.5	459.0	458.4	457.8	456.3	453.9	451.6	449.2	446.9	445.2
55°	418.5	418.3	418.2	418.0	417.8	416.6	414.3	412.1	409.9	407.7	405.8
57.5°	378.9	378.3	377.7	377.2	376.6	375.4	373.5	371.8	370.0	368.2	366.6
60°	350.4	350.2	350.1	349.9	349.7	348.6	346.6	344.5	342.4	340.3	338.8
62.5°	325.1	324.6	324.2	323.8	323.3	322.0	319.9	317.9	315.8	313.8	312.3
65°	285.5	284.6	283.8	282.9	282.1	280.7	279.0	277.3	275.6	273.9	272.5
67.5°	243.5	242.8	242.0	241.3	240.4	239.4	238.1	236.8	235.5	234.3	233.1
70°	218.1	217.1	216.1	215.1	214.0	213.0	212.0	211.0	209.8	208.8	207.6
72.5°	191.6	190.8	190.1	189.2	188.5	187.5	186.4	185.2	184.0	182.9	181.8
75°	150.9	150.2	149.5	148.8	148.1	147.5	146.9	146.4	145.9	145.4	144.6
77.5°	114.8	114.4	114.0	113.7	113.3	112.8	112.2	111.6	110.9	110.3	109.8
80°	91.3	90.8	90.3	89.8	89.2	88.8	88.5	88.1	87.8	87.5	87.3
82.5°	68.4	68.3	68.2	68.1	68.0	67.9	67.9	67.8	67.7	67.7	67.3
85°	40.2	39.9	39.6	39.2	38.9	38.7	38.7	38.7	38.7	38.7	38.4
87.5°	16.4	16.6	16.7	16.9	17.1	17.5	18.1	18.7	19.3	19.9	20.0
90°	1.3	4.2	7.2	10.0	12.9	16.3	20.1	23.8	27.7	31.4	32.6
92.5°	31.7	33.6	35.6	37.7	39.6	41.7	43.8	45.9	48.2	50.3	51.2
95°	77.3	79.3	81.4	83.4	85.4	87.7	90.0	92.3	94.6	96.9	98.1
97.5°	137.2	138.8	140.3	141.8	143.3	144.9	146.6	148.2	150.0	151.7	153.0
100°	178.1	179.9	181.6	183.4	185.1	186.7	188.1	189.7	191.1	192.6	193.4
102.5°	225.3	226.3	227.4	228.4	229.4	231.0	232.9	234.8	236.7	238.6	239.5
105°	294.7	295.3	295.9	296.4	297.0	298.6	301.2	303.9	306.5	309.1	309.1
107.5°	375.4	375.8	376.1	376.5	376.8	377.5	378.5	379.6	380.6	381.6	382.6
110°	425.7	426.3	426.9	427.4	428.0	428.6	429.2	429.8	430.3	430.9	432.1



TEST NUMBER: P332143-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	478.1	478.4	478.8	479.1	479.5	479.7	479.8	479.9	480.1	480.2	481.6
115°	556.6	557.5	558.4	559.3	560.2	560.3	559.7	559.2	558.6	558.0	558.3
117.5°	635.8	636.3	636.9	637.5	638.1	638.0	637.2	636.5	635.7	635.0	634.9
120°	685.0	686.7	688.5	690.2	692.0	692.2	690.6	689.2	687.8	686.3	686.0
122.5°	736.4	737.6	738.9	740.2	741.4	741.7	740.9	740.2	739.4	738.7	737.9
125°	814.7	815.6	816.4	817.3	818.2	818.3	817.7	817.2	816.6	816.0	814.9
127.5°	887.0	888.9	890.7	892.5	894.4	895.0	894.4	893.7	893.1	892.5	890.8
130°	935.1	937.5	939.9	942.2	944.5	945.2	944.3	943.5	942.6	941.7	940.6
132.5°	983.4	985.7	988.1	990.4	992.7	993.5	992.9	992.3	991.6	991.0	989.6
135°	1057.0	1058.7	1060.5	1062.2	1064.0	1064.7	1064.4	1064.1	1063.8	1063.5	1062.4
137.5°	1125.1	1126.5	1128.0	1129.4	1130.9	1132.1	1132.8	1133.6	1134.3	1135.1	1133.8
140°	1172.3	1173.7	1175.2	1176.6	1178.1	1178.9	1179.2	1179.5	1179.8	1180.1	1179.8
142.5°	1215.2	1216.7	1218.1	1219.6	1221.0	1222.0	1222.5	1223.0	1223.6	1224.2	1223.9
145°	1282.2	1282.8	1283.4	1284.0	1284.5	1285.4	1286.2	1287.1	1288.0	1288.8	1288.5
147.5°	1340.9	1342.0	1343.0	1344.1	1345.1	1346.0	1346.9	1347.7	1348.5	1349.3	1349.3
150°	1381.8	1382.4	1383.0	1383.5	1384.1	1384.7	1385.3	1385.8	1386.4	1387.0	1387.0
152.5°	1415.3	1416.1	1416.9	1417.7	1418.6	1419.2	1419.6	1419.9	1420.3	1420.6	1421.1
155°	1468.2	1468.2	1468.2	1468.2	1468.2	1468.4	1468.6	1468.9	1469.3	1469.6	1470.8
157.5°	1513.3	1513.0	1512.6	1512.3	1511.9	1511.9	1512.1	1512.3	1512.6	1512.8	1514.0
160°	1541.6	1541.1	1540.4	1539.8	1539.2	1538.9	1538.9	1538.9	1538.9	1538.9	1540.4
162.5°	1566.7	1565.9	1565.1	1564.3	1563.5	1563.2	1563.5	1563.7	1563.9	1564.1	1565.6
165°	1599.2	1598.3	1597.5	1596.6	1595.8	1595.3	1595.3	1595.3	1595.3	1595.3	1597.0
167.5°	1625.2	1624.0	1622.9	1621.6	1620.5	1620.0	1620.2	1620.5	1620.7	1620.9	1622.8
170°	1639.8	1638.7	1637.5	1636.4	1635.2	1634.6	1634.6	1634.6	1634.6	1634.6	1636.6
172.5°	1651.3	1650.2	1649.0	1647.9	1646.7	1646.1	1646.1	1646.1	1646.1	1646.1	1647.9
175°	1663.4	1662.2	1661.1	1659.9	1658.7	1658.2	1658.2	1658.2	1658.2	1658.2	1659.9
177.5°	1668.4	1667.5	1666.5	1665.6	1664.7	1664.2	1664.2	1664.2	1664.2	1664.2	1665.6
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4



TEST NUMBER: P332143-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7
2.5°	896.3	897.6	899.0	899.6	899.5	899.3	899.2	899.1
5°	891.5	893.2	894.9	895.6	895.2	894.9	894.6	894.2
7.5°	882.0	883.5	885.1	885.8	885.6	885.3	885.1	884.9
10°	873.3	874.9	876.5	877.1	876.8	876.4	876.1	875.7
12.5°	863.8	865.1	866.2	866.6	866.4	866.2	866.0	865.8
15°	846.8	848.1	849.5	849.6	848.6	847.6	846.6	845.6
17.5°	825.1	826.0	827.0	827.2	826.9	826.5	826.1	825.7
20°	809.0	809.7	810.3	810.4	809.9	809.4	808.9	808.4
22.5°	792.0	792.5	793.1	793.0	792.4	791.7	791.1	790.4
25°	763.9	764.1	764.2	764.1	763.6	763.1	762.4	761.9
27.5°	734.0	734.1	734.2	734.0	733.3	732.7	732.0	731.3
30°	713.3	713.3	713.3	712.7	711.4	710.2	709.0	707.8
32.5°	691.6	690.5	689.5	688.7	688.1	687.5	686.8	686.2
35°	656.2	655.2	654.2	653.3	652.4	651.6	650.7	649.8
37.5°	619.8	618.5	617.3	616.4	615.9	615.3	614.8	614.2
40°	596.0	594.6	593.3	592.2	591.5	590.9	590.2	589.5
42.5°	571.3	569.9	568.5	567.4	566.7	566.1	565.4	564.7
45°	534.3	532.2	530.2	528.7	527.9	526.9	526.1	525.2
47.5°	495.3	493.3	491.3	489.9	489.2	488.4	487.7	486.9
50°	469.7	467.8	465.9	464.4	463.3	462.3	461.3	460.3
52.5°	443.6	442.0	440.4	439.0	438.0	437.0	436.0	434.9
55°	403.8	402.0	400.1	398.7	397.9	397.0	396.2	395.3
57.5°	364.9	363.1	361.5	360.1	359.1	358.2	357.2	356.2
60°	337.3	335.8	334.2	333.0	332.1	331.2	330.4	329.5
62.5°	310.6	309.1	307.6	306.5	305.9	305.4	304.8	304.2
65°	271.0	269.7	268.3	267.4	266.9	266.4	265.9	265.3
67.5°	231.9	230.7	229.4	228.4	227.7	227.0	226.3	225.6
70°	206.4	205.3	204.1	203.0	202.2	201.3	200.5	199.5
72.5°	180.8	179.7	178.6	177.8	177.4	176.9	176.5	176.0
75°	143.7	142.9	142.0	141.3	140.8	140.3	139.8	139.3
77.5°	109.2	108.6	108.0	107.7	107.7	107.7	107.7	107.7
80°	87.1	86.8	86.7	86.6	86.6	86.6	86.6	86.6
82.5°	67.0	66.7	66.3	66.1	66.0	65.8	65.7	65.6
85°	38.0	37.7	37.3	37.2	37.2	37.2	37.2	37.2
87.5°	20.1	20.2	20.3	20.4	20.5	20.6	20.7	20.9
90°	33.7	34.9	36.1	37.0	37.6	38.2	38.7	39.3
92.5°	52.1	53.1	54.0	54.3	53.9	53.6	53.2	52.9
95°	99.3	100.4	101.6	102.2	102.2	102.2	102.2	102.2
97.5°	154.3	155.7	157.0	157.6	157.5	157.4	157.3	157.1
100°	194.3	195.1	196.0	196.7	197.3	197.9	198.5	199.0
102.5°	240.3	241.3	242.2	242.5	242.4	242.3	242.2	242.1
105°	309.1	309.1	309.1	309.4	310.0	310.5	311.1	311.7
107.5°	383.5	384.5	385.4	385.7	385.4	385.0	384.7	384.3
110°	433.2	434.4	435.6	435.9	435.3	434.7	434.1	433.5



TEST NUMBER: P332143-840

CATALOG NUMBER: S123DIW-S560D1320U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	482.9	484.3	485.7	486.4	486.3	486.1	486.0	485.9
115°	558.6	558.9	559.2	559.2	558.9	558.6	558.3	558.0
117.5°	634.9	634.8	634.7	634.3	633.5	632.7	631.9	631.1
120°	685.7	685.5	685.2	684.7	684.2	683.6	683.0	682.4
122.5°	737.2	736.4	735.7	734.9	734.1	733.3	732.5	731.6
125°	813.6	812.5	811.3	810.2	809.0	807.8	806.7	805.5
127.5°	889.2	887.6	886.0	884.4	883.1	881.8	880.5	879.1
130°	939.4	938.3	937.1	935.4	933.4	931.4	929.4	927.4
132.5°	988.2	986.7	985.4	983.9	982.3	980.8	979.2	977.7
135°	1061.2	1060.1	1058.8	1058.0	1057.4	1056.8	1056.2	1055.7
137.5°	1132.6	1131.4	1130.1	1129.0	1127.9	1126.8	1125.7	1124.6
140°	1179.5	1179.2	1178.9	1177.8	1175.8	1173.7	1171.6	1169.6
142.5°	1223.6	1223.2	1222.9	1222.0	1220.4	1218.9	1217.3	1215.8
145°	1288.2	1288.0	1287.7	1287.0	1285.8	1284.5	1283.4	1282.2
147.5°	1349.3	1349.3	1349.3	1348.5	1346.8	1344.9	1343.2	1341.5
150°	1387.0	1387.0	1387.0	1386.1	1384.4	1382.7	1380.9	1379.2
152.5°	1421.5	1422.0	1422.4	1421.9	1420.4	1418.9	1417.3	1415.8
155°	1471.9	1473.1	1474.2	1473.8	1471.8	1469.8	1467.6	1465.6
157.5°	1515.2	1516.4	1517.7	1517.4	1515.8	1514.2	1512.6	1511.0
160°	1541.9	1543.4	1544.8	1545.0	1543.8	1542.7	1541.5	1540.2
162.5°	1567.0	1568.5	1569.9	1569.7	1567.9	1566.0	1564.2	1562.3
165°	1598.8	1600.5	1602.3	1602.2	1600.1	1598.1	1596.0	1594.0
167.5°	1624.6	1626.4	1628.2	1628.2	1626.4	1624.6	1622.8	1620.9
170°	1638.7	1640.7	1642.7	1642.7	1640.7	1638.7	1636.6	1634.6
172.5°	1649.7	1651.5	1653.4	1653.3	1651.2	1649.1	1647.1	1645.1
175°	1661.6	1663.4	1665.2	1665.0	1662.9	1660.9	1658.9	1656.9
177.5°	1667.0	1668.4	1669.8	1669.7	1668.0	1666.4	1664.8	1663.1
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4

(END OF REPORT)