

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332486-930

Luminaire Tested: **S123RDIW-S1165D1535U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332486-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D1535U930-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8734.7 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332486-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332486-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43																												
1	97	93	89	86	88	85	82	79	70	68	66	57	55	54	44	44	43	37																												
2	88	81	76	71	81	75	70	66	62	59	55	50	48	46	40	38	37	32																												
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	27																												
4	74	64	56	51	68	59	52	47	49	44	41	40	37	34	32	30	28	24																												
5	68	57	49	44	62	53	46	41	44	39	35	36	33	30	29	27	24	21																												
6	63	51	44	38	57	47	41	36	40	35	31	33	29	26	27	24	22	19																												
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17																												
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	22	20	18	15																												
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14																												
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16113	16113	16113	16113
5°	19207	16181	14249	16181
10°	23981	16088	12873	16088
15°	28149	15924	11739	15924
20°	31416	15678	10775	15678
25°	30914	15419	10183	15419
30°	22222	15181	9573	15181
35°	14837	14870	9179	14870
40°	10932	14497	8769	14497
45°	9168	13842	8369	13842
50°	8090	12983	7812	12983
55°	7096	12001	7047	12001
60°	6318	11063	6456	11063
65°	5547	10055	6006	10055
70°	4356	9155	5485	9155
75°	3839	7993	5011	7993
80°	3335	6794	4928	6794
85°	2692	5459	5224	5459



TEST NUMBER: P332486-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.2	1.7
10°-20°	459.9	5.3
20°-30°	722.5	8.3
30°-40°	753.8	8.6
40°-50°	645.1	7.4
50°-60°	491.7	5.6
60°-70°	315.1	3.6
70°-80°	151.6	1.7
80°-90°	44.7	0.5
90°-100°	59.6	0.7
100°-110°	284.3	3.3
110°-120°	682.8	7.8
120°-130°	869.5	10.0
130°-140°	929.1	10.6
140°-150°	868.8	9.9
150°-160°	700.8	8.0
160°-170°	452.3	5.2
170°-180°	155.9	1.8
0°-30°	1329.6	15.2
0°-40°	2083.4	23.9
0°-60°	3220.2	36.9
0°-90°	3731.6	42.7
90°-120°	1026.8	11.8
90°-150°	3694.1	42.3
90°-180°	5003.0	57.3
0°-180°	8734.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1497	1497	1497	1497	1497	
5°	1778	1498	1319	1498	1778	184
15°	2526	1429	1053	1429	2526	716
25°	2603	1298	857	1298	2603	1119
35°	1129	1132	698	1132	1129	740
45°	602	909	550	909	602	474
55°	378	640	376	640	378	342
65°	218	395	236	395	218	214
75°	92	192	120	192	92	99
85°	22	44	42	44	22	26
90°	36	1	36	1	36	17
95°	46	74	46	74	46	39
105°	54	363	54	363	54	123
115°	717	681	717	681	717	662
125°	980	960	980	960	980	875
135°	1208	1196	1208	1196	1208	931
145°	1393	1380	1393	1380	1393	870
155°	1518	1520	1518	1520	1518	700
165°	1599	1603	1599	1603	1599	452
175°	1634	1640	1634	1640	1634	156
180°	1640	1640	1640	1640	1640	



TEST NUMBER: P332486-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1594.3	1596.4	1589.7	1588.7	1580.9	1578.9	1578.9	1568.1	1561.5	1552.8	1547.7
5°	1777.6	1787.9	1782.7	1771.2	1751.9	1747.4	1735.3	1716.0	1694.3	1667.4	1654.6
7.5°	2006.5	2020.5	2015.1	1997.2	1977.1	1960.9	1926.5	1894.6	1849.8	1810.6	1777.0
10°	2194.1	2179.4	2167.8	2150.5	2131.9	2101.8	2066.0	2016.6	1959.6	1914.7	1864.8
12.5°	2334.5	2332.2	2317.5	2299.7	2273.5	2244.8	2200.7	2140.6	2074.4	2009.5	1952.4
15°	2526.0	2529.9	2520.3	2501.7	2464.5	2413.9	2347.2	2322.3	2227.4	2157.0	2086.4
17.5°	2658.5	2657.8	2656.5	2630.7	2592.8	2556.8	2495.0	2429.3	2343.4	2244.1	2149.1
20°	2742.6	2736.2	2737.5	2708.7	2680.5	2638.8	2578.5	2483.1	2412.6	2297.9	2199.8
22.5°	2740.5	2739.3	2744.1	2734.3	2713.8	2681.8	2634.5	2553.8	2463.9	2348.1	2237.8
25°	2602.9	2597.8	2628.0	2636.3	2669.0	2674.7	2660.6	2616.4	2531.2	2412.0	2275.5
27.5°	2178.5	2175.6	2231.6	2301.5	2390.2	2459.1	2525.8	2557.9	2531.2	2445.8	2309.1
30°	1787.9	1848.0	1876.2	1977.5	2090.3	2224.9	2342.8	2454.9	2482.4	2445.3	2333.1
32.5°	1484.3	1536.9	1560.5	1647.4	1752.5	1910.1	2086.9	2245.7	2357.9	2386.3	2318.8
35°	1129.1	1129.8	1183.6	1222.0	1319.4	1481.6	1653.3	1866.0	2077.5	2237.7	2254.3
37.5°	901.0	904.2	936.7	975.0	1048.1	1133.8	1285.1	1461.9	1706.2	1952.2	2096.3
40°	778.0	783.7	808.0	845.9	898.4	963.1	1081.0	1247.7	1451.4	1725.0	1948.6
42.5°	699.0	708.3	720.9	750.0	782.5	843.2	938.5	1067.2	1252.5	1511.2	1769.3
45°	602.3	607.5	617.1	630.6	660.0	702.3	766.4	852.9	1006.7	1215.0	1473.2
47.5°	531.3	528.6	538.7	549.7	569.3	598.1	641.1	711.7	821.4	988.5	1207.5
50°	483.1	482.5	489.6	497.9	516.5	537.6	572.9	626.1	713.2	851.7	1052.2
52.5°	438.1	440.5	445.5	455.8	469.3	486.4	518.0	556.4	631.2	750.6	917.9
55°	378.1	380.0	387.0	392.8	402.4	419.7	439.6	471.7	522.9	606.2	744.0
57.5°	327.3	326.4	333.2	334.6	345.5	359.6	375.0	399.8	437.0	499.0	591.7
60°	293.5	291.6	297.3	301.8	307.6	319.1	331.9	356.3	385.8	431.3	510.7
62.5°	262.7	261.8	266.0	270.5	275.3	285.8	296.5	315.3	338.6	376.9	439.9
65°	217.8	219.8	221.7	223.6	226.2	232.6	242.9	255.7	271.7	298.6	344.1
67.5°	171.2	173.2	173.8	177.7	183.3	187.3	193.6	205.0	216.1	238.8	264.6
70°	138.4	137.8	138.4	140.3	147.4	154.4	162.7	171.1	178.1	194.1	216.0
72.5°	119.0	117.8	119.4	119.8	123.3	125.2	130.4	138.3	147.4	158.2	173.9
75°	92.3	92.3	92.3	92.3	94.8	96.1	98.1	100.0	103.1	108.3	119.8
77.5°	68.2	68.3	69.2	69.9	70.4	71.1	72.3	74.2	75.3	78.0	83.1
80°	53.8	54.5	53.8	54.5	54.5	55.8	56.4	58.3	58.9	62.1	64.1
82.5°	40.5	40.1	40.5	41.2	41.2	42.4	42.6	43.9	44.1	45.7	47.7
85°	21.8	20.5	21.8	21.1	22.4	21.1	21.8	23.1	23.1	23.7	26.3
87.5°	12.5	13.4	12.2	12.6	12.6	12.9	12.6	12.5	13.2	12.5	12.3
90°	36.5	36.0	35.5	35.0	34.4	33.6	32.5	31.4	30.3	29.3	25.8
92.5°	40.4	40.1	39.8	39.5	39.1	38.2	36.4	34.7	32.9	31.2	28.5
95°	46.3	46.3	46.3	46.3	46.3	45.3	43.5	41.6	39.7	37.7	34.8
97.5°	50.2	50.0	49.7	49.4	49.2	47.9	45.7	43.6	41.4	39.2	58.8
100°	51.2	51.0	50.6	50.4	50.1	48.9	46.7	44.5	42.4	40.2	82.5
102.5°	52.2	51.7	51.2	50.7	50.2	53.3	60.1	66.8	73.5	80.2	126.4
105°	53.6	53.1	52.6	52.0	51.4	75.2	123.1	171.0	219.0	266.9	291.3
107.5°	168.4	204.6	240.7	276.9	313.0	348.6	383.8	418.9	454.1	489.3	485.4
110°	335.2	373.9	412.6	451.3	490.1	514.0	522.9	531.8	540.8	549.7	546.7



TEST NUMBER: P332486-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	575.0	583.3	591.4	599.6	607.8	611.8	611.6	611.5	611.3	611.1	608.1
115°	716.7	715.6	714.5	713.5	712.3	710.5	707.8	705.1	702.3	699.6	697.2
117.5°	796.1	796.0	795.7	795.5	795.3	794.1	791.9	789.8	787.6	785.5	784.2
120°	850.8	850.8	850.8	850.8	850.8	849.7	847.5	845.4	843.2	841.0	840.2
122.5°	904.4	904.2	903.9	903.8	903.5	902.7	901.2	899.6	898.1	896.6	895.5
125°	980.0	979.4	978.8	978.4	977.8	977.2	976.7	976.2	975.7	975.1	974.0
127.5°	1052.6	1053.1	1053.7	1054.3	1054.8	1054.6	1053.8	1052.9	1052.0	1051.2	1049.9
130°	1099.4	1099.9	1100.5	1101.1	1101.6	1101.3	1100.2	1099.1	1098.0	1097.0	1095.9
132.5°	1142.3	1143.0	1143.9	1144.6	1145.3	1145.2	1144.1	1143.0	1141.9	1140.8	1140.0
135°	1207.9	1208.7	1209.5	1210.3	1211.1	1211.1	1210.3	1209.5	1208.7	1207.9	1206.8
137.5°	1269.6	1270.1	1270.6	1271.2	1271.7	1271.4	1270.1	1268.8	1267.5	1266.2	1265.6
140°	1306.6	1307.2	1307.7	1308.2	1308.8	1308.5	1307.4	1306.4	1305.3	1304.2	1303.3
142.5°	1340.8	1341.5	1342.2	1343.0	1343.8	1343.7	1342.9	1342.0	1341.1	1340.3	1339.5
145°	1393.2	1393.2	1393.2	1393.2	1393.2	1392.9	1392.4	1391.8	1391.2	1390.7	1390.2
147.5°	1432.2	1433.4	1434.7	1435.9	1437.1	1437.5	1437.0	1436.4	1435.9	1435.3	1434.8
150°	1461.4	1462.2	1463.1	1463.9	1464.7	1464.8	1464.3	1463.7	1463.1	1462.6	1462.1
152.5°	1484.8	1486.0	1487.3	1488.6	1489.8	1490.0	1489.0	1488.0	1487.0	1486.0	1485.7
155°	1517.5	1519.1	1520.7	1522.3	1524.0	1524.1	1522.7	1521.4	1520.0	1518.7	1518.4
157.5°	1545.0	1547.1	1549.2	1551.4	1553.5	1553.7	1552.1	1550.5	1548.8	1547.2	1547.5
160°	1562.6	1564.5	1566.4	1568.2	1570.2	1570.3	1568.6	1567.1	1565.5	1563.8	1564.1
162.5°	1579.2	1580.9	1582.5	1584.2	1585.8	1585.8	1584.0	1582.1	1580.3	1578.4	1578.7
165°	1599.1	1601.0	1603.0	1604.8	1606.7	1606.6	1604.4	1602.2	1600.1	1597.9	1598.2
167.5°	1613.6	1615.7	1617.9	1620.0	1622.2	1622.2	1620.0	1617.9	1615.7	1613.6	1613.6
170°	1622.3	1624.5	1626.6	1628.8	1631.0	1631.0	1628.8	1626.6	1624.5	1622.3	1622.3
172.5°	1627.2	1629.5	1632.0	1634.3	1636.7	1636.8	1634.7	1632.5	1630.4	1628.2	1627.9
175°	1634.5	1636.6	1638.8	1641.0	1643.2	1643.3	1641.4	1639.5	1637.6	1635.7	1635.4
177.5°	1636.7	1638.8	1641.0	1643.2	1645.4	1645.6	1643.8	1642.1	1640.4	1638.7	1638.4
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332486-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1545.6	1544.1	1536.9	1528.7	1517.9	1510.7	1505.1	1502.0	1492.8	1481.6	1473.8
5°	1641.1	1621.9	1601.3	1576.4	1553.3	1529.6	1514.8	1497.5	1476.4	1452.7	1436.1
7.5°	1743.4	1705.7	1665.1	1623.2	1581.8	1544.6	1511.8	1483.7	1450.0	1416.0	1392.2
10°	1821.8	1766.7	1709.7	1651.3	1598.1	1548.2	1509.7	1471.9	1431.6	1392.4	1363.0
12.5°	1893.0	1820.5	1754.8	1683.1	1615.1	1555.3	1500.0	1455.5	1407.0	1365.3	1331.7
15°	1983.3	1908.9	1829.5	1720.5	1630.2	1554.6	1487.3	1429.0	1370.0	1318.7	1286.1
17.5°	2067.6	1955.7	1848.9	1758.1	1640.7	1546.2	1464.1	1394.4	1329.7	1275.3	1235.1
20°	2102.5	1994.1	1878.2	1762.2	1646.8	1541.2	1445.6	1368.7	1301.5	1239.9	1202.8
22.5°	2123.4	2000.8	1878.7	1754.0	1631.5	1521.7	1427.2	1342.6	1269.7	1211.2	1165.4
25°	2148.0	2001.9	1867.3	1744.3	1619.3	1500.2	1388.0	1298.3	1219.4	1157.3	1108.6
27.5°	2164.1	1992.3	1833.2	1696.5	1569.7	1451.0	1348.3	1253.1	1173.2	1107.4	1055.2
30°	2167.1	1984.5	1807.0	1659.1	1530.2	1421.3	1312.4	1221.4	1136.8	1066.9	1018.2
32.5°	2171.3	1965.6	1771.6	1614.5	1482.5	1374.7	1275.9	1189.0	1102.4	1033.6	983.9
35°	2154.3	1955.1	1718.0	1537.2	1405.2	1300.8	1211.8	1131.6	1046.4	979.7	929.2
37.5°	2081.5	1913.4	1662.4	1450.4	1312.4	1215.6	1143.0	1073.2	995.1	923.2	875.5
40°	2008.2	1872.4	1619.3	1397.6	1253.4	1154.1	1088.8	1031.7	956.1	888.8	837.6
42.5°	1899.1	1816.6	1578.3	1342.2	1186.7	1091.0	1035.9	982.4	916.1	847.7	799.6
45°	1698.8	1709.7	1494.4	1254.0	1094.5	998.3	946.5	909.3	850.4	793.9	744.6
47.5°	1447.6	1549.5	1395.8	1160.1	997.2	907.0	861.6	829.2	789.5	734.1	689.1
50°	1283.5	1429.0	1316.9	1097.1	936.2	846.5	801.6	775.3	740.8	697.2	654.3
52.5°	1132.3	1288.5	1221.5	1026.8	870.1	788.1	744.2	722.6	695.1	654.1	615.3
55°	923.4	1081.7	1066.3	920.8	770.9	697.2	663.9	639.5	620.9	590.2	559.5
57.5°	746.9	897.0	904.9	802.9	683.5	610.7	582.0	563.6	551.5	528.3	499.9
60°	635.7	773.5	800.4	723.5	620.9	556.8	528.6	513.9	504.3	485.8	463.9
62.5°	543.4	660.6	691.1	635.8	560.9	501.0	478.9	464.7	458.2	442.1	422.9
65°	415.9	513.3	542.7	512.0	472.9	424.9	406.9	394.8	389.0	380.0	365.9
67.5°	312.7	383.7	416.0	394.4	380.3	349.8	338.4	331.9	326.8	320.7	308.8
70°	251.2	303.7	337.0	331.3	319.8	303.7	295.4	290.9	285.8	280.7	270.4
72.5°	201.9	238.1	269.4	272.3	262.9	259.7	252.3	250.5	247.4	241.2	235.5
75°	134.0	158.9	180.7	189.1	192.9	196.1	192.9	192.2	191.6	186.5	183.3
77.5°	87.8	101.3	115.0	129.2	135.2	139.6	140.6	142.9	141.2	138.5	137.0
80°	67.3	70.5	80.1	92.3	101.9	105.7	108.3	109.6	108.9	108.3	105.7
82.5°	48.8	51.5	56.0	64.6	72.6	79.1	80.6	80.4	81.8	82.2	80.1
85°	26.3	26.9	28.2	29.5	34.0	41.0	43.0	44.2	45.5	45.5	41.7
87.5°	12.6	11.4	11.7	11.1	12.1	12.1	14.6	16.6	17.7	16.2	16.7
90°	22.2	18.7	15.2	12.1	9.4	6.6	3.9	1.2	3.9	6.6	9.4
92.5°	25.9	23.2	20.5	19.6	20.4	21.1	21.9	22.7	21.9	21.1	20.4
95°	31.8	28.9	25.8	29.9	41.0	52.2	63.3	74.4	63.3	52.2	41.0
97.5°	78.3	97.8	117.2	129.5	134.4	139.5	144.5	149.4	144.5	139.5	134.4
100°	124.7	167.0	209.2	227.6	222.3	216.8	211.4	206.0	211.4	216.8	222.3
102.5°	172.5	218.7	264.8	285.9	282.0	278.2	274.3	270.4	274.3	278.2	282.0
105°	315.7	340.1	364.4	375.1	372.2	369.2	366.2	363.2	366.2	369.2	372.2
107.5°	481.6	477.7	473.9	470.8	468.4	465.9	463.6	461.2	463.6	465.9	468.4
110°	543.7	540.8	537.8	535.2	533.0	530.8	528.7	526.5	528.7	530.8	533.0



TEST NUMBER: P332486-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	605.2	602.2	599.2	596.7	594.8	592.9	590.9	589.0	590.9	592.9	594.8
115°	694.7	692.4	689.9	687.9	686.2	684.6	683.0	681.3	683.0	684.6	686.2
117.5°	782.9	781.7	780.5	778.9	776.8	774.8	772.8	770.8	772.8	774.8	776.8
120°	839.4	838.5	837.8	836.2	833.7	831.3	828.8	826.4	828.8	831.3	833.7
122.5°	894.5	893.5	892.5	891.0	888.9	887.0	884.9	883.0	884.9	887.0	888.9
125°	972.9	971.8	970.8	969.1	966.9	964.8	962.6	960.4	962.6	964.8	966.9
127.5°	1048.6	1047.3	1045.9	1044.2	1042.0	1039.9	1037.7	1035.5	1037.7	1039.9	1042.0
130°	1094.8	1093.7	1092.7	1091.0	1088.8	1086.7	1084.5	1082.3	1084.5	1086.7	1088.8
132.5°	1139.1	1138.2	1137.4	1135.9	1133.7	1131.6	1129.4	1127.2	1129.4	1131.6	1133.7
135°	1205.7	1204.6	1203.5	1202.2	1200.6	1199.0	1197.3	1195.7	1197.3	1199.0	1200.6
137.5°	1264.9	1264.4	1263.8	1262.4	1260.4	1258.3	1256.3	1254.2	1256.3	1258.3	1260.4
140°	1302.5	1301.7	1300.9	1299.8	1298.1	1296.5	1294.9	1293.2	1294.9	1296.5	1298.1
142.5°	1338.6	1337.8	1337.0	1335.8	1334.2	1332.5	1330.9	1329.3	1330.9	1332.5	1334.2
145°	1389.6	1389.1	1388.5	1387.3	1385.4	1383.6	1381.6	1379.7	1381.6	1383.6	1385.4
147.5°	1434.3	1433.7	1433.1	1432.2	1431.0	1429.8	1428.6	1427.3	1428.6	1429.8	1431.0
150°	1461.6	1461.0	1460.4	1459.8	1459.0	1458.2	1457.3	1456.5	1457.3	1458.2	1459.0
152.5°	1485.4	1485.1	1484.7	1484.4	1484.0	1483.6	1483.3	1482.9	1483.3	1483.6	1484.0
155°	1518.2	1517.9	1517.6	1517.8	1518.3	1518.8	1519.4	1519.9	1519.4	1518.8	1518.3
157.5°	1547.8	1548.0	1548.3	1548.5	1548.5	1548.6	1548.7	1548.7	1548.7	1548.6	1548.5
160°	1564.3	1564.6	1564.9	1565.1	1565.5	1565.7	1565.9	1566.3	1565.9	1565.7	1565.5
162.5°	1579.0	1579.2	1579.5	1580.0	1580.7	1581.4	1582.1	1582.8	1582.1	1581.4	1580.7
165°	1598.5	1598.7	1599.0	1599.5	1600.4	1601.2	1602.0	1602.8	1602.0	1601.2	1600.4
167.5°	1613.6	1613.6	1613.6	1614.0	1615.2	1616.2	1617.3	1618.4	1617.3	1616.2	1615.2
170°	1622.3	1622.3	1622.3	1622.9	1623.9	1625.0	1626.1	1627.2	1626.1	1625.0	1623.9
172.5°	1627.7	1627.5	1627.3	1627.8	1629.1	1630.4	1631.7	1633.0	1631.7	1630.4	1629.1
175°	1635.2	1634.9	1634.6	1635.2	1636.6	1637.9	1639.2	1640.5	1639.2	1637.9	1636.6
177.5°	1638.2	1638.0	1637.8	1638.2	1639.3	1640.4	1641.4	1642.5	1641.4	1640.4	1639.3
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332486-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1471.3	1464.6	1460.0	1449.8	1443.1	1435.9	1428.7	1433.4	1432.8	1432.3	1432.3
5°	1422.0	1407.2	1393.8	1376.5	1365.5	1352.1	1341.8	1340.5	1343.1	1334.2	1329.0
7.5°	1373.0	1352.8	1333.7	1314.7	1294.5	1278.3	1268.1	1263.4	1256.9	1251.3	1245.6
10°	1338.6	1314.9	1296.3	1272.6	1250.8	1231.6	1219.4	1211.1	1206.6	1202.2	1193.8
12.5°	1303.3	1280.1	1256.4	1229.6	1208.8	1186.5	1177.4	1168.1	1159.4	1154.5	1143.0
15°	1251.5	1221.4	1196.4	1168.2	1145.1	1123.3	1110.5	1091.9	1089.3	1083.0	1071.4
17.5°	1199.5	1166.9	1132.5	1111.5	1085.5	1062.8	1043.3	1037.1	1018.7	1011.8	1001.8
20°	1158.5	1128.5	1102.2	1074.6	1036.8	1015.7	1000.3	992.0	977.2	968.2	961.8
22.5°	1123.2	1092.6	1062.2	1030.0	998.9	975.2	963.9	951.0	942.9	930.3	923.4
25°	1072.7	1039.3	1002.8	968.2	945.8	927.9	910.0	898.4	886.9	881.1	868.3
27.5°	1014.0	979.2	945.0	918.8	891.2	873.5	857.3	847.0	833.2	823.5	816.4
30°	981.7	940.7	911.2	887.5	852.2	835.6	823.5	810.7	800.4	790.1	783.1
32.5°	944.3	906.9	878.9	849.5	822.6	804.3	788.6	777.3	768.6	758.8	751.8
35°	885.6	854.2	825.3	795.9	776.0	757.4	738.8	729.2	720.9	711.9	705.6
37.5°	832.5	803.2	775.8	747.8	723.2	708.1	693.1	685.7	674.5	668.5	661.9
40°	799.7	770.9	741.4	714.5	688.8	677.4	663.9	653.0	642.7	638.2	631.2
42.5°	763.9	735.0	710.1	681.2	660.1	644.5	632.1	620.2	612.5	605.9	601.9
45°	710.6	685.0	660.6	631.9	612.0	598.5	584.4	573.5	566.5	562.0	554.9
47.5°	659.0	633.4	608.6	583.5	564.3	548.9	534.8	527.3	517.9	512.4	507.6
50°	621.6	598.5	572.3	549.2	529.9	514.5	503.0	493.4	485.1	478.0	474.8
52.5°	587.3	562.6	540.0	518.4	498.1	480.7	470.2	460.1	453.8	445.7	442.1
55°	530.6	506.9	487.6	466.5	446.6	431.9	419.1	410.1	403.7	394.8	389.6
57.5°	477.4	456.2	433.2	414.8	394.4	381.9	371.3	359.1	351.3	344.2	339.2
60°	441.5	417.2	397.3	380.0	362.1	346.0	336.4	326.8	318.5	311.4	307.0
62.5°	404.1	382.8	363.9	345.1	328.7	314.8	303.6	295.5	288.2	283.7	279.2
65°	346.7	330.0	310.8	295.4	280.1	269.8	260.8	253.7	248.7	245.4	241.6
67.5°	293.8	277.7	260.9	245.8	235.5	227.7	221.8	215.8	213.3	209.1	206.6
70°	259.5	242.9	228.1	216.6	206.4	200.6	196.7	192.2	189.6	184.6	182.0
72.5°	222.1	210.0	199.4	190.0	181.7	176.5	171.6	166.1	162.0	156.4	153.8
75°	175.0	164.0	155.7	149.3	144.1	137.1	130.1	124.3	122.4	120.5	119.8
77.5°	129.6	122.6	116.6	111.2	104.8	99.7	98.2	96.9	96.5	95.5	95.5
80°	101.9	95.5	91.0	84.5	80.7	80.7	80.7	79.5	80.1	80.1	80.1
82.5°	75.7	69.9	67.4	65.1	64.3	64.8	64.8	65.1	64.7	65.7	65.2
85°	39.1	39.7	41.0	40.4	41.0	41.0	42.3	41.7	42.3	41.0	42.3
87.5°	16.8	18.9	20.1	21.4	22.6	22.7	23.5	23.7	24.5	24.6	24.8
90°	12.1	15.2	18.7	22.2	25.8	29.3	30.3	31.4	32.5	33.6	34.4
92.5°	19.6	20.5	23.2	25.9	28.5	31.2	32.9	34.7	36.4	38.2	39.1
95°	29.9	25.8	28.9	31.8	34.8	37.7	39.7	41.6	43.5	45.3	46.3
97.5°	129.5	117.2	97.8	78.3	58.8	39.2	41.4	43.6	45.7	47.9	49.2
100°	227.6	209.2	167.0	124.7	82.5	40.2	42.4	44.5	46.7	48.9	50.1
102.5°	285.9	264.8	218.7	172.5	126.4	80.2	73.5	66.8	60.1	53.3	50.2
105°	375.1	364.4	340.1	315.7	291.3	266.9	219.0	171.0	123.1	75.2	51.4
107.5°	470.8	473.9	477.7	481.6	485.4	489.3	454.1	418.9	383.8	348.6	313.0
110°	535.2	537.8	540.8	543.7	546.7	549.7	540.8	531.8	522.9	514.0	490.1



TEST NUMBER: P332486-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	596.7	599.2	602.2	605.2	608.1	611.1	611.3	611.5	611.6	611.8	607.8
115°	687.9	689.9	692.4	694.7	697.2	699.6	702.3	705.1	707.8	710.5	712.3
117.5°	778.9	780.5	781.7	782.9	784.2	785.5	787.6	789.8	791.9	794.1	795.3
120°	836.2	837.8	838.5	839.4	840.2	841.0	843.2	845.4	847.5	849.7	850.8
122.5°	891.0	892.5	893.5	894.5	895.5	896.6	898.1	899.6	901.2	902.7	903.5
125°	969.1	970.8	971.8	972.9	974.0	975.1	975.7	976.2	976.7	977.2	977.8
127.5°	1044.2	1045.9	1047.3	1048.6	1049.9	1051.2	1052.0	1052.9	1053.8	1054.6	1054.8
130°	1091.0	1092.7	1093.7	1094.8	1095.9	1097.0	1098.0	1099.1	1100.2	1101.3	1101.6
132.5°	1135.9	1137.4	1138.2	1139.1	1140.0	1140.8	1141.9	1143.0	1144.1	1145.2	1145.3
135°	1202.2	1203.5	1204.6	1205.7	1206.8	1207.9	1208.7	1209.5	1210.3	1211.1	1211.1
137.5°	1262.4	1263.8	1264.4	1264.9	1265.6	1266.2	1267.5	1268.8	1270.1	1271.4	1271.7
140°	1299.8	1300.9	1301.7	1302.5	1303.3	1304.2	1305.3	1306.4	1307.4	1308.5	1308.8
142.5°	1335.8	1337.0	1337.8	1338.6	1339.5	1340.3	1341.1	1342.0	1342.9	1343.7	1343.8
145°	1387.3	1388.5	1389.1	1389.6	1390.2	1390.7	1391.2	1391.8	1392.4	1392.9	1393.2
147.5°	1432.2	1433.1	1433.7	1434.3	1434.8	1435.3	1435.9	1436.4	1437.0	1437.5	1437.1
150°	1459.8	1460.4	1461.0	1461.6	1462.1	1462.6	1463.1	1463.7	1464.3	1464.8	1464.7
152.5°	1484.4	1484.7	1485.1	1485.4	1485.7	1486.0	1487.0	1488.0	1489.0	1490.0	1489.8
155°	1517.8	1517.6	1517.9	1518.2	1518.4	1518.7	1520.0	1521.4	1522.7	1524.1	1524.0
157.5°	1548.5	1548.3	1548.0	1547.8	1547.5	1547.2	1548.8	1550.5	1552.1	1553.7	1553.5
160°	1565.1	1564.9	1564.6	1564.3	1564.1	1563.8	1565.5	1567.1	1568.6	1570.3	1570.2
162.5°	1580.0	1579.5	1579.2	1579.0	1578.7	1578.4	1580.3	1582.1	1584.0	1585.8	1585.8
165°	1599.5	1599.0	1598.7	1598.5	1598.2	1597.9	1600.1	1602.2	1604.4	1606.6	1606.7
167.5°	1614.0	1613.6	1613.6	1613.6	1613.6	1613.6	1615.7	1617.9	1620.0	1622.2	1622.2
170°	1622.9	1622.3	1622.3	1622.3	1622.3	1622.3	1624.5	1626.6	1628.8	1631.0	1631.0
172.5°	1627.8	1627.3	1627.5	1627.7	1627.9	1628.2	1630.4	1632.5	1634.7	1636.8	1636.7
175°	1635.2	1634.6	1634.9	1635.2	1635.4	1635.7	1637.6	1639.5	1641.4	1643.3	1643.2
177.5°	1638.2	1637.8	1638.0	1638.2	1638.4	1638.7	1640.4	1642.1	1643.8	1645.6	1645.4
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332486-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1426.2	1425.6	1426.2	1424.1	1426.2	1425.6	1426.2	1432.3	1432.3	1432.8	1433.4
5°	1327.1	1326.5	1324.5	1318.7	1324.5	1326.5	1327.1	1329.0	1334.2	1343.1	1340.5
7.5°	1240.6	1239.7	1234.0	1234.2	1234.0	1239.7	1240.6	1245.6	1251.3	1256.9	1263.4
10°	1189.4	1189.9	1182.3	1177.8	1182.3	1189.9	1189.4	1193.8	1202.2	1206.6	1211.1
12.5°	1139.6	1136.7	1130.5	1125.5	1130.5	1136.7	1139.6	1143.0	1154.5	1159.4	1168.1
15°	1074.0	1067.6	1052.2	1053.4	1052.2	1067.6	1074.0	1071.4	1083.0	1089.3	1091.9
17.5°	996.7	992.0	991.7	982.8	991.7	992.0	996.7	1001.8	1011.8	1018.7	1037.1
20°	951.6	948.4	949.7	940.7	949.7	948.4	951.6	961.8	968.2	977.2	992.0
22.5°	916.2	913.0	907.6	904.8	907.6	913.0	916.2	923.4	930.3	942.9	951.0
25°	864.5	859.3	854.2	857.4	854.2	859.3	864.5	868.3	881.1	886.9	898.4
27.5°	812.7	808.9	803.7	803.1	803.7	808.9	812.7	816.4	823.5	833.2	847.0
30°	779.8	776.0	773.5	770.2	773.5	776.0	779.8	783.1	790.1	800.4	810.7
32.5°	746.6	745.8	741.2	740.5	741.2	745.8	746.6	751.8	758.8	768.6	777.3
35°	703.0	699.1	697.8	698.5	697.8	699.1	703.0	705.6	711.9	720.9	729.2
37.5°	661.5	656.4	654.1	651.8	654.1	656.4	661.5	661.9	668.5	674.5	685.7
40°	631.9	626.7	625.4	624.1	625.4	626.7	631.9	631.2	638.2	642.7	653.0
42.5°	598.5	596.5	595.7	593.4	595.7	596.5	598.5	601.9	605.9	612.5	620.2
45°	553.0	552.4	548.5	549.8	548.5	552.4	553.0	554.9	562.0	566.5	573.5
47.5°	505.1	502.2	499.5	501.3	499.5	502.2	505.1	507.6	512.4	517.9	527.3
50°	472.3	471.0	465.2	466.5	465.2	471.0	472.3	474.8	478.0	485.1	493.4
52.5°	439.4	434.6	432.4	431.6	432.4	434.6	439.4	442.1	445.7	453.8	460.1
55°	385.1	379.4	376.7	375.5	376.7	379.4	385.1	389.6	394.8	403.7	410.1
57.5°	331.8	330.3	328.2	329.6	328.2	330.3	331.8	339.2	344.2	351.3	359.1
60°	300.5	300.5	300.5	299.9	300.5	300.5	300.5	307.0	311.4	318.5	326.8
62.5°	276.5	274.9	274.4	275.3	274.4	274.9	276.5	279.2	283.7	288.2	295.5
65°	239.7	239.0	236.4	235.8	236.4	239.0	239.7	241.6	245.4	248.7	253.7
67.5°	205.0	202.6	201.9	201.0	201.9	202.6	205.0	206.6	209.1	213.3	215.8
70°	178.8	177.5	173.7	174.3	173.7	177.5	178.8	182.0	184.6	189.6	192.2
72.5°	150.6	149.3	148.5	147.7	148.5	149.3	150.6	153.8	156.4	162.0	166.1
75°	119.2	118.5	117.9	120.5	117.9	118.5	119.2	119.8	120.5	122.4	124.3
77.5°	95.5	95.5	95.9	94.8	95.9	95.5	95.5	95.5	95.5	96.5	96.9
80°	80.1	80.1	79.5	79.5	79.5	80.1	80.1	80.1	80.1	80.1	79.5
82.5°	64.2	64.7	65.1	64.1	65.1	64.7	64.2	65.2	65.7	64.7	65.1
85°	42.3	41.7	43.0	42.3	43.0	41.7	42.3	42.3	41.0	42.3	41.7
87.5°	25.9	25.0	25.1	25.8	25.1	25.0	25.9	24.8	24.6	24.5	23.7
90°	35.0	35.5	36.0	36.5	36.0	35.5	35.0	34.4	33.6	32.5	31.4
92.5°	39.5	39.8	40.1	40.4	40.1	39.8	39.5	39.1	38.2	36.4	34.7
95°	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3	45.3	43.5	41.6
97.5°	49.4	49.7	50.0	50.2	50.0	49.7	49.4	49.2	47.9	45.7	43.6
100°	50.4	50.6	51.0	51.2	51.0	50.6	50.4	50.1	48.9	46.7	44.5
102.5°	50.7	51.2	51.7	52.2	51.7	51.2	50.7	50.2	53.3	60.1	66.8
105°	52.0	52.6	53.1	53.6	53.1	52.6	52.0	51.4	75.2	123.1	171.0
107.5°	276.9	240.7	204.6	168.4	204.6	240.7	276.9	313.0	348.6	383.8	418.9
110°	451.3	412.6	373.9	335.2	373.9	412.6	451.3	490.1	514.0	522.9	531.8



TEST NUMBER: P332486-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	599.6	591.4	583.3	575.0	583.3	591.4	599.6	607.8	611.8	611.6	611.5
115°	713.5	714.5	715.6	716.7	715.6	714.5	713.5	712.3	710.5	707.8	705.1
117.5°	795.5	795.7	796.0	796.1	796.0	795.7	795.5	795.3	794.1	791.9	789.8
120°	850.8	850.8	850.8	850.8	850.8	850.8	850.8	850.8	849.7	847.5	845.4
122.5°	903.8	903.9	904.2	904.4	904.2	903.9	903.8	903.5	902.7	901.2	899.6
125°	978.4	978.8	979.4	980.0	979.4	978.8	978.4	977.8	977.2	976.7	976.2
127.5°	1054.3	1053.7	1053.1	1052.6	1053.1	1053.7	1054.3	1054.8	1054.6	1053.8	1052.9
130°	1101.1	1100.5	1099.9	1099.4	1099.9	1100.5	1101.1	1101.6	1101.3	1100.2	1099.1
132.5°	1144.6	1143.9	1143.0	1142.3	1143.0	1143.9	1144.6	1145.3	1145.2	1144.1	1143.0
135°	1210.3	1209.5	1208.7	1207.9	1208.7	1209.5	1210.3	1211.1	1211.1	1210.3	1209.5
137.5°	1271.2	1270.6	1270.1	1269.6	1270.1	1270.6	1271.2	1271.7	1271.4	1270.1	1268.8
140°	1308.2	1307.7	1307.2	1306.6	1307.2	1307.7	1308.2	1308.8	1308.5	1307.4	1306.4
142.5°	1343.0	1342.2	1341.5	1340.8	1341.5	1342.2	1343.0	1343.8	1343.7	1342.9	1342.0
145°	1393.2	1393.2	1393.2	1393.2	1393.2	1393.2	1393.2	1393.2	1392.9	1392.4	1391.8
147.5°	1435.9	1434.7	1433.4	1432.2	1433.4	1434.7	1435.9	1437.1	1437.5	1437.0	1436.4
150°	1463.9	1463.1	1462.2	1461.4	1462.2	1463.1	1463.9	1464.7	1464.8	1464.3	1463.7
152.5°	1488.6	1487.3	1486.0	1484.8	1486.0	1487.3	1488.6	1489.8	1490.0	1489.0	1488.0
155°	1522.3	1520.7	1519.1	1517.5	1519.1	1520.7	1522.3	1524.0	1524.1	1522.7	1521.4
157.5°	1551.4	1549.2	1547.1	1545.0	1547.1	1549.2	1551.4	1553.5	1553.7	1552.1	1550.5
160°	1568.2	1566.4	1564.5	1562.6	1564.5	1566.4	1568.2	1570.2	1570.3	1568.6	1567.1
162.5°	1584.2	1582.5	1580.9	1579.2	1580.9	1582.5	1584.2	1585.8	1585.8	1584.0	1582.1
165°	1604.8	1603.0	1601.0	1599.1	1601.0	1603.0	1604.8	1606.7	1606.6	1604.4	1602.2
167.5°	1620.0	1617.9	1615.7	1613.6	1615.7	1617.9	1620.0	1622.2	1622.2	1620.0	1617.9
170°	1628.8	1626.6	1624.5	1622.3	1624.5	1626.6	1628.8	1631.0	1631.0	1628.8	1626.6
172.5°	1634.3	1632.0	1629.5	1627.2	1629.5	1632.0	1634.3	1636.7	1636.8	1634.7	1632.5
175°	1641.0	1638.8	1636.6	1634.5	1636.6	1638.8	1641.0	1643.2	1643.3	1641.4	1639.5
177.5°	1643.2	1641.0	1638.8	1636.7	1638.8	1641.0	1643.2	1645.4	1645.6	1643.8	1642.1
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332486-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1428.7	1435.9	1443.1	1449.8	1460.0	1464.6	1471.3	1473.8	1481.6	1492.8	1502.0
5°	1341.8	1352.1	1365.5	1376.5	1393.8	1407.2	1422.0	1436.1	1452.7	1476.4	1497.5
7.5°	1268.1	1278.3	1294.5	1314.7	1333.7	1352.8	1373.0	1392.2	1416.0	1450.0	1483.7
10°	1219.4	1231.6	1250.8	1272.6	1296.3	1314.9	1338.6	1363.0	1392.4	1431.6	1471.9
12.5°	1177.4	1186.5	1208.8	1229.6	1256.4	1280.1	1303.3	1331.7	1365.3	1407.0	1455.5
15°	1110.5	1123.3	1145.1	1168.2	1196.4	1221.4	1251.5	1286.1	1318.7	1370.0	1429.0
17.5°	1043.3	1062.8	1085.5	1111.5	1132.5	1166.9	1199.5	1235.1	1275.3	1329.7	1394.4
20°	1000.3	1015.7	1036.8	1074.6	1102.2	1128.5	1158.5	1202.8	1239.9	1301.5	1368.7
22.5°	963.9	975.2	998.9	1030.0	1062.2	1092.6	1123.2	1165.4	1211.2	1269.7	1342.6
25°	910.0	927.9	945.8	968.2	1002.8	1039.3	1072.7	1108.6	1157.3	1219.4	1298.3
27.5°	857.3	873.5	891.2	918.8	945.0	979.2	1014.0	1055.2	1107.4	1173.2	1253.1
30°	823.5	835.6	852.2	887.5	911.2	940.7	981.7	1018.2	1066.9	1136.8	1221.4
32.5°	788.6	804.3	822.6	849.5	878.9	906.9	944.3	983.9	1033.6	1102.4	1189.0
35°	738.8	757.4	776.0	795.9	825.3	854.2	885.6	929.2	979.7	1046.4	1131.6
37.5°	693.1	708.1	723.2	747.8	775.8	803.2	832.5	875.5	923.2	995.1	1073.2
40°	663.9	677.4	688.8	714.5	741.4	770.9	799.7	837.6	888.8	956.1	1031.7
42.5°	632.1	644.5	660.1	681.2	710.1	735.0	763.9	799.6	847.7	916.1	982.4
45°	584.4	598.5	612.0	631.9	660.6	685.0	710.6	744.6	793.9	850.4	909.3
47.5°	534.8	548.9	564.3	583.5	608.6	633.4	659.0	689.1	734.1	789.5	829.2
50°	503.0	514.5	529.9	549.2	572.3	598.5	621.6	654.3	697.2	740.8	775.3
52.5°	470.2	480.7	498.1	518.4	540.0	562.6	587.3	615.3	654.1	695.1	722.6
55°	419.1	431.9	446.6	466.5	487.6	506.9	530.6	559.5	590.2	620.9	639.5
57.5°	371.3	381.9	394.4	414.8	433.2	456.2	477.4	499.9	528.3	551.5	563.6
60°	336.4	346.0	362.1	380.0	397.3	417.2	441.5	463.9	485.8	504.3	513.9
62.5°	303.6	314.8	328.7	345.1	363.9	382.8	404.1	422.9	442.1	458.2	464.7
65°	260.8	269.8	280.1	295.4	310.8	330.0	346.7	365.9	380.0	389.0	394.8
67.5°	221.8	227.7	235.5	245.8	260.9	277.7	293.8	308.8	320.7	326.8	331.9
70°	196.7	200.6	206.4	216.6	228.1	242.9	259.5	270.4	280.7	285.8	290.9
72.5°	171.6	176.5	181.7	190.0	199.4	210.0	222.1	235.5	241.2	247.4	250.5
75°	130.1	137.1	144.1	149.3	155.7	164.0	175.0	183.3	186.5	191.6	192.2
77.5°	98.2	99.7	104.8	111.2	116.6	122.6	129.6	137.0	138.5	141.2	142.9
80°	80.7	80.7	80.7	84.5	91.0	95.5	101.9	105.7	108.3	108.9	109.6
82.5°	64.8	64.8	64.3	65.1	67.4	69.9	75.7	80.1	82.2	81.8	80.4
85°	42.3	41.0	41.0	40.4	41.0	39.7	39.1	41.7	45.5	45.5	44.2
87.5°	23.5	22.7	22.6	21.4	20.1	18.9	16.8	16.7	16.2	17.7	16.6
90°	30.3	29.3	25.8	22.2	18.7	15.2	12.1	9.4	6.6	3.9	1.2
92.5°	32.9	31.2	28.5	25.9	23.2	20.5	19.6	20.4	21.1	21.9	22.7
95°	39.7	37.7	34.8	31.8	28.9	25.8	29.9	41.0	52.2	63.3	74.4
97.5°	41.4	39.2	58.8	78.3	97.8	117.2	129.5	134.4	139.5	144.5	149.4
100°	42.4	40.2	82.5	124.7	167.0	209.2	227.6	222.3	216.8	211.4	206.0
102.5°	73.5	80.2	126.4	172.5	218.7	264.8	285.9	282.0	278.2	274.3	270.4
105°	219.0	266.9	291.3	315.7	340.1	364.4	375.1	372.2	369.2	366.2	363.2
107.5°	454.1	489.3	485.4	481.6	477.7	473.9	470.8	468.4	465.9	463.6	461.2
110°	540.8	549.7	546.7	543.7	540.8	537.8	535.2	533.0	530.8	528.7	526.5



TEST NUMBER: P332486-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	611.3	611.1	608.1	605.2	602.2	599.2	596.7	594.8	592.9	590.9	589.0
115°	702.3	699.6	697.2	694.7	692.4	689.9	687.9	686.2	684.6	683.0	681.3
117.5°	787.6	785.5	784.2	782.9	781.7	780.5	778.9	776.8	774.8	772.8	770.8
120°	843.2	841.0	840.2	839.4	838.5	837.8	836.2	833.7	831.3	828.8	826.4
122.5°	898.1	896.6	895.5	894.5	893.5	892.5	891.0	888.9	887.0	884.9	883.0
125°	975.7	975.1	974.0	972.9	971.8	970.8	969.1	966.9	964.8	962.6	960.4
127.5°	1052.0	1051.2	1049.9	1048.6	1047.3	1045.9	1044.2	1042.0	1039.9	1037.7	1035.5
130°	1098.0	1097.0	1095.9	1094.8	1093.7	1092.7	1091.0	1088.8	1086.7	1084.5	1082.3
132.5°	1141.9	1140.8	1140.0	1139.1	1138.2	1137.4	1135.9	1133.7	1131.6	1129.4	1127.2
135°	1208.7	1207.9	1206.8	1205.7	1204.6	1203.5	1202.2	1200.6	1199.0	1197.3	1195.7
137.5°	1267.5	1266.2	1265.6	1264.9	1264.4	1263.8	1262.4	1260.4	1258.3	1256.3	1254.2
140°	1305.3	1304.2	1303.3	1302.5	1301.7	1300.9	1299.8	1298.1	1296.5	1294.9	1293.2
142.5°	1341.1	1340.3	1339.5	1338.6	1337.8	1337.0	1335.8	1334.2	1332.5	1330.9	1329.3
145°	1391.2	1390.7	1390.2	1389.6	1389.1	1388.5	1387.3	1385.4	1383.6	1381.6	1379.7
147.5°	1435.9	1435.3	1434.8	1434.3	1433.7	1433.1	1432.2	1431.0	1429.8	1428.6	1427.3
150°	1463.1	1462.6	1462.1	1461.6	1461.0	1460.4	1459.8	1459.0	1458.2	1457.3	1456.5
152.5°	1487.0	1486.0	1485.7	1485.4	1485.1	1484.7	1484.4	1484.0	1483.6	1483.3	1482.9
155°	1520.0	1518.7	1518.4	1518.2	1517.9	1517.6	1517.8	1518.3	1518.8	1519.4	1519.9
157.5°	1548.8	1547.2	1547.5	1547.8	1548.0	1548.3	1548.5	1548.5	1548.6	1548.7	1548.7
160°	1565.5	1563.8	1564.1	1564.3	1564.6	1564.9	1565.1	1565.5	1565.7	1565.9	1566.3
162.5°	1580.3	1578.4	1578.7	1579.0	1579.2	1579.5	1580.0	1580.7	1581.4	1582.1	1582.8
165°	1600.1	1597.9	1598.2	1598.5	1598.7	1599.0	1599.5	1600.4	1601.2	1602.0	1602.8
167.5°	1615.7	1613.6	1613.6	1613.6	1613.6	1613.6	1614.0	1615.2	1616.2	1617.3	1618.4
170°	1624.5	1622.3	1622.3	1622.3	1622.3	1622.3	1622.9	1623.9	1625.0	1626.1	1627.2
172.5°	1630.4	1628.2	1627.9	1627.7	1627.5	1627.3	1627.8	1629.1	1630.4	1631.7	1633.0
175°	1637.6	1635.7	1635.4	1635.2	1634.9	1634.6	1635.2	1636.6	1637.9	1639.2	1640.5
177.5°	1640.4	1638.7	1638.4	1638.2	1638.0	1637.8	1638.2	1639.3	1640.4	1641.4	1642.5
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332486-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1505.1	1510.7	1517.9	1528.7	1536.9	1544.1	1545.6	1547.7	1552.8	1561.5	1568.1
5°	1514.8	1529.6	1553.3	1576.4	1601.3	1621.9	1641.1	1654.6	1667.4	1694.3	1716.0
7.5°	1511.8	1544.6	1581.8	1623.2	1665.1	1705.7	1743.4	1777.0	1810.6	1849.8	1894.6
10°	1509.7	1548.2	1598.1	1651.3	1709.7	1766.7	1821.8	1864.8	1914.7	1959.6	2016.6
12.5°	1500.0	1555.3	1615.1	1683.1	1754.8	1820.5	1893.0	1952.4	2009.5	2074.4	2140.6
15°	1487.3	1554.6	1630.2	1720.5	1829.5	1908.9	1983.3	2086.4	2157.0	2227.4	2322.3
17.5°	1464.1	1546.2	1640.7	1758.1	1848.9	1955.7	2067.6	2149.1	2244.1	2343.4	2429.3
20°	1445.6	1541.2	1646.8	1762.2	1878.2	1994.1	2102.5	2199.8	2297.9	2412.6	2483.1
22.5°	1427.2	1521.7	1631.5	1754.0	1878.7	2000.8	2123.4	2237.8	2348.1	2463.9	2553.8
25°	1388.0	1500.2	1619.3	1744.3	1867.3	2001.9	2148.0	2275.5	2412.0	2531.2	2616.4
27.5°	1348.3	1451.0	1569.7	1696.5	1833.2	1992.3	2164.1	2309.1	2445.8	2531.2	2557.9
30°	1312.4	1421.3	1530.2	1659.1	1807.0	1984.5	2167.1	2333.1	2445.3	2482.4	2454.9
32.5°	1275.9	1374.7	1482.5	1614.5	1771.6	1965.6	2171.3	2318.8	2386.3	2357.9	2245.7
35°	1211.8	1300.8	1405.2	1537.2	1718.0	1955.1	2154.3	2254.3	2237.7	2077.5	1866.0
37.5°	1143.0	1215.6	1312.4	1450.4	1662.4	1913.4	2081.5	2096.3	1952.2	1706.2	1461.9
40°	1088.8	1154.1	1253.4	1397.6	1619.3	1872.4	2008.2	1948.6	1725.0	1451.4	1247.7
42.5°	1035.9	1091.0	1186.7	1342.2	1578.3	1816.6	1899.1	1769.3	1511.2	1252.5	1067.2
45°	946.5	998.3	1094.5	1254.0	1494.4	1709.7	1698.8	1473.2	1215.0	1006.7	852.9
47.5°	861.6	907.0	997.2	1160.1	1395.8	1549.5	1447.6	1207.5	988.5	821.4	711.7
50°	801.6	846.5	936.2	1097.1	1316.9	1429.0	1283.5	1052.2	851.7	713.2	626.1
52.5°	744.2	788.1	870.1	1026.8	1221.5	1288.5	1132.3	917.9	750.6	631.2	556.4
55°	663.9	697.2	770.9	920.8	1066.3	1081.7	923.4	744.0	606.2	522.9	471.7
57.5°	582.0	610.7	683.5	802.9	904.9	897.0	746.9	591.7	499.0	437.0	399.8
60°	528.6	556.8	620.9	723.5	800.4	773.5	635.7	510.7	431.3	385.8	356.3
62.5°	478.9	501.0	560.9	635.8	691.1	660.6	543.4	439.9	376.9	338.6	315.3
65°	406.9	424.9	472.9	512.0	542.7	513.3	415.9	344.1	298.6	271.7	255.7
67.5°	338.4	349.8	380.3	394.4	416.0	383.7	312.7	264.6	238.8	216.1	205.0
70°	295.4	303.7	319.8	331.3	337.0	303.7	251.2	216.0	194.1	178.1	171.1
72.5°	252.3	259.7	262.9	272.3	269.4	238.1	201.9	173.9	158.2	147.4	138.3
75°	192.9	196.1	192.9	189.1	180.7	158.9	134.0	119.8	108.3	103.1	100.0
77.5°	140.6	139.6	135.2	129.2	115.0	101.3	87.8	83.1	78.0	75.3	74.2
80°	108.3	105.7	101.9	92.3	80.1	70.5	67.3	64.1	62.1	58.9	58.3
82.5°	80.6	79.1	72.6	64.6	56.0	51.5	48.8	47.7	45.7	44.1	43.9
85°	43.0	41.0	34.0	29.5	28.2	26.9	26.3	26.3	23.7	23.1	23.1
87.5°	14.6	12.1	12.1	11.1	11.7	11.4	12.6	12.3	12.5	13.2	12.5
90°	3.9	6.6	9.4	12.1	15.2	18.7	22.2	25.8	29.3	30.3	31.4
92.5°	21.9	21.1	20.4	19.6	20.5	23.2	25.9	28.5	31.2	32.9	34.7
95°	63.3	52.2	41.0	29.9	25.8	28.9	31.8	34.8	37.7	39.7	41.6
97.5°	144.5	139.5	134.4	129.5	117.2	97.8	78.3	58.8	39.2	41.4	43.6
100°	211.4	216.8	222.3	227.6	209.2	167.0	124.7	82.5	40.2	42.4	44.5
102.5°	274.3	278.2	282.0	285.9	264.8	218.7	172.5	126.4	80.2	73.5	66.8
105°	366.2	369.2	372.2	375.1	364.4	340.1	315.7	291.3	266.9	219.0	171.0
107.5°	463.6	465.9	468.4	470.8	473.9	477.7	481.6	485.4	489.3	454.1	418.9
110°	528.7	530.8	533.0	535.2	537.8	540.8	543.7	546.7	549.7	540.8	531.8



TEST NUMBER: P332486-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	590.9	592.9	594.8	596.7	599.2	602.2	605.2	608.1	611.1	611.3	611.5
115°	683.0	684.6	686.2	687.9	689.9	692.4	694.7	697.2	699.6	702.3	705.1
117.5°	772.8	774.8	776.8	778.9	780.5	781.7	782.9	784.2	785.5	787.6	789.8
120°	828.8	831.3	833.7	836.2	837.8	838.5	839.4	840.2	841.0	843.2	845.4
122.5°	884.9	887.0	888.9	891.0	892.5	893.5	894.5	895.5	896.6	898.1	899.6
125°	962.6	964.8	966.9	969.1	970.8	971.8	972.9	974.0	975.1	975.7	976.2
127.5°	1037.7	1039.9	1042.0	1044.2	1045.9	1047.3	1048.6	1049.9	1051.2	1052.0	1052.9
130°	1084.5	1086.7	1088.8	1091.0	1092.7	1093.7	1094.8	1095.9	1097.0	1098.0	1099.1
132.5°	1129.4	1131.6	1133.7	1135.9	1137.4	1138.2	1139.1	1140.0	1140.8	1141.9	1143.0
135°	1197.3	1199.0	1200.6	1202.2	1203.5	1204.6	1205.7	1206.8	1207.9	1208.7	1209.5
137.5°	1256.3	1258.3	1260.4	1262.4	1263.8	1264.4	1264.9	1265.6	1266.2	1267.5	1268.8
140°	1294.9	1296.5	1298.1	1299.8	1300.9	1301.7	1302.5	1303.3	1304.2	1305.3	1306.4
142.5°	1330.9	1332.5	1334.2	1335.8	1337.0	1337.8	1338.6	1339.5	1340.3	1341.1	1342.0
145°	1381.6	1383.6	1385.4	1387.3	1388.5	1389.1	1389.6	1390.2	1390.7	1391.2	1391.8
147.5°	1428.6	1429.8	1431.0	1432.2	1433.1	1433.7	1434.3	1434.8	1435.3	1435.9	1436.4
150°	1457.3	1458.2	1459.0	1459.8	1460.4	1461.0	1461.6	1462.1	1462.6	1463.1	1463.7
152.5°	1483.3	1483.6	1484.0	1484.4	1484.7	1485.1	1485.4	1485.7	1486.0	1487.0	1488.0
155°	1519.4	1518.8	1518.3	1517.8	1517.6	1517.9	1518.2	1518.4	1518.7	1520.0	1521.4
157.5°	1548.7	1548.6	1548.5	1548.5	1548.3	1548.0	1547.8	1547.5	1547.2	1548.8	1550.5
160°	1565.9	1565.7	1565.5	1565.1	1564.9	1564.6	1564.3	1564.1	1563.8	1565.5	1567.1
162.5°	1582.1	1581.4	1580.7	1580.0	1579.5	1579.2	1579.0	1578.7	1578.4	1580.3	1582.1
165°	1602.0	1601.2	1600.4	1599.5	1599.0	1598.7	1598.5	1598.2	1597.9	1600.1	1602.2
167.5°	1617.3	1616.2	1615.2	1614.0	1613.6	1613.6	1613.6	1613.6	1613.6	1615.7	1617.9
170°	1626.1	1625.0	1623.9	1622.9	1622.3	1622.3	1622.3	1622.3	1622.3	1624.5	1626.6
172.5°	1631.7	1630.4	1629.1	1627.8	1627.3	1627.5	1627.7	1627.9	1628.2	1630.4	1632.5
175°	1639.2	1637.9	1636.6	1635.2	1634.6	1634.9	1635.2	1635.4	1635.7	1637.6	1639.5
177.5°	1641.4	1640.4	1639.3	1638.2	1637.8	1638.0	1638.2	1638.4	1638.7	1640.4	1642.1
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332486-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1578.9	1578.9	1580.9	1588.7	1589.7	1596.4	1594.3
5°	1735.3	1747.4	1751.9	1771.2	1782.7	1787.9	1777.6
7.5°	1926.5	1960.9	1977.1	1997.2	2015.1	2020.5	2006.5
10°	2066.0	2101.8	2131.9	2150.5	2167.8	2179.4	2194.1
12.5°	2200.7	2244.8	2273.5	2299.7	2317.5	2332.2	2334.5
15°	2347.2	2413.9	2464.5	2501.7	2520.3	2529.9	2526.0
17.5°	2495.0	2556.8	2592.8	2630.7	2656.5	2657.8	2658.5
20°	2578.5	2638.8	2680.5	2708.7	2737.5	2736.2	2742.6
22.5°	2634.5	2681.8	2713.8	2734.3	2744.1	2739.3	2740.5
25°	2660.6	2674.7	2669.0	2636.3	2628.0	2597.8	2602.9
27.5°	2525.8	2459.1	2390.2	2301.5	2231.6	2175.6	2178.5
30°	2342.8	2224.9	2090.3	1977.5	1876.2	1848.0	1787.9
32.5°	2086.9	1910.1	1752.5	1647.4	1560.5	1536.9	1484.3
35°	1653.3	1481.6	1319.4	1222.0	1183.6	1129.8	1129.1
37.5°	1285.1	1133.8	1048.1	975.0	936.7	904.2	901.0
40°	1081.0	963.1	898.4	845.9	808.0	783.7	778.0
42.5°	938.5	843.2	782.5	750.0	720.9	708.3	699.0
45°	766.4	702.3	660.0	630.6	617.1	607.5	602.3
47.5°	641.1	598.1	569.3	549.7	538.7	528.6	531.3
50°	572.9	537.6	516.5	497.9	489.6	482.5	483.1
52.5°	518.0	486.4	469.3	455.8	445.5	440.5	438.1
55°	439.6	419.7	402.4	392.8	387.0	380.0	378.1
57.5°	375.0	359.6	345.5	334.6	333.2	326.4	327.3
60°	331.9	319.1	307.6	301.8	297.3	291.6	293.5
62.5°	296.5	285.8	275.3	270.5	266.0	261.8	262.7
65°	242.9	232.6	226.2	223.6	221.7	219.8	217.8
67.5°	193.6	187.3	183.3	177.7	173.8	173.2	171.2
70°	162.7	154.4	147.4	140.3	138.4	137.8	138.4
72.5°	130.4	125.2	123.3	119.8	119.4	117.8	119.0
75°	98.1	96.1	94.8	92.3	92.3	92.3	92.3
77.5°	72.3	71.1	70.4	69.9	69.2	68.3	68.2
80°	56.4	55.8	54.5	54.5	53.8	54.5	53.8
82.5°	42.6	42.4	41.2	41.2	40.5	40.1	40.5
85°	21.8	21.1	22.4	21.1	21.8	20.5	21.8
87.5°	12.6	12.9	12.6	12.6	12.2	13.4	12.5
90°	32.5	33.6	34.4	35.0	35.5	36.0	36.5
92.5°	36.4	38.2	39.1	39.5	39.8	40.1	40.4
95°	43.5	45.3	46.3	46.3	46.3	46.3	46.3
97.5°	45.7	47.9	49.2	49.4	49.7	50.0	50.2
100°	46.7	48.9	50.1	50.4	50.6	51.0	51.2
102.5°	60.1	53.3	50.2	50.7	51.2	51.7	52.2
105°	123.1	75.2	51.4	52.0	52.6	53.1	53.6
107.5°	383.8	348.6	313.0	276.9	240.7	204.6	168.4
110°	522.9	514.0	490.1	451.3	412.6	373.9	335.2



TEST NUMBER: P332486-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	611.6	611.8	607.8	599.6	591.4	583.3	575.0
115°	707.8	710.5	712.3	713.5	714.5	715.6	716.7
117.5°	791.9	794.1	795.3	795.5	795.7	796.0	796.1
120°	847.5	849.7	850.8	850.8	850.8	850.8	850.8
122.5°	901.2	902.7	903.5	903.8	903.9	904.2	904.4
125°	976.7	977.2	977.8	978.4	978.8	979.4	980.0
127.5°	1053.8	1054.6	1054.8	1054.3	1053.7	1053.1	1052.6
130°	1100.2	1101.3	1101.6	1101.1	1100.5	1099.9	1099.4
132.5°	1144.1	1145.2	1145.3	1144.6	1143.9	1143.0	1142.3
135°	1210.3	1211.1	1211.1	1210.3	1209.5	1208.7	1207.9
137.5°	1270.1	1271.4	1271.7	1271.2	1270.6	1270.1	1269.6
140°	1307.4	1308.5	1308.8	1308.2	1307.7	1307.2	1306.6
142.5°	1342.9	1343.7	1343.8	1343.0	1342.2	1341.5	1340.8
145°	1392.4	1392.9	1393.2	1393.2	1393.2	1393.2	1393.2
147.5°	1437.0	1437.5	1437.1	1435.9	1434.7	1433.4	1432.2
150°	1464.3	1464.8	1464.7	1463.9	1463.1	1462.2	1461.4
152.5°	1489.0	1490.0	1489.8	1488.6	1487.3	1486.0	1484.8
155°	1522.7	1524.1	1524.0	1522.3	1520.7	1519.1	1517.5
157.5°	1552.1	1553.7	1553.5	1551.4	1549.2	1547.1	1545.0
160°	1568.6	1570.3	1570.2	1568.2	1566.4	1564.5	1562.6
162.5°	1584.0	1585.8	1585.8	1584.2	1582.5	1580.9	1579.2
165°	1604.4	1606.6	1606.7	1604.8	1603.0	1601.0	1599.1
167.5°	1620.0	1622.2	1622.2	1620.0	1617.9	1615.7	1613.6
170°	1628.8	1631.0	1631.0	1628.8	1626.6	1624.5	1622.3
172.5°	1634.7	1636.8	1636.7	1634.3	1632.0	1629.5	1627.2
175°	1641.4	1643.3	1643.2	1641.0	1638.8	1636.6	1634.5
177.5°	1643.8	1645.6	1645.4	1643.2	1641.0	1638.8	1636.7
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5

(END OF REPORT)