

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332488-930

Luminaire Tested: **S123RDIW-S1165D1535U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332488-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D1535U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8577.4 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332488-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332488-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42					42			
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36					36			
2	88	81	75	70	80	74	69	64	61	57	54	49	47	45	38	37	35	30					30			
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26					26			
4	73	63	55	50	67	58	51	46	48	43	39	39	36	33	31	28	26	22					22			
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	28	25	23	20					20			
6	62	50	43	37	57	46	40	34	39	34	30	32	28	25	25	23	20	17					17			
7	58	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	16					16			
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	21	18	16	14					14			
9	50	38	30	26	45	35	28	24	30	24	21	24	21	18	20	17	15	13					13			
10	46	35	28	23	42	32	26	22	27	22	19	23	19	16	18	15	13	12					12			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17009	17009	17009
5°	17074	16839	16935
10°	16978	16628	16571
15°	16796	16238	16067
20°	16544	15753	15385
25°	16286	15206	14719
30°	15945	14574	13779
35°	15594	13943	12917
40°	15271	13200	11849
45°	14846	12466	10886
50°	14380	11632	9808
55°	13902	10678	8801
60°	13464	9657	7698
65°	12893	8550	6594
70°	12180	7179	5325
75°	11137	5648	5011
80°	9930	5002	4612
85°	8386	4434	4113



TEST NUMBER: P332488-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.4	1.7
10°-20°	412.9	4.8
20°-30°	594.5	6.9
30°-40°	669.6	7.8
40°-50°	640.6	7.5
50°-60°	524.6	6.1
60°-70°	354.0	4.1
70°-80°	178.1	2.1
80°-90°	51.7	0.6
90°-100°	59.6	0.7
100°-110°	284.3	3.3
110°-120°	682.8	8.0
120°-130°	869.5	10.1
130°-140°	929.1	10.8
140°-150°	868.8	10.1
150°-160°	700.8	8.2
160°-170°	452.3	5.3
170°-180°	155.9	1.8
0°-30°	1155.7	13.5
0°-40°	1825.4	21.3
0°-60°	2990.6	34.9
0°-90°	3574.4	41.7
90°-120°	1026.8	12.0
90°-150°	3694.1	43.1
90°-180°	5003.0	58.3
0°-180°	8577.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1580	1580	1580	1580	1580	
5°	1580	1573	1558	1569	1567	150
15°	1507	1492	1457	1451	1442	424
25°	1371	1338	1280	1254	1239	630
35°	1187	1139	1061	1008	983	742
45°	975	915	819	748	715	752
55°	741	675	569	497	469	664
65°	506	434	336	276	259	501
75°	268	206	136	124	120	286
85°	68	41	36	33	33	76
90°	1	14	29	34	36	7
95°	74	28	38	46	46	92
105°	363	370	267	63	54	385
115°	681	689	700	711	717	672
125°	960	970	975	978	980	857
135°	1196	1203	1208	1211	1208	920
145°	1380	1388	1391	1393	1393	863
155°	1520	1518	1519	1524	1518	700
165°	1603	1599	1598	1607	1599	453
175°	1640	1635	1636	1643	1634	156
180°	1640	1640	1640	1640	1640	



TEST NUMBER: P332488-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2
2.5°	1585.3	1584.4	1583.5	1582.6	1581.7	1579.8	1577.1	1574.3	1571.7	1568.9	1571.4
5°	1580.2	1578.7	1577.4	1575.9	1574.5	1572.1	1568.6	1565.2	1561.8	1558.4	1561.0
7.5°	1565.5	1564.1	1562.5	1561.0	1559.4	1556.4	1552.0	1547.5	1543.1	1538.6	1540.1
10°	1553.3	1551.3	1549.3	1547.3	1545.3	1541.7	1536.6	1531.5	1526.3	1521.3	1521.5
12.5°	1535.9	1533.7	1531.4	1529.2	1527.0	1522.7	1516.5	1510.2	1503.9	1497.6	1497.5
15°	1507.2	1504.0	1500.9	1497.7	1494.6	1489.1	1481.1	1473.1	1465.1	1457.2	1455.7
17.5°	1471.0	1467.4	1463.7	1460.0	1456.5	1449.5	1439.4	1429.2	1419.1	1409.0	1406.0
20°	1444.3	1439.8	1435.3	1430.7	1426.1	1418.5	1407.6	1396.8	1385.9	1375.2	1371.4
22.5°	1414.6	1409.3	1404.1	1398.9	1393.7	1385.3	1373.8	1362.3	1350.8	1339.2	1334.6
25°	1371.3	1364.2	1357.1	1349.9	1342.8	1332.7	1319.6	1306.5	1293.4	1280.3	1274.3
27.5°	1318.7	1310.9	1303.0	1295.2	1287.3	1276.1	1261.5	1246.9	1232.3	1217.7	1209.4
30°	1282.9	1274.3	1265.8	1257.2	1248.7	1236.4	1220.5	1204.5	1188.6	1172.6	1162.9
32.5°	1247.0	1237.3	1227.6	1217.9	1208.3	1195.0	1178.1	1161.2	1144.4	1127.6	1117.0
35°	1186.7	1176.5	1166.2	1156.0	1145.7	1131.8	1114.1	1096.5	1078.8	1061.1	1048.9
37.5°	1125.8	1114.4	1102.9	1091.5	1080.2	1065.0	1046.2	1027.4	1008.5	989.6	975.8
40°	1086.8	1074.2	1061.7	1049.2	1036.7	1020.3	1000.0	979.8	959.6	939.4	924.5
42.5°	1042.7	1030.1	1017.7	1005.1	992.5	975.8	955.0	934.0	913.1	892.3	876.0
45°	975.3	962.5	949.7	936.9	924.0	906.6	884.7	862.7	840.8	818.9	802.7
47.5°	907.8	893.8	879.7	865.7	851.6	833.6	811.6	789.7	767.8	745.9	728.2
50°	858.7	845.3	831.8	818.5	805.1	786.9	763.9	740.8	717.7	694.6	676.9
52.5°	814.6	800.1	785.5	771.0	756.4	737.8	714.9	692.1	669.3	646.5	628.1
55°	740.8	726.8	712.8	698.9	684.9	665.9	641.6	617.4	593.2	569.0	552.5
57.5°	672.5	657.4	642.1	627.0	611.7	592.0	567.7	543.3	519.0	494.7	479.1
60°	625.4	609.8	594.1	578.5	562.7	543.1	519.4	495.9	472.2	448.6	433.2
62.5°	578.2	562.6	546.9	531.2	515.6	495.9	472.3	448.7	425.0	401.4	386.9
65°	506.2	490.6	474.9	459.3	443.6	424.6	402.4	380.2	358.0	335.7	321.8
67.5°	434.2	418.3	402.5	386.7	370.9	352.3	331.0	309.7	288.4	267.1	256.7
70°	387.0	371.7	356.3	340.9	325.5	307.9	288.0	268.0	248.1	228.1	218.2
72.5°	339.9	324.7	309.6	294.4	279.2	262.6	244.5	226.4	208.3	190.2	182.1
75°	267.8	254.2	240.5	226.8	213.2	198.5	182.9	167.1	151.5	135.8	133.0
77.5°	202.2	189.9	177.5	165.2	152.8	141.5	131.5	121.4	111.3	101.3	99.7
80°	160.2	148.5	136.8	125.1	113.5	104.7	98.7	92.7	86.7	80.7	79.9
82.5°	120.2	110.1	100.0	89.9	79.9	73.5	70.7	67.8	65.1	62.3	61.4
85°	67.9	61.6	55.4	49.2	42.9	39.3	38.5	37.6	36.8	35.9	35.3
87.5°	24.9	22.9	21.0	19.0	17.0	16.4	17.0	17.8	18.5	19.2	19.2
90°	1.2	3.9	6.6	9.4	12.1	15.2	18.7	22.2	25.8	29.3	30.3
92.5°	22.7	21.9	21.1	20.4	19.6	20.5	23.2	25.9	28.5	31.2	32.9
95°	74.4	63.3	52.2	41.0	29.9	25.8	28.9	31.8	34.8	37.7	39.7
97.5°	149.4	144.5	139.5	134.4	129.5	117.2	97.8	78.3	58.8	39.2	41.4
100°	206.0	211.4	216.8	222.3	227.6	209.2	167.0	124.7	82.5	40.2	42.4
102.5°	270.4	274.3	278.2	282.0	285.9	264.8	218.7	172.5	126.4	80.2	73.5
105°	363.2	366.2	369.2	372.2	375.1	364.4	340.1	315.7	291.3	266.9	219.0
107.5°	461.2	463.6	465.9	468.4	470.8	473.9	477.7	481.6	485.4	489.3	454.1
110°	526.5	528.7	530.8	533.0	535.2	537.8	540.8	543.7	546.7	549.7	540.8



TEST NUMBER: P332488-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	589.0	590.9	592.9	594.8	596.7	599.2	602.2	605.2	608.1	611.1	611.3
115°	681.3	683.0	684.6	686.2	687.9	689.9	692.4	694.7	697.2	699.6	702.3
117.5°	770.8	772.8	774.8	776.8	778.9	780.5	781.7	782.9	784.2	785.5	787.6
120°	826.4	828.8	831.3	833.7	836.2	837.8	838.5	839.4	840.2	841.0	843.2
122.5°	883.0	884.9	887.0	888.9	891.0	892.5	893.5	894.5	895.5	896.6	898.1
125°	960.4	962.6	964.8	966.9	969.1	970.8	971.8	972.9	974.0	975.1	975.7
127.5°	1035.5	1037.7	1039.9	1042.0	1044.2	1045.9	1047.3	1048.6	1049.9	1051.2	1052.0
130°	1082.3	1084.5	1086.7	1088.8	1091.0	1092.7	1093.7	1094.8	1095.9	1097.0	1098.0
132.5°	1127.2	1129.4	1131.6	1133.7	1135.9	1137.4	1138.2	1139.1	1140.0	1140.8	1141.9
135°	1195.7	1197.3	1199.0	1200.6	1202.2	1203.5	1204.6	1205.7	1206.8	1207.9	1208.7
137.5°	1254.2	1256.3	1258.3	1260.4	1262.4	1263.8	1264.4	1264.9	1265.6	1266.2	1267.5
140°	1293.2	1294.9	1296.5	1298.1	1299.8	1300.9	1301.7	1302.5	1303.3	1304.2	1305.3
142.5°	1329.3	1330.9	1332.5	1334.2	1335.8	1337.0	1337.8	1338.6	1339.5	1340.3	1341.1
145°	1379.7	1381.6	1383.6	1385.4	1387.3	1388.5	1389.1	1389.6	1390.2	1390.7	1391.2
147.5°	1427.3	1428.6	1429.8	1431.0	1432.2	1433.1	1433.7	1434.3	1434.8	1435.3	1435.9
150°	1456.5	1457.3	1458.2	1459.0	1459.8	1460.4	1461.0	1461.6	1462.1	1462.6	1463.1
152.5°	1482.9	1483.3	1483.6	1484.0	1484.4	1484.7	1485.1	1485.4	1485.7	1486.0	1487.0
155°	1519.9	1519.4	1518.8	1518.3	1517.8	1517.6	1517.9	1518.2	1518.4	1518.7	1520.0
157.5°	1548.7	1548.7	1548.6	1548.5	1548.5	1548.3	1548.0	1547.8	1547.5	1547.2	1548.8
160°	1566.3	1565.9	1565.7	1565.5	1565.1	1564.9	1564.6	1564.3	1564.1	1563.8	1565.5
162.5°	1582.8	1582.1	1581.4	1580.7	1580.0	1579.5	1579.2	1579.0	1578.7	1578.4	1580.3
165°	1602.8	1602.0	1601.2	1600.4	1599.5	1599.0	1598.7	1598.5	1598.2	1597.9	1600.1
167.5°	1618.4	1617.3	1616.2	1615.2	1614.0	1613.6	1613.6	1613.6	1613.6	1613.6	1615.7
170°	1627.2	1626.1	1625.0	1623.9	1622.9	1622.3	1622.3	1622.3	1622.3	1622.3	1624.5
172.5°	1633.0	1631.7	1630.4	1629.1	1627.8	1627.3	1627.5	1627.7	1627.9	1628.2	1630.4
175°	1640.5	1639.2	1637.9	1636.6	1635.2	1634.6	1634.9	1635.2	1635.4	1635.7	1637.6
177.5°	1642.5	1641.4	1640.4	1639.3	1638.2	1637.8	1638.0	1638.2	1638.4	1638.7	1640.4
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332488-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2
2.5°	1573.9	1576.5	1578.9	1580.0	1579.5	1579.1	1578.6	1578.1
5°	1563.5	1566.1	1568.6	1569.6	1569.0	1568.5	1567.9	1567.3
7.5°	1541.5	1543.0	1544.3	1544.6	1543.6	1542.6	1541.6	1540.7
10°	1521.8	1522.1	1522.4	1521.8	1520.4	1519.0	1517.5	1516.1
12.5°	1497.3	1497.1	1497.0	1496.1	1494.4	1492.7	1491.1	1489.5
15°	1454.3	1452.9	1451.5	1449.8	1447.7	1445.8	1443.7	1441.8
17.5°	1403.0	1399.9	1396.9	1393.9	1390.9	1388.0	1385.0	1382.0
20°	1367.7	1364.0	1360.3	1356.7	1353.3	1349.9	1346.5	1343.1
22.5°	1330.0	1325.4	1320.8	1316.9	1313.7	1310.5	1307.3	1304.2
25°	1268.4	1262.3	1256.4	1251.8	1248.7	1245.5	1242.4	1239.3
27.5°	1201.1	1192.8	1184.5	1177.9	1173.1	1168.4	1163.6	1158.8
30°	1153.2	1143.6	1133.9	1126.8	1122.3	1117.7	1113.1	1108.6
32.5°	1106.4	1095.8	1085.2	1077.5	1072.7	1067.9	1063.2	1058.3
35°	1036.7	1024.4	1012.2	1003.5	998.3	993.2	988.1	983.0
37.5°	961.8	947.9	934.0	923.9	917.6	911.3	905.0	898.6
40°	909.8	895.0	880.2	869.5	862.9	856.4	849.9	843.3
42.5°	859.9	843.7	827.5	816.5	810.7	804.8	798.9	793.0
45°	786.4	770.2	754.0	742.5	735.6	728.8	721.9	715.1
47.5°	710.5	692.9	675.2	663.4	657.3	651.2	645.1	639.0
50°	659.3	641.6	623.9	611.9	605.4	598.8	592.2	585.7
52.5°	609.8	591.4	573.1	560.9	555.1	549.3	543.4	537.5
55°	536.0	519.4	503.0	491.9	486.2	480.5	474.7	469.0
57.5°	463.5	447.8	432.3	422.0	417.2	412.4	407.5	402.7
60°	417.8	402.4	387.0	376.9	372.1	367.2	362.4	357.6
62.5°	372.4	358.0	343.5	333.8	328.6	323.6	318.5	313.5
65°	307.9	293.9	280.0	271.4	268.3	265.1	262.0	258.9
67.5°	246.2	235.8	225.3	218.5	215.2	211.7	208.4	205.0
70°	208.1	198.2	188.3	181.7	178.6	175.5	172.3	169.2
72.5°	173.9	165.8	157.6	152.9	151.6	150.3	149.0	147.7
75°	130.1	127.3	124.4	122.8	122.2	121.6	121.1	120.5
77.5°	98.2	96.6	95.1	94.0	93.4	92.9	92.3	91.7
80°	79.0	78.2	77.3	76.6	76.1	75.5	74.9	74.4
82.5°	60.6	59.8	58.9	58.4	58.3	58.1	58.0	58.0
85°	34.7	34.2	33.6	33.3	33.3	33.3	33.3	33.3
87.5°	19.2	19.2	19.2	19.1	18.9	18.8	18.7	18.6
90°	31.4	32.5	33.6	34.4	35.0	35.5	36.0	36.5
92.5°	34.7	36.4	38.2	39.1	39.5	39.8	40.1	40.4
95°	41.6	43.5	45.3	46.3	46.3	46.3	46.3	46.3
97.5°	43.6	45.7	47.9	49.2	49.4	49.7	50.0	50.2
100°	44.5	46.7	48.9	50.1	50.4	50.6	51.0	51.2
102.5°	66.8	60.1	53.3	50.2	50.7	51.2	51.7	52.2
105°	171.0	123.1	75.2	51.4	52.0	52.6	53.1	53.6
107.5°	418.9	383.8	348.6	313.0	276.9	240.7	204.6	168.4
110°	531.8	522.9	514.0	490.1	451.3	412.6	373.9	335.2



TEST NUMBER: P332488-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	611.5	611.6	611.8	607.8	599.6	591.4	583.3	575.0
115°	705.1	707.8	710.5	712.3	713.5	714.5	715.6	716.7
117.5°	789.8	791.9	794.1	795.3	795.5	795.7	796.0	796.1
120°	845.4	847.5	849.7	850.8	850.8	850.8	850.8	850.8
122.5°	899.6	901.2	902.7	903.5	903.8	903.9	904.2	904.4
125°	976.2	976.7	977.2	977.8	978.4	978.8	979.4	980.0
127.5°	1052.9	1053.8	1054.6	1054.8	1054.3	1053.7	1053.1	1052.6
130°	1099.1	1100.2	1101.3	1101.6	1101.1	1100.5	1099.9	1099.4
132.5°	1143.0	1144.1	1145.2	1145.3	1144.6	1143.9	1143.0	1142.3
135°	1209.5	1210.3	1211.1	1211.1	1210.3	1209.5	1208.7	1207.9
137.5°	1268.8	1270.1	1271.4	1271.7	1271.2	1270.6	1270.1	1269.6
140°	1306.4	1307.4	1308.5	1308.8	1308.2	1307.7	1307.2	1306.6
142.5°	1342.0	1342.9	1343.7	1343.8	1343.0	1342.2	1341.5	1340.8
145°	1391.8	1392.4	1392.9	1393.2	1393.2	1393.2	1393.2	1393.2
147.5°	1436.4	1437.0	1437.5	1437.1	1435.9	1434.7	1433.4	1432.2
150°	1463.7	1464.3	1464.8	1464.7	1463.9	1463.1	1462.2	1461.4
152.5°	1488.0	1489.0	1490.0	1489.8	1488.6	1487.3	1486.0	1484.8
155°	1521.4	1522.7	1524.1	1524.0	1522.3	1520.7	1519.1	1517.5
157.5°	1550.5	1552.1	1553.7	1553.5	1551.4	1549.2	1547.1	1545.0
160°	1567.1	1568.6	1570.3	1570.2	1568.2	1566.4	1564.5	1562.6
162.5°	1582.1	1584.0	1585.8	1585.8	1584.2	1582.5	1580.9	1579.2
165°	1602.2	1604.4	1606.6	1606.7	1604.8	1603.0	1601.0	1599.1
167.5°	1617.9	1620.0	1622.2	1622.2	1620.0	1617.9	1615.7	1613.6
170°	1626.6	1628.8	1631.0	1631.0	1628.8	1626.6	1624.5	1622.3
172.5°	1632.5	1634.7	1636.8	1636.7	1634.3	1632.0	1629.5	1627.2
175°	1639.5	1641.4	1643.3	1643.2	1641.0	1638.8	1636.6	1634.5
177.5°	1642.1	1643.8	1645.6	1645.4	1643.2	1641.0	1638.8	1636.7
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5

(END OF REPORT)