

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332464-840

Luminaire Tested: **S123RDIW-S1000D1320U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332464-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1000D1320U840-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1320 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9163.4 lumens  
Efficiency: N/A  
Efficacy: 131.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332464-840

CATALOG NUMBER: S123RDIW-S1000D1320U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332464-840

CATALOG NUMBER: S123RDIW-S1000D1320U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	42	36
2	88	81	75	70	80	74	69	65	61	57	54	49	47	45	38	37	35	30
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	73	63	55	50	67	58	51	46	48	43	39	39	36	33	31	28	26	23
5	68	56	48	43	61	52	45	40	43	38	34	35	31	29	28	25	23	20
6	62	50	43	37	57	46	40	35	39	34	30	32	28	25	25	23	20	17
7	58	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	21	19	16	14
9	50	38	30	26	45	35	28	24	30	24	21	25	21	18	20	17	15	13
10	46	35	28	23	42	32	26	22	27	22	19	23	19	16	18	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18243	18243	18243
5°	18312	18058	18163
10°	18208	17832	17772
15°	18013	17415	17231
20°	17743	16893	16501
25°	17467	16308	15785
30°	17100	15632	14777
35°	16724	14954	13853
40°	16378	14155	12708
45°	15923	13370	11676
50°	15421	12476	10518
55°	14910	11453	9439
60°	14441	10357	8254
65°	13827	9172	7070
70°	13064	7701	5712
75°	11948	6059	5373
80°	10649	5362	4940
85°	8991	4755	4409



TEST NUMBER: P332464-840

CATALOG NUMBER: S123RDIW-S1000D1320U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.1	1.7
10°-20°	442.8	4.8
20°-30°	637.6	7.0
30°-40°	718.2	7.8
40°-50°	687.1	7.5
50°-60°	562.6	6.1
60°-70°	379.6	4.1
70°-80°	191.0	2.1
80°-90°	55.4	0.6
90°-100°	63.5	0.7
100°-110°	302.9	3.3
110°-120°	727.5	7.9
120°-130°	926.3	10.1
130°-140°	989.8	10.8
140°-150°	925.5	10.1
150°-160°	746.6	8.1
160°-170°	481.8	5.3
170°-180°	166.1	1.8
0°-30°	1239.5	13.5
0°-40°	1957.7	21.4
0°-60°	3207.4	35.0
0°-90°	3833.4	41.8
90°-120°	1093.9	11.9
90°-150°	3935.5	42.9
90°-180°	5330.0	58.2
0°-180°	9163.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1695	1695	1695	1695	1695	
5°	1695	1687	1671	1683	1681	161
15°	1616	1600	1563	1556	1546	455
25°	1471	1435	1373	1345	1329	676
35°	1273	1221	1138	1081	1054	796
45°	1046	982	878	802	767	807
55°	794	724	610	533	503	712
65°	543	466	360	296	278	537
75°	287	221	146	133	129	306
85°	73	44	38	36	36	82
90°	1	14	31	36	39	7
95°	79	30	40	49	49	98
105°	387	394	284	67	57	410
115°	726	734	745	758	764	716
125°	1023	1033	1039	1041	1044	913
135°	1274	1282	1287	1290	1287	980
145°	1470	1479	1482	1484	1484	920
155°	1619	1617	1618	1624	1617	746
165°	1708	1704	1702	1712	1704	482
175°	1748	1742	1743	1751	1741	166
180°	1748	1748	1748	1748	1748	



TEST NUMBER: P332464-840

CATALOG NUMBER: S123RDIW-S1000D1320U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1700.2	1699.2	1698.3	1697.3	1696.3	1694.4	1691.4	1688.5	1685.6	1682.6	1685.3
5°	1694.8	1693.1	1691.6	1690.1	1688.6	1686.0	1682.3	1678.7	1675.1	1671.3	1674.1
7.5°	1679.0	1677.4	1675.8	1674.1	1672.4	1669.2	1664.5	1659.7	1655.0	1650.2	1651.7
10°	1665.9	1663.8	1661.5	1659.4	1657.3	1653.5	1648.0	1642.4	1637.0	1631.5	1631.8
12.5°	1647.2	1644.8	1642.4	1640.0	1637.6	1633.1	1626.4	1619.6	1613.0	1606.2	1606.0
15°	1616.4	1613.1	1609.6	1606.3	1603.0	1597.0	1588.4	1579.8	1571.3	1562.8	1561.3
17.5°	1577.6	1573.7	1569.8	1565.9	1562.0	1554.6	1543.7	1532.9	1522.0	1511.1	1507.8
20°	1549.0	1544.2	1539.2	1534.4	1529.4	1521.3	1509.6	1498.0	1486.4	1474.8	1470.9
22.5°	1517.1	1511.6	1505.9	1500.3	1494.7	1485.7	1473.3	1461.0	1448.7	1436.3	1431.4
25°	1470.7	1463.1	1455.4	1447.7	1440.2	1429.3	1415.2	1401.2	1387.2	1373.1	1366.7
27.5°	1414.3	1405.9	1397.5	1389.1	1380.6	1368.6	1352.9	1337.3	1321.6	1306.1	1297.1
30°	1375.8	1366.7	1357.6	1348.4	1339.2	1326.1	1309.0	1291.8	1274.8	1257.7	1247.3
32.5°	1337.4	1327.0	1316.6	1306.2	1295.9	1281.6	1263.5	1245.5	1227.3	1209.2	1197.9
35°	1272.7	1261.7	1250.7	1239.8	1228.8	1213.8	1194.9	1175.9	1157.0	1138.0	1124.9
37.5°	1207.3	1195.1	1182.9	1170.6	1158.4	1142.3	1122.1	1101.8	1081.6	1061.4	1046.4
40°	1165.6	1152.2	1138.6	1125.2	1111.8	1094.2	1072.6	1050.9	1029.2	1007.4	991.6
42.5°	1118.2	1104.8	1091.4	1077.9	1064.5	1046.6	1024.2	1001.8	979.4	956.9	939.6
45°	1046.0	1032.2	1018.4	1004.7	991.0	972.4	948.9	925.3	901.8	878.3	860.9
47.5°	973.7	958.6	943.5	928.4	913.3	894.0	870.5	847.0	823.4	799.9	781.0
50°	920.9	906.6	892.2	877.9	863.4	843.9	819.2	794.5	769.7	745.0	726.0
52.5°	873.6	858.1	842.4	826.9	811.3	791.2	766.8	742.3	717.8	693.3	673.6
55°	794.5	779.5	764.5	749.5	734.6	714.1	688.1	662.2	636.2	610.3	592.6
57.5°	721.3	705.0	688.7	672.4	656.1	634.9	608.7	582.7	556.6	530.6	513.8
60°	670.8	654.0	637.1	620.4	603.5	582.5	557.1	531.8	506.4	481.1	464.5
62.5°	620.2	603.4	586.5	569.8	553.0	531.9	506.5	481.2	455.9	430.5	415.0
65°	542.9	526.1	509.3	492.5	475.7	455.4	431.6	407.8	384.0	360.1	345.2
67.5°	465.6	448.7	431.7	414.8	397.8	377.8	355.0	332.1	309.3	286.4	275.3
70°	415.1	398.6	382.1	365.6	349.1	330.2	308.8	287.4	266.0	244.7	234.0
72.5°	364.5	348.3	332.0	315.8	299.5	281.7	262.3	242.9	223.4	204.0	195.2
75°	287.3	272.6	257.9	243.3	228.6	212.9	196.1	179.3	162.5	145.7	142.6
77.5°	216.9	203.6	190.4	177.1	163.9	151.8	141.0	130.2	119.4	108.6	106.9
80°	171.8	159.3	146.7	134.2	121.7	112.3	105.8	99.4	93.0	86.5	85.6
82.5°	129.0	118.2	107.3	96.4	85.6	78.8	75.7	72.8	69.8	66.8	65.8
85°	72.8	66.1	59.4	52.7	45.9	42.1	41.2	40.3	39.4	38.5	37.9
87.5°	26.7	24.5	22.4	20.3	18.2	17.6	18.3	19.0	19.8	20.5	20.5
90°	1.3	4.1	7.1	10.0	12.8	16.2	19.9	23.6	27.4	31.2	32.3
92.5°	24.1	23.3	22.5	21.7	20.9	21.9	24.7	27.6	30.4	33.2	35.0
95°	79.2	67.4	55.5	43.7	31.9	27.6	30.7	33.9	37.1	40.3	42.3
97.5°	159.2	153.9	148.6	143.3	137.9	124.9	104.1	83.4	62.6	41.8	44.1
100°	219.4	225.2	231.0	236.7	242.6	222.9	177.9	132.9	87.9	42.8	45.1
102.5°	288.0	292.2	296.3	300.4	304.7	282.2	233.0	183.8	134.6	85.4	78.3
105°	387.0	390.1	393.3	396.5	399.6	388.3	362.2	336.3	310.3	284.4	233.3
107.5°	491.4	493.9	496.4	499.0	501.5	504.8	509.0	513.0	517.2	521.2	483.7
110°	561.0	563.3	565.5	567.8	570.2	572.9	576.1	579.3	582.5	585.6	576.1



TEST NUMBER: P332464-840

CATALOG NUMBER: S123RDIW-S1000D1320U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	627.4	629.5	631.6	633.7	635.7	638.3	641.6	644.7	647.9	651.1	651.3
115°	725.9	727.6	729.3	731.0	732.8	735.0	737.5	740.1	742.8	745.4	748.2
117.5°	821.2	823.3	825.5	827.6	829.7	831.4	832.7	834.1	835.5	836.8	839.1
120°	880.4	883.0	885.6	888.2	890.8	892.5	893.3	894.2	895.1	896.0	898.3
122.5°	940.7	942.8	944.9	947.1	949.2	950.8	951.9	953.0	954.1	955.2	956.8
125°	1023.2	1025.5	1027.8	1030.2	1032.5	1034.2	1035.3	1036.5	1037.6	1038.8	1039.4
127.5°	1103.2	1105.5	1107.8	1110.1	1112.5	1114.3	1115.7	1117.1	1118.4	1119.8	1120.7
130°	1153.1	1155.4	1157.7	1160.0	1162.4	1164.1	1165.2	1166.4	1167.5	1168.6	1169.8
132.5°	1200.8	1203.2	1205.5	1207.8	1210.1	1211.7	1212.6	1213.6	1214.5	1215.4	1216.6
135°	1273.8	1275.6	1277.3	1279.0	1280.8	1282.2	1283.3	1284.5	1285.7	1286.9	1287.7
137.5°	1336.2	1338.4	1340.6	1342.7	1344.9	1346.4	1347.0	1347.7	1348.3	1348.9	1350.3
140°	1377.8	1379.5	1381.2	1382.9	1384.6	1385.9	1386.8	1387.7	1388.6	1389.4	1390.6
142.5°	1416.1	1417.9	1419.7	1421.4	1423.1	1424.4	1425.2	1426.1	1426.9	1427.8	1428.8
145°	1470.0	1472.0	1474.0	1476.0	1478.0	1479.3	1479.9	1480.5	1481.1	1481.6	1482.2
147.5°	1520.6	1521.9	1523.2	1524.5	1525.9	1526.8	1527.4	1527.9	1528.5	1529.1	1529.7
150°	1551.8	1552.6	1553.5	1554.3	1555.2	1555.9	1556.5	1557.0	1557.6	1558.2	1558.8
152.5°	1579.7	1580.1	1580.5	1580.9	1581.3	1581.8	1582.2	1582.5	1582.8	1583.2	1584.2
155°	1619.2	1618.7	1618.1	1617.5	1616.9	1616.8	1617.1	1617.4	1617.7	1617.9	1619.4
157.5°	1649.9	1649.8	1649.8	1649.7	1649.6	1649.5	1649.2	1648.9	1648.6	1648.3	1650.0
160°	1668.6	1668.3	1668.0	1667.7	1667.4	1667.2	1666.9	1666.6	1666.3	1666.0	1667.7
162.5°	1686.3	1685.5	1684.8	1683.9	1683.2	1682.7	1682.4	1682.1	1681.8	1681.5	1683.5
165°	1707.6	1706.7	1705.8	1705.0	1704.0	1703.5	1703.2	1702.9	1702.6	1702.3	1704.7
167.5°	1724.1	1723.0	1721.8	1720.7	1719.5	1719.0	1719.0	1719.0	1719.0	1719.0	1721.3
170°	1733.5	1732.3	1731.2	1730.1	1728.9	1728.3	1728.3	1728.3	1728.3	1728.3	1730.6
172.5°	1739.8	1738.4	1737.0	1735.6	1734.2	1733.6	1733.8	1734.1	1734.3	1734.5	1736.9
175°	1747.8	1746.4	1744.9	1743.4	1742.0	1741.4	1741.7	1742.0	1742.3	1742.6	1744.6
177.5°	1749.9	1748.7	1747.6	1746.5	1745.2	1744.8	1745.0	1745.2	1745.5	1745.8	1747.6
180°	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8



TEST NUMBER: P332464-840

CATALOG NUMBER: S123RDIW-S1000D1320U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1688.0	1690.7	1693.3	1694.5	1693.9	1693.5	1693.0	1692.5
5°	1676.9	1679.6	1682.3	1683.4	1682.8	1682.2	1681.6	1681.0
7.5°	1653.3	1654.8	1656.3	1656.6	1655.5	1654.5	1653.5	1652.3
10°	1632.1	1632.4	1632.7	1632.1	1630.5	1629.0	1627.5	1626.0
12.5°	1605.8	1605.7	1605.5	1604.5	1602.8	1600.9	1599.2	1597.4
15°	1559.7	1558.2	1556.7	1554.8	1552.7	1550.5	1548.4	1546.3
17.5°	1504.6	1501.4	1498.1	1494.9	1491.8	1488.5	1485.4	1482.2
20°	1466.8	1462.9	1459.0	1455.1	1451.5	1447.7	1444.1	1440.5
22.5°	1426.4	1421.5	1416.5	1412.3	1409.0	1405.5	1402.1	1398.7
25°	1360.3	1353.8	1347.5	1342.5	1339.2	1335.8	1332.5	1329.1
27.5°	1288.2	1279.3	1270.3	1263.3	1258.2	1253.0	1247.9	1242.8
30°	1236.9	1226.5	1216.1	1208.5	1203.6	1198.7	1193.8	1188.9
32.5°	1186.5	1175.2	1163.8	1155.6	1150.4	1145.3	1140.1	1135.0
35°	1111.8	1098.6	1085.5	1076.2	1070.8	1065.2	1059.8	1054.2
37.5°	1031.6	1016.6	1001.8	990.9	984.1	977.3	970.6	963.8
40°	975.7	959.9	943.9	932.5	925.4	918.5	911.4	904.4
42.5°	922.2	904.8	887.5	875.7	869.4	863.1	856.8	850.5
45°	843.4	826.1	808.6	796.3	788.9	781.6	774.3	767.0
47.5°	762.0	743.2	724.2	711.4	704.9	698.4	691.9	685.3
50°	707.1	688.1	669.2	656.2	649.2	642.2	635.2	628.1
52.5°	654.0	634.3	614.6	601.6	595.3	589.1	582.8	576.4
55°	574.8	557.1	539.4	527.5	521.4	515.2	509.2	503.0
57.5°	497.1	480.3	463.6	452.6	447.5	442.2	437.1	431.8
60°	448.1	431.6	415.1	404.2	399.1	393.8	388.7	383.4
62.5°	399.4	384.0	368.4	357.9	352.5	347.1	341.6	336.2
65°	330.2	315.2	300.2	291.0	287.7	284.4	281.0	277.6
67.5°	264.1	252.9	241.8	234.3	230.8	227.1	223.5	219.9
70°	223.3	212.6	201.9	194.9	191.5	188.1	184.8	181.5
72.5°	186.5	177.7	169.1	164.0	162.6	161.2	159.8	158.3
75°	139.6	136.5	133.5	131.7	131.1	130.4	129.8	129.2
77.5°	105.3	103.6	102.0	100.9	100.3	99.7	99.1	98.5
80°	84.7	83.8	82.9	82.2	81.6	81.0	80.3	79.7
82.5°	64.9	64.0	63.1	62.6	62.5	62.4	62.2	62.1
85°	37.3	36.7	36.1	35.7	35.7	35.7	35.7	35.7
87.5°	20.5	20.5	20.5	20.4	20.3	20.1	20.0	19.9
90°	33.4	34.6	35.7	36.7	37.3	37.8	38.4	39.0
92.5°	37.0	38.8	40.6	41.7	42.1	42.4	42.7	43.1
95°	44.3	46.4	48.4	49.4	49.4	49.4	49.4	49.4
97.5°	46.5	48.8	51.0	52.3	52.6	52.9	53.2	53.5
100°	47.5	49.8	52.1	53.4	53.6	53.9	54.2	54.5
102.5°	71.1	63.9	56.9	53.5	54.0	54.5	55.0	55.5
105°	182.2	131.2	80.1	54.8	55.4	55.9	56.6	57.2
107.5°	446.4	408.9	371.4	333.5	295.0	256.4	217.9	179.5
110°	566.5	557.0	547.5	522.1	480.9	439.6	398.4	357.1





TEST NUMBER: P332464-840

CATALOG NUMBER: S123RDIW-S1000D1320U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	651.5	651.6	651.8	647.5	638.7	630.1	621.4	612.7
115°	751.1	754.0	756.9	758.9	760.0	761.2	762.3	763.6
117.5°	841.4	843.6	846.0	847.3	847.5	847.7	848.0	848.2
120°	900.6	902.9	905.2	906.4	906.4	906.4	906.4	906.4
122.5°	958.5	960.1	961.7	962.6	962.8	963.0	963.3	963.5
125°	1040.0	1040.6	1041.1	1041.7	1042.3	1042.9	1043.4	1044.0
127.5°	1121.7	1122.6	1123.6	1123.7	1123.2	1122.6	1122.0	1121.4
130°	1170.9	1172.2	1173.3	1173.6	1173.0	1172.5	1171.8	1171.2
132.5°	1217.7	1218.9	1220.0	1220.2	1219.4	1218.6	1217.8	1217.0
135°	1288.6	1289.4	1290.3	1290.3	1289.4	1288.6	1287.7	1286.9
137.5°	1351.7	1353.0	1354.4	1354.8	1354.2	1353.7	1353.1	1352.5
140°	1391.7	1392.9	1394.0	1394.3	1393.7	1393.1	1392.6	1392.0
142.5°	1429.7	1430.6	1431.6	1431.6	1430.8	1430.0	1429.2	1428.4
145°	1482.8	1483.3	1483.9	1484.2	1484.2	1484.2	1484.2	1484.2
147.5°	1530.2	1530.9	1531.5	1531.1	1529.7	1528.4	1527.1	1525.7
150°	1559.3	1559.9	1560.5	1560.3	1559.5	1558.6	1557.8	1556.9
152.5°	1585.2	1586.3	1587.3	1587.2	1585.8	1584.5	1583.2	1581.9
155°	1620.8	1622.2	1623.8	1623.6	1621.8	1620.1	1618.4	1616.7
157.5°	1651.8	1653.6	1655.3	1655.0	1652.7	1650.5	1648.2	1646.0
160°	1669.4	1671.2	1672.9	1672.7	1670.7	1668.7	1666.7	1664.7
162.5°	1685.5	1687.5	1689.4	1689.5	1687.7	1686.0	1684.2	1682.3
165°	1707.0	1709.3	1711.6	1711.7	1709.7	1707.7	1705.7	1703.6
167.5°	1723.6	1725.9	1728.2	1728.2	1725.9	1723.6	1721.3	1719.0
170°	1732.9	1735.3	1737.6	1737.6	1735.3	1732.9	1730.6	1728.3
172.5°	1739.2	1741.5	1743.8	1743.6	1741.1	1738.6	1736.1	1733.5
175°	1746.7	1748.7	1750.7	1750.5	1748.3	1746.0	1743.6	1741.3
177.5°	1749.4	1751.3	1753.1	1752.9	1750.6	1748.3	1746.0	1743.6
180°	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8

(END OF REPORT)