

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332469-840

Luminaire Tested: **S123RDIW-S1000D1535U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332469-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D1535U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9205.3 lumens
Efficiency: N/A
Efficacy: 120.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332469-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332469-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	88	81	75	70	80	74	69	64	61	57	54	49	47	45	38	37	35	30
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	73	63	55	50	67	58	51	46	48	43	39	39	36	33	31	28	26	22
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	28	25	23	20
6	62	50	43	37	57	46	40	34	39	34	30	32	28	25	25	23	20	17
7	57	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	21	18	16	14
9	50	38	30	26	45	35	28	24	30	24	21	24	21	18	20	17	15	13
10	46	35	28	23	42	32	26	22	27	22	19	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18243	18243	18243
5°	18312	18058	18163
10°	18208	17832	17772
15°	18013	17415	17231
20°	17743	16893	16501
25°	17467	16308	15785
30°	17100	15632	14777
35°	16724	14954	13853
40°	16378	14155	12708
45°	15923	13370	11676
50°	15421	12476	10518
55°	14910	11453	9439
60°	14441	10357	8254
65°	13827	9172	7070
70°	13064	7701	5712
75°	11948	6059	5373
80°	10649	5362	4940
85°	8991	4755	4409



TEST NUMBER: P332469-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.1	1.7
10°-20°	442.8	4.8
20°-30°	637.6	6.9
30°-40°	718.2	7.8
40°-50°	687.1	7.5
50°-60°	562.6	6.1
60°-70°	379.6	4.1
70°-80°	191.0	2.1
80°-90°	56.2	0.6
90°-100°	126.3	1.4
100°-110°	378.0	4.1
110°-120°	642.9	7.0
120°-130°	845.6	9.2
130°-140°	950.5	10.3
140°-150°	934.3	10.1
150°-160°	786.5	8.5
160°-170°	523.6	5.7
170°-180°	183.3	2.0
0°-30°	1239.5	13.5
0°-40°	1957.7	21.3
0°-60°	3207.4	34.8
0°-90°	3834.3	41.7
90°-120°	1147.2	12.5
90°-150°	3877.6	42.1
90°-180°	5371.0	58.3
0°-180°	9205.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1695	1695	1695	1695	1695	
5°	1695	1687	1671	1683	1681	161
15°	1616	1600	1563	1556	1546	455
25°	1471	1435	1373	1345	1329	676
35°	1273	1221	1138	1081	1054	796
45°	1046	982	878	802	767	807
55°	794	724	610	533	503	712
65°	543	466	360	296	278	537
75°	287	221	146	133	129	306
85°	73	44	38	36	36	82
90°	2	17	37	42	46	9
95°	90	101	113	118	119	101
105°	343	346	359	360	362	367
115°	647	651	649	650	649	640
125°	947	951	949	943	936	844
135°	1229	1238	1237	1231	1227	947
145°	1491	1494	1498	1497	1491	931
155°	1707	1707	1709	1714	1704	785
165°	1859	1855	1855	1863	1853	524
175°	1934	1928	1928	1936	1926	184
180°	1938	1938	1938	1938	1938	



TEST NUMBER: P332469-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1700.2	1699.2	1698.3	1697.3	1696.3	1694.4	1691.4	1688.5	1685.6	1682.6	1685.3
5°	1694.8	1693.1	1691.6	1690.1	1688.6	1686.0	1682.3	1678.7	1675.1	1671.3	1674.1
7.5°	1679.0	1677.4	1675.8	1674.1	1672.4	1669.2	1664.5	1659.7	1655.0	1650.2	1651.7
10°	1665.9	1663.8	1661.5	1659.4	1657.3	1653.5	1648.0	1642.4	1637.0	1631.5	1631.8
12.5°	1647.2	1644.8	1642.4	1640.0	1637.6	1633.1	1626.4	1619.6	1613.0	1606.2	1606.0
15°	1616.4	1613.1	1609.6	1606.3	1603.0	1597.0	1588.4	1579.8	1571.3	1562.8	1561.3
17.5°	1577.6	1573.7	1569.8	1565.9	1562.0	1554.6	1543.7	1532.9	1522.0	1511.1	1507.8
20°	1549.0	1544.2	1539.2	1534.4	1529.4	1521.3	1509.6	1498.0	1486.4	1474.8	1470.9
22.5°	1517.1	1511.6	1505.9	1500.3	1494.7	1485.7	1473.3	1461.0	1448.7	1436.3	1431.4
25°	1470.7	1463.1	1455.4	1447.7	1440.2	1429.3	1415.2	1401.2	1387.2	1373.1	1366.7
27.5°	1414.3	1405.9	1397.5	1389.1	1380.6	1368.6	1352.9	1337.3	1321.6	1306.1	1297.1
30°	1375.8	1366.7	1357.6	1348.4	1339.2	1326.1	1309.0	1291.8	1274.8	1257.7	1247.3
32.5°	1337.4	1327.0	1316.6	1306.2	1295.9	1281.6	1263.5	1245.5	1227.3	1209.2	1197.9
35°	1272.7	1261.7	1250.7	1239.8	1228.8	1213.8	1194.9	1175.9	1157.0	1138.0	1124.9
37.5°	1207.3	1195.1	1182.9	1170.6	1158.4	1142.3	1122.1	1101.8	1081.6	1061.4	1046.4
40°	1165.6	1152.2	1138.6	1125.2	1111.8	1094.2	1072.6	1050.9	1029.2	1007.4	991.6
42.5°	1118.2	1104.8	1091.4	1077.9	1064.5	1046.6	1024.2	1001.8	979.4	956.9	939.6
45°	1046.0	1032.2	1018.4	1004.7	991.0	972.4	948.9	925.3	901.8	878.3	860.9
47.5°	973.7	958.6	943.5	928.4	913.3	894.0	870.5	847.0	823.4	799.9	781.0
50°	920.9	906.6	892.2	877.9	863.4	843.9	819.2	794.5	769.7	745.0	726.0
52.5°	873.6	858.1	842.4	826.9	811.3	791.2	766.8	742.3	717.8	693.3	673.6
55°	794.5	779.5	764.5	749.5	734.6	714.1	688.1	662.2	636.2	610.3	592.6
57.5°	721.3	705.0	688.7	672.4	656.1	634.9	608.7	582.7	556.6	530.6	513.8
60°	670.8	654.0	637.1	620.4	603.5	582.5	557.1	531.8	506.4	481.1	464.5
62.5°	620.2	603.4	586.5	569.8	553.0	531.9	506.5	481.2	455.9	430.5	415.0
65°	542.9	526.1	509.3	492.5	475.7	455.4	431.6	407.8	384.0	360.1	345.2
67.5°	465.6	448.7	431.7	414.8	397.8	377.8	355.0	332.1	309.3	286.4	275.3
70°	415.1	398.6	382.1	365.6	349.1	330.2	308.8	287.4	266.0	244.7	234.0
72.5°	364.5	348.3	332.0	315.8	299.5	281.7	262.3	242.9	223.4	204.0	195.2
75°	287.3	272.6	257.9	243.3	228.6	212.9	196.1	179.3	162.5	145.7	142.6
77.5°	216.9	203.6	190.4	177.1	163.9	151.8	141.0	130.2	119.4	108.6	106.9
80°	171.8	159.3	146.7	134.2	121.7	112.3	105.8	99.4	93.0	86.5	85.6
82.5°	129.0	118.2	107.3	96.4	85.6	78.8	75.7	72.8	69.8	66.8	65.8
85°	72.8	66.1	59.4	52.7	45.9	42.1	41.2	40.3	39.4	38.5	37.9
87.5°	26.7	24.6	22.7	20.7	18.7	18.1	19.0	19.9	20.7	21.6	21.6
90°	1.5	4.9	8.3	11.7	15.0	19.0	23.3	27.8	32.1	36.6	37.9
92.5°	36.9	39.2	41.4	43.7	46.0	48.5	51.0	53.4	55.9	58.5	59.6
95°	89.9	92.2	94.6	96.9	99.4	101.9	104.5	107.2	110.0	112.7	114.0
97.5°	159.6	161.4	163.1	164.9	166.6	168.4	170.5	172.4	174.4	176.3	177.9
100°	207.1	209.1	211.2	213.2	215.2	217.1	218.7	220.5	222.2	223.9	224.9
102.5°	262.0	263.2	264.4	265.6	266.8	268.5	270.7	273.0	275.2	277.4	278.5
105°	342.6	343.4	344.0	344.7	345.4	347.2	350.2	353.3	356.4	359.4	359.4
107.5°	436.5	436.9	437.3	437.7	438.1	438.9	440.1	441.3	442.5	443.7	444.8
110°	494.9	495.6	496.2	497.0	497.7	498.3	499.0	499.7	500.3	501.0	502.4



TEST NUMBER: P332469-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	555.8	556.2	556.6	557.0	557.4	557.7	557.8	558.0	558.2	558.3	559.9
115°	647.2	648.2	649.2	650.3	651.3	651.5	650.8	650.1	649.4	648.7	649.0
117.5°	739.2	739.8	740.5	741.2	741.8	741.7	740.9	740.0	739.1	738.3	738.2
120°	796.5	798.5	800.5	802.5	804.6	804.8	803.0	801.3	799.6	798.0	797.6
122.5°	856.2	857.6	859.1	860.6	862.1	862.4	861.5	860.6	859.8	858.9	858.0
125°	947.2	948.2	949.3	950.3	951.3	951.4	950.8	950.1	949.4	948.8	947.4
127.5°	1031.3	1033.4	1035.6	1037.7	1040.0	1040.7	1039.9	1039.2	1038.4	1037.6	1035.7
130°	1087.3	1090.0	1092.7	1095.4	1098.1	1098.9	1097.9	1096.9	1095.9	1094.9	1093.6
132.5°	1143.4	1146.0	1148.7	1151.4	1154.2	1155.2	1154.4	1153.7	1152.9	1152.2	1150.5
135°	1228.9	1230.9	1232.9	1235.0	1237.1	1237.9	1237.6	1237.2	1236.9	1236.6	1235.2
137.5°	1308.1	1309.8	1311.5	1313.2	1314.8	1316.2	1317.1	1317.9	1318.8	1319.7	1318.3
140°	1362.9	1364.6	1366.3	1368.0	1369.7	1370.7	1371.1	1371.4	1371.7	1372.1	1371.7
142.5°	1412.9	1414.5	1416.2	1418.0	1419.7	1420.8	1421.4	1422.0	1422.6	1423.2	1422.9
145°	1490.9	1491.6	1492.2	1492.9	1493.6	1494.4	1495.4	1496.4	1497.4	1498.4	1498.1
147.5°	1559.0	1560.2	1561.5	1562.8	1564.0	1565.0	1566.0	1566.9	1567.8	1568.8	1568.8
150°	1606.6	1607.3	1607.9	1608.6	1609.3	1609.9	1610.6	1611.3	1611.9	1612.7	1612.7
152.5°	1645.6	1646.5	1647.5	1648.4	1649.3	1650.0	1650.4	1650.8	1651.2	1651.6	1652.2
155°	1707.1	1707.1	1707.1	1707.1	1707.1	1707.3	1707.6	1707.9	1708.3	1708.6	1710.0
157.5°	1759.5	1759.1	1758.7	1758.3	1757.9	1757.8	1758.1	1758.3	1758.6	1758.9	1760.3
160°	1792.4	1791.7	1791.0	1790.3	1789.7	1789.3	1789.3	1789.3	1789.3	1789.3	1791.0
162.5°	1821.6	1820.7	1819.7	1818.8	1817.9	1817.5	1817.8	1818.1	1818.3	1818.6	1820.3
165°	1859.4	1858.4	1857.3	1856.3	1855.3	1854.8	1854.8	1854.8	1854.8	1854.8	1856.8
167.5°	1889.6	1888.1	1886.8	1885.4	1884.1	1883.6	1883.8	1884.1	1884.4	1884.6	1886.7
170°	1906.5	1905.2	1903.9	1902.5	1901.2	1900.5	1900.5	1900.5	1900.5	1900.5	1902.9
172.5°	1920.0	1918.6	1917.2	1915.9	1914.6	1913.9	1913.9	1913.9	1913.9	1913.9	1916.0
175°	1934.0	1932.7	1931.3	1930.0	1928.5	1927.9	1927.9	1927.9	1927.9	1927.9	1930.0
177.5°	1939.7	1938.7	1937.6	1936.5	1935.4	1934.9	1934.9	1934.9	1934.9	1934.9	1936.5
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332469-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8	1694.8
2.5°	1688.0	1690.7	1693.3	1694.5	1693.9	1693.5	1693.0	1692.5
5°	1676.9	1679.6	1682.3	1683.4	1682.8	1682.2	1681.6	1681.0
7.5°	1653.3	1654.8	1656.3	1656.6	1655.5	1654.5	1653.5	1652.3
10°	1632.1	1632.4	1632.7	1632.1	1630.5	1629.0	1627.5	1626.0
12.5°	1605.8	1605.7	1605.5	1604.5	1602.8	1600.9	1599.2	1597.4
15°	1559.7	1558.2	1556.7	1554.8	1552.7	1550.5	1548.4	1546.3
17.5°	1504.6	1501.4	1498.1	1494.9	1491.8	1488.5	1485.4	1482.2
20°	1466.8	1462.9	1459.0	1455.1	1451.5	1447.7	1444.1	1440.5
22.5°	1426.4	1421.5	1416.5	1412.3	1409.0	1405.5	1402.1	1398.7
25°	1360.3	1353.8	1347.5	1342.5	1339.2	1335.8	1332.5	1329.1
27.5°	1288.2	1279.3	1270.3	1263.3	1258.2	1253.0	1247.9	1242.8
30°	1236.9	1226.5	1216.1	1208.5	1203.6	1198.7	1193.8	1188.9
32.5°	1186.5	1175.2	1163.8	1155.6	1150.4	1145.3	1140.1	1135.0
35°	1111.8	1098.6	1085.5	1076.2	1070.8	1065.2	1059.8	1054.2
37.5°	1031.6	1016.6	1001.8	990.9	984.1	977.3	970.6	963.8
40°	975.7	959.9	943.9	932.5	925.4	918.5	911.4	904.4
42.5°	922.2	904.8	887.5	875.7	869.4	863.1	856.8	850.5
45°	843.4	826.1	808.6	796.3	788.9	781.6	774.3	767.0
47.5°	762.0	743.2	724.2	711.4	704.9	698.4	691.9	685.3
50°	707.1	688.1	669.2	656.2	649.2	642.2	635.2	628.1
52.5°	654.0	634.3	614.6	601.6	595.3	589.1	582.8	576.4
55°	574.8	557.1	539.4	527.5	521.4	515.2	509.2	503.0
57.5°	497.1	480.3	463.6	452.6	447.5	442.2	437.1	431.8
60°	448.1	431.6	415.1	404.2	399.1	393.8	388.7	383.4
62.5°	399.4	384.0	368.4	357.9	352.5	347.1	341.6	336.2
65°	330.2	315.2	300.2	291.0	287.7	284.4	281.0	277.6
67.5°	264.1	252.9	241.8	234.3	230.8	227.1	223.5	219.9
70°	223.3	212.6	201.9	194.9	191.5	188.1	184.8	181.5
72.5°	186.5	177.7	169.1	164.0	162.6	161.2	159.8	158.3
75°	139.6	136.5	133.5	131.7	131.1	130.4	129.8	129.2
77.5°	105.3	103.6	102.0	100.9	100.3	99.7	99.1	98.5
80°	84.7	83.8	82.9	82.2	81.6	81.0	80.3	79.7
82.5°	64.9	64.0	63.1	62.6	62.5	62.4	62.2	62.1
85°	37.3	36.7	36.1	35.7	35.7	35.7	35.7	35.7
87.5°	21.6	21.7	21.7	21.7	21.5	21.4	21.3	21.2
90°	39.3	40.6	42.0	43.0	43.6	44.3	45.0	45.6
92.5°	60.6	61.7	62.8	63.1	62.7	62.3	61.9	61.5
95°	115.4	116.7	118.1	118.8	118.8	118.8	118.8	118.8
97.5°	179.5	181.0	182.6	183.3	183.2	183.0	182.9	182.8
100°	225.9	226.9	227.9	228.7	229.4	230.1	230.8	231.5
102.5°	279.5	280.5	281.6	282.0	281.9	281.7	281.6	281.4
105°	359.4	359.4	359.4	359.7	360.4	361.1	361.7	362.4
107.5°	446.0	447.0	448.1	448.4	448.0	447.6	447.2	446.8
110°	503.7	505.0	506.4	506.8	506.0	505.4	504.7	504.0



TEST NUMBER: P332469-840

CATALOG NUMBER: S123RDIW-S1000D1535U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	561.5	563.1	564.7	565.5	565.4	565.2	565.1	564.9
115°	649.4	649.7	650.1	650.1	649.7	649.4	649.0	648.7
117.5°	738.1	738.1	738.0	737.5	736.5	735.6	734.7	733.7
120°	797.3	797.0	796.6	796.1	795.5	794.8	794.1	793.3
122.5°	857.1	856.3	855.4	854.4	853.5	852.5	851.6	850.6
125°	946.0	944.6	943.3	941.9	940.6	939.3	937.9	936.5
127.5°	1033.9	1032.0	1030.1	1028.3	1026.8	1025.2	1023.7	1022.1
130°	1092.2	1090.9	1089.5	1087.6	1085.3	1082.9	1080.6	1078.1
132.5°	1148.9	1147.3	1145.7	1144.0	1142.2	1140.3	1138.4	1136.6
135°	1233.9	1232.4	1231.1	1230.1	1229.4	1228.7	1228.1	1227.4
137.5°	1316.9	1315.5	1314.0	1312.6	1311.3	1310.1	1308.8	1307.5
140°	1371.4	1371.1	1370.7	1369.4	1367.0	1364.6	1362.2	1359.9
142.5°	1422.6	1422.2	1421.9	1420.8	1419.0	1417.1	1415.3	1413.5
145°	1497.7	1497.4	1497.1	1496.2	1494.9	1493.6	1492.2	1490.9
147.5°	1568.8	1568.8	1568.8	1567.8	1565.8	1563.8	1561.7	1559.6
150°	1612.7	1612.7	1612.7	1611.6	1609.6	1607.6	1605.6	1603.6
152.5°	1652.7	1653.3	1653.9	1653.3	1651.4	1649.7	1647.9	1646.2
155°	1711.3	1712.6	1714.0	1713.5	1711.1	1708.8	1706.4	1704.0
157.5°	1761.7	1763.1	1764.5	1764.3	1762.4	1760.5	1758.6	1756.8
160°	1792.7	1794.4	1796.0	1796.2	1794.9	1793.5	1792.2	1790.8
162.5°	1821.9	1823.6	1825.3	1825.1	1822.9	1820.8	1818.6	1816.4
165°	1858.9	1860.9	1862.9	1862.8	1860.4	1858.1	1855.6	1853.3
167.5°	1888.9	1891.0	1893.0	1893.0	1891.0	1888.9	1886.7	1884.6
170°	1905.2	1907.6	1910.0	1910.0	1907.6	1905.2	1902.9	1900.5
172.5°	1918.0	1920.2	1922.3	1922.2	1919.8	1917.4	1915.0	1912.7
175°	1932.0	1934.0	1936.0	1935.8	1933.5	1931.1	1928.7	1926.4
177.5°	1938.1	1939.7	1941.4	1941.3	1939.3	1937.4	1935.6	1933.7
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5

(END OF REPORT)