

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332408-930

Luminaire Tested: **S123RDIW-S340D1535U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332408-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S340D1535U930-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1535 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6065.8 lumens  
Efficiency: N/A  
Efficacy: 113.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332408-930

CATALOG NUMBER: S123RDIW-S340D1535U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332408-930

CATALOG NUMBER: S123RDIW-S340D1535U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	99	99	99	99	88	88	88	88	65	65	65	45	45	45	26	26	26	18
1	91	87	83	80	80	76	73	71	57	55	53	40	38	37	23	23	22	15
2	83	76	70	65	72	67	62	58	50	47	44	35	33	31	21	20	19	13
3	75	66	60	54	66	59	53	48	44	40	37	31	29	27	18	17	16	11
4	69	59	51	46	60	52	46	41	39	35	32	27	25	23	16	15	14	9
5	63	52	45	39	55	46	40	35	35	31	27	25	22	20	15	13	12	8
6	58	47	39	34	51	41	35	30	31	27	24	22	19	17	13	12	11	7
7	53	42	34	29	47	37	31	26	28	24	21	20	17	15	12	11	10	6
8	49	38	31	26	43	34	27	23	26	21	18	18	15	13	11	10	9	6
9	46	34	27	23	40	31	25	20	23	19	16	17	14	12	10	9	8	5
10	43	31	25	20	38	28	22	18	21	17	14	15	13	11	10	8	7	5

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5042	5042	5042
5°	5061	4991	5020
10°	5032	4928	4912
15°	4979	4813	4763
20°	4904	4669	4560
25°	4828	4507	4363
30°	4727	4320	4084
35°	4623	4133	3829
40°	4526	3912	3513
45°	4401	3694	3227
50°	4262	3448	2907
55°	4121	3166	2609
60°	3991	2863	2282
65°	3823	2534	1954
70°	3610	2127	1577
75°	3302	1676	1485
80°	2944	1488	1364
85°	2482	1309	1223



TEST NUMBER: P332408-930

CATALOG NUMBER: S123RDIW-S340D1535U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.0	0.7
10°-20°	122.4	2.0
20°-30°	176.2	2.9
30°-40°	198.5	3.3
40°-50°	189.9	3.1
50°-60°	155.5	2.6
60°-70°	104.9	1.7
70°-80°	52.8	0.9
80°-90°	18.6	0.3
90°-100°	59.6	1.0
100°-110°	284.3	4.7
110°-120°	682.8	11.3
120°-130°	869.5	14.3
130°-140°	929.1	15.3
140°-150°	868.8	14.3
150°-160°	700.8	11.6
160°-170°	452.3	7.5
170°-180°	155.9	2.6
0°-30°	342.6	5.6
0°-40°	541.1	8.9
0°-60°	886.5	14.6
0°-90°	1062.8	17.5
90°-120°	1026.8	16.9
90°-150°	3694.1	60.9
90°-180°	5003.0	82.5
0°-180°	6065.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	465	465	44
15°	447	442	432	430	427	126
25°	406	396	380	372	367	187
35°	352	338	314	299	291	220
45°	289	271	243	222	212	223
55°	220	200	169	147	139	197
65°	150	129	100	82	77	148
75°	79	61	40	37	36	85
85°	20	12	11	10	10	23
90°	1	14	29	34	36	4
95°	74	28	38	46	46	92
105°	363	370	267	63	54	385
115°	681	689	700	711	717	672
125°	960	970	975	978	980	857
135°	1196	1203	1208	1211	1208	920
145°	1380	1388	1391	1393	1393	863
155°	1520	1518	1519	1524	1518	700
165°	1603	1599	1598	1607	1599	453
175°	1640	1635	1636	1643	1634	156
180°	1640	1640	1640	1640	1640	



TEST NUMBER: P332408-930

CATALOG NUMBER: S123RDIW-S340D1535U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	469.9	469.6	469.4	469.1	468.9	468.3	467.5	466.7	465.9	465.0	465.8
5°	468.4	468.0	467.6	467.2	466.7	466.0	465.0	464.0	462.9	461.9	462.7
7.5°	464.1	463.6	463.2	462.7	462.3	461.4	460.1	458.8	457.4	456.1	456.5
10°	460.4	459.8	459.3	458.7	458.0	457.0	455.5	454.0	452.4	450.9	451.0
12.5°	455.3	454.6	454.0	453.3	452.7	451.3	449.5	447.7	445.8	443.9	443.8
15°	446.8	445.8	444.9	443.9	443.0	441.4	439.0	436.7	434.3	431.9	431.5
17.5°	436.0	435.0	433.9	432.8	431.7	429.7	426.6	423.6	420.7	417.7	416.8
20°	428.1	426.8	425.4	424.1	422.7	420.4	417.3	414.0	410.8	407.6	406.5
22.5°	419.3	417.8	416.2	414.7	413.1	410.7	407.2	403.8	400.4	397.0	395.6
25°	406.5	404.4	402.3	400.1	398.0	395.0	391.2	387.3	383.4	379.5	377.7
27.5°	390.9	388.6	386.2	383.9	381.6	378.3	374.0	369.6	365.3	360.9	358.5
30°	380.3	377.7	375.2	372.7	370.1	366.5	361.7	357.0	352.3	347.6	344.7
32.5°	369.7	366.7	363.9	361.0	358.2	354.2	349.2	344.2	339.2	334.2	331.1
35°	351.8	348.7	345.7	342.7	339.7	335.5	330.3	325.0	319.8	314.5	311.0
37.5°	333.7	330.3	326.9	323.6	320.2	315.7	310.1	304.5	299.0	293.3	289.3
40°	322.1	318.5	314.7	311.0	307.3	302.4	296.4	290.4	284.5	278.4	274.1
42.5°	309.1	305.3	301.7	297.9	294.2	289.3	283.1	276.9	270.7	264.5	259.7
45°	289.1	285.3	281.5	277.7	273.9	268.7	262.3	255.8	249.2	242.7	237.9
47.5°	269.1	265.0	260.7	256.6	252.4	247.1	240.6	234.1	227.6	221.1	215.9
50°	254.5	250.5	246.6	242.6	238.6	233.3	226.4	219.6	212.7	205.9	200.6
52.5°	241.5	237.2	232.8	228.5	224.2	218.7	211.9	205.1	198.4	191.6	186.2
55°	219.6	215.4	211.3	207.2	203.0	197.4	190.2	183.0	175.9	168.7	163.8
57.5°	199.3	194.9	190.4	185.8	181.3	175.5	168.3	161.0	153.8	146.7	142.0
60°	185.4	180.8	176.1	171.5	166.8	161.0	154.0	147.0	140.0	133.0	128.4
62.5°	171.4	166.7	162.1	157.5	152.9	147.0	140.0	133.0	126.0	119.0	114.7
65°	150.1	145.4	140.8	136.2	131.5	125.9	119.3	112.7	106.2	99.5	95.4
67.5°	128.7	124.0	119.3	114.6	109.9	104.4	98.1	91.8	85.4	79.2	76.1
70°	114.7	110.1	105.6	101.0	96.5	91.2	85.4	79.4	73.5	67.6	64.7
72.5°	100.8	96.3	91.8	87.2	82.8	77.9	72.5	67.1	61.7	56.3	54.0
75°	79.4	75.3	71.3	67.3	63.2	58.9	54.2	49.6	44.9	40.3	39.5
77.5°	59.9	56.3	52.6	48.9	45.3	42.0	39.0	36.0	33.0	30.0	29.6
80°	47.5	44.0	40.6	37.1	33.7	31.1	29.3	27.5	25.7	24.0	23.6
82.5°	35.6	32.6	29.7	26.7	23.6	21.8	21.0	20.1	19.3	18.4	18.2
85°	20.1	18.3	16.4	14.6	12.7	11.7	11.4	11.2	10.9	10.6	10.4
87.5°	7.5	7.3	7.2	6.9	6.8	7.0	7.7	8.4	9.1	9.8	9.9
90°	1.2	3.9	6.6	9.4	12.1	15.2	18.7	22.2	25.8	29.3	30.3
92.5°	22.7	21.9	21.1	20.4	19.6	20.5	23.2	25.9	28.5	31.2	32.9
95°	74.4	63.3	52.2	41.0	29.9	25.8	28.9	31.8	34.8	37.7	39.7
97.5°	149.4	144.5	139.5	134.4	129.5	117.2	97.8	78.3	58.8	39.2	41.4
100°	206.0	211.4	216.8	222.3	227.6	209.2	167.0	124.7	82.5	40.2	42.4
102.5°	270.4	274.3	278.2	282.0	285.9	264.8	218.7	172.5	126.4	80.2	73.5
105°	363.2	366.2	369.2	372.2	375.1	364.4	340.1	315.7	291.3	266.9	219.0
107.5°	461.2	463.6	465.9	468.4	470.8	473.9	477.7	481.6	485.4	489.3	454.1
110°	526.5	528.7	530.8	533.0	535.2	537.8	540.8	543.7	546.7	549.7	540.8



TEST NUMBER: P332408-930

CATALOG NUMBER: S123RDIW-S340D1535U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	589.0	590.9	592.9	594.8	596.7	599.2	602.2	605.2	608.1	611.1	611.3
115°	681.3	683.0	684.6	686.2	687.9	689.9	692.4	694.7	697.2	699.6	702.3
117.5°	770.8	772.8	774.8	776.8	778.9	780.5	781.7	782.9	784.2	785.5	787.6
120°	826.4	828.8	831.3	833.7	836.2	837.8	838.5	839.4	840.2	841.0	843.2
122.5°	883.0	884.9	887.0	888.9	891.0	892.5	893.5	894.5	895.5	896.6	898.1
125°	960.4	962.6	964.8	966.9	969.1	970.8	971.8	972.9	974.0	975.1	975.7
127.5°	1035.5	1037.7	1039.9	1042.0	1044.2	1045.9	1047.3	1048.6	1049.9	1051.2	1052.0
130°	1082.3	1084.5	1086.7	1088.8	1091.0	1092.7	1093.7	1094.8	1095.9	1097.0	1098.0
132.5°	1127.2	1129.4	1131.6	1133.7	1135.9	1137.4	1138.2	1139.1	1140.0	1140.8	1141.9
135°	1195.7	1197.3	1199.0	1200.6	1202.2	1203.5	1204.6	1205.7	1206.8	1207.9	1208.7
137.5°	1254.2	1256.3	1258.3	1260.4	1262.4	1263.8	1264.4	1264.9	1265.6	1266.2	1267.5
140°	1293.2	1294.9	1296.5	1298.1	1299.8	1300.9	1301.7	1302.5	1303.3	1304.2	1305.3
142.5°	1329.3	1330.9	1332.5	1334.2	1335.8	1337.0	1337.8	1338.6	1339.5	1340.3	1341.1
145°	1379.7	1381.6	1383.6	1385.4	1387.3	1388.5	1389.1	1389.6	1390.2	1390.7	1391.2
147.5°	1427.3	1428.6	1429.8	1431.0	1432.2	1433.1	1433.7	1434.3	1434.8	1435.3	1435.9
150°	1456.5	1457.3	1458.2	1459.0	1459.8	1460.4	1461.0	1461.6	1462.1	1462.6	1463.1
152.5°	1482.9	1483.3	1483.6	1484.0	1484.4	1484.7	1485.1	1485.4	1485.7	1486.0	1487.0
155°	1519.9	1519.4	1518.8	1518.3	1517.8	1517.6	1517.9	1518.2	1518.4	1518.7	1520.0
157.5°	1548.7	1548.7	1548.6	1548.5	1548.5	1548.3	1548.0	1547.8	1547.5	1547.2	1548.8
160°	1566.3	1565.9	1565.7	1565.5	1565.1	1564.9	1564.6	1564.3	1564.1	1563.8	1565.5
162.5°	1582.8	1582.1	1581.4	1580.7	1580.0	1579.5	1579.2	1579.0	1578.7	1578.4	1580.3
165°	1602.8	1602.0	1601.2	1600.4	1599.5	1599.0	1598.7	1598.5	1598.2	1597.9	1600.1
167.5°	1618.4	1617.3	1616.2	1615.2	1614.0	1613.6	1613.6	1613.6	1613.6	1613.6	1615.7
170°	1627.2	1626.1	1625.0	1623.9	1622.9	1622.3	1622.3	1622.3	1622.3	1622.3	1624.5
172.5°	1633.0	1631.7	1630.4	1629.1	1627.8	1627.3	1627.5	1627.7	1627.9	1628.2	1630.4
175°	1640.5	1639.2	1637.9	1636.6	1635.2	1634.6	1634.9	1635.2	1635.4	1635.7	1637.6
177.5°	1642.5	1641.4	1640.4	1639.3	1638.2	1637.8	1638.0	1638.2	1638.4	1638.7	1640.4
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332408-930

CATALOG NUMBER: S123RDIW-S340D1535U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	466.5	467.2	468.1	468.3	468.2	468.1	467.9	467.8
5°	463.5	464.2	465.0	465.3	465.1	465.0	464.8	464.6
7.5°	457.0	457.4	457.8	457.9	457.5	457.3	457.0	456.7
10°	451.1	451.2	451.3	451.1	450.7	450.3	449.8	449.4
12.5°	443.8	443.8	443.8	443.4	443.0	442.5	442.0	441.5
15°	431.0	430.6	430.2	429.7	429.2	428.5	428.0	427.4
17.5°	415.9	415.0	414.1	413.2	412.3	411.4	410.6	409.7
20°	405.4	404.3	403.2	402.2	401.1	400.1	399.2	398.1
22.5°	394.3	392.9	391.5	390.4	389.4	388.5	387.5	386.6
25°	375.9	374.2	372.4	371.0	370.1	369.2	368.3	367.4
27.5°	356.0	353.6	351.1	349.2	347.7	346.3	345.0	343.5
30°	341.9	339.0	336.1	334.0	332.6	331.3	330.0	328.6
32.5°	327.9	324.8	321.6	319.4	318.0	316.6	315.1	313.7
35°	307.3	303.6	300.0	297.4	296.0	294.4	292.9	291.4
37.5°	285.1	281.0	276.9	273.9	272.0	270.1	268.2	266.4
40°	269.7	265.3	260.9	257.7	255.8	253.9	251.9	250.0
42.5°	254.9	250.1	245.3	242.1	240.3	238.6	236.8	235.1
45°	233.1	228.3	223.5	220.0	218.1	216.1	214.0	212.0
47.5°	210.6	205.4	200.2	196.7	194.9	193.1	191.2	189.4
50°	195.4	190.2	185.0	181.4	179.4	177.5	175.5	173.6
52.5°	180.8	175.3	169.9	166.3	164.5	162.8	161.1	159.3
55°	158.9	154.0	149.1	145.8	144.1	142.4	140.7	139.0
57.5°	137.4	132.7	128.2	125.1	123.7	122.2	120.8	119.4
60°	123.8	119.3	114.7	111.7	110.3	108.8	107.5	106.0
62.5°	110.4	106.2	101.8	98.9	97.4	96.0	94.4	92.9
65°	91.2	87.2	83.0	80.5	79.5	78.6	77.7	76.7
67.5°	73.0	69.9	66.8	64.7	63.8	62.8	61.8	60.8
70°	61.7	58.8	55.8	53.9	52.9	52.0	51.0	50.1
72.5°	51.5	49.2	46.7	45.3	44.9	44.5	44.2	43.8
75°	38.6	37.7	36.9	36.4	36.2	36.0	35.9	35.7
77.5°	29.1	28.6	28.2	27.9	27.7	27.6	27.4	27.2
80°	23.4	23.2	22.9	22.7	22.5	22.3	22.2	22.0
82.5°	17.9	17.7	17.4	17.3	17.3	17.2	17.2	17.2
85°	10.3	10.1	9.9	9.9	9.9	9.9	9.9	9.9
87.5°	10.1	10.3	10.4	10.5	10.5	10.6	10.6	10.7
90°	31.4	32.5	33.6	34.4	35.0	35.5	36.0	36.5
92.5°	34.7	36.4	38.2	39.1	39.5	39.8	40.1	40.4
95°	41.6	43.5	45.3	46.3	46.3	46.3	46.3	46.3
97.5°	43.6	45.7	47.9	49.2	49.4	49.7	50.0	50.2
100°	44.5	46.7	48.9	50.1	50.4	50.6	51.0	51.2
102.5°	66.8	60.1	53.3	50.2	50.7	51.2	51.7	52.2
105°	171.0	123.1	75.2	51.4	52.0	52.6	53.1	53.6
107.5°	418.9	383.8	348.6	313.0	276.9	240.7	204.6	168.4
110°	531.8	522.9	514.0	490.1	451.3	412.6	373.9	335.2





TEST NUMBER: P332408-930

CATALOG NUMBER: S123RDIW-S340D1535U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	611.5	611.6	611.8	607.8	599.6	591.4	583.3	575.0
115°	705.1	707.8	710.5	712.3	713.5	714.5	715.6	716.7
117.5°	789.8	791.9	794.1	795.3	795.5	795.7	796.0	796.1
120°	845.4	847.5	849.7	850.8	850.8	850.8	850.8	850.8
122.5°	899.6	901.2	902.7	903.5	903.8	903.9	904.2	904.4
125°	976.2	976.7	977.2	977.8	978.4	978.8	979.4	980.0
127.5°	1052.9	1053.8	1054.6	1054.8	1054.3	1053.7	1053.1	1052.6
130°	1099.1	1100.2	1101.3	1101.6	1101.1	1100.5	1099.9	1099.4
132.5°	1143.0	1144.1	1145.2	1145.3	1144.6	1143.9	1143.0	1142.3
135°	1209.5	1210.3	1211.1	1211.1	1210.3	1209.5	1208.7	1207.9
137.5°	1268.8	1270.1	1271.4	1271.7	1271.2	1270.6	1270.1	1269.6
140°	1306.4	1307.4	1308.5	1308.8	1308.2	1307.7	1307.2	1306.6
142.5°	1342.0	1342.9	1343.7	1343.8	1343.0	1342.2	1341.5	1340.8
145°	1391.8	1392.4	1392.9	1393.2	1393.2	1393.2	1393.2	1393.2
147.5°	1436.4	1437.0	1437.5	1437.1	1435.9	1434.7	1433.4	1432.2
150°	1463.7	1464.3	1464.8	1464.7	1463.9	1463.1	1462.2	1461.4
152.5°	1488.0	1489.0	1490.0	1489.8	1488.6	1487.3	1486.0	1484.8
155°	1521.4	1522.7	1524.1	1524.0	1522.3	1520.7	1519.1	1517.5
157.5°	1550.5	1552.1	1553.7	1553.5	1551.4	1549.2	1547.1	1545.0
160°	1567.1	1568.6	1570.3	1570.2	1568.2	1566.4	1564.5	1562.6
162.5°	1582.1	1584.0	1585.8	1585.8	1584.2	1582.5	1580.9	1579.2
165°	1602.2	1604.4	1606.6	1606.7	1604.8	1603.0	1601.0	1599.1
167.5°	1617.9	1620.0	1622.2	1622.2	1620.0	1617.9	1615.7	1613.6
170°	1626.6	1628.8	1631.0	1631.0	1628.8	1626.6	1624.5	1622.3
172.5°	1632.5	1634.7	1636.8	1636.7	1634.3	1632.0	1629.5	1627.2
175°	1639.5	1641.4	1643.3	1643.2	1641.0	1638.8	1636.6	1634.5
177.5°	1642.1	1643.8	1645.6	1645.4	1643.2	1641.0	1638.8	1636.7
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5

(END OF REPORT)