

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332455-840

Luminaire Tested: **S123RDIW-S1000D755U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332455-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D755U840-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6643.7 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332455-840

CATALOG NUMBER: S123RDIW-S1000D755U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332455-840

CATALOG NUMBER: S123RDIW-S1000D755U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	101	97	93	90	94	91	87	84	79	77	75	69	67	65	59	58	57	52
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	45
3	85	76	68	63	79	71	65	60	63	58	54	55	51	48	47	45	42	39
4	78	67	60	54	73	63	57	51	56	51	46	49	45	42	43	40	37	34
5	72	60	52	47	67	57	50	45	51	45	41	45	40	37	39	35	33	30
6	66	55	47	41	62	52	44	39	46	40	36	40	36	32	36	32	29	26
7	62	49	42	36	58	47	40	35	42	36	32	37	32	29	33	29	26	24
8	57	45	37	32	54	43	36	31	38	33	28	34	29	26	30	26	24	21
9	53	41	34	29	50	39	32	28	35	30	26	31	27	24	28	24	21	19
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17280	17280	17280	17280
5°	20599	17354	15282	17354
10°	25719	17254	13806	17254
15°	30190	17079	12590	17079
20°	33693	16814	11557	16814
25°	33155	16537	10922	16537
30°	23832	16281	10268	16281
35°	15912	15948	9843	15948
40°	11724	15548	9405	15548
45°	9834	14845	8977	14845
50°	8678	13924	8378	13924
55°	7610	12872	7557	12872
60°	6777	11866	6923	11866
65°	5952	10781	6441	10781
70°	4674	9819	5882	9819
75°	4117	8576	5373	8576
80°	3583	7283	5281	7283
85°	2878	5866	5595	5866



TEST NUMBER: P332455-840

CATALOG NUMBER: S123RDIW-S1000D755U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.9	2.4
10°-20°	493.2	7.4
20°-30°	774.9	11.7
30°-40°	808.4	12.2
40°-50°	691.8	10.4
50°-60°	527.3	7.9
60°-70°	338.0	5.1
70°-80°	162.6	2.4
80°-90°	45.8	0.7
90°-100°	62.2	0.9
100°-110°	186.1	2.8
110°-120°	316.4	4.8
120°-130°	416.2	6.3
130°-140°	467.8	7.0
140°-150°	459.9	6.9
150°-160°	387.1	5.8
160°-170°	257.7	3.9
170°-180°	90.2	1.4
0°-30°	1426.0	21.5
0°-40°	2234.4	33.6
0°-60°	3453.6	52.0
0°-90°	4000.0	60.2
90°-120°	564.7	8.5
90°-150°	1908.6	28.7
90°-180°	2644.0	39.8
0°-180°	6643.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1605	1605	1605	1605	1605	
5°	1906	1606	1414	1606	1906	197
15°	2709	1533	1130	1533	2709	768
25°	2792	1392	920	1392	2792	1200
35°	1211	1214	749	1214	1211	794
45°	646	975	590	975	646	508
55°	406	686	403	686	406	367
65°	234	423	253	423	234	230
75°	99	206	129	206	99	106
85°	23	48	45	48	23	27
90°	22	1	22	1	22	12
95°	58	44	58	44	58	60
105°	178	169	178	169	178	189
115°	319	319	319	319	319	316
125°	461	466	461	466	461	412
135°	604	605	604	605	604	464
145°	734	734	734	734	734	458
155°	839	840	839	840	839	386
165°	912	915	912	915	912	257
175°	948	952	948	952	948	90
180°	954	954	954	954	954	



TEST NUMBER: P332455-840

CATALOG NUMBER: S123RDIW-S1000D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1709.9	1712.0	1705.0	1703.8	1695.6	1693.3	1693.3	1681.8	1674.7	1665.4	1659.8
5°	1906.4	1917.4	1911.9	1899.6	1879.0	1874.1	1861.1	1840.5	1817.1	1788.2	1774.4
7.5°	2151.9	2166.9	2161.1	2142.0	2120.4	2102.9	2066.2	2031.9	1984.0	1941.9	1905.9
10°	2353.1	2337.3	2324.9	2306.4	2286.4	2254.1	2215.6	2162.7	2101.6	2053.5	1999.9
12.5°	2503.8	2501.1	2485.5	2466.4	2438.2	2407.5	2360.3	2295.8	2224.7	2155.3	2093.9
15°	2709.2	2713.2	2702.9	2683.0	2643.1	2588.9	2517.4	2490.6	2388.8	2313.3	2237.7
17.5°	2851.3	2850.4	2849.0	2821.5	2780.8	2742.1	2675.8	2605.4	2513.3	2406.7	2304.9
20°	2941.4	2934.6	2935.9	2905.0	2874.8	2830.0	2765.5	2663.1	2587.5	2464.5	2359.3
22.5°	2939.2	2937.8	2943.0	2932.4	2910.5	2876.3	2825.4	2739.0	2642.4	2518.3	2400.0
25°	2791.6	2786.1	2818.4	2827.3	2862.4	2868.5	2853.5	2806.0	2714.6	2586.8	2440.4
27.5°	2336.3	2333.3	2393.3	2468.3	2563.4	2637.4	2708.9	2743.4	2714.6	2623.1	2476.4
30°	1917.4	1982.1	2012.3	2120.8	2241.8	2386.1	2512.5	2632.8	2662.4	2622.5	2502.2
32.5°	1592.0	1648.3	1673.5	1766.8	1879.5	2048.5	2238.3	2408.5	2528.8	2559.3	2486.9
35°	1210.9	1211.6	1269.3	1310.6	1415.0	1588.9	1773.1	2001.2	2228.1	2399.8	2417.7
37.5°	966.2	969.7	1004.6	1045.7	1124.1	1216.0	1378.2	1567.9	1829.9	2093.7	2248.3
40°	834.4	840.5	866.7	907.2	963.5	1032.9	1159.4	1338.1	1556.6	1850.1	2089.9
42.5°	749.6	759.7	773.2	804.4	839.3	904.2	1006.5	1144.6	1343.3	1620.8	1897.5
45°	646.0	651.5	661.9	676.2	707.8	753.3	821.9	914.7	1079.6	1303.0	1579.9
47.5°	569.9	566.9	577.8	589.6	610.6	641.5	687.5	763.3	880.9	1060.2	1295.1
50°	518.2	517.5	525.0	534.0	553.9	576.6	614.4	671.5	764.9	913.3	1128.4
52.5°	469.8	472.4	477.8	488.9	503.3	521.6	555.5	596.6	676.9	805.1	984.4
55°	405.5	407.6	415.1	421.3	431.6	450.1	471.4	505.8	560.8	650.2	797.9
57.5°	351.0	350.1	357.4	358.9	370.5	385.7	402.1	428.9	468.7	535.1	634.6
60°	314.8	312.7	318.9	323.7	329.9	342.2	356.0	382.1	413.7	462.5	547.8
62.5°	281.8	280.8	285.4	290.1	295.3	306.5	318.1	338.1	363.1	404.2	471.9
65°	233.7	235.7	237.8	239.8	242.6	249.4	260.4	274.2	291.3	320.2	369.0
67.5°	183.6	185.7	186.4	190.7	196.5	200.9	207.5	219.7	231.8	256.1	283.9
70°	148.5	147.7	148.5	150.5	158.0	165.6	174.6	183.5	191.1	208.2	231.6
72.5°	127.5	126.3	128.2	128.6	132.2	134.3	140.0	148.3	158.0	169.8	186.5
75°	99.0	99.0	99.0	99.0	101.7	103.1	105.1	107.2	110.7	116.1	128.6
77.5°	73.1	73.2	74.2	74.9	75.4	76.2	77.6	79.6	80.8	83.7	89.1
80°	57.8	58.4	57.8	58.4	58.4	59.8	60.5	62.5	63.2	66.7	68.8
82.5°	43.4	43.0	43.4	44.1	44.1	45.5	45.6	47.2	47.3	49.1	51.1
85°	23.3	22.0	23.3	22.7	24.0	22.7	23.3	24.7	24.7	25.4	28.2
87.5°	10.0	11.0	9.9	10.3	10.3	10.7	10.6	10.5	11.4	10.7	10.9
90°	22.5	22.1	21.8	21.5	21.1	20.7	20.0	19.3	18.7	18.0	15.9
92.5°	30.3	30.5	30.7	30.9	31.1	30.9	30.4	29.9	29.3	28.8	27.6
95°	58.5	58.5	58.5	58.5	58.5	58.2	57.5	56.8	56.1	55.4	54.1
97.5°	90.0	90.0	90.1	90.2	90.2	89.9	89.1	88.4	87.6	86.8	85.8
100°	113.9	113.6	113.3	112.9	112.6	112.2	111.7	111.2	110.7	110.2	109.4
102.5°	138.6	138.6	138.7	138.8	138.8	138.6	138.0	137.5	137.0	136.5	135.4
105°	178.4	178.0	177.7	177.4	177.0	176.9	176.9	176.9	176.9	176.9	175.4
107.5°	219.9	220.2	220.4	220.6	220.8	220.6	220.0	219.4	218.9	218.4	217.8
110°	248.1	248.4	248.7	249.1	249.4	249.2	248.6	247.9	247.3	246.6	246.3



TEST NUMBER: P332455-840

CATALOG NUMBER: S123RDIW-S1000D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	278.1	278.1	278.2	278.3	278.3	278.0	277.2	276.4	275.6	274.8	274.7
115°	319.3	319.5	319.6	319.8	320.0	320.0	319.8	319.6	319.5	319.3	319.6
117.5°	361.1	361.6	362.0	362.5	363.0	363.2	363.2	363.3	363.3	363.3	363.9
120°	390.5	390.8	391.2	391.5	391.8	392.1	392.2	392.4	392.6	392.7	393.6
122.5°	418.7	419.2	419.6	420.1	420.6	421.0	421.4	421.9	422.3	422.7	423.2
125°	461.0	461.6	462.3	463.0	463.6	464.3	464.9	465.6	466.4	467.0	467.3
127.5°	503.1	503.9	504.6	505.4	506.1	507.1	508.0	508.9	509.8	510.8	511.1
130°	530.7	531.9	533.0	534.2	535.3	536.2	536.9	537.7	538.3	539.0	539.5
132.5°	559.5	560.4	561.3	562.2	563.1	563.9	564.7	565.5	566.3	567.1	567.4
135°	604.1	604.5	604.8	605.1	605.5	606.0	606.6	607.3	607.9	608.6	608.8
137.5°	643.6	644.2	644.8	645.5	646.1	646.8	647.4	648.1	648.8	649.5	649.1
140°	669.3	670.6	671.7	672.9	674.0	674.7	674.9	675.0	675.2	675.4	675.2
142.5°	695.7	696.6	697.5	698.4	699.3	699.8	700.0	700.2	700.3	700.5	700.2
145°	733.9	734.5	735.2	735.8	736.5	736.9	737.1	737.2	737.4	737.6	737.1
147.5°	767.7	768.7	769.7	770.7	771.7	772.2	772.2	772.2	772.2	772.2	771.7
150°	789.3	790.3	791.3	792.2	793.2	793.8	793.8	793.8	793.8	793.8	793.5
152.5°	810.3	811.1	812.0	812.8	813.7	814.1	813.7	813.5	813.2	812.9	812.7
155°	838.8	839.9	841.1	842.2	843.4	843.6	843.0	842.3	841.7	841.0	840.8
157.5°	864.6	865.7	866.6	867.5	868.4	868.6	867.9	867.2	866.5	865.8	865.7
160°	881.5	882.1	882.8	883.5	884.1	884.0	883.2	882.4	881.6	880.7	880.7
162.5°	894.0	895.1	896.3	897.3	898.4	898.5	897.7	896.8	896.0	895.1	895.0
165°	912.2	913.4	914.5	915.7	916.9	917.0	915.9	914.9	913.9	912.9	912.9
167.5°	927.7	928.7	929.7	930.8	931.8	931.8	930.8	929.7	928.7	927.7	927.6
170°	935.4	936.6	937.8	939.0	940.1	940.1	939.0	937.8	936.6	935.4	935.4
172.5°	941.5	942.6	943.8	944.9	946.1	946.1	945.1	944.1	943.1	942.0	942.0
175°	948.2	949.4	950.5	951.7	952.9	952.9	951.9	951.0	950.0	949.0	949.0
177.5°	951.8	952.7	953.6	954.6	955.5	955.6	954.8	954.0	953.2	952.4	952.4
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2



TEST NUMBER: P332455-840

CATALOG NUMBER: S123RDIW-S1000D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1657.6	1656.0	1648.3	1639.5	1627.9	1620.2	1614.2	1610.9	1601.0	1588.9	1580.6
5°	1760.0	1739.4	1717.5	1690.6	1665.9	1640.4	1624.7	1606.1	1583.4	1558.0	1540.1
7.5°	1869.8	1829.3	1785.7	1740.8	1696.4	1656.6	1621.3	1591.2	1555.1	1518.6	1493.1
10°	1953.9	1894.7	1833.6	1771.0	1713.9	1660.4	1619.1	1578.6	1535.3	1493.4	1461.8
12.5°	2030.2	1952.5	1882.0	1805.1	1732.1	1668.1	1608.7	1561.0	1508.9	1464.2	1428.3
15°	2127.0	2047.3	1962.1	1845.2	1748.4	1667.3	1595.1	1532.6	1469.4	1414.3	1379.3
17.5°	2217.5	2097.5	1983.0	1885.5	1759.6	1658.3	1570.2	1495.4	1426.0	1367.8	1324.6
20°	2254.8	2138.7	2014.3	1890.0	1766.3	1652.8	1550.4	1467.9	1395.8	1329.8	1290.0
22.5°	2277.3	2145.9	2014.9	1881.2	1749.7	1631.9	1530.7	1440.0	1361.7	1299.0	1249.8
25°	2303.6	2147.0	2002.7	1870.7	1736.7	1608.8	1488.5	1392.4	1307.9	1241.1	1188.9
27.5°	2321.0	2136.7	1966.1	1819.4	1683.4	1556.2	1445.9	1343.9	1258.2	1187.7	1131.7
30°	2324.3	2128.4	1938.0	1779.3	1641.1	1524.3	1407.4	1309.9	1219.2	1144.3	1092.1
32.5°	2328.6	2108.1	1900.1	1731.4	1590.0	1474.3	1368.5	1275.3	1182.3	1108.5	1055.2
35°	2310.6	2096.8	1842.5	1648.7	1507.1	1395.1	1299.6	1213.7	1122.3	1050.8	996.5
37.5°	2232.4	2052.1	1782.8	1555.5	1407.4	1303.7	1225.9	1151.0	1067.1	990.1	938.9
40°	2153.8	2008.1	1736.7	1498.8	1344.2	1237.7	1167.6	1106.5	1025.4	953.2	898.3
42.5°	2036.7	1948.2	1692.7	1439.5	1272.7	1170.1	1111.0	1053.7	982.5	909.2	857.6
45°	1821.9	1833.6	1602.7	1344.9	1173.8	1070.8	1015.0	975.2	912.0	851.5	798.6
47.5°	1552.5	1661.7	1496.9	1244.2	1069.4	972.7	924.0	889.3	846.7	787.3	739.0
50°	1376.5	1532.6	1412.3	1176.6	1004.1	907.9	859.7	831.5	794.5	747.7	701.7
52.5°	1214.4	1381.9	1310.0	1101.3	933.1	845.2	798.2	775.0	745.5	701.6	659.8
55°	990.3	1160.0	1143.6	987.5	826.8	747.7	712.0	685.9	665.9	633.0	600.0
57.5°	801.0	962.0	970.5	861.1	733.1	654.9	624.2	604.5	591.5	566.5	536.0
60°	681.8	829.5	858.4	775.9	665.9	597.2	566.9	551.2	540.9	520.9	497.6
62.5°	582.8	708.5	741.2	681.9	601.6	537.2	513.6	498.4	491.4	474.2	453.6
65°	446.1	550.5	582.1	549.1	507.2	455.7	436.4	423.3	417.2	407.6	392.4
67.5°	335.4	411.5	446.2	422.9	407.8	375.3	363.0	356.0	350.5	343.9	331.2
70°	269.4	325.8	361.5	355.3	343.0	325.8	316.8	312.0	306.5	301.0	290.0
72.5°	216.6	255.4	288.9	292.1	282.0	278.5	270.6	268.6	265.3	258.7	252.7
75°	143.6	170.5	193.8	202.8	206.8	210.3	206.8	206.2	205.5	200.0	196.5
77.5°	94.1	108.6	123.3	138.6	145.0	149.7	150.8	153.3	151.5	148.6	146.9
80°	72.2	75.6	85.9	99.0	109.3	113.4	116.1	117.5	116.8	116.1	113.4
82.5°	52.4	55.2	60.1	69.3	78.0	84.8	86.4	86.1	87.7	88.1	85.9
85°	28.2	28.9	30.2	31.6	36.5	44.0	46.0	47.5	48.8	48.8	44.6
87.5°	11.5	10.5	11.2	10.8	12.1	12.3	15.3	17.8	18.6	16.8	17.1
90°	13.6	11.5	9.3	7.4	5.8	4.0	2.4	0.7	2.4	4.0	5.8
92.5°	26.4	25.0	23.8	22.6	21.5	20.4	19.3	18.2	19.3	20.4	21.5
95°	52.8	51.5	50.1	48.9	47.8	46.6	45.3	44.2	45.3	46.6	47.8
97.5°	84.8	83.9	82.9	82.0	81.2	80.3	79.4	78.6	79.4	80.3	81.2
100°	108.6	107.7	106.8	105.9	104.9	103.9	102.9	101.9	102.9	103.9	104.9
102.5°	134.4	133.3	132.2	131.3	130.7	130.2	129.6	129.0	129.6	130.2	130.7
105°	173.9	172.4	170.9	170.0	169.7	169.4	169.0	168.6	169.0	169.4	169.7
107.5°	217.2	216.6	216.0	215.6	215.4	215.2	215.0	214.8	215.0	215.2	215.4
110°	245.9	245.6	245.3	244.9	244.6	244.3	244.0	243.6	244.0	244.3	244.6



TEST NUMBER: P332455-840

CATALOG NUMBER: S123RDIW-S1000D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	274.7	274.6	274.5	274.4	274.2	274.0	273.8	273.6	273.8	274.0	274.2
115°	320.0	320.3	320.6	320.5	320.0	319.5	319.0	318.6	319.0	319.5	320.0
117.5°	364.3	364.7	365.2	365.2	364.9	364.5	364.2	363.9	364.2	364.5	364.9
120°	394.5	395.3	396.1	396.1	395.1	394.0	393.0	392.0	393.0	394.0	395.1
122.5°	423.6	424.0	424.4	424.3	423.6	422.8	422.1	421.4	422.1	422.8	423.6
125°	467.7	468.0	468.3	468.3	467.8	467.3	466.8	466.3	466.8	467.3	467.8
127.5°	511.5	511.9	512.2	511.9	510.8	509.8	508.7	507.6	508.7	509.8	510.8
130°	540.0	540.5	541.0	540.5	539.2	537.9	536.5	535.2	536.5	537.9	539.2
132.5°	567.8	568.3	568.6	568.2	566.7	565.4	564.1	562.8	564.1	565.4	566.7
135°	608.9	609.2	609.4	608.8	607.9	606.9	605.9	604.9	605.9	606.9	607.9
137.5°	648.7	648.2	647.8	647.2	646.4	645.5	644.7	643.9	644.7	645.5	646.4
140°	675.0	674.9	674.7	674.2	673.4	672.6	671.7	670.9	671.7	672.6	673.4
142.5°	699.9	699.6	699.3	698.7	697.9	697.1	696.3	695.5	696.3	697.1	697.9
145°	736.6	736.1	735.6	735.2	734.8	734.5	734.2	733.9	734.2	734.5	734.8
147.5°	771.2	770.8	770.3	769.8	769.2	768.6	768.0	767.4	768.0	768.6	769.2
150°	793.1	792.7	792.4	792.1	791.8	791.4	791.1	790.8	791.1	791.4	791.8
152.5°	812.5	812.3	812.1	811.8	811.4	810.9	810.4	810.0	810.4	810.9	811.4
155°	840.7	840.5	840.3	840.3	840.3	840.3	840.3	840.3	840.3	840.3	840.3
157.5°	865.5	865.4	865.3	865.3	865.5	865.7	865.9	866.1	865.9	865.7	865.5
160°	880.7	880.7	880.7	880.9	881.2	881.6	881.9	882.2	881.9	881.6	881.2
162.5°	894.8	894.7	894.6	894.7	895.2	895.6	896.2	896.7	896.2	895.6	895.2
165°	912.9	912.9	912.9	913.2	913.7	914.2	914.7	915.2	914.7	914.2	913.7
167.5°	927.4	927.3	927.2	927.4	928.1	928.8	929.4	930.1	929.4	928.8	928.1
170°	935.4	935.4	935.4	935.7	936.4	937.2	937.8	938.5	937.8	937.2	936.4
172.5°	942.0	942.0	942.0	942.4	943.0	943.7	944.4	945.0	944.4	943.7	943.0
175°	949.0	949.0	949.0	949.3	950.0	950.6	951.3	951.9	951.3	950.6	950.0
177.5°	952.4	952.4	952.4	952.7	953.2	953.7	954.2	954.8	954.2	953.7	953.2
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2



TEST NUMBER: P332455-840

CATALOG NUMBER: S123RDIW-S1000D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1577.9	1570.7	1565.8	1554.8	1547.7	1539.9	1532.3	1537.2	1536.7	1536.1	1536.1
5°	1525.0	1509.1	1494.8	1476.2	1464.5	1450.1	1439.1	1437.7	1440.5	1430.9	1425.3
7.5°	1472.5	1450.9	1430.5	1410.0	1388.3	1370.9	1360.1	1354.9	1348.0	1342.0	1335.8
10°	1435.6	1410.3	1390.3	1364.8	1341.5	1320.9	1307.9	1298.9	1294.0	1289.3	1280.3
12.5°	1397.8	1372.8	1347.5	1318.7	1296.5	1272.5	1262.7	1252.7	1243.5	1238.1	1225.9
15°	1342.2	1309.9	1283.1	1252.8	1228.1	1204.8	1191.0	1171.0	1168.3	1161.4	1149.1
17.5°	1286.6	1251.4	1214.5	1192.1	1164.2	1139.8	1118.9	1112.3	1092.6	1085.2	1074.4
20°	1242.5	1210.2	1182.0	1152.6	1112.0	1089.2	1072.8	1063.9	1048.0	1038.4	1031.6
22.5°	1204.6	1171.7	1139.2	1104.7	1071.3	1045.8	1033.8	1019.9	1011.2	997.7	990.3
25°	1150.4	1114.7	1075.5	1038.4	1014.4	995.1	975.9	963.5	951.2	944.9	931.2
27.5°	1087.5	1050.2	1013.5	985.3	955.8	936.9	919.4	908.4	893.5	883.1	875.6
30°	1052.9	1008.9	977.2	951.8	914.0	896.2	883.1	869.4	858.4	847.4	839.8
32.5°	1012.7	972.6	942.6	911.2	882.1	862.6	845.8	833.6	824.3	813.9	806.3
35°	949.8	916.1	885.1	853.5	832.2	812.3	792.4	782.0	773.2	763.6	756.7
37.5°	892.8	861.4	832.0	802.0	775.6	759.4	743.4	735.5	723.4	716.9	709.9
40°	857.7	826.8	795.2	766.3	738.8	726.4	712.0	700.3	689.3	684.5	676.9
42.5°	819.2	788.3	761.6	730.5	708.0	691.3	677.9	665.1	656.9	649.8	645.6
45°	762.1	734.7	708.5	677.6	656.3	641.9	626.7	615.1	607.5	602.7	595.1
47.5°	706.8	679.2	652.8	625.8	605.2	588.7	573.6	565.4	555.4	549.6	544.4
50°	666.6	641.9	613.7	589.0	568.4	551.9	539.5	529.2	520.3	512.7	509.3
52.5°	629.8	603.4	579.1	556.0	534.2	515.5	504.3	493.4	486.8	478.1	474.0
55°	569.1	543.6	523.0	500.3	479.0	463.2	449.5	439.8	432.9	423.3	417.9
57.5°	512.0	489.2	464.5	444.9	422.9	409.6	398.2	385.2	376.8	369.2	363.9
60°	473.5	447.4	426.1	407.6	388.3	371.1	360.8	350.5	341.5	334.0	329.2
62.5°	433.3	410.6	390.3	370.1	352.5	337.6	325.6	317.0	309.1	304.3	299.5
65°	371.8	354.0	333.4	316.8	300.3	289.3	279.7	272.2	266.6	263.2	259.1
67.5°	315.2	297.8	279.8	263.7	252.7	244.3	237.9	231.5	228.7	224.3	221.6
70°	278.3	260.4	244.7	232.3	221.3	215.1	211.0	206.2	203.4	197.9	195.2
72.5°	238.2	225.3	213.9	203.7	194.9	189.2	184.0	178.1	173.7	167.6	164.9
75°	187.6	175.9	167.0	160.2	154.6	147.0	139.5	133.3	131.3	129.2	128.6
77.5°	139.0	131.6	125.1	119.3	112.4	106.9	105.3	103.9	103.5	102.4	102.4
80°	109.3	102.4	97.6	90.7	86.5	86.5	86.5	85.2	85.9	85.9	85.9
82.5°	81.2	74.9	72.3	69.8	69.0	69.6	69.6	69.8	69.4	70.5	70.0
85°	41.9	42.6	44.0	43.3	44.0	44.0	45.3	44.6	45.3	44.0	45.3
87.5°	16.9	18.9	19.9	20.9	21.8	21.7	22.4	22.5	23.2	23.3	23.4
90°	7.4	9.3	11.5	13.6	15.9	18.0	18.7	19.3	20.0	20.7	21.1
92.5°	22.6	23.8	25.0	26.4	27.6	28.8	29.3	29.9	30.4	30.9	31.1
95°	48.9	50.1	51.5	52.8	54.1	55.4	56.1	56.8	57.5	58.2	58.5
97.5°	82.0	82.9	83.9	84.8	85.8	86.8	87.6	88.4	89.1	89.9	90.2
100°	105.9	106.8	107.7	108.6	109.4	110.2	110.7	111.2	111.7	112.2	112.6
102.5°	131.3	132.2	133.3	134.4	135.4	136.5	137.0	137.5	138.0	138.6	138.8
105°	170.0	170.9	172.4	173.9	175.4	176.9	176.9	176.9	176.9	176.9	177.0
107.5°	215.6	216.0	216.6	217.2	217.8	218.4	218.9	219.4	220.0	220.6	220.8
110°	244.9	245.3	245.6	245.9	246.3	246.6	247.3	247.9	248.6	249.2	249.4



TEST NUMBER: P332455-840

CATALOG NUMBER: S123RDIW-S1000D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	274.4	274.5	274.6	274.7	274.7	274.8	275.6	276.4	277.2	278.0	278.3
115°	320.5	320.6	320.3	320.0	319.6	319.3	319.5	319.6	319.8	320.0	320.0
117.5°	365.2	365.2	364.7	364.3	363.9	363.3	363.3	363.3	363.2	363.2	363.0
120°	396.1	396.1	395.3	394.5	393.6	392.7	392.6	392.4	392.2	392.1	391.8
122.5°	424.3	424.4	424.0	423.6	423.2	422.7	422.3	421.9	421.4	421.0	420.6
125°	468.3	468.3	468.0	467.7	467.3	467.0	466.4	465.6	464.9	464.3	463.6
127.5°	511.9	512.2	511.9	511.5	511.1	510.8	509.8	508.9	508.0	507.1	506.1
130°	540.5	541.0	540.5	540.0	539.5	539.0	538.3	537.7	536.9	536.2	535.3
132.5°	568.2	568.6	568.3	567.8	567.4	567.1	566.3	565.5	564.7	563.9	563.1
135°	608.8	609.4	609.2	608.9	608.8	608.6	607.9	607.3	606.6	606.0	605.5
137.5°	647.2	647.8	648.2	648.7	649.1	649.5	648.8	648.1	647.4	646.8	646.1
140°	674.2	674.7	674.9	675.0	675.2	675.4	675.2	675.0	674.9	674.7	674.0
142.5°	698.7	699.3	699.6	699.9	700.2	700.5	700.3	700.2	700.0	699.8	699.3
145°	735.2	735.6	736.1	736.6	737.1	737.6	737.4	737.2	737.1	736.9	736.5
147.5°	769.8	770.3	770.8	771.2	771.7	772.2	772.2	772.2	772.2	772.2	771.7
150°	792.1	792.4	792.7	793.1	793.5	793.8	793.8	793.8	793.8	793.8	793.2
152.5°	811.8	812.1	812.3	812.5	812.7	812.9	813.2	813.5	813.7	814.1	813.7
155°	840.3	840.3	840.5	840.7	840.8	841.0	841.7	842.3	843.0	843.6	843.4
157.5°	865.3	865.3	865.4	865.5	865.7	865.8	866.5	867.2	867.9	868.6	868.4
160°	880.9	880.7	880.7	880.7	880.7	880.7	881.6	882.4	883.2	884.0	884.1
162.5°	894.7	894.6	894.7	894.8	895.0	895.1	896.0	896.8	897.7	898.5	898.4
165°	913.2	912.9	912.9	912.9	912.9	912.9	913.9	914.9	915.9	917.0	916.9
167.5°	927.4	927.2	927.3	927.4	927.6	927.7	928.7	929.7	930.8	931.8	931.8
170°	935.7	935.4	935.4	935.4	935.4	935.4	936.6	937.8	939.0	940.1	940.1
172.5°	942.4	942.0	942.0	942.0	942.0	942.0	943.1	944.1	945.1	946.1	946.1
175°	949.3	949.0	949.0	949.0	949.0	949.0	950.0	951.0	951.9	952.9	952.9
177.5°	952.7	952.4	952.4	952.4	952.4	952.4	953.2	954.0	954.8	955.6	955.5
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2



TEST NUMBER: P332455-840

CATALOG NUMBER: S123RDIW-S1000D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1529.5	1528.9	1529.5	1527.3	1529.5	1528.9	1529.5	1536.1	1536.1	1536.7	1537.2
5°	1423.3	1422.6	1420.6	1414.3	1420.6	1422.6	1423.3	1425.3	1430.9	1440.5	1437.7
7.5°	1330.5	1329.6	1323.5	1323.6	1323.5	1329.6	1330.5	1335.8	1342.0	1348.0	1354.9
10°	1275.6	1276.2	1268.0	1263.1	1268.0	1276.2	1275.6	1280.3	1289.3	1294.0	1298.9
12.5°	1222.2	1219.0	1212.4	1207.1	1212.4	1219.0	1222.2	1225.9	1238.1	1243.5	1252.7
15°	1151.9	1145.0	1128.4	1129.8	1128.4	1145.0	1151.9	1149.1	1161.4	1168.3	1171.0
17.5°	1068.9	1063.9	1063.6	1054.0	1063.6	1063.9	1068.9	1074.4	1085.2	1092.6	1112.3
20°	1020.6	1017.1	1018.4	1008.9	1018.4	1017.1	1020.6	1031.6	1038.4	1048.0	1063.9
22.5°	982.6	979.2	973.4	970.4	973.4	979.2	982.6	990.3	997.7	1011.2	1019.9
25°	927.1	921.6	916.1	919.6	916.1	921.6	927.1	931.2	944.9	951.2	963.5
27.5°	871.6	867.5	861.9	861.2	861.9	867.5	871.6	875.6	883.1	893.5	908.4
30°	836.4	832.2	829.5	826.1	829.5	832.2	836.4	839.8	847.4	858.4	869.4
32.5°	800.6	799.8	794.9	794.2	794.9	799.8	800.6	806.3	813.9	824.3	833.6
35°	753.9	749.8	748.4	749.1	748.4	749.8	753.9	756.7	763.6	773.2	782.0
37.5°	709.5	704.0	701.6	699.0	701.6	704.0	709.5	709.9	716.9	723.4	735.5
40°	677.6	672.2	670.8	669.3	670.8	672.2	677.6	676.9	684.5	689.3	700.3
42.5°	641.9	639.6	638.8	636.4	638.8	639.6	641.9	645.6	649.8	656.9	665.1
45°	593.1	592.4	588.2	589.7	588.2	592.4	593.1	595.1	602.7	607.5	615.1
47.5°	541.7	538.7	535.7	537.7	535.7	538.7	541.7	544.4	549.6	555.4	565.4
50°	506.5	505.1	499.0	500.3	499.0	505.1	506.5	509.3	512.7	520.3	529.2
52.5°	471.3	466.1	463.7	462.9	463.7	466.1	471.3	474.0	478.1	486.8	493.4
55°	413.0	406.9	404.1	402.7	404.1	406.9	413.0	417.9	423.3	432.9	439.8
57.5°	355.9	354.2	352.0	353.6	352.0	354.2	355.9	363.9	369.2	376.8	385.2
60°	322.3	322.3	322.3	321.6	322.3	322.3	322.3	329.2	334.0	341.5	350.5
62.5°	296.5	294.8	294.3	295.3	294.3	294.8	296.5	299.5	304.3	309.1	317.0
65°	257.0	256.3	253.6	252.9	253.6	256.3	257.0	259.1	263.2	266.6	272.2
67.5°	219.7	217.3	216.5	215.5	216.5	217.3	219.7	221.6	224.3	228.7	231.5
70°	191.8	190.4	186.2	186.9	186.2	190.4	191.8	195.2	197.9	203.4	206.2
72.5°	161.5	160.2	159.3	158.3	159.3	160.2	161.5	164.9	167.6	173.7	178.1
75°	127.8	127.1	126.4	129.2	126.4	127.1	127.8	128.6	129.2	131.3	133.3
77.5°	102.4	102.4	102.8	101.7	102.8	102.4	102.4	102.4	102.4	103.5	103.9
80°	85.9	85.9	85.2	85.2	85.2	85.9	85.9	85.9	85.9	85.9	85.2
82.5°	68.9	69.4	69.8	68.8	69.8	69.4	68.9	70.0	70.5	69.4	69.8
85°	45.3	44.6	46.0	45.3	46.0	44.6	45.3	45.3	44.0	45.3	44.6
87.5°	24.6	23.6	23.6	24.3	23.6	23.6	24.6	23.4	23.3	23.2	22.5
90°	21.5	21.8	22.1	22.5	22.1	21.8	21.5	21.1	20.7	20.0	19.3
92.5°	30.9	30.7	30.5	30.3	30.5	30.7	30.9	31.1	30.9	30.4	29.9
95°	58.5	58.5	58.5	58.5	58.5	58.5	58.5	58.5	58.2	57.5	56.8
97.5°	90.2	90.1	90.0	90.0	90.0	90.1	90.2	90.2	89.9	89.1	88.4
100°	112.9	113.3	113.6	113.9	113.6	113.3	112.9	112.6	112.2	111.7	111.2
102.5°	138.8	138.7	138.6	138.6	138.6	138.7	138.8	138.8	138.6	138.0	137.5
105°	177.4	177.7	178.0	178.4	178.0	177.7	177.4	177.0	176.9	176.9	176.9
107.5°	220.6	220.4	220.2	219.9	220.2	220.4	220.6	220.8	220.6	220.0	219.4
110°	249.1	248.7	248.4	248.1	248.4	248.7	249.1	249.4	249.2	248.6	247.9



TEST NUMBER: P332455-840

CATALOG NUMBER: S123RDIW-S1000D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	278.3	278.2	278.1	278.1	278.1	278.2	278.3	278.3	278.0	277.2	276.4
115°	319.8	319.6	319.5	319.3	319.5	319.6	319.8	320.0	320.0	319.8	319.6
117.5°	362.5	362.0	361.6	361.1	361.6	362.0	362.5	363.0	363.2	363.2	363.3
120°	391.5	391.2	390.8	390.5	390.8	391.2	391.5	391.8	392.1	392.2	392.4
122.5°	420.1	419.6	419.2	418.7	419.2	419.6	420.1	420.6	421.0	421.4	421.9
125°	463.0	462.3	461.6	461.0	461.6	462.3	463.0	463.6	464.3	464.9	465.6
127.5°	505.4	504.6	503.9	503.1	503.9	504.6	505.4	506.1	507.1	508.0	508.9
130°	534.2	533.0	531.9	530.7	531.9	533.0	534.2	535.3	536.2	536.9	537.7
132.5°	562.2	561.3	560.4	559.5	560.4	561.3	562.2	563.1	563.9	564.7	565.5
135°	605.1	604.8	604.5	604.1	604.5	604.8	605.1	605.5	606.0	606.6	607.3
137.5°	645.5	644.8	644.2	643.6	644.2	644.8	645.5	646.1	646.8	647.4	648.1
140°	672.9	671.7	670.6	669.3	670.6	671.7	672.9	674.0	674.7	674.9	675.0
142.5°	698.4	697.5	696.6	695.7	696.6	697.5	698.4	699.3	699.8	700.0	700.2
145°	735.8	735.2	734.5	733.9	734.5	735.2	735.8	736.5	736.9	737.1	737.2
147.5°	770.7	769.7	768.7	767.7	768.7	769.7	770.7	771.7	772.2	772.2	772.2
150°	792.2	791.3	790.3	789.3	790.3	791.3	792.2	793.2	793.8	793.8	793.8
152.5°	812.8	812.0	811.1	810.3	811.1	812.0	812.8	813.7	814.1	813.7	813.5
155°	842.2	841.1	839.9	838.8	839.9	841.1	842.2	843.4	843.6	843.0	842.3
157.5°	867.5	866.6	865.7	864.6	865.7	866.6	867.5	868.4	868.6	867.9	867.2
160°	883.5	882.8	882.1	881.5	882.1	882.8	883.5	884.1	884.0	883.2	882.4
162.5°	897.3	896.3	895.1	894.0	895.1	896.3	897.3	898.4	898.5	897.7	896.8
165°	915.7	914.5	913.4	912.2	913.4	914.5	915.7	916.9	917.0	915.9	914.9
167.5°	930.8	929.7	928.7	927.7	928.7	929.7	930.8	931.8	931.8	930.8	929.7
170°	939.0	937.8	936.6	935.4	936.6	937.8	939.0	940.1	940.1	939.0	937.8
172.5°	944.9	943.8	942.6	941.5	942.6	943.8	944.9	946.1	946.1	945.1	944.1
175°	951.7	950.5	949.4	948.2	949.4	950.5	951.7	952.9	952.9	951.9	951.0
177.5°	954.6	953.6	952.7	951.8	952.7	953.6	954.6	955.5	955.6	954.8	954.0
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2



TEST NUMBER: P332455-840

CATALOG NUMBER: S123RDIW-S1000D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1532.3	1539.9	1547.7	1554.8	1565.8	1570.7	1577.9	1580.6	1588.9	1601.0	1610.9
5°	1439.1	1450.1	1464.5	1476.2	1494.8	1509.1	1525.0	1540.1	1558.0	1583.4	1606.1
7.5°	1360.1	1370.9	1388.3	1410.0	1430.5	1450.9	1472.5	1493.1	1518.6	1555.1	1591.2
10°	1307.9	1320.9	1341.5	1364.8	1390.3	1410.3	1435.6	1461.8	1493.4	1535.3	1578.6
12.5°	1262.7	1272.5	1296.5	1318.7	1347.5	1372.8	1397.8	1428.3	1464.2	1508.9	1561.0
15°	1191.0	1204.8	1228.1	1252.8	1283.1	1309.9	1342.2	1379.3	1414.3	1469.4	1532.6
17.5°	1118.9	1139.8	1164.2	1192.1	1214.5	1251.4	1286.6	1324.6	1367.8	1426.0	1495.4
20°	1072.8	1089.2	1112.0	1152.6	1182.0	1210.2	1242.5	1290.0	1329.8	1395.8	1467.9
22.5°	1033.8	1045.8	1071.3	1104.7	1139.2	1171.7	1204.6	1249.8	1299.0	1361.7	1440.0
25°	975.9	995.1	1014.4	1038.4	1075.5	1114.7	1150.4	1188.9	1241.1	1307.9	1392.4
27.5°	919.4	936.9	955.8	985.3	1013.5	1050.2	1087.5	1131.7	1187.7	1258.2	1343.9
30°	883.1	896.2	914.0	951.8	977.2	1008.9	1052.9	1092.1	1144.3	1219.2	1309.9
32.5°	845.8	862.6	882.1	911.2	942.6	972.6	1012.7	1055.2	1108.5	1182.3	1275.3
35°	792.4	812.3	832.2	853.5	885.1	916.1	949.8	996.5	1050.8	1122.3	1213.7
37.5°	743.4	759.4	775.6	802.0	832.0	861.4	892.8	938.9	990.1	1067.1	1151.0
40°	712.0	726.4	738.8	766.3	795.2	826.8	857.7	898.3	953.2	1025.4	1106.5
42.5°	677.9	691.3	708.0	730.5	761.6	788.3	819.2	857.6	909.2	982.5	1053.7
45°	626.7	641.9	656.3	677.6	708.5	734.7	762.1	798.6	851.5	912.0	975.2
47.5°	573.6	588.7	605.2	625.8	652.8	679.2	706.8	739.0	787.3	846.7	889.3
50°	539.5	551.9	568.4	589.0	613.7	641.9	666.6	701.7	747.7	794.5	831.5
52.5°	504.3	515.5	534.2	556.0	579.1	603.4	629.8	659.8	701.6	745.5	775.0
55°	449.5	463.2	479.0	500.3	523.0	543.6	569.1	600.0	633.0	665.9	685.9
57.5°	398.2	409.6	422.9	444.9	464.5	489.2	512.0	536.0	566.5	591.5	604.5
60°	360.8	371.1	388.3	407.6	426.1	447.4	473.5	497.6	520.9	540.9	551.2
62.5°	325.6	337.6	352.5	370.1	390.3	410.6	433.3	453.6	474.2	491.4	498.4
65°	279.7	289.3	300.3	316.8	333.4	354.0	371.8	392.4	407.6	417.2	423.3
67.5°	237.9	244.3	252.7	263.7	279.8	297.8	315.2	331.2	343.9	350.5	356.0
70°	211.0	215.1	221.3	232.3	244.7	260.4	278.3	290.0	301.0	306.5	312.0
72.5°	184.0	189.2	194.9	203.7	213.9	225.3	238.2	252.7	258.7	265.3	268.6
75°	139.5	147.0	154.6	160.2	167.0	175.9	187.6	196.5	200.0	205.5	206.2
77.5°	105.3	106.9	112.4	119.3	125.1	131.6	139.0	146.9	148.6	151.5	153.3
80°	86.5	86.5	86.5	90.7	97.6	102.4	109.3	113.4	116.1	116.8	117.5
82.5°	69.6	69.6	69.0	69.8	72.3	74.9	81.2	85.9	88.1	87.7	86.1
85°	45.3	44.0	44.0	43.3	44.0	42.6	41.9	44.6	48.8	48.8	47.5
87.5°	22.4	21.7	21.8	20.9	19.9	18.9	16.9	17.1	16.8	18.6	17.8
90°	18.7	18.0	15.9	13.6	11.5	9.3	7.4	5.8	4.0	2.4	0.7
92.5°	29.3	28.8	27.6	26.4	25.0	23.8	22.6	21.5	20.4	19.3	18.2
95°	56.1	55.4	54.1	52.8	51.5	50.1	48.9	47.8	46.6	45.3	44.2
97.5°	87.6	86.8	85.8	84.8	83.9	82.9	82.0	81.2	80.3	79.4	78.6
100°	110.7	110.2	109.4	108.6	107.7	106.8	105.9	104.9	103.9	102.9	101.9
102.5°	137.0	136.5	135.4	134.4	133.3	132.2	131.3	130.7	130.2	129.6	129.0
105°	176.9	176.9	175.4	173.9	172.4	170.9	170.0	169.7	169.4	169.0	168.6
107.5°	218.9	218.4	217.8	217.2	216.6	216.0	215.6	215.4	215.2	215.0	214.8
110°	247.3	246.6	246.3	245.9	245.6	245.3	244.9	244.6	244.3	244.0	243.6



TEST NUMBER: P332455-840

CATALOG NUMBER: S123RDIW-S1000D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	275.6	274.8	274.7	274.7	274.6	274.5	274.4	274.2	274.0	273.8	273.6
115°	319.5	319.3	319.6	320.0	320.3	320.6	320.5	320.0	319.5	319.0	318.6
117.5°	363.3	363.3	363.9	364.3	364.7	365.2	365.2	364.9	364.5	364.2	363.9
120°	392.6	392.7	393.6	394.5	395.3	396.1	396.1	395.1	394.0	393.0	392.0
122.5°	422.3	422.7	423.2	423.6	424.0	424.4	424.3	423.6	422.8	422.1	421.4
125°	466.4	467.0	467.3	467.7	468.0	468.3	468.3	467.8	467.3	466.8	466.3
127.5°	509.8	510.8	511.1	511.5	511.9	512.2	511.9	510.8	509.8	508.7	507.6
130°	538.3	539.0	539.5	540.0	540.5	541.0	540.5	539.2	537.9	536.5	535.2
132.5°	566.3	567.1	567.4	567.8	568.3	568.6	568.2	566.7	565.4	564.1	562.8
135°	607.9	608.6	608.8	608.9	609.2	609.4	608.8	607.9	606.9	605.9	604.9
137.5°	648.8	649.5	649.1	648.7	648.2	647.8	647.2	646.4	645.5	644.7	643.9
140°	675.2	675.4	675.2	675.0	674.9	674.7	674.2	673.4	672.6	671.7	670.9
142.5°	700.3	700.5	700.2	699.9	699.6	699.3	698.7	697.9	697.1	696.3	695.5
145°	737.4	737.6	737.1	736.6	736.1	735.6	735.2	734.8	734.5	734.2	733.9
147.5°	772.2	772.2	771.7	771.2	770.8	770.3	769.8	769.2	768.6	768.0	767.4
150°	793.8	793.8	793.5	793.1	792.7	792.4	792.1	791.8	791.4	791.1	790.8
152.5°	813.2	812.9	812.7	812.5	812.3	812.1	811.8	811.4	810.9	810.4	810.0
155°	841.7	841.0	840.8	840.7	840.5	840.3	840.3	840.3	840.3	840.3	840.3
157.5°	866.5	865.8	865.7	865.5	865.4	865.3	865.3	865.5	865.7	865.9	866.1
160°	881.6	880.7	880.7	880.7	880.7	880.7	880.9	881.2	881.6	881.9	882.2
162.5°	896.0	895.1	895.0	894.8	894.7	894.6	894.7	895.2	895.6	896.2	896.7
165°	913.9	912.9	912.9	912.9	912.9	912.9	913.2	913.7	914.2	914.7	915.2
167.5°	928.7	927.7	927.6	927.4	927.3	927.2	927.4	928.1	928.8	929.4	930.1
170°	936.6	935.4	935.4	935.4	935.4	935.4	935.7	936.4	937.2	937.8	938.5
172.5°	943.1	942.0	942.0	942.0	942.0	942.0	942.4	943.0	943.7	944.4	945.0
175°	950.0	949.0	949.0	949.0	949.0	949.0	949.3	950.0	950.6	951.3	951.9
177.5°	953.2	952.4	952.4	952.4	952.4	952.4	952.7	953.2	953.7	954.2	954.8
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2



TEST NUMBER: P332455-840

CATALOG NUMBER: S123RDIW-S1000D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1614.2	1620.2	1627.9	1639.5	1648.3	1656.0	1657.6	1659.8	1665.4	1674.7	1681.8
5°	1624.7	1640.4	1665.9	1690.6	1717.5	1739.4	1760.0	1774.4	1788.2	1817.1	1840.5
7.5°	1621.3	1656.6	1696.4	1740.8	1785.7	1829.3	1869.8	1905.9	1941.9	1984.0	2031.9
10°	1619.1	1660.4	1713.9	1771.0	1833.6	1894.7	1953.9	1999.9	2053.5	2101.6	2162.7
12.5°	1608.7	1668.1	1732.1	1805.1	1882.0	1952.5	2030.2	2093.9	2155.3	2224.7	2295.8
15°	1595.1	1667.3	1748.4	1845.2	1962.1	2047.3	2127.0	2237.7	2313.3	2388.8	2490.6
17.5°	1570.2	1658.3	1759.6	1885.5	1983.0	2097.5	2217.5	2304.9	2406.7	2513.3	2605.4
20°	1550.4	1652.8	1766.3	1890.0	2014.3	2138.7	2254.8	2359.3	2464.5	2587.5	2663.1
22.5°	1530.7	1631.9	1749.7	1881.2	2014.9	2145.9	2277.3	2400.0	2518.3	2642.4	2739.0
25°	1488.5	1608.8	1736.7	1870.7	2002.7	2147.0	2303.6	2440.4	2586.8	2714.6	2806.0
27.5°	1445.9	1556.2	1683.4	1819.4	1966.1	2136.7	2321.0	2476.4	2623.1	2714.6	2743.4
30°	1407.4	1524.3	1641.1	1779.3	1938.0	2128.4	2324.3	2502.2	2622.5	2662.4	2632.8
32.5°	1368.5	1474.3	1590.0	1731.4	1900.1	2108.1	2328.6	2486.9	2559.3	2528.8	2408.5
35°	1299.6	1395.1	1507.1	1648.7	1842.5	2096.8	2310.6	2417.7	2399.8	2228.1	2001.2
37.5°	1225.9	1303.7	1407.4	1555.5	1782.8	2052.1	2232.4	2248.3	2093.7	1829.9	1567.9
40°	1167.6	1237.7	1344.2	1498.8	1736.7	2008.1	2153.8	2089.9	1850.1	1556.6	1338.1
42.5°	1111.0	1170.1	1272.7	1439.5	1692.7	1948.2	2036.7	1897.5	1620.8	1343.3	1144.6
45°	1015.0	1070.8	1173.8	1344.9	1602.7	1833.6	1821.9	1579.9	1303.0	1079.6	914.7
47.5°	924.0	972.7	1069.4	1244.2	1496.9	1661.7	1552.5	1295.1	1060.2	880.9	763.3
50°	859.7	907.9	1004.1	1176.6	1412.3	1532.6	1376.5	1128.4	913.3	764.9	671.5
52.5°	798.2	845.2	933.1	1101.3	1310.0	1381.9	1214.4	984.4	805.1	676.9	596.6
55°	712.0	747.7	826.8	987.5	1143.6	1160.0	990.3	797.9	650.2	560.8	505.8
57.5°	624.2	654.9	733.1	861.1	970.5	962.0	801.0	634.6	535.1	468.7	428.9
60°	566.9	597.2	665.9	775.9	858.4	829.5	681.8	547.8	462.5	413.7	382.1
62.5°	513.6	537.2	601.6	681.9	741.2	708.5	582.8	471.9	404.2	363.1	338.1
65°	436.4	455.7	507.2	549.1	582.1	550.5	446.1	369.0	320.2	291.3	274.2
67.5°	363.0	375.3	407.8	422.9	446.2	411.5	335.4	283.9	256.1	231.8	219.7
70°	316.8	325.8	343.0	355.3	361.5	325.8	269.4	231.6	208.2	191.1	183.5
72.5°	270.6	278.5	282.0	292.1	288.9	255.4	216.6	186.5	169.8	158.0	148.3
75°	206.8	210.3	206.8	202.8	193.8	170.5	143.6	128.6	116.1	110.7	107.2
77.5°	150.8	149.7	145.0	138.6	123.3	108.6	94.1	89.1	83.7	80.8	79.6
80°	116.1	113.4	109.3	99.0	85.9	75.6	72.2	68.8	66.7	63.2	62.5
82.5°	86.4	84.8	78.0	69.3	60.1	55.2	52.4	51.1	49.1	47.3	47.2
85°	46.0	44.0	36.5	31.6	30.2	28.9	28.2	28.2	25.4	24.7	24.7
87.5°	15.3	12.3	12.1	10.8	11.2	10.5	11.5	10.9	10.7	11.4	10.5
90°	2.4	4.0	5.8	7.4	9.3	11.5	13.6	15.9	18.0	18.7	19.3
92.5°	19.3	20.4	21.5	22.6	23.8	25.0	26.4	27.6	28.8	29.3	29.9
95°	45.3	46.6	47.8	48.9	50.1	51.5	52.8	54.1	55.4	56.1	56.8
97.5°	79.4	80.3	81.2	82.0	82.9	83.9	84.8	85.8	86.8	87.6	88.4
100°	102.9	103.9	104.9	105.9	106.8	107.7	108.6	109.4	110.2	110.7	111.2
102.5°	129.6	130.2	130.7	131.3	132.2	133.3	134.4	135.4	136.5	137.0	137.5
105°	169.0	169.4	169.7	170.0	170.9	172.4	173.9	175.4	176.9	176.9	176.9
107.5°	215.0	215.2	215.4	215.6	216.0	216.6	217.2	217.8	218.4	218.9	219.4
110°	244.0	244.3	244.6	244.9	245.3	245.6	245.9	246.3	246.6	247.3	247.9



TEST NUMBER: P332455-840

CATALOG NUMBER: S123RDIW-S1000D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	273.8	274.0	274.2	274.4	274.5	274.6	274.7	274.7	274.8	275.6	276.4
115°	319.0	319.5	320.0	320.5	320.6	320.3	320.0	319.6	319.3	319.5	319.6
117.5°	364.2	364.5	364.9	365.2	365.2	364.7	364.3	363.9	363.3	363.3	363.3
120°	393.0	394.0	395.1	396.1	396.1	395.3	394.5	393.6	392.7	392.6	392.4
122.5°	422.1	422.8	423.6	424.3	424.4	424.0	423.6	423.2	422.7	422.3	421.9
125°	466.8	467.3	467.8	468.3	468.3	468.0	467.7	467.3	467.0	466.4	465.6
127.5°	508.7	509.8	510.8	511.9	512.2	511.9	511.5	511.1	510.8	509.8	508.9
130°	536.5	537.9	539.2	540.5	541.0	540.5	540.0	539.5	539.0	538.3	537.7
132.5°	564.1	565.4	566.7	568.2	568.6	568.3	567.8	567.4	567.1	566.3	565.5
135°	605.9	606.9	607.9	608.8	609.4	609.2	608.9	608.8	608.6	607.9	607.3
137.5°	644.7	645.5	646.4	647.2	647.8	648.2	648.7	649.1	649.5	648.8	648.1
140°	671.7	672.6	673.4	674.2	674.7	674.9	675.0	675.2	675.4	675.2	675.0
142.5°	696.3	697.1	697.9	698.7	699.3	699.6	699.9	700.2	700.5	700.3	700.2
145°	734.2	734.5	734.8	735.2	735.6	736.1	736.6	737.1	737.6	737.4	737.2
147.5°	768.0	768.6	769.2	769.8	770.3	770.8	771.2	771.7	772.2	772.2	772.2
150°	791.1	791.4	791.8	792.1	792.4	792.7	793.1	793.5	793.8	793.8	793.8
152.5°	810.4	810.9	811.4	811.8	812.1	812.3	812.5	812.7	812.9	813.2	813.5
155°	840.3	840.3	840.3	840.3	840.3	840.5	840.7	840.8	841.0	841.7	842.3
157.5°	865.9	865.7	865.5	865.3	865.3	865.4	865.5	865.7	865.8	866.5	867.2
160°	881.9	881.6	881.2	880.9	880.7	880.7	880.7	880.7	880.7	881.6	882.4
162.5°	896.2	895.6	895.2	894.7	894.6	894.7	894.8	895.0	895.1	896.0	896.8
165°	914.7	914.2	913.7	913.2	912.9	912.9	912.9	912.9	912.9	913.9	914.9
167.5°	929.4	928.8	928.1	927.4	927.2	927.3	927.4	927.6	927.7	928.7	929.7
170°	937.8	937.2	936.4	935.7	935.4	935.4	935.4	935.4	935.4	936.6	937.8
172.5°	944.4	943.7	943.0	942.4	942.0	942.0	942.0	942.0	942.0	943.1	944.1
175°	951.3	950.6	950.0	949.3	949.0	949.0	949.0	949.0	949.0	950.0	951.0
177.5°	954.2	953.7	953.2	952.7	952.4	952.4	952.4	952.4	952.4	953.2	954.0
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2	954.2



TEST NUMBER: P332455-840

CATALOG NUMBER: S123RDIW-S1000D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4	1605.4
2.5°	1693.3	1693.3	1695.6	1703.8	1705.0	1712.0	1709.9
5°	1861.1	1874.1	1879.0	1899.6	1911.9	1917.4	1906.4
7.5°	2066.2	2102.9	2120.4	2142.0	2161.1	2166.9	2151.9
10°	2215.6	2254.1	2286.4	2306.4	2324.9	2337.3	2353.1
12.5°	2360.3	2407.5	2438.2	2466.4	2485.5	2501.1	2503.8
15°	2517.4	2588.9	2643.1	2683.0	2702.9	2713.2	2709.2
17.5°	2675.8	2742.1	2780.8	2821.5	2849.0	2850.4	2851.3
20°	2765.5	2830.0	2874.8	2905.0	2935.9	2934.6	2941.4
22.5°	2825.4	2876.3	2910.5	2932.4	2943.0	2937.8	2939.2
25°	2853.5	2868.5	2862.4	2827.3	2818.4	2786.1	2791.6
27.5°	2708.9	2637.4	2563.4	2468.3	2393.3	2333.3	2336.3
30°	2512.5	2386.1	2241.8	2120.8	2012.3	1982.1	1917.4
32.5°	2238.3	2048.5	1879.5	1766.8	1673.5	1648.3	1592.0
35°	1773.1	1588.9	1415.0	1310.6	1269.3	1211.6	1210.9
37.5°	1378.2	1216.0	1124.1	1045.7	1004.6	969.7	966.2
40°	1159.4	1032.9	963.5	907.2	866.7	840.5	834.4
42.5°	1006.5	904.2	839.3	804.4	773.2	759.7	749.6
45°	821.9	753.3	707.8	676.2	661.9	651.5	646.0
47.5°	687.5	641.5	610.6	589.6	577.8	566.9	569.9
50°	614.4	576.6	553.9	534.0	525.0	517.5	518.2
52.5°	555.5	521.6	503.3	488.9	477.8	472.4	469.8
55°	471.4	450.1	431.6	421.3	415.1	407.6	405.5
57.5°	402.1	385.7	370.5	358.9	357.4	350.1	351.0
60°	356.0	342.2	329.9	323.7	318.9	312.7	314.8
62.5°	318.1	306.5	295.3	290.1	285.4	280.8	281.8
65°	260.4	249.4	242.6	239.8	237.8	235.7	233.7
67.5°	207.5	200.9	196.5	190.7	186.4	185.7	183.6
70°	174.6	165.6	158.0	150.5	148.5	147.7	148.5
72.5°	140.0	134.3	132.2	128.6	128.2	126.3	127.5
75°	105.1	103.1	101.7	99.0	99.0	99.0	99.0
77.5°	77.6	76.2	75.4	74.9	74.2	73.2	73.1
80°	60.5	59.8	58.4	58.4	57.8	58.4	57.8
82.5°	45.6	45.5	44.1	44.1	43.4	43.0	43.4
85°	23.3	22.7	24.0	22.7	23.3	22.0	23.3
87.5°	10.6	10.7	10.3	10.3	9.9	11.0	10.0
90°	20.0	20.7	21.1	21.5	21.8	22.1	22.5
92.5°	30.4	30.9	31.1	30.9	30.7	30.5	30.3
95°	57.5	58.2	58.5	58.5	58.5	58.5	58.5
97.5°	89.1	89.9	90.2	90.2	90.1	90.0	90.0
100°	111.7	112.2	112.6	112.9	113.3	113.6	113.9
102.5°	138.0	138.6	138.8	138.8	138.7	138.6	138.6
105°	176.9	176.9	177.0	177.4	177.7	178.0	178.4
107.5°	220.0	220.6	220.8	220.6	220.4	220.2	219.9
110°	248.6	249.2	249.4	249.1	248.7	248.4	248.1



TEST NUMBER: P332455-840

CATALOG NUMBER: S123RDIW-S1000D755U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	277.2	278.0	278.3	278.3	278.2	278.1	278.1
115°	319.8	320.0	320.0	319.8	319.6	319.5	319.3
117.5°	363.2	363.2	363.0	362.5	362.0	361.6	361.1
120°	392.2	392.1	391.8	391.5	391.2	390.8	390.5
122.5°	421.4	421.0	420.6	420.1	419.6	419.2	418.7
125°	464.9	464.3	463.6	463.0	462.3	461.6	461.0
127.5°	508.0	507.1	506.1	505.4	504.6	503.9	503.1
130°	536.9	536.2	535.3	534.2	533.0	531.9	530.7
132.5°	564.7	563.9	563.1	562.2	561.3	560.4	559.5
135°	606.6	606.0	605.5	605.1	604.8	604.5	604.1
137.5°	647.4	646.8	646.1	645.5	644.8	644.2	643.6
140°	674.9	674.7	674.0	672.9	671.7	670.6	669.3
142.5°	700.0	699.8	699.3	698.4	697.5	696.6	695.7
145°	737.1	736.9	736.5	735.8	735.2	734.5	733.9
147.5°	772.2	772.2	771.7	770.7	769.7	768.7	767.7
150°	793.8	793.8	793.2	792.2	791.3	790.3	789.3
152.5°	813.7	814.1	813.7	812.8	812.0	811.1	810.3
155°	843.0	843.6	843.4	842.2	841.1	839.9	838.8
157.5°	867.9	868.6	868.4	867.5	866.6	865.7	864.6
160°	883.2	884.0	884.1	883.5	882.8	882.1	881.5
162.5°	897.7	898.5	898.4	897.3	896.3	895.1	894.0
165°	915.9	917.0	916.9	915.7	914.5	913.4	912.2
167.5°	930.8	931.8	931.8	930.8	929.7	928.7	927.7
170°	939.0	940.1	940.1	939.0	937.8	936.6	935.4
172.5°	945.1	946.1	946.1	944.9	943.8	942.6	941.5
175°	951.9	952.9	952.9	951.7	950.5	949.4	948.2
177.5°	954.8	955.6	955.5	954.6	953.6	952.7	951.8
180°	954.2	954.2	954.2	954.2	954.2	954.2	954.2

(END OF REPORT)