

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332392-930

Luminaire Tested: **S123RDIW-S340D460U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332392-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D460U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2563.1 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332392-930

CATALOG NUMBER: S123RDIW-S340D460U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332392-930

CATALOG NUMBER: S123RDIW-S340D460U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	81	75	70	80	74	69	64	61	57	54	49	47	44	38	37	35	30
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	35	33	31	28	26	22
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	28	25	23	20
6	62	50	43	37	57	46	39	34	39	34	30	32	28	25	25	22	20	17
7	57	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	29	49	38	31	27	32	27	23	26	23	20	21	18	16	14
9	50	38	30	25	45	35	28	24	29	24	21	24	21	18	20	17	15	13
10	46	35	28	23	42	32	26	21	27	22	19	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5042	5042	5042
5°	5061	4991	5020
10°	5032	4928	4912
15°	4979	4813	4763
20°	4904	4669	4560
25°	4828	4507	4363
30°	4727	4320	4084
35°	4623	4133	3829
40°	4526	3912	3513
45°	4401	3694	3227
50°	4262	3448	2907
55°	4121	3166	2609
60°	3991	2863	2282
65°	3823	2534	1954
70°	3610	2127	1577
75°	3302	1676	1485
80°	2944	1488	1364
85°	2482	1309	1223



TEST NUMBER: P332392-930

CATALOG NUMBER: S123RDIW-S340D460U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	1.7
10°-20°	122.4	4.8
20°-30°	176.2	6.9
30°-40°	198.5	7.7
40°-50°	189.9	7.4
50°-60°	155.5	6.1
60°-70°	104.9	4.1
70°-80°	52.8	2.1
80°-90°	15.3	0.6
90°-100°	17.9	0.7
100°-110°	85.4	3.3
110°-120°	205.2	8.0
120°-130°	261.3	10.2
130°-140°	279.2	10.9
140°-150°	261.1	10.2
150°-160°	210.6	8.2
160°-170°	135.9	5.3
170°-180°	46.8	1.8
0°-30°	342.6	13.4
0°-40°	541.1	21.1
0°-60°	886.5	34.6
0°-90°	1059.5	41.3
90°-120°	308.6	12.0
90°-150°	1110.2	43.3
90°-180°	1504.0	58.7
0°-180°	2563.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	465	465	44
15°	447	442	432	430	427	126
25°	406	396	380	372	367	187
35°	352	338	314	299	291	220
45°	289	271	243	222	212	223
55°	220	200	169	147	139	197
65°	150	129	100	82	77	148
75°	79	61	40	37	36	85
85°	20	12	11	10	10	23
90°	0	4	9	10	11	2
95°	22	8	11	14	14	28
105°	109	111	80	19	16	116
115°	205	207	210	214	215	202
125°	289	291	293	294	294	258
135°	359	362	363	364	363	277
145°	415	417	418	419	419	259
155°	457	456	456	458	456	210
165°	482	481	480	483	481	136
175°	493	491	492	494	491	47
180°	493	493	493	493	493	



TEST NUMBER: P332392-930

CATALOG NUMBER: S123RDIW-S340D460U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	469.9	469.6	469.4	469.1	468.9	468.3	467.5	466.7	465.9	465.0	465.8
5°	468.4	468.0	467.6	467.2	466.7	466.0	465.0	464.0	462.9	461.9	462.7
7.5°	464.1	463.6	463.2	462.7	462.3	461.4	460.1	458.8	457.4	456.1	456.5
10°	460.4	459.8	459.3	458.7	458.0	457.0	455.5	454.0	452.4	450.9	451.0
12.5°	455.3	454.6	454.0	453.3	452.7	451.3	449.5	447.7	445.8	443.9	443.8
15°	446.8	445.8	444.9	443.9	443.0	441.4	439.0	436.7	434.3	431.9	431.5
17.5°	436.0	435.0	433.9	432.8	431.7	429.7	426.6	423.6	420.7	417.7	416.8
20°	428.1	426.8	425.4	424.1	422.7	420.4	417.3	414.0	410.8	407.6	406.5
22.5°	419.3	417.8	416.2	414.7	413.1	410.7	407.2	403.8	400.4	397.0	395.6
25°	406.5	404.4	402.3	400.1	398.0	395.0	391.2	387.3	383.4	379.5	377.7
27.5°	390.9	388.6	386.2	383.9	381.6	378.3	374.0	369.6	365.3	360.9	358.5
30°	380.3	377.7	375.2	372.7	370.1	366.5	361.7	357.0	352.3	347.6	344.7
32.5°	369.7	366.7	363.9	361.0	358.2	354.2	349.2	344.2	339.2	334.2	331.1
35°	351.8	348.7	345.7	342.7	339.7	335.5	330.3	325.0	319.8	314.5	311.0
37.5°	333.7	330.3	326.9	323.6	320.2	315.7	310.1	304.5	299.0	293.3	289.3
40°	322.1	318.5	314.7	311.0	307.3	302.4	296.4	290.4	284.5	278.4	274.1
42.5°	309.1	305.3	301.7	297.9	294.2	289.3	283.1	276.9	270.7	264.5	259.7
45°	289.1	285.3	281.5	277.7	273.9	268.7	262.3	255.8	249.2	242.7	237.9
47.5°	269.1	265.0	260.7	256.6	252.4	247.1	240.6	234.1	227.6	221.1	215.9
50°	254.5	250.5	246.6	242.6	238.6	233.3	226.4	219.6	212.7	205.9	200.6
52.5°	241.5	237.2	232.8	228.5	224.2	218.7	211.9	205.1	198.4	191.6	186.2
55°	219.6	215.4	211.3	207.2	203.0	197.4	190.2	183.0	175.9	168.7	163.8
57.5°	199.3	194.9	190.4	185.8	181.3	175.5	168.3	161.0	153.8	146.7	142.0
60°	185.4	180.8	176.1	171.5	166.8	161.0	154.0	147.0	140.0	133.0	128.4
62.5°	171.4	166.7	162.1	157.5	152.9	147.0	140.0	133.0	126.0	119.0	114.7
65°	150.1	145.4	140.8	136.2	131.5	125.9	119.3	112.7	106.2	99.5	95.4
67.5°	128.7	124.0	119.3	114.6	109.9	104.4	98.1	91.8	85.4	79.2	76.1
70°	114.7	110.1	105.6	101.0	96.5	91.2	85.4	79.4	73.5	67.6	64.7
72.5°	100.8	96.3	91.8	87.2	82.8	77.9	72.5	67.1	61.7	56.3	54.0
75°	79.4	75.3	71.3	67.3	63.2	58.9	54.2	49.6	44.9	40.3	39.5
77.5°	59.9	56.3	52.6	48.9	45.3	42.0	39.0	36.0	33.0	30.0	29.6
80°	47.5	44.0	40.6	37.1	33.7	31.1	29.3	27.5	25.7	24.0	23.6
82.5°	35.6	32.6	29.7	26.7	23.6	21.8	21.0	20.1	19.3	18.4	18.2
85°	20.1	18.3	16.4	14.6	12.7	11.7	11.4	11.2	10.9	10.6	10.4
87.5°	7.3	6.8	6.2	5.6	5.1	4.9	5.1	5.3	5.5	5.7	5.7
90°	0.3	1.1	2.0	2.8	3.6	4.6	5.6	6.7	7.7	8.8	9.1
92.5°	6.8	6.6	6.4	6.1	5.9	6.2	7.0	7.7	8.6	9.4	9.9
95°	22.3	19.0	15.7	12.3	9.0	7.7	8.6	9.5	10.4	11.3	11.9
97.5°	44.9	43.4	41.9	40.4	38.9	35.2	29.4	23.5	17.7	11.8	12.5
100°	61.9	63.5	65.1	66.8	68.4	62.9	50.2	37.5	24.8	12.1	12.7
102.5°	81.2	82.4	83.6	84.8	85.9	79.6	65.7	51.9	38.0	24.1	22.1
105°	109.2	110.1	111.0	111.9	112.8	109.5	102.2	94.9	87.6	80.2	65.8
107.5°	138.6	139.3	140.1	140.7	141.5	142.4	143.6	144.7	145.9	147.0	136.5
110°	158.2	158.9	159.6	160.2	160.9	161.6	162.5	163.4	164.3	165.2	162.5



TEST NUMBER: P332392-930

CATALOG NUMBER: S123RDIW-S340D460U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	177.0	177.6	178.1	178.7	179.4	180.1	181.0	181.9	182.8	183.7	183.7
115°	204.7	205.2	205.7	206.2	206.7	207.3	208.1	208.8	209.5	210.3	211.1
117.5°	231.6	232.3	232.8	233.4	234.1	234.6	234.9	235.3	235.7	236.0	236.7
120°	248.3	249.1	249.8	250.5	251.3	251.8	252.0	252.3	252.5	252.7	253.4
122.5°	265.4	266.0	266.5	267.2	267.7	268.2	268.6	268.8	269.1	269.5	269.9
125°	288.6	289.3	289.9	290.6	291.2	291.7	292.0	292.4	292.7	293.0	293.2
127.5°	311.2	311.9	312.5	313.2	313.8	314.3	314.7	315.1	315.5	315.9	316.2
130°	325.3	326.0	326.6	327.3	327.9	328.4	328.7	329.1	329.4	329.6	330.0
132.5°	338.8	339.4	340.1	340.7	341.4	341.8	342.1	342.3	342.6	342.8	343.2
135°	359.3	359.8	360.3	360.8	361.3	361.7	362.0	362.3	362.6	363.0	363.2
137.5°	376.9	377.6	378.1	378.8	379.4	379.8	380.0	380.2	380.3	380.5	380.9
140°	388.7	389.1	389.6	390.1	390.6	390.9	391.2	391.4	391.7	391.9	392.2
142.5°	399.5	400.0	400.5	401.0	401.5	401.8	402.0	402.3	402.5	402.8	403.0
145°	414.7	415.2	415.8	416.4	416.9	417.3	417.4	417.6	417.8	417.9	418.1
147.5°	428.9	429.3	429.7	430.1	430.4	430.7	430.9	431.0	431.2	431.4	431.5
150°	437.7	438.0	438.2	438.5	438.7	438.9	439.0	439.2	439.4	439.5	439.7
152.5°	445.6	445.7	445.9	446.0	446.1	446.2	446.3	446.4	446.5	446.6	446.9
155°	456.7	456.6	456.4	456.3	456.2	456.1	456.2	456.2	456.3	456.4	456.8
157.5°	465.5	465.4	465.4	465.4	465.4	465.3	465.2	465.1	465.0	465.0	465.5
160°	470.7	470.6	470.5	470.4	470.3	470.3	470.2	470.1	470.0	469.9	470.4
162.5°	475.6	475.5	475.2	475.1	474.8	474.7	474.6	474.5	474.4	474.3	474.9
165°	481.7	481.4	481.2	480.9	480.7	480.5	480.5	480.4	480.3	480.2	480.9
167.5°	486.4	486.1	485.8	485.4	485.1	484.9	484.9	484.9	484.9	484.9	485.6
170°	489.0	488.7	488.4	488.0	487.7	487.5	487.5	487.5	487.5	487.5	488.2
172.5°	490.7	490.4	490.0	489.6	489.2	489.0	489.1	489.2	489.3	489.3	489.9
175°	493.0	492.6	492.2	491.8	491.4	491.2	491.3	491.4	491.5	491.5	492.1
177.5°	493.6	493.3	492.9	492.6	492.3	492.2	492.3	492.3	492.4	492.4	492.9
180°	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0



TEST NUMBER: P332392-930

CATALOG NUMBER: S123RDIW-S340D460U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	466.5	467.2	468.1	468.3	468.2	468.1	467.9	467.8
5°	463.5	464.2	465.0	465.3	465.1	465.0	464.8	464.6
7.5°	457.0	457.4	457.8	457.9	457.5	457.3	457.0	456.7
10°	451.1	451.2	451.3	451.1	450.7	450.3	449.8	449.4
12.5°	443.8	443.8	443.8	443.4	443.0	442.5	442.0	441.5
15°	431.0	430.6	430.2	429.7	429.2	428.5	428.0	427.4
17.5°	415.9	415.0	414.1	413.2	412.3	411.4	410.6	409.7
20°	405.4	404.3	403.2	402.2	401.1	400.1	399.2	398.1
22.5°	394.3	392.9	391.5	390.4	389.4	388.5	387.5	386.6
25°	375.9	374.2	372.4	371.0	370.1	369.2	368.3	367.4
27.5°	356.0	353.6	351.1	349.2	347.7	346.3	345.0	343.5
30°	341.9	339.0	336.1	334.0	332.6	331.3	330.0	328.6
32.5°	327.9	324.8	321.6	319.4	318.0	316.6	315.1	313.7
35°	307.3	303.6	300.0	297.4	296.0	294.4	292.9	291.4
37.5°	285.1	281.0	276.9	273.9	272.0	270.1	268.2	266.4
40°	269.7	265.3	260.9	257.7	255.8	253.9	251.9	250.0
42.5°	254.9	250.1	245.3	242.1	240.3	238.6	236.8	235.1
45°	233.1	228.3	223.5	220.0	218.1	216.1	214.0	212.0
47.5°	210.6	205.4	200.2	196.7	194.9	193.1	191.2	189.4
50°	195.4	190.2	185.0	181.4	179.4	177.5	175.5	173.6
52.5°	180.8	175.3	169.9	166.3	164.5	162.8	161.1	159.3
55°	158.9	154.0	149.1	145.8	144.1	142.4	140.7	139.0
57.5°	137.4	132.7	128.2	125.1	123.7	122.2	120.8	119.4
60°	123.8	119.3	114.7	111.7	110.3	108.8	107.5	106.0
62.5°	110.4	106.2	101.8	98.9	97.4	96.0	94.4	92.9
65°	91.2	87.2	83.0	80.5	79.5	78.6	77.7	76.7
67.5°	73.0	69.9	66.8	64.7	63.8	62.8	61.8	60.8
70°	61.7	58.8	55.8	53.9	52.9	52.0	51.0	50.1
72.5°	51.5	49.2	46.7	45.3	44.9	44.5	44.2	43.8
75°	38.6	37.7	36.9	36.4	36.2	36.0	35.9	35.7
77.5°	29.1	28.6	28.2	27.9	27.7	27.6	27.4	27.2
80°	23.4	23.2	22.9	22.7	22.5	22.3	22.2	22.0
82.5°	17.9	17.7	17.4	17.3	17.3	17.2	17.2	17.2
85°	10.3	10.1	9.9	9.9	9.9	9.9	9.9	9.9
87.5°	5.7	5.7	5.7	5.7	5.6	5.6	5.5	5.5
90°	9.5	9.8	10.1	10.4	10.5	10.7	10.8	11.0
92.5°	10.4	10.9	11.5	11.7	11.9	12.0	12.1	12.1
95°	12.5	13.0	13.6	13.9	13.9	13.9	13.9	13.9
97.5°	13.1	13.8	14.4	14.8	14.8	14.9	15.0	15.1
100°	13.4	14.0	14.7	15.1	15.2	15.2	15.3	15.4
102.5°	20.1	18.0	16.1	15.1	15.2	15.4	15.5	15.7
105°	51.4	37.0	22.6	15.5	15.7	15.8	16.0	16.1
107.5°	125.9	115.4	104.8	94.1	83.2	72.3	61.5	50.6
110°	159.8	157.1	154.4	147.3	135.7	124.0	112.3	100.8



TEST NUMBER: P332392-930

CATALOG NUMBER: S123RDIW-S340D460U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	183.8	183.8	183.8	182.6	180.2	177.7	175.3	172.8
115°	211.9	212.7	213.5	214.1	214.4	214.7	215.1	215.4
117.5°	237.3	238.0	238.6	239.0	239.0	239.1	239.2	239.3
120°	254.0	254.7	255.4	255.7	255.7	255.7	255.7	255.7
122.5°	270.4	270.8	271.3	271.5	271.6	271.7	271.7	271.8
125°	293.3	293.5	293.7	293.8	294.0	294.2	294.3	294.5
127.5°	316.4	316.7	316.9	317.0	316.8	316.7	316.5	316.3
130°	330.3	330.6	330.9	331.0	330.8	330.7	330.5	330.4
132.5°	343.5	343.8	344.1	344.2	344.0	343.7	343.5	343.3
135°	363.5	363.7	363.9	363.9	363.7	363.5	363.2	363.0
137.5°	381.3	381.6	382.0	382.2	382.0	381.9	381.7	381.6
140°	392.6	392.9	393.2	393.3	393.1	393.0	392.8	392.6
142.5°	403.3	403.6	403.8	403.8	403.6	403.4	403.2	402.9
145°	418.2	418.4	418.6	418.7	418.7	418.7	418.7	418.7
147.5°	431.7	431.9	432.0	431.9	431.5	431.1	430.8	430.4
150°	439.9	440.0	440.2	440.2	439.9	439.7	439.4	439.2
152.5°	447.2	447.4	447.8	447.7	447.4	446.9	446.6	446.2
155°	457.2	457.6	458.0	458.0	457.5	457.0	456.5	456.1
157.5°	465.9	466.4	466.9	466.8	466.2	465.6	465.0	464.3
160°	470.9	471.4	471.9	471.9	471.3	470.8	470.2	469.6
162.5°	475.5	476.1	476.5	476.6	476.1	475.6	475.1	474.6
165°	481.5	482.2	482.8	482.8	482.2	481.8	481.2	480.6
167.5°	486.2	486.8	487.5	487.5	486.8	486.2	485.6	484.9
170°	488.9	489.5	490.2	490.2	489.5	488.9	488.2	487.5
172.5°	490.6	491.2	491.9	491.9	491.1	490.4	489.8	489.0
175°	492.7	493.3	493.8	493.8	493.2	492.5	491.9	491.2
177.5°	493.5	494.0	494.6	494.5	493.8	493.2	492.5	491.9
180°	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0

(END OF REPORT)