

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332418-930

Luminaire Tested: **S123RDIW-S560D1030U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332418-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S560D1030U930-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1030 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5180.7 lumens  
Efficiency: N/A  
Efficacy: 114.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 45.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332418-930

CATALOG NUMBER: S123RDIW-S560D1030U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332418-930

CATALOG NUMBER: S123RDIW-S560D1030U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	31	26
3	79	70	63	58	71	64	58	53	52	48	44	41	38	36	31	29	27	23
4	73	62	55	49	66	57	50	45	46	42	38	37	33	31	27	25	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17
6	62	50	42	37	56	46	39	34	38	33	29	30	26	24	23	20	19	15
7	57	45	38	32	51	41	35	30	34	29	25	27	24	21	21	18	17	14
8	53	41	34	29	48	38	31	27	31	26	23	25	21	19	19	17	15	12
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	14	11
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7851	7851	7851	7851
5°	9360	7886	6944	7886
10°	11687	7840	6274	7840
15°	13718	7759	5721	7759
20°	15309	7640	5251	7640
25°	15064	7514	4962	7514
30°	10828	7398	4666	7398
35°	7230	7247	4473	7247
40°	5327	7065	4274	7065
45°	4468	6745	4078	6745
50°	3944	6328	3806	6328
55°	3459	5849	3434	5849
60°	3078	5393	3147	5393
65°	2705	4898	2929	4898
70°	2121	4463	2675	4463
75°	1871	3897	2441	3897
80°	1630	3310	2399	3310
85°	1309	2655	2544	2655



TEST NUMBER: P332418-930

CATALOG NUMBER: S123RDIW-S560D1030U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.7	1.4
10°-20°	224.1	4.3
20°-30°	352.1	6.8
30°-40°	367.3	7.1
40°-50°	314.4	6.1
50°-60°	239.6	4.6
60°-70°	153.6	3.0
70°-80°	73.9	1.4
80°-90°	22.6	0.4
90°-100°	40.1	0.8
100°-110°	191.0	3.7
110°-120°	458.8	8.9
120°-130°	584.2	11.3
130°-140°	624.2	12.0
140°-150°	583.7	11.3
150°-160°	470.8	9.1
160°-170°	303.9	5.9
170°-180°	104.7	2.0
0°-30°	647.9	12.5
0°-40°	1015.3	19.6
0°-60°	1569.3	30.3
0°-90°	1819.4	35.1
90°-120°	689.8	13.3
90°-150°	2481.9	47.9
90°-180°	3361.0	64.9
0°-180°	5180.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	729	729	729	729	729	
5°	866	730	643	730	866	89
15°	1231	696	513	696	1231	349
25°	1268	633	418	633	1268	545
35°	550	552	340	552	550	361
45°	294	443	268	443	294	231
55°	184	312	183	312	184	167
65°	106	192	115	192	106	104
75°	45	94	59	94	45	48
85°	11	22	21	22	11	13
90°	24	1	24	1	24	11
95°	31	50	31	50	31	26
105°	36	244	36	244	36	82
115°	482	458	482	458	482	445
125°	658	645	658	645	658	588
135°	812	803	812	803	812	626
145°	936	927	936	927	936	584
155°	1020	1021	1020	1021	1020	470
165°	1074	1077	1074	1077	1074	303
175°	1098	1102	1098	1102	1098	105
180°	1102	1102	1102	1102	1102	



TEST NUMBER: P332418-930

CATALOG NUMBER: S123RDIW-S560D1030U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	776.9	778.0	774.7	774.2	770.5	769.5	769.5	764.2	760.9	756.7	754.2
5°	866.3	871.2	868.8	863.2	853.8	851.6	845.6	836.3	825.7	812.5	806.3
7.5°	977.8	984.6	981.9	973.3	963.5	955.5	938.8	923.2	901.5	882.4	866.0
10°	1069.3	1062.0	1056.5	1048.0	1038.9	1024.3	1006.8	982.8	955.0	933.1	908.7
12.5°	1137.7	1136.5	1129.4	1120.7	1107.9	1094.0	1072.4	1043.2	1010.9	979.3	951.5
15°	1231.0	1232.9	1228.2	1219.1	1201.0	1176.3	1143.9	1131.7	1085.5	1051.1	1016.8
17.5°	1295.6	1295.2	1294.5	1282.0	1263.6	1245.9	1215.9	1183.8	1142.0	1093.6	1047.3
20°	1336.5	1333.4	1334.1	1320.0	1306.3	1286.0	1256.6	1210.1	1175.7	1119.8	1072.0
22.5°	1335.5	1334.9	1337.3	1332.4	1322.5	1306.9	1283.9	1244.6	1200.7	1144.3	1090.5
25°	1268.4	1266.0	1280.7	1284.7	1300.6	1303.4	1296.6	1275.0	1233.5	1175.4	1108.9
27.5°	1061.6	1060.2	1087.4	1121.5	1164.8	1198.4	1230.9	1246.5	1233.5	1191.9	1125.3
30°	871.2	900.6	914.4	963.7	1018.6	1084.2	1141.7	1196.3	1209.7	1191.6	1137.0
32.5°	723.3	748.9	760.4	802.8	854.0	930.8	1017.0	1094.4	1149.1	1162.9	1130.0
35°	550.2	550.6	576.7	595.5	642.9	721.9	805.7	909.3	1012.4	1090.5	1098.6
37.5°	439.0	440.6	456.5	475.2	510.8	552.5	626.2	712.4	831.4	951.3	1021.6
40°	379.1	381.9	393.8	412.2	437.8	469.4	526.8	608.0	707.3	840.7	949.7
42.5°	340.6	345.2	351.3	365.5	381.3	410.9	457.4	520.1	610.3	736.5	862.2
45°	293.5	296.0	300.7	307.3	321.6	342.3	373.5	415.6	490.6	592.1	718.0
47.5°	258.9	257.6	262.5	267.9	277.4	291.5	312.4	346.8	400.3	481.7	588.5
50°	235.5	235.1	238.6	242.6	251.7	262.0	279.2	305.1	347.6	415.0	512.7
52.5°	213.4	214.7	217.1	222.2	228.7	237.0	252.4	271.1	307.6	365.8	447.3
55°	184.3	185.2	188.6	191.4	196.1	204.6	214.3	229.8	254.8	295.4	362.6
57.5°	159.5	159.1	162.4	163.1	168.4	175.2	182.7	194.9	213.0	243.1	288.4
60°	143.0	142.1	144.9	147.1	149.9	155.5	161.8	173.7	188.0	210.2	248.9
62.5°	128.0	127.6	129.6	131.8	134.1	139.3	144.6	153.6	165.0	183.7	214.4
65°	106.2	107.1	108.0	109.0	110.2	113.3	118.4	124.6	132.4	145.5	167.7
67.5°	83.4	84.4	84.7	86.6	89.3	91.2	94.3	99.9	105.3	116.3	129.0
70°	67.4	67.1	67.4	68.4	71.8	75.3	79.3	83.4	86.8	94.7	105.3
72.5°	58.0	57.4	58.2	58.4	60.1	61.0	63.6	67.4	71.8	77.1	84.8
75°	45.0	45.0	45.0	45.0	46.2	46.9	47.8	48.8	50.3	52.7	58.4
77.5°	33.3	33.3	33.8	34.0	34.3	34.7	35.2	36.2	36.7	38.1	40.4
80°	26.3	26.6	26.3	26.6	26.6	27.1	27.5	28.5	28.7	30.3	31.2
82.5°	19.7	19.6	19.7	20.1	20.1	20.7	20.7	21.4	21.5	22.3	23.2
85°	10.6	10.0	10.6	10.3	10.9	10.3	10.6	11.3	11.3	11.6	12.8
87.5°	7.4	7.8	7.3	7.4	7.3	7.5	7.3	7.3	7.6	7.2	6.9
90°	24.5	24.2	23.8	23.5	23.1	22.6	21.9	21.1	20.4	19.6	17.3
92.5°	27.1	27.0	26.7	26.5	26.3	25.6	24.5	23.3	22.1	21.0	19.2
95°	31.1	31.1	31.1	31.1	31.1	30.5	29.2	28.0	26.7	25.4	23.4
97.5°	33.8	33.6	33.3	33.2	33.0	32.2	30.7	29.3	27.8	26.3	39.5
100°	34.4	34.2	34.0	33.8	33.7	32.9	31.4	29.9	28.5	27.0	55.4
102.5°	35.1	34.7	34.4	34.1	33.8	35.8	40.4	44.8	49.4	53.9	84.9
105°	36.0	35.6	35.3	35.0	34.6	50.5	82.7	115.0	147.2	179.4	195.8
107.5°	113.2	137.5	161.8	186.0	210.3	234.2	257.9	281.4	305.1	328.7	326.1
110°	225.2	251.2	277.2	303.3	329.3	345.3	351.3	357.3	363.3	369.3	367.3



TEST NUMBER: P332418-930

CATALOG NUMBER: S123RDIW-S560D1030U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	386.4	391.8	397.4	402.8	408.3	411.0	410.9	410.8	410.7	410.6	408.6
115°	481.5	480.8	480.0	479.3	478.6	477.4	475.5	473.7	471.9	470.0	468.4
117.5°	534.9	534.8	534.6	534.4	534.3	533.5	532.1	530.6	529.1	527.7	526.8
120°	571.6	571.6	571.6	571.6	571.6	570.9	569.4	567.9	566.5	565.0	564.5
122.5°	607.6	607.5	607.3	607.2	607.1	606.4	605.4	604.4	603.4	602.3	601.7
125°	658.4	658.0	657.6	657.3	657.0	656.6	656.2	655.8	655.5	655.1	654.4
127.5°	707.2	707.6	707.9	708.3	708.7	708.6	707.9	707.4	706.8	706.2	705.3
130°	738.7	739.0	739.4	739.7	740.1	739.9	739.2	738.5	737.8	737.0	736.3
132.5°	767.4	768.0	768.5	769.0	769.5	769.4	768.7	767.9	767.2	766.5	765.9
135°	811.5	812.0	812.6	813.2	813.7	813.7	813.2	812.6	812.0	811.5	810.8
137.5°	853.0	853.3	853.7	854.0	854.4	854.2	853.3	852.4	851.5	850.7	850.3
140°	877.8	878.2	878.6	879.0	879.3	879.1	878.4	877.7	876.9	876.2	875.6
142.5°	900.7	901.3	901.8	902.3	902.8	902.8	902.2	901.6	901.1	900.4	899.9
145°	936.0	936.0	936.0	936.0	936.0	935.8	935.5	935.1	934.7	934.3	934.0
147.5°	962.2	963.0	963.8	964.7	965.6	965.8	965.4	965.1	964.7	964.3	963.9
150°	981.9	982.4	982.9	983.5	984.1	984.1	983.7	983.4	983.0	982.7	982.3
152.5°	997.6	998.4	999.2	1000.0	1000.9	1001.0	1000.4	999.7	999.1	998.4	998.2
155°	1019.5	1020.6	1021.7	1022.8	1023.9	1024.0	1023.0	1022.1	1021.2	1020.3	1020.2
157.5°	1038.0	1039.4	1040.9	1042.3	1043.7	1043.8	1042.8	1041.7	1040.6	1039.5	1039.7
160°	1049.8	1051.1	1052.4	1053.6	1054.9	1055.0	1053.9	1052.8	1051.7	1050.7	1050.8
162.5°	1060.9	1062.1	1063.2	1064.4	1065.4	1065.4	1064.2	1062.9	1061.7	1060.5	1060.6
165°	1074.4	1075.6	1076.9	1078.2	1079.5	1079.4	1077.9	1076.4	1075.1	1073.6	1073.7
167.5°	1084.0	1085.5	1087.0	1088.4	1089.9	1089.9	1088.4	1087.0	1085.5	1084.0	1084.0
170°	1090.0	1091.4	1092.8	1094.3	1095.8	1095.8	1094.3	1092.8	1091.4	1090.0	1090.0
172.5°	1093.2	1094.8	1096.4	1098.0	1099.6	1099.7	1098.2	1096.8	1095.4	1093.9	1093.7
175°	1098.1	1099.6	1101.1	1102.5	1104.0	1104.1	1102.8	1101.5	1100.2	1098.9	1098.8
177.5°	1099.6	1101.1	1102.5	1104.0	1105.5	1105.5	1104.4	1103.3	1102.1	1100.9	1100.7
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2



TEST NUMBER: P332418-930

CATALOG NUMBER: S123RDIW-S560D1030U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	753.2	752.4	748.9	744.9	739.7	736.2	733.4	732.0	727.5	721.9	718.2
5°	799.7	790.4	780.4	768.2	756.9	745.4	738.3	729.8	719.5	707.9	699.8
7.5°	849.5	831.2	811.4	791.0	770.8	752.7	736.7	723.0	706.6	690.1	678.4
10°	887.8	861.0	833.2	804.7	778.8	754.5	735.7	717.3	697.7	678.6	664.2
12.5°	922.5	887.2	855.2	820.2	787.1	758.0	731.0	709.3	685.7	665.4	649.0
15°	966.5	930.3	891.5	838.5	794.4	757.6	724.8	696.3	667.6	642.7	626.7
17.5°	1007.5	953.1	901.1	856.7	799.6	753.5	713.5	679.5	648.0	621.5	601.9
20°	1024.6	971.8	915.3	858.8	802.6	751.1	704.5	667.0	634.2	604.2	586.1
22.5°	1034.8	975.0	915.5	854.8	795.1	741.5	695.5	654.3	618.7	590.3	567.9
25°	1046.8	975.5	910.0	850.0	789.1	731.0	676.4	632.7	594.3	563.9	540.2
27.5°	1054.6	970.9	893.3	826.7	764.9	707.1	657.0	610.7	571.7	539.6	514.2
30°	1056.1	967.1	880.6	808.5	745.7	692.6	639.5	595.2	554.0	519.9	496.2
32.5°	1058.1	957.9	863.4	786.8	722.5	669.9	621.8	579.4	537.2	503.7	479.5
35°	1049.9	952.8	837.2	749.2	684.9	633.9	590.5	551.5	510.0	477.4	452.8
37.5°	1014.4	932.5	810.1	706.8	639.5	592.4	557.0	523.0	484.9	449.9	426.6
40°	978.7	912.5	789.1	681.1	610.8	562.4	530.5	502.8	465.9	433.1	408.1
42.5°	925.4	885.3	769.2	654.1	578.3	531.7	504.8	478.7	446.5	413.1	389.6
45°	827.9	833.2	728.2	611.1	533.4	486.5	461.2	443.1	414.4	386.9	362.9
47.5°	705.4	755.0	680.2	565.3	486.0	442.0	419.9	404.1	384.7	357.8	335.8
50°	625.5	696.3	641.7	534.6	456.2	412.5	390.7	377.9	361.0	339.7	318.9
52.5°	551.8	627.9	595.3	500.3	424.0	384.0	362.6	352.1	338.8	318.8	299.9
55°	450.0	527.1	519.6	448.7	375.7	339.7	323.5	311.7	302.6	287.6	272.6
57.5°	363.9	437.1	441.0	391.3	333.0	297.6	283.6	274.7	268.7	257.5	243.6
60°	309.8	376.9	390.0	352.5	302.6	271.3	257.6	250.5	245.7	236.7	226.1
62.5°	264.8	322.0	336.8	309.8	273.4	244.1	233.4	226.5	223.3	215.5	206.1
65°	202.7	250.1	264.5	249.5	230.5	207.0	198.3	192.3	189.6	185.2	178.3
67.5°	152.4	187.0	202.8	192.2	185.3	170.5	164.9	161.8	159.2	156.3	150.5
70°	122.4	148.1	164.3	161.4	155.8	148.1	144.0	141.8	139.3	136.8	131.8
72.5°	98.4	116.0	131.3	132.7	128.1	126.5	122.9	122.1	120.5	117.6	114.8
75°	65.3	77.5	88.1	92.1	94.0	95.6	94.0	93.7	93.4	90.9	89.3
77.5°	42.8	49.3	56.0	62.9	65.9	68.0	68.5	69.6	68.8	67.5	66.8
80°	32.8	34.3	39.1	45.0	49.7	51.5	52.7	53.4	53.1	52.7	51.5
82.5°	23.8	25.1	27.3	31.5	35.4	38.6	39.3	39.1	39.9	40.0	39.1
85°	12.8	13.1	13.8	14.3	16.6	20.0	21.0	21.5	22.2	22.2	20.3
87.5°	7.0	6.3	6.3	5.9	6.3	6.1	7.3	8.2	8.8	8.2	8.5
90°	14.9	12.6	10.2	8.1	6.3	4.5	2.6	0.8	2.6	4.5	6.3
92.5°	17.4	15.7	13.9	13.2	13.7	14.2	14.8	15.2	14.8	14.2	13.7
95°	21.4	19.4	17.4	20.1	27.6	35.1	42.5	50.0	42.5	35.1	27.6
97.5°	52.6	65.7	78.8	87.0	90.3	93.7	97.0	100.4	97.0	93.7	90.3
100°	83.8	112.2	140.6	153.0	149.3	145.7	142.0	138.4	142.0	145.7	149.3
102.5°	115.9	146.9	177.9	192.1	189.5	186.9	184.3	181.6	184.3	186.9	189.5
105°	212.1	228.4	244.8	252.0	250.1	248.0	246.1	244.0	246.1	248.0	250.1
107.5°	323.5	321.0	318.4	316.3	314.7	313.1	311.4	309.9	311.4	313.1	314.7
110°	365.3	363.3	361.3	359.5	358.2	356.7	355.2	353.8	355.2	356.7	358.2





TEST NUMBER: P332418-930

CATALOG NUMBER: S123RDIW-S560D1030U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	406.6	404.6	402.6	401.0	399.7	398.3	397.0	395.7	397.0	398.3	399.7
115°	466.8	465.1	463.5	462.1	461.1	459.9	458.9	457.8	458.9	459.9	461.1
117.5°	526.0	525.2	524.3	523.3	521.9	520.6	519.2	517.9	519.2	520.6	521.9
120°	563.9	563.4	562.9	561.7	560.1	558.5	556.8	555.2	556.8	558.5	560.1
122.5°	601.0	600.3	599.6	598.6	597.2	595.9	594.5	593.2	594.5	595.9	597.2
125°	653.6	652.9	652.2	651.1	649.6	648.2	646.8	645.3	646.8	648.2	649.6
127.5°	704.5	703.6	702.7	701.6	700.1	698.6	697.2	695.7	697.2	698.6	700.1
130°	735.6	734.8	734.1	733.0	731.6	730.1	728.6	727.2	728.6	730.1	731.6
132.5°	765.3	764.8	764.2	763.1	761.7	760.2	758.8	757.3	758.8	760.2	761.7
135°	810.1	809.3	808.6	807.7	806.6	805.5	804.5	803.3	804.5	805.5	806.6
137.5°	849.9	849.5	849.1	848.2	846.8	845.4	844.0	842.6	844.0	845.4	846.8
140°	875.1	874.6	874.0	873.2	872.1	871.1	869.9	868.9	869.9	871.1	872.1
142.5°	899.4	898.8	898.3	897.5	896.3	895.3	894.1	893.1	894.1	895.3	896.3
145°	933.6	933.3	932.9	932.1	930.8	929.5	928.2	927.0	928.2	929.5	930.8
147.5°	963.6	963.2	962.9	962.3	961.4	960.6	959.8	959.0	959.8	960.6	961.4
150°	981.9	981.5	981.2	980.7	980.2	979.7	979.1	978.6	979.1	979.7	980.2
152.5°	997.9	997.8	997.5	997.3	997.0	996.8	996.5	996.3	996.5	996.8	997.0
155°	1019.9	1019.8	1019.6	1019.7	1020.1	1020.4	1020.8	1021.2	1020.8	1020.4	1020.1
157.5°	1039.8	1040.1	1040.2	1040.3	1040.4	1040.4	1040.5	1040.5	1040.5	1040.4	1040.4
160°	1051.0	1051.2	1051.3	1051.6	1051.7	1051.9	1052.1	1052.3	1052.1	1051.9	1051.7
162.5°	1060.9	1061.0	1061.2	1061.5	1062.0	1062.5	1062.9	1063.4	1062.9	1062.5	1062.0
165°	1073.9	1074.1	1074.3	1074.6	1075.2	1075.8	1076.3	1076.8	1076.3	1075.8	1075.2
167.5°	1084.0	1084.0	1084.0	1084.4	1085.2	1085.9	1086.6	1087.3	1086.6	1085.9	1085.2
170°	1090.0	1090.0	1090.0	1090.3	1091.0	1091.8	1092.5	1093.2	1092.5	1091.8	1091.0
172.5°	1093.6	1093.4	1093.3	1093.6	1094.5	1095.4	1096.3	1097.1	1096.3	1095.4	1094.5
175°	1098.6	1098.4	1098.2	1098.6	1099.5	1100.4	1101.3	1102.2	1101.3	1100.4	1099.5
177.5°	1100.7	1100.5	1100.3	1100.7	1101.4	1102.1	1102.8	1103.5	1102.8	1102.1	1101.4
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2



TEST NUMBER: P332418-930

CATALOG NUMBER: S123RDIW-S560D1030U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	717.0	713.7	711.5	706.5	703.3	699.8	696.3	698.5	698.2	698.0	698.0
5°	692.9	685.7	679.2	670.7	665.4	658.9	653.9	653.3	654.5	650.1	647.7
7.5°	669.1	659.3	650.0	640.7	630.8	622.9	618.0	615.7	612.5	609.8	607.0
10°	652.3	640.8	631.7	620.2	609.6	600.2	594.3	590.2	588.0	585.8	581.8
12.5°	635.1	623.8	612.2	599.2	589.1	578.2	573.8	569.2	565.0	562.6	557.0
15°	609.8	595.2	583.0	569.2	558.1	547.4	541.2	532.1	530.8	527.7	522.1
17.5°	584.6	568.7	551.9	541.7	529.0	518.0	508.4	505.4	496.4	493.1	488.2
20°	564.6	549.9	537.1	523.7	505.2	495.0	487.5	483.4	476.2	471.8	468.7
22.5°	547.4	532.4	517.6	502.0	486.7	475.2	469.7	463.4	459.5	453.4	450.0
25°	522.8	506.5	488.7	471.8	460.9	452.2	443.4	437.8	432.2	429.3	423.1
27.5°	494.2	477.2	460.6	447.8	434.3	425.7	417.8	412.8	406.0	401.3	397.9
30°	478.4	458.4	444.1	432.5	415.3	407.2	401.3	395.0	390.0	385.1	381.6
32.5°	460.2	441.9	428.3	414.0	400.8	392.0	384.3	378.8	374.5	369.8	366.4
35°	431.5	416.3	402.2	387.8	378.1	369.1	360.0	355.4	351.3	346.9	343.8
37.5°	405.7	391.4	378.1	364.4	352.5	345.0	337.8	334.2	328.7	325.8	322.6
40°	389.7	375.7	361.3	348.2	335.7	330.1	323.5	318.2	313.2	311.0	307.6
42.5°	372.3	358.2	346.1	331.9	321.7	314.1	308.0	302.2	298.5	295.3	293.3
45°	346.3	333.8	322.0	307.9	298.2	291.6	284.8	279.5	276.1	273.9	270.4
47.5°	321.1	308.7	296.6	284.4	275.0	267.5	260.7	256.9	252.4	249.7	247.4
50°	302.9	291.6	278.8	267.6	258.3	250.8	245.2	240.4	236.4	232.9	231.4
52.5°	286.2	274.2	263.1	252.7	242.8	234.2	229.2	224.2	221.2	217.2	215.4
55°	258.5	247.0	237.7	227.3	217.7	210.5	204.2	199.8	196.7	192.3	189.9
57.5°	232.6	222.3	211.1	202.2	192.2	186.1	180.9	175.0	171.2	167.8	165.3
60°	215.2	203.3	193.6	185.2	176.4	168.6	164.0	159.2	155.2	151.7	149.6
62.5°	196.9	186.5	177.4	168.2	160.2	153.4	148.0	144.0	140.5	138.3	136.1
65°	168.9	160.9	151.5	144.0	136.5	131.5	127.1	123.7	121.2	119.6	117.7
67.5°	143.2	135.3	127.2	119.8	114.8	111.0	108.1	105.2	104.0	101.9	100.7
70°	126.5	118.4	111.2	105.6	100.5	97.8	95.9	93.7	92.5	89.9	88.7
72.5°	108.3	102.4	97.2	92.5	88.5	86.0	83.6	81.0	78.9	76.2	74.9
75°	85.3	80.0	75.9	72.7	70.3	66.9	63.4	60.6	59.7	58.7	58.4
77.5°	63.1	59.8	56.8	54.2	51.1	48.6	47.9	47.2	47.0	46.6	46.6
80°	49.7	46.6	44.4	41.3	39.4	39.4	39.4	38.7	39.1	39.1	39.1
82.5°	36.9	34.0	32.9	31.7	31.4	31.6	31.6	31.7	31.6	32.0	31.8
85°	19.1	19.3	20.0	19.6	20.0	20.0	20.6	20.3	20.6	20.0	20.6
87.5°	8.6	9.8	10.5	11.3	12.0	12.1	12.6	12.7	13.1	13.3	13.4
90°	8.1	10.2	12.6	14.9	17.3	19.6	20.4	21.1	21.9	22.6	23.1
92.5°	13.2	13.9	15.7	17.4	19.2	21.0	22.1	23.3	24.5	25.6	26.3
95°	20.1	17.4	19.4	21.4	23.4	25.4	26.7	28.0	29.2	30.5	31.1
97.5°	87.0	78.8	65.7	52.6	39.5	26.3	27.8	29.3	30.7	32.2	33.0
100°	153.0	140.6	112.2	83.8	55.4	27.0	28.5	29.9	31.4	32.9	33.7
102.5°	192.1	177.9	146.9	115.9	84.9	53.9	49.4	44.8	40.4	35.8	33.8
105°	252.0	244.8	228.4	212.1	195.8	179.4	147.2	115.0	82.7	50.5	34.6
107.5°	316.3	318.4	321.0	323.5	326.1	328.7	305.1	281.4	257.9	234.2	210.3
110°	359.5	361.3	363.3	365.3	367.3	369.3	363.3	357.3	351.3	345.3	329.3



TEST NUMBER: P332418-930

CATALOG NUMBER: S123RDIW-S560D1030U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	401.0	402.6	404.6	406.6	408.6	410.6	410.7	410.8	410.9	411.0	408.3
115°	462.1	463.5	465.1	466.8	468.4	470.0	471.9	473.7	475.5	477.4	478.6
117.5°	523.3	524.3	525.2	526.0	526.8	527.7	529.1	530.6	532.1	533.5	534.3
120°	561.7	562.9	563.4	563.9	564.5	565.0	566.5	567.9	569.4	570.9	571.6
122.5°	598.6	599.6	600.3	601.0	601.7	602.3	603.4	604.4	605.4	606.4	607.1
125°	651.1	652.2	652.9	653.6	654.4	655.1	655.5	655.8	656.2	656.6	657.0
127.5°	701.6	702.7	703.6	704.5	705.3	706.2	706.8	707.4	707.9	708.6	708.7
130°	733.0	734.1	734.8	735.6	736.3	737.0	737.8	738.5	739.2	739.9	740.1
132.5°	763.1	764.2	764.8	765.3	765.9	766.5	767.2	767.9	768.7	769.4	769.5
135°	807.7	808.6	809.3	810.1	810.8	811.5	812.0	812.6	813.2	813.7	813.7
137.5°	848.2	849.1	849.5	849.9	850.3	850.7	851.5	852.4	853.3	854.2	854.4
140°	873.2	874.0	874.6	875.1	875.6	876.2	876.9	877.7	878.4	879.1	879.3
142.5°	897.5	898.3	898.8	899.4	899.9	900.4	901.1	901.6	902.2	902.8	902.8
145°	932.1	932.9	933.3	933.6	934.0	934.3	934.7	935.1	935.5	935.8	936.0
147.5°	962.3	962.9	963.2	963.6	963.9	964.3	964.7	965.1	965.4	965.8	965.6
150°	980.7	981.2	981.5	981.9	982.3	982.7	983.0	983.4	983.7	984.1	984.1
152.5°	997.3	997.5	997.8	997.9	998.2	998.4	999.1	999.7	1000.4	1001.0	1000.9
155°	1019.7	1019.6	1019.8	1019.9	1020.2	1020.3	1021.2	1022.1	1023.0	1024.0	1023.9
157.5°	1040.3	1040.2	1040.1	1039.8	1039.7	1039.5	1040.6	1041.7	1042.8	1043.8	1043.7
160°	1051.6	1051.3	1051.2	1051.0	1050.8	1050.7	1051.7	1052.8	1053.9	1055.0	1054.9
162.5°	1061.5	1061.2	1061.0	1060.9	1060.6	1060.5	1061.7	1062.9	1064.2	1065.4	1065.4
165°	1074.6	1074.3	1074.1	1073.9	1073.7	1073.6	1075.1	1076.4	1077.9	1079.4	1079.5
167.5°	1084.4	1084.0	1084.0	1084.0	1084.0	1084.0	1085.5	1087.0	1088.4	1089.9	1089.9
170°	1090.3	1090.0	1090.0	1090.0	1090.0	1090.0	1091.4	1092.8	1094.3	1095.8	1095.8
172.5°	1093.6	1093.3	1093.4	1093.6	1093.7	1093.9	1095.4	1096.8	1098.2	1099.7	1099.6
175°	1098.6	1098.2	1098.4	1098.6	1098.8	1098.9	1100.2	1101.5	1102.8	1104.1	1104.0
177.5°	1100.7	1100.3	1100.5	1100.7	1100.7	1100.9	1102.1	1103.3	1104.4	1105.5	1105.5
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2



TEST NUMBER: P332418-930

CATALOG NUMBER: S123RDIW-S560D1030U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	695.0	694.7	695.0	694.0	695.0	694.7	695.0	698.0	698.0	698.2	698.5
5°	646.7	646.4	645.5	642.7	645.5	646.4	646.7	647.7	650.1	654.5	653.3
7.5°	604.5	604.1	601.4	601.4	601.4	604.1	604.5	607.0	609.8	612.5	615.7
10°	579.6	579.9	576.2	574.0	576.2	579.9	579.6	581.8	585.8	588.0	590.2
12.5°	555.4	553.9	550.9	548.5	550.9	553.9	555.4	557.0	562.6	565.0	569.2
15°	523.3	520.2	512.7	513.4	512.7	520.2	523.3	522.1	527.7	530.8	532.1
17.5°	485.7	483.4	483.3	478.9	483.3	483.4	485.7	488.2	493.1	496.4	505.4
20°	463.7	462.2	462.8	458.4	462.8	462.2	463.7	468.7	471.8	476.2	483.4
22.5°	446.5	444.9	442.3	440.9	442.3	444.9	446.5	450.0	453.4	459.5	463.4
25°	421.3	418.7	416.3	417.8	416.3	418.7	421.3	423.1	429.3	432.2	437.8
27.5°	396.0	394.1	391.7	391.3	391.7	394.1	396.0	397.9	401.3	406.0	412.8
30°	380.0	378.1	376.9	375.4	376.9	378.1	380.0	381.6	385.1	390.0	395.0
32.5°	363.8	363.5	361.2	360.9	361.2	363.5	363.8	366.4	369.8	374.5	378.8
35°	342.6	340.7	340.1	340.4	340.1	340.7	342.6	343.8	346.9	351.3	355.4
37.5°	322.4	319.9	318.8	317.6	318.8	319.9	322.4	322.6	325.8	328.7	334.2
40°	307.9	305.4	304.8	304.2	304.8	305.4	307.9	307.6	311.0	313.2	318.2
42.5°	291.6	290.7	290.3	289.2	290.3	290.7	291.6	293.3	295.3	298.5	302.2
45°	269.5	269.2	267.3	267.9	267.3	269.2	269.5	270.4	273.9	276.1	279.5
47.5°	246.1	244.8	243.4	244.3	243.4	244.8	246.1	247.4	249.7	252.4	256.9
50°	230.2	229.5	226.7	227.3	226.7	229.5	230.2	231.4	232.9	236.4	240.4
52.5°	214.2	211.8	210.8	210.3	210.8	211.8	214.2	215.4	217.2	221.2	224.2
55°	187.7	184.8	183.6	183.0	183.6	184.8	187.7	189.9	192.3	196.7	199.8
57.5°	161.7	160.9	160.0	160.6	160.0	160.9	161.7	165.3	167.8	171.2	175.0
60°	146.4	146.4	146.4	146.2	146.4	146.4	146.4	149.6	151.7	155.2	159.2
62.5°	134.7	134.0	133.7	134.1	133.7	134.0	134.7	136.1	138.3	140.5	144.0
65°	116.8	116.5	115.2	115.0	115.2	116.5	116.8	117.7	119.6	121.2	123.7
67.5°	99.9	98.7	98.4	97.9	98.4	98.7	99.9	100.7	101.9	104.0	105.2
70°	87.2	86.5	84.6	85.0	84.6	86.5	87.2	88.7	89.9	92.5	93.7
72.5°	73.4	72.7	72.4	71.9	72.4	72.7	73.4	74.9	76.2	78.9	81.0
75°	58.0	57.8	57.5	58.7	57.5	57.8	58.0	58.4	58.7	59.7	60.6
77.5°	46.6	46.6	46.7	46.2	46.7	46.6	46.6	46.6	46.6	47.0	47.2
80°	39.1	39.1	38.7	38.7	38.7	39.1	39.1	39.1	39.1	39.1	38.7
82.5°	31.3	31.6	31.7	31.2	31.7	31.6	31.3	31.8	32.0	31.6	31.7
85°	20.6	20.3	21.0	20.6	21.0	20.3	20.6	20.6	20.0	20.6	20.3
87.5°	13.9	13.5	13.6	13.9	13.6	13.5	13.9	13.4	13.3	13.1	12.7
90°	23.5	23.8	24.2	24.5	24.2	23.8	23.5	23.1	22.6	21.9	21.1
92.5°	26.5	26.7	27.0	27.1	27.0	26.7	26.5	26.3	25.6	24.5	23.3
95°	31.1	31.1	31.1	31.1	31.1	31.1	31.1	31.1	30.5	29.2	28.0
97.5°	33.2	33.3	33.6	33.8	33.6	33.3	33.2	33.0	32.2	30.7	29.3
100°	33.8	34.0	34.2	34.4	34.2	34.0	33.8	33.7	32.9	31.4	29.9
102.5°	34.1	34.4	34.7	35.1	34.7	34.4	34.1	33.8	35.8	40.4	44.8
105°	35.0	35.3	35.6	36.0	35.6	35.3	35.0	34.6	50.5	82.7	115.0
107.5°	186.0	161.8	137.5	113.2	137.5	161.8	186.0	210.3	234.2	257.9	281.4
110°	303.3	277.2	251.2	225.2	251.2	277.2	303.3	329.3	345.3	351.3	357.3



TEST NUMBER: P332418-930

CATALOG NUMBER: S123RDIW-S560D1030U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	402.8	397.4	391.8	386.4	391.8	397.4	402.8	408.3	411.0	410.9	410.8
115°	479.3	480.0	480.8	481.5	480.8	480.0	479.3	478.6	477.4	475.5	473.7
117.5°	534.4	534.6	534.8	534.9	534.8	534.6	534.4	534.3	533.5	532.1	530.6
120°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	570.9	569.4	567.9
122.5°	607.2	607.3	607.5	607.6	607.5	607.3	607.2	607.1	606.4	605.4	604.4
125°	657.3	657.6	658.0	658.4	658.0	657.6	657.3	657.0	656.6	656.2	655.8
127.5°	708.3	707.9	707.6	707.2	707.6	707.9	708.3	708.7	708.6	707.9	707.4
130°	739.7	739.4	739.0	738.7	739.0	739.4	739.7	740.1	739.9	739.2	738.5
132.5°	769.0	768.5	768.0	767.4	768.0	768.5	769.0	769.5	769.4	768.7	767.9
135°	813.2	812.6	812.0	811.5	812.0	812.6	813.2	813.7	813.7	813.2	812.6
137.5°	854.0	853.7	853.3	853.0	853.3	853.7	854.0	854.4	854.2	853.3	852.4
140°	879.0	878.6	878.2	877.8	878.2	878.6	879.0	879.3	879.1	878.4	877.7
142.5°	902.3	901.8	901.3	900.7	901.3	901.8	902.3	902.8	902.8	902.2	901.6
145°	936.0	936.0	936.0	936.0	936.0	936.0	936.0	936.0	935.8	935.5	935.1
147.5°	964.7	963.8	963.0	962.2	963.0	963.8	964.7	965.6	965.8	965.4	965.1
150°	983.5	982.9	982.4	981.9	982.4	982.9	983.5	984.1	984.1	983.7	983.4
152.5°	1000.0	999.2	998.4	997.6	998.4	999.2	1000.0	1000.9	1001.0	1000.4	999.7
155°	1022.8	1021.7	1020.6	1019.5	1020.6	1021.7	1022.8	1023.9	1024.0	1023.0	1022.1
157.5°	1042.3	1040.9	1039.4	1038.0	1039.4	1040.9	1042.3	1043.7	1043.8	1042.8	1041.7
160°	1053.6	1052.4	1051.1	1049.8	1051.1	1052.4	1053.6	1054.9	1055.0	1053.9	1052.8
162.5°	1064.4	1063.2	1062.1	1060.9	1062.1	1063.2	1064.4	1065.4	1065.4	1064.2	1062.9
165°	1078.2	1076.9	1075.6	1074.4	1075.6	1076.9	1078.2	1079.5	1079.4	1077.9	1076.4
167.5°	1088.4	1087.0	1085.5	1084.0	1085.5	1087.0	1088.4	1089.9	1089.9	1088.4	1087.0
170°	1094.3	1092.8	1091.4	1090.0	1091.4	1092.8	1094.3	1095.8	1095.8	1094.3	1092.8
172.5°	1098.0	1096.4	1094.8	1093.2	1094.8	1096.4	1098.0	1099.6	1099.7	1098.2	1096.8
175°	1102.5	1101.1	1099.6	1098.1	1099.6	1101.1	1102.5	1104.0	1104.1	1102.8	1101.5
177.5°	1104.0	1102.5	1101.1	1099.6	1101.1	1102.5	1104.0	1105.5	1105.5	1104.4	1103.3
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2



TEST NUMBER: P332418-930

CATALOG NUMBER: S123RDIW-S560D1030U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	696.3	699.8	703.3	706.5	711.5	713.7	717.0	718.2	721.9	727.5	732.0
5°	653.9	658.9	665.4	670.7	679.2	685.7	692.9	699.8	707.9	719.5	729.8
7.5°	618.0	622.9	630.8	640.7	650.0	659.3	669.1	678.4	690.1	706.6	723.0
10°	594.3	600.2	609.6	620.2	631.7	640.8	652.3	664.2	678.6	697.7	717.3
12.5°	573.8	578.2	589.1	599.2	612.2	623.8	635.1	649.0	665.4	685.7	709.3
15°	541.2	547.4	558.1	569.2	583.0	595.2	609.8	626.7	642.7	667.6	696.3
17.5°	508.4	518.0	529.0	541.7	551.9	568.7	584.6	601.9	621.5	648.0	679.5
20°	487.5	495.0	505.2	523.7	537.1	549.9	564.6	586.1	604.2	634.2	667.0
22.5°	469.7	475.2	486.7	502.0	517.6	532.4	547.4	567.9	590.3	618.7	654.3
25°	443.4	452.2	460.9	471.8	488.7	506.5	522.8	540.2	563.9	594.3	632.7
27.5°	417.8	425.7	434.3	447.8	460.6	477.2	494.2	514.2	539.6	571.7	610.7
30°	401.3	407.2	415.3	432.5	444.1	458.4	478.4	496.2	519.9	554.0	595.2
32.5°	384.3	392.0	400.8	414.0	428.3	441.9	460.2	479.5	503.7	537.2	579.4
35°	360.0	369.1	378.1	387.8	402.2	416.3	431.5	452.8	477.4	510.0	551.5
37.5°	337.8	345.0	352.5	364.4	378.1	391.4	405.7	426.6	449.9	484.9	523.0
40°	323.5	330.1	335.7	348.2	361.3	375.7	389.7	408.1	433.1	465.9	502.8
42.5°	308.0	314.1	321.7	331.9	346.1	358.2	372.3	389.6	413.1	446.5	478.7
45°	284.8	291.6	298.2	307.9	322.0	333.8	346.3	362.9	386.9	414.4	443.1
47.5°	260.7	267.5	275.0	284.4	296.6	308.7	321.1	335.8	357.8	384.7	404.1
50°	245.2	250.8	258.3	267.6	278.8	291.6	302.9	318.9	339.7	361.0	377.9
52.5°	229.2	234.2	242.8	252.7	263.1	274.2	286.2	299.9	318.8	338.8	352.1
55°	204.2	210.5	217.7	227.3	237.7	247.0	258.5	272.6	287.6	302.6	311.7
57.5°	180.9	186.1	192.2	202.2	211.1	222.3	232.6	243.6	257.5	268.7	274.7
60°	164.0	168.6	176.4	185.2	193.6	203.3	215.2	226.1	236.7	245.7	250.5
62.5°	148.0	153.4	160.2	168.2	177.4	186.5	196.9	206.1	215.5	223.3	226.5
65°	127.1	131.5	136.5	144.0	151.5	160.9	168.9	178.3	185.2	189.6	192.3
67.5°	108.1	111.0	114.8	119.8	127.2	135.3	143.2	150.5	156.3	159.2	161.8
70°	95.9	97.8	100.5	105.6	111.2	118.4	126.5	131.8	136.8	139.3	141.8
72.5°	83.6	86.0	88.5	92.5	97.2	102.4	108.3	114.8	117.6	120.5	122.1
75°	63.4	66.9	70.3	72.7	75.9	80.0	85.3	89.3	90.9	93.4	93.7
77.5°	47.9	48.6	51.1	54.2	56.8	59.8	63.1	66.8	67.5	68.8	69.6
80°	39.4	39.4	39.4	41.3	44.4	46.6	49.7	51.5	52.7	53.1	53.4
82.5°	31.6	31.6	31.4	31.7	32.9	34.0	36.9	39.1	40.0	39.9	39.1
85°	20.6	20.0	20.0	19.6	20.0	19.3	19.1	20.3	22.2	22.2	21.5
87.5°	12.6	12.1	12.0	11.3	10.5	9.8	8.6	8.5	8.2	8.8	8.2
90°	20.4	19.6	17.3	14.9	12.6	10.2	8.1	6.3	4.5	2.6	0.8
92.5°	22.1	21.0	19.2	17.4	15.7	13.9	13.2	13.7	14.2	14.8	15.2
95°	26.7	25.4	23.4	21.4	19.4	17.4	20.1	27.6	35.1	42.5	50.0
97.5°	27.8	26.3	39.5	52.6	65.7	78.8	87.0	90.3	93.7	97.0	100.4
100°	28.5	27.0	55.4	83.8	112.2	140.6	153.0	149.3	145.7	142.0	138.4
102.5°	49.4	53.9	84.9	115.9	146.9	177.9	192.1	189.5	186.9	184.3	181.6
105°	147.2	179.4	195.8	212.1	228.4	244.8	252.0	250.1	248.0	246.1	244.0
107.5°	305.1	328.7	326.1	323.5	321.0	318.4	316.3	314.7	313.1	311.4	309.9
110°	363.3	369.3	367.3	365.3	363.3	361.3	359.5	358.2	356.7	355.2	353.8



TEST NUMBER: P332418-930

CATALOG NUMBER: S123RDIW-S560D1030U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	410.7	410.6	408.6	406.6	404.6	402.6	401.0	399.7	398.3	397.0	395.7
115°	471.9	470.0	468.4	466.8	465.1	463.5	462.1	461.1	459.9	458.9	457.8
117.5°	529.1	527.7	526.8	526.0	525.2	524.3	523.3	521.9	520.6	519.2	517.9
120°	566.5	565.0	564.5	563.9	563.4	562.9	561.7	560.1	558.5	556.8	555.2
122.5°	603.4	602.3	601.7	601.0	600.3	599.6	598.6	597.2	595.9	594.5	593.2
125°	655.5	655.1	654.4	653.6	652.9	652.2	651.1	649.6	648.2	646.8	645.3
127.5°	706.8	706.2	705.3	704.5	703.6	702.7	701.6	700.1	698.6	697.2	695.7
130°	737.8	737.0	736.3	735.6	734.8	734.1	733.0	731.6	730.1	728.6	727.2
132.5°	767.2	766.5	765.9	765.3	764.8	764.2	763.1	761.7	760.2	758.8	757.3
135°	812.0	811.5	810.8	810.1	809.3	808.6	807.7	806.6	805.5	804.5	803.3
137.5°	851.5	850.7	850.3	849.9	849.5	849.1	848.2	846.8	845.4	844.0	842.6
140°	876.9	876.2	875.6	875.1	874.6	874.0	873.2	872.1	871.1	869.9	868.9
142.5°	901.1	900.4	899.9	899.4	898.8	898.3	897.5	896.3	895.3	894.1	893.1
145°	934.7	934.3	934.0	933.6	933.3	932.9	932.1	930.8	929.5	928.2	927.0
147.5°	964.7	964.3	963.9	963.6	963.2	962.9	962.3	961.4	960.6	959.8	959.0
150°	983.0	982.7	982.3	981.9	981.5	981.2	980.7	980.2	979.7	979.1	978.6
152.5°	999.1	998.4	998.2	997.9	997.8	997.5	997.3	997.0	996.8	996.5	996.3
155°	1021.2	1020.3	1020.2	1019.9	1019.8	1019.6	1019.7	1020.1	1020.4	1020.8	1021.2
157.5°	1040.6	1039.5	1039.7	1039.8	1040.1	1040.2	1040.3	1040.4	1040.4	1040.5	1040.5
160°	1051.7	1050.7	1050.8	1051.0	1051.2	1051.3	1051.6	1051.7	1051.9	1052.1	1052.3
162.5°	1061.7	1060.5	1060.6	1060.9	1061.0	1061.2	1061.5	1062.0	1062.5	1062.9	1063.4
165°	1075.1	1073.6	1073.7	1073.9	1074.1	1074.3	1074.6	1075.2	1075.8	1076.3	1076.8
167.5°	1085.5	1084.0	1084.0	1084.0	1084.0	1084.0	1084.4	1085.2	1085.9	1086.6	1087.3
170°	1091.4	1090.0	1090.0	1090.0	1090.0	1090.0	1090.3	1091.0	1091.8	1092.5	1093.2
172.5°	1095.4	1093.9	1093.7	1093.6	1093.4	1093.3	1093.6	1094.5	1095.4	1096.3	1097.1
175°	1100.2	1098.9	1098.8	1098.6	1098.4	1098.2	1098.6	1099.5	1100.4	1101.3	1102.2
177.5°	1102.1	1100.9	1100.7	1100.7	1100.5	1100.3	1100.7	1101.4	1102.1	1102.8	1103.5
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2



TEST NUMBER: P332418-930

CATALOG NUMBER: S123RDIW-S560D1030U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	733.4	736.2	739.7	744.9	748.9	752.4	753.2	754.2	756.7	760.9	764.2
5°	738.3	745.4	756.9	768.2	780.4	790.4	799.7	806.3	812.5	825.7	836.3
7.5°	736.7	752.7	770.8	791.0	811.4	831.2	849.5	866.0	882.4	901.5	923.2
10°	735.7	754.5	778.8	804.7	833.2	861.0	887.8	908.7	933.1	955.0	982.8
12.5°	731.0	758.0	787.1	820.2	855.2	887.2	922.5	951.5	979.3	1010.9	1043.2
15°	724.8	757.6	794.4	838.5	891.5	930.3	966.5	1016.8	1051.1	1085.5	1131.7
17.5°	713.5	753.5	799.6	856.7	901.1	953.1	1007.5	1047.3	1093.6	1142.0	1183.8
20°	704.5	751.1	802.6	858.8	915.3	971.8	1024.6	1072.0	1119.8	1175.7	1210.1
22.5°	695.5	741.5	795.1	854.8	915.5	975.0	1034.8	1090.5	1144.3	1200.7	1244.6
25°	676.4	731.0	789.1	850.0	910.0	975.5	1046.8	1108.9	1175.4	1233.5	1275.0
27.5°	657.0	707.1	764.9	826.7	893.3	970.9	1054.6	1125.3	1191.9	1233.5	1246.5
30°	639.5	692.6	745.7	808.5	880.6	967.1	1056.1	1137.0	1191.6	1209.7	1196.3
32.5°	621.8	669.9	722.5	786.8	863.4	957.9	1058.1	1130.0	1162.9	1149.1	1094.4
35°	590.5	633.9	684.9	749.2	837.2	952.8	1049.9	1098.6	1090.5	1012.4	909.3
37.5°	557.0	592.4	639.5	706.8	810.1	932.5	1014.4	1021.6	951.3	831.4	712.4
40°	530.5	562.4	610.8	681.1	789.1	912.5	978.7	949.7	840.7	707.3	608.0
42.5°	504.8	531.7	578.3	654.1	769.2	885.3	925.4	862.2	736.5	610.3	520.1
45°	461.2	486.5	533.4	611.1	728.2	833.2	827.9	718.0	592.1	490.6	415.6
47.5°	419.9	442.0	486.0	565.3	680.2	755.0	705.4	588.5	481.7	400.3	346.8
50°	390.7	412.5	456.2	534.6	641.7	696.3	625.5	512.7	415.0	347.6	305.1
52.5°	362.6	384.0	424.0	500.3	595.3	627.9	551.8	447.3	365.8	307.6	271.1
55°	323.5	339.7	375.7	448.7	519.6	527.1	450.0	362.6	295.4	254.8	229.8
57.5°	283.6	297.6	333.0	391.3	441.0	437.1	363.9	288.4	243.1	213.0	194.9
60°	257.6	271.3	302.6	352.5	390.0	376.9	309.8	248.9	210.2	188.0	173.7
62.5°	233.4	244.1	273.4	309.8	336.8	322.0	264.8	214.4	183.7	165.0	153.6
65°	198.3	207.0	230.5	249.5	264.5	250.1	202.7	167.7	145.5	132.4	124.6
67.5°	164.9	170.5	185.3	192.2	202.8	187.0	152.4	129.0	116.3	105.3	99.9
70°	144.0	148.1	155.8	161.4	164.3	148.1	122.4	105.3	94.7	86.8	83.4
72.5°	122.9	126.5	128.1	132.7	131.3	116.0	98.4	84.8	77.1	71.8	67.4
75°	94.0	95.6	94.0	92.1	88.1	77.5	65.3	58.4	52.7	50.3	48.8
77.5°	68.5	68.0	65.9	62.9	56.0	49.3	42.8	40.4	38.1	36.7	36.2
80°	52.7	51.5	49.7	45.0	39.1	34.3	32.8	31.2	30.3	28.7	28.5
82.5°	39.3	38.6	35.4	31.5	27.3	25.1	23.8	23.2	22.3	21.5	21.4
85°	21.0	20.0	16.6	14.3	13.8	13.1	12.8	12.8	11.6	11.3	11.3
87.5°	7.3	6.1	6.3	5.9	6.3	6.3	7.0	6.9	7.2	7.6	7.3
90°	2.6	4.5	6.3	8.1	10.2	12.6	14.9	17.3	19.6	20.4	21.1
92.5°	14.8	14.2	13.7	13.2	13.9	15.7	17.4	19.2	21.0	22.1	23.3
95°	42.5	35.1	27.6	20.1	17.4	19.4	21.4	23.4	25.4	26.7	28.0
97.5°	97.0	93.7	90.3	87.0	78.8	65.7	52.6	39.5	26.3	27.8	29.3
100°	142.0	145.7	149.3	153.0	140.6	112.2	83.8	55.4	27.0	28.5	29.9
102.5°	184.3	186.9	189.5	192.1	177.9	146.9	115.9	84.9	53.9	49.4	44.8
105°	246.1	248.0	250.1	252.0	244.8	228.4	212.1	195.8	179.4	147.2	115.0
107.5°	311.4	313.1	314.7	316.3	318.4	321.0	323.5	326.1	328.7	305.1	281.4
110°	355.2	356.7	358.2	359.5	361.3	363.3	365.3	367.3	369.3	363.3	357.3





TEST NUMBER: P332418-930

CATALOG NUMBER: S123RDIW-S560D1030U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	397.0	398.3	399.7	401.0	402.6	404.6	406.6	408.6	410.6	410.7	410.8
115°	458.9	459.9	461.1	462.1	463.5	465.1	466.8	468.4	470.0	471.9	473.7
117.5°	519.2	520.6	521.9	523.3	524.3	525.2	526.0	526.8	527.7	529.1	530.6
120°	556.8	558.5	560.1	561.7	562.9	563.4	563.9	564.5	565.0	566.5	567.9
122.5°	594.5	595.9	597.2	598.6	599.6	600.3	601.0	601.7	602.3	603.4	604.4
125°	646.8	648.2	649.6	651.1	652.2	652.9	653.6	654.4	655.1	655.5	655.8
127.5°	697.2	698.6	700.1	701.6	702.7	703.6	704.5	705.3	706.2	706.8	707.4
130°	728.6	730.1	731.6	733.0	734.1	734.8	735.6	736.3	737.0	737.8	738.5
132.5°	758.8	760.2	761.7	763.1	764.2	764.8	765.3	765.9	766.5	767.2	767.9
135°	804.5	805.5	806.6	807.7	808.6	809.3	810.1	810.8	811.5	812.0	812.6
137.5°	844.0	845.4	846.8	848.2	849.1	849.5	849.9	850.3	850.7	851.5	852.4
140°	869.9	871.1	872.1	873.2	874.0	874.6	875.1	875.6	876.2	876.9	877.7
142.5°	894.1	895.3	896.3	897.5	898.3	898.8	899.4	899.9	900.4	901.1	901.6
145°	928.2	929.5	930.8	932.1	932.9	933.3	933.6	934.0	934.3	934.7	935.1
147.5°	959.8	960.6	961.4	962.3	962.9	963.2	963.6	963.9	964.3	964.7	965.1
150°	979.1	979.7	980.2	980.7	981.2	981.5	981.9	982.3	982.7	983.0	983.4
152.5°	996.5	996.8	997.0	997.3	997.5	997.8	997.9	998.2	998.4	999.1	999.7
155°	1020.8	1020.4	1020.1	1019.7	1019.6	1019.8	1019.9	1020.2	1020.3	1021.2	1022.1
157.5°	1040.5	1040.4	1040.4	1040.3	1040.2	1040.1	1039.8	1039.7	1039.5	1040.6	1041.7
160°	1052.1	1051.9	1051.7	1051.6	1051.3	1051.2	1051.0	1050.8	1050.7	1051.7	1052.8
162.5°	1062.9	1062.5	1062.0	1061.5	1061.2	1061.0	1060.9	1060.6	1060.5	1061.7	1062.9
165°	1076.3	1075.8	1075.2	1074.6	1074.3	1074.1	1073.9	1073.7	1073.6	1075.1	1076.4
167.5°	1086.6	1085.9	1085.2	1084.4	1084.0	1084.0	1084.0	1084.0	1084.0	1085.5	1087.0
170°	1092.5	1091.8	1091.0	1090.3	1090.0	1090.0	1090.0	1090.0	1090.0	1091.4	1092.8
172.5°	1096.3	1095.4	1094.5	1093.6	1093.3	1093.4	1093.6	1093.7	1093.9	1095.4	1096.8
175°	1101.3	1100.4	1099.5	1098.6	1098.2	1098.4	1098.6	1098.8	1098.9	1100.2	1101.5
177.5°	1102.8	1102.1	1101.4	1100.7	1100.3	1100.5	1100.7	1100.7	1100.9	1102.1	1103.3
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2



TEST NUMBER: P332418-930

CATALOG NUMBER: S123RDIW-S560D1030U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	729.4	729.4	729.4	729.4	729.4	729.4	729.4
2.5°	769.5	769.5	770.5	774.2	774.7	778.0	776.9
5°	845.6	851.6	853.8	863.2	868.8	871.2	866.3
7.5°	938.8	955.5	963.5	973.3	981.9	984.6	977.8
10°	1006.8	1024.3	1038.9	1048.0	1056.5	1062.0	1069.3
12.5°	1072.4	1094.0	1107.9	1120.7	1129.4	1136.5	1137.7
15°	1143.9	1176.3	1201.0	1219.1	1228.2	1232.9	1231.0
17.5°	1215.9	1245.9	1263.6	1282.0	1294.5	1295.2	1295.6
20°	1256.6	1286.0	1306.3	1320.0	1334.1	1333.4	1336.5
22.5°	1283.9	1306.9	1322.5	1332.4	1337.3	1334.9	1335.5
25°	1296.6	1303.4	1300.6	1284.7	1280.7	1266.0	1268.4
27.5°	1230.9	1198.4	1164.8	1121.5	1087.4	1060.2	1061.6
30°	1141.7	1084.2	1018.6	963.7	914.4	900.6	871.2
32.5°	1017.0	930.8	854.0	802.8	760.4	748.9	723.3
35°	805.7	721.9	642.9	595.5	576.7	550.6	550.2
37.5°	626.2	552.5	510.8	475.2	456.5	440.6	439.0
40°	526.8	469.4	437.8	412.2	393.8	381.9	379.1
42.5°	457.4	410.9	381.3	365.5	351.3	345.2	340.6
45°	373.5	342.3	321.6	307.3	300.7	296.0	293.5
47.5°	312.4	291.5	277.4	267.9	262.5	257.6	258.9
50°	279.2	262.0	251.7	242.6	238.6	235.1	235.5
52.5°	252.4	237.0	228.7	222.2	217.1	214.7	213.4
55°	214.3	204.6	196.1	191.4	188.6	185.2	184.3
57.5°	182.7	175.2	168.4	163.1	162.4	159.1	159.5
60°	161.8	155.5	149.9	147.1	144.9	142.1	143.0
62.5°	144.6	139.3	134.1	131.8	129.6	127.6	128.0
65°	118.4	113.3	110.2	109.0	108.0	107.1	106.2
67.5°	94.3	91.2	89.3	86.6	84.7	84.4	83.4
70°	79.3	75.3	71.8	68.4	67.4	67.1	67.4
72.5°	63.6	61.0	60.1	58.4	58.2	57.4	58.0
75°	47.8	46.9	46.2	45.0	45.0	45.0	45.0
77.5°	35.2	34.7	34.3	34.0	33.8	33.3	33.3
80°	27.5	27.1	26.6	26.6	26.3	26.6	26.3
82.5°	20.7	20.7	20.1	20.1	19.7	19.6	19.7
85°	10.6	10.3	10.9	10.3	10.6	10.0	10.6
87.5°	7.3	7.5	7.3	7.4	7.3	7.8	7.4
90°	21.9	22.6	23.1	23.5	23.8	24.2	24.5
92.5°	24.5	25.6	26.3	26.5	26.7	27.0	27.1
95°	29.2	30.5	31.1	31.1	31.1	31.1	31.1
97.5°	30.7	32.2	33.0	33.2	33.3	33.6	33.8
100°	31.4	32.9	33.7	33.8	34.0	34.2	34.4
102.5°	40.4	35.8	33.8	34.1	34.4	34.7	35.1
105°	82.7	50.5	34.6	35.0	35.3	35.6	36.0
107.5°	257.9	234.2	210.3	186.0	161.8	137.5	113.2
110°	351.3	345.3	329.3	303.3	277.2	251.2	225.2



TEST NUMBER: P332418-930

CATALOG NUMBER: S123RDIW-S560D1030U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	410.9	411.0	408.3	402.8	397.4	391.8	386.4
115°	475.5	477.4	478.6	479.3	480.0	480.8	481.5
117.5°	532.1	533.5	534.3	534.4	534.6	534.8	534.9
120°	569.4	570.9	571.6	571.6	571.6	571.6	571.6
122.5°	605.4	606.4	607.1	607.2	607.3	607.5	607.6
125°	656.2	656.6	657.0	657.3	657.6	658.0	658.4
127.5°	707.9	708.6	708.7	708.3	707.9	707.6	707.2
130°	739.2	739.9	740.1	739.7	739.4	739.0	738.7
132.5°	768.7	769.4	769.5	769.0	768.5	768.0	767.4
135°	813.2	813.7	813.7	813.2	812.6	812.0	811.5
137.5°	853.3	854.2	854.4	854.0	853.7	853.3	853.0
140°	878.4	879.1	879.3	879.0	878.6	878.2	877.8
142.5°	902.2	902.8	902.8	902.3	901.8	901.3	900.7
145°	935.5	935.8	936.0	936.0	936.0	936.0	936.0
147.5°	965.4	965.8	965.6	964.7	963.8	963.0	962.2
150°	983.7	984.1	984.1	983.5	982.9	982.4	981.9
152.5°	1000.4	1001.0	1000.9	1000.0	999.2	998.4	997.6
155°	1023.0	1024.0	1023.9	1022.8	1021.7	1020.6	1019.5
157.5°	1042.8	1043.8	1043.7	1042.3	1040.9	1039.4	1038.0
160°	1053.9	1055.0	1054.9	1053.6	1052.4	1051.1	1049.8
162.5°	1064.2	1065.4	1065.4	1064.4	1063.2	1062.1	1060.9
165°	1077.9	1079.4	1079.5	1078.2	1076.9	1075.6	1074.4
167.5°	1088.4	1089.9	1089.9	1088.4	1087.0	1085.5	1084.0
170°	1094.3	1095.8	1095.8	1094.3	1092.8	1091.4	1090.0
172.5°	1098.2	1099.7	1099.6	1098.0	1096.4	1094.8	1093.2
175°	1102.8	1104.1	1104.0	1102.5	1101.1	1099.6	1098.1
177.5°	1104.4	1105.5	1105.5	1104.0	1102.5	1101.1	1099.6
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2

(END OF REPORT)