

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332485-840

Luminaire Tested: **S123RDIW-S1165D1320U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332485-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D1320U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9046.2 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332485-840

CATALOG NUMBER: S123RDIW-S1165D1320U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332485-840

CATALOG NUMBER: S123RDIW-S1165D1320U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	87	90	86	83	80	73	71	69	61	59	58	49	48	47	42
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40	36
3	82	72	65	60	75	67	61	56	57	52	48	48	44	41	39	37	35	30
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	26
5	69	57	49	44	63	53	46	41	46	40	36	38	34	31	32	29	26	23
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	20
7	59	47	39	33	54	43	36	32	37	32	28	32	27	24	26	23	21	18
8	55	42	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	22	19	17	15
10	47	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	15	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21068	21068	21068
5°	21149	20857	20977
10°	21029	20595	20525
15°	20803	20113	19900
20°	20492	19511	19057
25°	20173	18834	18231
30°	19750	18053	17066
35°	19316	17270	16000
40°	18916	16350	14677
45°	18389	15440	13484
50°	17811	14408	12149
55°	17220	13226	10903
60°	16678	11961	9535
65°	15969	10593	8166
70°	15087	8894	6593
75°	13795	6995	6209
80°	12298	6199	5709
85°	10387	5483	5101



TEST NUMBER: P332485-840

CATALOG NUMBER: S123RDIW-S1165D1320U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	2.0
10°-20°	511.4	5.7
20°-30°	736.4	8.1
30°-40°	829.4	9.2
40°-50°	793.5	8.8
50°-60°	649.8	7.2
60°-70°	438.4	4.8
70°-80°	220.6	2.4
80°-90°	63.3	0.7
90°-100°	108.6	1.2
100°-110°	325.1	3.6
110°-120°	553.0	6.1
120°-130°	727.3	8.0
130°-140°	817.5	9.0
140°-150°	803.6	8.9
150°-160°	676.5	7.5
160°-170°	450.3	5.0
170°-180°	157.7	1.7
0°-30°	1431.6	15.8
0°-40°	2261.0	25.0
0°-60°	3704.3	40.9
0°-90°	4426.6	48.9
90°-120°	986.7	10.9
90°-150°	3335.1	36.9
90°-180°	4620.0	51.1
0°-180°	9046.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1957	1957	1957	1957	1957	
5°	1957	1949	1930	1944	1941	186
15°	1867	1848	1805	1797	1786	526
25°	1698	1657	1586	1553	1535	781
35°	1470	1411	1314	1248	1218	920
45°	1208	1134	1014	927	886	932
55°	918	837	705	616	581	822
65°	627	538	416	342	321	620
75°	332	255	168	153	149	354
85°	84	51	44	41	41	94
90°	1	15	31	37	39	9
95°	77	87	97	102	102	87
105°	295	298	309	309	312	316
115°	557	560	558	559	558	551
125°	815	818	816	811	806	726
135°	1057	1064	1064	1058	1056	814
145°	1282	1285	1289	1287	1282	801
155°	1468	1468	1470	1474	1466	676
165°	1599	1596	1595	1602	1594	451
175°	1663	1658	1658	1665	1657	158
180°	1667	1667	1667	1667	1667	



TEST NUMBER: P332485-840

CATALOG NUMBER: S123RDIW-S1165D1320U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1963.7	1962.5	1961.4	1960.2	1959.1	1956.8	1953.5	1950.0	1946.7	1943.3	1946.4
5°	1957.3	1955.5	1953.8	1952.0	1950.3	1947.2	1943.0	1938.7	1934.5	1930.3	1933.5
7.5°	1939.1	1937.3	1935.4	1933.5	1931.6	1927.8	1922.4	1916.8	1911.4	1905.8	1907.6
10°	1924.0	1921.5	1919.0	1916.5	1914.1	1909.7	1903.3	1896.9	1890.6	1884.3	1884.6
12.5°	1902.4	1899.7	1896.8	1894.1	1891.4	1886.1	1878.3	1870.6	1862.8	1855.0	1854.8
15°	1866.8	1862.9	1859.1	1855.1	1851.3	1844.4	1834.5	1824.6	1814.7	1804.9	1803.1
17.5°	1822.0	1817.6	1813.0	1808.5	1804.0	1795.4	1782.9	1770.3	1757.8	1745.2	1741.5
20°	1789.0	1783.4	1777.8	1772.1	1766.5	1757.0	1743.5	1730.1	1716.7	1703.3	1698.7
22.5°	1752.2	1745.7	1739.2	1732.7	1726.3	1715.9	1701.6	1687.4	1673.1	1658.8	1653.1
25°	1698.5	1689.7	1680.9	1672.0	1663.2	1650.7	1634.5	1618.3	1602.0	1585.8	1578.4
27.5°	1633.5	1623.8	1614.0	1604.3	1594.5	1580.6	1562.6	1544.5	1526.4	1508.3	1498.0
30°	1589.0	1578.4	1567.8	1557.2	1546.7	1531.5	1511.8	1492.0	1472.3	1452.5	1440.5
32.5°	1544.6	1532.6	1520.6	1508.5	1496.6	1480.2	1459.3	1438.4	1417.4	1396.6	1383.5
35°	1470.0	1457.2	1444.5	1431.9	1419.2	1401.9	1380.0	1358.2	1336.3	1314.3	1299.2
37.5°	1394.4	1380.3	1366.1	1352.0	1338.0	1319.2	1295.9	1272.5	1249.2	1225.8	1208.6
40°	1346.2	1330.6	1315.0	1299.6	1284.0	1263.7	1238.7	1213.7	1188.6	1163.6	1145.2
42.5°	1291.5	1276.0	1260.5	1245.0	1229.4	1208.7	1182.9	1156.9	1131.0	1105.2	1085.1
45°	1208.0	1192.1	1176.3	1160.4	1144.5	1123.0	1095.8	1068.6	1041.5	1014.3	994.2
47.5°	1124.5	1107.1	1089.6	1072.3	1054.8	1032.5	1005.3	978.2	951.0	923.9	902.0
50°	1063.6	1047.0	1030.4	1013.8	997.2	974.7	946.1	917.6	889.0	860.4	838.5
52.5°	1009.0	991.0	973.0	955.0	937.0	913.8	885.6	857.3	829.0	800.7	778.0
55°	917.6	900.2	882.9	865.7	848.4	824.8	794.8	764.8	734.8	704.8	684.4
57.5°	833.0	814.3	795.4	776.6	757.7	733.3	703.2	673.0	642.9	612.8	593.4
60°	774.7	755.3	735.9	716.5	697.0	672.7	643.4	614.2	584.9	555.6	536.5
62.5°	716.2	696.8	677.4	658.0	638.6	614.3	585.0	555.7	526.4	497.2	479.3
65°	627.0	607.6	588.2	568.9	549.5	525.9	498.5	470.9	443.4	415.9	398.6
67.5°	537.9	518.2	498.6	479.0	459.4	436.4	410.0	383.5	357.2	330.8	317.9
70°	479.4	460.4	441.3	422.2	403.2	381.3	356.7	331.9	307.3	282.6	270.2
72.5°	421.0	402.2	383.4	364.7	345.9	325.3	302.9	280.4	258.0	235.6	225.5
75°	331.7	314.9	297.9	280.9	264.1	245.9	226.5	207.0	187.6	168.2	164.7
77.5°	250.4	235.2	219.8	204.6	189.2	175.3	162.9	150.4	137.8	125.4	123.5
80°	198.4	184.0	169.5	155.0	140.6	129.7	122.2	114.8	107.4	100.0	99.0
82.5°	148.9	136.4	123.9	111.4	99.0	91.0	87.6	84.0	80.6	77.2	76.0
85°	84.1	76.3	68.6	60.9	53.1	48.7	47.7	46.6	45.5	44.4	43.7
87.5°	30.7	28.2	25.7	23.1	20.6	19.8	20.5	21.3	22.0	22.8	22.7
90°	1.3	4.2	7.2	10.0	12.9	16.3	20.1	23.8	27.7	31.4	32.6
92.5°	31.7	33.6	35.6	37.7	39.6	41.7	43.8	45.9	48.2	50.3	51.2
95°	77.3	79.3	81.4	83.4	85.4	87.7	90.0	92.3	94.6	96.9	98.1
97.5°	137.2	138.8	140.3	141.8	143.3	144.9	146.6	148.2	150.0	151.7	153.0
100°	178.1	179.9	181.6	183.4	185.1	186.7	188.1	189.7	191.1	192.6	193.4
102.5°	225.3	226.3	227.4	228.4	229.4	231.0	232.9	234.8	236.7	238.6	239.5
105°	294.7	295.3	295.9	296.4	297.0	298.6	301.2	303.9	306.5	309.1	309.1
107.5°	375.4	375.8	376.1	376.5	376.8	377.5	378.5	379.6	380.6	381.6	382.6
110°	425.7	426.3	426.9	427.4	428.0	428.6	429.2	429.8	430.3	430.9	432.1



TEST NUMBER: P332485-840

CATALOG NUMBER: S123RDIW-S1165D1320U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	478.1	478.4	478.8	479.1	479.5	479.7	479.8	479.9	480.1	480.2	481.6
115°	556.6	557.5	558.4	559.3	560.2	560.3	559.7	559.2	558.6	558.0	558.3
117.5°	635.8	636.3	636.9	637.5	638.1	638.0	637.2	636.5	635.7	635.0	634.9
120°	685.0	686.7	688.5	690.2	692.0	692.2	690.6	689.2	687.8	686.3	686.0
122.5°	736.4	737.6	738.9	740.2	741.4	741.7	740.9	740.2	739.4	738.7	737.9
125°	814.7	815.6	816.4	817.3	818.2	818.3	817.7	817.2	816.6	816.0	814.9
127.5°	887.0	888.9	890.7	892.5	894.4	895.0	894.4	893.7	893.1	892.5	890.8
130°	935.1	937.5	939.9	942.2	944.5	945.2	944.3	943.5	942.6	941.7	940.6
132.5°	983.4	985.7	988.1	990.4	992.7	993.5	992.9	992.3	991.6	991.0	989.6
135°	1057.0	1058.7	1060.5	1062.2	1064.0	1064.7	1064.4	1064.1	1063.8	1063.5	1062.4
137.5°	1125.1	1126.5	1128.0	1129.4	1130.9	1132.1	1132.8	1133.6	1134.3	1135.1	1133.8
140°	1172.3	1173.7	1175.2	1176.6	1178.1	1178.9	1179.2	1179.5	1179.8	1180.1	1179.8
142.5°	1215.2	1216.7	1218.1	1219.6	1221.0	1222.0	1222.5	1223.0	1223.6	1224.2	1223.9
145°	1282.2	1282.8	1283.4	1284.0	1284.5	1285.4	1286.2	1287.1	1288.0	1288.8	1288.5
147.5°	1340.9	1342.0	1343.0	1344.1	1345.1	1346.0	1346.9	1347.7	1348.5	1349.3	1349.3
150°	1381.8	1382.4	1383.0	1383.5	1384.1	1384.7	1385.3	1385.8	1386.4	1387.0	1387.0
152.5°	1415.3	1416.1	1416.9	1417.7	1418.6	1419.2	1419.6	1419.9	1420.3	1420.6	1421.1
155°	1468.2	1468.2	1468.2	1468.2	1468.2	1468.4	1468.6	1468.9	1469.3	1469.6	1470.8
157.5°	1513.3	1513.0	1512.6	1512.3	1511.9	1511.9	1512.1	1512.3	1512.6	1512.8	1514.0
160°	1541.6	1541.1	1540.4	1539.8	1539.2	1538.9	1538.9	1538.9	1538.9	1538.9	1540.4
162.5°	1566.7	1565.9	1565.1	1564.3	1563.5	1563.2	1563.5	1563.7	1563.9	1564.1	1565.6
165°	1599.2	1598.3	1597.5	1596.6	1595.8	1595.3	1595.3	1595.3	1595.3	1595.3	1597.0
167.5°	1625.2	1624.0	1622.9	1621.6	1620.5	1620.0	1620.2	1620.5	1620.7	1620.9	1622.8
170°	1639.8	1638.7	1637.5	1636.4	1635.2	1634.6	1634.6	1634.6	1634.6	1634.6	1636.6
172.5°	1651.3	1650.2	1649.0	1647.9	1646.7	1646.1	1646.1	1646.1	1646.1	1646.1	1647.9
175°	1663.4	1662.2	1661.1	1659.9	1658.7	1658.2	1658.2	1658.2	1658.2	1658.2	1659.9
177.5°	1668.4	1667.5	1666.5	1665.6	1664.7	1664.2	1664.2	1664.2	1664.2	1664.2	1665.6
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4



TEST NUMBER: P332485-840

CATALOG NUMBER: S123RDIW-S1165D1320U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1949.5	1952.7	1955.7	1957.0	1956.4	1955.9	1955.3	1954.7
5°	1936.6	1939.8	1943.0	1944.2	1943.5	1942.8	1942.1	1941.4
7.5°	1909.4	1911.2	1912.9	1913.2	1912.0	1910.8	1909.6	1908.3
10°	1885.0	1885.3	1885.7	1885.0	1883.2	1881.5	1879.7	1877.9
12.5°	1854.6	1854.4	1854.2	1853.1	1851.1	1849.0	1846.9	1844.9
15°	1801.4	1799.6	1797.9	1795.7	1793.2	1790.8	1788.3	1785.8
17.5°	1737.8	1733.9	1730.2	1726.6	1722.8	1719.2	1715.6	1711.8
20°	1694.1	1689.5	1685.0	1680.5	1676.3	1672.0	1667.9	1663.7
22.5°	1647.4	1641.7	1636.0	1631.1	1627.2	1623.3	1619.3	1615.4
25°	1571.0	1563.6	1556.2	1550.5	1546.7	1542.8	1538.9	1535.0
27.5°	1487.7	1477.4	1467.1	1459.1	1453.1	1447.2	1441.3	1435.3
30°	1428.5	1416.5	1404.5	1395.7	1390.1	1384.4	1378.8	1373.1
32.5°	1370.4	1357.3	1344.1	1334.6	1328.7	1322.7	1316.9	1310.9
35°	1284.0	1268.9	1253.7	1242.9	1236.6	1230.2	1223.9	1217.6
37.5°	1191.3	1174.2	1156.9	1144.4	1136.6	1128.7	1121.0	1113.1
40°	1126.9	1108.5	1090.3	1077.0	1068.8	1060.8	1052.7	1044.5
42.5°	1065.1	1045.0	1025.0	1011.4	1004.1	996.8	989.6	982.3
45°	974.1	954.0	933.9	919.7	911.2	902.7	894.2	885.8
47.5°	880.1	858.3	836.4	821.7	814.2	806.6	799.0	791.5
50°	816.7	794.8	772.8	757.9	749.8	741.6	733.6	725.5
52.5°	755.3	732.6	709.8	694.8	687.5	680.3	673.1	665.8
55°	663.9	643.4	623.0	609.3	602.2	595.1	588.0	581.0
57.5°	574.1	554.7	535.4	522.7	516.7	510.8	504.7	498.8
60°	517.5	498.5	479.4	466.9	460.9	454.8	448.9	442.9
62.5°	461.3	443.4	425.5	413.4	407.1	400.8	394.6	388.3
65°	381.3	364.1	346.8	336.2	332.3	328.4	324.6	320.6
67.5°	305.0	292.1	279.1	270.6	266.5	262.3	258.1	254.0
70°	257.8	245.5	233.2	225.1	221.2	217.3	213.4	209.5
72.5°	215.4	205.3	195.2	189.3	187.7	186.1	184.5	182.9
75°	161.2	157.6	154.1	152.1	151.4	150.7	150.0	149.3
77.5°	121.6	119.7	117.8	116.4	115.7	115.0	114.3	113.6
80°	97.9	96.8	95.7	94.9	94.2	93.5	92.8	92.1
82.5°	75.0	74.0	72.9	72.3	72.2	72.0	71.9	71.8
85°	43.0	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	22.7	22.6	22.6	22.5	22.3	22.1	22.0	21.8
90°	33.7	34.9	36.1	37.0	37.6	38.2	38.7	39.3
92.5°	52.1	53.1	54.0	54.3	53.9	53.6	53.2	52.9
95°	99.3	100.4	101.6	102.2	102.2	102.2	102.2	102.2
97.5°	154.3	155.7	157.0	157.6	157.5	157.4	157.3	157.1
100°	194.3	195.1	196.0	196.7	197.3	197.9	198.5	199.0
102.5°	240.3	241.3	242.2	242.5	242.4	242.3	242.2	242.1
105°	309.1	309.1	309.1	309.4	310.0	310.5	311.1	311.7
107.5°	383.5	384.5	385.4	385.7	385.4	385.0	384.7	384.3
110°	433.2	434.4	435.6	435.9	435.3	434.7	434.1	433.5



TEST NUMBER: P332485-840

CATALOG NUMBER: S123RDIW-S1165D1320U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	482.9	484.3	485.7	486.4	486.3	486.1	486.0	485.9
115°	558.6	558.9	559.2	559.2	558.9	558.6	558.3	558.0
117.5°	634.9	634.8	634.7	634.3	633.5	632.7	631.9	631.1
120°	685.7	685.5	685.2	684.7	684.2	683.6	683.0	682.4
122.5°	737.2	736.4	735.7	734.9	734.1	733.3	732.5	731.6
125°	813.6	812.5	811.3	810.2	809.0	807.8	806.7	805.5
127.5°	889.2	887.6	886.0	884.4	883.1	881.8	880.5	879.1
130°	939.4	938.3	937.1	935.4	933.4	931.4	929.4	927.4
132.5°	988.2	986.7	985.4	983.9	982.3	980.8	979.2	977.7
135°	1061.2	1060.1	1058.8	1058.0	1057.4	1056.8	1056.2	1055.7
137.5°	1132.6	1131.4	1130.1	1129.0	1127.9	1126.8	1125.7	1124.6
140°	1179.5	1179.2	1178.9	1177.8	1175.8	1173.7	1171.6	1169.6
142.5°	1223.6	1223.2	1222.9	1222.0	1220.4	1218.9	1217.3	1215.8
145°	1288.2	1288.0	1287.7	1287.0	1285.8	1284.5	1283.4	1282.2
147.5°	1349.3	1349.3	1349.3	1348.5	1346.8	1344.9	1343.2	1341.5
150°	1387.0	1387.0	1387.0	1386.1	1384.4	1382.7	1380.9	1379.2
152.5°	1421.5	1422.0	1422.4	1421.9	1420.4	1418.9	1417.3	1415.8
155°	1471.9	1473.1	1474.2	1473.8	1471.8	1469.8	1467.6	1465.6
157.5°	1515.2	1516.4	1517.7	1517.4	1515.8	1514.2	1512.6	1511.0
160°	1541.9	1543.4	1544.8	1545.0	1543.8	1542.7	1541.5	1540.2
162.5°	1567.0	1568.5	1569.9	1569.7	1567.9	1566.0	1564.2	1562.3
165°	1598.8	1600.5	1602.3	1602.2	1600.1	1598.1	1596.0	1594.0
167.5°	1624.6	1626.4	1628.2	1628.2	1626.4	1624.6	1622.8	1620.9
170°	1638.7	1640.7	1642.7	1642.7	1640.7	1638.7	1636.6	1634.6
172.5°	1649.7	1651.5	1653.4	1653.3	1651.2	1649.1	1647.1	1645.1
175°	1661.6	1663.4	1665.2	1665.0	1662.9	1660.9	1658.9	1656.9
177.5°	1667.0	1668.4	1669.8	1669.7	1668.0	1666.4	1664.8	1663.1
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4

(END OF REPORT)