

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332424-930

Luminaire Tested: **S123RDIW-S560D1320U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332424-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S560D1320U930-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1320 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6046.7 lumens  
Efficiency: N/A  
Efficacy: 112.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332424-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332424-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31
2	85	78	72	67	76	70	65	61	55	52	49	42	39	38	29	28	27
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20
5	65	54	46	41	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	41	35	54	44	37	32	35	30	26	27	23	21	19	17	15
7	55	44	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11
10	44	33	26	21	40	30	24	20	24	20	16	19	15	13	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8289	8289	8289
5°	8321	8206	8253
10°	8273	8103	8075
15°	8184	7913	7830
20°	8062	7676	7497
25°	7936	7410	7172
30°	7771	7102	6714
35°	7599	6795	6294
40°	7442	6433	5774
45°	7234	6075	5305
50°	7006	5668	4779
55°	6775	5204	4290
60°	6562	4706	3750
65°	6283	4167	3212
70°	5936	3500	2593
75°	5427	2753	2441
80°	4841	2442	2244
85°	4088	2149	2001



TEST NUMBER: P332424-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.3	1.2
10°-20°	201.2	3.3
20°-30°	289.7	4.8
30°-40°	326.3	5.4
40°-50°	312.2	5.2
50°-60°	255.7	4.2
60°-70°	172.5	2.9
70°-80°	86.8	1.4
80°-90°	26.9	0.4
90°-100°	51.3	0.8
100°-110°	244.5	4.0
110°-120°	587.3	9.7
120°-130°	747.9	12.4
130°-140°	799.1	13.2
140°-150°	747.2	12.4
150°-160°	602.7	10.0
160°-170°	389.0	6.4
170°-180°	134.1	2.2
0°-30°	563.2	9.3
0°-40°	889.5	14.7
0°-60°	1457.4	24.1
0°-90°	1743.6	28.8
90°-120°	883.1	14.6
90°-150°	3177.3	52.5
90°-180°	4303.0	71.2
0°-180°	6046.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	770	770	770	770	770	
5°	770	767	760	765	764	73
15°	734	727	710	707	703	207
25°	668	652	624	611	604	307
35°	578	555	517	491	479	362
45°	475	446	399	365	348	367
55°	361	329	277	242	229	324
65°	247	212	164	134	126	244
75°	130	100	66	60	59	139
85°	33	20	17	16	16	37
90°	1	12	25	29	32	5
95°	64	24	32	40	40	79
105°	312	318	230	54	46	331
115°	586	592	602	612	616	578
125°	826	834	839	841	843	737
135°	1028	1035	1039	1042	1039	791
145°	1187	1194	1196	1198	1198	743
155°	1307	1305	1306	1311	1305	602
165°	1379	1376	1374	1382	1375	389
175°	1411	1406	1407	1413	1406	134
180°	1411	1411	1411	1411	1411	



TEST NUMBER: P332424-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1
2.5°	772.6	772.1	771.7	771.2	770.8	769.9	768.6	767.2	765.9	764.6	765.8
5°	770.1	769.4	768.7	768.0	767.3	766.1	764.4	762.8	761.1	759.5	760.7
7.5°	763.0	762.2	761.4	760.7	759.9	758.5	756.4	754.2	752.0	749.8	750.5
10°	756.9	755.9	755.0	754.0	753.1	751.3	748.9	746.3	743.8	741.4	741.4
12.5°	748.4	747.4	746.2	745.2	744.1	742.1	739.0	736.0	732.9	729.9	729.8
15°	734.4	733.0	731.4	729.9	728.4	725.6	721.8	717.9	714.0	710.1	709.4
17.5°	716.8	715.1	713.3	711.5	709.7	706.4	701.4	696.5	691.5	686.6	685.2
20°	703.8	701.6	699.4	697.2	695.0	691.2	685.9	680.7	675.4	670.1	668.3
22.5°	689.3	686.8	684.3	681.7	679.1	675.1	669.4	663.8	658.3	652.6	650.4
25°	668.2	664.8	661.3	657.9	654.4	649.5	643.0	636.7	630.3	623.9	621.0
27.5°	642.6	638.8	635.0	631.1	627.3	621.8	614.7	607.6	600.5	593.5	589.4
30°	625.2	621.0	616.9	612.7	608.5	602.5	594.8	587.0	579.2	571.4	566.7
32.5°	607.6	603.0	598.3	593.5	588.8	582.4	574.1	565.9	557.7	549.4	544.3
35°	578.3	573.3	568.3	563.4	558.3	551.5	542.9	534.3	525.7	517.1	511.1
37.5°	548.6	543.1	537.5	531.9	526.4	519.0	509.8	500.7	491.5	482.2	475.5
40°	529.6	523.5	517.4	511.3	505.2	497.2	487.4	477.5	467.7	457.8	450.5
42.5°	508.1	502.0	495.9	489.8	483.7	475.6	465.4	455.2	445.0	434.8	426.9
45°	475.2	469.0	462.8	456.6	450.3	441.8	431.1	420.4	409.8	399.1	391.2
47.5°	442.4	435.5	428.7	421.8	415.0	406.3	395.5	384.8	374.1	363.5	354.9
50°	418.4	411.9	405.4	398.8	392.3	383.4	372.2	361.0	349.8	338.5	329.9
52.5°	397.0	389.9	382.8	375.7	368.7	359.5	348.4	337.3	326.1	315.0	306.1
55°	361.0	354.2	347.4	340.6	333.8	324.5	312.7	300.9	289.1	277.3	269.2
57.5°	327.8	320.3	312.9	305.5	298.1	288.5	276.6	264.8	252.9	241.1	233.5
60°	304.8	297.2	289.5	281.8	274.3	264.6	253.2	241.7	230.1	218.6	211.1
62.5°	281.8	274.2	266.5	258.9	251.3	241.7	230.2	218.7	207.1	195.6	188.6
65°	246.7	239.0	231.5	223.8	216.1	206.9	196.1	185.3	174.5	163.6	156.9
67.5°	211.6	203.9	196.2	188.4	180.8	171.7	161.3	150.9	140.6	130.1	125.1
70°	188.6	181.1	173.7	166.2	158.7	150.0	140.3	130.6	120.9	111.2	106.3
72.5°	165.6	158.2	150.8	143.5	136.1	128.0	119.2	110.3	101.5	92.7	88.7
75°	130.5	123.8	117.2	110.6	103.9	96.7	89.1	81.4	73.9	66.2	64.8
77.5°	98.6	92.5	86.5	80.5	74.4	69.0	64.1	59.2	54.2	49.3	48.6
80°	78.1	72.4	66.7	61.0	55.3	51.0	48.1	45.2	42.2	39.4	38.9
82.5°	58.6	53.6	48.8	43.9	38.9	35.8	34.4	33.1	31.7	30.3	29.9
85°	33.1	30.1	27.0	24.0	20.9	19.2	18.8	18.3	17.9	17.4	17.2
87.5°	12.2	11.4	10.7	9.9	9.2	9.1	9.7	10.4	10.9	11.5	11.6
90°	1.1	3.3	5.7	8.1	10.4	13.0	16.1	19.1	22.1	25.2	26.1
92.5°	19.5	18.8	18.2	17.5	16.9	17.7	20.0	22.3	24.5	26.8	28.3
95°	63.9	54.4	44.8	35.3	25.8	22.3	24.8	27.4	29.9	32.5	34.2
97.5°	128.5	124.3	119.9	115.7	111.4	100.9	84.1	67.3	50.5	33.8	35.6
100°	177.2	181.8	186.5	191.1	195.8	179.9	143.7	107.3	70.9	34.6	36.4
102.5°	232.5	235.9	239.2	242.6	246.0	227.8	188.1	148.4	108.7	69.0	63.2
105°	312.4	315.0	317.6	320.1	322.6	313.5	292.4	271.5	250.5	229.6	188.3
107.5°	396.7	398.8	400.8	402.8	404.9	407.6	410.9	414.2	417.5	420.8	390.5
110°	452.9	454.8	456.6	458.4	460.3	462.5	465.1	467.7	470.3	472.8	465.1



TEST NUMBER: P332424-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	506.5	508.3	509.9	511.6	513.2	515.4	518.0	520.5	523.1	525.6	525.8
115°	586.0	587.4	588.8	590.2	591.6	593.4	595.4	597.5	599.7	601.8	604.1
117.5°	663.0	664.7	666.4	668.1	669.8	671.2	672.3	673.4	674.5	675.6	677.4
120°	710.8	712.9	714.9	717.1	719.2	720.6	721.2	721.9	722.7	723.3	725.2
122.5°	759.5	761.2	762.9	764.6	766.3	767.6	768.5	769.4	770.3	771.2	772.5
125°	826.1	827.9	829.8	831.7	833.6	834.9	835.8	836.8	837.7	838.7	839.1
127.5°	890.6	892.5	894.4	896.3	898.1	899.6	900.7	901.9	902.9	904.1	904.8
130°	930.9	932.8	934.7	936.5	938.4	939.8	940.7	941.7	942.6	943.5	944.4
132.5°	969.5	971.3	973.2	975.1	977.0	978.3	979.0	979.7	980.5	981.2	982.2
135°	1028.4	1029.8	1031.2	1032.6	1034.0	1035.2	1036.1	1037.1	1038.0	1038.9	1039.6
137.5°	1078.7	1080.5	1082.3	1084.0	1085.8	1087.0	1087.4	1088.0	1088.5	1089.0	1090.1
140°	1112.3	1113.7	1115.1	1116.5	1117.9	1118.9	1119.7	1120.3	1121.0	1121.7	1122.7
142.5°	1143.3	1144.7	1146.1	1147.5	1148.9	1150.0	1150.6	1151.4	1152.0	1152.8	1153.5
145°	1186.7	1188.4	1190.0	1191.6	1193.3	1194.3	1194.7	1195.2	1195.7	1196.1	1196.6
147.5°	1227.6	1228.7	1229.7	1230.8	1231.9	1232.7	1233.1	1233.5	1234.0	1234.5	1235.0
150°	1252.8	1253.4	1254.2	1254.8	1255.6	1256.1	1256.6	1257.0	1257.5	1258.0	1258.5
152.5°	1275.4	1275.7	1276.0	1276.4	1276.7	1277.0	1277.3	1277.6	1277.8	1278.1	1279.0
155°	1307.3	1306.8	1306.4	1305.9	1305.4	1305.3	1305.5	1305.8	1306.0	1306.2	1307.4
157.5°	1332.0	1332.0	1332.0	1331.9	1331.8	1331.7	1331.5	1331.2	1331.0	1330.7	1332.1
160°	1347.1	1346.9	1346.6	1346.4	1346.1	1346.0	1345.7	1345.5	1345.2	1345.0	1346.4
162.5°	1361.4	1360.7	1360.2	1359.5	1358.9	1358.5	1358.3	1358.0	1357.8	1357.6	1359.2
165°	1378.6	1377.9	1377.1	1376.5	1375.7	1375.3	1375.1	1374.8	1374.6	1374.4	1376.2
167.5°	1392.0	1391.1	1390.1	1389.2	1388.2	1387.8	1387.8	1387.8	1387.8	1387.8	1389.7
170°	1399.5	1398.6	1397.7	1396.8	1395.8	1395.3	1395.3	1395.3	1395.3	1395.3	1397.2
172.5°	1404.6	1403.5	1402.3	1401.2	1400.1	1399.6	1399.8	1400.0	1400.2	1400.4	1402.2
175°	1411.0	1409.9	1408.8	1407.5	1406.4	1405.9	1406.1	1406.4	1406.6	1406.9	1408.5
177.5°	1412.8	1411.8	1410.9	1410.0	1409.0	1408.7	1408.8	1409.0	1409.2	1409.4	1410.9
180°	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0



TEST NUMBER: P332424-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1
2.5°	767.0	768.3	769.5	770.0	769.7	769.5	769.3	769.1
5°	761.9	763.2	764.4	764.9	764.7	764.3	764.1	763.8
7.5°	751.2	751.9	752.6	752.7	752.2	751.8	751.3	750.8
10°	741.6	741.8	741.8	741.6	740.9	740.2	739.6	738.8
12.5°	729.7	729.6	729.5	729.0	728.2	727.4	726.7	725.9
15°	708.7	708.0	707.4	706.5	705.5	704.6	703.6	702.6
17.5°	683.7	682.2	680.7	679.3	677.8	676.4	674.9	673.5
20°	666.5	664.7	662.9	661.2	659.5	657.9	656.2	654.5
22.5°	648.2	645.9	643.7	641.7	640.2	638.6	637.1	635.5
25°	618.1	615.1	612.3	610.0	608.5	607.0	605.4	603.9
27.5°	585.3	581.3	577.2	574.1	571.7	569.4	567.0	564.7
30°	562.0	557.3	552.6	549.1	546.9	544.7	542.4	540.2
32.5°	539.2	533.9	528.8	525.1	522.8	520.4	518.0	515.8
35°	505.2	499.2	493.3	489.0	486.5	484.0	481.5	479.0
37.5°	468.7	461.9	455.2	450.3	447.2	444.1	441.0	437.9
40°	443.4	436.1	428.9	423.7	420.5	417.4	414.2	410.9
42.5°	419.1	411.2	403.2	397.9	395.0	392.2	389.3	386.5
45°	383.3	375.4	367.5	361.8	358.5	355.1	351.8	348.5
47.5°	346.3	337.7	329.1	323.3	320.3	317.3	314.4	311.4
50°	321.3	312.7	304.1	298.2	295.0	291.8	288.6	285.4
52.5°	297.2	288.2	279.2	273.4	270.5	267.7	264.8	262.0
55°	261.2	253.2	245.1	239.7	236.9	234.2	231.4	228.6
57.5°	225.8	218.3	210.7	205.7	203.3	201.0	198.6	196.2
60°	203.6	196.1	188.6	183.7	181.3	179.0	176.6	174.2
62.5°	181.5	174.5	167.4	162.7	160.2	157.7	155.2	152.8
65°	150.0	143.2	136.4	132.2	130.8	129.2	127.7	126.1
67.5°	120.0	114.9	109.8	106.5	104.8	103.2	101.6	100.0
70°	101.4	96.6	91.7	88.5	87.0	85.5	84.0	82.4
72.5°	84.7	80.8	76.8	74.5	73.9	73.2	72.6	71.9
75°	63.4	62.0	60.7	59.8	59.5	59.3	58.9	58.7
77.5°	47.9	47.1	46.3	45.8	45.6	45.2	45.0	44.7
80°	38.5	38.1	37.7	37.3	37.1	36.8	36.5	36.2
82.5°	29.5	29.1	28.7	28.5	28.4	28.4	28.3	28.2
85°	17.0	16.6	16.4	16.2	16.2	16.2	16.2	16.2
87.5°	11.7	11.7	11.8	11.8	11.8	11.8	11.8	11.8
90°	27.0	28.0	28.9	29.6	30.1	30.5	31.0	31.5
92.5°	29.8	31.3	32.8	33.7	34.0	34.2	34.5	34.8
95°	35.8	37.4	39.1	39.9	39.9	39.9	39.9	39.9
97.5°	37.5	39.4	41.2	42.2	42.5	42.7	43.0	43.2
100°	38.3	40.2	42.1	43.1	43.3	43.5	43.8	44.0
102.5°	57.4	51.6	45.9	43.2	43.6	44.0	44.4	44.8
105°	147.1	105.9	64.7	44.3	44.8	45.2	45.7	46.1
107.5°	360.4	330.1	299.9	269.2	238.1	207.0	175.9	144.9
110°	457.4	449.7	442.1	421.5	388.2	354.9	321.6	288.3





TEST NUMBER: P332424-930

CATALOG NUMBER: S123RDIW-S560D1320U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	525.9	526.0	526.2	522.8	515.7	508.7	501.7	494.6
115°	606.4	608.7	611.1	612.7	613.6	614.6	615.5	616.4
117.5°	679.3	681.1	683.0	684.0	684.2	684.4	684.6	684.8
120°	727.1	729.0	730.8	731.7	731.7	731.7	731.7	731.7
122.5°	773.8	775.1	776.4	777.1	777.3	777.5	777.7	777.9
125°	839.6	840.1	840.5	841.0	841.5	842.0	842.4	842.9
127.5°	905.6	906.3	907.1	907.2	906.8	906.3	905.8	905.3
130°	945.3	946.3	947.2	947.5	947.0	946.6	946.1	945.6
132.5°	983.1	984.1	985.0	985.1	984.5	983.8	983.2	982.5
135°	1040.3	1041.0	1041.7	1041.7	1041.0	1040.3	1039.6	1038.9
137.5°	1091.3	1092.3	1093.5	1093.8	1093.3	1092.9	1092.4	1091.9
140°	1123.6	1124.5	1125.4	1125.7	1125.2	1124.7	1124.3	1123.8
142.5°	1154.2	1155.0	1155.8	1155.8	1155.1	1154.5	1153.8	1153.2
145°	1197.1	1197.5	1198.0	1198.2	1198.2	1198.2	1198.2	1198.2
147.5°	1235.4	1235.9	1236.4	1236.1	1235.0	1234.0	1232.9	1231.8
150°	1258.9	1259.4	1259.9	1259.7	1259.1	1258.3	1257.7	1256.9
152.5°	1279.8	1280.7	1281.5	1281.4	1280.3	1279.2	1278.1	1277.1
155°	1308.6	1309.7	1310.9	1310.8	1309.4	1308.0	1306.6	1305.2
157.5°	1333.6	1335.0	1336.4	1336.1	1334.3	1332.5	1330.6	1328.9
160°	1347.8	1349.2	1350.6	1350.5	1348.8	1347.2	1345.6	1343.9
162.5°	1360.7	1362.4	1363.9	1364.0	1362.5	1361.1	1359.7	1358.2
165°	1378.1	1380.0	1381.9	1381.9	1380.3	1378.7	1377.0	1375.4
167.5°	1391.6	1393.3	1395.2	1395.2	1393.3	1391.6	1389.7	1387.8
170°	1399.1	1400.9	1402.8	1402.8	1400.9	1399.1	1397.2	1395.3
172.5°	1404.1	1406.0	1407.9	1407.7	1405.7	1403.6	1401.6	1399.5
175°	1410.1	1411.8	1413.4	1413.2	1411.4	1409.6	1407.7	1405.8
177.5°	1412.3	1413.9	1415.4	1415.2	1413.3	1411.4	1409.6	1407.7
180°	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0

(END OF REPORT)