

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332476-840

Luminaire Tested: **S123RDIW-S1165D755U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332476-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D755U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7474.7 lumens
Efficiency: N/A
Efficacy: 125.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332476-840

CATALOG NUMBER: S123RDIW-S1165D755U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332476-840

CATALOG NUMBER: S123RDIW-S1165D755U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	109	109	109	109	102	102	102	102	88	88	88		76	76	76		65	65	65	59
1	100	96	92	89	93	90	87	84	78	76	74		68	66	64		58	56	55	51
2	92	84	78	73	85	79	74	69	69	65	61		60	57	54		51	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52		53	49	46		46	43	41	37
4	77	66	58	52	72	62	55	50	55	49	45		48	43	40		41	38	35	32
5	71	59	51	45	66	56	48	43	49	43	39		43	38	35		37	34	31	28
6	65	53	45	39	61	50	43	38	44	39	34		39	34	31		34	30	27	25
7	60	48	40	35	56	46	38	33	40	35	30		36	31	27		31	27	24	22
8	56	44	36	31	52	42	34	30	37	31	27		33	28	25		29	25	22	20
9	52	40	33	28	49	38	31	27	34	28	24		30	25	22		26	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22		28	23	20		25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21068	21068	21068
5°	21149	20857	20977
10°	21029	20595	20525
15°	20803	20113	19900
20°	20492	19511	19057
25°	20173	18834	18231
30°	19750	18053	17066
35°	19316	17270	16000
40°	18916	16350	14677
45°	18389	15440	13484
50°	17811	14408	12149
55°	17220	13226	10903
60°	16678	11961	9535
65°	15969	10593	8166
70°	15087	8894	6593
75°	13795	6995	6209
80°	12298	6199	5709
85°	10387	5483	5101



TEST NUMBER: P332476-840

CATALOG NUMBER: S123RDIW-S1165D755U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	2.5
10°-20°	511.4	6.8
20°-30°	736.4	9.9
30°-40°	829.4	11.1
40°-50°	793.5	10.6
50°-60°	649.8	8.7
60°-70°	438.4	5.9
70°-80°	220.6	3.0
80°-90°	61.2	0.8
90°-100°	36.4	0.5
100°-110°	173.3	2.3
110°-120°	416.3	5.6
120°-130°	530.1	7.1
130°-140°	566.4	7.6
140°-150°	529.7	7.1
150°-160°	427.3	5.7
160°-170°	275.7	3.7
170°-180°	95.0	1.3
0°-30°	1431.6	19.2
0°-40°	2261.0	30.2
0°-60°	3704.3	49.6
0°-90°	4424.5	59.2
90°-120°	626.0	8.4
90°-150°	2252.2	30.1
90°-180°	3050.0	40.8
0°-180°	7474.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1957	1957	1957	1957	1957	
5°	1957	1949	1930	1944	1941	186
15°	1867	1848	1805	1797	1786	526
25°	1698	1657	1586	1553	1535	781
35°	1470	1411	1314	1248	1218	920
45°	1208	1134	1014	927	886	932
55°	918	837	705	616	581	822
65°	627	538	416	342	321	620
75°	332	255	168	153	149	354
85°	84	51	44	41	41	94
90°	1	8	18	21	22	6
95°	45	17	23	28	28	56
105°	222	225	163	39	33	235
115°	415	420	427	434	437	410
125°	586	591	594	596	597	523
135°	729	733	736	738	736	561
145°	841	846	848	849	849	526
155°	927	925	926	929	925	427
165°	977	975	974	980	975	276
175°	1000	997	997	1002	996	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P332476-840

CATALOG NUMBER: S123RDIW-S1165D755U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1963.7	1962.5	1961.4	1960.2	1959.1	1956.8	1953.5	1950.0	1946.7	1943.3	1946.4
5°	1957.3	1955.5	1953.8	1952.0	1950.3	1947.2	1943.0	1938.7	1934.5	1930.3	1933.5
7.5°	1939.1	1937.3	1935.4	1933.5	1931.6	1927.8	1922.4	1916.8	1911.4	1905.8	1907.6
10°	1924.0	1921.5	1919.0	1916.5	1914.1	1909.7	1903.3	1896.9	1890.6	1884.3	1884.6
12.5°	1902.4	1899.7	1896.8	1894.1	1891.4	1886.1	1878.3	1870.6	1862.8	1855.0	1854.8
15°	1866.8	1862.9	1859.1	1855.1	1851.3	1844.4	1834.5	1824.6	1814.7	1804.9	1803.1
17.5°	1822.0	1817.6	1813.0	1808.5	1804.0	1795.4	1782.9	1770.3	1757.8	1745.2	1741.5
20°	1789.0	1783.4	1777.8	1772.1	1766.5	1757.0	1743.5	1730.1	1716.7	1703.3	1698.7
22.5°	1752.2	1745.7	1739.2	1732.7	1726.3	1715.9	1701.6	1687.4	1673.1	1658.8	1653.1
25°	1698.5	1689.7	1680.9	1672.0	1663.2	1650.7	1634.5	1618.3	1602.0	1585.8	1578.4
27.5°	1633.5	1623.8	1614.0	1604.3	1594.5	1580.6	1562.6	1544.5	1526.4	1508.3	1498.0
30°	1589.0	1578.4	1567.8	1557.2	1546.7	1531.5	1511.8	1492.0	1472.3	1452.5	1440.5
32.5°	1544.6	1532.6	1520.6	1508.5	1496.6	1480.2	1459.3	1438.4	1417.4	1396.6	1383.5
35°	1470.0	1457.2	1444.5	1431.9	1419.2	1401.9	1380.0	1358.2	1336.3	1314.3	1299.2
37.5°	1394.4	1380.3	1366.1	1352.0	1338.0	1319.2	1295.9	1272.5	1249.2	1225.8	1208.6
40°	1346.2	1330.6	1315.0	1299.6	1284.0	1263.7	1238.7	1213.7	1188.6	1163.6	1145.2
42.5°	1291.5	1276.0	1260.5	1245.0	1229.4	1208.7	1182.9	1156.9	1131.0	1105.2	1085.1
45°	1208.0	1192.1	1176.3	1160.4	1144.5	1123.0	1095.8	1068.6	1041.5	1014.3	994.2
47.5°	1124.5	1107.1	1089.6	1072.3	1054.8	1032.5	1005.3	978.2	951.0	923.9	902.0
50°	1063.6	1047.0	1030.4	1013.8	997.2	974.7	946.1	917.6	889.0	860.4	838.5
52.5°	1009.0	991.0	973.0	955.0	937.0	913.8	885.6	857.3	829.0	800.7	778.0
55°	917.6	900.2	882.9	865.7	848.4	824.8	794.8	764.8	734.8	704.8	684.4
57.5°	833.0	814.3	795.4	776.6	757.7	733.3	703.2	673.0	642.9	612.8	593.4
60°	774.7	755.3	735.9	716.5	697.0	672.7	643.4	614.2	584.9	555.6	536.5
62.5°	716.2	696.8	677.4	658.0	638.6	614.3	585.0	555.7	526.4	497.2	479.3
65°	627.0	607.6	588.2	568.9	549.5	525.9	498.5	470.9	443.4	415.9	398.6
67.5°	537.9	518.2	498.6	479.0	459.4	436.4	410.0	383.5	357.2	330.8	317.9
70°	479.4	460.4	441.3	422.2	403.2	381.3	356.7	331.9	307.3	282.6	270.2
72.5°	421.0	402.2	383.4	364.7	345.9	325.3	302.9	280.4	258.0	235.6	225.5
75°	331.7	314.9	297.9	280.9	264.1	245.9	226.5	207.0	187.6	168.2	164.7
77.5°	250.4	235.2	219.8	204.6	189.2	175.3	162.9	150.4	137.8	125.4	123.5
80°	198.4	184.0	169.5	155.0	140.6	129.7	122.2	114.8	107.4	100.0	99.0
82.5°	148.9	136.4	123.9	111.4	99.0	91.0	87.6	84.0	80.6	77.2	76.0
85°	84.1	76.3	68.6	60.9	53.1	48.7	47.7	46.6	45.5	44.4	43.7
87.5°	30.6	27.9	25.0	22.3	19.5	18.4	18.8	19.2	19.7	20.1	19.9
90°	0.7	2.4	4.0	5.7	7.4	9.3	11.4	13.5	15.7	17.9	18.5
92.5°	13.8	13.3	12.9	12.4	12.0	12.5	14.1	15.8	17.4	19.0	20.1
95°	45.3	38.6	31.8	25.0	18.3	15.8	17.6	19.4	21.2	23.0	24.2
97.5°	91.1	88.1	85.0	82.0	79.0	71.5	59.6	47.7	35.9	23.9	25.2
100°	125.6	128.9	132.2	135.5	138.8	127.5	101.8	76.0	50.3	24.5	25.9
102.5°	164.8	167.2	169.6	172.0	174.3	161.5	133.3	105.1	77.1	48.9	44.8
105°	221.5	223.3	225.1	226.9	228.7	222.2	207.3	192.5	177.6	162.8	133.5
107.5°	281.1	282.7	284.1	285.6	287.0	288.9	291.2	293.6	296.0	298.3	276.8
110°	321.0	322.3	323.7	325.0	326.3	327.9	329.7	331.5	333.4	335.2	329.7



TEST NUMBER: P332476-840

CATALOG NUMBER: S123RDIW-S1165D755U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	359.1	360.2	361.4	362.6	363.9	365.4	367.2	369.0	370.8	372.6	372.7
115°	415.4	416.4	417.4	418.4	419.4	420.6	422.1	423.5	425.1	426.6	428.2
117.5°	470.0	471.2	472.4	473.6	474.8	475.8	476.6	477.4	478.1	478.9	480.2
120°	503.8	505.3	506.9	508.3	509.8	510.8	511.3	511.8	512.3	512.7	514.1
122.5°	538.4	539.6	540.8	542.0	543.2	544.1	544.7	545.4	546.0	546.6	547.5
125°	585.6	586.9	588.2	589.6	590.9	591.9	592.5	593.2	593.8	594.5	594.8
127.5°	631.4	632.7	634.0	635.3	636.6	637.7	638.5	639.2	640.1	640.9	641.4
130°	659.8	661.3	662.6	663.9	665.2	666.2	666.8	667.5	668.1	668.8	669.4
132.5°	687.2	688.5	689.8	691.2	692.6	693.5	694.0	694.5	695.0	695.6	696.2
135°	729.0	730.0	730.9	732.0	733.0	733.8	734.5	735.1	735.8	736.4	736.9
137.5°	764.7	765.9	767.2	768.4	769.7	770.5	770.8	771.2	771.6	771.9	772.7
140°	788.4	789.4	790.4	791.4	792.4	793.1	793.7	794.2	794.7	795.2	795.8
142.5°	810.4	811.4	812.4	813.4	814.5	815.2	815.7	816.2	816.7	817.2	817.7
145°	841.2	842.3	843.5	844.7	845.9	846.6	846.9	847.3	847.6	847.9	848.2
147.5°	870.2	870.9	871.7	872.4	873.2	873.7	874.1	874.4	874.7	875.0	875.5
150°	888.1	888.5	889.0	889.5	890.0	890.4	890.8	891.1	891.4	891.7	892.1
152.5°	904.0	904.3	904.5	904.7	905.0	905.2	905.4	905.6	905.8	906.1	906.6
155°	926.7	926.3	926.0	925.6	925.3	925.2	925.4	925.6	925.7	925.9	926.8
157.5°	944.2	944.2	944.1	944.1	944.1	944.0	943.8	943.6	943.5	943.3	944.3
160°	954.9	954.7	954.6	954.4	954.2	954.1	953.9	953.7	953.6	953.4	954.4
162.5°	965.0	964.6	964.1	963.7	963.3	963.0	962.8	962.7	962.5	962.3	963.5
165°	977.2	976.7	976.2	975.7	975.2	974.9	974.7	974.5	974.4	974.2	975.5
167.5°	986.7	986.0	985.4	984.7	984.1	983.7	983.7	983.7	983.7	983.7	985.0
170°	992.1	991.4	990.8	990.1	989.5	989.1	989.1	989.1	989.1	989.1	990.4
172.5°	995.6	994.8	994.0	993.3	992.5	992.1	992.3	992.4	992.5	992.7	994.0
175°	1000.3	999.4	998.6	997.7	996.9	996.6	996.7	996.9	997.1	997.2	998.5
177.5°	1001.4	1000.8	1000.1	999.5	998.8	998.6	998.7	998.8	999.0	999.1	1000.1
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3



TEST NUMBER: P332476-840

CATALOG NUMBER: S123RDIW-S1165D755U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1949.5	1952.7	1955.7	1957.0	1956.4	1955.9	1955.3	1954.7
5°	1936.6	1939.8	1943.0	1944.2	1943.5	1942.8	1942.1	1941.4
7.5°	1909.4	1911.2	1912.9	1913.2	1912.0	1910.8	1909.6	1908.3
10°	1885.0	1885.3	1885.7	1885.0	1883.2	1881.5	1879.7	1877.9
12.5°	1854.6	1854.4	1854.2	1853.1	1851.1	1849.0	1846.9	1844.9
15°	1801.4	1799.6	1797.9	1795.7	1793.2	1790.8	1788.3	1785.8
17.5°	1737.8	1733.9	1730.2	1726.6	1722.8	1719.2	1715.6	1711.8
20°	1694.1	1689.5	1685.0	1680.5	1676.3	1672.0	1667.9	1663.7
22.5°	1647.4	1641.7	1636.0	1631.1	1627.2	1623.3	1619.3	1615.4
25°	1571.0	1563.6	1556.2	1550.5	1546.7	1542.8	1538.9	1535.0
27.5°	1487.7	1477.4	1467.1	1459.1	1453.1	1447.2	1441.3	1435.3
30°	1428.5	1416.5	1404.5	1395.7	1390.1	1384.4	1378.8	1373.1
32.5°	1370.4	1357.3	1344.1	1334.6	1328.7	1322.7	1316.9	1310.9
35°	1284.0	1268.9	1253.7	1242.9	1236.6	1230.2	1223.9	1217.6
37.5°	1191.3	1174.2	1156.9	1144.4	1136.6	1128.7	1121.0	1113.1
40°	1126.9	1108.5	1090.3	1077.0	1068.8	1060.8	1052.7	1044.5
42.5°	1065.1	1045.0	1025.0	1011.4	1004.1	996.8	989.6	982.3
45°	974.1	954.0	933.9	919.7	911.2	902.7	894.2	885.8
47.5°	880.1	858.3	836.4	821.7	814.2	806.6	799.0	791.5
50°	816.7	794.8	772.8	757.9	749.8	741.6	733.6	725.5
52.5°	755.3	732.6	709.8	694.8	687.5	680.3	673.1	665.8
55°	663.9	643.4	623.0	609.3	602.2	595.1	588.0	581.0
57.5°	574.1	554.7	535.4	522.7	516.7	510.8	504.7	498.8
60°	517.5	498.5	479.4	466.9	460.9	454.8	448.9	442.9
62.5°	461.3	443.4	425.5	413.4	407.1	400.8	394.6	388.3
65°	381.3	364.1	346.8	336.2	332.3	328.4	324.6	320.6
67.5°	305.0	292.1	279.1	270.6	266.5	262.3	258.1	254.0
70°	257.8	245.5	233.2	225.1	221.2	217.3	213.4	209.5
72.5°	215.4	205.3	195.2	189.3	187.7	186.1	184.5	182.9
75°	161.2	157.6	154.1	152.1	151.4	150.7	150.0	149.3
77.5°	121.6	119.7	117.8	116.4	115.7	115.0	114.3	113.6
80°	97.9	96.8	95.7	94.9	94.2	93.5	92.8	92.1
82.5°	75.0	74.0	72.9	72.3	72.2	72.0	71.9	71.8
85°	43.0	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	19.8	19.6	19.5	19.3	19.1	18.9	18.7	18.4
90°	19.2	19.8	20.5	21.0	21.3	21.6	21.9	22.3
92.5°	21.1	22.2	23.2	23.8	24.0	24.2	24.4	24.6
95°	25.3	26.5	27.7	28.3	28.3	28.3	28.3	28.3
97.5°	26.6	27.9	29.2	30.0	30.1	30.3	30.5	30.6
100°	27.2	28.5	29.8	30.6	30.7	30.9	31.0	31.2
102.5°	40.7	36.7	32.5	30.6	30.9	31.2	31.5	31.8
105°	104.3	75.0	45.8	31.4	31.7	32.0	32.4	32.7
107.5°	255.4	234.0	212.6	190.9	168.7	146.7	124.7	102.7
110°	324.3	318.8	313.4	298.8	275.2	251.6	227.9	204.4



TEST NUMBER: P332476-840

CATALOG NUMBER: S123RDIW-S1165D755U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	372.8	372.9	373.0	370.5	365.6	360.6	355.6	350.6
115°	429.9	431.5	433.1	434.3	434.9	435.7	436.3	437.0
117.5°	481.5	482.8	484.1	484.8	485.0	485.1	485.2	485.4
120°	515.4	516.7	518.1	518.7	518.7	518.7	518.7	518.7
122.5°	548.5	549.4	550.4	550.9	551.0	551.1	551.3	551.4
125°	595.1	595.5	595.8	596.1	596.5	596.8	597.1	597.4
127.5°	642.0	642.5	643.0	643.1	642.8	642.4	642.1	641.8
130°	670.1	670.8	671.5	671.7	671.3	671.0	670.7	670.2
132.5°	696.9	697.5	698.2	698.3	697.8	697.4	696.9	696.4
135°	737.4	737.9	738.4	738.4	737.9	737.4	736.9	736.4
137.5°	773.6	774.4	775.2	775.4	775.1	774.7	774.4	774.1
140°	796.5	797.1	797.8	798.0	797.6	797.3	797.0	796.6
142.5°	818.2	818.7	819.2	819.3	818.8	818.4	817.9	817.4
145°	848.6	848.9	849.2	849.4	849.4	849.4	849.4	849.4
147.5°	875.8	876.1	876.5	876.2	875.5	874.6	873.9	873.1
150°	892.4	892.7	893.0	893.0	892.5	892.0	891.5	891.0
152.5°	907.2	907.8	908.4	908.3	907.6	906.8	906.1	905.2
155°	927.6	928.4	929.3	929.2	928.2	927.2	926.1	925.1
157.5°	945.3	946.2	947.3	947.2	945.8	944.5	943.3	942.0
160°	955.4	956.4	957.4	957.4	956.1	955.0	953.8	952.7
162.5°	964.6	965.7	966.8	966.8	965.8	964.8	963.8	962.8
165°	976.8	978.2	979.5	979.6	978.5	977.2	976.1	974.9
167.5°	986.3	987.7	989.1	989.1	987.7	986.3	985.0	983.7
170°	991.7	993.1	994.4	994.4	993.1	991.7	990.4	989.1
172.5°	995.3	996.6	997.9	997.8	996.4	995.0	993.5	992.1
175°	999.6	1000.8	1001.9	1001.8	1000.5	999.2	997.8	996.5
177.5°	1001.2	1002.2	1003.3	1003.1	1001.8	1000.5	999.2	997.8
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3

(END OF REPORT)