

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332429-930

Luminaire Tested: **S123RDIW-S560D1535U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332429-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D1535U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6080.5 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332429-930

CATALOG NUMBER: S123RDIW-S560D1535U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332429-930

CATALOG NUMBER: S123RDIW-S560D1535U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	28	26	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	15
5	65	54	46	41	58	49	42	37	39	34	30	29	26	24	21	19	17	14
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	44	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14	11
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9
10	44	33	26	21	40	30	24	20	24	20	16	19	15	13	14	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8289	8289	8289
5°	8321	8206	8253
10°	8273	8103	8075
15°	8184	7913	7830
20°	8062	7676	7497
25°	7936	7410	7172
30°	7771	7102	6714
35°	7599	6795	6294
40°	7442	6433	5774
45°	7234	6075	5305
50°	7006	5668	4779
55°	6775	5204	4290
60°	6562	4706	3750
65°	6283	4167	3212
70°	5936	3500	2593
75°	5427	2753	2441
80°	4841	2442	2244
85°	4088	2149	2001



TEST NUMBER: P332429-930

CATALOG NUMBER: S123RDIW-S560D1535U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	1.2
10°-20°	201.2	3.3
20°-30°	289.7	4.8
30°-40°	326.3	5.4
40°-50°	312.2	5.1
50°-60°	255.7	4.2
60°-70°	172.5	2.8
70°-80°	86.8	1.4
80°-90°	27.6	0.5
90°-100°	102.0	1.7
100°-110°	305.2	5.0
110°-120°	519.0	8.5
120°-130°	682.7	11.2
130°-140°	767.4	12.6
140°-150°	754.3	12.4
150°-160°	635.0	10.4
160°-170°	422.7	7.0
170°-180°	148.0	2.4
0°-30°	563.2	9.3
0°-40°	889.5	14.6
0°-60°	1457.4	24.0
0°-90°	1744.3	28.7
90°-120°	926.2	15.2
90°-150°	3130.5	51.5
90°-180°	4336.0	71.3
0°-180°	6080.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	770	770	770	770	770	
5°	770	767	760	765	764	73
15°	734	727	710	707	703	207
25°	668	652	624	611	604	307
35°	578	555	517	491	479	362
45°	475	446	399	365	348	367
55°	361	329	277	242	229	324
65°	247	212	164	134	126	244
75°	130	100	66	60	59	139
85°	33	20	17	16	16	37
90°	1	14	30	34	37	6
95°	73	81	91	96	96	82
105°	277	280	290	290	293	296
115°	522	526	524	525	524	517
125°	765	768	766	761	756	682
135°	992	999	998	994	991	764
145°	1204	1206	1210	1208	1204	752
155°	1378	1378	1379	1384	1376	634
165°	1501	1498	1498	1504	1496	423
175°	1561	1557	1556	1563	1555	148
180°	1565	1565	1565	1565	1565	



TEST NUMBER: P332429-930

CATALOG NUMBER: S123RDIW-S560D1535U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1
2.5°	772.6	772.1	771.7	771.2	770.8	769.9	768.6	767.2	765.9	764.6	765.8
5°	770.1	769.4	768.7	768.0	767.3	766.1	764.4	762.8	761.1	759.5	760.7
7.5°	763.0	762.2	761.4	760.7	759.9	758.5	756.4	754.2	752.0	749.8	750.5
10°	756.9	755.9	755.0	754.0	753.1	751.3	748.9	746.3	743.8	741.4	741.4
12.5°	748.4	747.4	746.2	745.2	744.1	742.1	739.0	736.0	732.9	729.9	729.8
15°	734.4	733.0	731.4	729.9	728.4	725.6	721.8	717.9	714.0	710.1	709.4
17.5°	716.8	715.1	713.3	711.5	709.7	706.4	701.4	696.5	691.5	686.6	685.2
20°	703.8	701.6	699.4	697.2	695.0	691.2	685.9	680.7	675.4	670.1	668.3
22.5°	689.3	686.8	684.3	681.7	679.1	675.1	669.4	663.8	658.3	652.6	650.4
25°	668.2	664.8	661.3	657.9	654.4	649.5	643.0	636.7	630.3	623.9	621.0
27.5°	642.6	638.8	635.0	631.1	627.3	621.8	614.7	607.6	600.5	593.5	589.4
30°	625.2	621.0	616.9	612.7	608.5	602.5	594.8	587.0	579.2	571.4	566.7
32.5°	607.6	603.0	598.3	593.5	588.8	582.4	574.1	565.9	557.7	549.4	544.3
35°	578.3	573.3	568.3	563.4	558.3	551.5	542.9	534.3	525.7	517.1	511.1
37.5°	548.6	543.1	537.5	531.9	526.4	519.0	509.8	500.7	491.5	482.2	475.5
40°	529.6	523.5	517.4	511.3	505.2	497.2	487.4	477.5	467.7	457.8	450.5
42.5°	508.1	502.0	495.9	489.8	483.7	475.6	465.4	455.2	445.0	434.8	426.9
45°	475.2	469.0	462.8	456.6	450.3	441.8	431.1	420.4	409.8	399.1	391.2
47.5°	442.4	435.5	428.7	421.8	415.0	406.3	395.5	384.8	374.1	363.5	354.9
50°	418.4	411.9	405.4	398.8	392.3	383.4	372.2	361.0	349.8	338.5	329.9
52.5°	397.0	389.9	382.8	375.7	368.7	359.5	348.4	337.3	326.1	315.0	306.1
55°	361.0	354.2	347.4	340.6	333.8	324.5	312.7	300.9	289.1	277.3	269.2
57.5°	327.8	320.3	312.9	305.5	298.1	288.5	276.6	264.8	252.9	241.1	233.5
60°	304.8	297.2	289.5	281.8	274.3	264.6	253.2	241.7	230.1	218.6	211.1
62.5°	281.8	274.2	266.5	258.9	251.3	241.7	230.2	218.7	207.1	195.6	188.6
65°	246.7	239.0	231.5	223.8	216.1	206.9	196.1	185.3	174.5	163.6	156.9
67.5°	211.6	203.9	196.2	188.4	180.8	171.7	161.3	150.9	140.6	130.1	125.1
70°	188.6	181.1	173.7	166.2	158.7	150.0	140.3	130.6	120.9	111.2	106.3
72.5°	165.6	158.2	150.8	143.5	136.1	128.0	119.2	110.3	101.5	92.7	88.7
75°	130.5	123.8	117.2	110.6	103.9	96.7	89.1	81.4	73.9	66.2	64.8
77.5°	98.6	92.5	86.5	80.5	74.4	69.0	64.1	59.2	54.2	49.3	48.6
80°	78.1	72.4	66.7	61.0	55.3	51.0	48.1	45.2	42.2	39.4	38.9
82.5°	58.6	53.6	48.8	43.9	38.9	35.8	34.4	33.1	31.7	30.3	29.9
85°	33.1	30.1	27.0	24.0	20.9	19.2	18.8	18.3	17.9	17.4	17.2
87.5°	12.2	11.6	10.9	10.2	9.5	9.5	10.3	11.0	11.7	12.4	12.5
90°	1.2	4.0	6.7	9.5	12.1	15.3	18.8	22.4	25.9	29.5	30.6
92.5°	29.8	31.6	33.4	35.3	37.2	39.1	41.2	43.1	45.2	47.2	48.1
95°	72.6	74.4	76.4	78.3	80.2	82.3	84.4	86.6	88.8	91.0	92.0
97.5°	128.8	130.3	131.7	133.1	134.5	136.0	137.6	139.2	140.8	142.4	143.7
100°	167.2	168.8	170.5	172.1	173.7	175.3	176.6	178.0	179.4	180.8	181.6
102.5°	211.5	212.5	213.4	214.4	215.4	216.8	218.6	220.4	222.2	224.0	224.9
105°	276.6	277.2	277.7	278.3	278.8	280.3	282.7	285.2	287.7	290.2	290.2
107.5°	352.4	352.7	353.0	353.4	353.7	354.3	355.3	356.3	357.3	358.2	359.1
110°	399.6	400.1	400.6	401.2	401.8	402.3	402.8	403.4	403.9	404.5	405.6



TEST NUMBER: P332429-930

CATALOG NUMBER: S123RDIW-S560D1535U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	448.7	449.1	449.4	449.7	450.0	450.3	450.4	450.5	450.6	450.7	452.0
115°	522.5	523.3	524.2	525.0	525.8	525.9	525.4	524.8	524.3	523.7	524.0
117.5°	596.8	597.3	597.9	598.4	598.9	598.8	598.2	597.5	596.7	596.1	596.0
120°	643.0	644.7	646.3	647.9	649.5	649.7	648.3	646.9	645.6	644.2	643.9
122.5°	691.2	692.4	693.6	694.8	696.0	696.3	695.5	694.8	694.1	693.4	692.7
125°	764.7	765.5	766.4	767.2	768.0	768.1	767.6	767.0	766.5	766.0	764.8
127.5°	832.6	834.3	836.1	837.8	839.6	840.2	839.5	838.9	838.4	837.7	836.2
130°	877.8	880.0	882.2	884.4	886.6	887.2	886.4	885.6	884.8	883.9	882.9
132.5°	923.1	925.2	927.4	929.6	931.8	932.6	932.0	931.4	930.7	930.2	928.9
135°	992.1	993.8	995.4	997.0	998.7	999.4	999.1	998.8	998.6	998.3	997.2
137.5°	1056.1	1057.4	1058.8	1060.2	1061.5	1062.6	1063.3	1064.0	1064.7	1065.4	1064.3
140°	1100.3	1101.7	1103.1	1104.4	1105.8	1106.6	1106.9	1107.2	1107.4	1107.7	1107.4
142.5°	1140.7	1142.0	1143.4	1144.8	1146.1	1147.0	1147.5	1148.0	1148.5	1149.0	1148.8
145°	1203.6	1204.2	1204.7	1205.3	1205.8	1206.5	1207.3	1208.1	1208.9	1209.7	1209.5
147.5°	1258.7	1259.6	1260.6	1261.7	1262.7	1263.5	1264.3	1265.0	1265.8	1266.6	1266.6
150°	1297.1	1297.6	1298.1	1298.7	1299.3	1299.8	1300.3	1300.9	1301.4	1302.0	1302.0
152.5°	1328.5	1329.3	1330.1	1330.8	1331.5	1332.1	1332.4	1332.8	1333.1	1333.4	1333.9
155°	1378.2	1378.2	1378.2	1378.2	1378.2	1378.3	1378.6	1378.8	1379.2	1379.4	1380.5
157.5°	1420.5	1420.2	1419.8	1419.5	1419.2	1419.1	1419.4	1419.5	1419.8	1420.0	1421.1
160°	1447.1	1446.5	1445.9	1445.4	1444.9	1444.5	1444.5	1444.5	1444.5	1444.5	1445.9
162.5°	1470.6	1469.9	1469.1	1468.4	1467.6	1467.3	1467.5	1467.8	1467.9	1468.2	1469.6
165°	1501.1	1500.3	1499.5	1498.7	1497.9	1497.5	1497.5	1497.5	1497.5	1497.5	1499.1
167.5°	1525.5	1524.4	1523.3	1522.2	1521.1	1520.7	1520.9	1521.1	1521.3	1521.5	1523.2
170°	1539.2	1538.1	1537.1	1535.9	1534.9	1534.3	1534.3	1534.3	1534.3	1534.3	1536.3
172.5°	1550.0	1549.0	1547.8	1546.8	1545.7	1545.2	1545.2	1545.2	1545.2	1545.2	1546.9
175°	1561.4	1560.3	1559.2	1558.1	1557.0	1556.5	1556.5	1556.5	1556.5	1556.5	1558.1
177.5°	1566.0	1565.2	1564.3	1563.4	1562.5	1562.1	1562.1	1562.1	1562.1	1562.1	1563.4
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0



TEST NUMBER: P332429-930

CATALOG NUMBER: S123RDIW-S560D1535U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1
2.5°	767.0	768.3	769.5	770.0	769.7	769.5	769.3	769.1
5°	761.9	763.2	764.4	764.9	764.7	764.3	764.1	763.8
7.5°	751.2	751.9	752.6	752.7	752.2	751.8	751.3	750.8
10°	741.6	741.8	741.8	741.6	740.9	740.2	739.6	738.8
12.5°	729.7	729.6	729.5	729.0	728.2	727.4	726.7	725.9
15°	708.7	708.0	707.4	706.5	705.5	704.6	703.6	702.6
17.5°	683.7	682.2	680.7	679.3	677.8	676.4	674.9	673.5
20°	666.5	664.7	662.9	661.2	659.5	657.9	656.2	654.5
22.5°	648.2	645.9	643.7	641.7	640.2	638.6	637.1	635.5
25°	618.1	615.1	612.3	610.0	608.5	607.0	605.4	603.9
27.5°	585.3	581.3	577.2	574.1	571.7	569.4	567.0	564.7
30°	562.0	557.3	552.6	549.1	546.9	544.7	542.4	540.2
32.5°	539.2	533.9	528.8	525.1	522.8	520.4	518.0	515.8
35°	505.2	499.2	493.3	489.0	486.5	484.0	481.5	479.0
37.5°	468.7	461.9	455.2	450.3	447.2	444.1	441.0	437.9
40°	443.4	436.1	428.9	423.7	420.5	417.4	414.2	410.9
42.5°	419.1	411.2	403.2	397.9	395.0	392.2	389.3	386.5
45°	383.3	375.4	367.5	361.8	358.5	355.1	351.8	348.5
47.5°	346.3	337.7	329.1	323.3	320.3	317.3	314.4	311.4
50°	321.3	312.7	304.1	298.2	295.0	291.8	288.6	285.4
52.5°	297.2	288.2	279.2	273.4	270.5	267.7	264.8	262.0
55°	261.2	253.2	245.1	239.7	236.9	234.2	231.4	228.6
57.5°	225.8	218.3	210.7	205.7	203.3	201.0	198.6	196.2
60°	203.6	196.1	188.6	183.7	181.3	179.0	176.6	174.2
62.5°	181.5	174.5	167.4	162.7	160.2	157.7	155.2	152.8
65°	150.0	143.2	136.4	132.2	130.8	129.2	127.7	126.1
67.5°	120.0	114.9	109.8	106.5	104.8	103.2	101.6	100.0
70°	101.4	96.6	91.7	88.5	87.0	85.5	84.0	82.4
72.5°	84.7	80.8	76.8	74.5	73.9	73.2	72.6	71.9
75°	63.4	62.0	60.7	59.8	59.5	59.3	58.9	58.7
77.5°	47.9	47.1	46.3	45.8	45.6	45.2	45.0	44.7
80°	38.5	38.1	37.7	37.3	37.1	36.8	36.5	36.2
82.5°	29.5	29.1	28.7	28.5	28.4	28.4	28.3	28.2
85°	17.0	16.6	16.4	16.2	16.2	16.2	16.2	16.2
87.5°	12.6	12.7	12.8	12.9	12.9	12.9	12.9	12.9
90°	31.7	32.8	33.9	34.7	35.2	35.8	36.4	36.9
92.5°	48.9	49.8	50.7	51.0	50.6	50.3	50.0	49.7
95°	93.2	94.2	95.3	95.9	95.9	95.9	95.9	95.9
97.5°	144.9	146.1	147.4	148.0	147.9	147.7	147.7	147.6
100°	182.4	183.2	184.0	184.7	185.2	185.8	186.3	186.9
102.5°	225.7	226.5	227.3	227.6	227.6	227.4	227.3	227.2
105°	290.2	290.2	290.2	290.4	291.0	291.6	292.0	292.6
107.5°	360.0	360.9	361.7	362.0	361.7	361.3	361.0	360.7
110°	406.7	407.7	408.9	409.1	408.5	408.1	407.5	406.9



TEST NUMBER: P332429-930

CATALOG NUMBER: S123RDIW-S560D1535U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	453.3	454.6	455.9	456.6	456.5	456.3	456.2	456.1
115°	524.3	524.6	524.8	524.8	524.6	524.3	524.0	523.7
117.5°	595.9	595.9	595.8	595.4	594.6	593.9	593.1	592.3
120°	643.7	643.4	643.1	642.7	642.2	641.6	641.1	640.5
122.5°	691.9	691.3	690.6	689.8	689.1	688.3	687.5	686.7
125°	763.8	762.6	761.6	760.4	759.4	758.3	757.2	756.1
127.5°	834.7	833.2	831.6	830.2	829.0	827.7	826.5	825.2
130°	881.7	880.7	879.6	878.1	876.2	874.2	872.4	870.4
132.5°	927.6	926.3	925.0	923.6	922.1	920.6	919.1	917.6
135°	996.1	995.0	993.9	993.1	992.5	992.0	991.5	990.9
137.5°	1063.2	1062.0	1060.9	1059.7	1058.7	1057.7	1056.6	1055.6
140°	1107.2	1106.9	1106.6	1105.5	1103.6	1101.7	1099.8	1097.9
142.5°	1148.5	1148.2	1147.9	1147.0	1145.6	1144.1	1142.6	1141.2
145°	1209.2	1208.9	1208.7	1207.9	1206.9	1205.8	1204.7	1203.6
147.5°	1266.6	1266.6	1266.6	1265.8	1264.1	1262.5	1260.8	1259.1
150°	1302.0	1302.0	1302.0	1301.1	1299.5	1297.9	1296.2	1294.6
152.5°	1334.3	1334.7	1335.2	1334.7	1333.3	1331.9	1330.4	1329.0
155°	1381.6	1382.7	1383.8	1383.4	1381.4	1379.6	1377.6	1375.7
157.5°	1422.3	1423.4	1424.6	1424.4	1422.9	1421.3	1419.8	1418.3
160°	1447.3	1448.7	1450.0	1450.2	1449.1	1448.0	1446.9	1445.8
162.5°	1470.9	1472.3	1473.7	1473.5	1471.7	1470.0	1468.2	1466.5
165°	1500.7	1502.4	1504.0	1503.9	1501.9	1500.1	1498.1	1496.2
167.5°	1524.9	1526.6	1528.3	1528.3	1526.6	1524.9	1523.2	1521.5
170°	1538.1	1540.1	1542.0	1542.0	1540.1	1538.1	1536.3	1534.3
172.5°	1548.5	1550.2	1551.9	1551.8	1549.9	1548.0	1546.1	1544.2
175°	1559.7	1561.4	1563.0	1562.8	1561.0	1559.0	1557.1	1555.3
177.5°	1564.7	1566.0	1567.3	1567.2	1565.7	1564.2	1562.7	1561.1
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0

(END OF REPORT)