

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332408-840

Luminaire Tested: **S123RDIW-S340D1535U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332408-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D1535U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7513.3 lumens
Efficiency: N/A
Efficacy: 140.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332408-840

CATALOG NUMBER: S123RDIW-S340D1535U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332408-840

CATALOG NUMBER: S123RDIW-S340D1535U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	99	99	99	99	88	88	88	88	65	65	65	45	45	45	26	26	26	18
1	91	87	83	80	80	76	73	71	57	55	53	40	38	37	23	23	22	15
2	83	76	70	65	72	67	62	58	50	47	44	35	33	31	21	20	19	13
3	75	66	60	54	66	59	53	48	44	40	37	31	29	27	18	17	16	11
4	69	59	51	46	60	52	46	41	39	35	32	27	25	23	16	15	14	9
5	63	52	45	39	55	46	40	35	35	31	27	25	22	20	15	13	12	8
6	58	47	39	34	51	41	35	30	31	27	24	22	19	17	13	12	11	7
7	53	42	34	29	47	37	31	26	28	24	21	20	17	15	12	11	10	6
8	49	38	31	26	43	34	27	23	26	21	18	18	15	13	11	10	9	6
9	46	34	27	23	40	31	25	20	23	19	16	17	14	12	10	9	8	5
10	43	31	25	20	38	28	22	18	21	17	14	15	13	11	10	8	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6245	6245	6245
5°	6269	6183	6218
10°	6233	6105	6084
15°	6167	5962	5899
20°	6074	5783	5648
25°	5980	5583	5404
30°	5854	5351	5059
35°	5727	5119	4742
40°	5606	4846	4350
45°	5451	4576	3997
50°	5280	4270	3600
55°	5104	3920	3232
60°	4943	3546	2827
65°	4735	3140	2420
70°	4472	2634	1954
75°	4092	2075	1838
80°	3645	1841	1692
85°	3075	1618	1507



TEST NUMBER: P332408-840

CATALOG NUMBER: S123RDIW-S340D1535U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	0.7
10°-20°	151.6	2.0
20°-30°	218.3	2.9
30°-40°	245.9	3.3
40°-50°	235.2	3.1
50°-60°	192.6	2.6
60°-70°	130.0	1.7
70°-80°	65.4	0.9
80°-90°	23.0	0.3
90°-100°	73.9	1.0
100°-110°	352.1	4.7
110°-120°	845.8	11.3
120°-130°	1077.0	14.3
130°-140°	1150.8	15.3
140°-150°	1076.1	14.3
150°-160°	868.0	11.6
160°-170°	560.2	7.5
170°-180°	193.1	2.6
0°-30°	424.3	5.6
0°-40°	670.2	8.9
0°-60°	1098.1	14.6
0°-90°	1316.4	17.5
90°-120°	1271.8	16.9
90°-150°	4575.6	60.9
90°-180°	6197.0	82.5
0°-180°	7513.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	580	580	580	580	580	
5°	580	578	572	576	576	55
15°	553	548	535	533	529	156
25°	504	491	470	460	455	231
35°	436	418	390	370	361	273
45°	358	336	301	275	263	276
55°	272	248	209	183	172	244
65°	186	159	123	101	95	184
75°	98	76	50	45	44	105
85°	25	15	13	12	12	28
90°	2	17	36	42	45	6
95°	92	35	47	57	57	114
105°	450	458	331	78	66	477
115°	844	853	867	881	888	833
125°	1190	1201	1208	1211	1214	1062
135°	1481	1490	1496	1500	1496	1140
145°	1709	1719	1723	1726	1726	1069
155°	1883	1880	1881	1888	1880	867
165°	1985	1981	1979	1990	1981	561
175°	2032	2025	2026	2035	2025	193
180°	2032	2032	2032	2032	2032	



TEST NUMBER: P332408-840

CATALOG NUMBER: S123RDIW-S340D1535U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2
2.5°	582.1	581.7	581.4	581.1	580.8	580.1	579.1	578.0	577.0	576.0	576.9
5°	580.2	579.7	579.2	578.7	578.0	577.2	575.9	574.7	573.4	572.2	573.1
7.5°	574.8	574.2	573.7	573.1	572.6	571.5	569.9	568.3	566.5	564.9	565.4
10°	570.3	569.6	568.9	568.2	567.3	566.0	564.2	562.3	560.4	558.6	558.7
12.5°	563.9	563.1	562.3	561.5	560.7	559.1	556.7	554.5	552.2	549.9	549.8
15°	553.4	552.2	551.1	549.9	548.8	546.7	543.8	540.9	538.0	535.0	534.5
17.5°	540.1	538.8	537.5	536.0	534.7	532.2	528.5	524.7	521.1	517.4	516.2
20°	530.3	528.7	526.9	525.3	523.6	520.8	516.8	512.8	508.9	504.9	503.5
22.5°	519.4	517.5	515.5	513.6	511.7	508.7	504.4	500.2	495.9	491.7	490.0
25°	503.5	500.9	498.3	495.6	493.0	489.3	484.5	479.7	474.8	470.1	467.9
27.5°	484.2	481.3	478.4	475.5	472.6	468.6	463.2	457.8	452.4	447.1	444.0
30°	471.0	467.9	464.7	461.6	458.5	453.9	448.1	442.2	436.4	430.5	427.0
32.5°	457.9	454.2	450.7	447.2	443.6	438.8	432.5	426.4	420.2	413.9	410.1
35°	435.8	431.9	428.2	424.4	420.7	415.6	409.1	402.5	396.1	389.6	385.2
37.5°	413.3	409.1	405.0	400.8	396.6	391.0	384.2	377.2	370.3	363.3	358.3
40°	399.0	394.5	389.8	385.3	380.6	374.6	367.2	359.7	352.3	344.9	339.5
42.5°	382.8	378.2	373.7	369.0	364.5	358.3	350.6	343.0	335.3	327.6	321.6
45°	358.1	353.4	348.7	344.0	339.2	332.9	324.9	316.8	308.7	300.6	294.7
47.5°	333.4	328.2	323.0	317.8	312.7	306.1	298.0	289.9	282.0	273.9	267.4
50°	315.3	310.3	305.5	300.5	295.6	288.9	280.4	272.0	263.5	255.0	248.5
52.5°	299.1	293.8	288.4	283.1	277.7	270.8	262.5	254.1	245.7	237.3	230.7
55°	272.0	266.8	261.8	256.6	251.5	244.5	235.6	226.7	217.8	208.9	202.9
57.5°	246.9	241.4	235.8	230.1	224.6	217.3	208.4	199.4	190.6	181.7	175.9
60°	229.6	223.9	218.1	212.4	206.6	199.4	190.8	182.1	173.4	164.7	159.1
62.5°	212.3	206.5	200.8	195.1	189.3	182.1	173.4	164.7	156.0	147.3	142.1
65°	185.9	180.2	174.4	168.6	162.9	155.9	147.7	139.6	131.5	123.3	118.2
67.5°	159.5	153.6	147.7	142.0	136.1	129.4	121.5	113.7	105.8	98.1	94.2
70°	142.1	136.4	130.8	125.1	119.6	113.0	105.7	98.4	91.1	83.7	80.1
72.5°	124.8	119.3	113.7	108.1	102.5	96.4	89.8	83.1	76.4	69.8	66.9
75°	98.4	93.3	88.3	83.3	78.3	72.9	67.2	61.4	55.6	49.9	48.9
77.5°	74.2	69.7	65.1	60.6	56.1	52.0	48.3	44.5	40.9	37.2	36.7
80°	58.8	54.5	50.3	45.9	41.7	38.5	36.3	34.0	31.8	29.7	29.3
82.5°	44.1	40.4	36.8	33.0	29.3	27.0	26.0	24.9	23.9	22.8	22.5
85°	24.9	22.6	20.3	18.1	15.8	14.4	14.1	13.8	13.5	13.1	12.9
87.5°	9.3	9.1	8.9	8.6	8.4	8.7	9.5	10.4	11.3	12.1	12.3
90°	1.5	4.8	8.2	11.6	14.9	18.8	23.1	27.5	31.9	36.3	37.6
92.5°	28.1	27.2	26.2	25.2	24.3	25.4	28.8	32.1	35.3	38.7	40.8
95°	92.1	78.4	64.6	50.8	37.1	32.0	35.7	39.4	43.1	46.8	49.2
97.5°	185.1	178.9	172.8	166.5	160.4	145.2	121.1	96.9	72.8	48.6	51.3
100°	255.2	261.9	268.5	275.3	282.0	259.1	206.8	154.5	102.2	49.8	52.5
102.5°	334.9	339.7	344.6	349.3	354.2	328.0	270.8	213.7	156.5	99.4	91.0
105°	449.9	453.6	457.3	461.0	464.6	451.4	421.2	391.0	360.8	330.6	271.2
107.5°	571.3	574.2	577.1	580.2	583.1	586.9	591.7	596.5	601.3	606.0	562.5
110°	652.2	654.9	657.5	660.2	663.0	666.1	669.8	673.5	677.2	680.9	669.8



TEST NUMBER: P332408-840

CATALOG NUMBER: S123RDIW-S340D1535U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	729.5	732.0	734.4	736.8	739.1	742.3	745.9	749.6	753.3	757.0	757.2
115°	843.9	846.0	848.0	850.0	852.0	854.5	857.6	860.5	863.5	866.6	869.9
117.5°	954.7	957.3	959.7	962.2	964.7	966.7	968.3	969.8	971.3	972.9	975.5
120°	1023.6	1026.6	1029.7	1032.7	1035.7	1037.7	1038.6	1039.7	1040.7	1041.7	1044.4
122.5°	1093.7	1096.1	1098.6	1101.1	1103.6	1105.5	1106.7	1108.0	1109.2	1110.5	1112.5
125°	1189.6	1192.3	1195.1	1197.7	1200.4	1202.4	1203.8	1205.1	1206.5	1207.8	1208.5
127.5°	1282.6	1285.4	1288.1	1290.7	1293.4	1295.6	1297.2	1298.8	1300.4	1302.0	1303.0
130°	1340.6	1343.3	1346.0	1348.7	1351.4	1353.4	1354.7	1356.0	1357.5	1358.8	1360.1
132.5°	1396.2	1398.9	1401.6	1404.2	1406.9	1408.9	1409.9	1411.0	1412.0	1413.1	1414.4
135°	1481.1	1483.1	1485.1	1487.1	1489.1	1490.8	1492.1	1493.5	1494.8	1496.1	1497.1
137.5°	1553.5	1556.1	1558.6	1561.2	1563.7	1565.4	1566.1	1566.8	1567.6	1568.3	1569.9
140°	1601.8	1603.9	1605.9	1607.9	1609.9	1611.3	1612.4	1613.4	1614.4	1615.4	1616.8
142.5°	1646.5	1648.5	1650.5	1652.5	1654.6	1656.1	1657.1	1658.1	1659.1	1660.1	1661.1
145°	1709.0	1711.3	1713.7	1716.1	1718.4	1719.9	1720.6	1721.2	1721.9	1722.6	1723.2
147.5°	1767.9	1769.5	1771.0	1772.5	1774.0	1775.1	1775.8	1776.6	1777.2	1777.9	1778.6
150°	1804.1	1805.1	1806.1	1807.2	1808.2	1809.0	1809.7	1810.4	1811.0	1811.7	1812.3
152.5°	1836.7	1837.2	1837.7	1838.2	1838.7	1839.1	1839.5	1839.9	1840.3	1840.7	1841.9
155°	1882.6	1882.0	1881.3	1880.7	1880.0	1879.8	1880.2	1880.5	1880.8	1881.1	1882.8
157.5°	1918.2	1918.2	1918.1	1918.0	1918.0	1917.8	1917.4	1917.1	1916.8	1916.4	1918.4
160°	1940.1	1939.6	1939.3	1939.0	1938.6	1938.3	1938.0	1937.6	1937.3	1937.0	1939.0
162.5°	1960.6	1959.6	1958.8	1957.9	1957.0	1956.4	1956.1	1955.8	1955.4	1955.1	1957.4
165°	1985.3	1984.3	1983.3	1982.3	1981.3	1980.6	1980.2	1979.9	1979.6	1979.2	1982.0
167.5°	2004.6	2003.3	2002.0	2000.6	1999.2	1998.6	1998.6	1998.6	1998.6	1998.6	2001.2
170°	2015.5	2014.2	2012.8	2011.4	2010.1	2009.4	2009.4	2009.4	2009.4	2009.4	2012.2
172.5°	2022.8	2021.1	2019.5	2017.9	2016.3	2015.6	2015.9	2016.2	2016.4	2016.7	2019.4
175°	2032.1	2030.4	2028.7	2027.1	2025.4	2024.7	2025.1	2025.4	2025.7	2026.1	2028.4
177.5°	2034.5	2033.2	2031.8	2030.5	2029.1	2028.6	2028.9	2029.1	2029.4	2029.7	2031.8
180°	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1



TEST NUMBER: P332408-840

CATALOG NUMBER: S123RDIW-S340D1535U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2
2.5°	577.8	578.8	579.8	580.1	580.0	579.8	579.6	579.5
5°	574.1	575.0	575.9	576.3	576.1	575.9	575.7	575.5
7.5°	566.0	566.5	567.0	567.1	566.7	566.4	566.0	565.7
10°	558.8	558.9	559.0	558.8	558.3	557.7	557.1	556.6
12.5°	549.8	549.7	549.7	549.3	548.7	548.1	547.4	546.8
15°	533.9	533.4	532.9	532.3	531.6	530.8	530.1	529.4
17.5°	515.1	514.0	512.9	511.8	510.7	509.6	508.6	507.5
20°	502.2	500.8	499.5	498.2	496.9	495.6	494.4	493.1
22.5°	488.4	486.7	484.9	483.5	482.3	481.2	480.0	478.9
25°	465.6	463.5	461.3	459.6	458.5	457.4	456.2	455.0
27.5°	441.0	438.0	434.9	432.5	430.7	429.0	427.3	425.5
30°	423.4	419.9	416.4	413.7	412.0	410.4	408.7	407.0
32.5°	406.2	402.3	398.4	395.6	393.8	392.1	390.3	388.6
35°	380.6	376.1	371.6	368.4	366.6	364.7	362.7	360.9
37.5°	353.1	348.0	343.0	339.2	336.9	334.6	332.2	329.9
40°	334.1	328.6	323.2	319.2	316.8	314.5	312.0	309.6
42.5°	315.7	309.8	303.9	299.8	297.6	295.5	293.4	291.1
45°	288.7	282.8	276.8	272.6	270.1	267.6	265.1	262.6
47.5°	260.8	254.4	247.9	243.6	241.4	239.1	236.8	234.6
50°	242.1	235.6	229.1	224.7	222.3	219.8	217.4	215.0
52.5°	223.9	217.1	210.5	206.0	203.8	201.7	199.5	197.3
55°	196.8	190.8	184.7	180.6	178.5	176.4	174.3	172.2
57.5°	170.2	164.4	158.8	154.9	153.2	151.4	149.7	147.8
60°	153.4	147.7	142.1	138.4	136.6	134.8	133.1	131.3
62.5°	136.7	131.5	126.1	122.5	120.7	118.9	116.9	115.1
65°	113.0	108.0	102.8	99.7	98.5	97.4	96.2	95.0
67.5°	90.4	86.5	82.7	80.2	79.0	77.8	76.5	75.3
70°	76.4	72.8	69.1	66.8	65.5	64.4	63.2	62.1
72.5°	63.8	60.9	57.9	56.1	55.6	55.1	54.7	54.2
75°	47.8	46.8	45.6	45.0	44.8	44.6	44.4	44.2
77.5°	36.1	35.4	34.9	34.5	34.3	34.1	33.9	33.7
80°	29.0	28.7	28.4	28.2	27.9	27.7	27.5	27.3
82.5°	22.2	21.9	21.6	21.4	21.4	21.3	21.3	21.3
85°	12.7	12.5	12.3	12.2	12.2	12.2	12.2	12.2
87.5°	12.5	12.7	12.9	13.0	13.0	13.1	13.1	13.2
90°	38.9	40.3	41.6	42.6	43.3	43.9	44.6	45.2
92.5°	42.9	45.1	47.3	48.5	48.9	49.3	49.7	50.1
95°	51.5	53.8	56.1	57.4	57.4	57.4	57.4	57.4
97.5°	54.0	56.7	59.4	60.9	61.2	61.5	61.9	62.2
100°	55.1	57.9	60.6	62.1	62.4	62.7	63.1	63.4
102.5°	82.7	74.4	66.0	62.2	62.8	63.4	64.0	64.6
105°	211.9	152.5	93.1	63.7	64.4	65.1	65.7	66.4
107.5°	518.9	475.3	431.8	387.7	343.0	298.1	253.4	208.6
110°	658.7	647.6	636.6	607.0	559.1	511.1	463.1	415.2



TEST NUMBER: P332408-840

CATALOG NUMBER: S123RDIW-S340D1535U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	757.4	757.6	757.8	752.9	742.7	732.6	722.5	712.3
115°	873.3	876.7	880.0	882.3	883.7	885.0	886.4	887.8
117.5°	978.3	980.9	983.6	985.1	985.3	985.6	985.9	986.1
120°	1047.1	1049.8	1052.5	1053.8	1053.8	1053.8	1053.8	1053.8
122.5°	1114.3	1116.2	1118.1	1119.1	1119.4	1119.6	1119.9	1120.2
125°	1209.1	1209.8	1210.4	1211.1	1211.8	1212.4	1213.2	1213.9
127.5°	1304.1	1305.3	1306.3	1306.5	1305.9	1305.1	1304.4	1303.8
130°	1361.4	1362.8	1364.1	1364.4	1363.8	1363.1	1362.4	1361.8
132.5°	1415.8	1417.1	1418.5	1418.7	1417.7	1416.8	1415.8	1414.9
135°	1498.1	1499.1	1500.2	1500.2	1499.1	1498.1	1497.1	1496.1
137.5°	1571.6	1573.2	1574.8	1575.2	1574.6	1573.9	1573.2	1572.6
140°	1618.1	1619.4	1620.7	1621.1	1620.4	1619.8	1619.1	1618.4
142.5°	1662.2	1663.3	1664.4	1664.5	1663.6	1662.5	1661.6	1660.7
145°	1723.9	1724.6	1725.3	1725.7	1725.7	1725.7	1725.7	1725.7
147.5°	1779.2	1779.9	1780.6	1780.1	1778.6	1777.1	1775.4	1773.9
150°	1813.0	1813.7	1814.3	1814.2	1813.2	1812.2	1811.2	1810.2
152.5°	1843.1	1844.3	1845.5	1845.3	1843.8	1842.2	1840.7	1839.2
155°	1884.5	1886.1	1887.8	1887.6	1885.6	1883.6	1881.6	1879.7
157.5°	1920.5	1922.5	1924.5	1924.2	1921.6	1918.9	1916.3	1913.7
160°	1941.1	1943.0	1945.0	1944.9	1942.5	1940.2	1937.8	1935.5
162.5°	1959.6	1962.0	1964.2	1964.3	1962.3	1960.1	1958.1	1956.0
165°	1984.6	1987.3	1990.0	1990.1	1987.8	1985.5	1983.1	1980.7
167.5°	2004.0	2006.6	2009.3	2009.3	2006.6	2004.0	2001.2	1998.6
170°	2014.8	2017.5	2020.2	2020.2	2017.5	2014.8	2012.2	2009.4
172.5°	2022.1	2024.8	2027.4	2027.3	2024.4	2021.4	2018.4	2015.5
175°	2030.7	2033.1	2035.5	2035.3	2032.6	2029.9	2027.2	2024.6
177.5°	2034.0	2036.1	2038.3	2038.0	2035.3	2032.7	2029.9	2027.3
180°	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1	2032.1

(END OF REPORT)