

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332427-840

Luminaire Tested: **S123RDIW-S560D1535U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332427-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D1535U840-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7626.5 lumens
Efficiency: N/A
Efficacy: 125.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332427-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332427-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	30
1	94	89	86	83	84	80	77	75	63	61	60	48	47	45	33	33	32	26
2	85	78	73	68	76	71	66	62	56	53	50	42	40	38	30	29	28	22
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24	19
4	72	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	13
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	14	12
8	52	40	33	28	46	36	30	26	29	25	21	23	20	17	17	15	13	10
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	15	13	12	10
10	45	33	27	22	40	30	24	20	25	20	17	19	16	14	14	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9725	9725	9725	9725
5°	11594	9767	8602	9767
10°	14476	9711	7770	9711
15°	16992	9611	7086	9611
20°	18963	9464	6504	9464
25°	18659	9308	6147	9308
30°	13412	9163	5778	9163
35°	8956	8976	5540	8976
40°	6598	8751	5295	8751
45°	5535	8356	5051	8356
50°	4883	7839	4716	7839
55°	4282	7246	4252	7246
60°	3813	6678	3899	6678
65°	3349	6067	3627	6067
70°	2628	5526	3311	5526
75°	2316	4824	3023	4824
80°	2015	4097	2975	4097
85°	1618	3298	3149	3298



TEST NUMBER: P332427-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.9	1.2
10°-20°	277.6	3.6
20°-30°	436.1	5.7
30°-40°	455.0	6.0
40°-50°	389.4	5.1
50°-60°	296.8	3.9
60°-70°	190.2	2.5
70°-80°	91.5	1.2
80°-90°	30.0	0.4
90°-100°	126.3	1.7
100°-110°	378.0	5.0
110°-120°	642.9	8.4
120°-130°	845.6	11.1
130°-140°	950.5	12.5
140°-150°	934.3	12.3
150°-160°	786.5	10.3
160°-170°	523.6	6.9
170°-180°	183.3	2.4
0°-30°	802.6	10.5
0°-40°	1257.6	16.5
0°-60°	1943.7	25.5
0°-90°	2255.4	29.6
90°-120°	1147.2	15.0
90°-150°	3877.6	50.8
90°-180°	5371.0	70.4
0°-180°	7626.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	904	904	904	904	904	
5°	1073	904	796	904	1073	111
15°	1525	862	636	862	1525	432
25°	1571	784	518	784	1571	675
35°	682	683	422	683	682	447
45°	364	549	332	549	364	286
55°	228	386	227	386	228	206
65°	132	238	142	238	132	129
75°	56	116	73	116	56	60
85°	13	27	26	27	13	16
90°	46	2	46	2	46	23
95°	119	90	119	90	119	122
105°	362	343	362	343	362	385
115°	649	647	649	647	649	642
125°	936	947	936	947	936	837
135°	1227	1229	1227	1229	1227	944
145°	1491	1491	1491	1491	1491	931
155°	1704	1707	1704	1707	1704	785
165°	1853	1859	1853	1859	1853	523
175°	1926	1934	1926	1934	1926	183
180°	1938	1938	1938	1938	1938	



TEST NUMBER: P332427-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	962.3	963.6	959.6	959.0	954.3	953.1	953.1	946.5	942.5	937.3	934.2
5°	1073.0	1079.1	1076.1	1069.1	1057.5	1054.8	1047.4	1035.8	1022.7	1006.4	998.8
7.5°	1211.1	1219.6	1216.3	1205.6	1193.5	1183.6	1162.9	1143.6	1116.6	1093.0	1072.7
10°	1324.4	1315.5	1308.6	1298.1	1286.9	1268.7	1247.1	1217.3	1182.9	1155.8	1125.6
12.5°	1409.2	1407.8	1398.9	1388.2	1372.3	1355.0	1328.4	1292.1	1252.1	1212.9	1178.5
15°	1524.8	1527.1	1521.3	1510.1	1487.6	1457.0	1416.8	1401.8	1344.5	1301.9	1259.4
17.5°	1604.8	1604.3	1603.5	1587.9	1565.1	1543.3	1506.0	1466.3	1414.5	1354.5	1297.3
20°	1655.5	1651.6	1652.4	1635.0	1618.0	1592.9	1556.5	1498.8	1456.3	1387.0	1327.9
22.5°	1654.3	1653.5	1656.4	1650.4	1638.1	1618.8	1590.2	1541.6	1487.2	1417.3	1350.8
25°	1571.1	1568.1	1586.3	1591.2	1611.0	1614.5	1606.0	1579.3	1527.8	1455.9	1373.5
27.5°	1314.9	1313.2	1347.0	1389.2	1442.8	1484.4	1524.6	1544.0	1527.8	1476.3	1393.8
30°	1079.1	1115.5	1132.6	1193.7	1261.7	1342.9	1414.1	1481.8	1498.4	1476.0	1408.4
32.5°	896.0	927.7	941.9	994.4	1057.8	1153.0	1259.7	1355.5	1423.3	1440.5	1399.7
35°	681.6	682.0	714.4	737.6	796.4	894.2	997.9	1126.3	1253.9	1350.7	1360.8
37.5°	543.8	545.7	565.4	588.5	632.7	684.4	775.7	882.4	1029.9	1178.3	1265.4
40°	469.6	473.0	487.8	510.6	542.3	581.4	652.6	753.1	876.1	1041.3	1176.3
42.5°	421.9	427.6	435.2	452.7	472.3	509.0	566.5	644.2	756.0	912.2	1067.9
45°	363.6	366.7	372.4	380.6	398.4	423.9	462.6	514.8	607.6	733.4	889.3
47.5°	320.7	319.1	325.2	331.8	343.7	361.0	387.0	429.6	495.8	596.6	728.9
50°	291.6	291.2	295.5	300.5	311.7	324.6	345.8	377.9	430.5	514.0	635.1
52.5°	264.4	265.9	268.9	275.2	283.3	293.6	312.7	335.8	381.0	453.1	554.0
55°	228.2	229.3	233.6	237.1	242.9	253.4	265.4	284.7	315.6	365.9	449.1
57.5°	197.5	197.0	201.2	202.0	208.5	217.0	226.3	241.4	263.8	301.1	357.2
60°	177.1	176.0	179.5	182.2	185.6	192.6	200.4	215.1	232.9	260.3	308.3
62.5°	158.5	158.0	160.6	163.3	166.1	172.5	179.0	190.3	204.4	227.5	265.6
65°	131.5	132.7	133.8	135.0	136.5	140.4	146.6	154.3	164.0	180.3	207.7
67.5°	103.3	104.5	104.9	107.2	110.6	113.0	116.8	123.7	130.5	144.1	159.8
70°	83.5	83.1	83.5	84.7	89.0	93.2	98.3	103.3	107.6	117.2	130.4
72.5°	71.8	71.1	72.1	72.3	74.4	75.5	78.8	83.5	89.0	95.5	105.0
75°	55.7	55.7	55.7	55.7	57.3	58.1	59.2	60.4	62.3	65.3	72.3
77.5°	41.2	41.2	41.8	42.1	42.5	42.9	43.6	44.8	45.4	47.2	50.1
80°	32.5	32.9	32.5	32.9	32.9	33.6	34.0	35.2	35.5	37.6	38.7
82.5°	24.4	24.2	24.4	24.8	24.8	25.7	25.7	26.6	26.7	27.6	28.8
85°	13.1	12.4	13.1	12.7	13.5	12.7	13.1	13.9	13.9	14.3	15.9
87.5°	12.2	12.7	11.9	12.1	12.0	12.1	11.8	11.6	11.9	11.3	10.8
90°	45.6	45.0	44.3	43.6	43.0	42.0	40.6	39.3	37.9	36.6	32.1
92.5°	61.5	61.9	62.3	62.7	63.1	62.8	61.7	60.6	59.6	58.5	55.9
95°	118.8	118.8	118.8	118.8	118.8	118.1	116.7	115.4	114.0	112.7	110.0
97.5°	182.8	182.9	183.0	183.2	183.3	182.6	181.0	179.5	177.9	176.3	174.4
100°	231.5	230.8	230.1	229.4	228.7	227.9	226.9	225.9	224.9	223.9	222.2
102.5°	281.4	281.6	281.7	281.9	282.0	281.6	280.5	279.5	278.5	277.4	275.2
105°	362.4	361.7	361.1	360.4	359.7	359.4	359.4	359.4	359.4	359.4	356.4
107.5°	446.8	447.2	447.6	448.0	448.4	448.1	447.0	446.0	444.8	443.7	442.5
110°	504.0	504.7	505.4	506.0	506.8	506.4	505.0	503.7	502.4	501.0	500.3



TEST NUMBER: P332427-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	564.9	565.1	565.2	565.4	565.5	564.7	563.1	561.5	559.9	558.3	558.2
115°	648.7	649.0	649.4	649.7	650.1	650.1	649.7	649.4	649.0	648.7	649.4
117.5°	733.7	734.7	735.6	736.5	737.5	738.0	738.1	738.1	738.2	738.3	739.1
120°	793.3	794.1	794.8	795.5	796.1	796.6	797.0	797.3	797.6	798.0	799.6
122.5°	850.6	851.6	852.5	853.5	854.4	855.4	856.3	857.1	858.0	858.9	859.8
125°	936.5	937.9	939.3	940.6	941.9	943.3	944.6	946.0	947.4	948.8	949.4
127.5°	1022.1	1023.7	1025.2	1026.8	1028.3	1030.1	1032.0	1033.9	1035.7	1037.6	1038.4
130°	1078.1	1080.6	1082.9	1085.3	1087.6	1089.5	1090.9	1092.2	1093.6	1094.9	1095.9
132.5°	1136.6	1138.4	1140.3	1142.2	1144.0	1145.7	1147.3	1148.9	1150.5	1152.2	1152.9
135°	1227.4	1228.1	1228.7	1229.4	1230.1	1231.1	1232.4	1233.9	1235.2	1236.6	1236.9
137.5°	1307.5	1308.8	1310.1	1311.3	1312.6	1314.0	1315.5	1316.9	1318.3	1319.7	1318.8
140°	1359.9	1362.2	1364.6	1367.0	1369.4	1370.7	1371.1	1371.4	1371.7	1372.1	1371.7
142.5°	1413.5	1415.3	1417.1	1419.0	1420.8	1421.9	1422.2	1422.6	1422.9	1423.2	1422.6
145°	1490.9	1492.2	1493.6	1494.9	1496.2	1497.1	1497.4	1497.7	1498.1	1498.4	1497.4
147.5°	1559.6	1561.7	1563.8	1565.8	1567.8	1568.8	1568.8	1568.8	1568.8	1568.8	1567.8
150°	1603.6	1605.6	1607.6	1609.6	1611.6	1612.7	1612.7	1612.7	1612.7	1612.7	1611.9
152.5°	1646.2	1647.9	1649.7	1651.4	1653.3	1653.9	1653.3	1652.7	1652.2	1651.6	1651.2
155°	1704.0	1706.4	1708.8	1711.1	1713.5	1714.0	1712.6	1711.3	1710.0	1708.6	1708.3
157.5°	1756.8	1758.6	1760.5	1762.4	1764.3	1764.5	1763.1	1761.7	1760.3	1758.9	1758.6
160°	1790.8	1792.2	1793.5	1794.9	1796.2	1796.0	1794.4	1792.7	1791.0	1789.3	1789.3
162.5°	1816.4	1818.6	1820.8	1822.9	1825.1	1825.3	1823.6	1821.9	1820.3	1818.6	1818.3
165°	1853.3	1855.6	1858.1	1860.4	1862.8	1862.9	1860.9	1858.9	1856.8	1854.8	1854.8
167.5°	1884.6	1886.7	1888.9	1891.0	1893.0	1893.0	1891.0	1888.9	1886.7	1884.6	1884.4
170°	1900.5	1902.9	1905.2	1907.6	1910.0	1910.0	1907.6	1905.2	1902.9	1900.5	1900.5
172.5°	1912.7	1915.0	1917.4	1919.8	1922.2	1922.3	1920.2	1918.0	1916.0	1913.9	1913.9
175°	1926.4	1928.7	1931.1	1933.5	1935.8	1936.0	1934.0	1932.0	1930.0	1927.9	1927.9
177.5°	1933.7	1935.6	1937.4	1939.3	1941.3	1941.4	1939.7	1938.1	1936.5	1934.9	1934.9
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332427-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	932.9	932.0	927.7	922.7	916.3	911.9	908.5	906.7	901.1	894.2	889.6
5°	990.6	979.0	966.6	951.5	937.6	923.3	914.4	903.9	891.2	876.9	866.8
7.5°	1052.3	1029.6	1005.0	979.8	954.7	932.3	912.5	895.5	875.3	854.7	840.3
10°	1099.6	1066.4	1032.0	996.7	964.6	934.5	911.3	888.5	864.1	840.5	822.7
12.5°	1142.7	1098.9	1059.2	1015.9	974.9	938.9	905.4	878.6	849.3	824.2	803.9
15°	1197.1	1152.3	1104.3	1038.5	984.0	938.4	897.8	862.5	827.0	796.1	776.3
17.5°	1248.0	1180.5	1116.1	1061.2	990.4	933.3	883.7	841.6	802.6	769.8	745.5
20°	1269.1	1203.8	1133.7	1063.7	994.1	930.3	872.6	826.2	785.6	748.4	726.0
22.5°	1281.7	1207.7	1134.0	1058.7	984.8	918.5	861.5	810.4	766.4	731.1	703.5
25°	1296.6	1208.3	1127.1	1052.9	977.4	905.4	837.8	783.7	736.1	698.5	669.1
27.5°	1306.3	1202.5	1106.5	1024.0	947.5	875.9	813.9	756.4	708.1	668.4	636.9
30°	1308.2	1197.9	1090.8	1001.4	923.6	857.9	792.1	737.2	686.2	644.0	614.6
32.5°	1310.6	1186.5	1069.4	974.5	894.9	829.8	770.2	717.7	665.4	623.9	593.9
35°	1300.4	1180.1	1037.0	928.0	848.3	785.2	731.4	683.1	631.7	591.4	560.9
37.5°	1256.5	1155.0	1003.4	875.5	792.1	733.8	689.9	647.8	600.7	557.2	528.5
40°	1212.2	1130.2	977.4	843.6	756.6	696.6	657.1	622.8	577.1	536.4	505.5
42.5°	1146.3	1096.5	952.7	810.2	716.3	658.5	625.3	593.0	553.0	511.7	482.6
45°	1025.4	1032.0	902.0	757.0	660.7	602.6	571.3	548.9	513.3	479.3	449.5
47.5°	873.7	935.2	842.5	700.2	602.0	547.4	520.1	500.5	476.6	443.1	416.0
50°	774.8	862.5	794.9	662.2	565.1	511.0	483.9	468.1	447.2	420.8	395.0
52.5°	683.5	777.8	737.3	619.8	525.2	475.6	449.2	436.2	419.6	394.9	371.4
55°	557.3	652.9	643.6	555.8	465.3	420.8	400.7	386.1	374.8	356.3	337.7
57.5°	450.8	541.4	546.2	484.6	412.5	368.6	351.3	340.2	332.9	318.9	301.7
60°	383.7	466.9	483.1	436.7	374.8	336.1	319.1	310.2	304.4	293.2	280.0
62.5°	328.0	398.8	417.2	383.7	338.6	302.4	289.1	280.5	276.6	266.9	255.3
65°	251.1	309.8	327.6	309.0	285.5	256.4	245.6	238.2	234.8	229.3	220.9
67.5°	188.7	231.7	251.2	238.0	229.5	211.2	204.3	200.4	197.2	193.6	186.4
70°	151.6	183.4	203.5	200.0	193.0	183.4	178.3	175.6	172.5	169.5	163.2
72.5°	121.9	143.7	162.6	164.4	158.6	156.7	152.3	151.2	149.3	145.6	142.2
75°	80.9	95.9	109.1	114.1	116.4	118.4	116.4	116.0	115.6	112.6	110.6
77.5°	53.0	61.1	69.4	78.0	81.6	84.2	84.8	86.2	85.2	83.6	82.7
80°	40.6	42.5	48.4	55.7	61.5	63.8	65.3	66.1	65.7	65.3	63.8
82.5°	29.5	31.1	33.8	39.0	43.8	47.8	48.7	48.5	49.4	49.6	48.4
85°	15.9	16.3	17.1	17.8	20.5	24.7	26.0	26.7	27.5	27.5	25.1
87.5°	10.5	9.3	9.1	8.3	8.5	8.2	9.3	10.2	11.2	10.6	11.3
90°	27.8	23.3	19.0	15.0	11.7	8.3	4.9	1.5	4.9	8.3	11.7
92.5°	53.4	51.0	48.5	46.0	43.7	41.4	39.2	36.9	39.2	41.4	43.7
95°	107.2	104.5	101.9	99.4	96.9	94.6	92.2	89.9	92.2	94.6	96.9
97.5°	172.4	170.5	168.4	166.6	164.9	163.1	161.4	159.6	161.4	163.1	164.9
100°	220.5	218.7	217.1	215.2	213.2	211.2	209.1	207.1	209.1	211.2	213.2
102.5°	273.0	270.7	268.5	266.8	265.6	264.4	263.2	262.0	263.2	264.4	265.6
105°	353.3	350.2	347.2	345.4	344.7	344.0	343.4	342.6	343.4	344.0	344.7
107.5°	441.3	440.1	438.9	438.1	437.7	437.3	436.9	436.5	436.9	437.3	437.7
110°	499.7	499.0	498.3	497.7	497.0	496.2	495.6	494.9	495.6	496.2	497.0



TEST NUMBER: P332427-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	558.0	557.8	557.7	557.4	557.0	556.6	556.2	555.8	556.2	556.6	557.0
115°	650.1	650.8	651.5	651.3	650.3	649.2	648.2	647.2	648.2	649.2	650.3
117.5°	740.0	740.9	741.7	741.8	741.2	740.5	739.8	739.2	739.8	740.5	741.2
120°	801.3	803.0	804.8	804.6	802.5	800.5	798.5	796.5	798.5	800.5	802.5
122.5°	860.6	861.5	862.4	862.1	860.6	859.1	857.6	856.2	857.6	859.1	860.6
125°	950.1	950.8	951.4	951.3	950.3	949.3	948.2	947.2	948.2	949.3	950.3
127.5°	1039.2	1039.9	1040.7	1040.0	1037.7	1035.6	1033.4	1031.3	1033.4	1035.6	1037.7
130°	1096.9	1097.9	1098.9	1098.1	1095.4	1092.7	1090.0	1087.3	1090.0	1092.7	1095.4
132.5°	1153.7	1154.4	1155.2	1154.2	1151.4	1148.7	1146.0	1143.4	1146.0	1148.7	1151.4
135°	1237.2	1237.6	1237.9	1237.1	1235.0	1232.9	1230.9	1228.9	1230.9	1232.9	1235.0
137.5°	1317.9	1317.1	1316.2	1314.8	1313.2	1311.5	1309.8	1308.1	1309.8	1311.5	1313.2
140°	1371.4	1371.1	1370.7	1369.7	1368.0	1366.3	1364.6	1362.9	1364.6	1366.3	1368.0
142.5°	1422.0	1421.4	1420.8	1419.7	1418.0	1416.2	1414.5	1412.9	1414.5	1416.2	1418.0
145°	1496.4	1495.4	1494.4	1493.6	1492.9	1492.2	1491.6	1490.9	1491.6	1492.2	1492.9
147.5°	1566.9	1566.0	1565.0	1564.0	1562.8	1561.5	1560.2	1559.0	1560.2	1561.5	1562.8
150°	1611.3	1610.6	1609.9	1609.3	1608.6	1607.9	1607.3	1606.6	1607.3	1607.9	1608.6
152.5°	1650.8	1650.4	1650.0	1649.3	1648.4	1647.5	1646.5	1645.6	1646.5	1647.5	1648.4
155°	1707.9	1707.6	1707.3	1707.1	1707.1	1707.1	1707.1	1707.1	1707.1	1707.1	1707.1
157.5°	1758.3	1758.1	1757.8	1757.9	1758.3	1758.7	1759.1	1759.5	1759.1	1758.7	1758.3
160°	1789.3	1789.3	1789.3	1789.7	1790.3	1791.0	1791.7	1792.4	1791.7	1791.0	1790.3
162.5°	1818.1	1817.8	1817.5	1817.9	1818.8	1819.7	1820.7	1821.6	1820.7	1819.7	1818.8
165°	1854.8	1854.8	1854.8	1855.3	1856.3	1857.3	1858.4	1859.4	1858.4	1857.3	1856.3
167.5°	1884.1	1883.8	1883.6	1884.1	1885.4	1886.8	1888.1	1889.6	1888.1	1886.8	1885.4
170°	1900.5	1900.5	1900.5	1901.2	1902.5	1903.9	1905.2	1906.5	1905.2	1903.9	1902.5
172.5°	1913.9	1913.9	1913.9	1914.6	1915.9	1917.2	1918.6	1920.0	1918.6	1917.2	1915.9
175°	1927.9	1927.9	1927.9	1928.5	1930.0	1931.3	1932.7	1934.0	1932.7	1931.3	1930.0
177.5°	1934.9	1934.9	1934.9	1935.4	1936.5	1937.6	1938.7	1939.7	1938.7	1937.6	1936.5
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332427-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	888.1	884.0	881.3	875.0	871.1	866.8	862.4	865.2	864.8	864.5	864.5
5°	858.3	849.4	841.3	830.8	824.3	816.2	809.9	809.2	810.7	805.3	802.2
7.5°	828.8	816.6	805.1	793.6	781.3	771.5	765.5	762.7	758.7	755.4	751.8
10°	808.0	793.8	782.4	768.2	755.1	743.5	736.1	731.0	728.3	725.6	720.6
12.5°	786.7	772.6	758.3	742.1	729.6	716.2	710.7	705.1	699.8	696.8	689.9
15°	755.4	737.2	722.2	705.1	691.3	678.0	670.3	659.1	657.5	653.7	646.7
17.5°	724.1	704.4	683.6	671.0	655.2	641.6	629.8	626.0	614.9	610.8	604.7
20°	699.3	681.2	665.3	648.6	625.8	613.1	603.8	598.7	589.9	584.4	580.6
22.5°	678.0	659.4	641.2	621.8	602.9	588.7	581.8	574.0	569.2	561.6	557.3
25°	647.5	627.4	605.3	584.4	570.9	560.1	549.3	542.3	535.3	531.8	524.1
27.5°	612.1	591.1	570.5	554.6	538.0	527.3	517.5	511.3	502.9	497.1	492.8
30°	592.6	567.8	550.1	535.7	514.4	504.4	497.1	489.3	483.1	477.0	472.6
32.5°	570.0	547.3	530.5	512.8	496.4	485.5	475.9	469.2	463.9	458.1	453.8
35°	534.5	515.6	498.2	480.4	468.4	457.2	446.0	440.2	435.2	429.7	425.9
37.5°	502.5	484.8	468.3	451.4	436.6	427.4	418.4	413.9	407.2	403.5	399.6
40°	482.7	465.3	447.6	431.3	415.8	408.9	400.7	394.2	388.0	385.3	381.0
42.5°	461.1	443.6	428.7	411.1	398.5	389.0	381.5	374.4	369.7	365.8	363.3
45°	429.0	413.4	398.8	381.4	369.4	361.2	352.7	346.2	341.9	339.2	335.0
47.5°	397.8	382.3	367.4	352.2	340.6	331.3	322.9	318.2	312.7	309.3	306.4
50°	375.2	361.2	345.4	331.4	319.9	310.6	303.7	297.8	292.8	288.5	286.6
52.5°	354.5	339.6	325.9	313.0	300.7	290.1	283.9	277.7	274.0	269.0	266.8
55°	320.2	306.0	294.4	281.6	269.6	260.7	253.0	247.5	243.7	238.2	235.2
57.5°	288.1	275.3	261.5	250.4	238.0	230.6	224.1	216.7	212.1	207.8	204.8
60°	266.5	251.8	239.8	229.3	218.5	208.8	203.1	197.2	192.3	187.9	185.3
62.5°	243.9	231.1	219.7	208.3	198.4	190.0	183.3	178.3	174.0	171.3	168.5
65°	209.2	199.2	187.6	178.3	169.1	162.9	157.4	153.2	150.1	148.1	145.8
67.5°	177.4	167.6	157.5	148.3	142.2	137.4	133.9	130.3	128.8	126.2	124.7
70°	156.6	146.6	137.7	130.8	124.5	121.1	118.8	116.0	114.5	111.4	109.9
72.5°	134.1	126.8	120.4	114.6	109.7	106.5	103.6	100.3	97.8	94.4	92.8
75°	105.6	99.1	94.0	90.1	87.1	82.8	78.6	75.0	73.9	72.7	72.3
77.5°	78.2	74.0	70.4	67.2	63.3	60.2	59.3	58.5	58.3	57.7	57.7
80°	61.5	57.7	54.9	51.1	48.8	48.8	48.8	48.0	48.4	48.4	48.4
82.5°	45.7	42.1	40.7	39.3	38.9	39.2	39.2	39.3	39.1	39.7	39.4
85°	23.6	23.9	24.7	24.3	24.7	24.7	25.5	25.1	25.5	24.7	25.5
87.5°	11.7	13.4	14.5	15.8	17.0	17.5	18.1	18.4	19.0	19.2	19.4
90°	15.0	19.0	23.3	27.8	32.1	36.6	37.9	39.3	40.6	42.0	43.0
92.5°	46.0	48.5	51.0	53.4	55.9	58.5	59.6	60.6	61.7	62.8	63.1
95°	99.4	101.9	104.5	107.2	110.0	112.7	114.0	115.4	116.7	118.1	118.8
97.5°	166.6	168.4	170.5	172.4	174.4	176.3	177.9	179.5	181.0	182.6	183.3
100°	215.2	217.1	218.7	220.5	222.2	223.9	224.9	225.9	226.9	227.9	228.7
102.5°	266.8	268.5	270.7	273.0	275.2	277.4	278.5	279.5	280.5	281.6	282.0
105°	345.4	347.2	350.2	353.3	356.4	359.4	359.4	359.4	359.4	359.4	359.7
107.5°	438.1	438.9	440.1	441.3	442.5	443.7	444.8	446.0	447.0	448.1	448.4
110°	497.7	498.3	499.0	499.7	500.3	501.0	502.4	503.7	505.0	506.4	506.8



TEST NUMBER: P332427-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	557.4	557.7	557.8	558.0	558.2	558.3	559.9	561.5	563.1	564.7	565.5
115°	651.3	651.5	650.8	650.1	649.4	648.7	649.0	649.4	649.7	650.1	650.1
117.5°	741.8	741.7	740.9	740.0	739.1	738.3	738.2	738.1	738.1	738.0	737.5
120°	804.6	804.8	803.0	801.3	799.6	798.0	797.6	797.3	797.0	796.6	796.1
122.5°	862.1	862.4	861.5	860.6	859.8	858.9	858.0	857.1	856.3	855.4	854.4
125°	951.3	951.4	950.8	950.1	949.4	948.8	947.4	946.0	944.6	943.3	941.9
127.5°	1040.0	1040.7	1039.9	1039.2	1038.4	1037.6	1035.7	1033.9	1032.0	1030.1	1028.3
130°	1098.1	1098.9	1097.9	1096.9	1095.9	1094.9	1093.6	1092.2	1090.9	1089.5	1087.6
132.5°	1154.2	1155.2	1154.4	1153.7	1152.9	1152.2	1150.5	1148.9	1147.3	1145.7	1144.0
135°	1237.1	1237.9	1237.6	1237.2	1236.9	1236.6	1235.2	1233.9	1232.4	1231.1	1230.1
137.5°	1314.8	1316.2	1317.1	1317.9	1318.8	1319.7	1318.3	1316.9	1315.5	1314.0	1312.6
140°	1369.7	1370.7	1371.1	1371.4	1371.7	1372.1	1371.7	1371.4	1371.1	1370.7	1369.4
142.5°	1419.7	1420.8	1421.4	1422.0	1422.6	1423.2	1422.9	1422.6	1422.2	1421.9	1420.8
145°	1493.6	1494.4	1495.4	1496.4	1497.4	1498.4	1498.1	1497.7	1497.4	1497.1	1496.2
147.5°	1564.0	1565.0	1566.0	1566.9	1567.8	1568.8	1568.8	1568.8	1568.8	1568.8	1567.8
150°	1609.3	1609.9	1610.6	1611.3	1611.9	1612.7	1612.7	1612.7	1612.7	1612.7	1611.6
152.5°	1649.3	1650.0	1650.4	1650.8	1651.2	1651.6	1652.2	1652.7	1653.3	1653.9	1653.3
155°	1707.1	1707.3	1707.6	1707.9	1708.3	1708.6	1710.0	1711.3	1712.6	1714.0	1713.5
157.5°	1757.9	1757.8	1758.1	1758.3	1758.6	1758.9	1760.3	1761.7	1763.1	1764.5	1764.3
160°	1789.7	1789.3	1789.3	1789.3	1789.3	1789.3	1791.0	1792.7	1794.4	1796.0	1796.2
162.5°	1817.9	1817.5	1817.8	1818.1	1818.3	1818.6	1820.3	1821.9	1823.6	1825.3	1825.1
165°	1855.3	1854.8	1854.8	1854.8	1854.8	1854.8	1856.8	1858.9	1860.9	1862.9	1862.8
167.5°	1884.1	1883.6	1883.8	1884.1	1884.4	1884.6	1886.7	1888.9	1891.0	1893.0	1893.0
170°	1901.2	1900.5	1900.5	1900.5	1900.5	1900.5	1902.9	1905.2	1907.6	1910.0	1910.0
172.5°	1914.6	1913.9	1913.9	1913.9	1913.9	1913.9	1916.0	1918.0	1920.2	1922.3	1922.2
175°	1928.5	1927.9	1927.9	1927.9	1927.9	1927.9	1930.0	1932.0	1934.0	1936.0	1935.8
177.5°	1935.4	1934.9	1934.9	1934.9	1934.9	1934.9	1936.5	1938.1	1939.7	1941.4	1941.3
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332427-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	860.8	860.5	860.8	859.6	860.8	860.5	860.8	864.5	864.5	864.8	865.2
5°	801.0	800.6	799.5	796.1	799.5	800.6	801.0	802.2	805.3	810.7	809.2
7.5°	748.8	748.3	744.9	745.0	744.9	748.3	748.8	751.8	755.4	758.7	762.7
10°	717.9	718.3	713.7	710.9	713.7	718.3	717.9	720.6	725.6	728.3	731.0
12.5°	687.9	686.1	682.4	679.3	682.4	686.1	687.9	689.9	696.8	699.8	705.1
15°	648.2	644.4	635.1	635.9	635.1	644.4	648.2	646.7	653.7	657.5	659.1
17.5°	601.6	598.7	598.6	593.2	598.6	598.7	601.6	604.7	610.8	614.9	626.0
20°	574.4	572.5	573.2	567.8	573.2	572.5	574.4	580.6	584.4	589.9	598.7
22.5°	553.0	551.1	547.9	546.1	547.9	551.1	553.0	557.3	561.6	569.2	574.0
25°	521.8	518.7	515.6	517.6	515.6	518.7	521.8	524.1	531.8	535.3	542.3
27.5°	490.5	488.2	485.1	484.7	485.1	488.2	490.5	492.8	497.1	502.9	511.3
30°	470.7	468.4	466.9	464.9	466.9	468.4	470.7	472.6	477.0	483.1	489.3
32.5°	450.6	450.2	447.4	447.0	447.4	450.2	450.6	453.8	458.1	463.9	469.2
35°	424.3	422.0	421.2	421.6	421.2	422.0	424.3	425.9	429.7	435.2	440.2
37.5°	399.3	396.3	394.9	393.4	394.9	396.3	399.3	399.6	403.5	407.2	413.9
40°	381.4	378.3	377.5	376.8	377.5	378.3	381.4	381.0	385.3	388.0	394.2
42.5°	361.2	360.0	359.6	358.2	359.6	360.0	361.2	363.3	365.8	369.7	374.4
45°	333.8	333.5	331.1	331.8	331.1	333.5	333.8	335.0	339.2	341.9	346.2
47.5°	304.9	303.2	301.5	302.7	301.5	303.2	304.9	306.4	309.3	312.7	318.2
50°	285.1	284.3	280.8	281.6	280.8	284.3	285.1	286.6	288.5	292.8	297.8
52.5°	265.3	262.4	261.1	260.5	261.1	262.4	265.3	266.8	269.0	274.0	277.7
55°	232.5	228.9	227.4	226.6	227.4	228.9	232.5	235.2	238.2	243.7	247.5
57.5°	200.3	199.3	198.1	198.9	198.1	199.3	200.3	204.8	207.8	212.1	216.7
60°	181.4	181.4	181.4	181.1	181.4	181.4	181.4	185.3	187.9	192.3	197.2
62.5°	166.8	165.9	165.6	166.1	165.6	165.9	166.8	168.5	171.3	174.0	178.3
65°	144.6	144.3	142.7	142.4	142.7	144.3	144.6	145.8	148.1	150.1	153.2
67.5°	123.7	122.3	121.9	121.3	121.9	122.3	123.7	124.7	126.2	128.8	130.3
70°	108.0	107.1	104.8	105.2	104.8	107.1	108.0	109.9	111.4	114.5	116.0
72.5°	90.9	90.1	89.7	89.1	89.7	90.1	90.9	92.8	94.4	97.8	100.3
75°	71.9	71.6	71.2	72.7	71.2	71.6	71.9	72.3	72.7	73.9	75.0
77.5°	57.7	57.7	57.9	57.3	57.9	57.7	57.7	57.7	57.7	58.3	58.5
80°	48.4	48.4	48.0	48.0	48.0	48.4	48.4	48.4	48.4	48.4	48.0
82.5°	38.8	39.1	39.3	38.7	39.3	39.1	38.8	39.4	39.7	39.1	39.3
85°	25.5	25.1	26.0	25.5	26.0	25.1	25.5	25.5	24.7	25.5	25.1
87.5°	20.2	19.7	19.8	20.3	19.8	19.7	20.2	19.4	19.2	19.0	18.4
90°	43.6	44.3	45.0	45.6	45.0	44.3	43.6	43.0	42.0	40.6	39.3
92.5°	62.7	62.3	61.9	61.5	61.9	62.3	62.7	63.1	62.8	61.7	60.6
95°	118.8	118.8	118.8	118.8	118.8	118.8	118.8	118.8	118.1	116.7	115.4
97.5°	183.2	183.0	182.9	182.8	182.9	183.0	183.2	183.3	182.6	181.0	179.5
100°	229.4	230.1	230.8	231.5	230.8	230.1	229.4	228.7	227.9	226.9	225.9
102.5°	281.9	281.7	281.6	281.4	281.6	281.7	281.9	282.0	281.6	280.5	279.5
105°	360.4	361.1	361.7	362.4	361.7	361.1	360.4	359.7	359.4	359.4	359.4
107.5°	448.0	447.6	447.2	446.8	447.2	447.6	448.0	448.4	448.1	447.0	446.0
110°	506.0	505.4	504.7	504.0	504.7	505.4	506.0	506.8	506.4	505.0	503.7



TEST NUMBER: P332427-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	565.4	565.2	565.1	564.9	565.1	565.2	565.4	565.5	564.7	563.1	561.5
115°	649.7	649.4	649.0	648.7	649.0	649.4	649.7	650.1	650.1	649.7	649.4
117.5°	736.5	735.6	734.7	733.7	734.7	735.6	736.5	737.5	738.0	738.1	738.1
120°	795.5	794.8	794.1	793.3	794.1	794.8	795.5	796.1	796.6	797.0	797.3
122.5°	853.5	852.5	851.6	850.6	851.6	852.5	853.5	854.4	855.4	856.3	857.1
125°	940.6	939.3	937.9	936.5	937.9	939.3	940.6	941.9	943.3	944.6	946.0
127.5°	1026.8	1025.2	1023.7	1022.1	1023.7	1025.2	1026.8	1028.3	1030.1	1032.0	1033.9
130°	1085.3	1082.9	1080.6	1078.1	1080.6	1082.9	1085.3	1087.6	1089.5	1090.9	1092.2
132.5°	1142.2	1140.3	1138.4	1136.6	1138.4	1140.3	1142.2	1144.0	1145.7	1147.3	1148.9
135°	1229.4	1228.7	1228.1	1227.4	1228.1	1228.7	1229.4	1230.1	1231.1	1232.4	1233.9
137.5°	1311.3	1310.1	1308.8	1307.5	1308.8	1310.1	1311.3	1312.6	1314.0	1315.5	1316.9
140°	1367.0	1364.6	1362.2	1359.9	1362.2	1364.6	1367.0	1369.4	1370.7	1371.1	1371.4
142.5°	1419.0	1417.1	1415.3	1413.5	1415.3	1417.1	1419.0	1420.8	1421.9	1422.2	1422.6
145°	1494.9	1493.6	1492.2	1490.9	1492.2	1493.6	1494.9	1496.2	1497.1	1497.4	1497.7
147.5°	1565.8	1563.8	1561.7	1559.6	1561.7	1563.8	1565.8	1567.8	1568.8	1568.8	1568.8
150°	1609.6	1607.6	1605.6	1603.6	1605.6	1607.6	1609.6	1611.6	1612.7	1612.7	1612.7
152.5°	1651.4	1649.7	1647.9	1646.2	1647.9	1649.7	1651.4	1653.3	1653.9	1653.3	1652.7
155°	1711.1	1708.8	1706.4	1704.0	1706.4	1708.8	1711.1	1713.5	1714.0	1712.6	1711.3
157.5°	1762.4	1760.5	1758.6	1756.8	1758.6	1760.5	1762.4	1764.3	1764.5	1763.1	1761.7
160°	1794.9	1793.5	1792.2	1790.8	1792.2	1793.5	1794.9	1796.2	1796.0	1794.4	1792.7
162.5°	1822.9	1820.8	1818.6	1816.4	1818.6	1820.8	1822.9	1825.1	1825.3	1823.6	1821.9
165°	1860.4	1858.1	1855.6	1853.3	1855.6	1858.1	1860.4	1862.8	1862.9	1860.9	1858.9
167.5°	1891.0	1888.9	1886.7	1884.6	1886.7	1888.9	1891.0	1893.0	1893.0	1891.0	1888.9
170°	1907.6	1905.2	1902.9	1900.5	1902.9	1905.2	1907.6	1910.0	1910.0	1907.6	1905.2
172.5°	1919.8	1917.4	1915.0	1912.7	1915.0	1917.4	1919.8	1922.2	1922.3	1920.2	1918.0
175°	1933.5	1931.1	1928.7	1926.4	1928.7	1931.1	1933.5	1935.8	1936.0	1934.0	1932.0
177.5°	1939.3	1937.4	1935.6	1933.7	1935.6	1937.4	1939.3	1941.3	1941.4	1939.7	1938.1
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332427-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	862.4	866.8	871.1	875.0	881.3	884.0	888.1	889.6	894.2	901.1	906.7
5°	809.9	816.2	824.3	830.8	841.3	849.4	858.3	866.8	876.9	891.2	903.9
7.5°	765.5	771.5	781.3	793.6	805.1	816.6	828.8	840.3	854.7	875.3	895.5
10°	736.1	743.5	755.1	768.2	782.4	793.8	808.0	822.7	840.5	864.1	888.5
12.5°	710.7	716.2	729.6	742.1	758.3	772.6	786.7	803.9	824.2	849.3	878.6
15°	670.3	678.0	691.3	705.1	722.2	737.2	755.4	776.3	796.1	827.0	862.5
17.5°	629.8	641.6	655.2	671.0	683.6	704.4	724.1	745.5	769.8	802.6	841.6
20°	603.8	613.1	625.8	648.6	665.3	681.2	699.3	726.0	748.4	785.6	826.2
22.5°	581.8	588.7	602.9	621.8	641.2	659.4	678.0	703.5	731.1	766.4	810.4
25°	549.3	560.1	570.9	584.4	605.3	627.4	647.5	669.1	698.5	736.1	783.7
27.5°	517.5	527.3	538.0	554.6	570.5	591.1	612.1	636.9	668.4	708.1	756.4
30°	497.1	504.4	514.4	535.7	550.1	567.8	592.6	614.6	644.0	686.2	737.2
32.5°	475.9	485.5	496.4	512.8	530.5	547.3	570.0	593.9	623.9	665.4	717.7
35°	446.0	457.2	468.4	480.4	498.2	515.6	534.5	560.9	591.4	631.7	683.1
37.5°	418.4	427.4	436.6	451.4	468.3	484.8	502.5	528.5	557.2	600.7	647.8
40°	400.7	408.9	415.8	431.3	447.6	465.3	482.7	505.5	536.4	577.1	622.8
42.5°	381.5	389.0	398.5	411.1	428.7	443.6	461.1	482.6	511.7	553.0	593.0
45°	352.7	361.2	369.4	381.4	398.8	413.4	429.0	449.5	479.3	513.3	548.9
47.5°	322.9	331.3	340.6	352.2	367.4	382.3	397.8	416.0	443.1	476.6	500.5
50°	303.7	310.6	319.9	331.4	345.4	361.2	375.2	395.0	420.8	447.2	468.1
52.5°	283.9	290.1	300.7	313.0	325.9	339.6	354.5	371.4	394.9	419.6	436.2
55°	253.0	260.7	269.6	281.6	294.4	306.0	320.2	337.7	356.3	374.8	386.1
57.5°	224.1	230.6	238.0	250.4	261.5	275.3	288.1	301.7	318.9	332.9	340.2
60°	203.1	208.8	218.5	229.3	239.8	251.8	266.5	280.0	293.2	304.4	310.2
62.5°	183.3	190.0	198.4	208.3	219.7	231.1	243.9	255.3	266.9	276.6	280.5
65°	157.4	162.9	169.1	178.3	187.6	199.2	209.2	220.9	229.3	234.8	238.2
67.5°	133.9	137.4	142.2	148.3	157.5	167.6	177.4	186.4	193.6	197.2	200.4
70°	118.8	121.1	124.5	130.8	137.7	146.6	156.6	163.2	169.5	172.5	175.6
72.5°	103.6	106.5	109.7	114.6	120.4	126.8	134.1	142.2	145.6	149.3	151.2
75°	78.6	82.8	87.1	90.1	94.0	99.1	105.6	110.6	112.6	115.6	116.0
77.5°	59.3	60.2	63.3	67.2	70.4	74.0	78.2	82.7	83.6	85.2	86.2
80°	48.8	48.8	48.8	51.1	54.9	57.7	61.5	63.8	65.3	65.7	66.1
82.5°	39.2	39.2	38.9	39.3	40.7	42.1	45.7	48.4	49.6	49.4	48.5
85°	25.5	24.7	24.7	24.3	24.7	23.9	23.6	25.1	27.5	27.5	26.7
87.5°	18.1	17.5	17.0	15.8	14.5	13.4	11.7	11.3	10.6	11.2	10.2
90°	37.9	36.6	32.1	27.8	23.3	19.0	15.0	11.7	8.3	4.9	1.5
92.5°	59.6	58.5	55.9	53.4	51.0	48.5	46.0	43.7	41.4	39.2	36.9
95°	114.0	112.7	110.0	107.2	104.5	101.9	99.4	96.9	94.6	92.2	89.9
97.5°	177.9	176.3	174.4	172.4	170.5	168.4	166.6	164.9	163.1	161.4	159.6
100°	224.9	223.9	222.2	220.5	218.7	217.1	215.2	213.2	211.2	209.1	207.1
102.5°	278.5	277.4	275.2	273.0	270.7	268.5	266.8	265.6	264.4	263.2	262.0
105°	359.4	359.4	356.4	353.3	350.2	347.2	345.4	344.7	344.0	343.4	342.6
107.5°	444.8	443.7	442.5	441.3	440.1	438.9	438.1	437.7	437.3	436.9	436.5
110°	502.4	501.0	500.3	499.7	499.0	498.3	497.7	497.0	496.2	495.6	494.9



TEST NUMBER: P332427-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	559.9	558.3	558.2	558.0	557.8	557.7	557.4	557.0	556.6	556.2	555.8
115°	649.0	648.7	649.4	650.1	650.8	651.5	651.3	650.3	649.2	648.2	647.2
117.5°	738.2	738.3	739.1	740.0	740.9	741.7	741.8	741.2	740.5	739.8	739.2
120°	797.6	798.0	799.6	801.3	803.0	804.8	804.6	802.5	800.5	798.5	796.5
122.5°	858.0	858.9	859.8	860.6	861.5	862.4	862.1	860.6	859.1	857.6	856.2
125°	947.4	948.8	949.4	950.1	950.8	951.4	951.3	950.3	949.3	948.2	947.2
127.5°	1035.7	1037.6	1038.4	1039.2	1039.9	1040.7	1040.0	1037.7	1035.6	1033.4	1031.3
130°	1093.6	1094.9	1095.9	1096.9	1097.9	1098.9	1098.1	1095.4	1092.7	1090.0	1087.3
132.5°	1150.5	1152.2	1152.9	1153.7	1154.4	1155.2	1154.2	1151.4	1148.7	1146.0	1143.4
135°	1235.2	1236.6	1236.9	1237.2	1237.6	1237.9	1237.1	1235.0	1232.9	1230.9	1228.9
137.5°	1318.3	1319.7	1318.8	1317.9	1317.1	1316.2	1314.8	1313.2	1311.5	1309.8	1308.1
140°	1371.7	1372.1	1371.7	1371.4	1371.1	1370.7	1369.7	1368.0	1366.3	1364.6	1362.9
142.5°	1422.9	1423.2	1422.6	1422.0	1421.4	1420.8	1419.7	1418.0	1416.2	1414.5	1412.9
145°	1498.1	1498.4	1497.4	1496.4	1495.4	1494.4	1493.6	1492.9	1492.2	1491.6	1490.9
147.5°	1568.8	1568.8	1567.8	1566.9	1566.0	1565.0	1564.0	1562.8	1561.5	1560.2	1559.0
150°	1612.7	1612.7	1611.9	1611.3	1610.6	1609.9	1609.3	1608.6	1607.9	1607.3	1606.6
152.5°	1652.2	1651.6	1651.2	1650.8	1650.4	1650.0	1649.3	1648.4	1647.5	1646.5	1645.6
155°	1710.0	1708.6	1708.3	1707.9	1707.6	1707.3	1707.1	1707.1	1707.1	1707.1	1707.1
157.5°	1760.3	1758.9	1758.6	1758.3	1758.1	1757.8	1757.9	1758.3	1758.7	1759.1	1759.5
160°	1791.0	1789.3	1789.3	1789.3	1789.3	1789.3	1789.7	1790.3	1791.0	1791.7	1792.4
162.5°	1820.3	1818.6	1818.3	1818.1	1817.8	1817.5	1817.9	1818.8	1819.7	1820.7	1821.6
165°	1856.8	1854.8	1854.8	1854.8	1854.8	1854.8	1855.3	1856.3	1857.3	1858.4	1859.4
167.5°	1886.7	1884.6	1884.4	1884.1	1883.8	1883.6	1884.1	1885.4	1886.8	1888.1	1889.6
170°	1902.9	1900.5	1900.5	1900.5	1900.5	1900.5	1901.2	1902.5	1903.9	1905.2	1906.5
172.5°	1916.0	1913.9	1913.9	1913.9	1913.9	1913.9	1914.6	1915.9	1917.2	1918.6	1920.0
175°	1930.0	1927.9	1927.9	1927.9	1927.9	1927.9	1928.5	1930.0	1931.3	1932.7	1934.0
177.5°	1936.5	1934.9	1934.9	1934.9	1934.9	1934.9	1935.4	1936.5	1937.6	1938.7	1939.7
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332427-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	908.5	911.9	916.3	922.7	927.7	932.0	932.9	934.2	937.3	942.5	946.5
5°	914.4	923.3	937.6	951.5	966.6	979.0	990.6	998.8	1006.4	1022.7	1035.8
7.5°	912.5	932.3	954.7	979.8	1005.0	1029.6	1052.3	1072.7	1093.0	1116.6	1143.6
10°	911.3	934.5	964.6	996.7	1032.0	1066.4	1099.6	1125.6	1155.8	1182.9	1217.3
12.5°	905.4	938.9	974.9	1015.9	1059.2	1098.9	1142.7	1178.5	1212.9	1252.1	1292.1
15°	897.8	938.4	984.0	1038.5	1104.3	1152.3	1197.1	1259.4	1301.9	1344.5	1401.8
17.5°	883.7	933.3	990.4	1061.2	1116.1	1180.5	1248.0	1297.3	1354.5	1414.5	1466.3
20°	872.6	930.3	994.1	1063.7	1133.7	1203.8	1269.1	1327.9	1387.0	1456.3	1498.8
22.5°	861.5	918.5	984.8	1058.7	1134.0	1207.7	1281.7	1350.8	1417.3	1487.2	1541.6
25°	837.8	905.4	977.4	1052.9	1127.1	1208.3	1296.6	1373.5	1455.9	1527.8	1579.3
27.5°	813.9	875.9	947.5	1024.0	1106.5	1202.5	1306.3	1393.8	1476.3	1527.8	1544.0
30°	792.1	857.9	923.6	1001.4	1090.8	1197.9	1308.2	1408.4	1476.0	1498.4	1481.8
32.5°	770.2	829.8	894.9	974.5	1069.4	1186.5	1310.6	1399.7	1440.5	1423.3	1355.5
35°	731.4	785.2	848.3	928.0	1037.0	1180.1	1300.4	1360.8	1350.7	1253.9	1126.3
37.5°	689.9	733.8	792.1	875.5	1003.4	1155.0	1256.5	1265.4	1178.3	1029.9	882.4
40°	657.1	696.6	756.6	843.6	977.4	1130.2	1212.2	1176.3	1041.3	876.1	753.1
42.5°	625.3	658.5	716.3	810.2	952.7	1096.5	1146.3	1067.9	912.2	756.0	644.2
45°	571.3	602.6	660.7	757.0	902.0	1032.0	1025.4	889.3	733.4	607.6	514.8
47.5°	520.1	547.4	602.0	700.2	842.5	935.2	873.7	728.9	596.6	495.8	429.6
50°	483.9	511.0	565.1	662.2	794.9	862.5	774.8	635.1	514.0	430.5	377.9
52.5°	449.2	475.6	525.2	619.8	737.3	777.8	683.5	554.0	453.1	381.0	335.8
55°	400.7	420.8	465.3	555.8	643.6	652.9	557.3	449.1	365.9	315.6	284.7
57.5°	351.3	368.6	412.5	484.6	546.2	541.4	450.8	357.2	301.1	263.8	241.4
60°	319.1	336.1	374.8	436.7	483.1	466.9	383.7	308.3	260.3	232.9	215.1
62.5°	289.1	302.4	338.6	383.7	417.2	398.8	328.0	265.6	227.5	204.4	190.3
65°	245.6	256.4	285.5	309.0	327.6	309.8	251.1	207.7	180.3	164.0	154.3
67.5°	204.3	211.2	229.5	238.0	251.2	231.7	188.7	159.8	144.1	130.5	123.7
70°	178.3	183.4	193.0	200.0	203.5	183.4	151.6	130.4	117.2	107.6	103.3
72.5°	152.3	156.7	158.6	164.4	162.6	143.7	121.9	105.0	95.5	89.0	83.5
75°	116.4	118.4	116.4	114.1	109.1	95.9	80.9	72.3	65.3	62.3	60.4
77.5°	84.8	84.2	81.6	78.0	69.4	61.1	53.0	50.1	47.2	45.4	44.8
80°	65.3	63.8	61.5	55.7	48.4	42.5	40.6	38.7	37.6	35.5	35.2
82.5°	48.7	47.8	43.8	39.0	33.8	31.1	29.5	28.8	27.6	26.7	26.6
85°	26.0	24.7	20.5	17.8	17.1	16.3	15.9	15.9	14.3	13.9	13.9
87.5°	9.3	8.2	8.5	8.3	9.1	9.3	10.5	10.8	11.3	11.9	11.6
90°	4.9	8.3	11.7	15.0	19.0	23.3	27.8	32.1	36.6	37.9	39.3
92.5°	39.2	41.4	43.7	46.0	48.5	51.0	53.4	55.9	58.5	59.6	60.6
95°	92.2	94.6	96.9	99.4	101.9	104.5	107.2	110.0	112.7	114.0	115.4
97.5°	161.4	163.1	164.9	166.6	168.4	170.5	172.4	174.4	176.3	177.9	179.5
100°	209.1	211.2	213.2	215.2	217.1	218.7	220.5	222.2	223.9	224.9	225.9
102.5°	263.2	264.4	265.6	266.8	268.5	270.7	273.0	275.2	277.4	278.5	279.5
105°	343.4	344.0	344.7	345.4	347.2	350.2	353.3	356.4	359.4	359.4	359.4
107.5°	436.9	437.3	437.7	438.1	438.9	440.1	441.3	442.5	443.7	444.8	446.0
110°	495.6	496.2	497.0	497.7	498.3	499.0	499.7	500.3	501.0	502.4	503.7



TEST NUMBER: P332427-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	556.2	556.6	557.0	557.4	557.7	557.8	558.0	558.2	558.3	559.9	561.5
115°	648.2	649.2	650.3	651.3	651.5	650.8	650.1	649.4	648.7	649.0	649.4
117.5°	739.8	740.5	741.2	741.8	741.7	740.9	740.0	739.1	738.3	738.2	738.1
120°	798.5	800.5	802.5	804.6	804.8	803.0	801.3	799.6	798.0	797.6	797.3
122.5°	857.6	859.1	860.6	862.1	862.4	861.5	860.6	859.8	858.9	858.0	857.1
125°	948.2	949.3	950.3	951.3	951.4	950.8	950.1	949.4	948.8	947.4	946.0
127.5°	1033.4	1035.6	1037.7	1040.0	1040.7	1039.9	1039.2	1038.4	1037.6	1035.7	1033.9
130°	1090.0	1092.7	1095.4	1098.1	1098.9	1097.9	1096.9	1095.9	1094.9	1093.6	1092.2
132.5°	1146.0	1148.7	1151.4	1154.2	1155.2	1154.4	1153.7	1152.9	1152.2	1150.5	1148.9
135°	1230.9	1232.9	1235.0	1237.1	1237.9	1237.6	1237.2	1236.9	1236.6	1235.2	1233.9
137.5°	1309.8	1311.5	1313.2	1314.8	1316.2	1317.1	1317.9	1318.8	1319.7	1318.3	1316.9
140°	1364.6	1366.3	1368.0	1369.7	1370.7	1371.1	1371.4	1371.7	1372.1	1371.7	1371.4
142.5°	1414.5	1416.2	1418.0	1419.7	1420.8	1421.4	1422.0	1422.6	1423.2	1422.9	1422.6
145°	1491.6	1492.2	1492.9	1493.6	1494.4	1495.4	1496.4	1497.4	1498.4	1498.1	1497.7
147.5°	1560.2	1561.5	1562.8	1564.0	1565.0	1566.0	1566.9	1567.8	1568.8	1568.8	1568.8
150°	1607.3	1607.9	1608.6	1609.3	1609.9	1610.6	1611.3	1611.9	1612.7	1612.7	1612.7
152.5°	1646.5	1647.5	1648.4	1649.3	1650.0	1650.4	1650.8	1651.2	1651.6	1652.2	1652.7
155°	1707.1	1707.1	1707.1	1707.1	1707.3	1707.6	1707.9	1708.3	1708.6	1710.0	1711.3
157.5°	1759.1	1758.7	1758.3	1757.9	1757.8	1758.1	1758.3	1758.6	1758.9	1760.3	1761.7
160°	1791.7	1791.0	1790.3	1789.7	1789.3	1789.3	1789.3	1789.3	1789.3	1791.0	1792.7
162.5°	1820.7	1819.7	1818.8	1817.9	1817.5	1817.8	1818.1	1818.3	1818.6	1820.3	1821.9
165°	1858.4	1857.3	1856.3	1855.3	1854.8	1854.8	1854.8	1854.8	1854.8	1856.8	1858.9
167.5°	1888.1	1886.8	1885.4	1884.1	1883.6	1883.8	1884.1	1884.4	1884.6	1886.7	1888.9
170°	1905.2	1903.9	1902.5	1901.2	1900.5	1900.5	1900.5	1900.5	1900.5	1902.9	1905.2
172.5°	1918.6	1917.2	1915.9	1914.6	1913.9	1913.9	1913.9	1913.9	1913.9	1916.0	1918.0
175°	1932.7	1931.3	1930.0	1928.5	1927.9	1927.9	1927.9	1927.9	1927.9	1930.0	1932.0
177.5°	1938.7	1937.6	1936.5	1935.4	1934.9	1934.9	1934.9	1934.9	1934.9	1936.5	1938.1
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332427-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	953.1	953.1	954.3	959.0	959.6	963.6	962.3
5°	1047.4	1054.8	1057.5	1069.1	1076.1	1079.1	1073.0
7.5°	1162.9	1183.6	1193.5	1205.6	1216.3	1219.6	1211.1
10°	1247.1	1268.7	1286.9	1298.1	1308.6	1315.5	1324.4
12.5°	1328.4	1355.0	1372.3	1388.2	1398.9	1407.8	1409.2
15°	1416.8	1457.0	1487.6	1510.1	1521.3	1527.1	1524.8
17.5°	1506.0	1543.3	1565.1	1587.9	1603.5	1604.3	1604.8
20°	1556.5	1592.9	1618.0	1635.0	1652.4	1651.6	1655.5
22.5°	1590.2	1618.8	1638.1	1650.4	1656.4	1653.5	1654.3
25°	1606.0	1614.5	1611.0	1591.2	1586.3	1568.1	1571.1
27.5°	1524.6	1484.4	1442.8	1389.2	1347.0	1313.2	1314.9
30°	1414.1	1342.9	1261.7	1193.7	1132.6	1115.5	1079.1
32.5°	1259.7	1153.0	1057.8	994.4	941.9	927.7	896.0
35°	997.9	894.2	796.4	737.6	714.4	682.0	681.6
37.5°	775.7	684.4	632.7	588.5	565.4	545.7	543.8
40°	652.6	581.4	542.3	510.6	487.8	473.0	469.6
42.5°	566.5	509.0	472.3	452.7	435.2	427.6	421.9
45°	462.6	423.9	398.4	380.6	372.4	366.7	363.6
47.5°	387.0	361.0	343.7	331.8	325.2	319.1	320.7
50°	345.8	324.6	311.7	300.5	295.5	291.2	291.6
52.5°	312.7	293.6	283.3	275.2	268.9	265.9	264.4
55°	265.4	253.4	242.9	237.1	233.6	229.3	228.2
57.5°	226.3	217.0	208.5	202.0	201.2	197.0	197.5
60°	200.4	192.6	185.6	182.2	179.5	176.0	177.1
62.5°	179.0	172.5	166.1	163.3	160.6	158.0	158.5
65°	146.6	140.4	136.5	135.0	133.8	132.7	131.5
67.5°	116.8	113.0	110.6	107.2	104.9	104.5	103.3
70°	98.3	93.2	89.0	84.7	83.5	83.1	83.5
72.5°	78.8	75.5	74.4	72.3	72.1	71.1	71.8
75°	59.2	58.1	57.3	55.7	55.7	55.7	55.7
77.5°	43.6	42.9	42.5	42.1	41.8	41.2	41.2
80°	34.0	33.6	32.9	32.9	32.5	32.9	32.5
82.5°	25.7	25.7	24.8	24.8	24.4	24.2	24.4
85°	13.1	12.7	13.5	12.7	13.1	12.4	13.1
87.5°	11.8	12.1	12.0	12.1	11.9	12.7	12.2
90°	40.6	42.0	43.0	43.6	44.3	45.0	45.6
92.5°	61.7	62.8	63.1	62.7	62.3	61.9	61.5
95°	116.7	118.1	118.8	118.8	118.8	118.8	118.8
97.5°	181.0	182.6	183.3	183.2	183.0	182.9	182.8
100°	226.9	227.9	228.7	229.4	230.1	230.8	231.5
102.5°	280.5	281.6	282.0	281.9	281.7	281.6	281.4
105°	359.4	359.4	359.7	360.4	361.1	361.7	362.4
107.5°	447.0	448.1	448.4	448.0	447.6	447.2	446.8
110°	505.0	506.4	506.8	506.0	505.4	504.7	504.0



TEST NUMBER: P332427-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	563.1	564.7	565.5	565.4	565.2	565.1	564.9
115°	649.7	650.1	650.1	649.7	649.4	649.0	648.7
117.5°	738.1	738.0	737.5	736.5	735.6	734.7	733.7
120°	797.0	796.6	796.1	795.5	794.8	794.1	793.3
122.5°	856.3	855.4	854.4	853.5	852.5	851.6	850.6
125°	944.6	943.3	941.9	940.6	939.3	937.9	936.5
127.5°	1032.0	1030.1	1028.3	1026.8	1025.2	1023.7	1022.1
130°	1090.9	1089.5	1087.6	1085.3	1082.9	1080.6	1078.1
132.5°	1147.3	1145.7	1144.0	1142.2	1140.3	1138.4	1136.6
135°	1232.4	1231.1	1230.1	1229.4	1228.7	1228.1	1227.4
137.5°	1315.5	1314.0	1312.6	1311.3	1310.1	1308.8	1307.5
140°	1371.1	1370.7	1369.4	1367.0	1364.6	1362.2	1359.9
142.5°	1422.2	1421.9	1420.8	1419.0	1417.1	1415.3	1413.5
145°	1497.4	1497.1	1496.2	1494.9	1493.6	1492.2	1490.9
147.5°	1568.8	1568.8	1567.8	1565.8	1563.8	1561.7	1559.6
150°	1612.7	1612.7	1611.6	1609.6	1607.6	1605.6	1603.6
152.5°	1653.3	1653.9	1653.3	1651.4	1649.7	1647.9	1646.2
155°	1712.6	1714.0	1713.5	1711.1	1708.8	1706.4	1704.0
157.5°	1763.1	1764.5	1764.3	1762.4	1760.5	1758.6	1756.8
160°	1794.4	1796.0	1796.2	1794.9	1793.5	1792.2	1790.8
162.5°	1823.6	1825.3	1825.1	1822.9	1820.8	1818.6	1816.4
165°	1860.9	1862.9	1862.8	1860.4	1858.1	1855.6	1853.3
167.5°	1891.0	1893.0	1893.0	1891.0	1888.9	1886.7	1884.6
170°	1907.6	1910.0	1910.0	1907.6	1905.2	1902.9	1900.5
172.5°	1920.2	1922.3	1922.2	1919.8	1917.4	1915.0	1912.7
175°	1934.0	1936.0	1935.8	1933.5	1931.1	1928.7	1926.4
177.5°	1939.7	1941.4	1941.3	1939.3	1937.4	1935.6	1933.7
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5

(END OF REPORT)