

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332429-840

Luminaire Tested: **S123RDIW-S560D1535U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332429-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D1535U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7531.6 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332429-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332429-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37	29								
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25								
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	28	26	21								
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18								
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	15								
5	65	54	46	41	58	49	42	37	39	34	30	29	26	24	21	19	17	14								
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12								
7	55	44	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14	11								
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10								
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9								
10	44	33	26	21	40	30	24	20	24	20	16	19	15	13	14	11	10	8								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10267	10267	10267
5°	10306	10164	10222
10°	10248	10037	10002
15°	10137	9802	9698
20°	9986	9507	9286
25°	9830	9178	8884
30°	9625	8797	8316
35°	9412	8418	7796
40°	9218	7967	7152
45°	8961	7524	6570
50°	8679	7021	5921
55°	8392	6446	5315
60°	8127	5828	4646
65°	7784	5163	3978
70°	7352	4334	3213
75°	6725	3410	3023
80°	5994	3025	2777
85°	5064	2668	2482



TEST NUMBER: P332429-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	1.2
10°-20°	249.2	3.3
20°-30°	358.8	4.8
30°-40°	404.2	5.4
40°-50°	386.7	5.1
50°-60°	316.7	4.2
60°-70°	213.7	2.8
70°-80°	107.5	1.4
80°-90°	34.2	0.5
90°-100°	126.3	1.7
100°-110°	378.0	5.0
110°-120°	642.9	8.5
120°-130°	845.6	11.2
130°-140°	950.5	12.6
140°-150°	934.3	12.4
150°-160°	786.5	10.4
160°-170°	523.6	7.0
170°-180°	183.3	2.4
0°-30°	697.6	9.3
0°-40°	1101.8	14.6
0°-60°	1805.2	24.0
0°-90°	2160.5	28.7
90°-120°	1147.2	15.2
90°-150°	3877.6	51.5
90°-180°	5371.0	71.3
0°-180°	7531.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	954	954	954	954	954	
5°	954	950	941	947	946	90
15°	910	900	880	876	870	256
25°	828	808	773	757	748	381
35°	716	687	641	608	593	448
45°	589	552	494	452	432	454
55°	447	408	344	300	283	401
65°	306	262	203	166	156	302
75°	162	124	82	75	73	172
85°	41	25	22	20	20	46
90°	2	17	37	42	46	8
95°	90	101	113	118	119	101
105°	343	346	359	360	362	367
115°	647	651	649	650	649	640
125°	947	951	949	943	936	844
135°	1229	1238	1237	1231	1227	947
145°	1491	1494	1498	1497	1491	931
155°	1707	1707	1709	1714	1704	785
165°	1859	1855	1855	1863	1853	524
175°	1934	1928	1928	1936	1926	184
180°	1938	1938	1938	1938	1938	



TEST NUMBER: P332429-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	956.9	956.3	955.8	955.2	954.7	953.6	952.0	950.3	948.7	947.1	948.6
5°	953.8	953.0	952.1	951.3	950.4	949.0	946.8	944.8	942.7	940.7	942.2
7.5°	945.0	944.1	943.1	942.2	941.3	939.5	936.9	934.1	931.4	928.8	929.6
10°	937.6	936.3	935.1	933.9	932.8	930.6	927.6	924.4	921.3	918.3	918.4
12.5°	927.1	925.7	924.3	923.0	921.7	919.2	915.3	911.6	907.8	904.0	903.9
15°	909.7	907.9	905.9	904.0	902.2	898.8	894.0	889.2	884.3	879.6	878.7
17.5°	887.9	885.8	883.5	881.3	879.1	874.9	868.8	862.7	856.6	850.5	848.7
20°	871.8	869.1	866.4	863.5	860.8	856.2	849.6	843.1	836.6	830.0	827.8
22.5°	853.8	850.7	847.6	844.3	841.2	836.2	829.2	822.2	815.4	808.4	805.6
25°	827.7	823.4	819.1	814.9	810.5	804.5	796.5	788.6	780.7	772.8	769.2
27.5°	796.0	791.2	786.5	781.7	777.0	770.2	761.4	752.7	743.9	735.1	730.0
30°	774.4	769.2	764.1	758.9	753.8	746.3	736.7	727.1	717.4	707.8	702.0
32.5°	752.7	746.9	741.0	735.2	729.3	721.3	711.1	700.9	690.7	680.5	674.2
35°	716.3	710.1	704.0	697.8	691.6	683.2	672.5	661.9	651.2	640.6	633.1
37.5°	679.5	672.7	665.8	658.8	652.0	642.9	631.5	620.2	608.7	597.3	589.0
40°	656.0	648.4	640.9	633.3	625.7	615.8	603.7	591.5	579.3	567.0	558.1
42.5°	629.3	621.8	614.3	606.7	599.2	589.1	576.4	563.8	551.2	538.6	528.8
45°	588.7	581.0	573.2	565.5	557.7	547.2	534.0	520.8	507.6	494.3	484.5
47.5°	548.0	539.5	531.0	522.5	514.0	503.2	489.9	476.7	463.4	450.2	439.6
50°	518.3	510.2	502.1	494.0	485.9	474.9	461.0	447.2	433.2	419.3	408.6
52.5°	491.7	482.9	474.1	465.3	456.7	445.4	431.5	417.8	403.9	390.2	379.1
55°	447.2	438.7	430.3	421.8	413.4	401.9	387.3	372.7	358.1	343.5	333.5
57.5°	406.0	396.8	387.6	378.4	369.2	357.3	342.6	328.0	313.3	298.6	289.2
60°	377.5	368.1	358.6	349.1	339.7	327.8	313.6	299.3	285.0	270.7	261.5
62.5°	349.0	339.6	330.1	320.6	311.2	299.3	285.1	270.8	256.5	242.3	233.6
65°	305.6	296.1	286.7	277.2	267.7	256.3	242.9	229.5	216.1	202.7	194.3
67.5°	262.1	252.6	243.0	233.4	223.9	212.7	199.8	186.9	174.1	161.2	154.9
70°	233.6	224.3	215.1	205.8	196.5	185.8	173.8	161.8	149.8	137.7	131.7
72.5°	205.1	196.0	186.8	177.7	168.5	158.5	147.6	136.6	125.7	114.8	109.9
75°	161.7	153.4	145.2	136.9	128.7	119.8	110.4	100.9	91.5	82.0	80.3
77.5°	122.1	114.6	107.1	99.7	92.2	85.4	79.4	73.3	67.2	61.1	60.2
80°	96.7	89.7	82.6	75.5	68.5	63.2	59.6	55.9	52.3	48.8	48.2
82.5°	72.6	66.4	60.4	54.3	48.2	44.3	42.6	41.0	39.3	37.6	37.1
85°	41.0	37.3	33.4	29.7	25.9	23.7	23.2	22.7	22.2	21.6	21.3
87.5°	15.1	14.3	13.5	12.6	11.8	11.8	12.7	13.6	14.4	15.3	15.5
90°	1.5	4.9	8.3	11.7	15.0	19.0	23.3	27.8	32.1	36.6	37.9
92.5°	36.9	39.2	41.4	43.7	46.0	48.5	51.0	53.4	55.9	58.5	59.6
95°	89.9	92.2	94.6	96.9	99.4	101.9	104.5	107.2	110.0	112.7	114.0
97.5°	159.6	161.4	163.1	164.9	166.6	168.4	170.5	172.4	174.4	176.3	177.9
100°	207.1	209.1	211.2	213.2	215.2	217.1	218.7	220.5	222.2	223.9	224.9
102.5°	262.0	263.2	264.4	265.6	266.8	268.5	270.7	273.0	275.2	277.4	278.5
105°	342.6	343.4	344.0	344.7	345.4	347.2	350.2	353.3	356.4	359.4	359.4
107.5°	436.5	436.9	437.3	437.7	438.1	438.9	440.1	441.3	442.5	443.7	444.8
110°	494.9	495.6	496.2	497.0	497.7	498.3	499.0	499.7	500.3	501.0	502.4



TEST NUMBER: P332429-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	555.8	556.2	556.6	557.0	557.4	557.7	557.8	558.0	558.2	558.3	559.9
115°	647.2	648.2	649.2	650.3	651.3	651.5	650.8	650.1	649.4	648.7	649.0
117.5°	739.2	739.8	740.5	741.2	741.8	741.7	740.9	740.0	739.1	738.3	738.2
120°	796.5	798.5	800.5	802.5	804.6	804.8	803.0	801.3	799.6	798.0	797.6
122.5°	856.2	857.6	859.1	860.6	862.1	862.4	861.5	860.6	859.8	858.9	858.0
125°	947.2	948.2	949.3	950.3	951.3	951.4	950.8	950.1	949.4	948.8	947.4
127.5°	1031.3	1033.4	1035.6	1037.7	1040.0	1040.7	1039.9	1039.2	1038.4	1037.6	1035.7
130°	1087.3	1090.0	1092.7	1095.4	1098.1	1098.9	1097.9	1096.9	1095.9	1094.9	1093.6
132.5°	1143.4	1146.0	1148.7	1151.4	1154.2	1155.2	1154.4	1153.7	1152.9	1152.2	1150.5
135°	1228.9	1230.9	1232.9	1235.0	1237.1	1237.9	1237.6	1237.2	1236.9	1236.6	1235.2
137.5°	1308.1	1309.8	1311.5	1313.2	1314.8	1316.2	1317.1	1317.9	1318.8	1319.7	1318.3
140°	1362.9	1364.6	1366.3	1368.0	1369.7	1370.7	1371.1	1371.4	1371.7	1372.1	1371.7
142.5°	1412.9	1414.5	1416.2	1418.0	1419.7	1420.8	1421.4	1422.0	1422.6	1423.2	1422.9
145°	1490.9	1491.6	1492.2	1492.9	1493.6	1494.4	1495.4	1496.4	1497.4	1498.4	1498.1
147.5°	1559.0	1560.2	1561.5	1562.8	1564.0	1565.0	1566.0	1566.9	1567.8	1568.8	1568.8
150°	1606.6	1607.3	1607.9	1608.6	1609.3	1609.9	1610.6	1611.3	1611.9	1612.7	1612.7
152.5°	1645.6	1646.5	1647.5	1648.4	1649.3	1650.0	1650.4	1650.8	1651.2	1651.6	1652.2
155°	1707.1	1707.1	1707.1	1707.1	1707.1	1707.3	1707.6	1707.9	1708.3	1708.6	1710.0
157.5°	1759.5	1759.1	1758.7	1758.3	1757.9	1757.8	1758.1	1758.3	1758.6	1758.9	1760.3
160°	1792.4	1791.7	1791.0	1790.3	1789.7	1789.3	1789.3	1789.3	1789.3	1789.3	1791.0
162.5°	1821.6	1820.7	1819.7	1818.8	1817.9	1817.5	1817.8	1818.1	1818.3	1818.6	1820.3
165°	1859.4	1858.4	1857.3	1856.3	1855.3	1854.8	1854.8	1854.8	1854.8	1854.8	1856.8
167.5°	1889.6	1888.1	1886.8	1885.4	1884.1	1883.6	1883.8	1884.1	1884.4	1884.6	1886.7
170°	1906.5	1905.2	1903.9	1902.5	1901.2	1900.5	1900.5	1900.5	1900.5	1900.5	1902.9
172.5°	1920.0	1918.6	1917.2	1915.9	1914.6	1913.9	1913.9	1913.9	1913.9	1913.9	1916.0
175°	1934.0	1932.7	1931.3	1930.0	1928.5	1927.9	1927.9	1927.9	1927.9	1927.9	1930.0
177.5°	1939.7	1938.7	1937.6	1936.5	1935.4	1934.9	1934.9	1934.9	1934.9	1934.9	1936.5
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5



TEST NUMBER: P332429-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	950.1	951.6	953.1	953.7	953.4	953.1	952.9	952.6
5°	943.7	945.3	946.8	947.5	947.2	946.7	946.4	946.0
7.5°	930.5	931.3	932.2	932.3	931.7	931.2	930.6	930.0
10°	918.6	918.8	918.9	918.6	917.8	916.9	916.0	915.1
12.5°	903.8	903.7	903.6	903.0	902.0	901.0	900.1	899.1
15°	877.9	877.0	876.2	875.0	873.8	872.7	871.5	870.3
17.5°	846.9	845.1	843.1	841.4	839.6	837.8	836.0	834.2
20°	825.6	823.3	821.1	819.0	816.9	814.9	812.7	810.7
22.5°	802.8	800.0	797.3	794.9	792.9	791.0	789.1	787.2
25°	765.6	761.9	758.4	755.6	753.8	751.8	749.9	748.0
27.5°	725.0	720.0	715.0	711.0	708.1	705.3	702.4	699.4
30°	696.1	690.2	684.5	680.1	677.4	674.7	671.9	669.1
32.5°	667.8	661.4	655.0	650.4	647.5	644.6	641.7	638.8
35°	625.7	618.3	611.0	605.7	602.6	599.6	596.4	593.3
37.5°	580.6	572.2	563.8	557.7	553.9	550.1	546.2	542.4
40°	549.2	540.2	531.3	524.8	520.9	516.9	513.0	509.0
42.5°	519.1	509.3	499.5	492.8	489.3	485.7	482.2	478.7
45°	474.7	464.9	455.1	448.2	444.0	439.9	435.8	431.6
47.5°	428.9	418.3	407.6	400.4	396.8	393.0	389.4	385.7
50°	398.0	387.3	376.7	369.3	365.4	361.4	357.5	353.6
52.5°	368.1	357.0	345.9	338.6	335.1	331.5	328.0	324.5
55°	323.6	313.6	303.6	296.9	293.5	290.0	286.6	283.2
57.5°	279.7	270.3	260.9	254.8	251.9	248.9	246.0	243.1
60°	252.2	242.9	233.6	227.5	224.6	221.7	218.7	215.8
62.5°	224.8	216.1	207.3	201.5	198.4	195.3	192.3	189.2
65°	185.8	177.4	169.0	163.8	162.0	160.1	158.1	156.2
67.5°	148.7	142.3	136.0	131.9	129.9	127.8	125.8	123.8
70°	125.6	119.7	113.6	109.7	107.8	105.9	104.0	102.1
72.5°	104.9	100.1	95.1	92.3	91.5	90.7	89.9	89.1
75°	78.6	76.9	75.1	74.1	73.7	73.4	73.0	72.7
77.5°	59.3	58.4	57.4	56.8	56.5	56.0	55.7	55.3
80°	47.7	47.2	46.7	46.3	45.9	45.5	45.2	44.8
82.5°	36.6	36.1	35.5	35.2	35.1	35.1	35.0	34.9
85°	21.0	20.6	20.3	20.1	20.1	20.1	20.1	20.1
87.5°	15.7	15.8	15.9	16.0	16.0	16.0	16.0	16.0
90°	39.3	40.6	42.0	43.0	43.6	44.3	45.0	45.6
92.5°	60.6	61.7	62.8	63.1	62.7	62.3	61.9	61.5
95°	115.4	116.7	118.1	118.8	118.8	118.8	118.8	118.8
97.5°	179.5	181.0	182.6	183.3	183.2	183.0	182.9	182.8
100°	225.9	226.9	227.9	228.7	229.4	230.1	230.8	231.5
102.5°	279.5	280.5	281.6	282.0	281.9	281.7	281.6	281.4
105°	359.4	359.4	359.4	359.7	360.4	361.1	361.7	362.4
107.5°	446.0	447.0	448.1	448.4	448.0	447.6	447.2	446.8
110°	503.7	505.0	506.4	506.8	506.0	505.4	504.7	504.0



TEST NUMBER: P332429-840

CATALOG NUMBER: S123RDIW-S560D1535U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	561.5	563.1	564.7	565.5	565.4	565.2	565.1	564.9
115°	649.4	649.7	650.1	650.1	649.7	649.4	649.0	648.7
117.5°	738.1	738.1	738.0	737.5	736.5	735.6	734.7	733.7
120°	797.3	797.0	796.6	796.1	795.5	794.8	794.1	793.3
122.5°	857.1	856.3	855.4	854.4	853.5	852.5	851.6	850.6
125°	946.0	944.6	943.3	941.9	940.6	939.3	937.9	936.5
127.5°	1033.9	1032.0	1030.1	1028.3	1026.8	1025.2	1023.7	1022.1
130°	1092.2	1090.9	1089.5	1087.6	1085.3	1082.9	1080.6	1078.1
132.5°	1148.9	1147.3	1145.7	1144.0	1142.2	1140.3	1138.4	1136.6
135°	1233.9	1232.4	1231.1	1230.1	1229.4	1228.7	1228.1	1227.4
137.5°	1316.9	1315.5	1314.0	1312.6	1311.3	1310.1	1308.8	1307.5
140°	1371.4	1371.1	1370.7	1369.4	1367.0	1364.6	1362.2	1359.9
142.5°	1422.6	1422.2	1421.9	1420.8	1419.0	1417.1	1415.3	1413.5
145°	1497.7	1497.4	1497.1	1496.2	1494.9	1493.6	1492.2	1490.9
147.5°	1568.8	1568.8	1568.8	1567.8	1565.8	1563.8	1561.7	1559.6
150°	1612.7	1612.7	1612.7	1611.6	1609.6	1607.6	1605.6	1603.6
152.5°	1652.7	1653.3	1653.9	1653.3	1651.4	1649.7	1647.9	1646.2
155°	1711.3	1712.6	1714.0	1713.5	1711.1	1708.8	1706.4	1704.0
157.5°	1761.7	1763.1	1764.5	1764.3	1762.4	1760.5	1758.6	1756.8
160°	1792.7	1794.4	1796.0	1796.2	1794.9	1793.5	1792.2	1790.8
162.5°	1821.9	1823.6	1825.3	1825.1	1822.9	1820.8	1818.6	1816.4
165°	1858.9	1860.9	1862.9	1862.8	1860.4	1858.1	1855.6	1853.3
167.5°	1888.9	1891.0	1893.0	1893.0	1891.0	1888.9	1886.7	1884.6
170°	1905.2	1907.6	1910.0	1910.0	1907.6	1905.2	1902.9	1900.5
172.5°	1918.0	1920.2	1922.3	1922.2	1919.8	1917.4	1915.0	1912.7
175°	1932.0	1934.0	1936.0	1935.8	1933.5	1931.1	1928.7	1926.4
177.5°	1938.1	1939.7	1941.4	1941.3	1939.3	1937.4	1935.6	1933.7
180°	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5	1938.5

(END OF REPORT)