

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332440-840

Luminaire Tested: **S123RDIW-S775D1030U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332440-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D1030U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7112.6 lumens
Efficiency: N/A
Efficacy: 135.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332440-840

CATALOG NUMBER: S123RDIW-S775D1030U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332440-840

CATALOG NUMBER: S123RDIW-S775D1030U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	81	75	70	80	74	69	64	61	57	54	49	47	44	38	37	35	30
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	35	33	31	28	26	22
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	28	25	23	20
6	62	50	43	37	57	46	39	34	39	34	30	32	28	25	25	22	20	17
7	57	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	21	18	16	14
9	50	38	30	25	45	35	28	24	29	24	21	24	21	18	20	17	15	13
10	46	35	28	23	42	32	26	21	27	22	19	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14034	14034	14034
5°	14088	13894	13973
10°	14008	13719	13672
15°	13857	13397	13256
20°	13651	12997	12693
25°	13438	12545	12144
30°	13155	12026	11368
35°	12867	11506	10657
40°	12600	10891	9777
45°	12250	10286	8983
50°	11863	9597	8092
55°	11470	8811	7263
60°	11108	7967	6351
65°	10639	7055	5440
70°	10049	5923	4393
75°	9191	4662	4134
80°	8195	4135	3800
85°	6916	3656	3396



TEST NUMBER: P332440-840

CATALOG NUMBER: S123RDIW-S775D1030U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.4	1.7
10°-20°	340.6	4.8
20°-30°	490.5	6.9
30°-40°	552.5	7.8
40°-50°	528.6	7.4
50°-60°	432.9	6.1
60°-70°	292.0	4.1
70°-80°	146.9	2.1
80°-90°	42.7	0.6
90°-100°	49.6	0.7
100°-110°	236.6	3.3
110°-120°	568.2	8.0
120°-130°	723.6	10.2
130°-140°	773.1	10.9
140°-150°	723.0	10.2
150°-160°	583.2	8.2
160°-170°	376.4	5.3
170°-180°	129.7	1.8
0°-30°	953.6	13.4
0°-40°	1506.1	21.2
0°-60°	2467.5	34.7
0°-90°	2949.2	41.5
90°-120°	854.5	12.0
90°-150°	3074.2	43.2
90°-180°	4163.0	58.5
0°-180°	7112.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1304	1304	1304	1304	1304	
5°	1304	1298	1286	1295	1293	124
15°	1244	1231	1202	1197	1190	350
25°	1132	1104	1056	1035	1022	520
35°	979	940	876	832	811	613
45°	805	755	676	617	590	621
55°	611	557	470	410	387	548
65°	418	358	277	227	214	413
75°	221	170	112	102	99	236
85°	56	34	30	28	28	63
90°	1	11	24	28	30	6
95°	62	23	31	38	39	76
105°	302	308	222	53	45	320
115°	567	573	582	592	596	560
125°	799	807	811	813	816	714
135°	995	1001	1005	1008	1005	766
145°	1148	1155	1157	1159	1159	718
155°	1265	1263	1264	1268	1263	583
165°	1334	1331	1330	1337	1331	377
175°	1365	1361	1361	1368	1360	130
180°	1365	1365	1365	1365	1365	



TEST NUMBER: P332440-840

CATALOG NUMBER: S123RDIW-S775D1030U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8
2.5°	1308.0	1307.3	1306.5	1305.8	1305.0	1303.5	1301.2	1299.0	1296.8	1294.4	1296.6
5°	1303.8	1302.6	1301.4	1300.3	1299.1	1297.1	1294.2	1291.4	1288.6	1285.9	1287.9
7.5°	1291.7	1290.5	1289.2	1287.9	1286.7	1284.1	1280.5	1276.9	1273.2	1269.5	1270.7
10°	1281.6	1279.9	1278.3	1276.7	1275.0	1272.0	1267.8	1263.6	1259.4	1255.2	1255.4
12.5°	1267.2	1265.4	1263.5	1261.7	1259.9	1256.4	1251.2	1246.1	1240.8	1235.7	1235.6
15°	1243.5	1240.9	1238.3	1235.8	1233.1	1228.6	1222.0	1215.5	1208.8	1202.2	1201.1
17.5°	1213.7	1210.7	1207.7	1204.7	1201.6	1196.0	1187.6	1179.2	1170.8	1162.6	1160.0
20°	1191.7	1187.9	1184.2	1180.4	1176.7	1170.3	1161.3	1152.5	1143.6	1134.6	1131.6
22.5°	1167.2	1162.9	1158.5	1154.2	1149.8	1143.0	1133.5	1124.0	1114.5	1105.0	1101.2
25°	1131.5	1125.6	1119.6	1113.8	1107.9	1099.5	1088.7	1077.9	1067.1	1056.3	1051.4
27.5°	1088.0	1081.6	1075.1	1068.6	1062.2	1052.9	1040.9	1028.9	1016.7	1004.7	997.8
30°	1058.4	1051.4	1044.4	1037.3	1030.3	1020.2	1007.0	993.8	980.7	967.6	959.6
32.5°	1028.9	1020.9	1012.9	1004.9	996.9	985.9	972.0	958.2	944.2	930.3	921.6
35°	979.2	970.7	962.2	953.8	945.3	933.8	919.3	904.6	890.1	875.6	865.5
37.5°	928.9	919.4	910.0	900.6	891.2	878.8	863.2	847.7	832.1	816.6	805.1
40°	896.7	886.4	876.0	865.7	855.4	841.8	825.2	808.5	791.7	775.1	762.9
42.5°	860.3	850.0	839.6	829.3	819.0	805.2	787.9	770.6	753.5	736.2	722.9
45°	804.7	794.2	783.6	773.0	762.3	748.1	729.9	711.9	693.8	675.7	662.3
47.5°	749.1	737.5	725.9	714.3	702.7	687.8	669.7	651.6	633.5	615.4	600.9
50°	708.4	697.4	686.4	675.3	664.3	649.2	630.3	611.2	592.2	573.1	558.6
52.5°	672.1	660.1	648.1	636.1	624.2	608.7	589.9	571.1	552.2	533.3	518.3
55°	611.2	599.7	588.1	576.6	565.1	549.4	529.4	509.5	489.5	469.5	455.9
57.5°	554.9	542.4	529.9	517.3	504.7	488.5	468.4	448.3	428.2	408.2	395.3
60°	516.0	503.1	490.2	477.3	464.3	448.1	428.6	409.1	389.6	370.1	357.4
62.5°	477.1	464.1	451.2	438.3	425.5	409.2	389.7	370.2	350.7	331.1	319.2
65°	417.7	404.8	391.8	378.9	366.0	350.3	332.0	313.7	295.4	277.0	265.5
67.5°	358.3	345.2	332.1	319.0	306.0	290.6	273.1	255.5	237.9	220.4	211.8
70°	319.3	306.7	294.0	281.2	268.6	254.0	237.5	221.2	204.7	188.2	180.0
72.5°	280.4	267.9	255.4	242.9	230.5	216.7	201.8	186.8	171.9	156.9	150.2
75°	221.0	209.7	198.4	187.1	175.9	163.8	150.9	137.9	125.0	112.1	109.8
77.5°	166.8	156.6	146.4	136.2	126.0	116.8	108.5	100.2	91.9	83.5	82.3
80°	132.2	122.5	112.9	103.3	93.6	86.3	81.4	76.4	71.6	66.7	65.9
82.5°	99.2	90.9	82.5	74.2	65.9	60.6	58.3	55.9	53.7	51.4	50.7
85°	56.0	50.9	45.7	40.5	35.3	32.4	31.7	31.0	30.3	29.6	29.2
87.5°	20.5	18.9	17.3	15.7	14.0	13.5	14.1	14.7	15.2	15.9	15.9
90°	1.0	3.2	5.6	7.8	10.0	12.6	15.6	18.5	21.4	24.3	25.2
92.5°	18.9	18.3	17.6	17.0	16.4	17.2	19.4	21.5	23.7	26.0	27.4
95°	61.9	52.6	43.4	34.1	24.9	21.5	24.0	26.5	29.0	31.4	33.0
97.5°	124.3	120.2	116.0	111.9	107.8	97.6	81.4	65.1	48.9	32.6	34.4
100°	171.4	175.9	180.5	184.9	189.5	174.1	139.0	103.8	68.7	33.4	35.2
102.5°	225.0	228.2	231.5	234.7	237.9	220.4	182.0	143.6	105.1	66.8	61.2
105°	302.3	304.8	307.2	309.7	312.1	303.3	283.0	262.7	242.5	222.2	182.3
107.5°	383.8	385.8	387.8	389.8	391.7	394.4	397.6	400.7	403.9	407.2	377.9
110°	438.2	440.0	441.8	443.6	445.4	447.6	450.0	452.5	454.9	457.5	450.0



TEST NUMBER: P332440-840

CATALOG NUMBER: S123RDIW-S775D1030U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	490.1	491.7	493.3	495.0	496.7	498.7	501.1	503.6	506.1	508.6	508.7
115°	567.0	568.4	569.7	571.1	572.4	574.1	576.1	578.1	580.2	582.2	584.5
117.5°	641.5	643.1	644.8	646.4	648.1	649.4	650.6	651.6	652.6	653.6	655.4
120°	687.7	689.7	691.8	693.8	695.8	697.2	697.8	698.5	699.2	699.8	701.7
122.5°	734.8	736.4	738.1	739.7	741.4	742.7	743.6	744.4	745.3	746.1	747.4
125°	799.3	801.1	802.8	804.7	806.5	807.9	808.7	809.6	810.5	811.4	811.9
127.5°	861.7	863.5	865.4	867.2	869.0	870.4	871.5	872.6	873.6	874.7	875.5
130°	900.7	902.5	904.3	906.2	908.0	909.3	910.2	911.1	912.0	912.9	913.8
132.5°	938.1	939.9	941.6	943.4	945.2	946.5	947.3	948.0	948.7	949.4	950.3
135°	995.0	996.4	997.7	999.1	1000.5	1001.6	1002.5	1003.4	1004.3	1005.2	1005.8
137.5°	1043.7	1045.4	1047.1	1048.8	1050.6	1051.7	1052.2	1052.7	1053.2	1053.7	1054.7
140°	1076.2	1077.5	1078.9	1080.3	1081.6	1082.6	1083.3	1084.0	1084.6	1085.3	1086.2
142.5°	1106.2	1107.5	1108.9	1110.2	1111.7	1112.7	1113.3	1114.0	1114.7	1115.3	1116.1
145°	1148.2	1149.7	1151.3	1153.0	1154.5	1155.5	1156.0	1156.4	1156.9	1157.3	1157.8
147.5°	1187.8	1188.8	1189.8	1190.8	1191.9	1192.7	1193.1	1193.6	1194.0	1194.5	1194.9
150°	1212.1	1212.7	1213.5	1214.2	1214.8	1215.4	1215.8	1216.3	1216.7	1217.2	1217.6
152.5°	1234.1	1234.4	1234.7	1235.0	1235.3	1235.6	1235.9	1236.1	1236.4	1236.7	1237.5
155°	1264.9	1264.4	1263.9	1263.5	1263.0	1262.9	1263.1	1263.3	1263.6	1263.8	1265.0
157.5°	1288.8	1288.8	1288.7	1288.7	1288.6	1288.5	1288.3	1288.0	1287.8	1287.6	1288.9
160°	1303.4	1303.1	1302.9	1302.7	1302.5	1302.2	1302.0	1301.8	1301.6	1301.4	1302.7
162.5°	1317.2	1316.6	1316.1	1315.5	1314.8	1314.4	1314.2	1314.0	1313.7	1313.5	1315.0
165°	1333.8	1333.1	1332.5	1331.8	1331.1	1330.7	1330.4	1330.2	1330.0	1329.8	1331.6
167.5°	1346.8	1345.9	1345.0	1344.1	1343.2	1342.7	1342.7	1342.7	1342.7	1342.7	1344.5
170°	1354.1	1353.2	1352.3	1351.4	1350.5	1350.1	1350.1	1350.1	1350.1	1350.1	1351.8
172.5°	1359.0	1357.9	1356.9	1355.7	1354.6	1354.2	1354.3	1354.5	1354.7	1354.9	1356.8
175°	1365.2	1364.1	1363.0	1361.9	1360.8	1360.3	1360.5	1360.8	1361.0	1361.2	1362.8
177.5°	1366.9	1365.9	1365.1	1364.2	1363.3	1362.9	1363.1	1363.3	1363.4	1363.6	1365.1
180°	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2



TEST NUMBER: P332440-840

CATALOG NUMBER: S123RDIW-S775D1030U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8
2.5°	1298.6	1300.7	1302.7	1303.6	1303.2	1302.8	1302.4	1302.1
5°	1290.0	1292.1	1294.2	1295.1	1294.6	1294.1	1293.6	1293.2
7.5°	1271.9	1273.0	1274.2	1274.4	1273.6	1272.8	1272.0	1271.2
10°	1255.7	1255.9	1256.1	1255.7	1254.5	1253.2	1252.1	1250.9
12.5°	1235.4	1235.3	1235.2	1234.4	1233.0	1231.6	1230.3	1228.9
15°	1199.9	1198.7	1197.6	1196.2	1194.6	1192.9	1191.2	1189.6
17.5°	1157.5	1155.1	1152.6	1150.1	1147.6	1145.2	1142.8	1140.3
20°	1128.5	1125.4	1122.4	1119.4	1116.6	1113.8	1111.0	1108.1
22.5°	1097.4	1093.6	1089.7	1086.5	1083.9	1081.3	1078.6	1076.0
25°	1046.5	1041.6	1036.6	1032.9	1030.3	1027.6	1025.1	1022.5
27.5°	991.0	984.2	977.3	971.9	968.0	964.0	960.1	956.1
30°	951.6	943.5	935.5	929.7	925.9	922.2	918.4	914.6
32.5°	912.8	904.1	895.3	889.0	885.0	881.1	877.2	873.2
35°	855.4	845.3	835.2	828.0	823.7	819.5	815.3	811.0
37.5°	793.6	782.1	770.6	762.3	757.1	751.8	746.7	741.4
40°	750.6	738.4	726.2	717.4	712.0	706.6	701.1	695.8
42.5°	709.4	696.1	682.8	673.7	668.8	664.0	659.1	654.3
45°	648.9	635.5	622.1	612.6	606.9	601.3	595.7	590.1
47.5°	586.2	571.7	557.1	547.3	542.3	537.2	532.3	527.3
50°	544.0	529.4	514.8	504.8	499.5	494.0	488.7	483.2
52.5°	503.1	488.0	472.8	462.8	458.0	453.1	448.3	443.4
55°	442.2	428.6	415.0	405.8	401.1	396.4	391.7	387.0
57.5°	382.4	369.5	356.7	348.2	344.3	340.2	336.2	332.2
60°	344.7	332.0	319.3	311.0	307.0	303.0	299.0	295.0
62.5°	307.3	295.4	283.5	275.4	271.1	267.0	262.9	258.6
65°	254.0	242.5	231.0	223.9	221.4	218.7	216.2	213.6
67.5°	203.2	194.6	185.9	180.3	177.5	174.7	172.0	169.2
70°	171.8	163.5	155.3	150.0	147.3	144.7	142.2	139.6
72.5°	143.5	136.7	130.1	126.1	125.0	124.0	122.9	121.8
75°	107.3	105.0	102.7	101.3	100.8	100.4	99.9	99.4
77.5°	81.0	79.7	78.5	77.6	77.2	76.6	76.1	75.7
80°	65.2	64.5	63.8	63.2	62.7	62.3	61.8	61.3
82.5°	50.0	49.3	48.6	48.2	48.1	48.0	47.9	47.8
85°	28.7	28.2	27.8	27.5	27.5	27.5	27.5	27.5
87.5°	15.9	15.9	15.9	15.8	15.7	15.6	15.5	15.3
90°	26.2	27.1	28.0	28.6	29.1	29.5	30.0	30.4
92.5°	28.9	30.3	31.7	32.6	32.8	33.1	33.4	33.6
95°	34.6	36.2	37.8	38.6	38.6	38.6	38.6	38.6
97.5°	36.3	38.1	39.9	40.9	41.1	41.3	41.6	41.8
100°	37.1	38.9	40.7	41.7	41.9	42.1	42.4	42.6
102.5°	55.5	50.0	44.3	41.8	42.2	42.6	43.0	43.4
105°	142.4	102.4	62.5	42.8	43.3	43.7	44.1	44.6
107.5°	348.6	319.4	290.1	260.4	230.4	200.4	170.3	140.2
110°	442.6	435.2	427.7	407.9	375.7	343.4	311.1	278.9



TEST NUMBER: P332440-840

CATALOG NUMBER: S123RDIW-S775D1030U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	508.9	509.0	509.1	505.7	499.0	492.2	485.3	478.6
115°	586.7	589.0	591.3	592.8	593.7	594.6	595.5	596.4
117.5°	657.2	659.0	660.9	661.9	662.0	662.2	662.4	662.6
120°	703.5	705.3	707.1	708.0	708.0	708.0	708.0	708.0
122.5°	748.6	749.9	751.1	751.9	752.0	752.2	752.5	752.7
125°	812.3	812.8	813.2	813.7	814.2	814.6	815.1	815.5
127.5°	876.2	876.9	877.7	877.8	877.3	876.9	876.5	876.0
130°	914.7	915.5	916.5	916.8	916.3	915.8	915.3	914.9
132.5°	951.2	952.1	953.0	953.1	952.5	951.9	951.3	950.6
135°	1006.5	1007.2	1007.8	1007.8	1007.2	1006.5	1005.8	1005.2
137.5°	1055.8	1056.9	1058.0	1058.3	1057.8	1057.4	1056.9	1056.5
140°	1087.1	1088.0	1088.9	1089.1	1088.7	1088.2	1087.8	1087.3
142.5°	1116.8	1117.5	1118.2	1118.2	1117.6	1117.0	1116.4	1115.7
145°	1158.2	1158.7	1159.1	1159.3	1159.3	1159.3	1159.3	1159.3
147.5°	1195.4	1195.8	1196.3	1196.0	1195.0	1193.9	1192.9	1191.8
150°	1218.1	1218.5	1219.0	1218.9	1218.2	1217.5	1216.9	1216.2
152.5°	1238.3	1239.1	1239.9	1239.8	1238.7	1237.7	1236.7	1235.7
155°	1266.1	1267.2	1268.4	1268.2	1266.9	1265.6	1264.1	1262.8
157.5°	1290.3	1291.6	1292.9	1292.7	1291.0	1289.3	1287.5	1285.8
160°	1304.0	1305.5	1306.8	1306.7	1305.0	1303.5	1301.9	1300.3
162.5°	1316.6	1318.2	1319.7	1319.7	1318.4	1317.0	1315.6	1314.1
165°	1333.3	1335.1	1337.0	1337.1	1335.5	1333.9	1332.3	1330.8
167.5°	1346.4	1348.2	1350.0	1350.0	1348.2	1346.4	1344.5	1342.7
170°	1353.6	1355.4	1357.3	1357.3	1355.4	1353.6	1351.8	1350.1
172.5°	1358.6	1360.3	1362.1	1362.0	1360.1	1358.1	1356.0	1354.1
175°	1364.3	1365.9	1367.6	1367.5	1365.6	1363.8	1362.0	1360.2
177.5°	1366.5	1368.0	1369.4	1369.3	1367.5	1365.6	1363.8	1362.0
180°	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2

(END OF REPORT)