

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332441-930

Luminaire Tested: **S123RDIW-S775D1030U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332441-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D1030U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5294.3 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332441-930

CATALOG NUMBER: S123RDIW-S775D1030U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332441-930

CATALOG NUMBER: S123RDIW-S775D1030U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	88	81	75	70	81	75	70	65	63	59	56	51	49	46	41	39	38	33
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	36	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	21
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	19	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11330	11330	11330
5°	11373	11217	11282
10°	11309	11075	11038
15°	11188	10816	10702
20°	11021	10493	10247
25°	10849	10128	9804
30°	10621	9708	9178
35°	10387	9289	8604
40°	10172	8792	7893
45°	9889	8304	7252
50°	9577	7748	6532
55°	9259	7112	5863
60°	8968	6433	5126
65°	8588	5695	4391
70°	8113	4784	3547
75°	7419	3764	3335
80°	6614	3335	3068
85°	5582	2952	2742



TEST NUMBER: P332441-930

CATALOG NUMBER: S123RDIW-S775D1030U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	1.9
10°-20°	275.0	5.2
20°-30°	396.0	7.5
30°-40°	446.1	8.4
40°-50°	426.7	8.1
50°-60°	349.5	6.6
60°-70°	235.8	4.5
70°-80°	118.6	2.2
80°-90°	34.5	0.7
90°-100°	68.5	1.3
100°-110°	205.0	3.9
110°-120°	348.7	6.6
120°-130°	458.7	8.7
130°-140°	515.5	9.7
140°-150°	506.8	9.6
150°-160°	426.6	8.1
160°-170°	284.0	5.4
170°-180°	99.4	1.9
0°-30°	769.9	14.5
0°-40°	1215.9	23.0
0°-60°	1992.1	37.6
0°-90°	2381.0	45.0
90°-120°	622.2	11.8
90°-150°	2103.2	39.7
90°-180°	2913.0	55.0
0°-180°	5294.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1053	1053	1053	1053	1053	
5°	1053	1048	1038	1045	1044	100
15°	1004	994	971	966	960	283
25°	914	891	853	835	826	420
35°	790	759	707	671	655	495
45°	650	610	546	498	476	501
55°	493	450	379	331	312	442
65°	337	289	224	184	172	334
75°	178	137	90	82	80	190
85°	45	27	24	22	22	51
90°	1	9	20	23	25	5
95°	49	55	61	64	64	55
105°	186	188	195	195	197	199
115°	351	353	352	353	352	347
125°	514	516	515	511	508	458
135°	667	671	671	667	666	513
145°	809	810	813	812	809	505
155°	926	926	927	930	924	426
165°	1008	1006	1006	1010	1005	284
175°	1049	1046	1046	1050	1045	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P332441-930

CATALOG NUMBER: S123RDIW-S775D1030U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6
2.5°	1056.0	1055.4	1054.8	1054.2	1053.6	1052.4	1050.5	1048.7	1046.9	1045.1	1046.8
5°	1052.6	1051.7	1050.7	1049.8	1048.8	1047.2	1044.9	1042.6	1040.3	1038.1	1039.8
7.5°	1042.8	1041.9	1040.8	1039.8	1038.8	1036.7	1033.8	1030.9	1027.9	1024.9	1025.9
10°	1034.7	1033.3	1032.0	1030.7	1029.3	1027.0	1023.5	1020.2	1016.8	1013.3	1013.5
12.5°	1023.0	1021.6	1020.1	1018.6	1017.2	1014.3	1010.2	1006.0	1001.8	997.6	997.5
15°	1004.0	1001.8	999.7	997.7	995.6	991.9	986.6	981.3	975.9	970.6	969.7
17.5°	979.8	977.5	975.0	972.6	970.1	965.6	958.8	952.0	945.3	938.6	936.5
20°	962.1	959.0	956.0	953.0	950.0	944.9	937.6	930.4	923.2	916.0	913.5
22.5°	942.3	938.8	935.3	931.8	928.3	922.8	915.1	907.4	899.8	892.1	889.0
25°	913.5	908.7	903.9	899.2	894.5	887.7	879.0	870.3	861.5	852.8	848.8
27.5°	878.4	873.2	868.0	862.7	857.5	850.0	840.3	830.6	820.8	811.1	805.6
30°	854.5	848.8	843.2	837.5	831.8	823.6	813.0	802.3	791.7	781.1	774.7
32.5°	830.6	824.2	817.7	811.3	804.9	796.0	784.7	773.6	762.3	751.1	744.0
35°	790.5	783.7	776.8	770.1	763.2	753.9	742.2	730.3	718.6	706.9	698.7
37.5°	749.9	742.2	734.7	727.1	719.5	709.5	696.9	684.4	671.8	659.3	650.0
40°	723.9	715.6	707.2	698.9	690.6	679.6	666.2	652.7	639.2	625.7	615.9
42.5°	694.6	686.2	677.8	669.5	661.2	650.0	636.1	622.2	608.3	594.4	583.6
45°	649.6	641.2	632.6	624.0	615.5	604.0	589.3	574.7	560.1	545.5	534.7
47.5°	604.8	595.4	586.0	576.7	567.3	555.3	540.7	526.0	511.4	496.8	485.1
50°	571.9	563.0	554.2	545.2	536.3	524.2	508.8	493.4	478.1	462.7	450.9
52.5°	542.6	533.0	523.3	513.6	503.9	491.5	476.2	461.1	445.8	430.6	418.4
55°	493.4	484.1	474.8	465.5	456.2	443.5	427.4	411.3	395.2	379.0	368.0
57.5°	448.0	437.9	427.8	417.6	407.5	394.4	378.1	361.9	345.7	329.5	319.1
60°	416.6	406.2	395.7	385.3	374.9	361.7	346.0	330.3	314.5	298.8	288.5
62.5°	385.1	374.7	364.3	353.8	343.5	330.4	314.6	298.9	283.2	267.3	257.7
65°	337.2	326.8	316.3	305.9	295.5	282.8	268.1	253.2	238.5	223.6	214.3
67.5°	289.3	278.7	268.2	257.6	247.0	234.6	220.5	206.3	192.1	177.9	171.0
70°	257.8	247.6	237.3	227.1	216.9	205.0	191.8	178.6	165.3	152.0	145.3
72.5°	226.4	216.3	206.2	196.1	186.1	175.0	162.9	150.8	138.8	126.7	121.2
75°	178.4	169.3	160.2	151.1	142.0	132.2	121.8	111.4	100.9	90.5	88.6
77.5°	134.7	126.5	118.2	110.0	101.7	94.3	87.6	80.9	74.2	67.4	66.4
80°	106.7	98.9	91.2	83.4	75.6	69.7	65.7	61.7	57.8	53.8	53.2
82.5°	80.1	73.4	66.6	59.9	53.2	48.9	47.0	45.2	43.4	41.5	40.9
85°	45.2	41.1	36.9	32.7	28.5	26.2	25.6	25.0	24.5	23.9	23.6
87.5°	16.6	15.2	13.9	12.6	11.3	10.9	11.4	11.9	12.4	12.9	12.8
90°	0.8	2.7	4.5	6.4	8.2	10.3	12.6	15.1	17.4	19.8	20.5
92.5°	20.0	21.2	22.5	23.7	24.9	26.3	27.6	29.0	30.3	31.7	32.3
95°	48.8	50.0	51.3	52.6	53.9	55.3	56.7	58.2	59.7	61.1	61.9
97.5°	86.6	87.5	88.5	89.4	90.4	91.4	92.5	93.5	94.6	95.6	96.5
100°	112.3	113.4	114.5	115.6	116.8	117.7	118.7	119.6	120.5	121.4	122.0
102.5°	142.1	142.8	143.4	144.1	144.7	145.6	146.8	148.1	149.3	150.5	151.1
105°	185.9	186.2	186.6	186.9	187.4	188.3	190.0	191.6	193.3	194.9	194.9
107.5°	236.8	236.9	237.2	237.4	237.6	238.1	238.7	239.4	240.0	240.7	241.2
110°	268.5	268.8	269.2	269.5	269.9	270.3	270.7	271.0	271.4	271.7	272.5



TEST NUMBER: P332441-930

CATALOG NUMBER: S123RDIW-S775D1030U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	301.5	301.7	301.9	302.1	302.4	302.5	302.6	302.6	302.7	302.8	303.7
115°	351.1	351.6	352.1	352.7	353.3	353.4	352.9	352.6	352.2	351.9	352.0
117.5°	401.0	401.3	401.7	402.0	402.4	402.4	401.9	401.4	400.9	400.5	400.4
120°	432.0	433.1	434.2	435.3	436.4	436.5	435.5	434.6	433.7	432.8	432.6
122.5°	464.4	465.2	466.0	466.8	467.6	467.7	467.3	466.8	466.4	465.9	465.4
125°	513.8	514.3	514.9	515.4	516.0	516.1	515.7	515.4	514.9	514.6	513.9
127.5°	559.4	560.5	561.7	562.9	564.0	564.4	564.0	563.6	563.2	562.8	561.8
130°	589.8	591.3	592.7	594.2	595.7	596.1	595.6	595.0	594.4	593.9	593.1
132.5°	620.1	621.6	623.1	624.6	626.1	626.6	626.1	625.7	625.3	624.9	624.0
135°	666.6	667.6	668.8	669.8	671.0	671.4	671.2	671.1	670.9	670.7	669.9
137.5°	709.6	710.5	711.3	712.2	713.2	713.9	714.4	714.9	715.3	715.8	715.0
140°	739.2	740.2	741.1	742.0	742.9	743.5	743.6	743.9	744.0	744.2	744.0
142.5°	766.4	767.3	768.2	769.1	770.1	770.6	770.9	771.3	771.7	772.0	771.8
145°	808.6	809.0	809.3	809.8	810.1	810.6	811.1	811.7	812.2	812.8	812.6
147.5°	845.6	846.3	846.9	847.7	848.3	848.9	849.4	849.9	850.4	850.9	850.9
150°	871.4	871.8	872.1	872.5	872.9	873.3	873.6	874.0	874.3	874.7	874.7
152.5°	892.6	893.1	893.6	894.1	894.6	895.0	895.2	895.4	895.7	895.9	896.2
155°	925.9	925.9	925.9	925.9	925.9	926.0	926.2	926.4	926.6	926.8	927.5
157.5°	954.4	954.1	953.9	953.7	953.5	953.4	953.6	953.7	953.9	954.0	954.8
160°	972.2	971.8	971.4	971.1	970.7	970.5	970.5	970.5	970.5	970.5	971.4
162.5°	988.1	987.6	987.0	986.5	986.0	985.8	985.9	986.1	986.3	986.4	987.3
165°	1008.5	1008.0	1007.5	1006.9	1006.3	1006.1	1006.1	1006.1	1006.1	1006.1	1007.1
167.5°	1024.9	1024.2	1023.4	1022.7	1022.0	1021.7	1021.8	1022.0	1022.1	1022.2	1023.4
170°	1034.1	1033.4	1032.7	1031.9	1031.2	1030.9	1030.9	1030.9	1030.9	1030.9	1032.1
172.5°	1041.4	1040.6	1039.9	1039.2	1038.4	1038.1	1038.1	1038.1	1038.1	1038.1	1039.3
175°	1049.0	1048.3	1047.6	1046.8	1046.1	1045.7	1045.7	1045.7	1045.7	1045.7	1046.8
177.5°	1052.1	1051.6	1051.0	1050.4	1049.8	1049.5	1049.5	1049.5	1049.5	1049.5	1050.4
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332441-930

CATALOG NUMBER: S123RDIW-S775D1030U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6
2.5°	1048.4	1050.1	1051.7	1052.5	1052.1	1051.8	1051.5	1051.2
5°	1041.5	1043.2	1044.9	1045.5	1045.2	1044.8	1044.4	1044.1
7.5°	1026.9	1027.8	1028.7	1028.9	1028.3	1027.6	1027.0	1026.3
10°	1013.7	1013.9	1014.1	1013.7	1012.8	1011.8	1010.9	1009.9
12.5°	997.4	997.3	997.2	996.5	995.5	994.3	993.3	992.1
15°	968.7	967.8	966.9	965.7	964.4	963.0	961.7	960.4
17.5°	934.5	932.5	930.5	928.5	926.5	924.5	922.6	920.6
20°	911.1	908.6	906.1	903.8	901.5	899.2	896.9	894.6
22.5°	886.0	882.9	879.8	877.2	875.1	872.9	870.8	868.7
25°	844.9	840.9	836.9	833.9	831.8	829.6	827.6	825.5
27.5°	800.1	794.6	789.0	784.6	781.5	778.3	775.1	771.9
30°	768.3	761.7	755.3	750.6	747.5	744.5	741.4	738.4
32.5°	736.9	729.9	722.8	717.7	714.5	711.3	708.2	705.0
35°	690.6	682.4	674.3	668.5	665.0	661.6	658.2	654.8
37.5°	640.7	631.4	622.2	615.5	611.2	607.0	602.8	598.6
40°	606.0	596.1	586.3	579.2	574.8	570.5	566.1	561.7
42.5°	572.7	562.0	551.2	543.9	540.0	536.1	532.1	528.2
45°	523.9	513.1	502.2	494.6	490.0	485.4	480.9	476.4
47.5°	473.3	461.5	449.8	441.9	437.8	433.7	429.7	425.7
50°	439.2	427.4	415.6	407.6	403.2	398.8	394.5	390.1
52.5°	406.2	394.0	381.7	373.7	369.7	365.8	361.9	358.0
55°	357.0	346.0	335.0	327.6	323.8	320.0	316.3	312.4
57.5°	308.8	298.3	288.0	281.1	277.9	274.7	271.4	268.2
60°	278.3	268.1	257.8	251.1	247.9	244.6	241.4	238.1
62.5°	248.1	238.5	228.9	222.3	218.9	215.6	212.2	208.8
65°	205.0	195.8	186.5	180.8	178.7	176.6	174.6	172.4
67.5°	164.0	157.1	150.1	145.5	143.3	141.0	138.8	136.6
70°	138.7	132.0	125.4	121.1	119.0	116.8	114.8	112.7
72.5°	115.9	110.4	105.0	101.8	100.9	100.1	99.2	98.3
75°	86.7	84.8	82.9	81.8	81.4	81.0	80.6	80.2
77.5°	65.4	64.3	63.3	62.6	62.3	61.9	61.5	61.1
80°	52.7	52.1	51.5	51.0	50.6	50.3	49.9	49.5
82.5°	40.4	39.8	39.2	38.9	38.8	38.7	38.6	38.6
85°	23.2	22.7	22.4	22.2	22.2	22.2	22.2	22.2
87.5°	12.8	12.8	12.8	12.8	12.7	12.6	12.6	12.5
90°	21.3	22.0	22.7	23.3	23.6	24.1	24.4	24.8
92.5°	32.9	33.5	34.1	34.2	34.0	33.8	33.6	33.3
95°	62.6	63.3	64.1	64.4	64.4	64.4	64.4	64.4
97.5°	97.3	98.2	99.1	99.4	99.3	99.3	99.2	99.1
100°	122.5	123.1	123.6	124.1	124.4	124.8	125.1	125.6
102.5°	151.6	152.1	152.7	153.0	152.9	152.8	152.7	152.6
105°	194.9	194.9	194.9	195.1	195.5	195.8	196.2	196.6
107.5°	241.9	242.5	243.0	243.2	243.0	242.8	242.6	242.3
110°	273.2	273.9	274.7	274.8	274.5	274.1	273.8	273.4



TEST NUMBER: P332441-930

CATALOG NUMBER: S123RDIW-S775D1030U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	304.6	305.4	306.3	306.7	306.6	306.6	306.6	306.5
115°	352.2	352.5	352.6	352.6	352.5	352.2	352.0	351.9
117.5°	400.4	400.3	400.3	400.0	399.5	399.0	398.4	397.9
120°	432.4	432.3	432.1	431.8	431.5	431.0	430.7	430.3
122.5°	464.9	464.4	464.0	463.4	462.9	462.4	461.9	461.4
125°	513.1	512.4	511.7	510.9	510.2	509.5	508.7	508.0
127.5°	560.8	559.8	558.7	557.7	556.9	556.1	555.2	554.4
130°	592.4	591.7	590.9	590.0	588.6	587.3	586.1	584.8
132.5°	623.2	622.3	621.4	620.5	619.5	618.5	617.5	616.5
135°	669.2	668.5	667.7	667.2	666.8	666.5	666.1	665.8
137.5°	714.3	713.5	712.7	712.0	711.3	710.6	709.9	709.2
140°	743.9	743.6	743.5	742.7	741.4	740.2	738.9	737.6
142.5°	771.6	771.4	771.3	770.6	769.6	768.7	767.7	766.7
145°	812.4	812.2	812.0	811.5	810.8	810.1	809.3	808.6
147.5°	850.9	850.9	850.9	850.4	849.3	848.2	847.1	846.0
150°	874.7	874.7	874.7	874.2	873.1	872.0	870.9	869.8
152.5°	896.4	896.7	897.1	896.7	895.8	894.8	893.8	892.9
155°	928.2	929.0	929.7	929.4	928.1	926.8	925.6	924.3
157.5°	955.5	956.3	957.1	957.0	955.9	955.0	953.9	952.8
160°	972.4	973.3	974.2	974.3	973.5	972.8	972.1	971.3
162.5°	988.2	989.1	990.1	989.9	988.8	987.6	986.4	985.2
165°	1008.3	1009.3	1010.5	1010.4	1009.1	1007.8	1006.5	1005.3
167.5°	1024.5	1025.6	1026.8	1026.8	1025.6	1024.5	1023.4	1022.2
170°	1033.4	1034.7	1036.0	1036.0	1034.7	1033.4	1032.1	1030.9
172.5°	1040.4	1041.5	1042.7	1042.6	1041.3	1040.0	1038.7	1037.5
175°	1047.9	1049.0	1050.1	1050.0	1048.7	1047.4	1046.2	1044.9
177.5°	1051.2	1052.1	1053.0	1053.0	1051.9	1050.9	1049.9	1048.9
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5

(END OF REPORT)