

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332443-840

Luminaire Tested: **S123RDIW-S775D1320U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332443-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D1320U840-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7699.7 lumens
Efficiency: N/A
Efficacy: 125.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332443-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332443-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40								
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35								
2	88	81	75	70	80	74	69	65	61	57	54	49	46	44	38	36	35	30								
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	30	26								
4	74	63	56	50	67	58	52	47	48	43	40	39	36	33	30	28	26	22								
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20								
6	62	51	43	38	57	47	40	35	39	34	30	32	28	25	25	23	21	18								
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	20	18	16								
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17	14								
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13								
10	47	35	28	23	43	32	26	22	27	23	19	23	19	16	18	16	14	12								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13295	13295	13295	13295
5°	15847	13351	11757	13351
10°	19787	13274	10622	13274
15°	23226	13138	9686	13138
20°	25921	12936	8891	12936
25°	25508	12722	8402	12722
30°	18334	12525	7899	12525
35°	12242	12269	7573	12269
40°	9020	11960	7235	11960
45°	7566	11420	6905	11420
50°	6677	10712	6445	10712
55°	5853	9903	5814	9903
60°	5214	9128	5326	9128
65°	4579	8295	4956	8295
70°	3594	7553	4526	7553
75°	3165	6596	4134	6596
80°	2752	5604	4060	5604
85°	2223	4508	4310	4508



TEST NUMBER: P332443-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.5	1.6
10°-20°	379.5	4.9
20°-30°	596.1	7.7
30°-40°	621.9	8.1
40°-50°	532.3	6.9
50°-60°	405.7	5.3
60°-70°	260.0	3.4
70°-80°	125.1	1.6
80°-90°	38.0	0.5
90°-100°	108.6	1.4
100°-110°	325.1	4.2
110°-120°	553.0	7.2
120°-130°	727.3	9.4
130°-140°	817.5	10.6
140°-150°	803.6	10.4
150°-160°	676.5	8.8
160°-170°	450.3	5.8
170°-180°	157.7	2.0
0°-30°	1097.0	14.2
0°-40°	1719.0	22.3
0°-60°	2656.9	34.5
0°-90°	3080.1	40.0
90°-120°	986.7	12.8
90°-150°	3335.1	43.3
90°-180°	4620.0	60.0
0°-180°	7699.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1235	1235	1235	1235	1235	
5°	1467	1236	1088	1236	1467	151
15°	2084	1179	869	1179	2084	591
25°	2148	1071	707	1071	2148	923
35°	932	934	576	934	932	611
45°	497	750	454	750	497	391
55°	312	528	310	528	312	282
65°	180	326	195	326	180	177
75°	76	159	99	159	76	82
85°	18	36	35	36	18	22
90°	39	1	39	1	39	20
95°	102	77	102	77	102	105
105°	312	295	312	295	312	331
115°	558	557	558	557	558	552
125°	806	815	806	815	806	720
135°	1056	1057	1056	1057	1056	812
145°	1282	1282	1282	1282	1282	800
155°	1466	1468	1466	1468	1466	675
165°	1594	1599	1594	1599	1594	450
175°	1657	1663	1657	1663	1657	157
180°	1667	1667	1667	1667	1667	



TEST NUMBER: P332443-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1315.5	1317.2	1311.6	1310.8	1304.4	1302.7	1302.7	1293.8	1288.4	1281.2	1277.0
5°	1466.6	1475.1	1470.9	1461.4	1445.5	1441.8	1431.8	1415.9	1398.0	1375.7	1365.1
7.5°	1655.5	1667.1	1662.6	1647.9	1631.3	1617.9	1589.5	1563.2	1526.3	1493.9	1466.2
10°	1810.3	1798.2	1788.7	1774.3	1759.1	1734.1	1704.6	1663.9	1616.8	1579.8	1538.5
12.5°	1926.2	1924.2	1912.2	1897.4	1875.8	1852.2	1815.8	1766.3	1711.5	1658.1	1610.9
15°	2084.2	2087.4	2079.4	2064.1	2033.5	1991.7	1936.7	1916.0	1837.9	1779.7	1721.5
17.5°	2193.5	2192.9	2191.8	2170.6	2139.3	2109.6	2058.6	2004.4	1933.5	1851.6	1773.2
20°	2262.9	2257.7	2258.7	2234.8	2211.6	2177.3	2127.6	2048.8	1990.6	1896.0	1815.0
22.5°	2261.2	2260.2	2264.2	2256.0	2239.1	2212.8	2173.6	2107.2	2033.0	1937.4	1846.3
25°	2147.7	2143.4	2168.3	2175.1	2202.1	2206.9	2195.2	2158.8	2088.4	1990.0	1877.4
27.5°	1797.5	1795.1	1841.2	1899.0	1972.1	2029.0	2084.0	2110.5	2088.4	2018.0	1905.2
30°	1475.1	1524.8	1548.1	1631.6	1724.6	1835.7	1933.0	2025.5	2048.2	2017.6	1925.0
32.5°	1224.8	1268.1	1287.5	1359.2	1445.9	1576.0	1721.9	1852.9	1945.5	1968.9	1913.2
35°	931.6	932.1	976.5	1008.2	1088.6	1222.3	1364.1	1539.6	1714.0	1846.2	1860.0
37.5°	743.4	746.0	772.8	804.5	864.7	935.5	1060.3	1206.2	1407.8	1610.6	1729.6
40°	641.9	646.6	666.7	697.9	741.2	794.7	891.9	1029.5	1197.5	1423.3	1607.8
42.5°	576.7	584.4	594.8	618.8	645.7	695.7	774.4	880.5	1033.4	1246.9	1459.8
45°	497.0	501.2	509.2	520.3	544.6	579.5	632.4	703.7	830.6	1002.5	1215.5
47.5°	438.4	436.2	444.5	453.5	469.7	493.5	529.0	587.2	677.7	815.6	996.3
50°	398.7	398.1	403.9	410.8	426.2	443.6	472.7	516.5	588.4	702.7	868.2
52.5°	361.4	363.5	367.6	376.2	387.2	401.3	427.4	459.0	520.8	619.4	757.3
55°	311.9	313.6	319.3	324.1	332.0	346.3	362.7	389.1	431.4	500.2	613.8
57.5°	270.0	269.3	274.9	276.1	285.1	296.7	309.4	329.9	360.6	411.6	488.2
60°	242.2	240.5	245.3	249.0	253.8	263.3	273.9	294.0	318.3	355.8	421.4
62.5°	216.8	216.0	219.5	223.2	227.1	235.8	244.7	260.1	279.3	311.0	363.0
65°	179.8	181.4	182.9	184.5	186.6	191.9	200.4	211.0	224.2	246.4	283.9
67.5°	141.3	142.9	143.4	146.6	151.2	154.5	159.7	169.1	178.2	197.0	218.3
70°	114.2	113.7	114.2	115.8	121.6	127.4	134.3	141.2	146.9	160.2	178.1
72.5°	98.2	97.1	98.6	98.9	101.7	103.3	107.7	114.1	121.6	130.6	143.5
75°	76.1	76.1	76.1	76.1	78.3	79.3	80.9	82.5	85.1	89.4	98.9
77.5°	56.2	56.4	57.1	57.7	58.1	58.7	59.7	61.2	62.2	64.4	68.6
80°	44.4	44.9	44.4	44.9	44.9	45.9	46.6	48.1	48.7	51.3	52.9
82.5°	33.4	33.1	33.4	33.9	33.9	35.0	35.1	36.3	36.4	37.8	39.4
85°	18.0	17.0	18.0	17.5	18.5	17.5	18.0	19.0	19.0	19.6	21.7
87.5°	12.1	12.8	11.8	12.1	12.0	12.3	12.0	11.8	12.4	11.8	11.4
90°	39.3	38.7	38.2	37.6	37.0	36.1	34.9	33.7	32.6	31.4	27.7
92.5°	52.9	53.2	53.6	53.9	54.3	54.0	53.1	52.1	51.2	50.3	48.2
95°	102.2	102.2	102.2	102.2	102.2	101.6	100.4	99.3	98.1	96.9	94.6
97.5°	157.1	157.3	157.4	157.5	157.6	157.0	155.7	154.3	153.0	151.7	150.0
100°	199.0	198.5	197.9	197.3	196.7	196.0	195.1	194.3	193.4	192.6	191.1
102.5°	242.1	242.2	242.3	242.4	242.5	242.2	241.3	240.3	239.5	238.6	236.7
105°	311.7	311.1	310.5	310.0	309.4	309.1	309.1	309.1	309.1	309.1	306.5
107.5°	384.3	384.7	385.0	385.4	385.7	385.4	384.5	383.5	382.6	381.6	380.6
110°	433.5	434.1	434.7	435.3	435.9	435.6	434.4	433.2	432.1	430.9	430.3



TEST NUMBER: P332443-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	485.9	486.0	486.1	486.3	486.4	485.7	484.3	482.9	481.6	480.2	480.1
115°	558.0	558.3	558.6	558.9	559.2	559.2	558.9	558.6	558.3	558.0	558.6
117.5°	631.1	631.9	632.7	633.5	634.3	634.7	634.8	634.9	634.9	635.0	635.7
120°	682.4	683.0	683.6	684.2	684.7	685.2	685.5	685.7	686.0	686.3	687.8
122.5°	731.6	732.5	733.3	734.1	734.9	735.7	736.4	737.2	737.9	738.7	739.4
125°	805.5	806.7	807.8	809.0	810.2	811.3	812.5	813.6	814.9	816.0	816.6
127.5°	879.1	880.5	881.8	883.1	884.4	886.0	887.6	889.2	890.8	892.5	893.1
130°	927.4	929.4	931.4	933.4	935.4	937.1	938.3	939.4	940.6	941.7	942.6
132.5°	977.7	979.2	980.8	982.3	983.9	985.4	986.7	988.2	989.6	991.0	991.6
135°	1055.7	1056.2	1056.8	1057.4	1058.0	1058.8	1060.1	1061.2	1062.4	1063.5	1063.8
137.5°	1124.6	1125.7	1126.8	1127.9	1129.0	1130.1	1131.4	1132.6	1133.8	1135.1	1134.3
140°	1169.6	1171.6	1173.7	1175.8	1177.8	1178.9	1179.2	1179.5	1179.8	1180.1	1179.8
142.5°	1215.8	1217.3	1218.9	1220.4	1222.0	1222.9	1223.2	1223.6	1223.9	1224.2	1223.6
145°	1282.2	1283.4	1284.5	1285.8	1287.0	1287.7	1288.0	1288.2	1288.5	1288.8	1288.0
147.5°	1341.5	1343.2	1344.9	1346.8	1348.5	1349.3	1349.3	1349.3	1349.3	1349.3	1348.5
150°	1379.2	1380.9	1382.7	1384.4	1386.1	1387.0	1387.0	1387.0	1387.0	1387.0	1386.4
152.5°	1415.8	1417.3	1418.9	1420.4	1421.9	1422.4	1422.0	1421.5	1421.1	1420.6	1420.3
155°	1465.6	1467.6	1469.8	1471.8	1473.8	1474.2	1473.1	1471.9	1470.8	1469.6	1469.3
157.5°	1511.0	1512.6	1514.2	1515.8	1517.4	1517.7	1516.4	1515.2	1514.0	1512.8	1512.6
160°	1540.2	1541.5	1542.7	1543.8	1545.0	1544.8	1543.4	1541.9	1540.4	1538.9	1538.9
162.5°	1562.3	1564.2	1566.0	1567.9	1569.7	1569.9	1568.5	1567.0	1565.6	1564.1	1563.9
165°	1594.0	1596.0	1598.1	1600.1	1602.2	1602.3	1600.5	1598.8	1597.0	1595.3	1595.3
167.5°	1620.9	1622.8	1624.6	1626.4	1628.2	1628.2	1626.4	1624.6	1622.8	1620.9	1620.7
170°	1634.6	1636.6	1638.7	1640.7	1642.7	1642.7	1640.7	1638.7	1636.6	1634.6	1634.6
172.5°	1645.1	1647.1	1649.1	1651.2	1653.3	1653.4	1651.5	1649.7	1647.9	1646.1	1646.1
175°	1656.9	1658.9	1660.9	1662.9	1665.0	1665.2	1663.4	1661.6	1659.9	1658.2	1658.2
177.5°	1663.1	1664.8	1666.4	1668.0	1669.7	1669.8	1668.4	1667.0	1665.6	1664.2	1664.2
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4



TEST NUMBER: P332443-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1275.3	1273.9	1268.1	1261.3	1252.4	1246.5	1241.8	1239.3	1231.7	1222.3	1216.1
5°	1354.0	1338.2	1321.3	1300.6	1281.6	1262.0	1249.9	1235.6	1218.2	1198.6	1184.9
7.5°	1438.5	1407.3	1373.8	1339.3	1305.0	1274.4	1247.4	1224.2	1196.4	1168.3	1148.7
10°	1503.2	1457.6	1410.6	1362.5	1318.6	1277.4	1245.7	1214.5	1181.1	1148.9	1124.6
12.5°	1562.0	1502.1	1447.8	1388.8	1332.6	1283.3	1237.6	1200.9	1160.8	1126.5	1098.7
15°	1636.4	1575.1	1509.4	1419.6	1345.0	1282.6	1227.2	1179.0	1130.4	1088.1	1061.2
17.5°	1706.0	1613.7	1525.6	1450.6	1353.7	1275.8	1208.0	1150.4	1097.1	1052.3	1019.1
20°	1734.7	1645.4	1549.6	1454.0	1358.8	1271.5	1192.8	1129.3	1073.8	1023.1	992.4
22.5°	1752.0	1650.8	1550.0	1447.2	1346.2	1255.5	1177.6	1107.7	1047.6	999.4	961.5
25°	1772.2	1651.7	1540.7	1439.2	1336.1	1237.7	1145.2	1071.2	1006.1	954.8	914.6
27.5°	1785.5	1643.8	1512.6	1399.7	1295.2	1197.2	1112.4	1034.0	968.0	913.7	870.6
30°	1788.1	1637.4	1491.0	1368.9	1262.5	1172.7	1082.8	1007.7	938.0	880.3	840.1
32.5°	1791.5	1621.7	1461.8	1332.0	1223.2	1134.2	1052.8	981.1	909.6	852.8	811.8
35°	1777.6	1613.2	1417.4	1268.4	1159.4	1073.3	999.8	933.7	863.4	808.4	766.6
37.5°	1717.5	1578.7	1371.6	1196.7	1082.8	1003.0	943.1	885.4	821.0	761.6	722.4
40°	1657.0	1544.9	1336.1	1153.2	1034.2	952.2	898.3	851.2	788.8	733.4	691.1
42.5°	1566.9	1498.8	1302.2	1107.4	979.2	900.2	854.7	810.6	755.9	699.5	659.7
45°	1401.6	1410.6	1232.9	1034.7	903.0	823.7	780.9	750.2	701.7	655.1	614.4
47.5°	1194.4	1278.4	1151.7	957.2	822.7	748.3	710.9	684.2	651.4	605.7	568.6
50°	1059.0	1179.0	1086.5	905.1	772.4	698.4	661.5	639.7	611.2	575.2	539.8
52.5°	934.2	1063.2	1007.8	847.2	717.9	650.3	614.1	596.2	573.5	539.7	507.7
55°	761.8	892.5	879.8	759.7	636.0	575.2	547.8	527.7	512.3	487.0	461.6
57.5°	616.3	740.1	746.7	662.5	563.9	503.8	480.2	465.0	455.0	435.9	412.4
60°	524.5	638.1	660.4	596.9	512.3	459.5	436.2	424.0	416.1	400.8	382.8
62.5°	448.4	545.1	570.3	524.6	462.8	413.3	395.2	383.4	378.0	364.8	348.9
65°	343.2	423.5	447.8	422.4	390.2	350.5	335.8	325.7	320.9	313.6	301.8
67.5°	258.0	316.6	343.3	325.4	313.8	288.7	279.2	273.9	269.6	264.6	254.9
70°	207.2	250.6	278.1	273.4	263.9	250.6	243.8	240.0	235.8	231.6	223.1
72.5°	166.6	196.5	222.3	224.7	216.9	214.2	208.2	206.6	204.1	199.0	194.4
75°	110.5	131.1	149.1	155.9	159.2	161.8	159.2	158.6	158.0	153.9	151.2
77.5°	72.4	83.5	94.8	106.5	111.6	115.1	116.0	118.0	116.5	114.3	113.0
80°	55.5	58.2	66.0	76.1	84.0	87.3	89.4	90.4	89.9	89.4	87.3
82.5°	40.3	42.5	46.3	53.3	60.0	65.2	66.6	66.3	67.5	67.8	66.0
85°	21.7	22.2	23.2	24.3	28.0	33.8	35.4	36.5	37.6	37.6	34.3
87.5°	11.5	10.4	10.4	9.8	10.5	10.3	12.2	13.8	14.8	13.7	14.2
90°	23.8	20.1	16.3	12.9	10.0	7.2	4.2	1.3	4.2	7.2	10.0
92.5°	45.9	43.8	41.7	39.6	37.7	35.6	33.6	31.7	33.6	35.6	37.7
95°	92.3	90.0	87.7	85.4	83.4	81.4	79.3	77.3	79.3	81.4	83.4
97.5°	148.2	146.6	144.9	143.3	141.8	140.3	138.8	137.2	138.8	140.3	141.8
100°	189.7	188.1	186.7	185.1	183.4	181.6	179.9	178.1	179.9	181.6	183.4
102.5°	234.8	232.9	231.0	229.4	228.4	227.4	226.3	225.3	226.3	227.4	228.4
105°	303.9	301.2	298.6	297.0	296.4	295.9	295.3	294.7	295.3	295.9	296.4
107.5°	379.6	378.5	377.5	376.8	376.5	376.1	375.8	375.4	375.8	376.1	376.5
110°	429.8	429.2	428.6	428.0	427.4	426.9	426.3	425.7	426.3	426.9	427.4



TEST NUMBER: P332443-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	479.9	479.8	479.7	479.5	479.1	478.8	478.4	478.1	478.4	478.8	479.1
115°	559.2	559.7	560.3	560.2	559.3	558.4	557.5	556.6	557.5	558.4	559.3
117.5°	636.5	637.2	638.0	638.1	637.5	636.9	636.3	635.8	636.3	636.9	637.5
120°	689.2	690.6	692.2	692.0	690.2	688.5	686.7	685.0	686.7	688.5	690.2
122.5°	740.2	740.9	741.7	741.4	740.2	738.9	737.6	736.4	737.6	738.9	740.2
125°	817.2	817.7	818.3	818.2	817.3	816.4	815.6	814.7	815.6	816.4	817.3
127.5°	893.7	894.4	895.0	894.4	892.5	890.7	888.9	887.0	888.9	890.7	892.5
130°	943.5	944.3	945.2	944.5	942.2	939.9	937.5	935.1	937.5	939.9	942.2
132.5°	992.3	992.9	993.5	992.7	990.4	988.1	985.7	983.4	985.7	988.1	990.4
135°	1064.1	1064.4	1064.7	1064.0	1062.2	1060.5	1058.7	1057.0	1058.7	1060.5	1062.2
137.5°	1133.6	1132.8	1132.1	1130.9	1129.4	1128.0	1126.5	1125.1	1126.5	1128.0	1129.4
140°	1179.5	1179.2	1178.9	1178.1	1176.6	1175.2	1173.7	1172.3	1173.7	1175.2	1176.6
142.5°	1223.0	1222.5	1222.0	1221.0	1219.6	1218.1	1216.7	1215.2	1216.7	1218.1	1219.6
145°	1287.1	1286.2	1285.4	1284.5	1284.0	1283.4	1282.8	1282.2	1282.8	1283.4	1284.0
147.5°	1347.7	1346.9	1346.0	1345.1	1344.1	1343.0	1342.0	1340.9	1342.0	1343.0	1344.1
150°	1385.8	1385.3	1384.7	1384.1	1383.5	1383.0	1382.4	1381.8	1382.4	1383.0	1383.5
152.5°	1419.9	1419.6	1419.2	1418.6	1417.7	1416.9	1416.1	1415.3	1416.1	1416.9	1417.7
155°	1468.9	1468.6	1468.4	1468.2	1468.2	1468.2	1468.2	1468.2	1468.2	1468.2	1468.2
157.5°	1512.3	1512.1	1511.9	1511.9	1512.3	1512.6	1513.0	1513.3	1513.0	1512.6	1512.3
160°	1538.9	1538.9	1538.9	1539.2	1539.8	1540.4	1541.1	1541.6	1541.1	1540.4	1539.8
162.5°	1563.7	1563.5	1563.2	1563.5	1564.3	1565.1	1565.9	1566.7	1565.9	1565.1	1564.3
165°	1595.3	1595.3	1595.3	1595.8	1596.6	1597.5	1598.3	1599.2	1598.3	1597.5	1596.6
167.5°	1620.5	1620.2	1620.0	1620.5	1621.6	1622.9	1624.0	1625.2	1624.0	1622.9	1621.6
170°	1634.6	1634.6	1634.6	1635.2	1636.4	1637.5	1638.7	1639.8	1638.7	1637.5	1636.4
172.5°	1646.1	1646.1	1646.1	1646.7	1647.9	1649.0	1650.2	1651.3	1650.2	1649.0	1647.9
175°	1658.2	1658.2	1658.2	1658.7	1659.9	1661.1	1662.2	1663.4	1662.2	1661.1	1659.9
177.5°	1664.2	1664.2	1664.2	1664.7	1665.6	1666.5	1667.5	1668.4	1667.5	1666.5	1665.6
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4



TEST NUMBER: P332443-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1214.0	1208.4	1204.7	1196.2	1190.6	1184.8	1178.8	1182.7	1182.2	1181.7	1181.7
5°	1173.3	1161.0	1149.9	1135.7	1126.7	1115.6	1107.1	1106.1	1108.2	1100.8	1096.5
7.5°	1132.9	1116.2	1100.4	1084.7	1068.0	1054.7	1046.3	1042.4	1037.0	1032.5	1027.7
10°	1104.5	1084.9	1069.5	1050.1	1032.1	1016.2	1006.1	999.3	995.5	991.9	985.0
12.5°	1075.3	1056.1	1036.6	1014.5	997.3	979.0	971.5	963.7	956.6	952.5	943.1
15°	1032.6	1007.7	987.1	963.8	944.8	926.9	916.3	900.9	898.8	893.5	884.0
17.5°	989.8	962.8	934.3	917.2	895.6	877.0	860.8	855.7	840.5	834.9	826.6
20°	955.9	931.1	909.4	886.7	855.5	838.0	825.4	818.5	806.3	798.9	793.6
22.5°	926.8	901.5	876.4	849.9	824.2	804.6	795.3	784.6	778.0	767.6	761.8
25°	885.0	857.6	827.5	798.9	780.4	765.6	750.7	741.2	731.7	727.0	716.4
27.5°	836.7	807.9	779.7	758.1	735.4	720.7	707.3	698.8	687.4	679.4	673.6
30°	810.0	776.2	751.8	732.3	703.2	689.4	679.4	668.8	660.4	651.9	646.1
32.5°	779.1	748.2	725.2	700.9	678.6	663.7	650.7	641.4	634.1	626.1	620.3
35°	730.6	704.8	681.0	656.6	640.3	624.9	609.7	601.7	594.8	587.4	582.1
37.5°	686.9	662.7	640.1	617.0	596.7	584.2	571.9	565.8	556.5	551.6	546.1
40°	659.8	636.0	611.7	589.6	568.4	558.9	547.8	538.8	530.3	526.6	520.8
42.5°	630.3	606.4	585.9	562.0	544.7	531.8	521.5	511.7	505.3	500.0	496.7
45°	586.3	565.2	545.1	521.3	504.9	493.8	482.2	473.2	467.4	463.7	457.9
47.5°	543.7	522.6	502.2	481.4	465.5	452.9	441.3	435.0	427.3	422.7	418.9
50°	512.8	493.8	472.1	453.1	437.3	424.5	415.1	407.1	400.2	394.5	391.8
52.5°	484.5	464.2	445.5	427.8	411.0	396.7	388.0	379.6	374.5	367.8	364.7
55°	437.8	418.2	402.3	384.9	368.5	356.4	345.8	338.4	333.1	325.7	321.4
57.5°	393.8	376.4	357.4	342.2	325.4	315.1	306.3	296.3	289.8	284.1	279.9
60°	364.3	344.2	327.8	313.6	298.7	285.5	277.6	269.6	262.8	256.9	253.3
62.5°	333.5	315.9	300.3	284.8	271.2	259.7	250.5	243.9	237.8	234.1	230.5
65°	286.0	272.3	256.4	243.8	231.1	222.6	215.2	209.3	205.1	202.5	199.3
67.5°	242.5	229.1	215.3	202.8	194.4	187.9	183.1	178.0	175.9	172.6	170.5
70°	214.1	200.4	188.2	178.7	170.3	165.5	162.3	158.6	156.5	152.3	150.2
72.5°	183.3	173.3	164.5	156.7	150.0	145.6	141.6	137.0	133.7	129.0	126.9
75°	144.3	135.3	128.5	123.2	119.0	113.1	107.3	102.6	101.0	99.4	98.9
77.5°	106.9	101.2	96.2	91.8	86.5	82.3	81.0	80.0	79.6	78.8	78.8
80°	84.0	78.8	75.0	69.8	66.7	66.7	66.7	65.5	66.0	66.0	66.0
82.5°	62.5	57.7	55.6	53.7	53.1	53.5	53.5	53.7	53.4	54.2	53.8
85°	32.2	32.8	33.8	33.3	33.8	33.8	34.9	34.3	34.9	33.8	34.9
87.5°	14.4	16.4	17.6	18.7	19.9	20.2	20.9	21.1	21.8	22.0	22.2
90°	12.9	16.3	20.1	23.8	27.7	31.4	32.6	33.7	34.9	36.1	37.0
92.5°	39.6	41.7	43.8	45.9	48.2	50.3	51.2	52.1	53.1	54.0	54.3
95°	85.4	87.7	90.0	92.3	94.6	96.9	98.1	99.3	100.4	101.6	102.2
97.5°	143.3	144.9	146.6	148.2	150.0	151.7	153.0	154.3	155.7	157.0	157.6
100°	185.1	186.7	188.1	189.7	191.1	192.6	193.4	194.3	195.1	196.0	196.7
102.5°	229.4	231.0	232.9	234.8	236.7	238.6	239.5	240.3	241.3	242.2	242.5
105°	297.0	298.6	301.2	303.9	306.5	309.1	309.1	309.1	309.1	309.1	309.4
107.5°	376.8	377.5	378.5	379.6	380.6	381.6	382.6	383.5	384.5	385.4	385.7
110°	428.0	428.6	429.2	429.8	430.3	430.9	432.1	433.2	434.4	435.6	435.9



TEST NUMBER: P332443-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	479.5	479.7	479.8	479.9	480.1	480.2	481.6	482.9	484.3	485.7	486.4
115°	560.2	560.3	559.7	559.2	558.6	558.0	558.3	558.6	558.9	559.2	559.2
117.5°	638.1	638.0	637.2	636.5	635.7	635.0	634.9	634.9	634.8	634.7	634.3
120°	692.0	692.2	690.6	689.2	687.8	686.3	686.0	685.7	685.5	685.2	684.7
122.5°	741.4	741.7	740.9	740.2	739.4	738.7	737.9	737.2	736.4	735.7	734.9
125°	818.2	818.3	817.7	817.2	816.6	816.0	814.9	813.6	812.5	811.3	810.2
127.5°	894.4	895.0	894.4	893.7	893.1	892.5	890.8	889.2	887.6	886.0	884.4
130°	944.5	945.2	944.3	943.5	942.6	941.7	940.6	939.4	938.3	937.1	935.4
132.5°	992.7	993.5	992.9	992.3	991.6	991.0	989.6	988.2	986.7	985.4	983.9
135°	1064.0	1064.7	1064.4	1064.1	1063.8	1063.5	1062.4	1061.2	1060.1	1058.8	1058.0
137.5°	1130.9	1132.1	1132.8	1133.6	1134.3	1135.1	1133.8	1132.6	1131.4	1130.1	1129.0
140°	1178.1	1178.9	1179.2	1179.5	1179.8	1180.1	1179.8	1179.5	1179.2	1178.9	1177.8
142.5°	1221.0	1222.0	1222.5	1223.0	1223.6	1224.2	1223.9	1223.6	1223.2	1222.9	1222.0
145°	1284.5	1285.4	1286.2	1287.1	1288.0	1288.8	1288.5	1288.2	1288.0	1287.7	1287.0
147.5°	1345.1	1346.0	1346.9	1347.7	1348.5	1349.3	1349.3	1349.3	1349.3	1349.3	1348.5
150°	1384.1	1384.7	1385.3	1385.8	1386.4	1387.0	1387.0	1387.0	1387.0	1387.0	1386.1
152.5°	1418.6	1419.2	1419.6	1419.9	1420.3	1420.6	1421.1	1421.5	1422.0	1422.4	1421.9
155°	1468.2	1468.4	1468.6	1468.9	1469.3	1469.6	1470.8	1471.9	1473.1	1474.2	1473.8
157.5°	1511.9	1511.9	1512.1	1512.3	1512.6	1512.8	1514.0	1515.2	1516.4	1517.7	1517.4
160°	1539.2	1538.9	1538.9	1538.9	1538.9	1538.9	1540.4	1541.9	1543.4	1544.8	1545.0
162.5°	1563.5	1563.2	1563.5	1563.7	1563.9	1564.1	1565.6	1567.0	1568.5	1569.9	1569.7
165°	1595.8	1595.3	1595.3	1595.3	1595.3	1595.3	1597.0	1598.8	1600.5	1602.3	1602.2
167.5°	1620.5	1620.0	1620.2	1620.5	1620.7	1620.9	1622.8	1624.6	1626.4	1628.2	1628.2
170°	1635.2	1634.6	1634.6	1634.6	1634.6	1634.6	1636.6	1638.7	1640.7	1642.7	1642.7
172.5°	1646.7	1646.1	1646.1	1646.1	1646.1	1646.1	1647.9	1649.7	1651.5	1653.4	1653.3
175°	1658.7	1658.2	1658.2	1658.2	1658.2	1658.2	1659.9	1661.6	1663.4	1665.2	1665.0
177.5°	1664.7	1664.2	1664.2	1664.2	1664.2	1664.2	1665.6	1667.0	1668.4	1669.8	1669.7
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4



TEST NUMBER: P332443-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1176.7	1176.3	1176.7	1175.0	1176.7	1176.3	1176.7	1181.7	1181.7	1182.2	1182.7
5°	1095.0	1094.4	1092.9	1088.1	1092.9	1094.4	1095.0	1096.5	1100.8	1108.2	1106.1
7.5°	1023.6	1022.9	1018.2	1018.3	1018.2	1022.9	1023.6	1027.7	1032.5	1037.0	1042.4
10°	981.3	981.8	975.5	971.8	975.5	981.8	981.3	985.0	991.9	995.5	999.3
12.5°	940.3	937.9	932.7	928.7	932.7	937.9	940.3	943.1	952.5	956.6	963.7
15°	886.2	880.8	868.2	869.2	868.2	880.8	886.2	884.0	893.5	898.8	900.9
17.5°	822.3	818.5	818.2	810.8	818.2	818.5	822.3	826.6	834.9	840.5	855.7
20°	785.2	782.5	783.6	776.2	783.6	782.5	785.2	793.6	798.9	806.3	818.5
22.5°	756.0	753.4	748.9	746.6	748.9	753.4	756.0	761.8	767.6	778.0	784.6
25°	713.3	709.0	704.8	707.4	704.8	709.0	713.3	716.4	727.0	731.7	741.2
27.5°	670.6	667.3	663.1	662.6	663.1	667.3	670.6	673.6	679.4	687.4	698.8
30°	643.5	640.3	638.1	635.5	638.1	640.3	643.5	646.1	651.9	660.4	668.8
32.5°	615.9	615.3	611.5	611.0	611.5	615.3	615.9	620.3	626.1	634.1	641.4
35°	580.0	576.8	575.7	576.3	575.7	576.8	580.0	582.1	587.4	594.8	601.7
37.5°	545.8	541.6	539.7	537.9	539.7	541.6	545.8	546.1	551.6	556.5	565.8
40°	521.3	517.1	516.0	514.9	516.0	517.1	521.3	520.8	526.6	530.3	538.8
42.5°	493.8	492.1	491.5	489.6	491.5	492.1	493.8	496.7	500.0	505.3	511.7
45°	456.3	455.8	452.6	453.6	452.6	455.8	456.3	457.9	463.7	467.4	473.2
47.5°	416.8	414.4	412.2	413.6	412.2	414.4	416.8	418.9	422.7	427.3	435.0
50°	389.7	388.6	383.8	384.9	383.8	388.6	389.7	391.8	394.5	400.2	407.1
52.5°	362.6	358.6	356.8	356.2	356.8	358.6	362.6	364.7	367.8	374.5	379.6
55°	317.8	313.0	310.8	309.8	310.8	313.0	317.8	321.4	325.7	333.1	338.4
57.5°	273.8	272.5	270.8	272.0	270.8	272.5	273.8	279.9	284.1	289.8	296.3
60°	247.9	247.9	247.9	247.4	247.9	247.9	247.9	253.3	256.9	262.8	269.6
62.5°	228.1	226.8	226.4	227.1	226.4	226.8	228.1	230.5	234.1	237.8	243.9
65°	197.7	197.2	195.1	194.6	195.1	197.2	197.7	199.3	202.5	205.1	209.3
67.5°	169.1	167.1	166.5	165.8	166.5	167.1	169.1	170.5	172.6	175.9	178.0
70°	147.5	146.4	143.3	143.8	143.3	146.4	147.5	150.2	152.3	156.5	158.6
72.5°	124.2	123.2	122.6	121.8	122.6	123.2	124.2	126.9	129.0	133.7	137.0
75°	98.4	97.9	97.3	99.4	97.3	97.9	98.4	98.9	99.4	101.0	102.6
77.5°	78.8	78.8	79.1	78.3	79.1	78.8	78.8	78.8	78.8	79.6	80.0
80°	66.0	66.0	65.5	65.5	65.5	66.0	66.0	66.0	66.0	66.0	65.5
82.5°	53.0	53.4	53.7	52.9	53.7	53.4	53.0	53.8	54.2	53.4	53.7
85°	34.9	34.3	35.4	34.9	35.4	34.3	34.9	34.9	33.8	34.9	34.3
87.5°	23.1	22.4	22.5	23.1	22.5	22.4	23.1	22.2	22.0	21.8	21.1
90°	37.6	38.2	38.7	39.3	38.7	38.2	37.6	37.0	36.1	34.9	33.7
92.5°	53.9	53.6	53.2	52.9	53.2	53.6	53.9	54.3	54.0	53.1	52.1
95°	102.2	102.2	102.2	102.2	102.2	102.2	102.2	102.2	101.6	100.4	99.3
97.5°	157.5	157.4	157.3	157.1	157.3	157.4	157.5	157.6	157.0	155.7	154.3
100°	197.3	197.9	198.5	199.0	198.5	197.9	197.3	196.7	196.0	195.1	194.3
102.5°	242.4	242.3	242.2	242.1	242.2	242.3	242.4	242.5	242.2	241.3	240.3
105°	310.0	310.5	311.1	311.7	311.1	310.5	310.0	309.4	309.1	309.1	309.1
107.5°	385.4	385.0	384.7	384.3	384.7	385.0	385.4	385.7	385.4	384.5	383.5
110°	435.3	434.7	434.1	433.5	434.1	434.7	435.3	435.9	435.6	434.4	433.2



TEST NUMBER: P332443-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	486.3	486.1	486.0	485.9	486.0	486.1	486.3	486.4	485.7	484.3	482.9
115°	558.9	558.6	558.3	558.0	558.3	558.6	558.9	559.2	559.2	558.9	558.6
117.5°	633.5	632.7	631.9	631.1	631.9	632.7	633.5	634.3	634.7	634.8	634.9
120°	684.2	683.6	683.0	682.4	683.0	683.6	684.2	684.7	685.2	685.5	685.7
122.5°	734.1	733.3	732.5	731.6	732.5	733.3	734.1	734.9	735.7	736.4	737.2
125°	809.0	807.8	806.7	805.5	806.7	807.8	809.0	810.2	811.3	812.5	813.6
127.5°	883.1	881.8	880.5	879.1	880.5	881.8	883.1	884.4	886.0	887.6	889.2
130°	933.4	931.4	929.4	927.4	929.4	931.4	933.4	935.4	937.1	938.3	939.4
132.5°	982.3	980.8	979.2	977.7	979.2	980.8	982.3	983.9	985.4	986.7	988.2
135°	1057.4	1056.8	1056.2	1055.7	1056.2	1056.8	1057.4	1058.0	1058.8	1060.1	1061.2
137.5°	1127.9	1126.8	1125.7	1124.6	1125.7	1126.8	1127.9	1129.0	1130.1	1131.4	1132.6
140°	1175.8	1173.7	1171.6	1169.6	1171.6	1173.7	1175.8	1177.8	1178.9	1179.2	1179.5
142.5°	1220.4	1218.9	1217.3	1215.8	1217.3	1218.9	1220.4	1222.0	1222.9	1223.2	1223.6
145°	1285.8	1284.5	1283.4	1282.2	1283.4	1284.5	1285.8	1287.0	1287.7	1288.0	1288.2
147.5°	1346.8	1344.9	1343.2	1341.5	1343.2	1344.9	1346.8	1348.5	1349.3	1349.3	1349.3
150°	1384.4	1382.7	1380.9	1379.2	1380.9	1382.7	1384.4	1386.1	1387.0	1387.0	1387.0
152.5°	1420.4	1418.9	1417.3	1415.8	1417.3	1418.9	1420.4	1421.9	1422.4	1422.0	1421.5
155°	1471.8	1469.8	1467.6	1465.6	1467.6	1469.8	1471.8	1473.8	1474.2	1473.1	1471.9
157.5°	1515.8	1514.2	1512.6	1511.0	1512.6	1514.2	1515.8	1517.4	1517.7	1516.4	1515.2
160°	1543.8	1542.7	1541.5	1540.2	1541.5	1542.7	1543.8	1545.0	1544.8	1543.4	1541.9
162.5°	1567.9	1566.0	1564.2	1562.3	1564.2	1566.0	1567.9	1569.7	1569.9	1568.5	1567.0
165°	1600.1	1598.1	1596.0	1594.0	1596.0	1598.1	1600.1	1602.2	1602.3	1600.5	1598.8
167.5°	1626.4	1624.6	1622.8	1620.9	1622.8	1624.6	1626.4	1628.2	1628.2	1626.4	1624.6
170°	1640.7	1638.7	1636.6	1634.6	1636.6	1638.7	1640.7	1642.7	1642.7	1640.7	1638.7
172.5°	1651.2	1649.1	1647.1	1645.1	1647.1	1649.1	1651.2	1653.3	1653.4	1651.5	1649.7
175°	1662.9	1660.9	1658.9	1656.9	1658.9	1660.9	1662.9	1665.0	1665.2	1663.4	1661.6
177.5°	1668.0	1666.4	1664.8	1663.1	1664.8	1666.4	1668.0	1669.7	1669.8	1668.4	1667.0
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4



TEST NUMBER: P332443-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1178.8	1184.8	1190.6	1196.2	1204.7	1208.4	1214.0	1216.1	1222.3	1231.7	1239.3
5°	1107.1	1115.6	1126.7	1135.7	1149.9	1161.0	1173.3	1184.9	1198.6	1218.2	1235.6
7.5°	1046.3	1054.7	1068.0	1084.7	1100.4	1116.2	1132.9	1148.7	1168.3	1196.4	1224.2
10°	1006.1	1016.2	1032.1	1050.1	1069.5	1084.9	1104.5	1124.6	1148.9	1181.1	1214.5
12.5°	971.5	979.0	997.3	1014.5	1036.6	1056.1	1075.3	1098.7	1126.5	1160.8	1200.9
15°	916.3	926.9	944.8	963.8	987.1	1007.7	1032.6	1061.2	1088.1	1130.4	1179.0
17.5°	860.8	877.0	895.6	917.2	934.3	962.8	989.8	1019.1	1052.3	1097.1	1150.4
20°	825.4	838.0	855.5	886.7	909.4	931.1	955.9	992.4	1023.1	1073.8	1129.3
22.5°	795.3	804.6	824.2	849.9	876.4	901.5	926.8	961.5	999.4	1047.6	1107.7
25°	750.7	765.6	780.4	798.9	827.5	857.6	885.0	914.6	954.8	1006.1	1071.2
27.5°	707.3	720.7	735.4	758.1	779.7	807.9	836.7	870.6	913.7	968.0	1034.0
30°	679.4	689.4	703.2	732.3	751.8	776.2	810.0	840.1	880.3	938.0	1007.7
32.5°	650.7	663.7	678.6	700.9	725.2	748.2	779.1	811.8	852.8	909.6	981.1
35°	609.7	624.9	640.3	656.6	681.0	704.8	730.6	766.6	808.4	863.4	933.7
37.5°	571.9	584.2	596.7	617.0	640.1	662.7	686.9	722.4	761.6	821.0	885.4
40°	547.8	558.9	568.4	589.6	611.7	636.0	659.8	691.1	733.4	788.8	851.2
42.5°	521.5	531.8	544.7	562.0	585.9	606.4	630.3	659.7	699.5	755.9	810.6
45°	482.2	493.8	504.9	521.3	545.1	565.2	586.3	614.4	655.1	701.7	750.2
47.5°	441.3	452.9	465.5	481.4	502.2	522.6	543.7	568.6	605.7	651.4	684.2
50°	415.1	424.5	437.3	453.1	472.1	493.8	512.8	539.8	575.2	611.2	639.7
52.5°	388.0	396.7	411.0	427.8	445.5	464.2	484.5	507.7	539.7	573.5	596.2
55°	345.8	356.4	368.5	384.9	402.3	418.2	437.8	461.6	487.0	512.3	527.7
57.5°	306.3	315.1	325.4	342.2	357.4	376.4	393.8	412.4	435.9	455.0	465.0
60°	277.6	285.5	298.7	313.6	327.8	344.2	364.3	382.8	400.8	416.1	424.0
62.5°	250.5	259.7	271.2	284.8	300.3	315.9	333.5	348.9	364.8	378.0	383.4
65°	215.2	222.6	231.1	243.8	256.4	272.3	286.0	301.8	313.6	320.9	325.7
67.5°	183.1	187.9	194.4	202.8	215.3	229.1	242.5	254.9	264.6	269.6	273.9
70°	162.3	165.5	170.3	178.7	188.2	200.4	214.1	223.1	231.6	235.8	240.0
72.5°	141.6	145.6	150.0	156.7	164.5	173.3	183.3	194.4	199.0	204.1	206.6
75°	107.3	113.1	119.0	123.2	128.5	135.3	144.3	151.2	153.9	158.0	158.6
77.5°	81.0	82.3	86.5	91.8	96.2	101.2	106.9	113.0	114.3	116.5	118.0
80°	66.7	66.7	66.7	69.8	75.0	78.8	84.0	87.3	89.4	89.9	90.4
82.5°	53.5	53.5	53.1	53.7	55.6	57.7	62.5	66.0	67.8	67.5	66.3
85°	34.9	33.8	33.8	33.3	33.8	32.8	32.2	34.3	37.6	37.6	36.5
87.5°	20.9	20.2	19.9	18.7	17.6	16.4	14.4	14.2	13.7	14.8	13.8
90°	32.6	31.4	27.7	23.8	20.1	16.3	12.9	10.0	7.2	4.2	1.3
92.5°	51.2	50.3	48.2	45.9	43.8	41.7	39.6	37.7	35.6	33.6	31.7
95°	98.1	96.9	94.6	92.3	90.0	87.7	85.4	83.4	81.4	79.3	77.3
97.5°	153.0	151.7	150.0	148.2	146.6	144.9	143.3	141.8	140.3	138.8	137.2
100°	193.4	192.6	191.1	189.7	188.1	186.7	185.1	183.4	181.6	179.9	178.1
102.5°	239.5	238.6	236.7	234.8	232.9	231.0	229.4	228.4	227.4	226.3	225.3
105°	309.1	309.1	306.5	303.9	301.2	298.6	297.0	296.4	295.9	295.3	294.7
107.5°	382.6	381.6	380.6	379.6	378.5	377.5	376.8	376.5	376.1	375.8	375.4
110°	432.1	430.9	430.3	429.8	429.2	428.6	428.0	427.4	426.9	426.3	425.7



TEST NUMBER: P332443-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	481.6	480.2	480.1	479.9	479.8	479.7	479.5	479.1	478.8	478.4	478.1
115°	558.3	558.0	558.6	559.2	559.7	560.3	560.2	559.3	558.4	557.5	556.6
117.5°	634.9	635.0	635.7	636.5	637.2	638.0	638.1	637.5	636.9	636.3	635.8
120°	686.0	686.3	687.8	689.2	690.6	692.2	692.0	690.2	688.5	686.7	685.0
122.5°	737.9	738.7	739.4	740.2	740.9	741.7	741.4	740.2	738.9	737.6	736.4
125°	814.9	816.0	816.6	817.2	817.7	818.3	818.2	817.3	816.4	815.6	814.7
127.5°	890.8	892.5	893.1	893.7	894.4	895.0	894.4	892.5	890.7	888.9	887.0
130°	940.6	941.7	942.6	943.5	944.3	945.2	944.5	942.2	939.9	937.5	935.1
132.5°	989.6	991.0	991.6	992.3	992.9	993.5	992.7	990.4	988.1	985.7	983.4
135°	1062.4	1063.5	1063.8	1064.1	1064.4	1064.7	1064.0	1062.2	1060.5	1058.7	1057.0
137.5°	1133.8	1135.1	1134.3	1133.6	1132.8	1132.1	1130.9	1129.4	1128.0	1126.5	1125.1
140°	1179.8	1180.1	1179.8	1179.5	1179.2	1178.9	1178.1	1176.6	1175.2	1173.7	1172.3
142.5°	1223.9	1224.2	1223.6	1223.0	1222.5	1222.0	1221.0	1219.6	1218.1	1216.7	1215.2
145°	1288.5	1288.8	1288.0	1287.1	1286.2	1285.4	1284.5	1284.0	1283.4	1282.8	1282.2
147.5°	1349.3	1349.3	1348.5	1347.7	1346.9	1346.0	1345.1	1344.1	1343.0	1342.0	1340.9
150°	1387.0	1387.0	1386.4	1385.8	1385.3	1384.7	1384.1	1383.5	1383.0	1382.4	1381.8
152.5°	1421.1	1420.6	1420.3	1419.9	1419.6	1419.2	1418.6	1417.7	1416.9	1416.1	1415.3
155°	1470.8	1469.6	1469.3	1468.9	1468.6	1468.4	1468.2	1468.2	1468.2	1468.2	1468.2
157.5°	1514.0	1512.8	1512.6	1512.3	1512.1	1511.9	1511.9	1512.3	1512.6	1513.0	1513.3
160°	1540.4	1538.9	1538.9	1538.9	1538.9	1538.9	1539.2	1539.8	1540.4	1541.1	1541.6
162.5°	1565.6	1564.1	1563.9	1563.7	1563.5	1563.2	1563.5	1564.3	1565.1	1565.9	1566.7
165°	1597.0	1595.3	1595.3	1595.3	1595.3	1595.3	1595.8	1596.6	1597.5	1598.3	1599.2
167.5°	1622.8	1620.9	1620.7	1620.5	1620.2	1620.0	1620.5	1621.6	1622.9	1624.0	1625.2
170°	1636.6	1634.6	1634.6	1634.6	1634.6	1634.6	1635.2	1636.4	1637.5	1638.7	1639.8
172.5°	1647.9	1646.1	1646.1	1646.1	1646.1	1646.1	1646.7	1647.9	1649.0	1650.2	1651.3
175°	1659.9	1658.2	1658.2	1658.2	1658.2	1658.2	1658.7	1659.9	1661.1	1662.2	1663.4
177.5°	1665.6	1664.2	1664.2	1664.2	1664.2	1664.2	1664.7	1665.6	1666.5	1667.5	1668.4
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4



TEST NUMBER: P332443-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1241.8	1246.5	1252.4	1261.3	1268.1	1273.9	1275.3	1277.0	1281.2	1288.4	1293.8
5°	1249.9	1262.0	1281.6	1300.6	1321.3	1338.2	1354.0	1365.1	1375.7	1398.0	1415.9
7.5°	1247.4	1274.4	1305.0	1339.3	1373.8	1407.3	1438.5	1466.2	1493.9	1526.3	1563.2
10°	1245.7	1277.4	1318.6	1362.5	1410.6	1457.6	1503.2	1538.5	1579.8	1616.8	1663.9
12.5°	1237.6	1283.3	1332.6	1388.8	1447.8	1502.1	1562.0	1610.9	1658.1	1711.5	1766.3
15°	1227.2	1282.6	1345.0	1419.6	1509.4	1575.1	1636.4	1721.5	1779.7	1837.9	1916.0
17.5°	1208.0	1275.8	1353.7	1450.6	1525.6	1613.7	1706.0	1773.2	1851.6	1933.5	2004.4
20°	1192.8	1271.5	1358.8	1454.0	1549.6	1645.4	1734.7	1815.0	1896.0	1990.6	2048.8
22.5°	1177.6	1255.5	1346.2	1447.2	1550.0	1650.8	1752.0	1846.3	1937.4	2033.0	2107.2
25°	1145.2	1237.7	1336.1	1439.2	1540.7	1651.7	1772.2	1877.4	1990.0	2088.4	2158.8
27.5°	1112.4	1197.2	1295.2	1399.7	1512.6	1643.8	1785.5	1905.2	2018.0	2088.4	2110.5
30°	1082.8	1172.7	1262.5	1368.9	1491.0	1637.4	1788.1	1925.0	2017.6	2048.2	2025.5
32.5°	1052.8	1134.2	1223.2	1332.0	1461.8	1621.7	1791.5	1913.2	1968.9	1945.5	1852.9
35°	999.8	1073.3	1159.4	1268.4	1417.4	1613.2	1777.6	1860.0	1846.2	1714.0	1539.6
37.5°	943.1	1003.0	1082.8	1196.7	1371.6	1578.7	1717.5	1729.6	1610.6	1407.8	1206.2
40°	898.3	952.2	1034.2	1153.2	1336.1	1544.9	1657.0	1607.8	1423.3	1197.5	1029.5
42.5°	854.7	900.2	979.2	1107.4	1302.2	1498.8	1566.9	1459.8	1246.9	1033.4	880.5
45°	780.9	823.7	903.0	1034.7	1232.9	1410.6	1401.6	1215.5	1002.5	830.6	703.7
47.5°	710.9	748.3	822.7	957.2	1151.7	1278.4	1194.4	996.3	815.6	677.7	587.2
50°	661.5	698.4	772.4	905.1	1086.5	1179.0	1059.0	868.2	702.7	588.4	516.5
52.5°	614.1	650.3	717.9	847.2	1007.8	1063.2	934.2	757.3	619.4	520.8	459.0
55°	547.8	575.2	636.0	759.7	879.8	892.5	761.8	613.8	500.2	431.4	389.1
57.5°	480.2	503.8	563.9	662.5	746.7	740.1	616.3	488.2	411.6	360.6	329.9
60°	436.2	459.5	512.3	596.9	660.4	638.1	524.5	421.4	355.8	318.3	294.0
62.5°	395.2	413.3	462.8	524.6	570.3	545.1	448.4	363.0	311.0	279.3	260.1
65°	335.8	350.5	390.2	422.4	447.8	423.5	343.2	283.9	246.4	224.2	211.0
67.5°	279.2	288.7	313.8	325.4	343.3	316.6	258.0	218.3	197.0	178.2	169.1
70°	243.8	250.6	263.9	273.4	278.1	250.6	207.2	178.1	160.2	146.9	141.2
72.5°	208.2	214.2	216.9	224.7	222.3	196.5	166.6	143.5	130.6	121.6	114.1
75°	159.2	161.8	159.2	155.9	149.1	131.1	110.5	98.9	89.4	85.1	82.5
77.5°	116.0	115.1	111.6	106.5	94.8	83.5	72.4	68.6	64.4	62.2	61.2
80°	89.4	87.3	84.0	76.1	66.0	58.2	55.5	52.9	51.3	48.7	48.1
82.5°	66.6	65.2	60.0	53.3	46.3	42.5	40.3	39.4	37.8	36.4	36.3
85°	35.4	33.8	28.0	24.3	23.2	22.2	21.7	21.7	19.6	19.0	19.0
87.5°	12.2	10.3	10.5	9.8	10.4	10.4	11.5	11.4	11.8	12.4	11.8
90°	4.2	7.2	10.0	12.9	16.3	20.1	23.8	27.7	31.4	32.6	33.7
92.5°	33.6	35.6	37.7	39.6	41.7	43.8	45.9	48.2	50.3	51.2	52.1
95°	79.3	81.4	83.4	85.4	87.7	90.0	92.3	94.6	96.9	98.1	99.3
97.5°	138.8	140.3	141.8	143.3	144.9	146.6	148.2	150.0	151.7	153.0	154.3
100°	179.9	181.6	183.4	185.1	186.7	188.1	189.7	191.1	192.6	193.4	194.3
102.5°	226.3	227.4	228.4	229.4	231.0	232.9	234.8	236.7	238.6	239.5	240.3
105°	295.3	295.9	296.4	297.0	298.6	301.2	303.9	306.5	309.1	309.1	309.1
107.5°	375.8	376.1	376.5	376.8	377.5	378.5	379.6	380.6	381.6	382.6	383.5
110°	426.3	426.9	427.4	428.0	428.6	429.2	429.8	430.3	430.9	432.1	433.2



TEST NUMBER: P332443-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	478.4	478.8	479.1	479.5	479.7	479.8	479.9	480.1	480.2	481.6	482.9
115°	557.5	558.4	559.3	560.2	560.3	559.7	559.2	558.6	558.0	558.3	558.6
117.5°	636.3	636.9	637.5	638.1	638.0	637.2	636.5	635.7	635.0	634.9	634.9
120°	686.7	688.5	690.2	692.0	692.2	690.6	689.2	687.8	686.3	686.0	685.7
122.5°	737.6	738.9	740.2	741.4	741.7	740.9	740.2	739.4	738.7	737.9	737.2
125°	815.6	816.4	817.3	818.2	818.3	817.7	817.2	816.6	816.0	814.9	813.6
127.5°	888.9	890.7	892.5	894.4	895.0	894.4	893.7	893.1	892.5	890.8	889.2
130°	937.5	939.9	942.2	944.5	945.2	944.3	943.5	942.6	941.7	940.6	939.4
132.5°	985.7	988.1	990.4	992.7	993.5	992.9	992.3	991.6	991.0	989.6	988.2
135°	1058.7	1060.5	1062.2	1064.0	1064.7	1064.4	1064.1	1063.8	1063.5	1062.4	1061.2
137.5°	1126.5	1128.0	1129.4	1130.9	1132.1	1132.8	1133.6	1134.3	1135.1	1133.8	1132.6
140°	1173.7	1175.2	1176.6	1178.1	1178.9	1179.2	1179.5	1179.8	1180.1	1179.8	1179.5
142.5°	1216.7	1218.1	1219.6	1221.0	1222.0	1222.5	1223.0	1223.6	1224.2	1223.9	1223.6
145°	1282.8	1283.4	1284.0	1284.5	1285.4	1286.2	1287.1	1288.0	1288.8	1288.5	1288.2
147.5°	1342.0	1343.0	1344.1	1345.1	1346.0	1346.9	1347.7	1348.5	1349.3	1349.3	1349.3
150°	1382.4	1383.0	1383.5	1384.1	1384.7	1385.3	1385.8	1386.4	1387.0	1387.0	1387.0
152.5°	1416.1	1416.9	1417.7	1418.6	1419.2	1419.6	1419.9	1420.3	1420.6	1421.1	1421.5
155°	1468.2	1468.2	1468.2	1468.2	1468.4	1468.6	1468.9	1469.3	1469.6	1470.8	1471.9
157.5°	1513.0	1512.6	1512.3	1511.9	1511.9	1512.1	1512.3	1512.6	1512.8	1514.0	1515.2
160°	1541.1	1540.4	1539.8	1539.2	1538.9	1538.9	1538.9	1538.9	1538.9	1540.4	1541.9
162.5°	1565.9	1565.1	1564.3	1563.5	1563.2	1563.5	1563.7	1563.9	1564.1	1565.6	1567.0
165°	1598.3	1597.5	1596.6	1595.8	1595.3	1595.3	1595.3	1595.3	1595.3	1597.0	1598.8
167.5°	1624.0	1622.9	1621.6	1620.5	1620.0	1620.2	1620.5	1620.7	1620.9	1622.8	1624.6
170°	1638.7	1637.5	1636.4	1635.2	1634.6	1634.6	1634.6	1634.6	1634.6	1636.6	1638.7
172.5°	1650.2	1649.0	1647.9	1646.7	1646.1	1646.1	1646.1	1646.1	1646.1	1647.9	1649.7
175°	1662.2	1661.1	1659.9	1658.7	1658.2	1658.2	1658.2	1658.2	1658.2	1659.9	1661.6
177.5°	1667.5	1666.5	1665.6	1664.7	1664.2	1664.2	1664.2	1664.2	1664.2	1665.6	1667.0
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4



TEST NUMBER: P332443-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1302.7	1302.7	1304.4	1310.8	1311.6	1317.2	1315.5
5°	1431.8	1441.8	1445.5	1461.4	1470.9	1475.1	1466.6
7.5°	1589.5	1617.9	1631.3	1647.9	1662.6	1667.1	1655.5
10°	1704.6	1734.1	1759.1	1774.3	1788.7	1798.2	1810.3
12.5°	1815.8	1852.2	1875.8	1897.4	1912.2	1924.2	1926.2
15°	1936.7	1991.7	2033.5	2064.1	2079.4	2087.4	2084.2
17.5°	2058.6	2109.6	2139.3	2170.6	2191.8	2192.9	2193.5
20°	2127.6	2177.3	2211.6	2234.8	2258.7	2257.7	2262.9
22.5°	2173.6	2212.8	2239.1	2256.0	2264.2	2260.2	2261.2
25°	2195.2	2206.9	2202.1	2175.1	2168.3	2143.4	2147.7
27.5°	2084.0	2029.0	1972.1	1899.0	1841.2	1795.1	1797.5
30°	1933.0	1835.7	1724.6	1631.6	1548.1	1524.8	1475.1
32.5°	1721.9	1576.0	1445.9	1359.2	1287.5	1268.1	1224.8
35°	1364.1	1222.3	1088.6	1008.2	976.5	932.1	931.6
37.5°	1060.3	935.5	864.7	804.5	772.8	746.0	743.4
40°	891.9	794.7	741.2	697.9	666.7	646.6	641.9
42.5°	774.4	695.7	645.7	618.8	594.8	584.4	576.7
45°	632.4	579.5	544.6	520.3	509.2	501.2	497.0
47.5°	529.0	493.5	469.7	453.5	444.5	436.2	438.4
50°	472.7	443.6	426.2	410.8	403.9	398.1	398.7
52.5°	427.4	401.3	387.2	376.2	367.6	363.5	361.4
55°	362.7	346.3	332.0	324.1	319.3	313.6	311.9
57.5°	309.4	296.7	285.1	276.1	274.9	269.3	270.0
60°	273.9	263.3	253.8	249.0	245.3	240.5	242.2
62.5°	244.7	235.8	227.1	223.2	219.5	216.0	216.8
65°	200.4	191.9	186.6	184.5	182.9	181.4	179.8
67.5°	159.7	154.5	151.2	146.6	143.4	142.9	141.3
70°	134.3	127.4	121.6	115.8	114.2	113.7	114.2
72.5°	107.7	103.3	101.7	98.9	98.6	97.1	98.2
75°	80.9	79.3	78.3	76.1	76.1	76.1	76.1
77.5°	59.7	58.7	58.1	57.7	57.1	56.4	56.2
80°	46.6	45.9	44.9	44.9	44.4	44.9	44.4
82.5°	35.1	35.0	33.9	33.9	33.4	33.1	33.4
85°	18.0	17.5	18.5	17.5	18.0	17.0	18.0
87.5°	12.0	12.3	12.0	12.1	11.8	12.8	12.1
90°	34.9	36.1	37.0	37.6	38.2	38.7	39.3
92.5°	53.1	54.0	54.3	53.9	53.6	53.2	52.9
95°	100.4	101.6	102.2	102.2	102.2	102.2	102.2
97.5°	155.7	157.0	157.6	157.5	157.4	157.3	157.1
100°	195.1	196.0	196.7	197.3	197.9	198.5	199.0
102.5°	241.3	242.2	242.5	242.4	242.3	242.2	242.1
105°	309.1	309.1	309.4	310.0	310.5	311.1	311.7
107.5°	384.5	385.4	385.7	385.4	385.0	384.7	384.3
110°	434.4	435.6	435.9	435.3	434.7	434.1	433.5



TEST NUMBER: P332443-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	484.3	485.7	486.4	486.3	486.1	486.0	485.9
115°	558.9	559.2	559.2	558.9	558.6	558.3	558.0
117.5°	634.8	634.7	634.3	633.5	632.7	631.9	631.1
120°	685.5	685.2	684.7	684.2	683.6	683.0	682.4
122.5°	736.4	735.7	734.9	734.1	733.3	732.5	731.6
125°	812.5	811.3	810.2	809.0	807.8	806.7	805.5
127.5°	887.6	886.0	884.4	883.1	881.8	880.5	879.1
130°	938.3	937.1	935.4	933.4	931.4	929.4	927.4
132.5°	986.7	985.4	983.9	982.3	980.8	979.2	977.7
135°	1060.1	1058.8	1058.0	1057.4	1056.8	1056.2	1055.7
137.5°	1131.4	1130.1	1129.0	1127.9	1126.8	1125.7	1124.6
140°	1179.2	1178.9	1177.8	1175.8	1173.7	1171.6	1169.6
142.5°	1223.2	1222.9	1222.0	1220.4	1218.9	1217.3	1215.8
145°	1288.0	1287.7	1287.0	1285.8	1284.5	1283.4	1282.2
147.5°	1349.3	1349.3	1348.5	1346.8	1344.9	1343.2	1341.5
150°	1387.0	1387.0	1386.1	1384.4	1382.7	1380.9	1379.2
152.5°	1422.0	1422.4	1421.9	1420.4	1418.9	1417.3	1415.8
155°	1473.1	1474.2	1473.8	1471.8	1469.8	1467.6	1465.6
157.5°	1516.4	1517.7	1517.4	1515.8	1514.2	1512.6	1511.0
160°	1543.4	1544.8	1545.0	1543.8	1542.7	1541.5	1540.2
162.5°	1568.5	1569.9	1569.7	1567.9	1566.0	1564.2	1562.3
165°	1600.5	1602.3	1602.2	1600.1	1598.1	1596.0	1594.0
167.5°	1626.4	1628.2	1628.2	1626.4	1624.6	1622.8	1620.9
170°	1640.7	1642.7	1642.7	1640.7	1638.7	1636.6	1634.6
172.5°	1651.5	1653.4	1653.3	1651.2	1649.1	1647.1	1645.1
175°	1663.4	1665.2	1665.0	1662.9	1660.9	1658.9	1656.9
177.5°	1668.4	1669.8	1669.7	1668.0	1666.4	1664.8	1663.1
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4

(END OF REPORT)