

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332445-840

Luminaire Tested: **S123RDIW-S775D1320U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332445-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S775D1320U840-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7569.9 lumens  
Efficiency: N/A  
Efficacy: 123.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 61.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332445-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332445-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	33	28
3	80	71	64	58	72	64	58	53	53	49	45	42	39	37	32	30	29	24
4	73	63	55	49	66	57	51	45	47	42	38	38	34	32	29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	37	32	52	41	35	30	35	29	26	28	24	21	22	19	17	14
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	17	15	13
9	49	37	30	25	45	34	28	24	29	24	20	24	20	17	19	16	14	12
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14034	14034	14034
5°	14088	13894	13973
10°	14008	13719	13672
15°	13857	13397	13256
20°	13651	12997	12693
25°	13438	12545	12144
30°	13155	12026	11368
35°	12867	11506	10657
40°	12600	10891	9777
45°	12250	10286	8983
50°	11863	9597	8092
55°	11470	8811	7263
60°	11108	7967	6351
65°	10639	7055	5440
70°	10049	5923	4393
75°	9191	4662	4134
80°	8195	4135	3800
85°	6916	3656	3396



TEST NUMBER: P332445-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.4	1.6
10°-20°	340.6	4.5
20°-30°	490.5	6.5
30°-40°	552.5	7.3
40°-50°	528.6	7.0
50°-60°	432.9	5.7
60°-70°	292.0	3.9
70°-80°	146.9	1.9
80°-90°	43.8	0.6
90°-100°	108.6	1.4
100°-110°	325.1	4.3
110°-120°	553.0	7.3
120°-130°	727.3	9.6
130°-140°	817.5	10.8
140°-150°	803.6	10.6
150°-160°	676.5	8.9
160°-170°	450.3	5.9
170°-180°	157.7	2.1
0°-30°	953.6	12.6
0°-40°	1506.1	19.9
0°-60°	2467.5	32.6
0°-90°	2950.3	39.0
90°-120°	986.7	13.0
90°-150°	3335.1	44.1
90°-180°	4620.0	61.0
0°-180°	7569.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1304	1304	1304	1304	1304	
5°	1304	1298	1286	1295	1293	124
15°	1244	1231	1202	1197	1190	350
25°	1132	1104	1056	1035	1022	520
35°	979	940	876	832	811	613
45°	805	755	676	617	590	621
55°	611	557	470	410	387	548
65°	418	358	277	227	214	413
75°	221	170	112	102	99	236
85°	56	34	30	28	28	63
90°	1	15	31	37	39	8
95°	77	87	97	102	102	87
105°	295	298	309	309	312	316
115°	557	560	558	559	558	551
125°	815	818	816	811	806	726
135°	1057	1064	1064	1058	1056	814
145°	1282	1285	1289	1287	1282	801
155°	1468	1468	1470	1474	1466	676
165°	1599	1596	1595	1602	1594	451
175°	1663	1658	1658	1665	1657	158
180°	1667	1667	1667	1667	1667	



TEST NUMBER: P332445-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8
2.5°	1308.0	1307.3	1306.5	1305.8	1305.0	1303.5	1301.2	1299.0	1296.8	1294.4	1296.6
5°	1303.8	1302.6	1301.4	1300.3	1299.1	1297.1	1294.2	1291.4	1288.6	1285.9	1287.9
7.5°	1291.7	1290.5	1289.2	1287.9	1286.7	1284.1	1280.5	1276.9	1273.2	1269.5	1270.7
10°	1281.6	1279.9	1278.3	1276.7	1275.0	1272.0	1267.8	1263.6	1259.4	1255.2	1255.4
12.5°	1267.2	1265.4	1263.5	1261.7	1259.9	1256.4	1251.2	1246.1	1240.8	1235.7	1235.6
15°	1243.5	1240.9	1238.3	1235.8	1233.1	1228.6	1222.0	1215.5	1208.8	1202.2	1201.1
17.5°	1213.7	1210.7	1207.7	1204.7	1201.6	1196.0	1187.6	1179.2	1170.8	1162.6	1160.0
20°	1191.7	1187.9	1184.2	1180.4	1176.7	1170.3	1161.3	1152.5	1143.6	1134.6	1131.6
22.5°	1167.2	1162.9	1158.5	1154.2	1149.8	1143.0	1133.5	1124.0	1114.5	1105.0	1101.2
25°	1131.5	1125.6	1119.6	1113.8	1107.9	1099.5	1088.7	1077.9	1067.1	1056.3	1051.4
27.5°	1088.0	1081.6	1075.1	1068.6	1062.2	1052.9	1040.9	1028.9	1016.7	1004.7	997.8
30°	1058.4	1051.4	1044.4	1037.3	1030.3	1020.2	1007.0	993.8	980.7	967.6	959.6
32.5°	1028.9	1020.9	1012.9	1004.9	996.9	985.9	972.0	958.2	944.2	930.3	921.6
35°	979.2	970.7	962.2	953.8	945.3	933.8	919.3	904.6	890.1	875.6	865.5
37.5°	928.9	919.4	910.0	900.6	891.2	878.8	863.2	847.7	832.1	816.6	805.1
40°	896.7	886.4	876.0	865.7	855.4	841.8	825.2	808.5	791.7	775.1	762.9
42.5°	860.3	850.0	839.6	829.3	819.0	805.2	787.9	770.6	753.5	736.2	722.9
45°	804.7	794.2	783.6	773.0	762.3	748.1	729.9	711.9	693.8	675.7	662.3
47.5°	749.1	737.5	725.9	714.3	702.7	687.8	669.7	651.6	633.5	615.4	600.9
50°	708.4	697.4	686.4	675.3	664.3	649.2	630.3	611.2	592.2	573.1	558.6
52.5°	672.1	660.1	648.1	636.1	624.2	608.7	589.9	571.1	552.2	533.3	518.3
55°	611.2	599.7	588.1	576.6	565.1	549.4	529.4	509.5	489.5	469.5	455.9
57.5°	554.9	542.4	529.9	517.3	504.7	488.5	468.4	448.3	428.2	408.2	395.3
60°	516.0	503.1	490.2	477.3	464.3	448.1	428.6	409.1	389.6	370.1	357.4
62.5°	477.1	464.1	451.2	438.3	425.5	409.2	389.7	370.2	350.7	331.1	319.2
65°	417.7	404.8	391.8	378.9	366.0	350.3	332.0	313.7	295.4	277.0	265.5
67.5°	358.3	345.2	332.1	319.0	306.0	290.6	273.1	255.5	237.9	220.4	211.8
70°	319.3	306.7	294.0	281.2	268.6	254.0	237.5	221.2	204.7	188.2	180.0
72.5°	280.4	267.9	255.4	242.9	230.5	216.7	201.8	186.8	171.9	156.9	150.2
75°	221.0	209.7	198.4	187.1	175.9	163.8	150.9	137.9	125.0	112.1	109.8
77.5°	166.8	156.6	146.4	136.2	126.0	116.8	108.5	100.2	91.9	83.5	82.3
80°	132.2	122.5	112.9	103.3	93.6	86.3	81.4	76.4	71.6	66.7	65.9
82.5°	99.2	90.9	82.5	74.2	65.9	60.6	58.3	55.9	53.7	51.4	50.7
85°	56.0	50.9	45.7	40.5	35.3	32.4	31.7	31.0	30.3	29.6	29.2
87.5°	20.6	19.1	17.6	16.1	14.6	14.2	15.0	15.8	16.6	17.3	17.4
90°	1.3	4.2	7.2	10.0	12.9	16.3	20.1	23.8	27.7	31.4	32.6
92.5°	31.7	33.6	35.6	37.7	39.6	41.7	43.8	45.9	48.2	50.3	51.2
95°	77.3	79.3	81.4	83.4	85.4	87.7	90.0	92.3	94.6	96.9	98.1
97.5°	137.2	138.8	140.3	141.8	143.3	144.9	146.6	148.2	150.0	151.7	153.0
100°	178.1	179.9	181.6	183.4	185.1	186.7	188.1	189.7	191.1	192.6	193.4
102.5°	225.3	226.3	227.4	228.4	229.4	231.0	232.9	234.8	236.7	238.6	239.5
105°	294.7	295.3	295.9	296.4	297.0	298.6	301.2	303.9	306.5	309.1	309.1
107.5°	375.4	375.8	376.1	376.5	376.8	377.5	378.5	379.6	380.6	381.6	382.6
110°	425.7	426.3	426.9	427.4	428.0	428.6	429.2	429.8	430.3	430.9	432.1



TEST NUMBER: P332445-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	478.1	478.4	478.8	479.1	479.5	479.7	479.8	479.9	480.1	480.2	481.6
115°	556.6	557.5	558.4	559.3	560.2	560.3	559.7	559.2	558.6	558.0	558.3
117.5°	635.8	636.3	636.9	637.5	638.1	638.0	637.2	636.5	635.7	635.0	634.9
120°	685.0	686.7	688.5	690.2	692.0	692.2	690.6	689.2	687.8	686.3	686.0
122.5°	736.4	737.6	738.9	740.2	741.4	741.7	740.9	740.2	739.4	738.7	737.9
125°	814.7	815.6	816.4	817.3	818.2	818.3	817.7	817.2	816.6	816.0	814.9
127.5°	887.0	888.9	890.7	892.5	894.4	895.0	894.4	893.7	893.1	892.5	890.8
130°	935.1	937.5	939.9	942.2	944.5	945.2	944.3	943.5	942.6	941.7	940.6
132.5°	983.4	985.7	988.1	990.4	992.7	993.5	992.9	992.3	991.6	991.0	989.6
135°	1057.0	1058.7	1060.5	1062.2	1064.0	1064.7	1064.4	1064.1	1063.8	1063.5	1062.4
137.5°	1125.1	1126.5	1128.0	1129.4	1130.9	1132.1	1132.8	1133.6	1134.3	1135.1	1133.8
140°	1172.3	1173.7	1175.2	1176.6	1178.1	1178.9	1179.2	1179.5	1179.8	1180.1	1179.8
142.5°	1215.2	1216.7	1218.1	1219.6	1221.0	1222.0	1222.5	1223.0	1223.6	1224.2	1223.9
145°	1282.2	1282.8	1283.4	1284.0	1284.5	1285.4	1286.2	1287.1	1288.0	1288.8	1288.5
147.5°	1340.9	1342.0	1343.0	1344.1	1345.1	1346.0	1346.9	1347.7	1348.5	1349.3	1349.3
150°	1381.8	1382.4	1383.0	1383.5	1384.1	1384.7	1385.3	1385.8	1386.4	1387.0	1387.0
152.5°	1415.3	1416.1	1416.9	1417.7	1418.6	1419.2	1419.6	1419.9	1420.3	1420.6	1421.1
155°	1468.2	1468.2	1468.2	1468.2	1468.2	1468.4	1468.6	1468.9	1469.3	1469.6	1470.8
157.5°	1513.3	1513.0	1512.6	1512.3	1511.9	1511.9	1512.1	1512.3	1512.6	1512.8	1514.0
160°	1541.6	1541.1	1540.4	1539.8	1539.2	1538.9	1538.9	1538.9	1538.9	1538.9	1540.4
162.5°	1566.7	1565.9	1565.1	1564.3	1563.5	1563.2	1563.5	1563.7	1563.9	1564.1	1565.6
165°	1599.2	1598.3	1597.5	1596.6	1595.8	1595.3	1595.3	1595.3	1595.3	1595.3	1597.0
167.5°	1625.2	1624.0	1622.9	1621.6	1620.5	1620.0	1620.2	1620.5	1620.7	1620.9	1622.8
170°	1639.8	1638.7	1637.5	1636.4	1635.2	1634.6	1634.6	1634.6	1634.6	1634.6	1636.6
172.5°	1651.3	1650.2	1649.0	1647.9	1646.7	1646.1	1646.1	1646.1	1646.1	1646.1	1647.9
175°	1663.4	1662.2	1661.1	1659.9	1658.7	1658.2	1658.2	1658.2	1658.2	1658.2	1659.9
177.5°	1668.4	1667.5	1666.5	1665.6	1664.7	1664.2	1664.2	1664.2	1664.2	1664.2	1665.6
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4



TEST NUMBER: P332445-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8
2.5°	1298.6	1300.7	1302.7	1303.6	1303.2	1302.8	1302.4	1302.1
5°	1290.0	1292.1	1294.2	1295.1	1294.6	1294.1	1293.6	1293.2
7.5°	1271.9	1273.0	1274.2	1274.4	1273.6	1272.8	1272.0	1271.2
10°	1255.7	1255.9	1256.1	1255.7	1254.5	1253.2	1252.1	1250.9
12.5°	1235.4	1235.3	1235.2	1234.4	1233.0	1231.6	1230.3	1228.9
15°	1199.9	1198.7	1197.6	1196.2	1194.6	1192.9	1191.2	1189.6
17.5°	1157.5	1155.1	1152.6	1150.1	1147.6	1145.2	1142.8	1140.3
20°	1128.5	1125.4	1122.4	1119.4	1116.6	1113.8	1111.0	1108.1
22.5°	1097.4	1093.6	1089.7	1086.5	1083.9	1081.3	1078.6	1076.0
25°	1046.5	1041.6	1036.6	1032.9	1030.3	1027.6	1025.1	1022.5
27.5°	991.0	984.2	977.3	971.9	968.0	964.0	960.1	956.1
30°	951.6	943.5	935.5	929.7	925.9	922.2	918.4	914.6
32.5°	912.8	904.1	895.3	889.0	885.0	881.1	877.2	873.2
35°	855.4	845.3	835.2	828.0	823.7	819.5	815.3	811.0
37.5°	793.6	782.1	770.6	762.3	757.1	751.8	746.7	741.4
40°	750.6	738.4	726.2	717.4	712.0	706.6	701.1	695.8
42.5°	709.4	696.1	682.8	673.7	668.8	664.0	659.1	654.3
45°	648.9	635.5	622.1	612.6	606.9	601.3	595.7	590.1
47.5°	586.2	571.7	557.1	547.3	542.3	537.2	532.3	527.3
50°	544.0	529.4	514.8	504.8	499.5	494.0	488.7	483.2
52.5°	503.1	488.0	472.8	462.8	458.0	453.1	448.3	443.4
55°	442.2	428.6	415.0	405.8	401.1	396.4	391.7	387.0
57.5°	382.4	369.5	356.7	348.2	344.3	340.2	336.2	332.2
60°	344.7	332.0	319.3	311.0	307.0	303.0	299.0	295.0
62.5°	307.3	295.4	283.5	275.4	271.1	267.0	262.9	258.6
65°	254.0	242.5	231.0	223.9	221.4	218.7	216.2	213.6
67.5°	203.2	194.6	185.9	180.3	177.5	174.7	172.0	169.2
70°	171.8	163.5	155.3	150.0	147.3	144.7	142.2	139.6
72.5°	143.5	136.7	130.1	126.1	125.0	124.0	122.9	121.8
75°	107.3	105.0	102.7	101.3	100.8	100.4	99.9	99.4
77.5°	81.0	79.7	78.5	77.6	77.2	76.6	76.1	75.7
80°	65.2	64.5	63.8	63.2	62.7	62.3	61.8	61.3
82.5°	50.0	49.3	48.6	48.2	48.1	48.0	47.9	47.8
85°	28.7	28.2	27.8	27.5	27.5	27.5	27.5	27.5
87.5°	17.4	17.4	17.5	17.5	17.4	17.3	17.3	17.2
90°	33.7	34.9	36.1	37.0	37.6	38.2	38.7	39.3
92.5°	52.1	53.1	54.0	54.3	53.9	53.6	53.2	52.9
95°	99.3	100.4	101.6	102.2	102.2	102.2	102.2	102.2
97.5°	154.3	155.7	157.0	157.6	157.5	157.4	157.3	157.1
100°	194.3	195.1	196.0	196.7	197.3	197.9	198.5	199.0
102.5°	240.3	241.3	242.2	242.5	242.4	242.3	242.2	242.1
105°	309.1	309.1	309.1	309.4	310.0	310.5	311.1	311.7
107.5°	383.5	384.5	385.4	385.7	385.4	385.0	384.7	384.3
110°	433.2	434.4	435.6	435.9	435.3	434.7	434.1	433.5





TEST NUMBER: P332445-840

CATALOG NUMBER: S123RDIW-S775D1320U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	482.9	484.3	485.7	486.4	486.3	486.1	486.0	485.9
115°	558.6	558.9	559.2	559.2	558.9	558.6	558.3	558.0
117.5°	634.9	634.8	634.7	634.3	633.5	632.7	631.9	631.1
120°	685.7	685.5	685.2	684.7	684.2	683.6	683.0	682.4
122.5°	737.2	736.4	735.7	734.9	734.1	733.3	732.5	731.6
125°	813.6	812.5	811.3	810.2	809.0	807.8	806.7	805.5
127.5°	889.2	887.6	886.0	884.4	883.1	881.8	880.5	879.1
130°	939.4	938.3	937.1	935.4	933.4	931.4	929.4	927.4
132.5°	988.2	986.7	985.4	983.9	982.3	980.8	979.2	977.7
135°	1061.2	1060.1	1058.8	1058.0	1057.4	1056.8	1056.2	1055.7
137.5°	1132.6	1131.4	1130.1	1129.0	1127.9	1126.8	1125.7	1124.6
140°	1179.5	1179.2	1178.9	1177.8	1175.8	1173.7	1171.6	1169.6
142.5°	1223.6	1223.2	1222.9	1222.0	1220.4	1218.9	1217.3	1215.8
145°	1288.2	1288.0	1287.7	1287.0	1285.8	1284.5	1283.4	1282.2
147.5°	1349.3	1349.3	1349.3	1348.5	1346.8	1344.9	1343.2	1341.5
150°	1387.0	1387.0	1387.0	1386.1	1384.4	1382.7	1380.9	1379.2
152.5°	1421.5	1422.0	1422.4	1421.9	1420.4	1418.9	1417.3	1415.8
155°	1471.9	1473.1	1474.2	1473.8	1471.8	1469.8	1467.6	1465.6
157.5°	1515.2	1516.4	1517.7	1517.4	1515.8	1514.2	1512.6	1511.0
160°	1541.9	1543.4	1544.8	1545.0	1543.8	1542.7	1541.5	1540.2
162.5°	1567.0	1568.5	1569.9	1569.7	1567.9	1566.0	1564.2	1562.3
165°	1598.8	1600.5	1602.3	1602.2	1600.1	1598.1	1596.0	1594.0
167.5°	1624.6	1626.4	1628.2	1628.2	1626.4	1624.6	1622.8	1620.9
170°	1638.7	1640.7	1642.7	1642.7	1640.7	1638.7	1636.6	1634.6
172.5°	1649.7	1651.5	1653.4	1653.3	1651.2	1649.1	1647.1	1645.1
175°	1661.6	1663.4	1665.2	1665.0	1662.9	1660.9	1658.9	1656.9
177.5°	1667.0	1668.4	1669.8	1669.7	1668.0	1666.4	1664.8	1663.1
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4

(END OF REPORT)