

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332185

Luminaire Tested: **S123DIW-S1000D460U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332185
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D460U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5718.9 lumens
Efficiency: N/A
Efficacy: 123.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332185

CATALOG NUMBER: S123DIW-S1000D460U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332185

CATALOG NUMBER: S123DIW-S1000D460U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76	72
1	103	98	94	90	97	93	90	86	84	81	79	75	73	71	67	66	64	61
2	93	86	79	74	88	81	76	71	73	69	65	66	63	59	59	57	54	51
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	53	49	46	43
4	78	67	58	52	74	64	56	50	58	52	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	42	37	42	38	35	32
6	66	54	45	39	63	51	43	38	47	40	35	42	37	33	38	34	30	28
7	61	49	40	34	58	46	39	33	42	36	31	39	33	29	35	31	27	25
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	22
9	53	40	33	27	50	39	32	27	36	29	25	33	27	24	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17038	17038	17038
5°	17117	16883	17001
10°	17004	16736	16840
15°	16805	16547	16577
20°	16573	16276	16292
25°	16262	15954	15922
30°	15918	15597	15478
35°	15559	15219	15023
40°	15185	14802	14573
45°	14772	14420	14067
50°	14359	13949	13561
55°	13818	13461	13052
60°	13272	12893	12482
65°	12791	12271	11889
70°	12079	11566	11050
75°	11038	10643	10189
80°	9955	9534	9447
85°	8744	8410	8065



TEST NUMBER: P332185

CATALOG NUMBER: S123DIW-S1000D460U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.1	2.6
10°-20°	421.0	7.4
20°-30°	621.9	10.9
30°-40°	726.5	12.7
40°-50°	730.4	12.8
50°-60°	641.5	11.2
60°-70°	478.0	8.4
70°-80°	272.3	4.8
80°-90°	79.9	1.4
90°-100°	37.6	0.7
100°-110°	112.5	2.0
110°-120°	191.3	3.3
120°-130°	251.7	4.4
130°-140°	282.9	4.9
140°-150°	278.0	4.9
150°-160°	234.1	4.1
160°-170°	155.8	2.7
170°-180°	54.6	1.0
0°-30°	1192.0	20.8
0°-40°	1918.5	33.5
0°-60°	3290.4	57.5
0°-90°	4120.5	72.1
90°-120°	341.4	6.0
90°-150°	1153.9	20.2
90°-180°	1598.0	27.9
0°-180°	5718.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1583	1583	1583	1583	1583	
5°	1584	1577	1562	1575	1573	150
15°	1508	1502	1485	1495	1488	425
25°	1369	1360	1343	1344	1341	630
35°	1184	1175	1158	1150	1143	740
45°	970	964	947	932	924	749
55°	736	734	717	703	696	659
65°	502	495	482	471	467	495
75°	265	260	256	249	245	284
85°	71	68	68	65	65	78
90°	0	5	11	13	14	6
95°	27	30	34	35	35	30
105°	102	103	107	107	108	109
115°	193	194	193	194	193	191
125°	282	283	282	280	279	251
135°	366	368	368	366	365	282
145°	444	445	446	445	444	277
155°	508	508	508	510	507	234
165°	553	552	552	554	552	156
175°	576	574	574	576	573	55
180°	577	577	577	577	577	



TEST NUMBER: P332185

CATALOG NUMBER: S123DIW-S1000D460U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9
2.5°	1588.3	1587.4	1586.4	1585.4	1584.5	1582.6	1580.0	1577.3	1574.7	1572.0	1574.4
5°	1584.2	1582.7	1581.2	1579.7	1578.2	1575.8	1572.5	1569.1	1565.8	1562.5	1565.5
7.5°	1568.7	1567.2	1565.7	1564.2	1562.7	1560.2	1556.8	1553.3	1549.9	1546.4	1549.1
10°	1555.7	1554.2	1552.6	1551.1	1549.6	1546.9	1543.0	1539.0	1535.1	1531.2	1533.9
12.5°	1538.2	1537.0	1535.7	1534.4	1533.2	1530.7	1527.0	1523.3	1519.6	1515.9	1517.9
15°	1508.0	1506.8	1505.6	1504.4	1503.2	1500.6	1496.7	1492.8	1488.8	1484.9	1487.3
17.5°	1472.9	1471.3	1469.8	1468.2	1466.6	1463.9	1459.9	1456.0	1452.1	1448.1	1449.8
20°	1446.8	1445.0	1443.2	1441.3	1439.5	1436.6	1432.7	1428.8	1424.9	1420.9	1422.1
22.5°	1417.4	1415.6	1413.8	1411.9	1410.1	1407.3	1403.3	1399.4	1395.5	1391.5	1392.5
25°	1369.2	1367.4	1365.6	1363.8	1361.9	1359.1	1355.1	1351.2	1347.3	1343.3	1343.6
27.5°	1317.8	1316.0	1314.2	1312.5	1310.7	1307.7	1303.5	1299.3	1295.0	1290.8	1291.0
30°	1280.7	1279.2	1277.7	1276.2	1274.7	1271.8	1267.6	1263.3	1259.1	1254.9	1254.9
32.5°	1243.7	1241.7	1239.7	1237.7	1235.7	1233.1	1229.8	1226.6	1223.3	1220.0	1218.3
35°	1184.1	1182.3	1180.5	1178.7	1176.8	1174.0	1170.0	1166.1	1162.2	1158.2	1156.4
37.5°	1123.1	1120.8	1118.5	1116.2	1113.9	1110.8	1106.8	1102.8	1098.8	1094.8	1092.6
40°	1080.7	1078.8	1077.0	1075.2	1073.4	1070.4	1066.1	1061.9	1057.7	1053.4	1051.0
42.5°	1038.2	1036.1	1034.1	1032.0	1030.0	1026.8	1022.6	1018.4	1014.1	1009.9	1007.5
45°	970.4	969.2	968.0	966.8	965.6	963.0	959.1	955.1	951.2	947.3	943.7
47.5°	903.2	901.4	899.7	897.9	896.2	893.4	889.8	886.1	882.4	878.7	875.1
50°	857.5	855.9	854.4	852.9	851.4	848.7	844.7	840.8	836.9	833.0	829.6
52.5°	809.5	808.5	807.5	806.5	805.4	802.8	798.7	794.5	790.3	786.1	783.3
55°	736.3	736.0	735.7	735.4	735.1	733.0	729.1	725.1	721.2	717.3	713.9
57.5°	666.6	665.6	664.6	663.6	662.5	660.4	657.3	654.1	651.0	647.9	644.9
60°	616.5	616.2	615.9	615.6	615.3	613.4	609.7	606.1	602.5	598.9	596.1
62.5°	571.9	571.1	570.3	569.5	568.8	566.6	562.9	559.3	555.7	552.0	549.3
65°	502.2	500.7	499.2	497.7	496.2	493.9	490.9	487.9	484.8	481.8	479.4
67.5°	428.5	427.1	425.8	424.5	423.1	421.3	419.0	416.7	414.4	412.1	410.0
70°	383.8	382.0	380.2	378.4	376.6	374.7	372.9	371.1	369.3	367.5	365.4
72.5°	337.0	335.7	334.3	333.0	331.7	330.0	327.9	325.9	323.8	321.7	319.9
75°	265.4	264.2	263.0	261.8	260.6	259.5	258.6	257.7	256.8	255.9	254.4
77.5°	202.0	201.3	200.6	200.0	199.3	198.4	197.4	196.3	195.2	194.1	193.1
80°	160.6	159.7	158.8	157.9	157.0	156.2	155.6	155.0	154.4	153.8	153.5
82.5°	120.3	120.1	120.0	119.8	119.6	119.4	119.3	119.2	119.1	119.0	118.4
85°	70.8	70.2	69.6	69.0	68.4	68.1	68.1	68.1	68.1	68.1	67.4
87.5°	28.4	27.9	27.4	26.8	26.3	26.0	26.1	26.1	26.1	26.1	26.0
90°	0.5	1.5	2.5	3.5	4.5	5.6	6.9	8.3	9.6	10.9	11.3
92.5°	11.0	11.7	12.3	13.0	13.7	14.4	15.2	15.9	16.7	17.4	17.7
95°	26.7	27.4	28.1	28.9	29.6	30.3	31.1	31.9	32.7	33.5	33.9
97.5°	47.5	48.0	48.5	49.1	49.6	50.1	50.7	51.3	51.9	52.5	52.9
100°	61.6	62.2	62.8	63.4	64.0	64.6	65.1	65.6	66.1	66.6	66.9
102.5°	77.9	78.3	78.7	79.0	79.4	79.9	80.6	81.2	81.9	82.6	82.9
105°	102.0	102.2	102.4	102.6	102.8	103.3	104.2	105.1	106.0	106.9	106.9
107.5°	129.9	130.0	130.1	130.2	130.4	130.6	131.0	131.3	131.7	132.1	132.4
110°	147.3	147.5	147.7	147.9	148.1	148.3	148.5	148.7	148.9	149.1	149.5



TEST NUMBER: P332185

CATALOG NUMBER: S123DIW-S1000D460U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	165.4	165.5	165.7	165.8	165.9	166.0	166.0	166.1	166.1	166.1	166.6
115°	192.6	192.9	193.2	193.5	193.8	193.9	193.7	193.5	193.3	193.1	193.2
117.5°	220.0	220.2	220.4	220.6	220.8	220.7	220.5	220.2	220.0	219.7	219.7
120°	237.0	237.6	238.2	238.8	239.4	239.5	239.0	238.5	238.0	237.5	237.4
122.5°	254.8	255.2	255.7	256.1	256.5	256.6	256.4	256.1	255.9	255.6	255.3
125°	281.9	282.2	282.5	282.8	283.1	283.1	282.9	282.7	282.5	282.3	281.9
127.5°	306.9	307.5	308.2	308.8	309.5	309.7	309.5	309.2	309.0	308.8	308.2
130°	323.6	324.4	325.2	326.0	326.8	327.0	326.7	326.4	326.1	325.8	325.4
132.5°	340.2	341.0	341.9	342.7	343.5	343.8	343.5	343.3	343.1	342.9	342.4
135°	365.7	366.3	366.9	367.5	368.1	368.4	368.3	368.2	368.1	368.0	367.6
137.5°	389.3	389.8	390.3	390.8	391.3	391.7	391.9	392.2	392.5	392.7	392.3
140°	405.6	406.1	406.6	407.1	407.6	407.9	408.0	408.1	408.2	408.3	408.2
142.5°	420.5	421.0	421.5	422.0	422.5	422.8	423.0	423.2	423.4	423.5	423.4
145°	443.7	443.9	444.1	444.3	444.5	444.7	445.0	445.3	445.6	445.9	445.8
147.5°	464.0	464.3	464.7	465.0	465.4	465.7	466.0	466.3	466.6	466.9	466.9
150°	478.1	478.3	478.5	478.7	478.9	479.1	479.3	479.5	479.7	479.9	479.9
152.5°	489.7	490.0	490.3	490.5	490.8	491.0	491.1	491.3	491.4	491.5	491.7
155°	508.0	508.0	508.0	508.0	508.0	508.1	508.2	508.3	508.4	508.5	508.9
157.5°	523.6	523.5	523.4	523.2	523.1	523.1	523.2	523.3	523.3	523.4	523.8
160°	533.4	533.2	533.0	532.8	532.6	532.5	532.5	532.5	532.5	532.5	533.0
162.5°	542.1	541.8	541.5	541.2	541.0	540.9	540.9	541.0	541.1	541.2	541.7
165°	553.3	553.0	552.7	552.4	552.1	552.0	552.0	552.0	552.0	552.0	552.6
167.5°	562.3	561.9	561.5	561.1	560.7	560.5	560.6	560.7	560.8	560.8	561.5
170°	567.4	567.0	566.6	566.2	565.8	565.6	565.6	565.6	565.6	565.6	566.3
172.5°	571.4	571.0	570.6	570.2	569.7	569.5	569.5	569.5	569.5	569.5	570.2
175°	575.5	575.1	574.7	574.3	573.9	573.7	573.7	573.7	573.7	573.7	574.3
177.5°	577.3	576.9	576.6	576.3	576.0	575.8	575.8	575.8	575.8	575.8	576.3
180°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9



TEST NUMBER: P332185

CATALOG NUMBER: S123DIW-S1000D460U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9
2.5°	1576.8	1579.3	1581.7	1582.8	1582.5	1582.3	1582.0	1581.8
5°	1568.5	1571.5	1574.6	1575.8	1575.2	1574.6	1574.0	1573.4
7.5°	1551.9	1554.6	1557.3	1558.5	1558.1	1557.8	1557.4	1557.0
10°	1536.6	1539.3	1542.1	1543.1	1542.5	1541.9	1541.3	1540.7
12.5°	1519.9	1521.9	1523.9	1524.7	1524.4	1524.0	1523.6	1523.3
15°	1489.7	1492.1	1494.6	1494.9	1493.1	1491.2	1489.4	1487.6
17.5°	1451.5	1453.2	1454.9	1455.4	1454.8	1454.1	1453.4	1452.8
20°	1423.3	1424.6	1425.8	1425.9	1425.0	1424.1	1423.2	1422.3
22.5°	1393.5	1394.4	1395.4	1395.3	1394.2	1393.0	1391.9	1390.7
25°	1343.9	1344.3	1344.6	1344.3	1343.3	1342.4	1341.5	1340.6
27.5°	1291.3	1291.5	1291.8	1291.3	1290.2	1289.0	1287.9	1286.7
30°	1254.9	1254.9	1254.9	1253.8	1251.7	1249.6	1247.5	1245.3
32.5°	1216.6	1215.0	1213.3	1211.8	1210.7	1209.5	1208.4	1207.2
35°	1154.6	1152.8	1151.0	1149.3	1147.8	1146.3	1144.8	1143.3
37.5°	1090.5	1088.3	1086.1	1084.5	1083.6	1082.6	1081.6	1080.7
40°	1048.6	1046.2	1043.8	1041.9	1040.7	1039.5	1038.3	1037.1
42.5°	1005.0	1002.6	1000.2	998.4	997.2	996.0	994.8	993.6
45°	940.0	936.4	932.8	930.2	928.7	927.2	925.7	924.1
47.5°	871.5	868.0	864.4	862.0	860.6	859.3	858.0	856.6
50°	826.3	823.0	819.6	817.1	815.3	813.4	811.6	809.8
52.5°	780.4	777.6	774.8	772.4	770.6	768.8	767.0	765.2
55°	710.6	707.3	704.0	701.5	700.0	698.5	697.0	695.5
57.5°	641.9	639.0	636.0	633.6	631.9	630.1	628.4	626.6
60°	593.4	590.7	588.0	585.9	584.3	582.8	581.3	579.8
62.5°	546.6	543.9	541.1	539.3	538.2	537.2	536.2	535.2
65°	477.0	474.5	472.1	470.5	469.6	468.7	467.7	466.8
67.5°	407.9	405.8	403.7	402.0	400.7	399.4	398.1	396.9
70°	363.2	361.1	359.0	357.2	355.7	354.2	352.7	351.1
72.5°	318.0	316.1	314.2	312.9	312.1	311.3	310.6	309.8
75°	252.9	251.3	249.8	248.6	247.7	246.8	245.9	245.0
77.5°	192.0	191.0	190.0	189.5	189.5	189.5	189.5	189.5
80°	153.2	152.9	152.6	152.4	152.4	152.4	152.4	152.4
82.5°	117.9	117.3	116.8	116.4	116.1	115.9	115.7	115.4
85°	66.8	66.2	65.6	65.3	65.3	65.3	65.3	65.3
87.5°	25.8	25.6	25.5	25.4	25.5	25.5	25.5	25.6
90°	11.7	12.1	12.5	12.8	13.0	13.2	13.4	13.6
92.5°	18.0	18.4	18.7	18.8	18.7	18.5	18.4	18.3
95°	34.3	34.7	35.1	35.3	35.3	35.3	35.3	35.3
97.5°	53.4	53.9	54.3	54.5	54.5	54.5	54.4	54.4
100°	67.2	67.5	67.8	68.1	68.3	68.5	68.7	68.9
102.5°	83.2	83.5	83.8	83.9	83.9	83.8	83.8	83.7
105°	106.9	106.9	106.9	107.0	107.3	107.5	107.7	107.9
107.5°	132.7	133.0	133.3	133.4	133.3	133.2	133.1	133.0
110°	149.9	150.3	150.7	150.8	150.6	150.4	150.2	150.0



TEST NUMBER: P332185

CATALOG NUMBER: S123DIW-S1000D460U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	167.1	167.6	168.1	168.3	168.2	168.2	168.2	168.1
115°	193.3	193.4	193.5	193.5	193.4	193.3	193.2	193.1
117.5°	219.7	219.6	219.6	219.5	219.2	218.9	218.6	218.3
120°	237.3	237.2	237.1	236.9	236.7	236.5	236.3	236.1
122.5°	255.1	254.8	254.5	254.3	254.0	253.7	253.4	253.1
125°	281.5	281.1	280.7	280.3	279.9	279.5	279.1	278.7
127.5°	307.7	307.1	306.5	306.0	305.6	305.1	304.6	304.2
130°	325.0	324.6	324.2	323.7	323.0	322.3	321.6	320.8
132.5°	341.9	341.4	340.9	340.4	339.9	339.3	338.8	338.2
135°	367.2	366.8	366.4	366.1	365.9	365.7	365.5	365.3
137.5°	391.9	391.5	391.0	390.6	390.2	389.9	389.5	389.1
140°	408.1	408.0	407.9	407.5	406.8	406.1	405.4	404.7
142.5°	423.3	423.2	423.1	422.8	422.3	421.7	421.2	420.6
145°	445.7	445.6	445.5	445.3	444.9	444.5	444.1	443.7
147.5°	466.9	466.9	466.9	466.6	466.0	465.3	464.7	464.1
150°	479.9	479.9	479.9	479.6	479.0	478.4	477.8	477.2
152.5°	491.8	492.0	492.2	492.0	491.5	490.9	490.4	489.9
155°	509.3	509.7	510.1	509.9	509.2	508.5	507.8	507.1
157.5°	524.3	524.7	525.1	525.0	524.5	523.9	523.3	522.8
160°	533.5	534.0	534.5	534.5	534.1	533.7	533.3	532.9
162.5°	542.2	542.7	543.2	543.1	542.5	541.8	541.2	540.5
165°	553.2	553.8	554.4	554.3	553.6	552.9	552.2	551.5
167.5°	562.1	562.7	563.3	563.3	562.7	562.1	561.5	560.8
170°	567.0	567.7	568.4	568.4	567.7	567.0	566.3	565.6
172.5°	570.8	571.4	572.0	572.0	571.3	570.6	569.9	569.2
175°	574.9	575.5	576.1	576.1	575.4	574.7	574.0	573.3
177.5°	576.8	577.3	577.7	577.7	577.1	576.6	576.0	575.4
180°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9

(END OF REPORT)