

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332233

Luminaire Tested: **S123DIW-S1165D1320U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332233
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D1320U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9336.3 lumens
Efficiency: N/A
Efficacy: 122.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332233

CATALOG NUMBER: S123DIW-S1165D1320U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332233

CATALOG NUMBER: S123DIW-S1165D1320U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	73	71	69	61	60	58	50	49	48	43
2	89	82	75	70	82	76	70	66	64	60	57	54	51	48	44	42	40	36
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	34	30
4	74	63	56	49	68	59	52	46	50	45	41	42	38	35	35	32	30	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	32	28	26	23
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23	20
7	58	46	38	32	54	43	36	30	37	31	27	31	27	24	26	23	20	18
8	54	42	34	28	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19678	19678	19678
5°	19770	19498	19634
10°	19638	19329	19449
15°	19409	19110	19146
20°	19140	18798	18816
25°	18781	18427	18389
30°	18385	18013	17877
35°	17971	17578	17350
40°	17537	17096	16831
45°	17061	16653	16247
50°	16583	16109	15662
55°	15959	15546	15073
60°	15330	14889	14415
65°	14772	14174	13733
70°	13951	13357	12765
75°	12747	12289	11765
80°	11499	11009	10916
85°	10090	9707	9324



TEST NUMBER: P332233

CATALOG NUMBER: S123DIW-S1165D1320U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.2	1.8
10°-20°	486.2	5.2
20°-30°	718.3	7.7
30°-40°	839.0	9.0
40°-50°	843.5	9.0
50°-60°	740.9	7.9
60°-70°	552.0	5.9
70°-80°	314.5	3.4
80°-90°	95.2	1.0
90°-100°	107.6	1.2
100°-110°	321.9	3.4
110°-120°	547.5	5.9
120°-130°	720.2	7.7
130°-140°	809.5	8.7
140°-150°	795.7	8.5
150°-160°	669.9	7.2
160°-170°	445.9	4.8
170°-180°	156.2	1.7
0°-30°	1376.7	14.7
0°-40°	2215.7	23.7
0°-60°	3800.2	40.7
0°-90°	4761.8	51.0
90°-120°	977.1	10.5
90°-150°	3302.5	35.4
90°-180°	4574.0	49.0
0°-180°	9336.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1828	1828	1828	1828	1828	
5°	1830	1821	1804	1819	1817	173
15°	1742	1735	1715	1726	1718	491
25°	1581	1571	1552	1553	1548	728
35°	1368	1358	1338	1328	1320	855
45°	1121	1114	1094	1076	1067	865
55°	850	848	828	812	803	761
65°	580	572	556	544	539	572
75°	306	300	296	288	283	328
85°	82	79	79	76	76	90
90°	1	14	31	36	39	9
95°	76	86	96	101	101	86
105°	292	295	306	306	309	313
115°	551	555	552	554	552	545
125°	807	810	808	803	798	719
135°	1047	1054	1053	1048	1045	806
145°	1270	1272	1276	1275	1270	793
155°	1454	1454	1455	1460	1451	669
165°	1584	1580	1580	1587	1578	446
175°	1647	1642	1642	1649	1641	156
180°	1651	1651	1651	1651	1651	



TEST NUMBER: P332233

CATALOG NUMBER: S123DIW-S1165D1320U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1834.4	1833.3	1832.2	1831.1	1829.9	1827.8	1824.8	1821.7	1818.6	1815.5	1818.3
5°	1829.7	1828.0	1826.2	1824.5	1822.7	1819.9	1816.1	1812.2	1808.4	1804.5	1808.0
7.5°	1811.8	1810.0	1808.3	1806.5	1804.8	1801.9	1797.9	1794.0	1790.0	1786.0	1789.1
10°	1796.7	1794.9	1793.2	1791.4	1789.7	1786.6	1782.0	1777.5	1772.9	1768.4	1771.5
12.5°	1776.6	1775.1	1773.6	1772.2	1770.7	1767.8	1763.6	1759.3	1755.0	1750.8	1753.1
15°	1741.7	1740.3	1738.9	1737.5	1736.1	1733.1	1728.6	1724.0	1719.5	1714.9	1717.7
17.5°	1701.1	1699.3	1697.5	1695.7	1693.8	1690.7	1686.1	1681.6	1677.0	1672.5	1674.5
20°	1670.9	1668.8	1666.7	1664.6	1662.6	1659.2	1654.7	1650.2	1645.6	1641.1	1642.5
22.5°	1637.0	1634.9	1632.8	1630.7	1628.6	1625.3	1620.7	1616.2	1611.7	1607.1	1608.2
25°	1581.3	1579.2	1577.1	1575.0	1573.0	1569.6	1565.1	1560.6	1556.0	1551.5	1551.8
27.5°	1521.9	1519.9	1517.9	1515.8	1513.8	1510.4	1505.5	1500.6	1495.7	1490.8	1491.1
30°	1479.2	1477.4	1475.7	1473.9	1472.2	1468.9	1464.0	1459.1	1454.2	1449.3	1449.3
32.5°	1436.4	1434.1	1431.8	1429.5	1427.2	1424.1	1420.4	1416.6	1412.8	1409.1	1407.1
35°	1367.6	1365.5	1363.4	1361.3	1359.2	1355.9	1351.3	1346.8	1342.2	1337.7	1335.6
37.5°	1297.1	1294.5	1291.8	1289.2	1286.5	1282.9	1278.3	1273.7	1269.1	1264.4	1261.9
40°	1248.1	1246.0	1243.9	1241.8	1239.7	1236.2	1231.3	1226.4	1221.5	1216.7	1213.9
42.5°	1199.0	1196.7	1194.3	1191.9	1189.5	1185.9	1181.0	1176.1	1171.2	1166.4	1163.6
45°	1120.8	1119.4	1118.0	1116.6	1115.2	1112.2	1107.7	1103.1	1098.6	1094.0	1089.9
47.5°	1043.1	1041.1	1039.1	1037.0	1035.0	1031.9	1027.6	1023.3	1019.1	1014.8	1010.7
50°	990.3	988.6	986.8	985.1	983.3	980.2	975.6	971.1	966.5	962.0	958.2
52.5°	935.0	933.8	932.6	931.4	930.2	927.2	922.4	917.6	912.8	907.9	904.6
55°	850.4	850.1	849.7	849.4	849.0	846.6	842.0	837.5	832.9	828.4	824.6
57.5°	769.9	768.7	767.5	766.4	765.2	762.8	759.1	755.5	751.9	748.2	744.8
60°	712.1	711.7	711.4	711.0	710.7	708.4	704.2	700.0	695.8	691.6	688.5
62.5°	660.5	659.6	658.7	657.8	656.9	654.3	650.1	645.9	641.8	637.6	634.4
65°	580.0	578.3	576.5	574.8	573.0	570.4	566.9	563.4	559.9	556.5	553.7
67.5°	494.8	493.3	491.8	490.2	488.7	486.6	483.9	481.3	478.6	476.0	473.5
70°	443.3	441.2	439.1	437.0	434.9	432.8	430.7	428.6	426.5	424.4	422.0
72.5°	389.2	387.7	386.1	384.6	383.1	381.1	378.7	376.3	374.0	371.6	369.4
75°	306.5	305.1	303.7	302.3	300.9	299.7	298.7	297.6	296.6	295.5	293.8
77.5°	233.3	232.5	231.7	231.0	230.2	229.2	227.9	226.7	225.4	224.2	223.0
80°	185.5	184.4	183.4	182.3	181.3	180.4	179.7	179.0	178.3	177.6	177.3
82.5°	139.0	138.7	138.5	138.3	138.1	137.9	137.8	137.7	137.5	137.4	136.8
85°	81.7	81.0	80.3	79.6	78.9	78.6	78.6	78.6	78.6	78.6	77.9
87.5°	33.0	32.7	32.4	32.2	31.9	32.0	32.5	33.0	33.4	33.9	33.8
90°	1.3	4.2	7.1	9.9	12.8	16.1	19.9	23.6	27.4	31.1	32.3
92.5°	31.4	33.3	35.3	37.3	39.2	41.3	43.4	45.5	47.7	49.8	50.7
95°	76.5	78.5	80.6	82.6	84.6	86.8	89.1	91.4	93.7	96.0	97.1
97.5°	135.9	137.4	138.9	140.4	141.9	143.5	145.2	146.8	148.5	150.2	151.5
100°	176.4	178.1	179.8	181.6	183.3	184.9	186.3	187.8	189.2	190.7	191.5
102.5°	223.1	224.1	225.2	226.2	227.2	228.7	230.6	232.5	234.4	236.3	237.2
105°	291.8	292.4	293.0	293.5	294.1	295.7	298.3	300.9	303.5	306.1	306.1
107.5°	371.7	372.1	372.4	372.8	373.1	373.8	374.8	375.9	376.9	377.9	378.9
110°	421.5	422.1	422.7	423.2	423.8	424.4	425.0	425.6	426.1	426.7	427.9



TEST NUMBER: P332233

CATALOG NUMBER: S123DIW-S1165D1320U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	473.4	473.7	474.1	474.4	474.8	475.0	475.1	475.2	475.4	475.5	476.9
115°	551.2	552.1	552.9	553.8	554.7	554.8	554.2	553.7	553.1	552.5	552.8
117.5°	629.6	630.1	630.7	631.3	631.9	631.8	631.0	630.3	629.5	628.8	628.7
120°	678.3	680.0	681.8	683.5	685.2	685.4	683.9	682.5	681.1	679.6	679.3
122.5°	729.2	730.4	731.7	733.0	734.2	734.5	733.7	733.0	732.2	731.5	730.7
125°	806.7	807.6	808.4	809.3	810.2	810.3	809.7	809.2	808.6	808.0	806.9
127.5°	878.3	880.2	882.0	883.8	885.7	886.3	885.7	885.0	884.4	883.8	882.1
130°	926.0	928.3	930.7	933.0	935.3	936.0	935.1	934.3	933.4	932.5	931.4
132.5°	973.8	976.1	978.4	980.7	983.0	983.8	983.2	982.6	981.9	981.3	979.9
135°	1046.7	1048.4	1050.1	1051.8	1053.6	1054.3	1054.0	1053.7	1053.4	1053.1	1052.0
137.5°	1114.1	1115.5	1117.0	1118.4	1119.9	1121.0	1121.7	1122.5	1123.2	1124.0	1122.7
140°	1160.8	1162.2	1163.7	1165.1	1166.6	1167.4	1167.7	1168.0	1168.3	1168.6	1168.3
142.5°	1203.3	1204.8	1206.2	1207.7	1209.1	1210.1	1210.6	1211.1	1211.6	1212.2	1211.9
145°	1269.7	1270.3	1270.9	1271.5	1272.0	1272.8	1273.6	1274.5	1275.4	1276.2	1275.9
147.5°	1327.8	1328.9	1329.9	1331.0	1332.0	1332.9	1333.7	1334.5	1335.3	1336.1	1336.1
150°	1368.3	1368.9	1369.5	1370.0	1370.6	1371.2	1371.8	1372.3	1372.9	1373.5	1373.5
152.5°	1401.5	1402.3	1403.1	1403.9	1404.7	1405.3	1405.7	1406.0	1406.4	1406.7	1407.2
155°	1453.9	1453.9	1453.9	1453.9	1453.9	1454.1	1454.3	1454.6	1454.9	1455.2	1456.4
157.5°	1498.5	1498.2	1497.8	1497.5	1497.1	1497.1	1497.3	1497.5	1497.8	1498.0	1499.2
160°	1526.5	1526.0	1525.4	1524.8	1524.2	1523.9	1523.9	1523.9	1523.9	1523.9	1525.4
162.5°	1551.4	1550.6	1549.8	1549.0	1548.2	1547.9	1548.2	1548.4	1548.6	1548.8	1550.3
165°	1583.6	1582.7	1581.9	1581.0	1580.2	1579.7	1579.7	1579.7	1579.7	1579.7	1581.4
167.5°	1609.3	1608.1	1607.0	1605.8	1604.7	1604.2	1604.4	1604.7	1604.9	1605.1	1606.9
170°	1623.8	1622.7	1621.5	1620.4	1619.2	1618.6	1618.6	1618.6	1618.6	1618.6	1620.6
172.5°	1635.2	1634.1	1632.9	1631.8	1630.6	1630.0	1630.0	1630.0	1630.0	1630.0	1631.8
175°	1647.2	1646.0	1644.9	1643.7	1642.5	1642.0	1642.0	1642.0	1642.0	1642.0	1643.7
177.5°	1652.1	1651.2	1650.2	1649.3	1648.4	1647.9	1647.9	1647.9	1647.9	1647.9	1649.3
180°	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1



TEST NUMBER: P332233

CATALOG NUMBER: S123DIW-S1165D1320U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1821.1	1823.9	1826.7	1828.0	1827.7	1827.4	1827.1	1826.9
5°	1811.5	1815.0	1818.5	1819.9	1819.2	1818.5	1817.8	1817.1
7.5°	1792.3	1795.4	1798.6	1799.9	1799.5	1799.1	1798.7	1798.3
10°	1774.7	1777.8	1781.0	1782.2	1781.5	1780.8	1780.1	1779.4
12.5°	1755.4	1757.7	1760.0	1761.0	1760.5	1760.1	1759.7	1759.3
15°	1720.5	1723.3	1726.1	1726.5	1724.4	1722.3	1720.2	1718.1
17.5°	1676.4	1678.4	1680.3	1680.9	1680.2	1679.4	1678.6	1677.9
20°	1643.9	1645.3	1646.7	1646.8	1645.8	1644.7	1643.7	1642.6
22.5°	1609.4	1610.5	1611.6	1611.5	1610.2	1608.8	1607.5	1606.2
25°	1552.2	1552.5	1552.9	1552.5	1551.5	1550.4	1549.4	1548.3
27.5°	1491.4	1491.6	1491.9	1491.4	1490.1	1488.7	1487.4	1486.1
30°	1449.3	1449.3	1449.3	1448.1	1445.6	1443.2	1440.7	1438.3
32.5°	1405.1	1403.2	1401.2	1399.6	1398.3	1396.9	1395.6	1394.3
35°	1333.5	1331.4	1329.3	1327.4	1325.6	1323.9	1322.1	1320.4
37.5°	1259.4	1256.9	1254.4	1252.6	1251.4	1250.3	1249.2	1248.1
40°	1211.1	1208.3	1205.5	1203.4	1202.0	1200.6	1199.2	1197.8
42.5°	1160.8	1158.0	1155.2	1153.1	1151.7	1150.3	1148.9	1147.5
45°	1085.7	1081.5	1077.3	1074.3	1072.6	1070.8	1069.1	1067.3
47.5°	1006.6	1002.5	998.3	995.5	994.0	992.4	990.9	989.4
50°	954.3	950.5	946.6	943.7	941.6	939.5	937.4	935.3
52.5°	901.4	898.1	894.8	892.1	890.0	887.9	885.8	883.7
55°	820.7	816.9	813.0	810.2	808.5	806.7	805.0	803.2
57.5°	741.4	738.0	734.5	731.8	729.8	727.8	725.7	723.7
60°	685.4	682.2	679.1	676.6	674.9	673.1	671.4	669.6
62.5°	631.3	628.1	625.0	622.8	621.6	620.4	619.3	618.1
65°	550.9	548.1	545.3	543.4	542.3	541.3	540.2	539.2
67.5°	471.1	468.6	466.2	464.2	462.8	461.3	459.8	458.4
70°	419.5	417.1	414.6	412.5	410.8	409.0	407.3	405.6
72.5°	367.3	365.1	362.9	361.4	360.5	359.6	358.7	357.8
75°	292.0	290.3	288.5	287.1	286.1	285.0	284.0	282.9
77.5°	221.8	220.6	219.4	218.8	218.8	218.8	218.8	218.8
80°	176.9	176.6	176.2	176.1	176.1	176.1	176.1	176.1
82.5°	136.1	135.5	134.9	134.4	134.1	133.9	133.6	133.3
85°	77.2	76.5	75.8	75.5	75.5	75.5	75.5	75.5
87.5°	33.8	33.7	33.7	33.7	33.8	34.0	34.1	34.2
90°	33.4	34.6	35.7	36.6	37.2	37.8	38.3	38.9
92.5°	51.6	52.6	53.5	53.8	53.4	53.1	52.7	52.4
95°	98.3	99.4	100.6	101.2	101.2	101.2	101.2	101.2
97.5°	152.8	154.2	155.5	156.1	156.0	155.9	155.8	155.6
100°	192.4	193.2	194.1	194.8	195.4	196.0	196.6	197.1
102.5°	238.0	238.9	239.8	240.1	240.0	239.9	239.8	239.7
105°	306.1	306.1	306.1	306.4	307.0	307.5	308.1	308.7
107.5°	379.8	380.7	381.6	381.9	381.6	381.2	380.9	380.5
110°	429.0	430.2	431.3	431.6	431.0	430.5	429.9	429.3



TEST NUMBER: P332233

CATALOG NUMBER: S123DIW-S1165D1320U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	478.2	479.6	481.0	481.6	481.5	481.4	481.3	481.2
115°	553.1	553.4	553.7	553.7	553.4	553.1	552.8	552.5
117.5°	628.7	628.6	628.5	628.1	627.3	626.5	625.7	624.9
120°	679.0	678.8	678.5	678.0	677.5	676.9	676.3	675.7
122.5°	730.0	729.2	728.5	727.7	726.9	726.1	725.3	724.5
125°	805.7	804.6	803.4	802.3	801.1	799.9	798.8	797.6
127.5°	880.5	878.9	877.3	875.8	874.5	873.2	871.9	870.5
130°	930.2	929.1	927.9	926.3	924.3	922.3	920.3	918.3
132.5°	978.5	977.1	975.8	974.3	972.7	971.2	969.6	968.1
135°	1050.8	1049.7	1048.5	1047.7	1047.1	1046.5	1045.9	1045.4
137.5°	1121.5	1120.3	1119.1	1118.0	1116.9	1115.8	1114.7	1113.6
140°	1168.0	1167.7	1167.4	1166.3	1164.3	1162.2	1160.2	1158.2
142.5°	1211.6	1211.3	1211.0	1210.1	1208.5	1207.0	1205.4	1203.9
145°	1275.6	1275.4	1275.1	1274.4	1273.2	1272.0	1270.9	1269.7
147.5°	1336.1	1336.1	1336.1	1335.3	1333.6	1331.8	1330.1	1328.4
150°	1373.5	1373.5	1373.5	1372.6	1370.9	1369.2	1367.4	1365.7
152.5°	1407.6	1408.1	1408.5	1408.0	1406.5	1405.0	1403.5	1402.0
155°	1457.5	1458.7	1459.8	1459.4	1457.4	1455.4	1453.3	1451.3
157.5°	1500.4	1501.6	1502.9	1502.6	1501.0	1499.4	1497.8	1496.2
160°	1526.8	1528.3	1529.7	1529.9	1528.7	1527.6	1526.4	1525.2
162.5°	1551.7	1553.2	1554.6	1554.4	1552.6	1550.7	1548.9	1547.0
165°	1583.2	1584.9	1586.6	1586.5	1584.5	1582.5	1580.4	1578.4
167.5°	1608.7	1610.5	1612.3	1612.3	1610.5	1608.7	1606.9	1605.1
170°	1622.7	1624.7	1626.7	1626.7	1624.7	1622.7	1620.6	1618.6
172.5°	1633.6	1635.4	1637.2	1637.1	1635.1	1633.0	1631.0	1629.0
175°	1645.4	1647.2	1648.9	1648.7	1646.7	1644.7	1642.7	1640.7
177.5°	1650.7	1652.1	1653.5	1653.4	1651.7	1650.1	1648.5	1646.9
180°	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1

(END OF REPORT)