

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332196-940

Luminaire Tested: **S123DIW-S1000D1030U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332196-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D1030U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7352.4 lumens
Efficiency: N/A
Efficacy: 120.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332196-940

CATALOG NUMBER: S123DIW-S1000D1030U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332196-940

CATALOG NUMBER: S123DIW-S1000D1030U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	89	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	44	42	40	35
3	81	72	64	58	75	66	60	55	56	51	47	47	44	41	39	36	34	30
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	32	29	25
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20	17
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18	15
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15193	15193	15193
5°	15263	15055	15159
10°	15162	14924	15017
15°	14985	14755	14782
20°	14778	14513	14528
25°	14500	14226	14197
30°	14194	13908	13801
35°	13875	13571	13397
40°	13541	13198	12995
45°	13172	12858	12543
50°	12804	12439	12092
55°	12322	12003	11639
60°	11834	11496	11130
65°	11405	10942	10603
70°	10770	10313	9854
75°	9844	9491	9087
80°	8877	8498	8424
85°	7793	7497	7188



TEST NUMBER: P332196-940

CATALOG NUMBER: S123DIW-S1000D1030U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.0	1.8
10°-20°	375.4	5.1
20°-30°	554.6	7.5
30°-40°	647.8	8.8
40°-50°	651.3	8.9
50°-60°	572.1	7.8
60°-70°	426.2	5.8
70°-80°	242.8	3.3
80°-90°	73.1	1.0
90°-100°	43.8	0.6
100°-110°	208.9	2.8
110°-120°	501.7	6.8
120°-130°	638.9	8.7
130°-140°	682.7	9.3
140°-150°	638.4	8.7
150°-160°	514.9	7.0
160°-170°	332.3	4.5
170°-180°	114.5	1.6
0°-30°	1062.9	14.5
0°-40°	1710.7	23.3
0°-60°	2934.1	39.9
0°-90°	3676.1	50.0
90°-120°	754.5	10.3
90°-150°	2714.5	36.9
90°-180°	3676.0	50.0
0°-180°	7352.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1412	1412	1412	1412	1412	
5°	1413	1406	1393	1405	1403	134
15°	1345	1339	1324	1333	1326	379
25°	1221	1213	1198	1199	1195	562
35°	1056	1048	1033	1026	1020	660
45°	865	860	845	831	824	668
55°	657	655	640	627	620	588
65°	448	441	430	420	416	442
75°	237	232	228	222	218	253
85°	63	61	61	58	58	69
90°	1	10	22	25	27	6
95°	55	20	28	34	34	68
105°	267	272	196	46	39	283
115°	501	506	514	523	527	494
125°	706	713	716	718	720	630
135°	879	884	888	890	888	676
145°	1014	1020	1022	1024	1024	634
155°	1117	1115	1116	1120	1115	514
165°	1178	1175	1174	1181	1175	333
175°	1206	1201	1202	1208	1201	115
180°	1206	1206	1206	1206	1206	



TEST NUMBER: P332196-940

CATALOG NUMBER: S123DIW-S1000D1030U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1416.3	1415.5	1414.6	1413.7	1412.9	1411.2	1408.9	1406.5	1404.2	1401.8	1403.9
5°	1412.6	1411.3	1410.0	1408.6	1407.3	1405.2	1402.2	1399.2	1396.2	1393.3	1396.0
7.5°	1398.8	1397.5	1396.2	1394.8	1393.5	1391.2	1388.2	1385.1	1382.1	1378.9	1381.3
10°	1387.2	1385.9	1384.5	1383.1	1381.8	1379.4	1375.9	1372.3	1368.9	1365.4	1367.8
12.5°	1371.6	1370.6	1369.4	1368.2	1367.2	1364.9	1361.6	1358.3	1355.0	1351.7	1353.5
15°	1344.7	1343.6	1342.6	1341.5	1340.4	1338.1	1334.6	1331.1	1327.6	1324.1	1326.2
17.5°	1313.4	1312.0	1310.6	1309.2	1307.8	1305.4	1301.8	1298.3	1294.9	1291.3	1292.8
20°	1290.1	1288.5	1286.9	1285.2	1283.6	1281.0	1277.6	1274.1	1270.6	1267.0	1268.1
22.5°	1263.9	1262.3	1260.7	1259.0	1257.4	1254.9	1251.3	1247.9	1244.4	1240.8	1241.7
25°	1220.9	1219.3	1217.7	1216.1	1214.4	1211.9	1208.4	1204.9	1201.4	1197.8	1198.1
27.5°	1175.1	1173.5	1171.9	1170.4	1168.8	1166.1	1162.3	1158.6	1154.8	1151.0	1151.2
30°	1142.0	1140.7	1139.3	1138.0	1136.7	1134.1	1130.3	1126.5	1122.8	1119.0	1119.0
32.5°	1109.0	1107.2	1105.5	1103.7	1101.9	1099.6	1096.6	1093.8	1090.8	1087.9	1086.4
35°	1055.9	1054.3	1052.7	1051.1	1049.4	1046.9	1043.3	1039.8	1036.3	1032.8	1031.2
37.5°	1001.5	999.4	997.4	995.3	993.3	990.5	986.9	983.4	979.8	976.2	974.3
40°	963.7	962.0	960.4	958.8	957.2	954.5	950.7	946.9	943.2	939.3	937.2
42.5°	925.8	923.9	922.1	920.2	918.5	915.6	911.9	908.1	904.3	900.5	898.4
45°	865.3	864.2	863.2	862.1	861.0	858.7	855.2	851.7	848.2	844.7	841.5
47.5°	805.4	803.8	802.3	800.7	799.2	796.7	793.4	790.1	786.8	783.5	780.3
50°	764.6	763.2	761.9	760.5	759.2	756.8	753.2	749.8	746.3	742.8	739.8
52.5°	721.8	720.9	720.1	719.2	718.2	715.9	712.2	708.5	704.7	701.0	698.5
55°	656.6	656.3	656.0	655.8	655.5	653.6	650.1	646.6	643.1	639.6	636.6
57.5°	594.4	593.5	592.6	591.7	590.8	588.9	586.1	583.3	580.5	577.7	575.1
60°	549.7	549.5	549.2	548.9	548.7	547.0	543.7	540.5	537.3	534.0	531.5
62.5°	510.0	509.3	508.5	507.8	507.2	505.2	501.9	498.7	495.5	492.2	489.8
65°	447.8	446.5	445.1	443.8	442.5	440.4	437.7	435.1	432.3	429.6	427.5
67.5°	382.1	380.8	379.7	378.5	377.3	375.7	373.6	371.6	369.5	367.5	365.6
70°	342.2	340.6	339.0	337.4	335.8	334.1	332.5	330.9	329.3	327.7	325.8
72.5°	300.5	299.3	298.1	296.9	295.8	294.3	292.4	290.6	288.7	286.9	285.3
75°	236.7	235.6	234.5	233.4	232.4	231.4	230.6	229.8	229.0	228.2	226.9
77.5°	180.1	179.5	178.9	178.3	177.7	176.9	176.0	175.0	174.1	173.1	172.2
80°	143.2	142.4	141.6	140.8	140.0	139.3	138.8	138.2	137.7	137.1	136.9
82.5°	107.3	107.1	107.0	106.8	106.6	106.5	106.4	106.3	106.2	106.1	105.6
85°	63.1	62.6	62.1	61.5	61.0	60.7	60.7	60.7	60.7	60.7	60.1
87.5°	25.4	25.1	25.0	24.7	24.4	24.4	24.8	25.1	25.3	25.7	25.6
90°	0.9	2.9	4.9	6.9	8.8	11.1	13.7	16.3	18.9	21.5	22.3
92.5°	16.7	16.1	15.5	15.0	14.4	15.2	17.1	19.0	21.0	22.9	24.2
95°	54.7	46.5	38.3	30.1	22.0	19.0	21.2	23.4	25.6	27.7	29.2
97.5°	109.8	106.1	102.5	98.8	95.1	86.1	71.9	57.5	43.2	28.8	30.4
100°	151.3	155.3	159.3	163.3	167.3	153.7	122.7	91.7	60.6	29.5	31.1
102.5°	198.7	201.5	204.4	207.2	210.1	194.6	160.7	126.8	92.8	58.9	54.0
105°	266.9	269.1	271.3	273.5	275.6	267.8	249.9	231.9	214.1	196.2	161.0
107.5°	338.9	340.6	342.4	344.2	345.9	348.2	351.1	353.8	356.7	359.5	333.7
110°	386.9	388.5	390.1	391.7	393.2	395.2	397.3	399.6	401.7	403.9	397.3



TEST NUMBER: P332196-940

CATALOG NUMBER: S123DIW-S1000D1030U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	432.7	434.2	435.6	437.1	438.5	440.3	442.5	444.7	446.9	449.1	449.2
115°	500.7	501.9	503.0	504.3	505.4	506.9	508.7	510.5	512.3	514.1	516.1
117.5°	566.4	567.8	569.4	570.8	572.3	573.5	574.4	575.3	576.2	577.1	578.7
120°	607.3	609.0	610.8	612.6	614.4	615.6	616.2	616.8	617.4	618.0	619.6
122.5°	648.8	650.2	651.8	653.2	654.7	655.8	656.6	657.3	658.1	658.8	660.0
125°	705.8	707.4	708.9	710.5	712.1	713.4	714.1	714.9	715.7	716.5	716.9
127.5°	760.9	762.5	764.1	765.7	767.3	768.6	769.5	770.5	771.4	772.4	773.0
130°	795.3	796.9	798.5	800.1	801.7	802.9	803.7	804.5	805.3	806.1	806.9
132.5°	828.3	829.9	831.4	833.0	834.6	835.8	836.4	837.0	837.7	838.3	839.1
135°	878.6	879.9	881.0	882.2	883.4	884.4	885.2	886.0	886.8	887.6	888.1
137.5°	921.6	923.1	924.6	926.1	927.6	928.6	929.1	929.5	930.0	930.4	931.3
140°	950.3	951.5	952.7	953.9	955.0	955.9	956.5	957.2	957.7	958.3	959.1
142.5°	976.8	977.9	979.2	980.3	981.6	982.5	983.0	983.6	984.3	984.8	985.5
145°	1013.9	1015.2	1016.6	1018.1	1019.4	1020.3	1020.7	1021.1	1021.5	1021.9	1022.3
147.5°	1048.8	1049.7	1050.6	1051.5	1052.5	1053.1	1053.5	1053.9	1054.3	1054.7	1055.1
150°	1070.3	1070.9	1071.5	1072.1	1072.6	1073.2	1073.5	1074.0	1074.3	1074.8	1075.1
152.5°	1089.7	1089.9	1090.2	1090.5	1090.7	1091.0	1091.3	1091.5	1091.7	1092.0	1092.7
155°	1116.9	1116.4	1116.1	1115.7	1115.3	1115.2	1115.4	1115.5	1115.8	1116.0	1117.0
157.5°	1138.0	1138.0	1137.9	1137.9	1137.8	1137.7	1137.6	1137.3	1137.1	1136.9	1138.1
160°	1150.9	1150.7	1150.5	1150.3	1150.1	1149.9	1149.7	1149.5	1149.3	1149.1	1150.3
162.5°	1163.1	1162.5	1162.1	1161.5	1161.0	1160.7	1160.5	1160.3	1160.0	1159.8	1161.2
165°	1177.8	1177.1	1176.6	1176.0	1175.4	1175.0	1174.7	1174.6	1174.4	1174.2	1175.8
167.5°	1189.2	1188.5	1187.7	1186.9	1186.1	1185.6	1185.6	1185.6	1185.6	1185.6	1187.2
170°	1195.7	1194.9	1194.1	1193.3	1192.5	1192.1	1192.1	1192.1	1192.1	1192.1	1193.6
172.5°	1200.0	1199.0	1198.1	1197.1	1196.1	1195.8	1195.9	1196.1	1196.2	1196.4	1198.0
175°	1205.5	1204.5	1203.5	1202.6	1201.6	1201.1	1201.3	1201.6	1201.8	1201.9	1203.4
177.5°	1206.9	1206.1	1205.4	1204.6	1203.8	1203.5	1203.6	1203.8	1203.9	1204.1	1205.4
180°	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5



TEST NUMBER: P332196-940

CATALOG NUMBER: S123DIW-S1000D1030U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1406.0	1408.3	1410.4	1411.4	1411.1	1411.0	1410.7	1410.5
5°	1398.6	1401.3	1404.1	1405.2	1404.6	1404.1	1403.6	1403.0
7.5°	1383.8	1386.3	1388.7	1389.7	1389.4	1389.1	1388.8	1388.4
10°	1370.2	1372.6	1375.1	1376.0	1375.5	1374.9	1374.4	1373.9
12.5°	1355.3	1357.1	1358.9	1359.6	1359.3	1359.0	1358.6	1358.3
15°	1328.4	1330.5	1332.8	1333.0	1331.4	1329.7	1328.1	1326.5
17.5°	1294.3	1295.8	1297.4	1297.8	1297.3	1296.6	1296.0	1295.5
20°	1269.2	1270.3	1271.4	1271.5	1270.7	1269.9	1269.1	1268.3
22.5°	1242.6	1243.4	1244.3	1244.2	1243.2	1242.2	1241.2	1240.1
25°	1198.4	1198.7	1199.0	1198.7	1197.8	1197.0	1196.2	1195.4
27.5°	1151.5	1151.6	1151.9	1151.5	1150.5	1149.4	1148.4	1147.4
30°	1119.0	1119.0	1119.0	1118.0	1116.2	1114.3	1112.4	1110.4
32.5°	1084.9	1083.4	1081.9	1080.6	1079.6	1078.5	1077.5	1076.5
35°	1029.6	1028.0	1026.4	1024.8	1023.5	1022.2	1020.8	1019.5
37.5°	972.4	970.4	968.5	967.1	966.3	965.4	964.5	963.7
40°	935.0	932.9	930.8	929.1	928.0	926.9	925.9	924.8
42.5°	896.2	894.0	891.9	890.3	889.2	888.1	887.1	886.0
45°	838.2	835.0	831.8	829.5	828.1	826.8	825.5	824.0
47.5°	777.1	774.0	770.8	768.7	767.4	766.2	765.1	763.8
50°	736.8	733.9	730.8	728.6	727.0	725.3	723.7	722.1
52.5°	695.9	693.4	690.9	688.8	687.2	685.5	683.9	682.3
55°	633.6	630.7	627.8	625.5	624.2	622.9	621.5	620.2
57.5°	572.4	569.8	567.1	565.0	563.5	561.9	560.4	558.7
60°	529.1	526.7	524.3	522.5	521.0	519.7	518.4	517.0
62.5°	487.4	485.0	482.5	480.9	479.9	479.0	478.1	477.2
65°	425.3	423.1	421.0	419.5	418.7	417.9	417.1	416.3
67.5°	363.7	361.9	360.0	358.5	357.3	356.1	355.0	353.9
70°	323.9	322.0	320.1	318.5	317.2	315.8	314.5	313.1
72.5°	283.6	281.9	280.2	279.0	278.3	277.6	277.0	276.3
75°	225.5	224.1	222.7	221.7	220.9	220.1	219.3	218.5
77.5°	171.2	170.3	169.4	169.0	169.0	169.0	169.0	169.0
80°	136.6	136.3	136.1	135.9	135.9	135.9	135.9	135.9
82.5°	105.1	104.6	104.2	103.8	103.5	103.3	103.2	102.9
85°	59.6	59.0	58.5	58.2	58.2	58.2	58.2	58.2
87.5°	25.5	25.5	25.4	25.4	25.5	25.6	25.7	25.8
90°	23.1	23.9	24.7	25.2	25.7	26.0	26.5	26.8
92.5°	25.5	26.8	28.0	28.8	29.0	29.2	29.5	29.7
95°	30.6	31.9	33.3	34.1	34.1	34.1	34.1	34.1
97.5°	32.0	33.6	35.2	36.1	36.3	36.5	36.7	36.9
100°	32.7	34.3	35.9	36.8	37.0	37.2	37.5	37.6
102.5°	49.0	44.1	39.1	36.9	37.3	37.6	38.0	38.3
105°	125.7	90.4	55.2	37.8	38.3	38.6	39.0	39.4
107.5°	307.8	282.0	256.2	230.0	203.4	176.9	150.3	123.8
110°	390.8	384.2	377.6	360.2	331.7	303.2	274.7	246.3



TEST NUMBER: P332196-940

CATALOG NUMBER: S123DIW-S1000D1030U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	449.3	449.4	449.5	446.6	440.6	434.6	428.6	422.6
115°	518.1	520.0	522.1	523.4	524.2	525.0	525.8	526.6
117.5°	580.3	581.9	583.5	584.4	584.5	584.7	584.9	585.1
120°	621.2	622.8	624.4	625.2	625.2	625.2	625.2	625.2
122.5°	661.0	662.2	663.3	664.0	664.1	664.2	664.4	664.6
125°	717.3	717.7	718.1	718.5	718.9	719.3	719.7	720.1
127.5°	773.6	774.3	775.0	775.1	774.6	774.3	773.9	773.5
130°	807.7	808.4	809.2	809.5	809.0	808.7	808.2	807.9
132.5°	839.9	840.7	841.5	841.6	841.1	840.5	840.0	839.4
135°	888.8	889.4	889.9	889.9	889.4	888.8	888.1	887.6
137.5°	932.3	933.3	934.2	934.5	934.1	933.7	933.3	932.9
140°	959.9	960.7	961.5	961.7	961.4	960.9	960.6	960.1
142.5°	986.1	986.8	987.4	987.4	986.9	986.3	985.8	985.2
145°	1022.7	1023.1	1023.5	1023.7	1023.7	1023.7	1023.7	1023.7
147.5°	1055.5	1055.9	1056.3	1056.1	1055.2	1054.2	1053.3	1052.4
150°	1075.6	1075.9	1076.4	1076.3	1075.7	1075.0	1074.5	1073.9
152.5°	1093.4	1094.1	1094.8	1094.8	1093.8	1092.9	1092.0	1091.1
155°	1117.9	1118.9	1120.0	1119.8	1118.7	1117.5	1116.2	1115.1
157.5°	1139.3	1140.5	1141.7	1141.5	1140.0	1138.4	1136.8	1135.3
160°	1151.5	1152.7	1153.9	1153.8	1152.4	1151.0	1149.6	1148.2
162.5°	1162.5	1164.0	1165.3	1165.3	1164.1	1162.9	1161.6	1160.4
165°	1177.3	1178.9	1180.5	1180.6	1179.3	1177.9	1176.4	1175.1
167.5°	1188.8	1190.4	1192.0	1192.0	1190.4	1188.8	1187.2	1185.6
170°	1195.2	1196.9	1198.5	1198.5	1196.9	1195.2	1193.6	1192.1
172.5°	1199.6	1201.1	1202.7	1202.7	1201.0	1199.2	1197.4	1195.7
175°	1204.7	1206.1	1207.6	1207.5	1205.9	1204.3	1202.7	1201.0
177.5°	1206.7	1207.9	1209.2	1209.1	1207.5	1205.9	1204.3	1202.7
180°	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5

(END OF REPORT)