

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332238

Luminaire Tested: **S123DIW-S1165D1535U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332238
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D1535U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10899.0 lumens
Efficiency: N/A
Efficacy: 131.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332238

CATALOG NUMBER: S123DIW-S1165D1535U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332238

CATALOG NUMBER: S123DIW-S1165D1535U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	96	92	88	85	88	84	81	78	70	68	65	57	55	54	44	43	42	37
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36	31
3	80	71	63	57	73	65	58	53	54	49	45	44	41	38	35	32	30	26
4	73	62	55	49	67	57	50	45	48	43	39	39	35	32	31	28	26	22
5	67	56	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	32	28	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19678	19678	19678
5°	19770	19498	19634
10°	19638	19329	19449
15°	19409	19110	19146
20°	19140	18798	18816
25°	18781	18427	18389
30°	18385	18013	17877
35°	17971	17578	17350
40°	17537	17096	16831
45°	17061	16653	16247
50°	16583	16109	15662
55°	15959	15546	15073
60°	15330	14889	14415
65°	14772	14174	13733
70°	13951	13357	12765
75°	12747	12289	11765
80°	11499	11009	10916
85°	10090	9707	9324



TEST NUMBER: P332238

CATALOG NUMBER: S123DIW-S1165D1535U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.2	1.6
10°-20°	486.2	4.5
20°-30°	718.3	6.6
30°-40°	839.0	7.7
40°-50°	843.5	7.7
50°-60°	740.9	6.8
60°-70°	552.0	5.1
70°-80°	314.5	2.9
80°-90°	95.9	0.9
90°-100°	73.2	0.7
100°-110°	348.7	3.2
110°-120°	837.5	7.7
120°-130°	1066.5	9.8
130°-140°	1139.5	10.5
140°-150°	1065.6	9.8
150°-160°	859.5	7.9
160°-170°	554.7	5.1
170°-180°	191.2	1.8
0°-30°	1376.7	12.6
0°-40°	2215.7	20.3
0°-60°	3800.2	34.9
0°-90°	4762.6	43.7
90°-120°	1259.4	11.6
90°-150°	4531.0	41.6
90°-180°	6136.0	56.3
0°-180°	10899.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1828	1828	1828	1828	1828	
5°	1830	1821	1804	1819	1817	173
15°	1742	1735	1715	1726	1718	491
25°	1581	1571	1552	1553	1548	728
35°	1368	1358	1338	1328	1320	855
45°	1121	1114	1094	1076	1067	865
55°	850	848	828	812	803	761
65°	580	572	556	544	539	572
75°	306	300	296	288	283	328
85°	82	79	79	76	76	90
90°	2	17	36	42	45	9
95°	91	34	46	56	57	113
105°	446	454	327	78	66	472
115°	836	845	858	873	879	825
125°	1178	1190	1196	1199	1202	1052
135°	1467	1475	1482	1486	1482	1129
145°	1692	1702	1706	1709	1709	1059
155°	1864	1862	1863	1869	1861	859
165°	1966	1962	1960	1971	1961	555
175°	2012	2005	2006	2016	2005	191
180°	2012	2012	2012	2012	2012	



TEST NUMBER: P332238

CATALOG NUMBER: S123DIW-S1165D1535U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1834.4	1833.3	1832.2	1831.1	1829.9	1827.8	1824.8	1821.7	1818.6	1815.5	1818.3
5°	1829.7	1828.0	1826.2	1824.5	1822.7	1819.9	1816.1	1812.2	1808.4	1804.5	1808.0
7.5°	1811.8	1810.0	1808.3	1806.5	1804.8	1801.9	1797.9	1794.0	1790.0	1786.0	1789.1
10°	1796.7	1794.9	1793.2	1791.4	1789.7	1786.6	1782.0	1777.5	1772.9	1768.4	1771.5
12.5°	1776.6	1775.1	1773.6	1772.2	1770.7	1767.8	1763.6	1759.3	1755.0	1750.8	1753.1
15°	1741.7	1740.3	1738.9	1737.5	1736.1	1733.1	1728.6	1724.0	1719.5	1714.9	1717.7
17.5°	1701.1	1699.3	1697.5	1695.7	1693.8	1690.7	1686.1	1681.6	1677.0	1672.5	1674.5
20°	1670.9	1668.8	1666.7	1664.6	1662.6	1659.2	1654.7	1650.2	1645.6	1641.1	1642.5
22.5°	1637.0	1634.9	1632.8	1630.7	1628.6	1625.3	1620.7	1616.2	1611.7	1607.1	1608.2
25°	1581.3	1579.2	1577.1	1575.0	1573.0	1569.6	1565.1	1560.6	1556.0	1551.5	1551.8
27.5°	1521.9	1519.9	1517.9	1515.8	1513.8	1510.4	1505.5	1500.6	1495.7	1490.8	1491.1
30°	1479.2	1477.4	1475.7	1473.9	1472.2	1468.9	1464.0	1459.1	1454.2	1449.3	1449.3
32.5°	1436.4	1434.1	1431.8	1429.5	1427.2	1424.1	1420.4	1416.6	1412.8	1409.1	1407.1
35°	1367.6	1365.5	1363.4	1361.3	1359.2	1355.9	1351.3	1346.8	1342.2	1337.7	1335.6
37.5°	1297.1	1294.5	1291.8	1289.2	1286.5	1282.9	1278.3	1273.7	1269.1	1264.4	1261.9
40°	1248.1	1246.0	1243.9	1241.8	1239.7	1236.2	1231.3	1226.4	1221.5	1216.7	1213.9
42.5°	1199.0	1196.7	1194.3	1191.9	1189.5	1185.9	1181.0	1176.1	1171.2	1166.4	1163.6
45°	1120.8	1119.4	1118.0	1116.6	1115.2	1112.2	1107.7	1103.1	1098.6	1094.0	1089.9
47.5°	1043.1	1041.1	1039.1	1037.0	1035.0	1031.9	1027.6	1023.3	1019.1	1014.8	1010.7
50°	990.3	988.6	986.8	985.1	983.3	980.2	975.6	971.1	966.5	962.0	958.2
52.5°	935.0	933.8	932.6	931.4	930.2	927.2	922.4	917.6	912.8	907.9	904.6
55°	850.4	850.1	849.7	849.4	849.0	846.6	842.0	837.5	832.9	828.4	824.6
57.5°	769.9	768.7	767.5	766.4	765.2	762.8	759.1	755.5	751.9	748.2	744.8
60°	712.1	711.7	711.4	711.0	710.7	708.4	704.2	700.0	695.8	691.6	688.5
62.5°	660.5	659.6	658.7	657.8	656.9	654.3	650.1	645.9	641.8	637.6	634.4
65°	580.0	578.3	576.5	574.8	573.0	570.4	566.9	563.4	559.9	556.5	553.7
67.5°	494.8	493.3	491.8	490.2	488.7	486.6	483.9	481.3	478.6	476.0	473.5
70°	443.3	441.2	439.1	437.0	434.9	432.8	430.7	428.6	426.5	424.4	422.0
72.5°	389.2	387.7	386.1	384.6	383.1	381.1	378.7	376.3	374.0	371.6	369.4
75°	306.5	305.1	303.7	302.3	300.9	299.7	298.7	297.6	296.6	295.5	293.8
77.5°	233.3	232.5	231.7	231.0	230.2	229.2	227.9	226.7	225.4	224.2	223.0
80°	185.5	184.4	183.4	182.3	181.3	180.4	179.7	179.0	178.3	177.6	177.3
82.5°	139.0	138.7	138.5	138.3	138.1	137.9	137.8	137.7	137.5	137.4	136.8
85°	81.7	81.0	80.3	79.6	78.9	78.6	78.6	78.6	78.6	78.6	77.9
87.5°	33.0	32.8	32.6	32.5	32.3	32.5	33.1	33.7	34.3	34.8	34.8
90°	1.5	4.8	8.1	11.5	14.8	18.6	22.9	27.2	31.6	35.9	37.2
92.5°	27.8	26.9	25.9	25.0	24.1	25.2	28.5	31.8	35.0	38.3	40.4
95°	91.2	77.6	64.0	50.3	36.7	31.7	35.4	39.0	42.7	46.3	48.7
97.5°	183.3	177.2	171.1	164.9	158.8	143.8	119.9	96.0	72.1	48.1	50.8
100°	252.7	259.3	265.9	272.6	279.2	256.6	204.8	153.0	101.2	49.3	52.0
102.5°	331.6	336.4	341.2	345.9	350.7	324.8	268.2	211.6	155.0	98.4	90.1
105°	445.5	449.2	452.8	456.5	460.1	447.0	417.1	387.2	357.3	327.4	268.6
107.5°	565.7	568.6	571.5	574.5	577.4	581.2	585.9	590.7	595.4	600.1	557.0
110°	645.8	648.5	651.1	653.8	656.5	659.6	663.3	666.9	670.6	674.2	663.3



TEST NUMBER: P332238

CATALOG NUMBER: S123DIW-S1165D1535U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	722.4	724.8	727.2	729.6	731.9	735.0	738.6	742.3	745.9	749.6	749.8
115°	835.7	837.7	839.7	841.7	843.7	846.2	849.2	852.1	855.1	858.1	861.4
117.5°	945.4	947.9	950.3	952.8	955.3	957.3	958.8	960.3	961.8	963.4	966.0
120°	1013.6	1016.6	1019.6	1022.6	1025.6	1027.6	1028.5	1029.5	1030.5	1031.5	1034.2
122.5°	1083.0	1085.4	1087.9	1090.3	1092.8	1094.7	1095.9	1097.2	1098.4	1099.7	1101.6
125°	1178.0	1180.7	1183.4	1186.0	1188.7	1190.7	1192.0	1193.3	1194.7	1196.0	1196.7
127.5°	1270.1	1272.8	1275.5	1278.1	1280.8	1282.9	1284.5	1286.1	1287.7	1289.3	1290.3
130°	1327.5	1330.2	1332.9	1335.5	1338.2	1340.2	1341.5	1342.8	1344.2	1345.5	1346.8
132.5°	1382.6	1385.2	1387.9	1390.5	1393.2	1395.1	1396.1	1397.2	1398.2	1399.3	1400.6
135°	1466.6	1468.6	1470.6	1472.6	1474.6	1476.2	1477.5	1478.9	1480.2	1481.5	1482.5
137.5°	1538.3	1540.9	1543.4	1545.9	1548.4	1550.1	1550.8	1551.5	1552.3	1553.0	1554.6
140°	1586.2	1588.2	1590.2	1592.2	1594.2	1595.6	1596.6	1597.6	1598.6	1599.6	1601.0
142.5°	1630.4	1632.4	1634.4	1636.4	1638.4	1639.9	1640.9	1641.9	1642.9	1643.9	1644.9
145°	1692.3	1694.6	1697.0	1699.3	1701.6	1703.1	1703.8	1704.4	1705.1	1705.8	1706.4
147.5°	1750.6	1752.2	1753.7	1755.2	1756.7	1757.8	1758.5	1759.2	1759.8	1760.5	1761.2
150°	1786.5	1787.5	1788.5	1789.5	1790.5	1791.3	1792.0	1792.7	1793.3	1794.0	1794.6
152.5°	1818.8	1819.3	1819.7	1820.2	1820.7	1821.1	1821.5	1821.9	1822.3	1822.7	1823.9
155°	1864.2	1863.6	1862.9	1862.3	1861.6	1861.4	1861.8	1862.1	1862.4	1862.7	1864.4
157.5°	1899.5	1899.5	1899.4	1899.3	1899.3	1899.1	1898.7	1898.4	1898.1	1897.7	1899.7
160°	1921.1	1920.7	1920.4	1920.1	1919.7	1919.4	1919.1	1918.7	1918.4	1918.1	1920.1
162.5°	1941.4	1940.5	1939.7	1938.8	1937.9	1937.3	1937.0	1936.7	1936.3	1936.0	1938.3
165°	1965.9	1964.9	1963.9	1962.9	1961.9	1961.3	1960.9	1960.6	1960.3	1959.9	1962.6
167.5°	1985.0	1983.7	1982.4	1981.1	1979.7	1979.1	1979.1	1979.1	1979.1	1979.1	1981.7
170°	1995.8	1994.5	1993.1	1991.8	1990.5	1989.8	1989.8	1989.8	1989.8	1989.8	1992.5
172.5°	2003.0	2001.4	1999.8	1998.2	1996.6	1995.9	1996.2	1996.5	1996.7	1997.0	1999.7
175°	2012.2	2010.6	2008.9	2007.3	2005.6	2004.9	2005.3	2005.6	2005.9	2006.3	2008.6
177.5°	2014.6	2013.3	2012.0	2010.7	2009.3	2008.8	2009.1	2009.3	2009.6	2009.9	2012.0
180°	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2



TEST NUMBER: P332238

CATALOG NUMBER: S123DIW-S1165D1535U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1821.1	1823.9	1826.7	1828.0	1827.7	1827.4	1827.1	1826.9
5°	1811.5	1815.0	1818.5	1819.9	1819.2	1818.5	1817.8	1817.1
7.5°	1792.3	1795.4	1798.6	1799.9	1799.5	1799.1	1798.7	1798.3
10°	1774.7	1777.8	1781.0	1782.2	1781.5	1780.8	1780.1	1779.4
12.5°	1755.4	1757.7	1760.0	1761.0	1760.5	1760.1	1759.7	1759.3
15°	1720.5	1723.3	1726.1	1726.5	1724.4	1722.3	1720.2	1718.1
17.5°	1676.4	1678.4	1680.3	1680.9	1680.2	1679.4	1678.6	1677.9
20°	1643.9	1645.3	1646.7	1646.8	1645.8	1644.7	1643.7	1642.6
22.5°	1609.4	1610.5	1611.6	1611.5	1610.2	1608.8	1607.5	1606.2
25°	1552.2	1552.5	1552.9	1552.5	1551.5	1550.4	1549.4	1548.3
27.5°	1491.4	1491.6	1491.9	1491.4	1490.1	1488.7	1487.4	1486.1
30°	1449.3	1449.3	1449.3	1448.1	1445.6	1443.2	1440.7	1438.3
32.5°	1405.1	1403.2	1401.2	1399.6	1398.3	1396.9	1395.6	1394.3
35°	1333.5	1331.4	1329.3	1327.4	1325.6	1323.9	1322.1	1320.4
37.5°	1259.4	1256.9	1254.4	1252.6	1251.4	1250.3	1249.2	1248.1
40°	1211.1	1208.3	1205.5	1203.4	1202.0	1200.6	1199.2	1197.8
42.5°	1160.8	1158.0	1155.2	1153.1	1151.7	1150.3	1148.9	1147.5
45°	1085.7	1081.5	1077.3	1074.3	1072.6	1070.8	1069.1	1067.3
47.5°	1006.6	1002.5	998.3	995.5	994.0	992.4	990.9	989.4
50°	954.3	950.5	946.6	943.7	941.6	939.5	937.4	935.3
52.5°	901.4	898.1	894.8	892.1	890.0	887.9	885.8	883.7
55°	820.7	816.9	813.0	810.2	808.5	806.7	805.0	803.2
57.5°	741.4	738.0	734.5	731.8	729.8	727.8	725.7	723.7
60°	685.4	682.2	679.1	676.6	674.9	673.1	671.4	669.6
62.5°	631.3	628.1	625.0	622.8	621.6	620.4	619.3	618.1
65°	550.9	548.1	545.3	543.4	542.3	541.3	540.2	539.2
67.5°	471.1	468.6	466.2	464.2	462.8	461.3	459.8	458.4
70°	419.5	417.1	414.6	412.5	410.8	409.0	407.3	405.6
72.5°	367.3	365.1	362.9	361.4	360.5	359.6	358.7	357.8
75°	292.0	290.3	288.5	287.1	286.1	285.0	284.0	282.9
77.5°	221.8	220.6	219.4	218.8	218.8	218.8	218.8	218.8
80°	176.9	176.6	176.2	176.1	176.1	176.1	176.1	176.1
82.5°	136.1	135.5	134.9	134.4	134.1	133.9	133.6	133.3
85°	77.2	76.5	75.8	75.5	75.5	75.5	75.5	75.5
87.5°	34.8	34.8	34.8	34.8	35.0	35.1	35.2	35.4
90°	38.5	39.9	41.2	42.2	42.9	43.5	44.2	44.8
92.5°	42.5	44.7	46.8	48.0	48.4	48.8	49.2	49.6
95°	51.0	53.3	55.6	56.8	56.8	56.8	56.8	56.8
97.5°	53.5	56.1	58.8	60.3	60.6	60.9	61.3	61.6
100°	54.6	57.3	60.0	61.5	61.8	62.1	62.5	62.8
102.5°	81.9	73.7	65.4	61.6	62.2	62.8	63.4	64.0
105°	209.8	151.0	92.2	63.1	63.8	64.5	65.1	65.8
107.5°	513.8	470.7	427.6	383.9	339.6	295.2	250.9	206.6
110°	652.3	641.3	630.4	601.1	553.6	506.1	458.6	411.1



TEST NUMBER: P332238

CATALOG NUMBER: S123DIW-S1165D1535U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	750.0	750.2	750.4	745.5	735.4	725.4	715.4	705.3
115°	864.8	868.1	871.4	873.7	875.1	876.4	877.7	879.1
117.5°	968.7	971.3	974.0	975.5	975.7	976.0	976.3	976.5
120°	1036.9	1039.5	1042.2	1043.5	1043.5	1043.5	1043.5	1043.5
122.5°	1103.4	1105.3	1107.2	1108.2	1108.5	1108.7	1109.0	1109.3
125°	1197.3	1198.0	1198.6	1199.3	1200.0	1200.6	1201.3	1202.0
127.5°	1291.4	1292.5	1293.5	1293.7	1293.1	1292.4	1291.7	1291.1
130°	1348.1	1349.5	1350.8	1351.1	1350.5	1349.8	1349.1	1348.5
132.5°	1402.0	1403.3	1404.6	1404.8	1403.9	1403.0	1402.0	1401.1
135°	1483.5	1484.5	1485.5	1485.5	1484.5	1483.5	1482.5	1481.5
137.5°	1556.2	1557.8	1559.4	1559.8	1559.2	1558.5	1557.8	1557.2
140°	1602.3	1603.6	1604.9	1605.3	1604.6	1604.0	1603.3	1602.6
142.5°	1646.0	1647.1	1648.1	1648.2	1647.3	1646.3	1645.4	1644.5
145°	1707.1	1707.8	1708.4	1708.8	1708.8	1708.8	1708.8	1708.8
147.5°	1761.8	1762.5	1763.2	1762.7	1761.2	1759.7	1758.1	1756.6
150°	1795.3	1796.0	1796.6	1796.5	1795.5	1794.5	1793.5	1792.5
152.5°	1825.1	1826.3	1827.5	1827.3	1825.8	1824.2	1822.7	1821.2
155°	1866.1	1867.7	1869.4	1869.2	1867.2	1865.2	1863.2	1861.3
157.5°	1901.7	1903.7	1905.7	1905.4	1902.8	1900.2	1897.6	1895.0
160°	1922.1	1924.0	1926.0	1925.9	1923.5	1921.2	1918.9	1916.6
162.5°	1940.5	1942.8	1945.0	1945.1	1943.1	1941.0	1939.0	1936.9
165°	1965.2	1967.9	1970.6	1970.7	1968.4	1966.1	1963.7	1961.4
167.5°	1984.4	1987.0	1989.7	1989.7	1987.0	1984.4	1981.7	1979.1
170°	1995.1	1997.8	2000.5	2000.5	1997.8	1995.1	1992.5	1989.8
172.5°	2002.3	2005.0	2007.6	2007.5	2004.6	2001.7	1998.7	1995.8
175°	2010.9	2013.2	2015.6	2015.4	2012.7	2010.1	2007.4	2004.8
177.5°	2014.1	2016.2	2018.4	2018.1	2015.4	2012.8	2010.1	2007.5
180°	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2

(END OF REPORT)